

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333738-940

Luminaire Tested: **S125RDIW-S1270D1560U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333738-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9913.1 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333738-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333738-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11889	11889	11889
5°	11916	11780	11852
10°	11825	11671	11671
15°	11685	11433	11340
20°	11504	11103	10970
25°	11294	10779	10541
30°	11032	10399	10068
35°	10764	10008	9536
40°	10514	9599	9014
45°	10209	9143	8444
50°	9904	8647	7850
55°	9549	8172	7218
60°	9195	7596	6536
65°	8775	6927	5757
70°	8295	6090	4962
75°	7633	5133	4127
80°	6721	4032	3466
85°	5669	3298	3090



TEST NUMBER: P333738-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	1.7
10°-20°	483.7	4.9
20°-30°	701.4	7.1
30°-40°	799.4	8.1
40°-50°	779.2	7.9
50°-60°	655.9	6.6
60°-70°	459.8	4.6
70°-80°	236.3	2.4
80°-90°	63.5	0.6
90°-100°	65.8	0.7
100°-110°	405.6	4.1
110°-120°	735.5	7.4
120°-130°	944.0	9.5
130°-140°	1015.3	10.2
140°-150°	953.0	9.6
150°-160°	770.9	7.8
160°-170°	498.6	5.0
170°-180°	172.0	1.7
0°-30°	1358.2	13.7
0°-40°	2157.6	21.8
0°-60°	3592.8	36.2
0°-90°	4352.4	43.9
90°-120°	1206.9	12.2
90°-150°	4119.2	41.6
90°-180°	5561.0	56.1
0°-180°	9913.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1841	1841	1841	1841	1841	
5°	1838	1832	1817	1830	1828	174
15°	1748	1738	1710	1708	1696	492
25°	1585	1562	1513	1495	1479	729
35°	1365	1330	1269	1230	1210	854
45°	1118	1075	1001	947	924	862
55°	848	802	726	665	641	758
65°	574	525	453	400	377	569
75°	306	263	206	176	165	324
85°	76	52	44	43	42	86
90°	1	12	22	28	32	7
95°	76	70	22	28	28	97
105°	395	400	400	400	399	418
115°	741	747	749	744	736	734
125°	1054	1063	1063	1058	1054	941
135°	1314	1322	1320	1316	1309	1013
145°	1524	1526	1526	1527	1520	952
155°	1678	1670	1673	1676	1666	773
165°	1771	1763	1764	1771	1761	500
175°	1811	1803	1804	1814	1803	172
180°	1811	1811	1811	1811	1811	



TEST NUMBER: P333738-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1844.1	1843.3	1842.5	1841.8	1841.1	1839.5	1837.0	1834.5	1832.1	1829.6	1832.1
5°	1838.0	1836.7	1835.5	1834.2	1833.0	1830.7	1827.3	1823.9	1820.5	1817.1	1820.2
7.5°	1819.9	1818.7	1817.6	1816.3	1815.2	1812.6	1808.5	1804.4	1800.4	1796.3	1798.4
10°	1803.2	1802.2	1801.3	1800.5	1799.5	1796.9	1792.5	1788.2	1783.9	1779.6	1780.5
12.5°	1784.3	1783.2	1781.9	1780.7	1779.6	1776.1	1770.3	1764.5	1758.6	1752.8	1753.5
15°	1747.6	1745.7	1743.9	1742.0	1740.2	1736.0	1729.5	1723.1	1716.5	1710.0	1709.8
17.5°	1706.1	1703.3	1700.5	1697.6	1694.8	1689.3	1681.1	1672.9	1664.8	1656.6	1655.1
20°	1673.9	1670.8	1667.7	1664.6	1661.5	1655.0	1645.2	1635.3	1625.4	1615.5	1614.0
22.5°	1638.3	1635.2	1632.1	1629.1	1625.9	1619.3	1608.8	1598.5	1588.0	1577.7	1574.7
25°	1584.9	1580.3	1575.7	1571.0	1566.4	1558.4	1546.9	1535.5	1524.0	1512.6	1508.6
27.5°	1523.8	1518.1	1512.5	1506.9	1501.3	1492.4	1480.1	1467.8	1455.6	1443.4	1437.8
30°	1479.3	1473.4	1467.5	1461.7	1455.8	1446.4	1433.3	1420.4	1407.4	1394.5	1387.3
32.5°	1435.9	1429.1	1422.2	1415.3	1408.5	1398.4	1385.2	1372.0	1358.7	1345.5	1337.7
35°	1365.3	1357.8	1350.4	1343.0	1335.6	1324.9	1311.0	1297.2	1283.3	1269.4	1260.3
37.5°	1296.0	1287.0	1278.0	1269.0	1259.9	1248.2	1233.9	1219.6	1205.2	1190.9	1180.2
40°	1247.1	1237.8	1228.5	1219.2	1210.1	1197.9	1183.1	1168.3	1153.4	1138.6	1126.9
42.5°	1196.0	1186.4	1176.9	1167.3	1157.9	1145.4	1130.2	1114.8	1099.5	1084.1	1072.9
45°	1117.8	1108.8	1099.8	1090.9	1081.9	1069.0	1052.0	1035.0	1018.0	1001.0	988.6
47.5°	1036.9	1027.4	1018.0	1008.5	999.1	985.8	968.7	951.5	934.4	917.3	904.6
50°	985.7	975.5	965.3	955.1	944.9	931.0	913.4	895.8	878.2	860.6	847.6
52.5°	930.1	919.6	909.2	898.8	888.3	874.8	858.2	841.6	824.9	808.3	794.3
55°	848.1	838.2	828.3	818.4	808.5	795.0	777.7	760.4	743.1	725.8	711.9
57.5°	765.2	754.7	744.0	733.5	722.9	709.4	692.7	675.9	659.2	642.6	629.0
60°	711.9	701.0	690.2	679.4	668.6	654.8	638.1	621.4	604.8	588.1	574.5
62.5°	655.1	644.8	634.5	624.1	613.9	600.2	583.3	566.3	549.4	532.4	519.9
65°	574.2	563.7	553.2	542.7	532.2	518.7	502.4	486.0	469.6	453.3	440.9
67.5°	493.8	483.3	472.8	462.4	451.8	438.7	423.0	407.3	391.6	375.9	364.6
70°	439.3	428.8	418.3	407.8	397.3	384.3	368.9	353.5	338.0	322.5	313.0
72.5°	385.9	375.7	365.4	355.2	344.9	332.5	318.1	303.6	289.2	274.7	265.9
75°	305.9	296.6	287.3	278.0	268.8	257.7	244.7	231.8	218.7	205.7	198.9
77.5°	226.3	218.9	211.5	204.1	196.7	187.8	177.4	167.0	156.7	146.2	141.5
80°	180.7	173.3	165.9	158.5	151.1	143.0	134.4	125.7	117.1	108.4	105.7
82.5°	136.3	129.6	122.9	116.2	109.6	103.3	97.3	91.4	85.4	79.5	78.2
85°	76.5	70.9	65.4	59.7	54.2	50.6	49.1	47.6	46.0	44.5	44.1
87.5°	25.9	24.6	23.4	22.1	20.9	20.3	20.5	20.6	20.8	21.0	21.3
90°	1.3	3.7	6.2	8.5	10.9	13.1	15.2	17.3	19.4	21.5	23.0
92.5°	20.7	19.0	17.3	15.7	14.0	14.1	16.0	17.7	19.6	21.5	23.0
95°	76.5	75.6	74.7	73.8	72.9	66.8	55.5	44.1	32.8	21.5	23.0
97.5°	159.7	161.3	162.9	164.6	166.2	155.8	133.3	110.9	88.5	66.1	57.6
100°	224.2	225.1	226.0	226.9	227.7	228.8	230.0	231.2	232.4	233.5	189.1
102.5°	289.7	290.8	291.9	293.1	294.2	295.2	295.9	296.6	297.3	298.0	289.6
105°	394.7	395.8	397.1	398.2	399.4	400.0	400.0	400.0	400.0	400.0	400.0
107.5°	503.6	503.6	503.6	503.6	503.6	503.9	504.5	505.2	505.8	506.3	506.4
110°	574.5	574.5	574.5	574.5	574.5	574.8	575.4	576.0	576.6	577.2	576.3



TEST NUMBER: P333738-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	641.1	641.9	642.6	643.3	644.0	644.5	644.9	645.2	645.6	646.0	644.8
115°	741.0	742.4	744.0	745.5	746.9	747.8	748.1	748.4	748.8	749.0	747.8
117.5°	844.4	844.3	844.2	844.2	844.1	844.6	845.8	846.9	848.0	849.2	847.6
120°	908.7	908.5	908.2	907.9	907.6	907.9	908.7	909.6	910.5	911.4	910.9
122.5°	965.7	966.8	968.0	969.1	970.2	971.0	971.4	971.8	972.2	972.7	972.1
125°	1053.7	1055.8	1057.9	1060.0	1062.1	1063.1	1063.1	1063.1	1063.1	1063.1	1061.9
127.5°	1137.7	1139.2	1140.8	1142.3	1143.7	1144.4	1144.2	1144.1	1143.9	1143.7	1143.0
130°	1189.3	1190.8	1192.3	1193.8	1195.2	1196.1	1196.5	1196.8	1197.0	1197.4	1196.5
132.5°	1240.8	1242.6	1244.3	1246.1	1247.8	1248.3	1247.7	1247.0	1246.3	1245.7	1245.5
135°	1314.1	1315.9	1317.8	1319.6	1321.3	1321.9	1321.3	1320.7	1320.1	1319.6	1318.9
137.5°	1381.5	1383.0	1384.6	1386.2	1387.8	1388.2	1387.7	1387.1	1386.6	1386.1	1386.3
140°	1425.6	1426.2	1426.7	1427.4	1428.0	1428.1	1427.8	1427.5	1427.2	1426.9	1427.5
142.5°	1465.3	1465.6	1466.0	1466.3	1466.7	1467.1	1467.6	1467.9	1468.4	1468.8	1468.9
145°	1523.6	1524.1	1524.7	1525.4	1526.0	1526.3	1526.3	1526.3	1526.3	1526.3	1526.5
147.5°	1574.6	1574.4	1574.3	1574.2	1574.0	1574.2	1574.6	1574.9	1575.3	1575.7	1576.0
150°	1606.8	1606.1	1605.6	1605.0	1604.4	1604.4	1605.0	1605.6	1606.1	1606.8	1607.4
152.5°	1637.9	1636.6	1635.3	1634.0	1632.6	1632.3	1632.9	1633.5	1634.1	1634.7	1635.3
155°	1677.9	1676.1	1674.4	1672.6	1670.8	1670.2	1670.8	1671.3	1672.0	1672.6	1673.5
157.5°	1708.8	1707.7	1706.6	1705.6	1704.5	1704.0	1704.1	1704.1	1704.1	1704.2	1705.2
160°	1730.3	1728.5	1726.7	1724.9	1723.1	1722.3	1722.7	1723.0	1723.2	1723.6	1724.7
162.5°	1747.5	1745.7	1743.9	1742.0	1740.3	1739.5	1739.8	1740.2	1740.4	1740.7	1742.4
165°	1770.6	1768.8	1766.9	1765.1	1763.4	1762.6	1762.9	1763.3	1763.5	1763.8	1765.6
167.5°	1787.7	1785.9	1784.0	1782.2	1780.3	1779.6	1779.9	1780.1	1780.5	1780.7	1782.9
170°	1797.4	1795.3	1793.2	1791.1	1789.0	1788.1	1788.4	1788.8	1789.0	1789.3	1791.7
172.5°	1803.8	1801.8	1799.7	1797.6	1795.5	1794.7	1795.3	1795.8	1796.4	1796.9	1799.0
175°	1810.8	1809.0	1807.2	1805.4	1803.7	1803.0	1803.2	1803.5	1803.8	1804.1	1806.5
177.5°	1814.0	1812.6	1811.2	1809.7	1808.3	1807.7	1807.9	1808.2	1808.4	1808.7	1810.4
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333738-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1834.5	1837.0	1839.5	1840.6	1840.4	1840.1	1839.9	1839.6
5°	1823.3	1826.4	1829.4	1830.7	1830.1	1829.4	1828.8	1828.2
7.5°	1800.5	1802.8	1804.9	1805.6	1804.9	1804.3	1803.6	1803.0
10°	1781.4	1782.4	1783.2	1783.2	1782.4	1781.4	1780.5	1779.6
12.5°	1754.3	1754.9	1755.6	1755.2	1753.8	1752.4	1751.0	1749.5
15°	1709.4	1709.1	1708.8	1707.3	1704.5	1701.7	1698.9	1696.1
17.5°	1653.6	1652.0	1650.5	1648.6	1646.3	1644.0	1641.7	1639.4
20°	1612.4	1610.9	1609.4	1607.1	1604.4	1601.6	1598.8	1596.1
22.5°	1571.6	1568.6	1565.6	1562.9	1560.7	1558.4	1556.0	1553.8
25°	1504.6	1500.6	1496.6	1492.8	1489.4	1486.0	1482.6	1479.3
27.5°	1432.2	1426.6	1420.9	1416.5	1413.2	1409.9	1406.6	1403.4
30°	1380.3	1373.1	1366.0	1361.1	1358.3	1355.5	1352.7	1350.0
32.5°	1329.8	1322.0	1314.1	1308.4	1304.9	1301.4	1297.9	1294.3
35°	1251.4	1242.4	1233.5	1226.8	1222.5	1218.2	1213.9	1209.5
37.5°	1169.4	1158.7	1147.9	1140.4	1136.2	1132.0	1127.8	1123.6
40°	1115.2	1103.4	1091.7	1084.0	1080.2	1076.6	1072.8	1069.2
42.5°	1061.7	1050.4	1039.2	1030.8	1025.4	1019.9	1014.5	1009.1
45°	976.2	963.9	951.5	943.1	938.4	933.8	929.2	924.5
47.5°	891.9	879.1	866.4	857.5	852.3	847.2	842.0	837.0
50°	834.6	821.6	808.7	799.9	795.2	790.6	786.0	781.3
52.5°	780.3	766.4	752.4	743.2	738.5	733.9	729.2	724.6
55°	697.9	684.0	670.1	660.7	655.8	650.8	645.9	641.0
57.5°	615.4	601.8	588.2	579.3	574.8	570.4	566.1	561.7
60°	560.9	547.3	533.7	524.6	520.0	515.3	510.7	506.0
62.5°	507.3	494.6	482.1	473.4	468.8	464.1	459.5	454.9
65°	428.6	416.2	403.8	395.3	390.7	386.0	381.4	376.7
67.5°	353.3	342.0	330.7	323.2	319.5	315.8	312.1	308.4
70°	303.4	293.8	284.3	277.6	273.8	270.2	266.4	262.8
72.5°	257.1	248.3	239.3	233.7	231.2	228.8	226.3	223.8
75°	192.2	185.4	178.6	174.1	171.9	169.8	167.6	165.4
77.5°	136.7	132.0	127.2	124.0	122.4	120.8	119.2	117.6
80°	102.9	100.1	97.3	95.6	95.0	94.3	93.8	93.2
82.5°	77.0	75.6	74.4	73.5	73.1	72.8	72.4	72.1
85°	43.9	43.6	43.2	43.0	42.6	42.4	42.0	41.7
87.5°	21.6	21.8	22.2	22.3	22.2	22.1	22.1	22.0
90°	24.4	25.9	27.5	28.6	29.5	30.4	31.3	32.2
92.5°	24.4	25.9	27.5	28.4	28.8	29.2	29.7	30.1
95°	24.4	25.9	27.5	28.2	28.2	28.2	28.2	28.2
97.5°	49.2	40.8	32.4	28.2	28.2	28.2	28.2	28.2
100°	144.6	100.2	55.8	33.0	31.7	30.6	29.4	28.2
102.5°	281.2	272.8	264.4	250.0	229.7	209.5	189.1	168.9
105°	400.0	400.0	400.0	399.8	399.6	399.3	399.0	398.7
107.5°	506.5	506.5	506.6	506.1	505.2	504.4	503.5	502.6
110°	575.4	574.5	573.6	573.4	573.6	573.9	574.3	574.5



TEST NUMBER: P333738-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	643.6	642.6	641.4	640.6	640.2	639.8	639.4	638.9
115°	746.6	745.5	744.2	742.8	741.0	739.1	737.4	735.6
117.5°	846.1	844.5	842.9	841.8	841.1	840.3	839.5	838.7
120°	910.3	909.6	909.1	908.0	906.5	905.0	903.6	902.1
122.5°	971.4	970.9	970.3	969.1	967.4	965.6	963.9	962.2
125°	1060.8	1059.5	1058.4	1057.3	1056.4	1055.5	1054.6	1053.7
127.5°	1142.4	1141.7	1141.0	1139.6	1137.4	1135.2	1133.0	1130.8
130°	1195.6	1194.7	1193.8	1192.6	1191.1	1189.6	1188.1	1186.6
132.5°	1245.4	1245.2	1245.0	1244.1	1242.7	1241.2	1239.7	1238.1
135°	1318.3	1317.8	1317.1	1315.9	1314.1	1312.3	1310.5	1308.8
137.5°	1386.3	1386.4	1386.6	1385.9	1384.3	1382.8	1381.2	1379.7
140°	1428.1	1428.7	1429.3	1428.7	1426.9	1425.1	1423.3	1421.6
142.5°	1469.0	1469.2	1469.3	1468.5	1466.6	1464.8	1463.0	1461.2
145°	1526.9	1527.1	1527.4	1526.7	1524.9	1523.1	1521.3	1519.6
147.5°	1576.4	1576.7	1577.1	1576.2	1574.0	1571.9	1569.8	1567.6
150°	1607.9	1608.6	1609.2	1608.3	1605.9	1603.5	1601.2	1598.7
152.5°	1635.9	1636.5	1637.1	1636.3	1634.1	1632.0	1629.9	1627.7
155°	1674.4	1675.3	1676.1	1675.3	1673.0	1670.6	1668.2	1665.8
157.5°	1706.1	1707.1	1708.1	1707.4	1705.0	1702.5	1700.1	1697.8
160°	1725.9	1727.2	1728.3	1727.8	1725.4	1723.0	1720.6	1718.2
162.5°	1744.1	1745.8	1747.4	1747.0	1744.4	1741.7	1739.1	1736.4
165°	1767.4	1769.2	1771.0	1770.7	1768.4	1765.9	1763.5	1761.1
167.5°	1785.0	1787.2	1789.3	1789.0	1786.4	1783.7	1781.0	1778.3
170°	1794.1	1796.5	1798.8	1798.8	1796.1	1793.4	1790.6	1788.0
172.5°	1801.2	1803.3	1805.4	1805.2	1802.5	1799.8	1797.2	1794.5
175°	1808.8	1811.2	1813.7	1813.5	1810.8	1808.1	1805.4	1802.8
177.5°	1812.0	1813.7	1815.3	1815.3	1813.3	1811.4	1809.5	1807.6
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8

(END OF REPORT)