

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333655-940

Luminaire Tested: **S125RDIW-S375D1340U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333655-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1340U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5439.8 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333655-940

CATALOG NUMBER: S125RDIW-S375D1340U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333655-940

CATALOG NUMBER: S125RDIW-S375D1340U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23	17
3	76	67	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	15
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3524	3524	3524
5°	3532	3492	3513
10°	3505	3459	3459
15°	3463	3389	3361
20°	3410	3291	3252
25°	3348	3195	3125
30°	3270	3082	2984
35°	3191	2967	2827
40°	3117	2845	2672
45°	3027	2711	2503
50°	2936	2563	2327
55°	2831	2422	2139
60°	2725	2251	1938
65°	2601	2054	1705
70°	2459	1805	1469
75°	2263	1522	1223
80°	1993	1194	1027
85°	1675	978	919



TEST NUMBER: P333655-940

CATALOG NUMBER: S125RDIW-S375D1340U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.3	0.9
10°-20°	143.4	2.6
20°-30°	207.9	3.8
30°-40°	237.0	4.4
40°-50°	231.0	4.2
50°-60°	194.4	3.6
60°-70°	136.3	2.5
70°-80°	70.1	1.3
80°-90°	20.9	0.4
90°-100°	99.5	1.8
100°-110°	294.0	5.4
110°-120°	497.9	9.2
120°-130°	655.3	12.0
130°-140°	734.3	13.5
140°-150°	719.7	13.2
150°-160°	604.5	11.1
160°-170°	401.8	7.4
170°-180°	140.6	2.6
0°-30°	402.6	7.4
0°-40°	639.6	11.8
0°-60°	1065.0	19.6
0°-90°	1292.3	23.8
90°-120°	891.4	16.4
90°-150°	3000.7	55.2
90°-180°	4148.0	76.3
0°-180°	5439.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	546	546	546	546	546	
5°	545	543	539	542	542	52
15°	518	515	507	506	503	146
25°	470	463	448	443	438	216
35°	405	394	376	365	359	253
45°	331	319	297	281	274	256
55°	251	238	215	197	190	225
65°	170	156	134	118	112	169
75°	91	78	61	52	49	96
85°	23	16	13	13	12	25
90°	1	10	18	24	28	5
95°	75	78	89	97	100	80
105°	264	270	276	283	287	282
115°	499	503	506	504	503	493
125°	728	734	736	733	732	651
135°	946	953	954	954	950	729
145°	1146	1151	1154	1154	1151	716
155°	1312	1312	1313	1317	1312	604
165°	1426	1424	1425	1429	1423	402
175°	1483	1479	1478	1484	1477	141
180°	1486	1486	1486	1486	1486	



TEST NUMBER: P333655-940

CATALOG NUMBER: S125RDIW-S375D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	546.6	546.4	546.2	546.0	545.7	545.3	544.6	543.8	543.1	542.3	543.1
5°	544.8	544.5	544.1	543.7	543.3	542.7	541.6	540.6	539.7	538.6	539.6
7.5°	539.5	539.1	538.8	538.4	538.1	537.3	536.1	534.8	533.7	532.4	533.1
10°	534.5	534.2	534.0	533.7	533.4	532.6	531.4	530.0	528.8	527.5	527.8
12.5°	528.9	528.5	528.2	527.9	527.5	526.5	524.8	523.1	521.3	519.6	519.8
15°	518.0	517.5	516.9	516.4	515.9	514.6	512.6	510.8	508.8	506.9	506.8
17.5°	505.8	504.9	504.1	503.2	502.4	500.8	498.3	495.9	493.5	491.1	490.6
20°	496.1	495.3	494.4	493.5	492.5	490.6	487.7	484.7	481.8	478.8	478.4
22.5°	485.6	484.7	483.8	482.9	482.0	480.0	476.9	473.9	470.7	467.7	466.8
25°	469.8	468.4	467.1	465.7	464.3	461.9	458.5	455.1	451.7	448.4	447.2
27.5°	451.7	450.0	448.4	446.7	445.0	442.4	438.7	435.1	431.5	427.8	426.1
30°	438.5	436.8	435.0	433.3	431.5	428.7	424.9	421.1	417.2	413.3	411.3
32.5°	425.6	423.6	421.6	419.5	417.5	414.6	410.6	406.7	402.8	398.9	396.5
35°	404.7	402.5	400.3	398.1	395.9	392.7	388.6	384.5	380.4	376.3	373.6
37.5°	384.1	381.5	378.8	376.1	373.4	370.0	365.8	361.5	357.3	353.0	349.8
40°	369.7	366.9	364.2	361.4	358.6	355.1	350.7	346.3	341.9	337.5	334.0
42.5°	354.5	351.7	348.8	346.1	343.2	339.6	335.0	330.5	325.9	321.4	318.1
45°	331.4	328.7	326.0	323.3	320.7	316.8	311.8	306.8	301.8	296.8	293.0
47.5°	307.4	304.5	301.8	298.9	296.1	292.2	287.1	282.0	277.0	271.9	268.1
50°	292.2	289.2	286.1	283.1	280.1	276.0	270.7	265.6	260.3	255.1	251.3
52.5°	275.7	272.6	269.5	266.4	263.3	259.3	254.4	249.4	244.5	239.6	235.5
55°	251.4	248.4	245.5	242.6	239.7	235.7	230.5	225.3	220.3	215.1	211.0
57.5°	226.9	223.7	220.5	217.4	214.3	210.3	205.3	200.4	195.5	190.5	186.5
60°	211.0	207.8	204.6	201.3	198.1	194.1	189.1	184.2	179.2	174.3	170.3
62.5°	194.2	191.1	188.1	185.0	181.9	177.9	172.9	167.9	162.8	157.8	154.1
65°	170.2	167.1	164.0	160.9	157.7	153.7	148.9	144.1	139.2	134.4	130.7
67.5°	146.4	143.3	140.2	137.1	133.9	130.0	125.4	120.7	116.1	111.5	108.1
70°	130.2	127.2	124.0	120.9	117.8	114.0	109.3	104.8	100.2	95.6	92.7
72.5°	114.4	111.4	108.3	105.3	102.3	98.5	94.3	90.0	85.7	81.4	78.8
75°	90.7	87.9	85.2	82.4	79.7	76.4	72.5	68.7	64.8	61.0	58.9
77.5°	67.1	64.9	62.7	60.5	58.3	55.6	52.6	49.5	46.5	43.3	41.9
80°	53.6	51.4	49.2	47.0	44.8	42.4	39.9	37.3	34.7	32.1	31.3
82.5°	40.4	38.4	36.5	34.4	32.5	30.6	28.9	27.1	25.3	23.5	23.2
85°	22.6	21.0	19.4	17.7	16.1	15.0	14.5	14.1	13.6	13.2	13.1
87.5°	7.8	7.7	7.6	7.5	7.4	7.5	7.8	8.1	8.4	8.6	8.9
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	28.0	29.4	30.9	32.3	33.7	35.6	37.8	40.0	42.2	44.4	46.1
95°	75.2	75.7	76.2	76.7	77.2	78.8	81.3	83.9	86.5	89.1	90.9
97.5°	124.9	125.1	125.4	125.6	125.7	127.6	131.2	134.7	138.3	141.8	143.5
100°	161.9	161.9	161.9	161.9	161.9	163.6	166.9	170.3	173.6	177.0	179.3
102.5°	201.7	202.8	203.8	204.8	205.8	207.2	208.9	210.6	212.3	214.0	216.5
105°	263.8	265.0	266.3	267.6	268.9	270.3	271.8	273.4	274.9	276.4	278.0
107.5°	332.2	333.5	334.7	336.1	337.3	338.6	339.7	340.9	342.1	343.3	344.1
110°	379.4	380.7	382.0	383.3	384.5	385.6	386.4	387.1	387.9	388.6	389.4



TEST NUMBER: P333655-940

CATALOG NUMBER: S125RDIW-S375D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	427.5	428.2	428.8	429.5	430.2	431.1	431.9	432.9	433.9	434.9	435.2
115°	498.6	499.5	500.6	501.6	502.7	503.5	503.9	504.4	505.0	505.5	505.2
117.5°	569.8	570.2	570.7	571.1	571.7	572.1	572.6	573.0	573.5	574.0	574.2
120°	614.2	615.5	616.8	618.0	619.4	620.1	620.4	620.6	620.9	621.2	621.2
122.5°	662.4	662.8	663.3	663.7	664.1	664.8	665.4	666.1	666.7	667.4	667.2
125°	727.5	729.1	730.7	732.2	733.7	734.6	734.9	735.1	735.4	735.7	735.1
127.5°	796.9	797.8	798.7	799.6	800.5	801.0	801.4	801.6	802.0	802.3	802.0
130°	838.6	839.9	841.2	842.5	843.7	844.6	845.2	845.7	846.1	846.7	846.4
132.5°	880.2	882.3	884.5	886.5	888.7	889.7	889.6	889.5	889.4	889.3	889.0
135°	946.2	947.7	949.2	950.8	952.3	953.2	953.5	953.8	954.0	954.3	954.3
137.5°	1008.2	1009.7	1011.2	1012.6	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7
140°	1047.9	1049.3	1050.5	1051.9	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7
142.5°	1087.8	1088.9	1089.9	1091.0	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3
145°	1146.3	1147.3	1148.3	1149.3	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4
147.5°	1200.4	1201.0	1201.6	1202.1	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4
150°	1236.5	1236.3	1236.0	1235.7	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0
152.5°	1266.1	1266.5	1266.9	1267.2	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2
155°	1311.7	1311.7	1311.7	1311.7	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8
157.5°	1352.4	1351.8	1351.3	1350.7	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0
160°	1376.4	1375.7	1374.9	1374.1	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2
162.5°	1397.8	1397.2	1396.6	1396.1	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7
165°	1426.2	1425.7	1425.1	1424.7	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1
167.5°	1450.3	1449.2	1448.2	1447.2	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2
170°	1463.2	1462.2	1461.2	1460.2	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2
172.5°	1472.5	1471.4	1470.4	1469.4	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4
175°	1482.9	1481.8	1480.9	1479.8	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8
177.5°	1488.2	1487.4	1486.6	1485.8	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333655-940

CATALOG NUMBER: S125RDIW-S375D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	543.8	544.6	545.3	545.6	545.5	545.5	545.4	545.3
5°	540.5	541.4	542.2	542.7	542.5	542.2	542.1	541.9
7.5°	533.7	534.4	535.0	535.2	535.0	534.8	534.7	534.4
10°	528.1	528.3	528.6	528.6	528.3	528.1	527.8	527.5
12.5°	520.0	520.2	520.4	520.3	519.9	519.4	519.1	518.6
15°	506.7	506.6	506.5	506.0	505.2	504.4	503.6	502.7
17.5°	490.2	489.7	489.3	488.7	488.0	487.3	486.6	486.0
20°	478.0	477.5	477.1	476.4	475.5	474.7	473.9	473.1
22.5°	465.8	464.9	464.0	463.2	462.6	461.9	461.3	460.6
25°	446.0	444.8	443.6	442.6	441.5	440.5	439.5	438.5
27.5°	424.5	422.8	421.2	419.9	418.9	417.9	417.0	416.0
30°	409.1	407.1	404.9	403.5	402.6	401.8	401.0	400.2
32.5°	394.2	391.9	389.5	387.9	386.8	385.8	384.7	383.7
35°	371.0	368.3	365.6	363.6	362.4	361.1	359.8	358.6
37.5°	346.6	343.5	340.3	338.0	336.8	335.6	334.3	333.1
40°	330.6	327.1	323.6	321.3	320.2	319.1	318.0	316.9
42.5°	314.7	311.4	308.0	305.6	304.0	302.3	300.7	299.1
45°	289.4	285.7	282.0	279.6	278.2	276.8	275.4	274.0
47.5°	264.4	260.6	256.8	254.1	252.6	251.1	249.6	248.1
50°	247.4	243.5	239.7	237.1	235.8	234.3	233.0	231.6
52.5°	231.3	227.2	223.0	220.3	218.9	217.6	216.2	214.8
55°	206.9	202.8	198.7	195.8	194.4	192.9	191.5	190.0
57.5°	182.4	178.4	174.3	171.7	170.4	169.1	167.8	166.5
60°	166.3	162.2	158.2	155.5	154.1	152.8	151.4	150.0
62.5°	150.3	146.6	142.9	140.4	138.9	137.6	136.3	134.8
65°	127.0	123.3	119.7	117.2	115.8	114.4	113.1	111.6
67.5°	104.7	101.4	98.0	95.8	94.7	93.6	92.5	91.4
70°	90.0	87.1	84.3	82.3	81.1	80.1	79.0	77.8
72.5°	76.2	73.6	71.0	69.3	68.6	67.9	67.1	66.3
75°	57.0	54.9	53.0	51.6	51.0	50.3	49.7	49.0
77.5°	40.6	39.1	37.7	36.7	36.3	35.8	35.3	34.9
80°	30.5	29.7	28.9	28.4	28.2	28.0	27.8	27.6
82.5°	22.8	22.4	22.0	21.8	21.7	21.6	21.5	21.3
85°	13.0	12.9	12.8	12.8	12.7	12.6	12.5	12.4
87.5°	9.2	9.5	9.6	9.8	9.9	10.0	10.1	10.2
90°	21.0	22.4	23.6	24.7	25.4	26.2	27.0	27.7
92.5°	47.8	49.5	51.2	52.3	52.9	53.5	54.0	54.6
95°	92.6	94.4	96.3	97.4	97.9	98.4	99.0	99.5
97.5°	145.2	146.9	148.6	149.6	149.9	150.3	150.5	150.9
100°	181.6	183.9	186.2	187.6	188.2	188.7	189.2	189.7
102.5°	219.0	221.5	224.1	225.7	226.4	227.1	227.8	228.5
105°	279.6	281.1	282.6	283.7	284.5	285.3	286.1	286.9
107.5°	344.8	345.6	346.4	346.8	346.7	346.6	346.6	346.5
110°	390.2	390.9	391.7	392.0	391.7	391.5	391.2	390.9





TEST NUMBER: P333655-940

CATALOG NUMBER: S125RDIW-S375D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.6	436.0	436.3	436.3	435.9	435.4	434.9	434.4
115°	505.0	504.7	504.4	504.2	503.9	503.6	503.5	503.2
117.5°	574.4	574.5	574.8	574.4	573.4	572.3	571.3	570.2
120°	621.2	621.2	621.2	620.6	619.6	618.6	617.5	616.5
122.5°	667.0	666.8	666.6	666.1	665.2	664.4	663.6	662.8
125°	734.6	734.1	733.6	733.3	733.0	732.7	732.5	732.2
127.5°	801.7	801.5	801.3	800.8	800.4	799.9	799.3	798.8
130°	846.1	846.0	845.7	845.3	844.8	844.3	843.7	843.2
132.5°	888.8	888.5	888.2	887.8	887.1	886.3	885.6	884.8
135°	954.3	954.3	954.3	953.8	952.7	951.7	950.7	949.7
137.5°	1018.1	1018.3	1018.7	1018.2	1016.9	1015.6	1014.3	1013.1
140°	1058.3	1058.7	1059.3	1058.9	1057.6	1056.3	1055.1	1053.7
142.5°	1097.6	1098.0	1098.2	1097.8	1096.4	1095.2	1093.9	1092.6
145°	1154.4	1154.4	1154.4	1154.0	1153.2	1152.4	1151.6	1150.9
147.5°	1206.9	1207.6	1208.2	1207.6	1205.9	1204.2	1202.4	1200.7
150°	1240.0	1240.0	1240.0	1239.7	1239.2	1238.7	1238.1	1237.7
152.5°	1270.8	1271.4	1272.0	1271.9	1271.0	1270.1	1269.1	1268.2
155°	1314.9	1315.9	1317.0	1316.8	1315.5	1314.3	1313.0	1311.7
157.5°	1353.1	1354.1	1355.1	1354.8	1353.1	1351.4	1349.7	1348.0
160°	1376.2	1377.2	1378.2	1378.1	1376.9	1375.6	1374.3	1373.0
162.5°	1397.9	1399.1	1400.3	1400.3	1398.7	1397.2	1395.8	1394.3
165°	1427.1	1428.2	1429.1	1428.9	1427.4	1425.8	1424.2	1422.7
167.5°	1448.8	1450.3	1451.8	1451.8	1450.2	1448.6	1447.0	1445.4
170°	1461.7	1463.2	1464.7	1464.6	1462.9	1461.1	1459.2	1457.4
172.5°	1471.0	1472.5	1474.0	1474.0	1472.4	1470.8	1469.2	1467.6
175°	1481.3	1482.9	1484.4	1484.3	1482.5	1480.7	1478.9	1477.1
177.5°	1486.0	1487.3	1488.5	1488.4	1486.9	1485.5	1484.1	1482.6
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4

(END OF REPORT)