

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333658-940

Luminaire Tested: **S125RDIW-S375D1560U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333658-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1560U940-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6853.5 lumens  
Efficiency: N/A  
Efficacy: 128.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333658-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333658-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	67	60	54	66	59	53	49	45	41	38	31	29	27	19	18	17	12
4	69	59	51	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	47	39	34	51	41	35	30	32	27	24	23	20	17	14	12	11	8
7	54	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7
8	49	38	31	26	44	34	27	23	26	21	18	19	16	14	12	10	9	6
9	46	34	27	23	40	31	25	20	24	19	16	17	14	12	11	9	8	6
10	43	31	25	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3524	3524	3524
5°	3532	3492	3513
10°	3505	3459	3459
15°	3463	3389	3361
20°	3410	3291	3252
25°	3348	3195	3125
30°	3270	3082	2984
35°	3191	2967	2827
40°	3117	2845	2672
45°	3027	2711	2503
50°	2936	2563	2327
55°	2831	2422	2139
60°	2725	2251	1938
65°	2601	2054	1705
70°	2459	1805	1469
75°	2263	1522	1223
80°	1993	1194	1027
85°	1675	978	919



TEST NUMBER: P333658-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.3	0.7
10°-20°	143.4	2.1
20°-30°	207.9	3.0
30°-40°	237.0	3.5
40°-50°	231.0	3.4
50°-60°	194.4	2.8
60°-70°	136.3	2.0
70°-80°	70.1	1.0
80°-90°	21.5	0.3
90°-100°	65.8	1.0
100°-110°	405.6	5.9
110°-120°	735.5	10.7
120°-130°	944.0	13.8
130°-140°	1015.3	14.8
140°-150°	953.0	13.9
150°-160°	770.9	11.2
160°-170°	498.6	7.3
170°-180°	172.0	2.5
0°-30°	402.6	5.9
0°-40°	639.6	9.3
0°-60°	1065.0	15.5
0°-90°	1292.8	18.9
90°-120°	1206.9	17.6
90°-150°	4119.2	60.1
90°-180°	5561.0	81.1
0°-180°	6853.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	546	546	546	546	546	
5°	545	543	539	542	542	52
15°	518	515	507	506	503	146
25°	470	463	448	443	438	216
35°	405	394	376	365	359	253
45°	331	319	297	281	274	256
55°	251	238	215	197	190	225
65°	170	156	134	118	112	169
75°	91	78	61	52	49	96
85°	23	16	13	13	12	25
90°	1	12	22	28	32	4
95°	76	70	22	28	28	97
105°	395	400	400	400	399	418
115°	741	747	749	744	736	734
125°	1054	1063	1063	1058	1054	941
135°	1314	1322	1320	1316	1309	1013
145°	1524	1526	1526	1527	1520	952
155°	1678	1670	1673	1676	1666	773
165°	1771	1763	1764	1771	1761	500
175°	1811	1803	1804	1814	1803	172
180°	1811	1811	1811	1811	1811	



TEST NUMBER: P333658-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	546.6	546.4	546.2	546.0	545.7	545.3	544.6	543.8	543.1	542.3	543.1
5°	544.8	544.5	544.1	543.7	543.3	542.7	541.6	540.6	539.7	538.6	539.6
7.5°	539.5	539.1	538.8	538.4	538.1	537.3	536.1	534.8	533.7	532.4	533.1
10°	534.5	534.2	534.0	533.7	533.4	532.6	531.4	530.0	528.8	527.5	527.8
12.5°	528.9	528.5	528.2	527.9	527.5	526.5	524.8	523.1	521.3	519.6	519.8
15°	518.0	517.5	516.9	516.4	515.9	514.6	512.6	510.8	508.8	506.9	506.8
17.5°	505.8	504.9	504.1	503.2	502.4	500.8	498.3	495.9	493.5	491.1	490.6
20°	496.1	495.3	494.4	493.5	492.5	490.6	487.7	484.7	481.8	478.8	478.4
22.5°	485.6	484.7	483.8	482.9	482.0	480.0	476.9	473.9	470.7	467.7	466.8
25°	469.8	468.4	467.1	465.7	464.3	461.9	458.5	455.1	451.7	448.4	447.2
27.5°	451.7	450.0	448.4	446.7	445.0	442.4	438.7	435.1	431.5	427.8	426.1
30°	438.5	436.8	435.0	433.3	431.5	428.7	424.9	421.1	417.2	413.3	411.3
32.5°	425.6	423.6	421.6	419.5	417.5	414.6	410.6	406.7	402.8	398.9	396.5
35°	404.7	402.5	400.3	398.1	395.9	392.7	388.6	384.5	380.4	376.3	373.6
37.5°	384.1	381.5	378.8	376.1	373.4	370.0	365.8	361.5	357.3	353.0	349.8
40°	369.7	366.9	364.2	361.4	358.6	355.1	350.7	346.3	341.9	337.5	334.0
42.5°	354.5	351.7	348.8	346.1	343.2	339.6	335.0	330.5	325.9	321.4	318.1
45°	331.4	328.7	326.0	323.3	320.7	316.8	311.8	306.8	301.8	296.8	293.0
47.5°	307.4	304.5	301.8	298.9	296.1	292.2	287.1	282.0	277.0	271.9	268.1
50°	292.2	289.2	286.1	283.1	280.1	276.0	270.7	265.6	260.3	255.1	251.3
52.5°	275.7	272.6	269.5	266.4	263.3	259.3	254.4	249.4	244.5	239.6	235.5
55°	251.4	248.4	245.5	242.6	239.7	235.7	230.5	225.3	220.3	215.1	211.0
57.5°	226.9	223.7	220.5	217.4	214.3	210.3	205.3	200.4	195.5	190.5	186.5
60°	211.0	207.8	204.6	201.3	198.1	194.1	189.1	184.2	179.2	174.3	170.3
62.5°	194.2	191.1	188.1	185.0	181.9	177.9	172.9	167.9	162.8	157.8	154.1
65°	170.2	167.1	164.0	160.9	157.7	153.7	148.9	144.1	139.2	134.4	130.7
67.5°	146.4	143.3	140.2	137.1	133.9	130.0	125.4	120.7	116.1	111.5	108.1
70°	130.2	127.2	124.0	120.9	117.8	114.0	109.3	104.8	100.2	95.6	92.7
72.5°	114.4	111.4	108.3	105.3	102.3	98.5	94.3	90.0	85.7	81.4	78.8
75°	90.7	87.9	85.2	82.4	79.7	76.4	72.5	68.7	64.8	61.0	58.9
77.5°	67.1	64.9	62.7	60.5	58.3	55.6	52.6	49.5	46.5	43.3	41.9
80°	53.6	51.4	49.2	47.0	44.8	42.4	39.9	37.3	34.7	32.1	31.3
82.5°	40.4	38.4	36.5	34.4	32.5	30.6	28.9	27.1	25.3	23.5	23.2
85°	22.6	21.0	19.4	17.7	16.1	15.0	14.5	14.1	13.6	13.2	13.1
87.5°	7.8	7.8	7.8	7.8	7.7	7.8	8.2	8.6	8.9	9.3	9.5
90°	1.3	3.7	6.2	8.5	10.9	13.1	15.2	17.3	19.4	21.5	23.0
92.5°	20.7	19.0	17.3	15.7	14.0	14.1	16.0	17.7	19.6	21.5	23.0
95°	76.5	75.6	74.7	73.8	72.9	66.8	55.5	44.1	32.8	21.5	23.0
97.5°	159.7	161.3	162.9	164.6	166.2	155.8	133.3	110.9	88.5	66.1	57.6
100°	224.2	225.1	226.0	226.9	227.7	228.8	230.0	231.2	232.4	233.5	189.1
102.5°	289.7	290.8	291.9	293.1	294.2	295.2	295.9	296.6	297.3	298.0	289.6
105°	394.7	395.8	397.1	398.2	399.4	400.0	400.0	400.0	400.0	400.0	400.0
107.5°	503.6	503.6	503.6	503.6	503.6	503.9	504.5	505.2	505.8	506.3	506.4
110°	574.5	574.5	574.5	574.5	574.5	574.8	575.4	576.0	576.6	577.2	576.3



TEST NUMBER: P333658-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	641.1	641.9	642.6	643.3	644.0	644.5	644.9	645.2	645.6	646.0	644.8
115°	741.0	742.4	744.0	745.5	746.9	747.8	748.1	748.4	748.8	749.0	747.8
117.5°	844.4	844.3	844.2	844.2	844.1	844.6	845.8	846.9	848.0	849.2	847.6
120°	908.7	908.5	908.2	907.9	907.6	907.9	908.7	909.6	910.5	911.4	910.9
122.5°	965.7	966.8	968.0	969.1	970.2	971.0	971.4	971.8	972.2	972.7	972.1
125°	1053.7	1055.8	1057.9	1060.0	1062.1	1063.1	1063.1	1063.1	1063.1	1063.1	1061.9
127.5°	1137.7	1139.2	1140.8	1142.3	1143.7	1144.4	1144.2	1144.1	1143.9	1143.7	1143.0
130°	1189.3	1190.8	1192.3	1193.8	1195.2	1196.1	1196.5	1196.8	1197.0	1197.4	1196.5
132.5°	1240.8	1242.6	1244.3	1246.1	1247.8	1248.3	1247.7	1247.0	1246.3	1245.7	1245.5
135°	1314.1	1315.9	1317.8	1319.6	1321.3	1321.9	1321.3	1320.7	1320.1	1319.6	1318.9
137.5°	1381.5	1383.0	1384.6	1386.2	1387.8	1388.2	1387.7	1387.1	1386.6	1386.1	1386.3
140°	1425.6	1426.2	1426.7	1427.4	1428.0	1428.1	1427.8	1427.5	1427.2	1426.9	1427.5
142.5°	1465.3	1465.6	1466.0	1466.3	1466.7	1467.1	1467.6	1467.9	1468.4	1468.8	1468.9
145°	1523.6	1524.1	1524.7	1525.4	1526.0	1526.3	1526.3	1526.3	1526.3	1526.3	1526.5
147.5°	1574.6	1574.4	1574.3	1574.2	1574.0	1574.2	1574.6	1574.9	1575.3	1575.7	1576.0
150°	1606.8	1606.1	1605.6	1605.0	1604.4	1604.4	1605.0	1605.6	1606.1	1606.8	1607.4
152.5°	1637.9	1636.6	1635.3	1634.0	1632.6	1632.3	1632.9	1633.5	1634.1	1634.7	1635.3
155°	1677.9	1676.1	1674.4	1672.6	1670.8	1670.2	1670.8	1671.3	1672.0	1672.6	1673.5
157.5°	1708.8	1707.7	1706.6	1705.6	1704.5	1704.0	1704.1	1704.1	1704.1	1704.2	1705.2
160°	1730.3	1728.5	1726.7	1724.9	1723.1	1722.3	1722.7	1723.0	1723.2	1723.6	1724.7
162.5°	1747.5	1745.7	1743.9	1742.0	1740.3	1739.5	1739.8	1740.2	1740.4	1740.7	1742.4
165°	1770.6	1768.8	1766.9	1765.1	1763.4	1762.6	1762.9	1763.3	1763.5	1763.8	1765.6
167.5°	1787.7	1785.9	1784.0	1782.2	1780.3	1779.6	1779.9	1780.1	1780.5	1780.7	1782.9
170°	1797.4	1795.3	1793.2	1791.1	1789.0	1788.1	1788.4	1788.8	1789.0	1789.3	1791.7
172.5°	1803.8	1801.8	1799.7	1797.6	1795.5	1794.7	1795.3	1795.8	1796.4	1796.9	1799.0
175°	1810.8	1809.0	1807.2	1805.4	1803.7	1803.0	1803.2	1803.5	1803.8	1804.1	1806.5
177.5°	1814.0	1812.6	1811.2	1809.7	1808.3	1807.7	1807.9	1808.2	1808.4	1808.7	1810.4
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8



TEST NUMBER: P333658-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	543.8	544.6	545.3	545.6	545.5	545.5	545.4	545.3
5°	540.5	541.4	542.2	542.7	542.5	542.2	542.1	541.9
7.5°	533.7	534.4	535.0	535.2	535.0	534.8	534.7	534.4
10°	528.1	528.3	528.6	528.6	528.3	528.1	527.8	527.5
12.5°	520.0	520.2	520.4	520.3	519.9	519.4	519.1	518.6
15°	506.7	506.6	506.5	506.0	505.2	504.4	503.6	502.7
17.5°	490.2	489.7	489.3	488.7	488.0	487.3	486.6	486.0
20°	478.0	477.5	477.1	476.4	475.5	474.7	473.9	473.1
22.5°	465.8	464.9	464.0	463.2	462.6	461.9	461.3	460.6
25°	446.0	444.8	443.6	442.6	441.5	440.5	439.5	438.5
27.5°	424.5	422.8	421.2	419.9	418.9	417.9	417.0	416.0
30°	409.1	407.1	404.9	403.5	402.6	401.8	401.0	400.2
32.5°	394.2	391.9	389.5	387.9	386.8	385.8	384.7	383.7
35°	371.0	368.3	365.6	363.6	362.4	361.1	359.8	358.6
37.5°	346.6	343.5	340.3	338.0	336.8	335.6	334.3	333.1
40°	330.6	327.1	323.6	321.3	320.2	319.1	318.0	316.9
42.5°	314.7	311.4	308.0	305.6	304.0	302.3	300.7	299.1
45°	289.4	285.7	282.0	279.6	278.2	276.8	275.4	274.0
47.5°	264.4	260.6	256.8	254.1	252.6	251.1	249.6	248.1
50°	247.4	243.5	239.7	237.1	235.8	234.3	233.0	231.6
52.5°	231.3	227.2	223.0	220.3	218.9	217.6	216.2	214.8
55°	206.9	202.8	198.7	195.8	194.4	192.9	191.5	190.0
57.5°	182.4	178.4	174.3	171.7	170.4	169.1	167.8	166.5
60°	166.3	162.2	158.2	155.5	154.1	152.8	151.4	150.0
62.5°	150.3	146.6	142.9	140.4	138.9	137.6	136.3	134.8
65°	127.0	123.3	119.7	117.2	115.8	114.4	113.1	111.6
67.5°	104.7	101.4	98.0	95.8	94.7	93.6	92.5	91.4
70°	90.0	87.1	84.3	82.3	81.1	80.1	79.0	77.8
72.5°	76.2	73.6	71.0	69.3	68.6	67.9	67.1	66.3
75°	57.0	54.9	53.0	51.6	51.0	50.3	49.7	49.0
77.5°	40.6	39.1	37.7	36.7	36.3	35.8	35.3	34.9
80°	30.5	29.7	28.9	28.4	28.2	28.0	27.8	27.6
82.5°	22.8	22.4	22.0	21.8	21.7	21.6	21.5	21.3
85°	13.0	12.9	12.8	12.8	12.7	12.6	12.5	12.4
87.5°	9.8	10.2	10.4	10.6	10.7	10.9	11.0	11.1
90°	24.4	25.9	27.5	28.6	29.5	30.4	31.3	32.2
92.5°	24.4	25.9	27.5	28.4	28.8	29.2	29.7	30.1
95°	24.4	25.9	27.5	28.2	28.2	28.2	28.2	28.2
97.5°	49.2	40.8	32.4	28.2	28.2	28.2	28.2	28.2
100°	144.6	100.2	55.8	33.0	31.7	30.6	29.4	28.2
102.5°	281.2	272.8	264.4	250.0	229.7	209.5	189.1	168.9
105°	400.0	400.0	400.0	399.8	399.6	399.3	399.0	398.7
107.5°	506.5	506.5	506.6	506.1	505.2	504.4	503.5	502.6
110°	575.4	574.5	573.6	573.4	573.6	573.9	574.3	574.5





TEST NUMBER: P333658-940

CATALOG NUMBER: S125RDIW-S375D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	643.6	642.6	641.4	640.6	640.2	639.8	639.4	638.9
115°	746.6	745.5	744.2	742.8	741.0	739.1	737.4	735.6
117.5°	846.1	844.5	842.9	841.8	841.1	840.3	839.5	838.7
120°	910.3	909.6	909.1	908.0	906.5	905.0	903.6	902.1
122.5°	971.4	970.9	970.3	969.1	967.4	965.6	963.9	962.2
125°	1060.8	1059.5	1058.4	1057.3	1056.4	1055.5	1054.6	1053.7
127.5°	1142.4	1141.7	1141.0	1139.6	1137.4	1135.2	1133.0	1130.8
130°	1195.6	1194.7	1193.8	1192.6	1191.1	1189.6	1188.1	1186.6
132.5°	1245.4	1245.2	1245.0	1244.1	1242.7	1241.2	1239.7	1238.1
135°	1318.3	1317.8	1317.1	1315.9	1314.1	1312.3	1310.5	1308.8
137.5°	1386.3	1386.4	1386.6	1385.9	1384.3	1382.8	1381.2	1379.7
140°	1428.1	1428.7	1429.3	1428.7	1426.9	1425.1	1423.3	1421.6
142.5°	1469.0	1469.2	1469.3	1468.5	1466.6	1464.8	1463.0	1461.2
145°	1526.9	1527.1	1527.4	1526.7	1524.9	1523.1	1521.3	1519.6
147.5°	1576.4	1576.7	1577.1	1576.2	1574.0	1571.9	1569.8	1567.6
150°	1607.9	1608.6	1609.2	1608.3	1605.9	1603.5	1601.2	1598.7
152.5°	1635.9	1636.5	1637.1	1636.3	1634.1	1632.0	1629.9	1627.7
155°	1674.4	1675.3	1676.1	1675.3	1673.0	1670.6	1668.2	1665.8
157.5°	1706.1	1707.1	1708.1	1707.4	1705.0	1702.5	1700.1	1697.8
160°	1725.9	1727.2	1728.3	1727.8	1725.4	1723.0	1720.6	1718.2
162.5°	1744.1	1745.8	1747.4	1747.0	1744.4	1741.7	1739.1	1736.4
165°	1767.4	1769.2	1771.0	1770.7	1768.4	1765.9	1763.5	1761.1
167.5°	1785.0	1787.2	1789.3	1789.0	1786.4	1783.7	1781.0	1778.3
170°	1794.1	1796.5	1798.8	1798.8	1796.1	1793.4	1790.6	1788.0
172.5°	1801.2	1803.3	1805.4	1805.2	1802.5	1799.8	1797.2	1794.5
175°	1808.8	1811.2	1813.7	1813.5	1810.8	1808.1	1805.4	1802.8
177.5°	1812.0	1813.7	1815.3	1815.3	1813.3	1811.4	1809.5	1807.6
180°	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8	1810.8

(END OF REPORT)