

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333441-840

Luminaire Tested: **S125DIW-S1090D770U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333441-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D770U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7174.2 lumens  
Efficiency: N/A  
Efficacy: 133.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333441-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333441-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	34	31
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	24	21
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19
10	48	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333441-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	2.3
10°-20°	459.0	6.4
20°-30°	677.7	9.4
30°-40°	790.7	11.0
40°-50°	794.2	11.1
50°-60°	697.1	9.7
60°-70°	519.5	7.2
70°-80°	297.0	4.1
80°-90°	88.5	1.2
90°-100°	64.5	0.9
100°-110°	190.5	2.7
110°-120°	322.7	4.5
120°-130°	424.7	5.9
130°-140°	475.9	6.6
140°-150°	466.4	6.5
150°-160°	391.7	5.5
160°-170°	260.4	3.6
170°-180°	91.1	1.3
0°-30°	1299.1	18.1
0°-40°	2089.8	29.1
0°-60°	3581.2	49.9
0°-90°	4486.1	62.5
90°-120°	577.8	8.1
90°-150°	1944.8	27.1
90°-180°	2688.0	37.5
0°-180°	7174.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	1	7	12	16	18	7
95°	49	51	58	63	64	52
105°	171	175	179	184	186	183
115°	323	326	328	327	326	319
125°	472	476	477	475	474	422
135°	613	618	618	618	616	472
145°	743	746	748	748	746	464
155°	850	850	851	853	850	391
165°	924	923	924	926	922	261
175°	961	958	958	962	957	91
180°	963	963	963	963	963	



TEST NUMBER: P333441-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.6	29.9	30.1	30.4	30.7	30.8	30.8	30.8	30.8	30.8	30.9
90°	0.7	2.1	3.4	4.7	6.1	7.4	8.5	9.7	10.8	12.0	12.8
92.5°	18.2	19.1	20.0	20.9	21.9	23.0	24.5	26.0	27.4	28.8	29.9
95°	48.8	49.1	49.4	49.7	50.1	51.1	52.7	54.4	56.0	57.8	58.9
97.5°	81.0	81.1	81.2	81.4	81.5	82.7	85.0	87.4	89.6	91.9	93.0
100°	104.9	104.9	104.9	104.9	104.9	106.0	108.2	110.4	112.5	114.7	116.2
102.5°	130.8	131.4	132.1	132.7	133.4	134.3	135.4	136.5	137.5	138.7	140.4
105°	171.0	171.8	172.6	173.4	174.3	175.2	176.2	177.1	178.1	179.2	180.2
107.5°	215.3	216.1	217.0	217.8	218.6	219.4	220.3	221.0	221.8	222.5	223.0
110°	245.9	246.7	247.5	248.4	249.2	249.8	250.3	250.9	251.4	251.9	252.4



TEST NUMBER: P333441-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.1	277.5	277.9	278.4	278.8	279.3	279.9	280.6	281.2	281.9	282.2
115°	323.2	323.8	324.5	325.1	325.8	326.3	326.6	326.9	327.3	327.6	327.4
117.5°	369.3	369.6	369.9	370.2	370.5	370.8	371.1	371.4	371.7	372.0	372.1
120°	398.1	398.9	399.7	400.6	401.4	401.9	402.0	402.2	402.4	402.5	402.5
122.5°	429.3	429.6	429.9	430.2	430.5	430.8	431.2	431.7	432.1	432.5	432.4
125°	471.5	472.5	473.5	474.5	475.5	476.2	476.3	476.5	476.7	476.8	476.5
127.5°	516.5	517.1	517.7	518.3	518.8	519.2	519.4	519.6	519.8	520.0	519.8
130°	543.5	544.3	545.2	546.0	546.8	547.4	547.8	548.1	548.5	548.8	548.6
132.5°	570.5	571.9	573.2	574.6	575.9	576.6	576.5	576.4	576.4	576.3	576.2
135°	613.2	614.2	615.2	616.2	617.2	617.8	617.9	618.1	618.3	618.4	618.4
137.5°	653.4	654.4	655.3	656.3	657.3	657.9	658.3	658.6	659.0	659.4	659.6
140°	679.2	680.0	680.9	681.7	682.6	683.2	683.7	684.2	684.7	685.2	685.5
142.5°	705.0	705.7	706.4	707.1	707.8	708.4	709.1	709.7	710.3	710.9	711.1
145°	743.0	743.6	744.3	744.9	745.6	746.2	746.7	747.2	747.7	748.2	748.2
147.5°	778.0	778.4	778.7	779.1	779.5	779.8	780.2	780.6	781.0	781.4	781.8
150°	801.4	801.2	801.0	800.9	800.7	801.0	801.6	802.3	802.9	803.7	803.7
152.5°	820.6	820.8	821.0	821.3	821.5	821.7	822.0	822.3	822.5	822.8	823.2
155°	850.1	850.1	850.1	850.1	850.1	850.2	850.4	850.5	850.7	850.9	851.5
157.5°	876.6	876.2	875.8	875.5	875.0	874.9	875.1	875.3	875.5	875.7	876.3
160°	892.1	891.6	891.1	890.6	890.1	889.9	890.1	890.3	890.4	890.6	891.3
162.5°	905.9	905.5	905.1	904.8	904.4	904.2	904.3	904.3	904.3	904.4	905.2
165°	924.3	924.0	923.7	923.3	923.0	922.9	923.1	923.2	923.4	923.6	924.2
167.5°	940.0	939.3	938.6	938.0	937.3	937.0	937.0	937.0	937.0	937.0	938.0
170°	948.4	947.7	947.0	946.3	945.6	945.3	945.3	945.3	945.3	945.3	946.3
172.5°	954.3	953.6	953.0	952.3	951.7	951.3	951.3	951.3	951.3	951.3	952.3
175°	961.1	960.4	959.8	959.1	958.4	958.1	958.1	958.1	958.1	958.1	959.1
177.5°	964.5	964.0	963.4	962.9	962.4	962.1	961.9	961.8	961.7	961.5	962.3
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333441-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	31.1	31.2	31.4	31.3	30.9	30.5	30.2	29.8
90°	13.6	14.5	15.3	16.0	16.5	17.0	17.5	18.0
92.5°	31.0	32.1	33.2	33.9	34.3	34.6	35.0	35.3
95°	60.1	61.2	62.4	63.1	63.5	63.8	64.1	64.4
97.5°	94.1	95.2	96.3	96.9	97.1	97.4	97.6	97.8
100°	117.6	119.2	120.7	121.6	122.0	122.3	122.6	122.9
102.5°	142.0	143.6	145.2	146.2	146.7	147.2	147.6	148.1
105°	181.2	182.2	183.2	183.9	184.4	184.9	185.4	185.9
107.5°	223.5	224.0	224.5	224.7	224.7	224.7	224.6	224.6
110°	252.9	253.4	253.9	254.1	253.9	253.7	253.6	253.4





TEST NUMBER: P333441-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	282.4	282.6	282.8	282.8	282.5	282.2	281.9	281.6
115°	327.3	327.1	326.9	326.8	326.6	326.5	326.3	326.1
117.5°	372.2	372.3	372.5	372.2	371.6	370.9	370.2	369.6
120°	402.5	402.5	402.5	402.2	401.6	400.9	400.2	399.6
122.5°	432.3	432.1	432.0	431.7	431.1	430.6	430.1	429.6
125°	476.2	475.7	475.4	475.2	475.0	474.8	474.7	474.5
127.5°	519.7	519.5	519.3	519.1	518.8	518.4	518.1	517.8
130°	548.5	548.3	548.1	547.9	547.5	547.1	546.8	546.5
132.5°	576.0	575.8	575.7	575.3	574.9	574.4	574.0	573.5
135°	618.4	618.4	618.4	618.1	617.4	616.8	616.1	615.5
137.5°	659.8	660.0	660.2	659.8	659.0	658.2	657.4	656.5
140°	685.9	686.2	686.5	686.3	685.5	684.6	683.8	683.0
142.5°	711.3	711.6	711.8	711.4	710.6	709.8	708.9	708.1
145°	748.2	748.2	748.2	747.9	747.4	746.9	746.4	745.9
147.5°	782.2	782.6	783.0	782.6	781.5	780.4	779.3	778.2
150°	803.7	803.7	803.7	803.4	803.1	802.8	802.4	802.1
152.5°	823.6	824.0	824.5	824.4	823.7	823.1	822.5	821.9
155°	852.2	852.8	853.5	853.4	852.6	851.8	850.9	850.1
157.5°	877.0	877.6	878.3	878.1	877.0	875.9	874.7	873.6
160°	891.9	892.6	893.2	893.2	892.3	891.5	890.7	889.9
162.5°	906.1	906.8	907.6	907.6	906.6	905.5	904.6	903.6
165°	924.9	925.6	926.2	926.0	925.1	924.1	923.1	922.1
167.5°	939.0	940.0	940.9	940.9	939.9	938.9	937.9	936.8
170°	947.4	948.4	949.4	949.3	948.1	947.0	945.7	944.6
172.5°	953.3	954.3	955.3	955.3	954.3	953.2	952.2	951.2
175°	960.1	961.1	962.1	962.0	960.8	959.7	958.5	957.4
177.5°	963.1	963.9	964.7	964.6	963.7	962.8	961.9	960.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3

(END OF REPORT)