

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333647-940

Luminaire Tested: **S125RDIW-S375D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333647-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D770U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3664.5 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333647-940

CATALOG NUMBER: S125RDIW-S375D770U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333647-940

CATALOG NUMBER: S125RDIW-S375D770U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	49	44	46	41	37	36	32	30	27	24	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3524	3524	3524
5°	3532	3492	3513
10°	3505	3459	3459
15°	3463	3389	3361
20°	3410	3291	3252
25°	3348	3195	3125
30°	3270	3082	2984
35°	3191	2967	2827
40°	3117	2845	2672
45°	3027	2711	2503
50°	2936	2563	2327
55°	2831	2422	2139
60°	2725	2251	1938
65°	2601	2054	1705
70°	2459	1805	1469
75°	2263	1522	1223
80°	1993	1194	1027
85°	1675	978	919



TEST NUMBER: P333647-940

CATALOG NUMBER: S125RDIW-S375D770U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	1.4
10°-20°	143.4	3.9
20°-30°	207.9	5.7
30°-40°	237.0	6.5
40°-50°	231.0	6.3
50°-60°	194.4	5.3
60°-70°	136.3	3.7
70°-80°	70.1	1.9
80°-90°	19.6	0.5
90°-100°	57.0	1.6
100°-110°	168.2	4.6
110°-120°	285.0	7.8
120°-130°	375.0	10.2
130°-140°	420.2	11.5
140°-150°	411.8	11.2
150°-160°	345.9	9.4
160°-170°	229.9	6.3
170°-180°	80.5	2.2
0°-30°	402.6	11.0
0°-40°	639.6	17.5
0°-60°	1065.0	29.1
0°-90°	1290.9	35.2
90°-120°	510.2	13.9
90°-150°	1717.2	46.9
90°-180°	2374.0	64.8
0°-180°	3664.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	546	546	546	546	546	
5°	545	543	539	542	542	52
15°	518	515	507	506	503	146
25°	470	463	448	443	438	216
35°	405	394	376	365	359	253
45°	331	319	297	281	274	256
55°	251	238	215	197	190	225
65°	170	156	134	118	112	169
75°	91	78	61	52	49	96
85°	23	16	13	13	12	25
90°	1	6	11	14	16	3
95°	43	45	51	55	57	46
105°	151	154	158	162	164	161
115°	285	288	289	289	288	282
125°	416	420	421	420	419	373
135°	541	545	546	546	544	417
145°	656	659	661	661	659	410
155°	751	751	751	754	751	346
165°	816	815	816	818	814	230
175°	849	846	846	849	845	81
180°	851	851	851	851	851	



TEST NUMBER: P333647-940

CATALOG NUMBER: S125RDIW-S375D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	546.6	546.4	546.2	546.0	545.7	545.3	544.6	543.8	543.1	542.3	543.1
5°	544.8	544.5	544.1	543.7	543.3	542.7	541.6	540.6	539.7	538.6	539.6
7.5°	539.5	539.1	538.8	538.4	538.1	537.3	536.1	534.8	533.7	532.4	533.1
10°	534.5	534.2	534.0	533.7	533.4	532.6	531.4	530.0	528.8	527.5	527.8
12.5°	528.9	528.5	528.2	527.9	527.5	526.5	524.8	523.1	521.3	519.6	519.8
15°	518.0	517.5	516.9	516.4	515.9	514.6	512.6	510.8	508.8	506.9	506.8
17.5°	505.8	504.9	504.1	503.2	502.4	500.8	498.3	495.9	493.5	491.1	490.6
20°	496.1	495.3	494.4	493.5	492.5	490.6	487.7	484.7	481.8	478.8	478.4
22.5°	485.6	484.7	483.8	482.9	482.0	480.0	476.9	473.9	470.7	467.7	466.8
25°	469.8	468.4	467.1	465.7	464.3	461.9	458.5	455.1	451.7	448.4	447.2
27.5°	451.7	450.0	448.4	446.7	445.0	442.4	438.7	435.1	431.5	427.8	426.1
30°	438.5	436.8	435.0	433.3	431.5	428.7	424.9	421.1	417.2	413.3	411.3
32.5°	425.6	423.6	421.6	419.5	417.5	414.6	410.6	406.7	402.8	398.9	396.5
35°	404.7	402.5	400.3	398.1	395.9	392.7	388.6	384.5	380.4	376.3	373.6
37.5°	384.1	381.5	378.8	376.1	373.4	370.0	365.8	361.5	357.3	353.0	349.8
40°	369.7	366.9	364.2	361.4	358.6	355.1	350.7	346.3	341.9	337.5	334.0
42.5°	354.5	351.7	348.8	346.1	343.2	339.6	335.0	330.5	325.9	321.4	318.1
45°	331.4	328.7	326.0	323.3	320.7	316.8	311.8	306.8	301.8	296.8	293.0
47.5°	307.4	304.5	301.8	298.9	296.1	292.2	287.1	282.0	277.0	271.9	268.1
50°	292.2	289.2	286.1	283.1	280.1	276.0	270.7	265.6	260.3	255.1	251.3
52.5°	275.7	272.6	269.5	266.4	263.3	259.3	254.4	249.4	244.5	239.6	235.5
55°	251.4	248.4	245.5	242.6	239.7	235.7	230.5	225.3	220.3	215.1	211.0
57.5°	226.9	223.7	220.5	217.4	214.3	210.3	205.3	200.4	195.5	190.5	186.5
60°	211.0	207.8	204.6	201.3	198.1	194.1	189.1	184.2	179.2	174.3	170.3
62.5°	194.2	191.1	188.1	185.0	181.9	177.9	172.9	167.9	162.8	157.8	154.1
65°	170.2	167.1	164.0	160.9	157.7	153.7	148.9	144.1	139.2	134.4	130.7
67.5°	146.4	143.3	140.2	137.1	133.9	130.0	125.4	120.7	116.1	111.5	108.1
70°	130.2	127.2	124.0	120.9	117.8	114.0	109.3	104.8	100.2	95.6	92.7
72.5°	114.4	111.4	108.3	105.3	102.3	98.5	94.3	90.0	85.7	81.4	78.8
75°	90.7	87.9	85.2	82.4	79.7	76.4	72.5	68.7	64.8	61.0	58.9
77.5°	67.1	64.9	62.7	60.5	58.3	55.6	52.6	49.5	46.5	43.3	41.9
80°	53.6	51.4	49.2	47.0	44.8	42.4	39.9	37.3	34.7	32.1	31.3
82.5°	40.4	38.4	36.5	34.4	32.5	30.6	28.9	27.1	25.3	23.5	23.2
85°	22.6	21.0	19.4	17.7	16.1	15.0	14.5	14.1	13.6	13.2	13.1
87.5°	7.8	7.4	7.1	6.9	6.6	6.5	6.7	6.8	7.0	7.0	7.2
90°	0.6	1.9	3.0	4.2	5.4	6.5	7.5	8.6	9.5	10.6	11.3
92.5°	16.1	16.9	17.7	18.5	19.4	20.3	21.7	22.9	24.2	25.4	26.4
95°	43.1	43.3	43.6	43.9	44.2	45.1	46.5	48.1	49.5	51.0	52.0
97.5°	71.5	71.6	71.7	71.9	72.0	73.0	75.1	77.1	79.1	81.1	82.1
100°	92.6	92.6	92.6	92.6	92.6	93.6	95.5	97.5	99.3	101.3	102.6
102.5°	115.5	116.0	116.6	117.2	117.8	118.6	119.6	120.6	121.5	122.4	123.9
105°	151.0	151.7	152.4	153.1	153.9	154.7	155.6	156.4	157.3	158.2	159.1
107.5°	190.1	190.8	191.6	192.3	193.1	193.8	194.5	195.1	195.8	196.4	196.9
110°	217.1	217.8	218.6	219.4	220.1	220.6	221.1	221.5	221.9	222.4	222.8



TEST NUMBER: P333647-940

CATALOG NUMBER: S125RDIW-S375D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	244.7	245.0	245.4	245.8	246.2	246.6	247.2	247.8	248.3	248.9	249.1
115°	285.3	285.9	286.5	287.0	287.7	288.1	288.4	288.6	289.0	289.3	289.1
117.5°	326.1	326.4	326.6	326.9	327.2	327.4	327.7	328.0	328.2	328.5	328.6
120°	351.5	352.2	352.9	353.7	354.5	354.9	355.0	355.2	355.3	355.4	355.4
122.5°	379.1	379.3	379.6	379.9	380.1	380.4	380.8	381.2	381.6	381.9	381.8
125°	416.3	417.2	418.1	419.0	419.9	420.4	420.5	420.7	420.9	421.0	420.7
127.5°	456.1	456.6	457.1	457.6	458.1	458.4	458.6	458.8	459.0	459.1	459.0
130°	479.9	480.6	481.4	482.1	482.9	483.4	483.7	483.9	484.3	484.6	484.4
132.5°	503.7	505.0	506.1	507.4	508.5	509.2	509.1	509.0	509.0	508.9	508.8
135°	541.4	542.3	543.2	544.1	545.0	545.5	545.6	545.8	546.0	546.1	546.1
137.5°	576.9	577.8	578.6	579.5	580.4	580.9	581.3	581.6	581.9	582.3	582.5
140°	599.8	600.5	601.2	601.9	602.7	603.2	603.7	604.1	604.6	605.0	605.3
142.5°	622.5	623.1	623.8	624.4	625.0	625.5	626.2	626.7	627.2	627.8	627.9
145°	656.0	656.6	657.2	657.7	658.4	658.9	659.3	659.8	660.2	660.7	660.7
147.5°	687.0	687.3	687.6	688.0	688.3	688.6	688.9	689.3	689.6	690.0	690.4
150°	707.7	707.5	707.3	707.2	707.0	707.3	707.8	708.5	709.0	709.6	709.6
152.5°	724.6	724.8	725.0	725.2	725.4	725.6	725.9	726.1	726.3	726.6	726.9
155°	750.6	750.6	750.6	750.6	750.6	750.7	750.9	751.0	751.2	751.4	751.9
157.5°	774.0	773.6	773.3	773.0	772.7	772.6	772.8	772.8	773.0	773.2	773.7
160°	787.7	787.3	786.8	786.4	786.0	785.8	786.0	786.1	786.2	786.4	787.0
162.5°	800.0	799.6	799.2	799.0	798.6	798.4	798.5	798.5	798.5	798.6	799.3
165°	816.2	815.9	815.6	815.3	815.0	814.9	815.1	815.2	815.4	815.6	816.1
167.5°	830.0	829.4	828.8	828.2	827.6	827.3	827.3	827.3	827.3	827.3	828.2
170°	837.4	836.8	836.2	835.6	835.0	834.7	834.7	834.7	834.7	834.7	835.6
172.5°	842.7	842.0	841.5	840.9	840.3	840.0	840.0	840.0	840.0	840.0	840.9
175°	848.6	848.0	847.5	846.9	846.2	846.0	846.0	846.0	846.0	846.0	846.9
177.5°	851.7	851.2	850.7	850.2	849.8	849.5	849.4	849.3	849.2	849.0	849.7
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333647-940

CATALOG NUMBER: S125RDIW-S375D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	543.8	544.6	545.3	545.6	545.5	545.5	545.4	545.3
5°	540.5	541.4	542.2	542.7	542.5	542.2	542.1	541.9
7.5°	533.7	534.4	535.0	535.2	535.0	534.8	534.7	534.4
10°	528.1	528.3	528.6	528.6	528.3	528.1	527.8	527.5
12.5°	520.0	520.2	520.4	520.3	519.9	519.4	519.1	518.6
15°	506.7	506.6	506.5	506.0	505.2	504.4	503.6	502.7
17.5°	490.2	489.7	489.3	488.7	488.0	487.3	486.6	486.0
20°	478.0	477.5	477.1	476.4	475.5	474.7	473.9	473.1
22.5°	465.8	464.9	464.0	463.2	462.6	461.9	461.3	460.6
25°	446.0	444.8	443.6	442.6	441.5	440.5	439.5	438.5
27.5°	424.5	422.8	421.2	419.9	418.9	417.9	417.0	416.0
30°	409.1	407.1	404.9	403.5	402.6	401.8	401.0	400.2
32.5°	394.2	391.9	389.5	387.9	386.8	385.8	384.7	383.7
35°	371.0	368.3	365.6	363.6	362.4	361.1	359.8	358.6
37.5°	346.6	343.5	340.3	338.0	336.8	335.6	334.3	333.1
40°	330.6	327.1	323.6	321.3	320.2	319.1	318.0	316.9
42.5°	314.7	311.4	308.0	305.6	304.0	302.3	300.7	299.1
45°	289.4	285.7	282.0	279.6	278.2	276.8	275.4	274.0
47.5°	264.4	260.6	256.8	254.1	252.6	251.1	249.6	248.1
50°	247.4	243.5	239.7	237.1	235.8	234.3	233.0	231.6
52.5°	231.3	227.2	223.0	220.3	218.9	217.6	216.2	214.8
55°	206.9	202.8	198.7	195.8	194.4	192.9	191.5	190.0
57.5°	182.4	178.4	174.3	171.7	170.4	169.1	167.8	166.5
60°	166.3	162.2	158.2	155.5	154.1	152.8	151.4	150.0
62.5°	150.3	146.6	142.9	140.4	138.9	137.6	136.3	134.8
65°	127.0	123.3	119.7	117.2	115.8	114.4	113.1	111.6
67.5°	104.7	101.4	98.0	95.8	94.7	93.6	92.5	91.4
70°	90.0	87.1	84.3	82.3	81.1	80.1	79.0	77.8
72.5°	76.2	73.6	71.0	69.3	68.6	67.9	67.1	66.3
75°	57.0	54.9	53.0	51.6	51.0	50.3	49.7	49.0
77.5°	40.6	39.1	37.7	36.7	36.3	35.8	35.3	34.9
80°	30.5	29.7	28.9	28.4	28.2	28.0	27.8	27.6
82.5°	22.8	22.4	22.0	21.8	21.7	21.6	21.5	21.3
85°	13.0	12.9	12.8	12.8	12.7	12.6	12.5	12.4
87.5°	7.4	7.5	7.7	7.8	7.8	7.8	7.8	7.8
90°	12.0	12.8	13.6	14.1	14.5	15.0	15.4	15.9
92.5°	27.4	28.4	29.3	30.0	30.3	30.6	30.9	31.2
95°	53.1	54.0	55.1	55.7	56.1	56.4	56.6	56.9
97.5°	83.1	84.1	85.1	85.6	85.8	86.0	86.1	86.3
100°	103.9	105.2	106.6	107.4	107.7	108.0	108.3	108.5
102.5°	125.4	126.8	128.2	129.1	129.6	130.0	130.4	130.8
105°	160.0	160.9	161.8	162.4	162.8	163.3	163.7	164.2
107.5°	197.3	197.8	198.2	198.4	198.4	198.4	198.3	198.3
110°	223.3	223.7	224.2	224.4	224.2	224.0	223.9	223.7



TEST NUMBER: P333647-940

CATALOG NUMBER: S125RDIW-S375D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.3	249.5	249.7	249.7	249.4	249.1	248.9	248.6
115°	289.0	288.8	288.6	288.6	288.4	288.3	288.1	287.9
117.5°	328.7	328.8	329.0	328.7	328.1	327.5	326.9	326.4
120°	355.4	355.4	355.4	355.2	354.6	354.0	353.4	352.8
122.5°	381.7	381.6	381.5	381.2	380.7	380.2	379.8	379.3
125°	420.4	420.1	419.8	419.6	419.5	419.3	419.2	419.0
127.5°	458.9	458.7	458.5	458.3	458.1	457.7	457.4	457.2
130°	484.3	484.1	483.9	483.8	483.5	483.1	482.9	482.6
132.5°	508.6	508.5	508.4	508.0	507.7	507.2	506.8	506.4
135°	546.1	546.1	546.1	545.8	545.2	544.7	544.0	543.5
137.5°	582.6	582.8	583.0	582.6	581.9	581.2	580.5	579.7
140°	605.6	605.9	606.2	606.0	605.3	604.5	603.8	603.1
142.5°	628.1	628.3	628.5	628.2	627.5	626.8	626.0	625.3
145°	660.7	660.7	660.7	660.4	660.0	659.5	659.1	658.6
147.5°	690.7	691.1	691.4	691.1	690.1	689.1	688.1	687.2
150°	709.6	709.6	709.6	709.4	709.2	708.9	708.6	708.3
152.5°	727.3	727.6	728.0	727.9	727.4	726.8	726.3	725.8
155°	752.5	753.0	753.7	753.6	752.9	752.2	751.4	750.6
157.5°	774.4	774.9	775.5	775.3	774.4	773.4	772.4	771.4
160°	787.6	788.2	788.7	788.7	787.9	787.2	786.5	785.8
162.5°	800.0	800.7	801.4	801.4	800.5	799.6	798.8	797.9
165°	816.7	817.3	817.9	817.7	816.9	816.0	815.1	814.2
167.5°	829.1	830.0	830.8	830.8	829.9	829.0	828.1	827.2
170°	836.5	837.4	838.3	838.2	837.1	836.2	835.1	834.1
172.5°	841.8	842.7	843.6	843.6	842.7	841.7	840.8	839.9
175°	847.7	848.6	849.5	849.4	848.4	847.4	846.3	845.3
177.5°	850.4	851.1	851.9	851.8	851.0	850.2	849.4	848.5
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6

(END OF REPORT)