

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333672-940

Luminaire Tested: **S125RDIW-S610D1340U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333672-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1340U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6923.8 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	27
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	26	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	12
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5329	5329	5329	5329
5°	6131	5336	4713	5336
10°	7033	5309	4158	5309
15°	7596	5255	3697	5255
20°	8377	5192	3413	5192
25°	9694	5108	3167	5108
30°	10549	5020	3006	5020
35°	8898	4917	2858	4917
40°	6214	4731	2731	4731
45°	4610	4483	2606	4483
50°	3676	4224	2498	4224
55°	3120	3902	2403	3902
60°	2696	3614	2250	3614
65°	2402	3304	1936	3304
70°	2111	3025	1766	3025
75°	1827	2620	1657	2620
80°	1387	2205	1387	2205
85°	1156	1734	1312	1734



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.1
10°-20°	231.9	3.3
20°-30°	367.7	5.3
30°-40°	443.4	6.4
40°-50°	396.0	5.7
50°-60°	303.6	4.4
60°-70°	197.3	2.9
70°-80°	95.9	1.4
80°-90°	26.1	0.4
90°-100°	56.6	0.8
100°-110°	348.8	5.0
110°-120°	632.6	9.1
120°-130°	811.9	11.7
130°-140°	873.3	12.6
140°-150°	819.7	11.8
150°-160°	663.1	9.6
160°-170°	428.8	6.2
170°-180°	147.9	2.1
0°-30°	678.7	9.8
0°-40°	1122.1	16.2
0°-60°	1821.7	26.3
0°-90°	2141.1	30.9
90°-120°	1038.1	15.0
90°-150°	3542.9	51.2
90°-180°	4783.0	69.1
0°-180°	6923.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	825	825	825	825	825	
5°	946	823	727	823	946	94
15°	1136	786	553	786	1136	326
25°	1360	717	444	717	1360	625
35°	1129	624	362	624	1129	682
45°	505	491	285	491	505	403
55°	277	346	213	346	277	251
65°	157	216	127	216	157	156
75°	73	105	66	105	73	78
85°	16	23	18	23	16	19
90°	28	1	28	1	28	13
95°	24	66	24	66	24	20
105°	343	340	343	340	343	310
115°	633	637	633	637	633	628
125°	906	906	906	906	906	806
135°	1126	1130	1126	1130	1126	869
145°	1307	1310	1307	1310	1307	816
155°	1433	1443	1433	1443	1433	660
165°	1515	1523	1515	1523	1515	427
175°	1550	1558	1550	1558	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	868.0	867.5	868.5	865.5	865.9	861.2	861.2	857.6	853.1	849.5	847.9
5°	945.7	946.5	945.0	940.0	936.6	931.5	925.8	915.6	907.1	899.0	892.6
7.5°	1025.8	1026.3	1021.8	1020.3	1011.7	1005.5	992.7	978.9	966.6	951.0	939.1
10°	1072.5	1072.1	1067.4	1063.6	1056.1	1046.7	1034.1	1017.9	1002.6	985.7	969.5
12.5°	1099.6	1098.7	1097.2	1092.6	1085.7	1077.3	1066.7	1050.7	1031.9	1013.3	994.4
15°	1136.1	1133.7	1129.4	1123.6	1113.7	1103.9	1092.1	1077.9	1059.9	1038.9	1021.3
17.5°	1181.3	1181.4	1174.7	1166.7	1153.3	1136.0	1117.7	1094.8	1070.3	1047.2	1028.5
20°	1218.8	1217.7	1210.9	1195.4	1180.2	1158.5	1137.5	1109.4	1079.6	1049.4	1026.0
22.5°	1272.4	1269.8	1262.8	1242.2	1218.6	1190.7	1158.6	1124.3	1088.2	1054.0	1023.3
25°	1360.4	1358.3	1344.4	1320.7	1287.5	1244.5	1202.5	1155.4	1103.6	1058.5	1021.3
27.5°	1420.5	1418.3	1408.0	1388.3	1357.6	1312.4	1255.5	1192.7	1127.9	1066.0	1012.2
30°	1414.5	1419.6	1418.3	1409.2	1386.1	1345.4	1293.0	1222.2	1145.2	1072.5	1008.4
32.5°	1329.5	1334.0	1345.9	1363.9	1365.2	1349.0	1309.7	1244.4	1164.8	1081.9	1005.4
35°	1128.6	1134.8	1157.8	1194.0	1241.4	1281.1	1289.2	1254.0	1182.5	1093.4	1000.9
37.5°	867.7	901.1	920.4	958.6	1030.2	1103.1	1173.2	1199.1	1168.7	1088.7	993.7
40°	737.1	745.2	779.8	822.8	883.1	958.9	1058.9	1131.0	1133.4	1077.9	982.3
42.5°	630.9	641.1	664.9	699.2	750.8	826.7	929.9	1025.1	1069.2	1048.0	967.4
45°	504.7	512.5	529.8	556.2	595.8	658.5	747.3	857.4	944.8	978.9	927.5
47.5°	414.6	418.8	433.8	454.0	483.3	529.0	597.6	693.2	798.1	871.6	864.3
50°	365.9	370.6	382.1	397.3	422.0	460.7	515.6	595.1	703.2	793.0	810.9
52.5°	327.9	331.8	339.0	353.5	373.8	403.5	447.8	519.9	617.1	712.5	754.0
55°	277.1	279.8	285.5	293.6	310.0	331.3	369.5	419.4	497.9	594.1	655.1
57.5°	235.2	236.6	240.2	247.7	259.0	274.6	302.2	344.5	400.8	487.4	554.7
60°	208.7	210.0	214.7	219.8	228.6	242.9	264.6	294.0	348.2	419.7	487.8
62.5°	187.5	188.3	190.4	195.5	203.1	214.2	231.2	255.3	298.4	361.1	425.4
65°	157.2	157.5	158.2	162.3	167.0	175.1	186.3	203.2	235.8	283.2	340.1
67.5°	128.0	128.5	130.9	132.3	137.2	141.5	148.1	161.0	184.0	215.9	260.1
70°	111.8	111.5	113.8	115.5	117.2	122.3	126.7	137.1	151.4	175.8	212.8
72.5°	96.6	95.8	96.8	97.4	99.6	103.1	107.5	113.9	124.8	141.7	169.9
75°	73.2	73.5	73.5	74.2	75.9	77.2	78.6	81.9	88.1	99.2	114.5
77.5°	51.4	50.8	52.3	52.4	53.4	54.9	56.1	57.4	59.9	64.6	72.4
80°	37.3	37.3	37.6	38.6	38.3	39.0	40.7	42.0	45.0	47.8	50.5
82.5°	28.6	28.4	28.6	28.9	28.8	29.4	30.1	30.3	31.5	32.8	34.8
85°	15.6	15.6	16.0	16.0	16.2	16.2	16.6	16.6	16.6	16.9	17.3
87.5°	11.5	11.1	10.6	10.5	10.6	11.0	10.4	9.9	9.6	9.4	9.3
90°	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0	19.8	18.5	16.7
92.5°	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0	19.8	18.5	16.9
95°	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0	19.8	18.5	28.2
97.5°	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4	49.6	56.8	76.1
100°	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4	162.6	200.9	199.8
102.5°	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8	249.1	256.3	255.7
105°	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6	435.5	435.5	435.0
110°	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9	495.7	496.4	496.0



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6	554.6	555.5	555.3
115°	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2	643.2	644.3	644.0
117.5°	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7	729.1	730.4	729.4
120°	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9	783.5	783.9	783.2
122.5°	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5	836.1	836.6	836.2
125°	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3	913.4	914.4	914.4
127.5°	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6	983.1	983.6	983.8
130°	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3	1029.1	1029.8	1029.6
132.5°	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1	1071.3	1071.4	1072.0
135°	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9	1134.4	1134.9	1135.4
137.5°	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4	1192.3	1192.2	1192.7
140°	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3	1227.8	1227.3	1227.5
142.5°	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5	1263.4	1263.3	1262.9
145°	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2	1313.0	1312.7	1312.7
147.5°	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8	1355.5	1355.2	1354.9
150°	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0	1382.5	1382.0	1381.4
152.5°	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0	1406.5	1406.0	1405.5
155°	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1	1439.3	1438.6	1438.1
157.5°	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5	1466.6	1465.8	1465.8
160°	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5	1483.5	1482.5	1482.2
162.5°	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0	1498.6	1497.2	1496.9
165°	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1	1518.6	1517.1	1516.8
167.5°	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3	1533.5	1531.6	1531.3
170°	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1	1541.1	1539.0	1538.7
172.5°	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2	1547.3	1545.4	1545.0
175°	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8	1553.7	1551.7	1551.5
177.5°	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5	1557.1	1555.6	1555.4
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	847.9	846.1	842.5	839.3	835.2	831.7	829.2	826.3	822.4	817.9	814.0
5°	885.5	878.0	868.2	859.7	848.9	840.4	831.6	823.1	814.7	803.8	794.3
7.5°	927.0	911.7	896.7	877.9	860.8	845.5	830.9	816.1	801.6	786.2	771.3
10°	952.5	933.9	913.2	889.5	867.8	847.2	828.2	809.6	790.0	772.7	754.0
12.5°	976.3	952.3	928.7	898.8	872.7	847.5	823.3	800.1	779.1	756.7	736.6
15°	997.9	974.2	947.8	911.2	874.9	844.5	816.0	785.9	759.8	734.7	712.4
17.5°	1006.2	981.4	950.7	915.5	875.9	837.6	800.9	767.9	737.2	707.9	682.8
20°	1003.0	978.9	947.4	913.9	871.6	831.6	791.9	755.4	721.1	690.4	663.6
22.5°	995.1	970.3	939.9	904.5	864.2	821.8	779.5	740.5	704.6	672.7	643.5
25°	983.4	949.5	918.3	883.8	845.5	803.5	759.8	716.8	678.5	646.0	614.1
27.5°	971.1	928.8	889.2	854.8	814.4	776.9	734.8	690.7	650.4	617.3	584.7
30°	960.0	912.6	868.9	829.9	791.7	756.1	716.0	673.1	631.8	597.5	564.4
32.5°	946.2	895.7	847.7	802.8	765.9	730.6	694.4	653.3	613.1	577.7	544.0
35°	928.8	864.4	812.3	764.6	723.5	689.3	656.8	623.6	583.3	546.7	513.9
37.5°	906.1	833.0	772.7	720.6	677.4	643.0	617.4	587.0	550.3	515.2	484.7
40°	892.2	810.3	744.2	692.7	647.3	611.1	587.0	561.2	527.7	494.9	464.4
42.5°	873.8	789.4	715.5	661.8	616.2	581.3	557.0	534.5	506.3	475.4	442.7
45°	837.7	748.9	671.4	613.8	567.8	533.5	510.8	490.8	469.5	441.0	412.6
47.5°	790.7	706.8	625.5	562.7	517.5	485.8	463.8	448.0	432.7	408.6	380.9
50°	753.0	672.1	592.8	531.8	483.8	453.5	432.9	420.4	406.4	384.5	361.4
52.5°	708.6	636.3	558.7	496.3	450.9	422.7	402.8	390.3	378.8	360.9	338.9
55°	638.6	575.2	504.0	447.5	405.8	377.4	358.4	346.5	339.7	324.5	307.2
57.5°	557.7	512.3	449.6	395.0	358.2	330.0	316.2	306.1	298.5	287.7	275.4
60°	501.3	469.5	413.2	361.4	327.5	300.8	288.3	279.8	272.7	263.5	254.0
62.5°	444.2	421.0	372.1	327.5	296.4	273.9	262.3	254.6	246.4	240.2	231.0
65°	367.6	346.9	313.0	278.1	249.3	231.4	222.9	216.2	211.1	204.3	197.8
67.5°	285.9	277.5	254.1	230.1	209.4	193.4	186.1	181.4	175.2	171.2	166.7
70°	235.8	231.7	215.1	199.2	179.9	169.1	162.3	160.2	152.8	148.7	145.6
72.5°	191.4	189.4	179.9	168.8	155.2	145.7	139.5	137.1	132.4	129.2	127.2
75°	131.1	131.8	130.1	123.0	117.9	111.8	106.4	105.0	101.7	98.9	97.2
77.5°	82.9	86.4	86.5	86.1	84.2	80.4	78.2	77.1	73.8	72.9	72.4
80°	56.9	60.6	64.0	63.7	63.0	62.0	60.3	59.3	57.6	56.5	55.9
82.5°	37.9	41.4	44.2	46.1	45.9	44.9	43.8	43.2	43.0	42.2	42.1
85°	17.9	18.6	19.6	22.0	23.7	24.1	23.7	23.4	22.4	22.7	23.0
87.5°	9.2	8.8	8.7	8.4	7.7	8.6	9.0	8.9	8.7	8.6	8.5
90°	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7	16.3	14.9	13.5
95°	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8	65.0	64.3	63.5
97.5°	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4	138.8	140.2	141.5
100°	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8	193.6	194.3	195.1
102.5°	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1	250.1	251.1	252.1
105°	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5	340.5	341.5	342.5
107.5°	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2	433.2	433.2	433.2
110°	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4	552.1	552.7	553.2
115°	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3	638.6	639.9	641.1
117.5°	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2	726.1	726.1	726.0
120°	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6	781.4	781.1	780.9
122.5°	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5	831.5	832.5	833.5
125°	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3	908.1	909.9	911.7
127.5°	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6	979.9	981.1	982.4
130°	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9	1024.2	1025.5	1026.8
132.5°	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3	1068.7	1070.2	1071.7
135°	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3	1131.8	1133.4	1134.9
137.5°	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3	1189.5	1190.9	1192.2
140°	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1	1226.6	1227.2	1227.6
142.5°	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3	1260.6	1260.9	1261.2
145°	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4	1310.9	1311.4	1312.0
147.5°	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2	1354.2	1354.1	1354.0
150°	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1381.4	1381.0	1380.5
152.5°	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7	1407.7	1406.5	1405.4
155°	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1	1441.6	1440.1	1438.6
157.5°	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7	1468.8	1467.8	1467.0
160°	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2	1486.7	1485.1	1483.5
162.5°	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0	1501.5	1499.9	1498.3
165°	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9	1521.3	1519.7	1518.2
167.5°	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6	1536.1	1534.5	1532.9
170°	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0	1544.2	1542.3	1540.5
172.5°	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5	1549.7	1547.9	1546.0
175°	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5	1555.9	1554.4	1552.8
177.5°	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2	1559.0	1557.8	1556.6
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	811.4	807.5	804.9	799.4	795.6	794.0	791.0	790.2	793.2	791.0	790.8
5°	787.2	777.4	769.6	761.8	753.3	748.0	739.8	738.4	736.4	733.3	732.7
7.5°	758.3	745.5	735.5	722.6	711.4	702.4	692.2	687.4	684.7	680.8	675.6
10°	738.8	723.5	710.0	697.1	683.2	672.1	661.9	654.1	649.0	644.3	642.2
12.5°	719.5	704.0	686.7	671.1	655.6	643.0	631.8	626.7	621.1	615.5	610.8
15°	689.6	669.0	650.1	632.0	618.8	605.3	594.5	587.0	578.5	576.2	567.0
17.5°	658.0	637.7	615.5	596.6	581.3	566.3	554.5	546.0	539.6	530.8	526.6
20°	638.2	614.1	592.5	575.2	558.2	540.6	528.4	521.3	515.2	508.1	504.7
22.5°	617.1	593.5	571.3	551.1	533.9	516.5	507.8	500.4	493.6	487.0	482.5
25°	586.0	562.3	539.0	517.9	500.0	487.4	477.2	468.8	465.1	458.6	453.9
27.5°	555.4	530.1	505.9	484.9	470.8	458.4	450.1	443.4	436.7	431.1	427.0
30°	535.6	509.8	483.4	466.8	451.8	440.1	430.9	424.5	419.4	414.3	411.3
32.5°	515.8	489.2	465.7	447.8	433.7	423.5	414.1	407.9	402.5	396.9	393.3
35°	484.0	456.9	438.0	420.4	406.4	397.0	390.6	381.7	377.4	373.3	369.5
37.5°	454.6	429.4	408.8	393.4	381.4	371.9	363.6	358.8	353.5	349.8	346.7
40°	432.9	409.8	391.3	375.0	366.1	355.7	347.9	341.8	337.7	333.0	329.6
42.5°	413.4	392.0	373.9	359.3	348.3	339.4	331.9	325.8	320.7	317.3	314.4
45°	385.8	364.4	346.9	333.3	323.2	314.7	306.9	303.8	297.0	293.0	291.7
47.5°	357.3	338.2	321.2	308.7	298.3	290.3	282.9	276.8	273.0	269.0	266.9
50°	338.0	319.8	303.8	291.7	281.5	272.7	265.9	261.8	256.7	253.1	250.3
52.5°	318.8	301.8	286.0	274.3	265.5	256.7	249.1	245.0	240.2	237.8	235.9
55°	291.3	273.4	259.8	248.3	239.2	231.0	223.9	219.8	216.8	214.5	213.7
57.5°	260.1	245.9	233.4	222.9	213.5	205.8	199.6	195.7	193.1	192.7	190.6
60°	239.8	226.9	215.4	204.3	196.1	189.0	183.6	179.2	176.5	176.1	175.5
62.5°	219.5	207.1	196.4	186.6	179.3	172.5	167.4	162.4	160.8	159.1	157.6
65°	189.3	178.2	169.3	161.6	153.8	148.0	142.9	139.9	136.2	134.1	130.5
67.5°	159.7	151.1	142.6	136.1	129.9	124.5	120.3	115.7	113.2	111.6	108.9
70°	140.3	133.5	125.0	117.9	113.2	108.7	105.3	100.2	98.5	97.2	95.9
72.5°	121.8	115.8	108.7	103.0	98.3	94.1	90.2	87.8	86.1	84.7	83.9
75°	95.9	90.1	84.0	79.9	76.6	73.2	71.2	69.5	68.8	68.4	67.1
77.5°	70.4	67.3	62.4	59.2	57.0	55.6	53.8	52.9	52.9	51.4	50.9
80°	53.9	52.2	48.1	46.7	45.0	43.7	42.7	41.0	39.3	38.6	37.6
82.5°	40.0	38.3	36.7	34.5	33.2	32.3	31.3	30.7	30.9	30.0	29.4
85°	21.3	19.6	19.0	18.6	17.9	18.6	18.3	17.9	17.7	17.3	17.7
87.5°	8.6	9.0	9.1	10.0	9.5	10.2	10.4	10.4	10.7	11.0	10.9
90°	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0	22.3	23.6	24.6
92.5°	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0	22.3	23.6	24.4
95°	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0	22.3	23.6	24.3
97.5°	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4	35.1	27.8	24.3
100°	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4	86.2	48.0	28.4
102.5°	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8	234.6	227.4	215.0
105°	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	343.9
107.5°	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6	435.7	435.7	435.3
110°	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9	494.2	493.4	493.1



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6	552.7	551.7	551.0
115°	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2	641.1	640.2	638.8
117.5°	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7	726.4	725.1	724.0
120°	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9	782.4	781.9	781.0
122.5°	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5	835.0	834.6	833.5
125°	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3	911.3	910.3	909.4
127.5°	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6	982.0	981.4	980.2
130°	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3	1027.5	1026.8	1025.7
132.5°	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1	1070.9	1070.8	1070.1
135°	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9	1133.4	1132.8	1131.8
137.5°	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4	1192.5	1192.6	1191.9
140°	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3	1228.8	1229.3	1228.8
142.5°	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5	1263.6	1263.7	1263.0
145°	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2	1313.5	1313.8	1313.1
147.5°	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8	1356.1	1356.5	1355.7
150°	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0	1383.5	1384.0	1383.2
152.5°	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0	1407.6	1408.0	1407.4
155°	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1	1440.8	1441.6	1441.0
157.5°	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5	1468.3	1469.1	1468.5
160°	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5	1485.5	1486.6	1486.0
162.5°	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0	1501.6	1503.0	1502.5
165°	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1	1521.7	1523.2	1523.0
167.5°	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3	1537.1	1539.0	1538.7
170°	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1	1545.2	1547.2	1547.1
172.5°	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2	1551.0	1552.8	1552.6
175°	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8	1557.8	1559.9	1559.8
177.5°	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5	1560.0	1561.4	1561.3
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	790.5	787.5	786.7	787.7	786.7	787.5	790.5	790.8	791.0	793.2	790.2
5°	729.3	725.9	727.6	726.9	727.6	725.9	729.3	732.7	733.3	736.4	738.4
7.5°	675.5	671.3	666.8	668.2	666.8	671.3	675.5	675.6	680.8	684.7	687.4
10°	637.8	634.5	632.4	634.1	632.4	634.5	637.8	642.2	644.3	649.0	654.1
12.5°	606.1	604.1	602.4	601.6	602.4	604.1	606.1	610.8	615.5	621.1	626.7
15°	562.9	558.9	557.2	552.9	557.2	558.9	562.9	567.0	576.2	578.5	587.0
17.5°	523.2	521.8	517.5	515.6	517.5	521.8	523.2	526.6	530.8	539.6	546.0
20°	499.6	498.3	493.9	496.6	493.9	498.3	499.6	504.7	508.1	515.2	521.3
22.5°	480.1	477.2	475.7	474.9	475.7	477.2	480.1	482.5	487.0	493.6	500.4
25°	452.5	448.2	446.5	444.4	446.5	448.2	452.5	453.9	458.6	465.1	468.8
27.5°	425.1	422.7	420.4	419.9	420.4	422.7	425.1	427.0	431.1	436.7	443.4
30°	407.2	404.7	403.1	403.1	403.1	404.7	407.2	411.3	414.3	419.4	424.5
32.5°	391.2	389.3	387.6	387.4	387.6	389.3	391.2	393.3	396.9	402.5	407.9
35°	367.8	365.2	364.4	362.5	364.4	365.2	367.8	369.5	373.3	377.4	381.7
37.5°	343.7	341.4	341.3	341.2	341.3	341.4	343.7	346.7	349.8	353.5	358.8
40°	328.2	326.5	326.2	323.9	326.2	326.5	328.2	329.6	333.0	337.7	341.8
42.5°	311.7	310.9	309.7	308.6	309.7	310.9	311.7	314.4	317.3	320.7	325.8
45°	289.3	287.0	287.0	285.3	287.0	287.0	289.3	291.7	293.0	297.0	303.8
47.5°	266.1	264.3	264.5	262.7	264.5	264.3	266.1	266.9	269.0	273.0	276.8
50°	250.7	249.7	249.3	248.6	249.3	249.7	250.7	250.3	253.1	256.7	261.8
52.5°	235.2	234.8	236.0	234.5	236.0	234.8	235.2	235.9	237.8	240.2	245.0
55°	214.5	213.4	215.4	213.4	215.4	213.4	214.5	213.7	214.5	216.8	219.8
57.5°	190.5	189.6	191.4	190.4	191.4	189.6	190.5	190.6	192.7	193.1	195.7
60°	174.8	172.7	173.8	174.2	173.8	172.7	174.8	175.5	176.1	176.5	179.2
62.5°	156.0	154.9	155.6	154.1	155.6	154.9	156.0	157.6	159.1	160.8	162.4
65°	129.7	128.8	127.3	126.7	127.3	128.8	129.7	130.5	134.1	136.2	139.9
67.5°	109.0	106.6	106.5	107.0	106.5	106.6	109.0	108.9	111.6	113.2	115.7
70°	93.8	93.8	93.5	93.5	93.5	93.8	93.8	95.9	97.2	98.5	100.2
72.5°	83.3	83.0	82.4	82.1	82.4	83.0	83.3	83.9	84.7	86.1	87.8
75°	67.1	67.4	66.7	66.4	66.7	67.4	67.1	67.1	68.4	68.8	69.5
77.5°	49.5	48.1	48.9	48.1	48.9	48.1	49.5	50.9	51.4	52.9	52.9
80°	37.6	37.3	38.3	37.3	38.3	37.3	37.6	37.6	38.6	39.3	41.0
82.5°	29.8	29.4	29.9	29.2	29.9	29.4	29.8	29.4	30.0	30.9	30.7
85°	17.9	17.7	17.3	17.7	17.3	17.7	17.9	17.7	17.3	17.7	17.9
87.5°	11.3	11.2	11.3	11.5	11.3	11.2	11.3	10.9	11.0	10.7	10.4
90°	25.4	26.1	26.9	27.7	26.9	26.1	25.4	24.6	23.6	22.3	21.0
92.5°	24.8	25.1	25.5	25.9	25.5	25.1	24.8	24.4	23.6	22.3	21.0
95°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.3	21.0
97.5°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	27.8	35.1	42.4
100°	27.3	26.3	25.2	24.3	25.2	26.3	27.3	28.4	48.0	86.2	124.4
102.5°	197.6	180.1	162.6	145.3	162.6	180.1	197.6	215.0	227.4	234.6	241.8
105°	343.7	343.4	343.1	342.9	343.1	343.4	343.7	343.9	344.0	344.0	344.0
107.5°	434.5	433.8	433.0	432.3	433.0	433.8	434.5	435.3	435.7	435.7	435.6
110°	493.4	493.7	493.9	494.2	493.9	493.7	493.4	493.1	493.4	494.2	494.9



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	550.6	550.3	549.9	549.6	549.9	550.3	550.6	551.0	551.7	552.7	553.6
115°	637.3	635.8	634.2	632.7	634.2	635.8	637.3	638.8	640.2	641.1	642.2
117.5°	723.4	722.7	722.0	721.4	722.0	722.7	723.4	724.0	725.1	726.4	727.7
120°	779.7	778.4	777.1	775.9	777.1	778.4	779.7	781.0	781.9	782.4	782.9
122.5°	832.1	830.5	829.0	827.6	829.0	830.5	832.1	833.5	834.6	835.0	835.5
125°	908.7	907.9	907.0	906.3	907.0	907.9	908.7	909.4	910.3	911.3	912.3
127.5°	978.3	976.4	974.5	972.6	974.5	976.4	978.3	980.2	981.4	982.0	982.6
130°	1024.5	1023.1	1021.9	1020.7	1021.9	1023.1	1024.5	1025.7	1026.8	1027.5	1028.3
132.5°	1068.8	1067.6	1066.2	1065.0	1066.2	1067.6	1068.8	1070.1	1070.8	1070.9	1071.1
135°	1130.3	1128.7	1127.2	1125.7	1127.2	1128.7	1130.3	1131.8	1132.8	1133.4	1133.9
137.5°	1190.6	1189.3	1187.9	1186.6	1187.9	1189.3	1190.6	1191.9	1192.6	1192.5	1192.4
140°	1227.3	1225.7	1224.2	1222.6	1224.2	1225.7	1227.3	1228.8	1229.3	1228.8	1228.3
142.5°	1261.4	1259.9	1258.4	1256.9	1258.4	1259.9	1261.4	1263.0	1263.7	1263.6	1263.5
145°	1311.5	1310.0	1308.5	1307.0	1308.5	1310.0	1311.5	1313.1	1313.8	1313.5	1313.2
147.5°	1353.8	1351.9	1350.1	1348.3	1350.1	1351.9	1353.8	1355.7	1356.5	1356.1	1355.8
150°	1381.2	1379.1	1377.1	1375.0	1377.1	1379.1	1381.2	1383.2	1384.0	1383.5	1383.0
152.5°	1405.5	1403.7	1401.9	1400.0	1401.9	1403.7	1405.5	1407.4	1408.0	1407.6	1407.0
155°	1439.0	1436.9	1434.9	1432.8	1434.9	1436.9	1439.0	1441.0	1441.6	1440.8	1440.1
157.5°	1466.4	1464.4	1462.3	1460.3	1462.3	1464.4	1466.4	1468.5	1469.1	1468.3	1467.5
160°	1484.0	1481.9	1479.9	1477.8	1479.9	1481.9	1484.0	1486.0	1486.6	1485.5	1484.5
162.5°	1500.3	1498.0	1495.8	1493.5	1495.8	1498.0	1500.3	1502.5	1503.0	1501.6	1500.0
165°	1520.9	1518.9	1516.8	1514.7	1516.8	1518.9	1520.9	1523.0	1523.2	1521.7	1520.1
167.5°	1536.4	1534.2	1531.9	1529.6	1531.9	1534.2	1536.4	1538.7	1539.0	1537.1	1535.3
170°	1544.8	1542.5	1540.2	1537.8	1540.2	1542.5	1544.8	1547.1	1547.2	1545.2	1543.1
172.5°	1550.3	1548.0	1545.7	1543.4	1545.7	1548.0	1550.3	1552.6	1552.8	1551.0	1549.2
175°	1557.5	1555.1	1552.8	1550.5	1552.8	1555.1	1557.5	1559.8	1559.9	1557.8	1555.8
177.5°	1559.6	1558.0	1556.3	1554.7	1556.3	1558.0	1559.6	1561.3	1561.4	1560.0	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	791.0	794.0	795.6	799.4	804.9	807.5	811.4	814.0	817.9	822.4	826.3
5°	739.8	748.0	753.3	761.8	769.6	777.4	787.2	794.3	803.8	814.7	823.1
7.5°	692.2	702.4	711.4	722.6	735.5	745.5	758.3	771.3	786.2	801.6	816.1
10°	661.9	672.1	683.2	697.1	710.0	723.5	738.8	754.0	772.7	790.0	809.6
12.5°	631.8	643.0	655.6	671.1	686.7	704.0	719.5	736.6	756.7	779.1	800.1
15°	594.5	605.3	618.8	632.0	650.1	669.0	689.6	712.4	734.7	759.8	785.9
17.5°	554.5	566.3	581.3	596.6	615.5	637.7	658.0	682.8	707.9	737.2	767.9
20°	528.4	540.6	558.2	575.2	592.5	614.1	638.2	663.6	690.4	721.1	755.4
22.5°	507.8	516.5	533.9	551.1	571.3	593.5	617.1	643.5	672.7	704.6	740.5
25°	477.2	487.4	500.0	517.9	539.0	562.3	586.0	614.1	646.0	678.5	716.8
27.5°	450.1	458.4	470.8	484.9	505.9	530.1	555.4	584.7	617.3	650.4	690.7
30°	430.9	440.1	451.8	466.8	483.4	509.8	535.6	564.4	597.5	631.8	673.1
32.5°	414.1	423.5	433.7	447.8	465.7	489.2	515.8	544.0	577.7	613.1	653.3
35°	390.6	397.0	406.4	420.4	438.0	456.9	484.0	513.9	546.7	583.3	623.6
37.5°	363.6	371.9	381.4	393.4	408.8	429.4	454.6	484.7	515.2	550.3	587.0
40°	347.9	355.7	366.1	375.0	391.3	409.8	432.9	464.4	494.9	527.7	561.2
42.5°	331.9	339.4	348.3	359.3	373.9	392.0	413.4	442.7	475.4	506.3	534.5
45°	306.9	314.7	323.2	333.3	346.9	364.4	385.8	412.6	441.0	469.5	490.8
47.5°	282.9	290.3	298.3	308.7	321.2	338.2	357.3	380.9	408.6	432.7	448.0
50°	265.9	272.7	281.5	291.7	303.8	319.8	338.0	361.4	384.5	406.4	420.4
52.5°	249.1	256.7	265.5	274.3	286.0	301.8	318.8	338.9	360.9	378.8	390.3
55°	223.9	231.0	239.2	248.3	259.8	273.4	291.3	307.2	324.5	339.7	346.5
57.5°	199.6	205.8	213.5	222.9	233.4	245.9	260.1	275.4	287.7	298.5	306.1
60°	183.6	189.0	196.1	204.3	215.4	226.9	239.8	254.0	263.5	272.7	279.8
62.5°	167.4	172.5	179.3	186.6	196.4	207.1	219.5	231.0	240.2	246.4	254.6
65°	142.9	148.0	153.8	161.6	169.3	178.2	189.3	197.8	204.3	211.1	216.2
67.5°	120.3	124.5	129.9	136.1	142.6	151.1	159.7	166.7	171.2	175.2	181.4
70°	105.3	108.7	113.2	117.9	125.0	133.5	140.3	145.6	148.7	152.8	160.2
72.5°	90.2	94.1	98.3	103.0	108.7	115.8	121.8	127.2	129.2	132.4	137.1
75°	71.2	73.2	76.6	79.9	84.0	90.1	95.9	97.2	98.9	101.7	105.0
77.5°	53.8	55.6	57.0	59.2	62.4	67.3	70.4	72.4	72.9	73.8	77.1
80°	42.7	43.7	45.0	46.7	48.1	52.2	53.9	55.9	56.5	57.6	59.3
82.5°	31.3	32.3	33.2	34.5	36.7	38.3	40.0	42.1	42.2	43.0	43.2
85°	18.3	18.6	17.9	18.6	19.0	19.6	21.3	23.0	22.7	22.4	23.4
87.5°	10.4	10.2	9.5	10.0	9.1	9.0	8.6	8.5	8.6	8.7	8.9
90°	19.8	18.5	16.7	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2
92.5°	19.8	18.5	16.9	15.2	13.7	12.1	12.0	13.5	14.9	16.3	17.7
95°	19.8	18.5	28.2	38.0	47.7	57.4	62.7	63.5	64.3	65.0	65.8
97.5°	49.6	56.8	76.1	95.4	114.7	133.9	142.9	141.5	140.2	138.8	137.4
100°	162.6	200.9	199.8	198.9	197.8	196.8	195.9	195.1	194.3	193.6	192.8
102.5°	249.1	256.3	255.7	255.1	254.5	253.9	253.1	252.1	251.1	250.1	249.1
105°	344.0	344.0	344.0	344.0	344.0	344.0	343.6	342.5	341.5	340.5	339.5
107.5°	435.5	435.5	435.0	434.4	434.0	433.5	433.2	433.2	433.2	433.2	433.2
110°	495.7	496.4	496.0	495.4	494.9	494.4	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	554.6	555.5	555.3	554.9	554.6	554.4	553.8	553.2	552.7	552.1	551.4
115°	643.2	644.3	644.0	643.7	643.5	643.2	642.5	641.1	639.9	638.6	637.3
117.5°	729.1	730.4	729.4	728.4	727.5	726.5	726.0	726.0	726.1	726.1	726.2
120°	783.5	783.9	783.2	782.4	781.6	780.9	780.6	780.9	781.1	781.4	781.6
122.5°	836.1	836.6	836.2	835.9	835.5	835.2	834.5	833.5	832.5	831.5	830.5
125°	913.4	914.4	914.4	914.4	914.4	914.4	913.5	911.7	909.9	908.1	906.3
127.5°	983.1	983.6	983.8	984.0	984.1	984.3	983.7	982.4	981.1	979.9	978.6
130°	1029.1	1029.8	1029.6	1029.3	1029.1	1028.9	1028.1	1026.8	1025.5	1024.2	1022.9
132.5°	1071.3	1071.4	1072.0	1072.5	1073.1	1073.7	1073.2	1071.7	1070.2	1068.7	1067.3
135°	1134.4	1134.9	1135.4	1136.0	1136.5	1136.9	1136.5	1134.9	1133.4	1131.8	1130.3
137.5°	1192.3	1192.2	1192.7	1193.1	1193.6	1194.0	1193.6	1192.2	1190.9	1189.5	1188.3
140°	1227.8	1227.3	1227.5	1227.8	1228.1	1228.3	1228.2	1227.6	1227.2	1226.6	1226.1
142.5°	1263.4	1263.3	1262.9	1262.6	1262.2	1261.9	1261.5	1261.2	1260.9	1260.6	1260.3
145°	1313.0	1312.7	1312.7	1312.7	1312.7	1312.7	1312.4	1312.0	1311.4	1310.9	1310.4
147.5°	1355.5	1355.2	1354.9	1354.6	1354.2	1354.0	1353.9	1354.0	1354.1	1354.2	1354.2
150°	1382.5	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0
152.5°	1406.5	1406.0	1405.5	1405.0	1404.4	1403.9	1404.3	1405.4	1406.5	1407.7	1408.7
155°	1439.3	1438.6	1438.1	1437.5	1437.0	1436.5	1437.0	1438.6	1440.1	1441.6	1443.1
157.5°	1466.6	1465.8	1465.8	1465.7	1465.6	1465.6	1466.1	1467.0	1467.8	1468.8	1469.7
160°	1483.5	1482.5	1482.2	1481.9	1481.7	1481.4	1482.0	1483.5	1485.1	1486.7	1488.2
162.5°	1498.6	1497.2	1496.9	1496.7	1496.5	1496.2	1496.8	1498.3	1499.9	1501.5	1503.0
165°	1518.6	1517.1	1516.8	1516.5	1516.3	1516.0	1516.7	1518.2	1519.7	1521.3	1522.9
167.5°	1533.5	1531.6	1531.3	1531.1	1530.8	1530.6	1531.2	1532.9	1534.5	1536.1	1537.6
170°	1541.1	1539.0	1538.7	1538.5	1538.2	1537.9	1538.7	1540.5	1542.3	1544.2	1546.0
172.5°	1547.3	1545.4	1545.0	1544.5	1544.1	1543.6	1544.3	1546.0	1547.9	1549.7	1551.5
175°	1553.7	1551.7	1551.5	1551.2	1551.0	1550.7	1551.3	1552.8	1554.4	1555.9	1557.5
177.5°	1557.1	1555.6	1555.4	1555.2	1555.1	1554.8	1555.3	1556.6	1557.8	1559.0	1560.2
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	829.2	831.7	835.2	839.3	842.5	846.1	847.9	847.9	849.5	853.1	857.6
5°	831.6	840.4	848.9	859.7	868.2	878.0	885.5	892.6	899.0	907.1	915.6
7.5°	830.9	845.5	860.8	877.9	896.7	911.7	927.0	939.1	951.0	966.6	978.9
10°	828.2	847.2	867.8	889.5	913.2	933.9	952.5	969.5	985.7	1002.6	1017.9
12.5°	823.3	847.5	872.7	898.8	928.7	952.3	976.3	994.4	1013.3	1031.9	1050.7
15°	816.0	844.5	874.9	911.2	947.8	974.2	997.9	1021.3	1038.9	1059.9	1077.9
17.5°	800.9	837.6	875.9	915.5	950.7	981.4	1006.2	1028.5	1047.2	1070.3	1094.8
20°	791.9	831.6	871.6	913.9	947.4	978.9	1003.0	1026.0	1049.4	1079.6	1109.4
22.5°	779.5	821.8	864.2	904.5	939.9	970.3	995.1	1023.3	1054.0	1088.2	1124.3
25°	759.8	803.5	845.5	883.8	918.3	949.5	983.4	1021.3	1058.5	1103.6	1155.4
27.5°	734.8	776.9	814.4	854.8	889.2	928.8	971.1	1012.2	1066.0	1127.9	1192.7
30°	716.0	756.1	791.7	829.9	868.9	912.6	960.0	1008.4	1072.5	1145.2	1222.2
32.5°	694.4	730.6	765.9	802.8	847.7	895.7	946.2	1005.4	1081.9	1164.8	1244.4
35°	656.8	689.3	723.5	764.6	812.3	864.4	928.8	1000.9	1093.4	1182.5	1254.0
37.5°	617.4	643.0	677.4	720.6	772.7	833.0	906.1	993.7	1088.7	1168.7	1199.1
40°	587.0	611.1	647.3	692.7	744.2	810.3	892.2	982.3	1077.9	1133.4	1131.0
42.5°	557.0	581.3	616.2	661.8	715.5	789.4	873.8	967.4	1048.0	1069.2	1025.1
45°	510.8	533.5	567.8	613.8	671.4	748.9	837.7	927.5	978.9	944.8	857.4
47.5°	463.8	485.8	517.5	562.7	625.5	706.8	790.7	864.3	871.6	798.1	693.2
50°	432.9	453.5	483.8	531.8	592.8	672.1	753.0	810.9	793.0	703.2	595.1
52.5°	402.8	422.7	450.9	496.3	558.7	636.3	708.6	754.0	712.5	617.1	519.9
55°	358.4	377.4	405.8	447.5	504.0	575.2	638.6	655.1	594.1	497.9	419.4
57.5°	316.2	330.0	358.2	395.0	449.6	512.3	557.7	554.7	487.4	400.8	344.5
60°	288.3	300.8	327.5	361.4	413.2	469.5	501.3	487.8	419.7	348.2	294.0
62.5°	262.3	273.9	296.4	327.5	372.1	421.0	444.2	425.4	361.1	298.4	255.3
65°	222.9	231.4	249.3	278.1	313.0	346.9	367.6	340.1	283.2	235.8	203.2
67.5°	186.1	193.4	209.4	230.1	254.1	277.5	285.9	260.1	215.9	184.0	161.0
70°	162.3	169.1	179.9	199.2	215.1	231.7	235.8	212.8	175.8	151.4	137.1
72.5°	139.5	145.7	155.2	168.8	179.9	189.4	191.4	169.9	141.7	124.8	113.9
75°	106.4	111.8	117.9	123.0	130.1	131.8	131.1	114.5	99.2	88.1	81.9
77.5°	78.2	80.4	84.2	86.1	86.5	86.4	82.9	72.4	64.6	59.9	57.4
80°	60.3	62.0	63.0	63.7	64.0	60.6	56.9	50.5	47.8	45.0	42.0
82.5°	43.8	44.9	45.9	46.1	44.2	41.4	37.9	34.8	32.8	31.5	30.3
85°	23.7	24.1	23.7	22.0	19.6	18.6	17.9	17.3	16.9	16.6	16.6
87.5°	9.0	8.6	7.7	8.4	8.7	8.8	9.2	9.3	9.4	9.6	9.9
90°	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0
92.5°	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8	21.0
95°	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8	21.0
97.5°	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6	42.4
100°	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6	124.4
102.5°	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1	241.8
105°	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5	435.6
110°	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7	494.9



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6	553.6
115°	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2	642.2
117.5°	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1	727.7
120°	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5	782.9
122.5°	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1	835.5
125°	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4	912.3
127.5°	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1	982.6
130°	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1	1028.3
132.5°	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3	1071.1
135°	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4	1133.9
137.5°	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3	1192.4
140°	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8	1228.3
142.5°	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4	1263.5
145°	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0	1313.2
147.5°	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5	1355.8
150°	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5	1383.0
152.5°	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5	1407.0
155°	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3	1440.1
157.5°	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6	1467.5
160°	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5	1484.5
162.5°	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6	1500.0
165°	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6	1520.1
167.5°	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5	1535.3
170°	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1	1543.1
172.5°	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3	1549.2
175°	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7	1555.8
177.5°	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1	1558.5
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	861.2	861.2	865.9	865.5	868.5	867.5	868.0
5°	925.8	931.5	936.6	940.0	945.0	946.5	945.7
7.5°	992.7	1005.5	1011.7	1020.3	1021.8	1026.3	1025.8
10°	1034.1	1046.7	1056.1	1063.6	1067.4	1072.1	1072.5
12.5°	1066.7	1077.3	1085.7	1092.6	1097.2	1098.7	1099.6
15°	1092.1	1103.9	1113.7	1123.6	1129.4	1133.7	1136.1
17.5°	1117.7	1136.0	1153.3	1166.7	1174.7	1181.4	1181.3
20°	1137.5	1158.5	1180.2	1195.4	1210.9	1217.7	1218.8
22.5°	1158.6	1190.7	1218.6	1242.2	1262.8	1269.8	1272.4
25°	1202.5	1244.5	1287.5	1320.7	1344.4	1358.3	1360.4
27.5°	1255.5	1312.4	1357.6	1388.3	1408.0	1418.3	1420.5
30°	1293.0	1345.4	1386.1	1409.2	1418.3	1419.6	1414.5
32.5°	1309.7	1349.0	1365.2	1363.9	1345.9	1334.0	1329.5
35°	1289.2	1281.1	1241.4	1194.0	1157.8	1134.8	1128.6
37.5°	1173.2	1103.1	1030.2	958.6	920.4	901.1	867.7
40°	1058.9	958.9	883.1	822.8	779.8	745.2	737.1
42.5°	929.9	826.7	750.8	699.2	664.9	641.1	630.9
45°	747.3	658.5	595.8	556.2	529.8	512.5	504.7
47.5°	597.6	529.0	483.3	454.0	433.8	418.8	414.6
50°	515.6	460.7	422.0	397.3	382.1	370.6	365.9
52.5°	447.8	403.5	373.8	353.5	339.0	331.8	327.9
55°	369.5	331.3	310.0	293.6	285.5	279.8	277.1
57.5°	302.2	274.6	259.0	247.7	240.2	236.6	235.2
60°	264.6	242.9	228.6	219.8	214.7	210.0	208.7
62.5°	231.2	214.2	203.1	195.5	190.4	188.3	187.5
65°	186.3	175.1	167.0	162.3	158.2	157.5	157.2
67.5°	148.1	141.5	137.2	132.3	130.9	128.5	128.0
70°	126.7	122.3	117.2	115.5	113.8	111.5	111.8
72.5°	107.5	103.1	99.6	97.4	96.8	95.8	96.6
75°	78.6	77.2	75.9	74.2	73.5	73.5	73.2
77.5°	56.1	54.9	53.4	52.4	52.3	50.8	51.4
80°	40.7	39.0	38.3	38.6	37.6	37.3	37.3
82.5°	30.1	29.4	28.8	28.9	28.6	28.4	28.6
85°	16.6	16.2	16.2	16.0	16.0	15.6	15.6
87.5°	10.4	11.0	10.6	10.5	10.6	11.1	11.5
90°	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333672-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)