

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333674-940

Luminaire Tested: **S125RDIW-S610D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333674-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1340U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6905.2 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333674-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333674-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	66	61	56	53	50	43	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	48	43	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333674-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	1.2
10°-20°	235.7	3.4
20°-30°	341.8	5.0
30°-40°	389.6	5.6
40°-50°	379.7	5.5
50°-60°	319.6	4.6
60°-70°	224.1	3.2
70°-80°	115.2	1.7
80°-90°	32.3	0.5
90°-100°	56.6	0.8
100°-110°	348.8	5.1
110°-120°	632.6	9.2
120°-130°	811.9	11.8
130°-140°	873.3	12.6
140°-150°	819.7	11.9
150°-160°	663.1	9.6
160°-170°	428.8	6.2
170°-180°	147.9	2.1
0°-30°	661.9	9.6
0°-40°	1051.5	15.2
0°-60°	1750.9	25.4
0°-90°	2122.4	30.7
90°-120°	1038.1	15.0
90°-150°	3542.9	51.3
90°-180°	4783.0	69.3
0°-180°	6905.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	1	10	18	24	28	4
95°	66	60	18	24	24	84
105°	340	344	344	344	343	360
115°	637	643	644	640	633	632
125°	906	914	914	910	906	809
135°	1130	1137	1135	1132	1126	871
145°	1310	1313	1313	1313	1307	819
155°	1443	1437	1439	1441	1433	665
165°	1523	1516	1517	1523	1515	430
175°	1558	1551	1552	1560	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333674-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.7	12.3	11.9	11.4	11.0	10.9	11.1	11.3	11.6	11.9	12.0
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	17.7	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8
95°	65.8	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8
97.5°	137.4	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6
100°	192.8	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6
102.5°	249.1	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1
105°	339.5	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5
110°	494.2	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7



TEST NUMBER: P333674-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	551.4	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6
115°	637.3	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2
117.5°	726.2	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1
120°	781.6	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5
122.5°	830.5	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1
125°	906.3	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4
127.5°	978.6	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1
130°	1022.9	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1
132.5°	1067.3	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3
135°	1130.3	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4
137.5°	1188.3	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3
140°	1226.1	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8
142.5°	1260.3	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4
145°	1310.4	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0
147.5°	1354.2	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5
150°	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5
152.5°	1408.7	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5
155°	1443.1	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3
157.5°	1469.7	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6
160°	1488.2	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5
162.5°	1503.0	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6
165°	1522.9	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6
167.5°	1537.6	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5
170°	1546.0	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1
172.5°	1551.5	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3
175°	1557.5	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7
177.5°	1560.2	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333674-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	12.3	12.6	12.8	13.0	13.0	13.0	13.1	13.1
90°	21.0	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	21.0	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	21.0	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	42.4	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	124.4	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	241.8	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.6	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.9	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333674-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	553.6	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	642.2	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	727.7	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.9	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.5	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	912.3	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.6	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1028.3	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1071.1	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.9	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.4	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.3	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.5	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.2	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1355.8	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.0	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.0	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.1	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1467.5	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1484.5	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1500.0	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1520.1	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1535.3	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1543.1	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1549.2	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1555.8	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1558.5	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)