

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333483-840

Luminaire Tested: **S125DIW-S1270D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333483-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D1340U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9879.6 lumens  
Efficiency: N/A  
Efficacy: 129.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333483-840

CATALOG NUMBER: S125DIW-S1270D1340U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333483-840

CATALOG NUMBER: S125DIW-S1270D1340U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49	44
2	89	82	76	71	83	76	71	66	65	61	57	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	68	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	18	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333483-840

CATALOG NUMBER: S125DIW-S1270D1340U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.6	1.9
10°-20°	530.1	5.4
20°-30°	782.7	7.9
30°-40°	913.3	9.2
40°-50°	917.2	9.3
50°-60°	805.1	8.1
60°-70°	599.9	6.1
70°-80°	343.0	3.5
80°-90°	103.5	1.0
90°-100°	112.7	1.1
100°-110°	332.9	3.4
110°-120°	563.9	5.7
120°-130°	742.1	7.5
130°-140°	831.6	8.4
140°-150°	815.0	8.2
150°-160°	684.5	6.9
160°-170°	455.0	4.6
170°-180°	159.2	1.6
0°-30°	1500.4	15.2
0°-40°	2413.6	24.4
0°-60°	4136.0	41.9
0°-90°	5182.4	52.5
90°-120°	1009.6	10.2
90°-150°	3398.3	34.4
90°-180°	4697.0	47.5
0°-180°	9879.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	1	12	21	27	31	9
95°	85	88	101	110	113	91
105°	299	305	313	321	325	319
115°	565	570	572	571	570	558
125°	824	831	833	831	829	738
135°	1072	1079	1081	1080	1076	826
145°	1298	1303	1307	1307	1303	811
155°	1486	1486	1487	1491	1486	684
165°	1615	1613	1614	1618	1611	455
175°	1679	1674	1674	1681	1673	160
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333483-840

CATALOG NUMBER: S125DIW-S1270D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.2	34.7	35.2	35.6	36.2	36.5	36.6	36.7	36.9	37.0	37.3
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4
92.5°	31.7	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2
95°	85.1	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9
97.5°	141.5	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5
100°	183.4	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1
102.5°	228.4	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2
105°	298.7	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9
107.5°	376.2	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7
110°	429.7	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0



TEST NUMBER: P333483-840

CATALOG NUMBER: S125DIW-S1270D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.1	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9
115°	564.6	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2
117.5°	645.3	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3
120°	695.6	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5
122.5°	750.1	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6
125°	823.9	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5
127.5°	902.5	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3
130°	949.7	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6
132.5°	996.8	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8
135°	1071.6	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8
137.5°	1141.8	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6
140°	1186.8	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9
142.5°	1231.9	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7
145°	1298.2	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4
147.5°	1359.5	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2
150°	1400.4	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3
152.5°	1433.9	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6
155°	1485.5	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9
157.5°	1531.6	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2
160°	1558.8	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4
162.5°	1583.0	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8
165°	1615.2	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1
167.5°	1642.4	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9
170°	1657.1	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7
172.5°	1667.6	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1
175°	1679.4	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9
177.5°	1685.4	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333483-840

CATALOG NUMBER: S125DIW-S1270D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	37.6	37.8	38.1	38.1	37.7	37.3	36.9	36.6
90°	23.8	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	54.1	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	104.9	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	164.4	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	205.7	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	248.0	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	316.6	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	390.5	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	441.9	442.7	443.6	443.9	443.6	443.3	443.0	442.7





TEST NUMBER: P333483-840

CATALOG NUMBER: S125DIW-S1270D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.3	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.9	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.5	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.4	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.9	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	908.0	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.3	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.5	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.0	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1198.5	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.0	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1366.9	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.2	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1489.1	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1532.4	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1558.5	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1583.2	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1616.2	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1640.7	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1655.4	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1665.9	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1677.6	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1682.9	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)