

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333675-940

Luminaire Tested: **S125RDIW-S610D1340U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333675-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1340U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6270.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333675-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333675-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	20	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	23	27	22	19	22	18	16	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333675-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	1.3
10°-20°	235.7	3.8
20°-30°	341.8	5.5
30°-40°	389.6	6.2
40°-50°	379.7	6.1
50°-60°	319.6	5.1
60°-70°	224.1	3.6
70°-80°	115.2	1.8
80°-90°	32.3	0.5
90°-100°	99.5	1.6
100°-110°	294.0	4.7
110°-120°	497.9	7.9
120°-130°	655.3	10.5
130°-140°	734.3	11.7
140°-150°	719.7	11.5
150°-160°	604.5	9.6
160°-170°	401.8	6.4
170°-180°	140.6	2.2
0°-30°	661.9	10.6
0°-40°	1051.5	16.8
0°-60°	1750.9	27.9
0°-90°	2122.4	33.9
90°-120°	891.4	14.2
90°-150°	3000.7	47.9
90°-180°	4148.0	66.2
0°-180°	6270.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	1	10	18	24	28	6
95°	75	78	89	97	100	80
105°	264	270	276	283	287	282
115°	499	503	506	504	503	493
125°	728	734	736	733	732	651
135°	946	953	954	954	950	729
145°	1146	1151	1154	1154	1151	716
155°	1312	1312	1313	1317	1312	604
165°	1426	1424	1425	1429	1423	402
175°	1483	1479	1478	1484	1477	141
180°	1486	1486	1486	1486	1486	



TEST NUMBER: P333675-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.7	12.3	11.9	11.4	11.0	10.9	11.1	11.3	11.6	11.9	12.1
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	28.0	29.4	30.9	32.3	33.7	35.6	37.8	40.0	42.2	44.4	46.1
95°	75.2	75.7	76.2	76.7	77.2	78.8	81.3	83.9	86.5	89.1	90.9
97.5°	124.9	125.1	125.4	125.6	125.7	127.6	131.2	134.7	138.3	141.8	143.5
100°	161.9	161.9	161.9	161.9	161.9	163.6	166.9	170.3	173.6	177.0	179.3
102.5°	201.7	202.8	203.8	204.8	205.8	207.2	208.9	210.6	212.3	214.0	216.5
105°	263.8	265.0	266.3	267.6	268.9	270.3	271.8	273.4	274.9	276.4	278.0
107.5°	332.2	333.5	334.7	336.1	337.3	338.6	339.7	340.9	342.1	343.3	344.1
110°	379.4	380.7	382.0	383.3	384.5	385.6	386.4	387.1	387.9	388.6	389.4



TEST NUMBER: P333675-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	427.5	428.2	428.8	429.5	430.2	431.1	431.9	432.9	433.9	434.9	435.2
115°	498.6	499.5	500.6	501.6	502.7	503.5	503.9	504.4	505.0	505.5	505.2
117.5°	569.8	570.2	570.7	571.1	571.7	572.1	572.6	573.0	573.5	574.0	574.2
120°	614.2	615.5	616.8	618.0	619.4	620.1	620.4	620.6	620.9	621.2	621.2
122.5°	662.4	662.8	663.3	663.7	664.1	664.8	665.4	666.1	666.7	667.4	667.2
125°	727.5	729.1	730.7	732.2	733.7	734.6	734.9	735.1	735.4	735.7	735.1
127.5°	796.9	797.8	798.7	799.6	800.5	801.0	801.4	801.6	802.0	802.3	802.0
130°	838.6	839.9	841.2	842.5	843.7	844.6	845.2	845.7	846.1	846.7	846.4
132.5°	880.2	882.3	884.5	886.5	888.7	889.7	889.6	889.5	889.4	889.3	889.0
135°	946.2	947.7	949.2	950.8	952.3	953.2	953.5	953.8	954.0	954.3	954.3
137.5°	1008.2	1009.7	1011.2	1012.6	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7
140°	1047.9	1049.3	1050.5	1051.9	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7
142.5°	1087.8	1088.9	1089.9	1091.0	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3
145°	1146.3	1147.3	1148.3	1149.3	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4
147.5°	1200.4	1201.0	1201.6	1202.1	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4
150°	1236.5	1236.3	1236.0	1235.7	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0
152.5°	1266.1	1266.5	1266.9	1267.2	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2
155°	1311.7	1311.7	1311.7	1311.7	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8
157.5°	1352.4	1351.8	1351.3	1350.7	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0
160°	1376.4	1375.7	1374.9	1374.1	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2
162.5°	1397.8	1397.2	1396.6	1396.1	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7
165°	1426.2	1425.7	1425.1	1424.7	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1
167.5°	1450.3	1449.2	1448.2	1447.2	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2
170°	1463.2	1462.2	1461.2	1460.2	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2
172.5°	1472.5	1471.4	1470.4	1469.4	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4
175°	1482.9	1481.8	1480.9	1479.8	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8
177.5°	1488.2	1487.4	1486.6	1485.8	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333675-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	12.3	12.6	12.8	13.0	13.0	13.1	13.1	13.1
90°	21.0	22.4	23.6	24.7	25.4	26.2	27.0	27.7
92.5°	47.8	49.5	51.2	52.3	52.9	53.5	54.0	54.6
95°	92.6	94.4	96.3	97.4	97.9	98.4	99.0	99.5
97.5°	145.2	146.9	148.6	149.6	149.9	150.3	150.5	150.9
100°	181.6	183.9	186.2	187.6	188.2	188.7	189.2	189.7
102.5°	219.0	221.5	224.1	225.7	226.4	227.1	227.8	228.5
105°	279.6	281.1	282.6	283.7	284.5	285.3	286.1	286.9
107.5°	344.8	345.6	346.4	346.8	346.7	346.6	346.6	346.5
110°	390.2	390.9	391.7	392.0	391.7	391.5	391.2	390.9



TEST NUMBER: P333675-940

CATALOG NUMBER: S125RDIW-S610D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.6	436.0	436.3	436.3	435.9	435.4	434.9	434.4
115°	505.0	504.7	504.4	504.2	503.9	503.6	503.5	503.2
117.5°	574.4	574.5	574.8	574.4	573.4	572.3	571.3	570.2
120°	621.2	621.2	621.2	620.6	619.6	618.6	617.5	616.5
122.5°	667.0	666.8	666.6	666.1	665.2	664.4	663.6	662.8
125°	734.6	734.1	733.6	733.3	733.0	732.7	732.5	732.2
127.5°	801.7	801.5	801.3	800.8	800.4	799.9	799.3	798.8
130°	846.1	846.0	845.7	845.3	844.8	844.3	843.7	843.2
132.5°	888.8	888.5	888.2	887.8	887.1	886.3	885.6	884.8
135°	954.3	954.3	954.3	953.8	952.7	951.7	950.7	949.7
137.5°	1018.1	1018.3	1018.7	1018.2	1016.9	1015.6	1014.3	1013.1
140°	1058.3	1058.7	1059.3	1058.9	1057.6	1056.3	1055.1	1053.7
142.5°	1097.6	1098.0	1098.2	1097.8	1096.4	1095.2	1093.9	1092.6
145°	1154.4	1154.4	1154.4	1154.0	1153.2	1152.4	1151.6	1150.9
147.5°	1206.9	1207.6	1208.2	1207.6	1205.9	1204.2	1202.4	1200.7
150°	1240.0	1240.0	1240.0	1239.7	1239.2	1238.7	1238.1	1237.7
152.5°	1270.8	1271.4	1272.0	1271.9	1271.0	1270.1	1269.1	1268.2
155°	1314.9	1315.9	1317.0	1316.8	1315.5	1314.3	1313.0	1311.7
157.5°	1353.1	1354.1	1355.1	1354.8	1353.1	1351.4	1349.7	1348.0
160°	1376.2	1377.2	1378.2	1378.1	1376.9	1375.6	1374.3	1373.0
162.5°	1397.9	1399.1	1400.3	1400.3	1398.7	1397.2	1395.8	1394.3
165°	1427.1	1428.2	1429.1	1428.9	1427.4	1425.8	1424.2	1422.7
167.5°	1448.8	1450.3	1451.8	1451.8	1450.2	1448.6	1447.0	1445.4
170°	1461.7	1463.2	1464.7	1464.6	1462.9	1461.1	1459.2	1457.4
172.5°	1471.0	1472.5	1474.0	1474.0	1472.4	1470.8	1469.2	1467.6
175°	1481.3	1482.9	1484.4	1484.3	1482.5	1480.7	1478.9	1477.1
177.5°	1486.0	1487.3	1488.5	1488.4	1486.9	1485.5	1484.1	1482.6
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4

(END OF REPORT)