

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333471-840

Luminaire Tested: **S125DIW-S1270D770U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333471-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D770U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7868.9 lumens  
Efficiency: N/A  
Efficacy: 131.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333471-840

CATALOG NUMBER: S125DIW-S1270D770U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333471-840

CATALOG NUMBER: S125DIW-S1270D770U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	60	55
2	92	84	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	55	50	45	49	45	41	43	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	32	41	35	30	36	31	28	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	26	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333471-840

CATALOG NUMBER: S125DIW-S1270D770U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.6	2.4
10°-20°	530.1	6.7
20°-30°	782.7	9.9
30°-40°	913.3	11.6
40°-50°	917.2	11.7
50°-60°	805.1	10.2
60°-70°	599.9	7.6
70°-80°	343.0	4.4
80°-90°	101.9	1.3
90°-100°	64.5	0.8
100°-110°	190.5	2.4
110°-120°	322.7	4.1
120°-130°	424.7	5.4
130°-140°	475.9	6.0
140°-150°	466.4	5.9
150°-160°	391.7	5.0
160°-170°	260.4	3.3
170°-180°	91.1	1.2
0°-30°	1500.4	19.1
0°-40°	2413.6	30.7
0°-60°	4136.0	52.6
0°-90°	5180.9	65.8
90°-120°	577.8	7.3
90°-150°	1944.8	24.7
90°-180°	2688.0	34.2
0°-180°	7868.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	1	7	12	16	18	7
95°	49	51	58	63	64	52
105°	171	175	179	184	186	183
115°	323	326	328	327	326	319
125°	472	476	477	475	474	422
135°	613	618	618	618	616	472
145°	743	746	748	748	746	464
155°	850	850	851	853	850	391
165°	924	923	924	926	922	261
175°	961	958	958	962	957	91
180°	963	963	963	963	963	



TEST NUMBER: P333471-840

CATALOG NUMBER: S125DIW-S1270D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.1	34.4	34.7	34.9	35.2	35.3	35.2	35.2	35.2	35.1	35.3
90°	0.7	2.1	3.4	4.7	6.1	7.4	8.5	9.7	10.8	12.0	12.8
92.5°	18.2	19.1	20.0	20.9	21.9	23.0	24.5	26.0	27.4	28.8	29.9
95°	48.8	49.1	49.4	49.7	50.1	51.1	52.7	54.4	56.0	57.8	58.9
97.5°	81.0	81.1	81.2	81.4	81.5	82.7	85.0	87.4	89.6	91.9	93.0
100°	104.9	104.9	104.9	104.9	104.9	106.0	108.2	110.4	112.5	114.7	116.2
102.5°	130.8	131.4	132.1	132.7	133.4	134.3	135.4	136.5	137.5	138.7	140.4
105°	171.0	171.8	172.6	173.4	174.3	175.2	176.2	177.1	178.1	179.2	180.2
107.5°	215.3	216.1	217.0	217.8	218.6	219.4	220.3	221.0	221.8	222.5	223.0
110°	245.9	246.7	247.5	248.4	249.2	249.8	250.3	250.9	251.4	251.9	252.4



TEST NUMBER: P333471-840

CATALOG NUMBER: S125DIW-S1270D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.1	277.5	277.9	278.4	278.8	279.3	279.9	280.6	281.2	281.9	282.2
115°	323.2	323.8	324.5	325.1	325.8	326.3	326.6	326.9	327.3	327.6	327.4
117.5°	369.3	369.6	369.9	370.2	370.5	370.8	371.1	371.4	371.7	372.0	372.1
120°	398.1	398.9	399.7	400.6	401.4	401.9	402.0	402.2	402.4	402.5	402.5
122.5°	429.3	429.6	429.9	430.2	430.5	430.8	431.2	431.7	432.1	432.5	432.4
125°	471.5	472.5	473.5	474.5	475.5	476.2	476.3	476.5	476.7	476.8	476.5
127.5°	516.5	517.1	517.7	518.3	518.8	519.2	519.4	519.6	519.8	520.0	519.8
130°	543.5	544.3	545.2	546.0	546.8	547.4	547.8	548.1	548.5	548.8	548.6
132.5°	570.5	571.9	573.2	574.6	575.9	576.6	576.5	576.4	576.4	576.3	576.2
135°	613.2	614.2	615.2	616.2	617.2	617.8	617.9	618.1	618.3	618.4	618.4
137.5°	653.4	654.4	655.3	656.3	657.3	657.9	658.3	658.6	659.0	659.4	659.6
140°	679.2	680.0	680.9	681.7	682.6	683.2	683.7	684.2	684.7	685.2	685.5
142.5°	705.0	705.7	706.4	707.1	707.8	708.4	709.1	709.7	710.3	710.9	711.1
145°	743.0	743.6	744.3	744.9	745.6	746.2	746.7	747.2	747.7	748.2	748.2
147.5°	778.0	778.4	778.7	779.1	779.5	779.8	780.2	780.6	781.0	781.4	781.8
150°	801.4	801.2	801.0	800.9	800.7	801.0	801.6	802.3	802.9	803.7	803.7
152.5°	820.6	820.8	821.0	821.3	821.5	821.7	822.0	822.3	822.5	822.8	823.2
155°	850.1	850.1	850.1	850.1	850.1	850.2	850.4	850.5	850.7	850.9	851.5
157.5°	876.6	876.2	875.8	875.5	875.0	874.9	875.1	875.3	875.5	875.7	876.3
160°	892.1	891.6	891.1	890.6	890.1	889.9	890.1	890.3	890.4	890.6	891.3
162.5°	905.9	905.5	905.1	904.8	904.4	904.2	904.3	904.3	904.3	904.4	905.2
165°	924.3	924.0	923.7	923.3	923.0	922.9	923.1	923.2	923.4	923.6	924.2
167.5°	940.0	939.3	938.6	938.0	937.3	937.0	937.0	937.0	937.0	937.0	938.0
170°	948.4	947.7	947.0	946.3	945.6	945.3	945.3	945.3	945.3	945.3	946.3
172.5°	954.3	953.6	953.0	952.3	951.7	951.3	951.3	951.3	951.3	951.3	952.3
175°	961.1	960.4	959.8	959.1	958.4	958.1	958.1	958.1	958.1	958.1	959.1
177.5°	964.5	964.0	963.4	962.9	962.4	962.1	961.9	961.8	961.7	961.5	962.3
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333471-840

CATALOG NUMBER: S125DIW-S1270D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	35.4	35.6	35.9	35.6	35.2	34.7	34.3	33.8
90°	13.6	14.5	15.3	16.0	16.5	17.0	17.5	18.0
92.5°	31.0	32.1	33.2	33.9	34.3	34.6	35.0	35.3
95°	60.1	61.2	62.4	63.1	63.5	63.8	64.1	64.4
97.5°	94.1	95.2	96.3	96.9	97.1	97.4	97.6	97.8
100°	117.6	119.2	120.7	121.6	122.0	122.3	122.6	122.9
102.5°	142.0	143.6	145.2	146.2	146.7	147.2	147.6	148.1
105°	181.2	182.2	183.2	183.9	184.4	184.9	185.4	185.9
107.5°	223.5	224.0	224.5	224.7	224.7	224.7	224.6	224.6
110°	252.9	253.4	253.9	254.1	253.9	253.7	253.6	253.4





TEST NUMBER: P333471-840

CATALOG NUMBER: S125DIW-S1270D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	282.4	282.6	282.8	282.8	282.5	282.2	281.9	281.6
115°	327.3	327.1	326.9	326.8	326.6	326.5	326.3	326.1
117.5°	372.2	372.3	372.5	372.2	371.6	370.9	370.2	369.6
120°	402.5	402.5	402.5	402.2	401.6	400.9	400.2	399.6
122.5°	432.3	432.1	432.0	431.7	431.1	430.6	430.1	429.6
125°	476.2	475.7	475.4	475.2	475.0	474.8	474.7	474.5
127.5°	519.7	519.5	519.3	519.1	518.8	518.4	518.1	517.8
130°	548.5	548.3	548.1	547.9	547.5	547.1	546.8	546.5
132.5°	576.0	575.8	575.7	575.3	574.9	574.4	574.0	573.5
135°	618.4	618.4	618.4	618.1	617.4	616.8	616.1	615.5
137.5°	659.8	660.0	660.2	659.8	659.0	658.2	657.4	656.5
140°	685.9	686.2	686.5	686.3	685.5	684.6	683.8	683.0
142.5°	711.3	711.6	711.8	711.4	710.6	709.8	708.9	708.1
145°	748.2	748.2	748.2	747.9	747.4	746.9	746.4	745.9
147.5°	782.2	782.6	783.0	782.6	781.5	780.4	779.3	778.2
150°	803.7	803.7	803.7	803.4	803.1	802.8	802.4	802.1
152.5°	823.6	824.0	824.5	824.4	823.7	823.1	822.5	821.9
155°	852.2	852.8	853.5	853.4	852.6	851.8	850.9	850.1
157.5°	877.0	877.6	878.3	878.1	877.0	875.9	874.7	873.6
160°	891.9	892.6	893.2	893.2	892.3	891.5	890.7	889.9
162.5°	906.1	906.8	907.6	907.6	906.6	905.5	904.6	903.6
165°	924.9	925.6	926.2	926.0	925.1	924.1	923.1	922.1
167.5°	939.0	940.0	940.9	940.9	939.9	938.9	937.9	936.8
170°	947.4	948.4	949.4	949.3	948.1	947.0	945.7	944.6
172.5°	953.3	954.3	955.3	955.3	954.3	953.2	952.2	951.2
175°	960.1	961.1	962.1	962.0	960.8	959.7	958.5	957.4
177.5°	963.1	963.9	964.7	964.6	963.7	962.8	961.9	960.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3

(END OF REPORT)