

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333356-840

Luminaire Tested: **S125DIW-S375D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333356-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1050U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5769.0 lumens
Efficiency: N/A
Efficacy: 151.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333356-840

CATALOG NUMBER: S125DIW-S375D1050U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333356-840

CATALOG NUMBER: S125DIW-S375D1050U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	31	30	29	22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24	19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3810	3810	3810
5°	3818	3782	3806
10°	3796	3756	3777
15°	3754	3710	3726
20°	3696	3647	3654
25°	3632	3572	3569
30°	3554	3491	3473
35°	3470	3404	3356
40°	3384	3309	3262
45°	3291	3222	3159
50°	3189	3118	3024
55°	3090	3001	2916
60°	2971	2882	2780
65°	2832	2740	2647
70°	2696	2574	2485
75°	2458	2376	2293
80°	2187	2153	2101
85°	1904	1941	1830



TEST NUMBER: P333356-840

CATALOG NUMBER: S125DIW-S375D1050U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.0
10°-20°	157.1	2.7
20°-30°	232.0	4.0
30°-40°	270.7	4.7
40°-50°	271.9	4.7
50°-60°	238.7	4.1
60°-70°	177.8	3.1
70°-80°	101.7	1.8
80°-90°	32.4	0.6
90°-100°	50.1	0.9
100°-110°	308.6	5.3
110°-120°	559.7	9.7
120°-130°	718.2	12.5
130°-140°	772.5	13.4
140°-150°	725.1	12.6
150°-160°	586.6	10.2
160°-170°	379.4	6.6
170°-180°	130.8	2.3
0°-30°	444.7	7.7
0°-40°	715.5	12.4
0°-60°	1226.0	21.3
0°-90°	1538.0	26.7
90°-120°	918.3	15.9
90°-150°	3134.2	54.3
90°-180°	4231.0	73.3
0°-180°	5769.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	589	588	583	587	587	56
15°	562	560	555	557	557	158
25°	510	507	501	502	501	234
35°	440	438	432	429	426	275
45°	360	358	353	348	346	278
55°	274	273	266	262	259	245
65°	185	184	179	175	173	184
75°	98	98	95	94	92	105
85°	26	26	26	26	25	29
90°	1	9	16	21	24	4
95°	58	53	16	21	21	74
105°	300	304	304	304	303	318
115°	564	569	570	566	560	559
125°	802	808	809	805	802	716
135°	1000	1006	1004	1002	996	770
145°	1159	1161	1161	1162	1156	725
155°	1277	1271	1273	1275	1268	588
165°	1347	1341	1342	1347	1340	380
175°	1378	1372	1373	1380	1372	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P333356-840

CATALOG NUMBER: S125DIW-S375D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	591.4	591.2	591.0	590.7	590.5	589.9	589.1	588.2	587.4	586.5	587.4
5°	589.0	588.8	588.5	588.3	588.1	587.5	586.5	585.5	584.4	583.4	584.3
7.5°	583.6	583.4	583.2	583.0	582.8	582.1	581.0	579.8	578.7	577.5	578.5
10°	578.8	578.6	578.3	578.1	577.9	577.2	576.1	574.9	573.8	572.7	573.5
12.5°	572.8	572.4	572.0	571.7	571.3	570.6	569.5	568.5	567.3	566.3	566.9
15°	561.5	561.2	560.9	560.6	560.2	559.5	558.4	557.2	556.0	554.9	555.4
17.5°	548.5	548.1	547.5	547.1	546.6	545.8	544.6	543.5	542.3	541.1	541.8
20°	537.7	537.5	537.2	537.0	536.8	536.0	534.7	533.3	532.0	530.7	531.4
22.5°	526.8	526.4	526.0	525.7	525.3	524.5	523.2	522.0	520.7	519.5	520.0
25°	509.7	509.2	508.6	508.1	507.6	506.6	505.3	503.9	502.6	501.3	501.5
27.5°	489.6	489.3	489.0	488.7	488.4	487.5	486.1	484.7	483.3	481.9	482.0
30°	476.6	476.3	475.8	475.5	475.2	474.3	472.8	471.2	469.7	468.1	467.9
32.5°	462.3	461.8	461.4	460.9	460.4	459.5	458.1	456.7	455.3	453.9	453.5
35°	440.1	439.7	439.3	438.9	438.5	437.5	436.1	434.6	433.1	431.7	431.2
37.5°	417.1	416.6	416.1	415.5	415.0	414.0	412.6	411.3	409.9	408.6	407.8
40°	401.4	400.8	400.3	399.8	399.3	398.3	396.9	395.5	393.9	392.5	391.6
42.5°	384.6	384.2	383.7	383.2	382.8	381.9	380.4	379.0	377.5	376.1	375.3
45°	360.3	359.9	359.5	359.1	358.6	357.8	356.6	355.4	354.1	352.8	351.6
47.5°	334.2	334.2	334.2	334.3	334.3	333.6	332.0	330.5	329.0	327.5	326.3
50°	317.4	317.1	316.8	316.4	316.1	315.4	314.1	312.9	311.6	310.3	309.0
52.5°	300.2	299.9	299.7	299.5	299.3	298.5	297.2	295.9	294.5	293.2	292.1
55°	274.4	274.1	273.8	273.5	273.2	272.3	270.8	269.4	267.9	266.5	265.6
57.5°	247.3	247.1	246.9	246.8	246.6	245.9	244.7	243.5	242.3	241.1	239.8
60°	230.0	229.6	229.2	228.8	228.4	227.6	226.5	225.4	224.2	223.1	222.1
62.5°	212.2	211.9	211.5	211.2	210.9	210.2	209.2	208.2	207.2	206.3	205.2
65°	185.3	185.1	184.9	184.7	184.5	183.8	182.7	181.5	180.4	179.3	178.2
67.5°	159.3	158.9	158.3	157.9	157.5	156.8	156.0	155.1	154.3	153.5	152.7
70°	142.8	142.3	141.8	141.3	140.8	140.0	139.1	138.1	137.2	136.3	135.6
72.5°	124.9	124.5	124.2	123.8	123.5	123.0	122.4	121.8	121.2	120.6	119.9
75°	98.5	98.3	98.1	97.9	97.7	97.3	96.7	96.2	95.7	95.2	94.9
77.5°	74.1	74.0	73.9	73.8	73.8	73.6	73.3	73.0	72.7	72.4	72.2
80°	58.8	58.8	58.8	58.8	58.8	58.7	58.5	58.3	58.1	57.9	57.8
82.5°	45.3	45.2	45.0	44.8	44.7	44.6	44.5	44.5	44.4	44.4	44.2
85°	25.7	25.8	25.9	26.0	26.1	26.2	26.2	26.2	26.2	26.2	26.1
87.5°	10.3	10.6	11.0	11.4	11.7	12.0	12.3	12.5	12.7	12.9	13.2
90°	1.0	2.8	4.6	6.5	8.3	10.0	11.6	13.1	14.7	16.4	17.5
92.5°	15.8	14.4	13.2	11.9	10.6	10.7	12.1	13.5	14.9	16.4	17.5
95°	58.2	57.6	56.9	56.1	55.5	50.8	42.2	33.6	24.9	16.4	17.5
97.5°	121.6	122.8	124.0	125.2	126.4	118.6	101.5	84.4	67.4	50.3	43.8
100°	170.6	171.3	171.9	172.6	173.3	174.1	175.0	175.9	176.8	177.7	143.9
102.5°	220.5	221.3	222.2	223.0	223.9	224.6	225.1	225.6	226.2	226.7	220.4
105°	300.2	301.1	302.1	303.0	303.9	304.4	304.4	304.4	304.4	304.4	304.4
107.5°	383.2	383.2	383.2	383.2	383.2	383.4	383.8	384.4	384.8	385.3	385.3
110°	437.2	437.2	437.2	437.2	437.2	437.4	437.8	438.3	438.7	439.2	438.5



TEST NUMBER: P333356-840

CATALOG NUMBER: S125DIW-S375D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	488.4	488.9	489.4	490.0	490.4	490.7	490.9	491.2	491.5	490.6
115°	563.8	564.9	566.0	567.1	568.4	569.0	569.3	569.5	569.7	569.9	569.0
117.5°	642.5	642.4	642.4	642.3	642.3	642.7	643.5	644.4	645.2	646.1	644.9
120°	691.5	691.3	690.9	690.7	690.5	690.7	691.5	692.2	692.8	693.5	693.1
122.5°	734.8	735.6	736.5	737.3	738.2	738.8	739.1	739.4	739.7	740.0	739.6
125°	801.7	803.3	805.0	806.5	808.1	808.9	808.9	808.9	808.9	808.9	808.0
127.5°	865.7	866.9	868.0	869.1	870.2	870.7	870.6	870.5	870.3	870.2	869.7
130°	904.9	906.1	907.2	908.3	909.5	910.1	910.4	910.6	910.8	911.0	910.4
132.5°	944.1	945.4	946.7	948.1	949.4	949.8	949.3	948.8	948.3	947.9	947.7
135°	999.9	1001.3	1002.6	1004.0	1005.3	1005.8	1005.3	1004.9	1004.4	1004.0	1003.5
137.5°	1051.2	1052.4	1053.5	1054.7	1055.9	1056.3	1055.9	1055.5	1055.0	1054.6	1054.7
140°	1084.7	1085.1	1085.6	1086.0	1086.5	1086.6	1086.4	1086.1	1085.9	1085.7	1086.1
142.5°	1114.9	1115.2	1115.5	1115.7	1116.0	1116.3	1116.6	1116.9	1117.2	1117.5	1117.6
145°	1159.2	1159.7	1160.1	1160.6	1161.0	1161.2	1161.2	1161.2	1161.2	1161.2	1161.5
147.5°	1198.0	1198.0	1197.9	1197.8	1197.7	1197.8	1198.0	1198.3	1198.6	1198.8	1199.1
150°	1222.5	1222.1	1221.6	1221.2	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5	1223.0
152.5°	1246.3	1245.3	1244.3	1243.2	1242.2	1242.0	1242.4	1242.9	1243.3	1243.7	1244.3
155°	1276.7	1275.4	1273.9	1272.6	1271.2	1270.8	1271.2	1271.7	1272.1	1272.6	1273.2
157.5°	1300.2	1299.4	1298.6	1297.8	1296.9	1296.6	1296.6	1296.6	1296.7	1296.7	1297.5
160°	1316.6	1315.1	1313.8	1312.4	1311.1	1310.5	1310.7	1311.0	1311.2	1311.4	1312.3
162.5°	1329.6	1328.3	1326.9	1325.5	1324.1	1323.5	1323.8	1324.0	1324.2	1324.4	1325.8
165°	1347.2	1345.8	1344.4	1343.1	1341.7	1341.1	1341.4	1341.6	1341.8	1342.0	1343.4
167.5°	1360.2	1358.9	1357.5	1356.0	1354.6	1354.0	1354.2	1354.4	1354.7	1354.9	1356.6
170°	1367.6	1366.0	1364.4	1362.8	1361.2	1360.6	1360.8	1361.0	1361.2	1361.5	1363.3
172.5°	1372.5	1370.9	1369.3	1367.8	1366.1	1365.5	1365.9	1366.3	1366.8	1367.2	1368.8
175°	1377.8	1376.4	1375.0	1373.7	1372.3	1371.8	1372.0	1372.2	1372.5	1372.7	1374.5
177.5°	1380.3	1379.2	1378.1	1377.0	1375.9	1375.4	1375.6	1375.8	1375.9	1376.1	1377.5
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333356-840

CATALOG NUMBER: S125DIW-S375D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	588.2	589.1	589.9	590.3	590.2	590.1	590.1	590.0
5°	585.2	586.2	587.1	587.5	587.4	587.3	587.2	587.1
7.5°	579.4	580.3	581.2	581.6	581.5	581.4	581.3	581.2
10°	574.3	575.1	576.0	576.3	576.2	576.1	576.0	575.9
12.5°	567.6	568.4	569.0	569.3	569.3	569.3	569.3	569.2
15°	555.9	556.4	557.0	557.2	557.2	557.2	557.2	557.2
17.5°	542.4	543.0	543.7	543.7	543.2	542.7	542.2	541.7
20°	532.1	532.8	533.5	533.7	533.1	532.6	532.1	531.6
22.5°	520.4	520.9	521.4	521.4	521.1	520.7	520.4	520.0
25°	501.7	501.9	502.1	502.0	501.7	501.4	501.1	500.8
27.5°	482.0	482.0	482.1	482.0	481.6	481.3	481.0	480.7
30°	467.7	467.5	467.3	467.1	466.8	466.5	466.1	465.7
32.5°	453.2	452.8	452.4	452.0	451.4	450.8	450.3	449.7
35°	430.7	430.2	429.6	429.0	428.2	427.3	426.5	425.7
37.5°	407.1	406.3	405.5	404.9	404.3	403.9	403.4	402.9
40°	390.6	389.7	388.8	388.2	387.9	387.5	387.2	386.9
42.5°	374.4	373.5	372.6	372.0	371.5	371.0	370.6	370.1
45°	350.3	349.1	347.9	347.1	346.8	346.5	346.2	345.9
47.5°	325.0	323.8	322.4	321.4	320.7	320.0	319.3	318.6
50°	307.7	306.3	305.0	304.0	303.2	302.5	301.7	301.0
52.5°	290.8	289.6	288.4	287.5	286.7	285.9	285.1	284.3
55°	264.6	263.7	262.8	262.0	261.3	260.4	259.7	259.0
57.5°	238.6	237.4	236.2	235.4	235.0	234.6	234.2	233.8
60°	221.1	219.9	218.9	218.0	217.3	216.6	215.9	215.2
62.5°	204.1	202.9	201.8	201.0	200.5	199.9	199.2	198.7
65°	177.3	176.4	175.5	174.8	174.4	174.0	173.6	173.2
67.5°	151.9	151.1	150.3	149.8	149.6	149.3	149.1	148.8
70°	135.0	134.4	133.8	133.3	132.9	132.5	132.0	131.6
72.5°	119.2	118.5	117.8	117.2	116.8	116.4	115.9	115.5
75°	94.6	94.3	93.9	93.6	93.2	92.8	92.4	91.9
77.5°	72.1	71.9	71.7	71.5	71.2	70.9	70.6	70.3
80°	57.7	57.6	57.5	57.3	57.1	56.9	56.7	56.5
82.5°	44.0	43.8	43.7	43.5	43.5	43.5	43.4	43.4
85°	26.0	25.9	25.8	25.5	25.3	25.1	24.9	24.7
87.5°	13.4	13.6	13.8	13.9	13.9	13.9	13.9	13.8
90°	18.6	19.8	20.9	21.8	22.5	23.1	23.8	24.5
92.5°	18.6	19.8	20.9	21.6	21.9	22.2	22.5	22.9
95°	18.6	19.8	20.9	21.4	21.4	21.4	21.4	21.4
97.5°	37.5	31.0	24.6	21.4	21.4	21.4	21.4	21.4
100°	110.1	76.2	42.4	25.0	24.1	23.2	22.3	21.4
102.5°	213.9	207.5	201.2	190.3	174.8	159.4	143.9	128.5
105°	304.4	304.4	304.4	304.3	304.1	303.8	303.6	303.4
107.5°	385.4	385.4	385.5	385.2	384.5	383.7	383.0	382.4
110°	437.8	437.2	436.5	436.3	436.5	436.7	436.9	437.2



TEST NUMBER: P333356-840

CATALOG NUMBER: S125DIW-S375D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	489.8	488.9	488.1	487.5	487.2	486.8	486.5	486.1
115°	568.0	567.1	566.2	565.1	563.8	562.4	561.1	559.7
117.5°	643.8	642.6	641.4	640.5	640.0	639.3	638.7	638.1
120°	692.6	692.2	691.7	690.8	689.7	688.6	687.5	686.3
122.5°	739.1	738.7	738.2	737.4	736.1	734.8	733.5	732.2
125°	807.1	806.2	805.3	804.5	803.9	803.1	802.4	801.7
127.5°	869.2	868.7	868.2	867.1	865.5	863.7	862.0	860.4
130°	909.7	909.0	908.3	907.4	906.3	905.1	904.0	902.9
132.5°	947.6	947.4	947.3	946.6	945.5	944.3	943.2	942.1
135°	1003.1	1002.6	1002.2	1001.3	999.9	998.6	997.1	995.8
137.5°	1054.8	1054.9	1055.0	1054.5	1053.3	1052.1	1051.0	1049.8
140°	1086.6	1087.0	1087.5	1087.0	1085.7	1084.3	1083.0	1081.6
142.5°	1117.7	1117.8	1117.9	1117.3	1115.9	1114.6	1113.2	1111.9
145°	1161.7	1162.0	1162.2	1161.6	1160.2	1158.9	1157.5	1156.2
147.5°	1199.4	1199.7	1199.9	1199.3	1197.6	1196.0	1194.4	1192.8
150°	1223.5	1224.0	1224.4	1223.7	1221.8	1220.0	1218.2	1216.4
152.5°	1244.7	1245.2	1245.6	1245.1	1243.3	1241.7	1240.1	1238.5
155°	1273.9	1274.7	1275.4	1274.8	1272.9	1271.1	1269.3	1267.5
157.5°	1298.2	1298.9	1299.6	1299.1	1297.3	1295.5	1293.6	1291.8
160°	1313.2	1314.1	1315.0	1314.5	1312.8	1311.0	1309.2	1307.4
162.5°	1327.1	1328.3	1329.6	1329.2	1327.2	1325.2	1323.2	1321.2
165°	1344.7	1346.2	1347.5	1347.3	1345.4	1343.6	1341.8	1340.0
167.5°	1358.2	1359.8	1361.5	1361.3	1359.2	1357.2	1355.1	1353.1
170°	1365.1	1367.0	1368.8	1368.6	1366.5	1364.5	1362.5	1360.4
172.5°	1370.5	1372.1	1373.7	1373.5	1371.5	1369.4	1367.4	1365.3
175°	1376.3	1378.2	1380.0	1379.9	1377.8	1375.7	1373.7	1371.7
177.5°	1378.7	1380.0	1381.3	1381.2	1379.7	1378.3	1376.8	1375.3
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8

(END OF REPORT)