

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333686-940

Luminaire Tested: **S125RDIW-S850D770U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333686-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D770U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5635.7 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333686-940

CATALOG NUMBER: S125RDIW-S850D770U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333686-940

CATALOG NUMBER: S125RDIW-S850D770U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	42	37
3	82	73	65	60	76	67	61	56	58	53	49	49	45	42	40	38	36	32
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	57	49	43	64	54	46	41	46	40	36	39	35	32	33	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7919	7919	7919
5°	7937	7847	7895
10°	7877	7774	7774
15°	7783	7616	7554
20°	7663	7396	7307
25°	7524	7180	7021
30°	7348	6927	6706
35°	7171	6666	6352
40°	7003	6395	6004
45°	6801	6090	5624
50°	6597	5760	5230
55°	6361	5443	4808
60°	6124	5059	4354
65°	5845	4614	3834
70°	5527	4056	3305
75°	5085	3421	2750
80°	4478	2685	2310
85°	3772	2193	2060



TEST NUMBER: P333686-940

CATALOG NUMBER: S125RDIW-S850D770U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	2.0
10°-20°	322.2	5.7
20°-30°	467.2	8.3
30°-40°	532.5	9.4
40°-50°	519.1	9.2
50°-60°	436.9	7.8
60°-70°	306.3	5.4
70°-80°	157.4	2.8
80°-90°	41.6	0.7
90°-100°	32.4	0.6
100°-110°	199.6	3.5
110°-120°	362.0	6.4
120°-130°	464.6	8.2
130°-140°	499.8	8.9
140°-150°	469.1	8.3
150°-160°	379.5	6.7
160°-170°	245.4	4.4
170°-180°	84.6	1.5
0°-30°	904.7	16.1
0°-40°	1437.3	25.5
0°-60°	2393.2	42.5
0°-90°	2898.6	51.4
90°-120°	594.1	10.5
90°-150°	2027.6	36.0
90°-180°	2737.0	48.6
0°-180°	5635.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1226	1226	1226	1226	1226	
5°	1224	1220	1210	1219	1218	116
15°	1164	1158	1139	1138	1130	328
25°	1056	1041	1008	996	985	486
35°	910	886	846	819	806	569
45°	745	716	667	631	616	574
55°	565	534	483	443	427	505
65°	382	350	302	266	251	379
75°	204	175	137	118	110	216
85°	51	35	30	29	28	57
90°	1	6	11	14	16	4
95°	38	34	11	14	14	48
105°	194	197	197	197	196	206
115°	365	368	369	366	362	361
125°	519	523	523	521	519	463
135°	647	651	650	648	644	498
145°	750	751	751	752	748	469
155°	826	822	823	825	820	380
165°	872	868	868	872	867	246
175°	891	888	888	893	887	85
180°	891	891	891	891	891	



TEST NUMBER: P333686-940

CATALOG NUMBER: S125RDIW-S850D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1228.3	1227.9	1227.4	1226.9	1226.4	1225.3	1223.7	1222.0	1220.4	1218.7	1220.4
5°	1224.3	1223.5	1222.6	1221.8	1221.0	1219.5	1217.2	1215.0	1212.6	1210.4	1212.5
7.5°	1212.3	1211.5	1210.7	1209.9	1209.2	1207.4	1204.7	1201.9	1199.3	1196.5	1197.9
10°	1201.1	1200.5	1199.9	1199.3	1198.6	1196.9	1194.1	1191.1	1188.3	1185.4	1186.0
12.5°	1188.6	1187.8	1187.0	1186.2	1185.4	1183.1	1179.2	1175.4	1171.5	1167.6	1168.1
15°	1164.1	1162.9	1161.6	1160.4	1159.1	1156.4	1152.1	1147.7	1143.4	1139.1	1138.9
17.5°	1136.5	1134.6	1132.7	1130.9	1128.9	1125.2	1119.8	1114.4	1108.9	1103.5	1102.5
20°	1115.0	1112.9	1110.9	1108.8	1106.8	1102.4	1095.9	1089.3	1082.7	1076.1	1075.1
22.5°	1091.3	1089.2	1087.2	1085.1	1083.1	1078.6	1071.7	1064.8	1057.8	1051.0	1048.9
25°	1055.8	1052.7	1049.5	1046.5	1043.4	1038.0	1030.5	1022.8	1015.2	1007.6	1005.0
27.5°	1015.0	1011.3	1007.5	1003.8	1000.1	994.1	986.0	977.8	969.6	961.4	957.7
30°	985.3	981.4	977.6	973.7	969.7	963.4	954.8	946.2	937.5	928.9	924.2
32.5°	956.4	951.9	947.4	942.8	938.2	931.5	922.7	913.9	905.1	896.3	891.1
35°	909.5	904.5	899.6	894.6	889.7	882.5	873.3	864.1	854.8	845.5	839.5
37.5°	863.3	857.3	851.3	845.3	839.3	831.5	822.0	812.3	802.8	793.3	786.1
40°	830.7	824.6	818.3	812.2	806.0	798.0	788.1	778.2	768.4	758.5	750.6
42.5°	796.7	790.3	784.0	777.6	771.2	763.0	752.8	742.6	732.4	722.2	714.7
45°	744.6	738.6	732.6	726.7	720.7	712.0	700.7	689.5	678.1	666.8	658.5
47.5°	690.7	684.4	678.1	671.8	665.5	656.7	645.2	633.8	622.4	611.0	602.5
50°	656.6	649.8	643.0	636.2	629.5	620.2	608.4	596.7	585.0	573.3	564.6
52.5°	619.6	612.6	605.6	598.7	591.7	582.7	571.7	560.6	549.5	538.4	529.1
55°	564.9	558.3	551.8	545.2	538.6	529.5	518.0	506.5	495.0	483.4	474.1
57.5°	509.7	502.7	495.6	488.6	481.6	472.5	461.4	450.2	439.2	428.0	419.0
60°	474.1	467.0	459.8	452.5	445.3	436.2	425.1	413.9	402.9	391.7	382.7
62.5°	436.4	429.5	422.7	415.7	408.8	399.8	388.5	377.3	366.0	354.7	346.3
65°	382.5	375.5	368.5	361.5	354.5	345.5	334.7	323.7	312.8	301.9	293.6
67.5°	329.0	321.9	315.0	308.0	301.0	292.2	281.8	271.3	260.9	250.4	242.9
70°	292.7	285.6	278.7	271.6	264.7	256.0	245.8	235.4	225.2	214.8	208.5
72.5°	257.1	250.2	243.4	236.6	229.8	221.5	211.9	202.2	192.6	183.0	177.1
75°	203.8	197.6	191.4	185.2	179.1	171.7	163.0	154.4	145.7	137.1	132.5
77.5°	150.8	145.8	140.9	136.0	131.0	125.1	118.2	111.3	104.3	97.5	94.3
80°	120.4	115.5	110.5	105.6	100.7	95.3	89.5	83.7	78.0	72.2	70.4
82.5°	90.8	86.3	81.9	77.4	72.9	68.8	64.8	60.9	56.9	53.0	52.1
85°	50.9	47.3	43.5	39.9	36.1	33.7	32.7	31.7	30.7	29.6	29.4
87.5°	17.2	16.2	15.3	14.4	13.5	13.1	13.1	13.1	13.2	13.2	13.4
90°	0.6	1.9	3.0	4.2	5.4	6.4	7.5	8.6	9.5	10.6	11.3
92.5°	10.2	9.4	8.6	7.7	6.9	7.0	7.8	8.7	9.6	10.6	11.3
95°	37.6	37.2	36.7	36.4	35.9	32.9	27.3	21.8	16.1	10.6	11.3
97.5°	78.6	79.5	80.3	81.0	81.8	76.7	65.6	54.6	43.5	32.5	28.4
100°	110.3	110.8	111.2	111.6	112.1	112.6	113.2	113.8	114.4	114.9	93.1
102.5°	142.6	143.1	143.7	144.3	144.8	145.3	145.6	146.0	146.3	146.7	142.6
105°	194.2	194.8	195.5	196.0	196.6	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.9	247.9	247.9	247.9	247.9	248.1	248.3	248.6	249.0	249.2	249.2
110°	282.8	282.8	282.8	282.8	282.8	282.9	283.2	283.6	283.8	284.1	283.7



TEST NUMBER: P333686-940

CATALOG NUMBER: S125RDIW-S850D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.6	315.9	316.3	316.6	317.0	317.3	317.4	317.6	317.8	318.0	317.4
115°	364.7	365.4	366.2	366.9	367.7	368.1	368.3	368.4	368.5	368.7	368.1
117.5°	415.6	415.5	415.5	415.5	415.4	415.7	416.3	416.9	417.4	417.9	417.2
120°	447.3	447.2	447.0	446.8	446.7	446.8	447.3	447.7	448.2	448.6	448.4
122.5°	475.3	475.9	476.4	477.0	477.6	478.0	478.1	478.3	478.6	478.8	478.5
125°	518.7	519.7	520.8	521.7	522.8	523.3	523.3	523.3	523.3	523.3	522.7
127.5°	560.0	560.8	561.5	562.2	562.9	563.3	563.2	563.1	563.0	562.9	562.6
130°	585.4	586.1	586.8	587.6	588.4	588.8	588.9	589.1	589.2	589.3	588.9
132.5°	610.7	611.6	612.5	613.3	614.2	614.5	614.1	613.8	613.5	613.1	613.1
135°	646.8	647.7	648.6	649.5	650.4	650.7	650.4	650.1	649.8	649.5	649.2
137.5°	680.0	680.8	681.5	682.3	683.1	683.3	683.1	682.8	682.5	682.2	682.3
140°	701.7	702.0	702.3	702.6	702.8	702.9	702.8	702.7	702.5	702.3	702.7
142.5°	721.2	721.4	721.6	721.8	721.9	722.1	722.4	722.6	722.7	723.0	723.0
145°	749.9	750.2	750.6	750.8	751.1	751.3	751.3	751.3	751.3	751.3	751.4
147.5°	775.1	775.0	774.9	774.9	774.8	774.9	775.1	775.2	775.3	775.5	775.7
150°	790.9	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	791.2
152.5°	806.2	805.6	804.9	804.3	803.6	803.4	803.8	804.1	804.3	804.6	804.9
155°	825.9	825.0	824.1	823.2	822.4	822.1	822.4	822.7	823.0	823.2	823.7
157.5°	841.1	840.6	840.1	839.5	839.0	838.7	838.7	838.8	838.8	838.8	839.4
160°	851.7	850.8	849.9	849.0	848.2	847.7	847.9	848.1	848.2	848.4	849.0
162.5°	860.1	859.3	858.4	857.5	856.6	856.2	856.4	856.6	856.7	856.8	857.6
165°	871.5	870.6	869.8	868.9	868.0	867.6	867.7	867.9	868.1	868.2	869.1
167.5°	879.9	879.0	878.2	877.3	876.3	875.9	876.1	876.2	876.4	876.6	877.5
170°	884.8	883.7	882.6	881.6	880.6	880.1	880.3	880.5	880.6	880.7	881.9
172.5°	887.9	886.9	885.8	884.8	883.8	883.4	883.7	884.0	884.2	884.5	885.5
175°	891.4	890.5	889.6	888.7	887.8	887.4	887.6	887.7	887.9	888.1	889.2
177.5°	892.9	892.2	891.5	890.8	890.1	889.7	889.9	890.0	890.1	890.3	891.1
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333686-940

CATALOG NUMBER: S125RDIW-S850D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1222.0	1223.7	1225.3	1226.1	1225.9	1225.7	1225.6	1225.4
5°	1214.5	1216.6	1218.6	1219.5	1219.1	1218.6	1218.3	1217.8
7.5°	1199.4	1200.9	1202.3	1202.7	1202.3	1201.8	1201.4	1201.0
10°	1186.6	1187.2	1187.8	1187.8	1187.2	1186.6	1186.0	1185.4
12.5°	1168.5	1168.9	1169.4	1169.2	1168.2	1167.2	1166.4	1165.4
15°	1138.7	1138.4	1138.3	1137.3	1135.4	1133.5	1131.7	1129.8
17.5°	1101.4	1100.5	1099.4	1098.1	1096.6	1095.1	1093.6	1092.1
20°	1074.1	1073.0	1072.0	1070.6	1068.7	1066.8	1065.0	1063.2
22.5°	1046.9	1044.9	1042.9	1041.1	1039.6	1038.0	1036.5	1035.0
25°	1002.3	999.6	996.9	994.4	992.1	989.9	987.7	985.3
27.5°	954.0	950.2	946.5	943.5	941.4	939.1	937.0	934.8
30°	919.4	914.7	909.9	906.7	904.8	902.9	901.1	899.2
32.5°	885.8	880.6	875.4	871.6	869.2	866.9	864.5	862.2
35°	833.6	827.6	821.6	817.3	814.3	811.5	808.6	805.7
37.5°	779.0	771.8	764.6	759.6	756.9	754.0	751.3	748.5
40°	742.8	735.0	727.2	722.0	719.6	717.1	714.6	712.2
42.5°	707.2	699.7	692.2	686.6	683.1	679.4	675.7	672.2
45°	650.3	642.1	633.8	628.2	625.1	622.1	618.9	615.8
47.5°	594.1	585.6	577.1	571.1	567.8	564.4	560.9	557.5
50°	556.0	547.3	538.7	532.8	529.8	526.6	523.5	520.5
52.5°	519.9	510.5	501.2	495.0	492.0	488.8	485.8	482.7
55°	464.9	455.7	446.4	440.1	436.8	433.5	430.3	427.0
57.5°	409.9	400.9	391.8	385.8	382.9	380.0	377.1	374.2
60°	373.6	364.5	355.5	349.5	346.3	343.3	340.2	337.1
62.5°	337.9	329.5	321.1	315.4	312.3	309.2	306.1	303.0
65°	285.4	277.2	268.9	263.3	260.2	257.2	254.0	250.9
67.5°	235.3	227.8	220.3	215.3	212.9	210.4	207.9	205.5
70°	202.1	195.7	189.3	184.9	182.4	179.9	177.5	175.0
72.5°	171.2	165.3	159.4	155.7	154.0	152.4	150.8	149.1
75°	128.0	123.5	119.0	116.0	114.5	113.1	111.6	110.2
77.5°	91.0	87.9	84.7	82.7	81.6	80.5	79.5	78.4
80°	68.6	66.7	64.8	63.7	63.3	62.9	62.4	62.1
82.5°	51.3	50.4	49.5	49.0	48.7	48.5	48.2	48.0
85°	29.2	29.0	28.8	28.6	28.4	28.2	28.0	27.8
87.5°	13.6	13.6	13.8	13.8	13.7	13.7	13.6	13.6
90°	12.0	12.8	13.5	14.1	14.5	15.0	15.4	15.9
92.5°	12.0	12.8	13.5	14.0	14.2	14.4	14.6	14.8
95°	12.0	12.8	13.5	13.9	13.9	13.9	13.9	13.9
97.5°	24.3	20.1	16.0	13.9	13.9	13.9	13.9	13.9
100°	71.2	49.3	27.5	16.2	15.6	15.1	14.4	13.9
102.5°	138.4	134.3	130.1	123.1	113.1	103.1	93.1	83.1
105°	196.9	196.9	196.9	196.8	196.7	196.5	196.4	196.3
107.5°	249.3	249.3	249.3	249.1	248.7	248.3	247.8	247.4
110°	283.2	282.8	282.3	282.2	282.3	282.5	282.7	282.8



TEST NUMBER: P333686-940

CATALOG NUMBER: S125RDIW-S850D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.8	316.3	315.7	315.3	315.1	315.0	314.7	314.5
115°	367.5	366.9	366.3	365.6	364.7	363.8	362.9	362.0
117.5°	416.4	415.7	414.9	414.4	413.9	413.6	413.2	412.9
120°	448.1	447.7	447.5	446.9	446.2	445.5	444.8	444.0
122.5°	478.1	477.9	477.6	477.0	476.2	475.3	474.5	473.6
125°	522.1	521.6	520.9	520.4	520.0	519.5	519.2	518.7
127.5°	562.3	562.0	561.7	561.0	559.8	558.7	557.7	556.6
130°	588.5	588.1	587.6	587.0	586.3	585.6	584.8	584.1
132.5°	613.0	612.9	612.8	612.4	611.6	610.9	610.2	609.5
135°	648.9	648.6	648.4	647.7	646.8	646.0	645.1	644.2
137.5°	682.4	682.4	682.5	682.2	681.4	680.6	679.8	679.1
140°	702.9	703.2	703.6	703.2	702.3	701.5	700.6	699.7
142.5°	723.1	723.2	723.2	722.8	721.9	721.0	720.1	719.3
145°	751.5	751.7	751.8	751.4	750.6	749.7	748.9	748.0
147.5°	775.9	776.1	776.2	775.8	774.8	773.7	772.7	771.6
150°	791.5	791.8	792.1	791.7	790.4	789.3	788.1	786.9
152.5°	805.2	805.5	805.8	805.4	804.3	803.3	802.3	801.2
155°	824.1	824.6	825.0	824.7	823.5	822.3	821.2	819.9
157.5°	839.8	840.3	840.7	840.3	839.2	838.0	836.9	835.7
160°	849.5	850.2	850.7	850.4	849.3	848.1	846.9	845.7
162.5°	858.4	859.3	860.1	859.9	858.6	857.3	856.0	854.7
165°	870.0	870.8	871.7	871.6	870.4	869.2	868.1	866.8
167.5°	878.6	879.7	880.7	880.7	879.3	878.0	876.6	875.3
170°	883.1	884.3	885.5	885.4	884.0	882.7	881.4	880.1
172.5°	886.5	887.6	888.7	888.5	887.3	885.9	884.6	883.2
175°	890.4	891.5	892.7	892.6	891.4	890.0	888.7	887.3
177.5°	891.9	892.7	893.6	893.5	892.5	891.6	890.6	889.7
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4

(END OF REPORT)