

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333351-840

Luminaire Tested: **S125DIW-S375D770U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333351-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D770U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4225.3 lumens  
Efficiency: N/A  
Efficacy: 139.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333351-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333351-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	22
4	72	61	53	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20	16
6	61	49	41	35	55	44	38	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3810	3810	3810
5°	3818	3782	3806
10°	3796	3756	3777
15°	3754	3710	3726
20°	3696	3647	3654
25°	3632	3572	3569
30°	3554	3491	3473
35°	3470	3404	3356
40°	3384	3309	3262
45°	3291	3222	3159
50°	3189	3118	3024
55°	3090	3001	2916
60°	2971	2882	2780
65°	2832	2740	2647
70°	2696	2574	2485
75°	2458	2376	2293
80°	2187	2153	2101
85°	1904	1941	1830



TEST NUMBER: P333351-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.6	1.3
10°-20°	157.1	3.7
20°-30°	232.0	5.5
30°-40°	270.7	6.4
40°-50°	271.9	6.4
50°-60°	238.7	5.6
60°-70°	177.8	4.2
70°-80°	101.7	2.4
80°-90°	31.7	0.7
90°-100°	64.5	1.5
100°-110°	190.5	4.5
110°-120°	322.7	7.6
120°-130°	424.7	10.1
130°-140°	475.9	11.3
140°-150°	466.4	11.0
150°-160°	391.7	9.3
160°-170°	260.4	6.2
170°-180°	91.1	2.2
0°-30°	444.7	10.5
0°-40°	715.5	16.9
0°-60°	1226.0	29.0
0°-90°	1537.2	36.4
90°-120°	577.8	13.7
90°-150°	1944.8	46.0
90°-180°	2688.0	63.6
0°-180°	4225.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	589	588	583	587	587	56
15°	562	560	555	557	557	158
25°	510	507	501	502	501	234
35°	440	438	432	429	426	275
45°	360	358	353	348	346	278
55°	274	273	266	262	259	245
65°	185	184	179	175	173	184
75°	98	98	95	94	92	105
85°	26	26	26	26	25	29
90°	1	7	12	16	18	4
95°	49	51	58	63	64	52
105°	171	175	179	184	186	183
115°	323	326	328	327	326	319
125°	472	476	477	475	474	422
135°	613	618	618	618	616	472
145°	743	746	748	748	746	464
155°	850	850	851	853	850	391
165°	924	923	924	926	922	261
175°	961	958	958	962	957	91
180°	963	963	963	963	963	



TEST NUMBER: P333351-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	591.4	591.2	591.0	590.7	590.5	589.9	589.1	588.2	587.4	586.5	587.4
5°	589.0	588.8	588.5	588.3	588.1	587.5	586.5	585.5	584.4	583.4	584.3
7.5°	583.6	583.4	583.2	583.0	582.8	582.1	581.0	579.8	578.7	577.5	578.5
10°	578.8	578.6	578.3	578.1	577.9	577.2	576.1	574.9	573.8	572.7	573.5
12.5°	572.8	572.4	572.0	571.7	571.3	570.6	569.5	568.5	567.3	566.3	566.9
15°	561.5	561.2	560.9	560.6	560.2	559.5	558.4	557.2	556.0	554.9	555.4
17.5°	548.5	548.1	547.5	547.1	546.6	545.8	544.6	543.5	542.3	541.1	541.8
20°	537.7	537.5	537.2	537.0	536.8	536.0	534.7	533.3	532.0	530.7	531.4
22.5°	526.8	526.4	526.0	525.7	525.3	524.5	523.2	522.0	520.7	519.5	520.0
25°	509.7	509.2	508.6	508.1	507.6	506.6	505.3	503.9	502.6	501.3	501.5
27.5°	489.6	489.3	489.0	488.7	488.4	487.5	486.1	484.7	483.3	481.9	482.0
30°	476.6	476.3	475.8	475.5	475.2	474.3	472.8	471.2	469.7	468.1	467.9
32.5°	462.3	461.8	461.4	460.9	460.4	459.5	458.1	456.7	455.3	453.9	453.5
35°	440.1	439.7	439.3	438.9	438.5	437.5	436.1	434.6	433.1	431.7	431.2
37.5°	417.1	416.6	416.1	415.5	415.0	414.0	412.6	411.3	409.9	408.6	407.8
40°	401.4	400.8	400.3	399.8	399.3	398.3	396.9	395.5	393.9	392.5	391.6
42.5°	384.6	384.2	383.7	383.2	382.8	381.9	380.4	379.0	377.5	376.1	375.3
45°	360.3	359.9	359.5	359.1	358.6	357.8	356.6	355.4	354.1	352.8	351.6
47.5°	334.2	334.2	334.2	334.3	334.3	333.6	332.0	330.5	329.0	327.5	326.3
50°	317.4	317.1	316.8	316.4	316.1	315.4	314.1	312.9	311.6	310.3	309.0
52.5°	300.2	299.9	299.7	299.5	299.3	298.5	297.2	295.9	294.5	293.2	292.1
55°	274.4	274.1	273.8	273.5	273.2	272.3	270.8	269.4	267.9	266.5	265.6
57.5°	247.3	247.1	246.9	246.8	246.6	245.9	244.7	243.5	242.3	241.1	239.8
60°	230.0	229.6	229.2	228.8	228.4	227.6	226.5	225.4	224.2	223.1	222.1
62.5°	212.2	211.9	211.5	211.2	210.9	210.2	209.2	208.2	207.2	206.3	205.2
65°	185.3	185.1	184.9	184.7	184.5	183.8	182.7	181.5	180.4	179.3	178.2
67.5°	159.3	158.9	158.3	157.9	157.5	156.8	156.0	155.1	154.3	153.5	152.7
70°	142.8	142.3	141.8	141.3	140.8	140.0	139.1	138.1	137.2	136.3	135.6
72.5°	124.9	124.5	124.2	123.8	123.5	123.0	122.4	121.8	121.2	120.6	119.9
75°	98.5	98.3	98.1	97.9	97.7	97.3	96.7	96.2	95.7	95.2	94.9
77.5°	74.1	74.0	73.9	73.8	73.8	73.6	73.3	73.0	72.7	72.4	72.2
80°	58.8	58.8	58.8	58.8	58.8	58.7	58.5	58.3	58.1	57.9	57.8
82.5°	45.3	45.2	45.0	44.8	44.7	44.6	44.5	44.5	44.4	44.4	44.2
85°	25.7	25.8	25.9	26.0	26.1	26.2	26.2	26.2	26.2	26.2	26.1
87.5°	10.2	10.5	10.8	11.0	11.3	11.5	11.6	11.8	11.9	12.1	12.3
90°	0.7	2.1	3.4	4.7	6.1	7.4	8.5	9.7	10.8	12.0	12.8
92.5°	18.2	19.1	20.0	20.9	21.9	23.0	24.5	26.0	27.4	28.8	29.9
95°	48.8	49.1	49.4	49.7	50.1	51.1	52.7	54.4	56.0	57.8	58.9
97.5°	81.0	81.1	81.2	81.4	81.5	82.7	85.0	87.4	89.6	91.9	93.0
100°	104.9	104.9	104.9	104.9	104.9	106.0	108.2	110.4	112.5	114.7	116.2
102.5°	130.8	131.4	132.1	132.7	133.4	134.3	135.4	136.5	137.5	138.7	140.4
105°	171.0	171.8	172.6	173.4	174.3	175.2	176.2	177.1	178.1	179.2	180.2
107.5°	215.3	216.1	217.0	217.8	218.6	219.4	220.3	221.0	221.8	222.5	223.0
110°	245.9	246.7	247.5	248.4	249.2	249.8	250.3	250.9	251.4	251.9	252.4



TEST NUMBER: P333351-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.1	277.5	277.9	278.4	278.8	279.3	279.9	280.6	281.2	281.9	282.2
115°	323.2	323.8	324.5	325.1	325.8	326.3	326.6	326.9	327.3	327.6	327.4
117.5°	369.3	369.6	369.9	370.2	370.5	370.8	371.1	371.4	371.7	372.0	372.1
120°	398.1	398.9	399.7	400.6	401.4	401.9	402.0	402.2	402.4	402.5	402.5
122.5°	429.3	429.6	429.9	430.2	430.5	430.8	431.2	431.7	432.1	432.5	432.4
125°	471.5	472.5	473.5	474.5	475.5	476.2	476.3	476.5	476.7	476.8	476.5
127.5°	516.5	517.1	517.7	518.3	518.8	519.2	519.4	519.6	519.8	520.0	519.8
130°	543.5	544.3	545.2	546.0	546.8	547.4	547.8	548.1	548.5	548.8	548.6
132.5°	570.5	571.9	573.2	574.6	575.9	576.6	576.5	576.4	576.4	576.3	576.2
135°	613.2	614.2	615.2	616.2	617.2	617.8	617.9	618.1	618.3	618.4	618.4
137.5°	653.4	654.4	655.3	656.3	657.3	657.9	658.3	658.6	659.0	659.4	659.6
140°	679.2	680.0	680.9	681.7	682.6	683.2	683.7	684.2	684.7	685.2	685.5
142.5°	705.0	705.7	706.4	707.1	707.8	708.4	709.1	709.7	710.3	710.9	711.1
145°	743.0	743.6	744.3	744.9	745.6	746.2	746.7	747.2	747.7	748.2	748.2
147.5°	778.0	778.4	778.7	779.1	779.5	779.8	780.2	780.6	781.0	781.4	781.8
150°	801.4	801.2	801.0	800.9	800.7	801.0	801.6	802.3	802.9	803.7	803.7
152.5°	820.6	820.8	821.0	821.3	821.5	821.7	822.0	822.3	822.5	822.8	823.2
155°	850.1	850.1	850.1	850.1	850.1	850.2	850.4	850.5	850.7	850.9	851.5
157.5°	876.6	876.2	875.8	875.5	875.0	874.9	875.1	875.3	875.5	875.7	876.3
160°	892.1	891.6	891.1	890.6	890.1	889.9	890.1	890.3	890.4	890.6	891.3
162.5°	905.9	905.5	905.1	904.8	904.4	904.2	904.3	904.3	904.3	904.4	905.2
165°	924.3	924.0	923.7	923.3	923.0	922.9	923.1	923.2	923.4	923.6	924.2
167.5°	940.0	939.3	938.6	938.0	937.3	937.0	937.0	937.0	937.0	937.0	938.0
170°	948.4	947.7	947.0	946.3	945.6	945.3	945.3	945.3	945.3	945.3	946.3
172.5°	954.3	953.6	953.0	952.3	951.7	951.3	951.3	951.3	951.3	951.3	952.3
175°	961.1	960.4	959.8	959.1	958.4	958.1	958.1	958.1	958.1	958.1	959.1
177.5°	964.5	964.0	963.4	962.9	962.4	962.1	961.9	961.8	961.7	961.5	962.3
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333351-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	588.2	589.1	589.9	590.3	590.2	590.1	590.1	590.0
5°	585.2	586.2	587.1	587.5	587.4	587.3	587.2	587.1
7.5°	579.4	580.3	581.2	581.6	581.5	581.4	581.3	581.2
10°	574.3	575.1	576.0	576.3	576.2	576.1	576.0	575.9
12.5°	567.6	568.4	569.0	569.3	569.3	569.3	569.3	569.2
15°	555.9	556.4	557.0	557.2	557.2	557.2	557.2	557.2
17.5°	542.4	543.0	543.7	543.7	543.2	542.7	542.2	541.7
20°	532.1	532.8	533.5	533.7	533.1	532.6	532.1	531.6
22.5°	520.4	520.9	521.4	521.4	521.1	520.7	520.4	520.0
25°	501.7	501.9	502.1	502.0	501.7	501.4	501.1	500.8
27.5°	482.0	482.0	482.1	482.0	481.6	481.3	481.0	480.7
30°	467.7	467.5	467.3	467.1	466.8	466.5	466.1	465.7
32.5°	453.2	452.8	452.4	452.0	451.4	450.8	450.3	449.7
35°	430.7	430.2	429.6	429.0	428.2	427.3	426.5	425.7
37.5°	407.1	406.3	405.5	404.9	404.3	403.9	403.4	402.9
40°	390.6	389.7	388.8	388.2	387.9	387.5	387.2	386.9
42.5°	374.4	373.5	372.6	372.0	371.5	371.0	370.6	370.1
45°	350.3	349.1	347.9	347.1	346.8	346.5	346.2	345.9
47.5°	325.0	323.8	322.4	321.4	320.7	320.0	319.3	318.6
50°	307.7	306.3	305.0	304.0	303.2	302.5	301.7	301.0
52.5°	290.8	289.6	288.4	287.5	286.7	285.9	285.1	284.3
55°	264.6	263.7	262.8	262.0	261.3	260.4	259.7	259.0
57.5°	238.6	237.4	236.2	235.4	235.0	234.6	234.2	233.8
60°	221.1	219.9	218.9	218.0	217.3	216.6	215.9	215.2
62.5°	204.1	202.9	201.8	201.0	200.5	199.9	199.2	198.7
65°	177.3	176.4	175.5	174.8	174.4	174.0	173.6	173.2
67.5°	151.9	151.1	150.3	149.8	149.6	149.3	149.1	148.8
70°	135.0	134.4	133.8	133.3	132.9	132.5	132.0	131.6
72.5°	119.2	118.5	117.8	117.2	116.8	116.4	115.9	115.5
75°	94.6	94.3	93.9	93.6	93.2	92.8	92.4	91.9
77.5°	72.1	71.9	71.7	71.5	71.2	70.9	70.6	70.3
80°	57.7	57.6	57.5	57.3	57.1	56.9	56.7	56.5
82.5°	44.0	43.8	43.7	43.5	43.5	43.5	43.4	43.4
85°	26.0	25.9	25.8	25.5	25.3	25.1	24.9	24.7
87.5°	12.4	12.6	12.7	12.8	12.7	12.7	12.6	12.5
90°	13.6	14.5	15.3	16.0	16.5	17.0	17.5	18.0
92.5°	31.0	32.1	33.2	33.9	34.3	34.6	35.0	35.3
95°	60.1	61.2	62.4	63.1	63.5	63.8	64.1	64.4
97.5°	94.1	95.2	96.3	96.9	97.1	97.4	97.6	97.8
100°	117.6	119.2	120.7	121.6	122.0	122.3	122.6	122.9
102.5°	142.0	143.6	145.2	146.2	146.7	147.2	147.6	148.1
105°	181.2	182.2	183.2	183.9	184.4	184.9	185.4	185.9
107.5°	223.5	224.0	224.5	224.7	224.7	224.7	224.6	224.6
110°	252.9	253.4	253.9	254.1	253.9	253.7	253.6	253.4





TEST NUMBER: P333351-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	282.4	282.6	282.8	282.8	282.5	282.2	281.9	281.6
115°	327.3	327.1	326.9	326.8	326.6	326.5	326.3	326.1
117.5°	372.2	372.3	372.5	372.2	371.6	370.9	370.2	369.6
120°	402.5	402.5	402.5	402.2	401.6	400.9	400.2	399.6
122.5°	432.3	432.1	432.0	431.7	431.1	430.6	430.1	429.6
125°	476.2	475.7	475.4	475.2	475.0	474.8	474.7	474.5
127.5°	519.7	519.5	519.3	519.1	518.8	518.4	518.1	517.8
130°	548.5	548.3	548.1	547.9	547.5	547.1	546.8	546.5
132.5°	576.0	575.8	575.7	575.3	574.9	574.4	574.0	573.5
135°	618.4	618.4	618.4	618.1	617.4	616.8	616.1	615.5
137.5°	659.8	660.0	660.2	659.8	659.0	658.2	657.4	656.5
140°	685.9	686.2	686.5	686.3	685.5	684.6	683.8	683.0
142.5°	711.3	711.6	711.8	711.4	710.6	709.8	708.9	708.1
145°	748.2	748.2	748.2	747.9	747.4	746.9	746.4	745.9
147.5°	782.2	782.6	783.0	782.6	781.5	780.4	779.3	778.2
150°	803.7	803.7	803.7	803.4	803.1	802.8	802.4	802.1
152.5°	823.6	824.0	824.5	824.4	823.7	823.1	822.5	821.9
155°	852.2	852.8	853.5	853.4	852.6	851.8	850.9	850.1
157.5°	877.0	877.6	878.3	878.1	877.0	875.9	874.7	873.6
160°	891.9	892.6	893.2	893.2	892.3	891.5	890.7	889.9
162.5°	906.1	906.8	907.6	907.6	906.6	905.5	904.6	903.6
165°	924.9	925.6	926.2	926.0	925.1	924.1	923.1	922.1
167.5°	939.0	940.0	940.9	940.9	939.9	938.9	937.9	936.8
170°	947.4	948.4	949.4	949.3	948.1	947.0	945.7	944.6
172.5°	953.3	954.3	955.3	955.3	954.3	953.2	952.2	951.2
175°	960.1	961.1	962.1	962.0	960.8	959.7	958.5	957.4
177.5°	963.1	963.9	964.7	964.6	963.7	962.8	961.9	960.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3

(END OF REPORT)