

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333399-840

Luminaire Tested: **S125DIW-S610D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333399-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1560U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7989.1 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333399-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333399-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28
3	78	68	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24
4	71	60	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	48	36	28	23	43	32	26	22	26	21	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333399-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.1
10°-20°	258.3	3.2
20°-30°	381.4	4.8
30°-40°	445.0	5.6
40°-50°	447.0	5.6
50°-60°	392.4	4.9
60°-70°	292.4	3.7
70°-80°	167.2	2.1
80°-90°	52.9	0.7
90°-100°	131.1	1.6
100°-110°	387.1	4.8
110°-120°	655.6	8.2
120°-130°	862.9	10.8
130°-140°	966.8	12.1
140°-150°	947.6	11.9
150°-160°	795.9	10.0
160°-170°	529.1	6.6
170°-180°	185.2	2.3
0°-30°	731.2	9.2
0°-40°	1176.2	14.7
0°-60°	2015.6	25.2
0°-90°	2528.0	31.6
90°-120°	1173.8	14.7
90°-150°	3951.1	49.5
90°-180°	5461.0	68.4
0°-180°	7989.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	2	14	24	32	37	8
95°	99	103	117	128	131	106
105°	347	355	364	373	378	371
115°	656	662	666	664	663	649
125°	958	967	969	966	964	858
135°	1246	1255	1256	1256	1250	960
145°	1509	1515	1520	1520	1515	943
155°	1727	1727	1729	1734	1727	795
165°	1878	1875	1876	1882	1873	530
175°	1953	1947	1946	1954	1945	185
180°	1957	1957	1957	1957	1957	



TEST NUMBER: P333399-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.9	17.4	18.0	18.5	19.1	19.5	19.8	20.2	20.5	20.8	21.2
90°	1.5	4.2	7.0	9.7	12.3	14.8	17.3	19.6	22.0	24.3	26.1
92.5°	36.9	38.8	40.7	42.5	44.4	46.9	49.8	52.6	55.5	58.5	60.7
95°	99.0	99.7	100.4	101.0	101.7	103.7	107.1	110.5	113.9	117.2	119.7
97.5°	164.5	164.7	165.0	165.3	165.6	168.0	172.7	177.4	182.1	186.7	188.9
100°	213.2	213.2	213.2	213.2	213.2	215.4	219.8	224.2	228.6	233.0	236.1
102.5°	265.6	267.0	268.3	269.6	271.0	272.9	275.1	277.3	279.5	281.8	285.1
105°	347.3	348.9	350.6	352.3	354.1	355.9	357.9	359.9	361.9	364.1	366.1
107.5°	437.4	439.1	440.8	442.5	444.1	445.9	447.4	448.9	450.5	452.0	453.0
110°	499.6	501.3	502.9	504.6	506.3	507.7	508.7	509.7	510.7	511.7	512.7



TEST NUMBER: P333399-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	562.9	563.8	564.7	565.5	566.4	567.5	568.8	570.1	571.4	572.7	573.1
115°	656.4	657.8	659.1	660.5	661.9	662.9	663.6	664.2	664.9	665.6	665.2
117.5°	750.2	750.8	751.4	752.0	752.7	753.3	753.9	754.5	755.1	755.8	756.0
120°	808.7	810.4	812.1	813.9	815.5	816.5	816.9	817.2	817.5	817.9	817.9
122.5°	872.1	872.7	873.3	873.9	874.5	875.3	876.2	877.1	877.9	878.8	878.5
125°	958.0	960.0	962.1	964.1	966.1	967.3	967.7	968.0	968.4	968.7	968.0
127.5°	1049.4	1050.6	1051.7	1052.8	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0
130°	1104.2	1105.9	1107.6	1109.2	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5
132.5°	1159.0	1161.8	1164.6	1167.4	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5
135°	1245.9	1247.9	1249.9	1251.9	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5
137.5°	1327.5	1329.5	1331.4	1333.3	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1
140°	1379.9	1381.6	1383.2	1384.9	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7
142.5°	1432.3	1433.7	1435.1	1436.5	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8
145°	1509.3	1510.7	1512.1	1513.4	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9
147.5°	1580.6	1581.3	1582.1	1582.9	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4
150°	1628.1	1627.8	1627.5	1627.1	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7
152.5°	1667.1	1667.6	1668.1	1668.5	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5
155°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0
157.5°	1780.7	1780.0	1779.3	1778.5	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3
160°	1812.4	1811.4	1810.4	1809.4	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7
162.5°	1840.5	1839.7	1839.0	1838.3	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1
165°	1877.9	1877.2	1876.5	1875.9	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7
167.5°	1909.6	1908.2	1906.9	1905.5	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5
170°	1926.6	1925.3	1923.9	1922.6	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6
172.5°	1938.8	1937.5	1936.1	1934.8	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8
175°	1952.6	1951.2	1949.8	1948.4	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4
177.5°	1959.5	1958.4	1957.4	1956.3	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333399-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	21.5	21.8	22.2	22.3	22.2	22.2	22.1	22.0
90°	27.8	29.5	31.1	32.5	33.5	34.5	35.5	36.6
92.5°	62.9	65.1	67.5	68.9	69.7	70.4	71.1	71.9
95°	122.0	124.4	126.7	128.3	129.0	129.7	130.3	131.0
97.5°	191.2	193.4	195.6	197.0	197.4	197.8	198.2	198.6
100°	239.1	242.2	245.2	247.1	247.7	248.4	249.1	249.7
102.5°	288.4	291.8	295.0	297.2	298.1	299.0	300.0	300.9
105°	368.1	370.1	372.1	373.7	374.7	375.7	376.7	377.7
107.5°	454.0	455.0	456.1	456.6	456.5	456.5	456.4	456.3
110°	513.8	514.8	515.8	516.1	515.8	515.4	515.1	514.8



TEST NUMBER: P333399-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	573.6	574.1	574.5	574.5	573.9	573.3	572.7	572.1
115°	664.9	664.6	664.2	663.9	663.6	663.2	662.9	662.6
117.5°	756.3	756.6	756.8	756.3	754.9	753.6	752.2	750.8
120°	817.9	817.9	817.9	817.2	815.9	814.5	813.1	811.8
122.5°	878.3	878.0	877.7	877.1	876.0	874.8	873.7	872.7
125°	967.3	966.6	965.9	965.4	965.1	964.7	964.4	964.1
127.5°	1055.7	1055.4	1055.0	1054.5	1053.8	1053.2	1052.5	1051.8
130°	1114.2	1113.9	1113.5	1113.0	1112.4	1111.7	1111.0	1110.3
132.5°	1170.2	1169.9	1169.5	1168.9	1168.0	1167.0	1166.1	1165.1
135°	1256.5	1256.5	1256.5	1255.9	1254.5	1253.1	1251.7	1250.4
137.5°	1340.5	1340.9	1341.3	1340.7	1339.0	1337.3	1335.5	1333.8
140°	1393.4	1394.1	1394.7	1394.2	1392.6	1390.9	1389.2	1387.5
142.5°	1445.2	1445.6	1446.1	1445.4	1443.7	1442.1	1440.4	1438.7
145°	1519.9	1519.9	1519.9	1519.4	1518.4	1517.4	1516.4	1515.4
147.5°	1589.2	1590.0	1590.8	1590.1	1587.8	1585.5	1583.3	1580.9
150°	1632.7	1632.7	1632.7	1632.3	1631.6	1631.0	1630.3	1629.6
152.5°	1673.3	1674.2	1675.0	1674.8	1673.5	1672.3	1671.1	1669.9
155°	1731.3	1732.7	1734.0	1733.9	1732.2	1730.5	1728.8	1727.2
157.5°	1781.6	1783.0	1784.3	1783.9	1781.6	1779.4	1777.2	1774.9
160°	1812.1	1813.4	1814.8	1814.6	1812.9	1811.2	1809.6	1807.9
162.5°	1840.7	1842.3	1843.9	1843.7	1841.8	1839.8	1837.9	1835.8
165°	1879.1	1880.5	1881.8	1881.5	1879.5	1877.4	1875.4	1873.3
167.5°	1907.5	1909.6	1911.6	1911.6	1909.5	1907.4	1905.3	1903.2
170°	1924.6	1926.6	1928.6	1928.5	1926.1	1923.8	1921.4	1919.0
172.5°	1936.8	1938.8	1940.9	1940.9	1938.7	1936.6	1934.5	1932.5
175°	1950.6	1952.6	1954.6	1954.4	1952.1	1949.6	1947.3	1944.9
177.5°	1956.7	1958.3	1959.9	1959.8	1957.9	1956.0	1954.1	1952.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1

(END OF REPORT)