

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334424

Luminaire Tested: **S125RDW-S1270D927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P334424  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDW-S1270D927-4F0-1E-UDD-F  
Description: DEFINE 5 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER  
PENDANT/SURFACE/WALL MOUNT, 1270 LUMENS PER FOOT  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3672.7 lumens  
Efficiency: N/A  
Efficacy: 89.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 41.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334424

CATALOG NUMBER: S125RDW-S1270D927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P334424

CATALOG NUMBER: S125RDW-S1270D927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	61
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	53
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	46
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	36
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	33
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	29
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	27

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10039	10039	10039
5°	10062	9948	10009
10°	9986	9855	9855
15°	9867	9655	9577
20°	9715	9377	9263
25°	9537	9103	8902
30°	9316	8782	8501
35°	9090	8451	8053
40°	8878	8107	7612
45°	8622	7721	7131
50°	8363	7302	6629
55°	8064	6901	6094
60°	7764	6414	5521
65°	7410	5848	4863
70°	7006	5144	4190
75°	6445	4337	3486
80°	5676	3407	2927
85°	4787	2786	2608



TEST NUMBER: P334424

CATALOG NUMBER: S125RDW-S1270D927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.3	4.0
10°-20°	408.9	11.1
20°-30°	592.8	16.1
30°-40°	675.4	18.4
40°-50°	658.3	17.9
50°-60°	554.0	15.1
60°-70°	388.2	10.6
70°-80°	199.0	5.4
80°-90°	49.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1148.0	31.3
0°-40°	1823.4	49.6
0°-60°	3035.7	82.7
0°-90°	3672.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3672.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1554	1554	1554	1554	1554	
5°	1552	1547	1534	1546	1544	147
15°	1476	1469	1444	1443	1432	416
25°	1338	1321	1277	1262	1249	616
35°	1153	1125	1072	1038	1021	722
45°	944	910	845	798	781	728
55°	716	679	613	560	541	640
65°	485	445	383	336	318	480
75°	258	223	174	148	140	273
85°	65	43	38	36	35	74
90°	0	0	0	0	0	



TEST NUMBER: P334424

CATALOG NUMBER: S125RDW-S1270D927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1554.5	1554.5	1554.5	1554.5	1554.5
2.5°	1558.0	1554.5	1542.7	1554.5	1553.3
5°	1552.1	1547.4	1534.5	1546.3	1543.9
7.5°	1540.4	1535.7	1520.4	1529.8	1527.5
10°	1522.8	1519.3	1502.8	1506.3	1502.8
12.5°	1502.8	1498.1	1474.6	1477.0	1471.1
15°	1475.8	1468.8	1444.1	1442.9	1432.4
17.5°	1447.6	1437.1	1407.7	1401.8	1393.6
20°	1413.6	1401.8	1364.3	1358.4	1347.8
22.5°	1376.0	1364.3	1324.4	1311.4	1303.2
25°	1338.4	1320.8	1277.4	1262.1	1249.2
27.5°	1296.2	1275.0	1229.3	1209.3	1196.4
30°	1249.2	1226.9	1177.6	1150.6	1140.0
32.5°	1203.4	1176.4	1125.9	1095.4	1081.3
35°	1152.9	1124.8	1071.9	1037.9	1021.4
37.5°	1104.8	1070.8	1016.7	976.8	960.4
40°	1053.1	1017.9	961.6	917.0	902.9
42.5°	999.1	962.7	904.0	861.8	839.5
45°	944.0	909.9	845.3	798.4	780.8
47.5°	886.4	851.2	786.6	738.5	718.5
50°	832.4	793.7	726.8	677.4	659.8
52.5°	773.7	733.8	671.6	617.6	600.0
55°	716.2	678.6	612.9	560.0	541.2
57.5°	657.5	617.6	554.2	502.5	486.1
60°	601.1	560.0	496.6	445.0	427.4
62.5°	541.2	502.5	437.9	391.0	373.4
65°	484.9	445.0	382.7	335.8	318.2
67.5°	428.5	388.6	328.7	284.1	270.0
70°	371.0	331.1	272.4	236.0	221.9
72.5°	314.7	275.9	221.9	189.0	180.8
75°	258.3	223.1	173.8	147.9	139.7
77.5°	200.8	172.6	131.5	111.5	104.5
80°	152.6	124.5	91.6	81.0	78.7
82.5°	105.7	81.0	61.1	57.5	56.4
85°	64.6	43.4	37.6	36.4	35.2
87.5°	27.0	18.8	17.6	17.6	16.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)