

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333374-840

Luminaire Tested: **S125DIW-S610D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333374-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D470U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4417.5 lumens
Efficiency: N/A
Efficacy: 146.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333374-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333374-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	33	29
5	69	57	49	43	64	54	46	41	47	41	37	41	36	32	35	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	36	31	38	33	28	33	29	25	29	25	22	20
8	55	42	34	29	51	40	33	28	35	29	25	31	26	22	26	23	20	18
9	51	39	31	26	48	36	30	25	32	26	22	28	24	20	24	21	18	16
10	48	36	28	23	44	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333374-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	2.1
10°-20°	258.3	5.8
20°-30°	381.4	8.6
30°-40°	445.0	10.1
40°-50°	447.0	10.1
50°-60°	392.4	8.9
60°-70°	292.4	6.6
70°-80°	167.2	3.8
80°-90°	49.9	1.1
90°-100°	22.4	0.5
100°-110°	138.0	3.1
110°-120°	250.3	5.7
120°-130°	321.3	7.3
130°-140°	345.6	7.8
140°-150°	324.4	7.3
150°-160°	262.4	5.9
160°-170°	169.7	3.8
170°-180°	58.5	1.3
0°-30°	731.2	16.6
0°-40°	1176.2	26.6
0°-60°	2015.6	45.6
0°-90°	2525.0	57.2
90°-120°	410.7	9.3
90°-150°	1401.9	31.7
90°-180°	1893.0	42.9
0°-180°	4417.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	0	4	7	10	11	3
95°	26	24	7	9	10	33
105°	134	136	136	136	136	142
115°	252	254	255	253	250	250
125°	359	362	362	360	359	320
135°	447	450	449	448	446	345
145°	519	519	520	520	517	324
155°	571	569	569	570	567	263
165°	603	600	600	603	599	170
175°	616	614	614	617	614	59
180°	616	616	616	616	616	



TEST NUMBER: P333374-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.7	16.9	17.0	17.2	17.3	17.4	17.4	17.4	17.4	17.5	17.6
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.3	7.8
92.5°	7.1	6.5	5.9	5.4	4.7	4.7	5.5	6.1	6.7	7.3	7.8
95°	26.1	25.8	25.4	25.1	24.8	22.7	18.9	15.0	11.2	7.3	7.8
97.5°	54.3	54.9	55.4	56.0	56.6	53.0	45.3	37.8	30.1	22.5	19.6
100°	76.2	76.6	77.0	77.3	77.6	77.9	78.3	78.7	79.1	79.5	64.3
102.5°	98.6	99.0	99.4	99.8	100.2	100.5	100.7	100.9	101.2	101.4	98.6
105°	134.3	134.7	135.1	135.5	135.9	136.1	136.1	136.1	136.1	136.1	136.1
107.5°	171.4	171.4	171.4	171.4	171.4	171.5	171.7	171.9	172.1	172.3	172.4
110°	195.5	195.5	195.5	195.5	195.5	195.6	195.8	196.0	196.2	196.4	196.1



TEST NUMBER: P333374-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.2	218.4	218.6	218.9	219.1	219.3	219.4	219.6	219.7	219.8	219.4
115°	252.2	252.7	253.2	253.7	254.2	254.5	254.6	254.7	254.8	254.9	254.5
117.5°	287.4	287.3	287.3	287.3	287.3	287.5	287.8	288.2	288.6	289.0	288.5
120°	309.3	309.2	309.1	309.0	308.9	309.0	309.3	309.6	309.9	310.2	310.0
122.5°	328.7	329.0	329.4	329.8	330.2	330.4	330.6	330.7	330.9	331.0	330.8
125°	358.6	359.3	360.0	360.7	361.4	361.8	361.8	361.8	361.8	361.8	361.4
127.5°	387.2	387.8	388.3	388.8	389.3	389.5	389.4	389.4	389.3	389.2	389.0
130°	404.8	405.3	405.8	406.3	406.8	407.1	407.2	407.3	407.4	407.5	407.2
132.5°	422.3	422.9	423.5	424.0	424.6	424.9	424.6	424.4	424.1	423.9	423.9
135°	447.3	447.9	448.5	449.1	449.7	449.9	449.7	449.5	449.3	449.1	448.9
137.5°	470.2	470.7	471.2	471.8	472.3	472.5	472.3	472.1	471.9	471.7	471.8
140°	485.1	485.3	485.5	485.7	485.9	486.0	485.9	485.8	485.7	485.6	485.8
142.5°	498.7	498.9	499.0	499.1	499.2	499.3	499.5	499.6	499.8	499.9	499.9
145°	518.6	518.8	519.0	519.2	519.4	519.5	519.5	519.5	519.5	519.5	519.6
147.5°	535.9	535.8	535.8	535.7	535.7	535.7	535.9	536.0	536.1	536.2	536.3
150°	546.8	546.6	546.4	546.2	546.0	546.0	546.2	546.4	546.6	546.8	547.0
152.5°	557.4	557.0	556.5	556.1	555.6	555.5	555.7	555.9	556.1	556.3	556.5
155°	571.1	570.5	569.9	569.3	568.7	568.5	568.7	568.9	569.1	569.3	569.6
157.5°	581.6	581.2	580.9	580.5	580.1	580.0	580.0	580.0	580.0	580.1	580.4
160°	588.9	588.2	587.6	587.0	586.4	586.2	586.3	586.4	586.5	586.6	587.0
162.5°	594.7	594.1	593.5	592.9	592.3	592.1	592.2	592.3	592.4	592.5	593.0
165°	602.6	602.0	601.4	600.8	600.2	599.9	600.0	600.1	600.2	600.3	600.9
167.5°	608.4	607.8	607.2	606.5	605.9	605.6	605.7	605.8	605.9	606.0	606.8
170°	611.8	611.1	610.3	609.6	608.8	608.5	608.6	608.7	608.8	608.9	609.8
172.5°	613.9	613.2	612.5	611.8	611.1	610.9	611.0	611.2	611.4	611.6	612.3
175°	616.3	615.7	615.1	614.5	613.9	613.6	613.7	613.8	613.9	614.0	614.8
177.5°	617.4	616.9	616.4	615.9	615.4	615.2	615.3	615.4	615.5	615.6	616.1
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333374-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	17.7	17.8	17.9	17.8	17.6	17.4	17.2	17.0
90°	8.3	8.8	9.3	9.8	10.1	10.4	10.7	11.0
92.5°	8.3	8.8	9.3	9.7	9.8	10.0	10.1	10.2
95°	8.3	8.8	9.3	9.6	9.6	9.6	9.6	9.6
97.5°	16.8	13.9	11.0	9.6	9.6	9.6	9.6	9.6
100°	49.3	34.1	19.0	11.2	10.8	10.4	10.0	9.6
102.5°	95.7	92.8	90.0	85.1	78.2	71.3	64.3	57.5
105°	136.1	136.1	136.1	136.1	136.0	135.9	135.8	135.7
107.5°	172.4	172.4	172.4	172.3	172.0	171.7	171.4	171.1
110°	195.8	195.5	195.2	195.1	195.2	195.3	195.4	195.5



TEST NUMBER: P333374-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	219.0	218.6	218.3	218.0	217.9	217.7	217.6	217.4
115°	254.1	253.7	253.3	252.8	252.2	251.6	251.0	250.3
117.5°	287.9	287.4	286.9	286.5	286.2	286.0	285.7	285.5
120°	309.8	309.6	309.4	309.0	308.5	308.0	307.5	307.0
122.5°	330.6	330.4	330.2	329.8	329.2	328.6	328.1	327.5
125°	361.0	360.6	360.2	359.8	359.5	359.2	358.9	358.6
127.5°	388.8	388.6	388.4	387.9	387.1	386.4	385.6	384.9
130°	406.9	406.6	406.3	405.9	405.4	404.9	404.3	403.8
132.5°	423.8	423.7	423.7	423.4	422.9	422.4	421.9	421.4
135°	448.7	448.5	448.3	447.9	447.3	446.7	446.1	445.5
137.5°	471.8	471.9	471.9	471.7	471.1	470.6	470.1	469.6
140°	486.0	486.3	486.5	486.3	485.6	485.0	484.4	483.8
142.5°	500.0	500.0	500.1	499.8	499.2	498.6	498.0	497.4
145°	519.7	519.8	519.9	519.6	519.0	518.4	517.8	517.2
147.5°	536.5	536.6	536.7	536.4	535.7	535.0	534.2	533.5
150°	547.2	547.4	547.6	547.3	546.5	545.7	544.9	544.1
152.5°	556.7	556.9	557.1	556.9	556.1	555.4	554.7	554.0
155°	569.9	570.2	570.5	570.2	569.4	568.6	567.7	566.9
157.5°	580.7	581.0	581.3	581.1	580.3	579.5	578.7	577.8
160°	587.4	587.8	588.2	588.0	587.2	586.4	585.6	584.8
162.5°	593.6	594.2	594.7	594.6	593.7	592.8	591.9	591.0
165°	601.6	602.2	602.8	602.7	601.9	601.0	600.2	599.4
167.5°	607.5	608.2	608.9	608.9	607.9	607.0	606.1	605.2
170°	610.6	611.5	612.3	612.2	611.3	610.4	609.5	608.5
172.5°	613.0	613.7	614.5	614.4	613.5	612.6	611.7	610.8
175°	615.6	616.4	617.2	617.2	616.3	615.4	614.5	613.6
177.5°	616.7	617.2	617.8	617.8	617.1	616.5	615.8	615.2
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3

(END OF REPORT)