

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333375-840

Luminaire Tested: **S125DIW-S610D470U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333375-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D470U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4166.2 lumens
Efficiency: N/A
Efficacy: 138.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333375-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333375-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	41	48	42	37	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333375-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	2.2
10°-20°	258.3	6.2
20°-30°	381.4	9.2
30°-40°	445.0	10.7
40°-50°	447.0	10.7
50°-60°	392.4	9.4
60°-70°	292.4	7.0
70°-80°	167.2	4.0
80°-90°	49.9	1.2
90°-100°	39.4	0.9
100°-110°	116.3	2.8
110°-120°	197.1	4.7
120°-130°	259.3	6.2
130°-140°	290.6	7.0
140°-150°	284.8	6.8
150°-160°	239.2	5.7
160°-170°	159.0	3.8
170°-180°	55.6	1.3
0°-30°	731.2	17.5
0°-40°	1176.2	28.2
0°-60°	2015.6	48.4
0°-90°	2525.0	60.6
90°-120°	352.8	8.5
90°-150°	1187.4	28.5
90°-180°	1641.0	39.4
0°-180°	4166.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	0	4	7	10	11	4
95°	30	31	35	38	39	32
105°	104	107	109	112	114	111
115°	197	199	200	200	199	195
125°	288	290	291	290	290	258
135°	374	377	378	378	376	288
145°	454	455	457	457	455	283
155°	519	519	520	521	519	239
165°	564	564	564	565	563	159
175°	587	585	585	587	584	56
180°	588	588	588	588	588	



TEST NUMBER: P333375-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.7	16.9	17.0	17.2	17.3	17.4	17.4	17.4	17.4	17.5	17.6
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.4	7.9
92.5°	11.1	11.6	12.2	12.8	13.3	14.0	14.9	15.9	16.7	17.6	18.3
95°	29.8	30.0	30.2	30.4	30.6	31.2	32.2	33.2	34.2	35.2	36.0
97.5°	49.4	49.5	49.6	49.7	49.8	50.5	51.9	53.3	54.7	56.1	56.8
100°	64.1	64.1	64.1	64.1	64.1	64.7	66.0	67.4	68.7	70.0	71.0
102.5°	79.8	80.2	80.7	81.1	81.5	82.0	82.7	83.3	84.0	84.6	85.6
105°	104.3	104.8	105.3	105.8	106.4	106.9	107.6	108.2	108.8	109.4	110.0
107.5°	131.5	132.0	132.5	133.0	133.5	134.0	134.4	134.9	135.4	135.8	136.1
110°	150.2	150.7	151.2	151.7	152.2	152.6	152.9	153.2	153.5	153.8	154.1



TEST NUMBER: P333375-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.2	169.5	169.7	170.0	170.3	170.6	171.0	171.4	171.7	172.1	172.3
115°	197.2	197.6	198.1	198.5	198.9	199.2	199.4	199.7	199.9	200.1	200.0
117.5°	225.5	225.6	225.8	226.0	226.2	226.4	226.6	226.7	226.9	227.1	227.2
120°	243.1	243.6	244.1	244.6	245.1	245.4	245.5	245.6	245.7	245.8	245.8
122.5°	262.1	262.3	262.5	262.7	262.8	263.1	263.3	263.6	263.9	264.1	264.0
125°	287.9	288.5	289.1	289.7	290.3	290.7	290.8	290.9	291.0	291.1	290.9
127.5°	315.4	315.7	316.1	316.4	316.8	317.0	317.1	317.2	317.3	317.5	317.4
130°	331.8	332.3	332.9	333.4	333.9	334.3	334.5	334.7	334.9	335.1	335.0
132.5°	348.3	349.1	350.0	350.8	351.6	352.0	352.0	351.9	351.9	351.8	351.7
135°	374.4	375.1	375.7	376.3	376.9	377.2	377.3	377.4	377.5	377.6	377.6
137.5°	398.9	399.5	400.1	400.7	401.3	401.7	401.9	402.1	402.3	402.6	402.7
140°	414.7	415.2	415.7	416.2	416.7	417.2	417.5	417.8	418.1	418.4	418.6
142.5°	430.4	430.8	431.3	431.7	432.1	432.5	432.9	433.3	433.7	434.1	434.2
145°	453.6	454.0	454.4	454.8	455.2	455.6	455.9	456.2	456.5	456.8	456.8
147.5°	475.0	475.2	475.4	475.6	475.9	476.2	476.4	476.7	476.9	477.2	477.4
150°	489.3	489.2	489.1	489.0	488.9	489.1	489.5	489.9	490.3	490.7	490.7
152.5°	501.0	501.2	501.3	501.4	501.6	501.7	501.9	502.1	502.2	502.4	502.6
155°	519.1	519.1	519.1	519.1	519.1	519.1	519.2	519.3	519.4	519.5	519.9
157.5°	535.1	534.9	534.7	534.5	534.2	534.2	534.3	534.4	534.5	534.6	535.0
160°	544.7	544.4	544.0	543.7	543.4	543.3	543.4	543.5	543.6	543.7	544.2
162.5°	553.1	552.9	552.7	552.4	552.2	552.1	552.1	552.1	552.2	552.2	552.7
165°	564.3	564.1	563.9	563.7	563.5	563.5	563.6	563.7	563.8	563.9	564.3
167.5°	573.9	573.5	573.1	572.7	572.3	572.1	572.1	572.1	572.1	572.1	572.7
170°	579.0	578.6	578.1	577.7	577.3	577.1	577.1	577.1	577.1	577.1	577.7
172.5°	582.7	582.3	581.9	581.5	581.1	580.9	580.9	580.9	580.9	580.9	581.5
175°	586.8	586.3	585.9	585.5	585.1	584.9	584.9	584.9	584.9	584.9	585.5
177.5°	588.9	588.5	588.2	587.9	587.5	587.3	587.3	587.2	587.1	587.0	587.5
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333375-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	17.7	17.8	17.9	17.8	17.6	17.4	17.2	17.0
90°	8.4	8.9	9.4	9.8	10.1	10.4	10.7	11.0
92.5°	18.9	19.6	20.3	20.7	20.9	21.1	21.4	21.6
95°	36.7	37.4	38.1	38.6	38.8	39.0	39.2	39.4
97.5°	57.5	58.2	58.8	59.2	59.3	59.5	59.6	59.7
100°	71.9	72.8	73.7	74.2	74.4	74.6	74.8	75.0
102.5°	86.6	87.7	88.7	89.3	89.6	89.9	90.2	90.5
105°	110.6	111.2	111.8	112.3	112.6	112.9	113.2	113.5
107.5°	136.4	136.7	137.0	137.2	137.2	137.1	137.1	137.1
110°	154.4	154.7	155.0	155.1	155.0	154.9	154.8	154.7



TEST NUMBER: P333375-840

CATALOG NUMBER: S125DIW-S610D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	172.4	172.5	172.7	172.7	172.5	172.3	172.1	171.9
115°	199.9	199.8	199.7	199.5	199.4	199.3	199.2	199.1
117.5°	227.3	227.3	227.4	227.3	226.9	226.5	226.0	225.6
120°	245.8	245.8	245.8	245.6	245.2	244.8	244.4	244.0
122.5°	264.0	263.9	263.8	263.6	263.3	263.0	262.6	262.3
125°	290.7	290.5	290.3	290.1	290.0	289.9	289.8	289.7
127.5°	317.3	317.2	317.1	316.9	316.7	316.5	316.3	316.1
130°	334.9	334.8	334.7	334.5	334.3	334.1	333.9	333.7
132.5°	351.6	351.5	351.4	351.3	351.0	350.7	350.4	350.1
135°	377.6	377.6	377.6	377.4	377.0	376.6	376.2	375.8
137.5°	402.8	402.9	403.1	402.9	402.4	401.9	401.3	400.8
140°	418.8	419.0	419.2	419.0	418.5	418.0	417.5	417.0
142.5°	434.3	434.4	434.5	434.3	433.8	433.3	432.8	432.3
145°	456.8	456.8	456.8	456.7	456.4	456.1	455.8	455.4
147.5°	477.6	477.9	478.1	477.9	477.2	476.5	475.7	475.1
150°	490.7	490.7	490.7	490.6	490.4	490.2	490.0	489.8
152.5°	502.9	503.1	503.3	503.3	502.9	502.6	502.2	501.8
155°	520.3	520.7	521.1	521.1	520.6	520.1	519.6	519.1
157.5°	535.4	535.8	536.2	536.1	535.4	534.7	534.1	533.4
160°	544.6	545.0	545.4	545.3	544.8	544.3	543.8	543.3
162.5°	553.2	553.6	554.1	554.1	553.5	552.9	552.3	551.7
165°	564.7	565.1	565.5	565.4	564.8	564.2	563.6	563.0
167.5°	573.3	573.9	574.5	574.5	573.8	573.2	572.6	572.0
170°	578.3	579.0	579.7	579.6	578.9	578.1	577.4	576.7
172.5°	582.1	582.7	583.3	583.3	582.6	582.0	581.4	580.8
175°	586.1	586.8	587.4	587.3	586.6	585.9	585.2	584.5
177.5°	588.0	588.5	589.1	589.0	588.4	587.8	587.2	586.7
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1

(END OF REPORT)