

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333376-840

Luminaire Tested: **S125DIW-S610D770U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333376-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D770U840-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5652.3 lumens
Efficiency: N/A
Efficacy: 150.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	85	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	41	39	37	33				
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	28	24				
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	28	49	38	32	27	33	27	23	27	23	20	22	19	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13				
10	46	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5837	5837	5837	5837
5°	6760	5857	5128	5857
10°	7864	5827	4494	5827
15°	8705	5784	4145	5784
20°	9745	5716	3865	5716
25°	11416	5640	3729	5640
30°	12331	5565	3610	5565
35°	10138	5423	3533	5423
40°	7206	5227	3447	5227
45°	5536	4961	3399	4961
50°	4725	4633	3392	4633
55°	4208	4310	3422	4310
60°	3796	3959	3509	3959
65°	3506	3605	3599	3605
70°	3186	3238	3652	3238
75°	2815	2852	3618	2852
80°	2369	2325	3310	2325
85°	1875	1675	2675	1675



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.5
10°-20°	259.1	4.6
20°-30°	420.7	7.4
30°-40°	513.1	9.1
40°-50°	466.8	8.3
50°-60°	371.8	6.6
60°-70°	259.0	4.6
70°-80°	138.1	2.4
80°-90°	36.9	0.7
90°-100°	36.7	0.6
100°-110°	226.1	4.0
110°-120°	410.0	7.3
120°-130°	526.2	9.3
130°-140°	566.0	10.0
140°-150°	531.3	9.4
150°-160°	429.7	7.6
160°-170°	277.9	4.9
170°-180°	95.9	1.7
0°-30°	766.7	13.6
0°-40°	1279.9	22.6
0°-60°	2118.5	37.5
0°-90°	2552.5	45.2
90°-120°	672.8	11.9
90°-150°	2296.2	40.6
90°-180°	3100.0	54.8
0°-180°	5652.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1043	903	791	903	1043	105
15°	1302	865	620	865	1302	373
25°	1602	791	523	791	1602	732
35°	1286	688	448	688	1286	787
45°	606	543	372	543	606	485
55°	374	383	304	383	374	337
65°	229	236	236	236	229	228
75°	113	114	145	114	113	121
85°	25	23	36	23	25	30
90°	18	1	18	1	18	9
95°	16	43	16	43	16	13
105°	222	220	222	220	222	201
115°	410	413	410	413	410	407
125°	587	587	587	587	587	523
135°	730	733	730	733	730	563
145°	847	849	847	849	847	529
155°	929	935	929	935	929	428
165°	982	987	982	987	982	277
175°	1005	1010	1005	1010	1005	96
180°	1010	1010	1010	1010	1010	



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	956.0	954.7	953.5	951.1	952.9	947.7	945.2	941.0	935.7	933.9	931.7
5°	1042.7	1044.6	1046.5	1038.4	1039.3	1033.9	1021.6	1011.6	1003.6	993.2	985.9
7.5°	1147.0	1142.5	1142.2	1136.9	1127.9	1120.7	1107.8	1091.4	1075.5	1057.4	1042.5
10°	1199.2	1199.6	1196.2	1190.0	1180.4	1173.5	1156.6	1140.5	1121.0	1097.9	1081.5
12.5°	1238.5	1240.1	1235.8	1227.5	1222.7	1207.3	1194.1	1174.9	1151.7	1133.3	1108.1
15°	1302.0	1297.8	1294.7	1284.3	1276.3	1260.2	1239.1	1219.1	1193.9	1170.4	1147.0
17.5°	1363.2	1366.7	1360.9	1351.4	1326.5	1307.6	1279.3	1252.0	1220.4	1189.1	1161.1
20°	1417.9	1421.0	1412.1	1395.6	1365.7	1346.9	1309.7	1274.3	1238.0	1197.7	1167.0
22.5°	1486.0	1483.6	1471.7	1446.5	1420.7	1385.8	1345.6	1302.6	1257.0	1211.4	1170.6
25°	1602.0	1585.9	1578.6	1547.5	1513.4	1462.4	1407.1	1344.2	1287.5	1227.2	1175.1
27.5°	1666.3	1661.2	1653.1	1631.4	1595.6	1541.1	1475.9	1399.3	1319.1	1243.1	1174.8
30°	1653.5	1654.2	1655.0	1648.0	1625.1	1584.0	1519.1	1436.6	1341.5	1256.0	1177.0
32.5°	1539.2	1553.2	1566.6	1582.4	1588.8	1580.9	1540.3	1465.8	1368.0	1270.7	1175.7
35°	1285.9	1290.1	1333.5	1376.4	1434.7	1480.1	1510.4	1477.3	1394.8	1283.2	1174.3
37.5°	1002.6	1023.4	1053.4	1102.0	1186.1	1261.4	1358.4	1402.9	1376.2	1287.3	1171.5
40°	854.7	873.9	893.4	942.9	1013.9	1105.2	1215.3	1309.3	1331.2	1274.3	1162.4
42.5°	740.5	755.8	777.5	814.7	873.9	954.8	1060.1	1182.9	1258.4	1237.0	1143.1
45°	606.1	615.7	632.6	662.2	705.1	768.4	861.2	995.5	1112.5	1151.2	1097.1
47.5°	518.8	518.8	531.9	552.3	583.3	637.0	705.7	810.9	935.8	1028.3	1024.0
50°	470.3	468.4	478.8	496.4	521.0	556.6	622.3	706.3	826.4	931.1	960.2
52.5°	428.6	428.8	435.2	448.2	468.8	499.3	548.3	624.0	726.6	834.0	889.0
55°	373.7	372.1	379.4	388.2	403.2	423.1	458.5	516.3	599.6	705.5	776.8
57.5°	323.4	327.5	330.4	336.6	349.0	362.3	392.1	434.6	500.7	591.6	667.0
60°	293.9	298.1	300.3	306.5	316.5	328.0	351.0	385.6	441.2	519.5	594.2
62.5°	267.4	270.7	271.6	277.0	285.2	296.4	314.5	343.5	387.5	455.9	529.2
65°	229.4	229.4	231.0	236.7	240.5	250.5	264.3	285.4	320.7	374.1	436.6
67.5°	192.7	194.6	194.2	196.7	200.3	208.0	217.9	235.3	261.5	300.3	350.4
70°	168.7	170.4	170.0	171.9	175.7	180.7	188.7	205.2	224.0	257.4	300.3
72.5°	147.3	147.9	146.9	149.5	151.8	156.1	165.1	173.9	191.5	219.6	255.0
75°	112.8	113.5	114.3	115.8	118.2	120.5	125.0	133.9	145.4	166.5	189.1
77.5°	84.5	83.1	84.9	84.7	86.0	87.8	91.8	96.5	105.9	119.3	136.8
80°	63.7	64.0	64.0	64.4	66.3	67.6	71.0	74.4	81.7	91.7	103.9
82.5°	46.5	47.5	46.9	47.6	49.2	50.0	51.9	54.7	59.0	66.9	75.7
85°	25.3	23.4	24.1	24.9	24.9	25.3	26.9	28.0	30.3	33.3	36.9
87.5°	11.0	11.5	11.7	11.6	11.8	11.6	12.7	12.5	13.3	14.0	15.0
90°	18.0	17.5	17.0	16.5	16.0	15.2	14.4	13.6	12.8	12.0	10.8
92.5°	16.8	16.6	16.3	16.1	15.9	15.2	14.4	13.6	12.8	12.0	10.9
95°	15.8	15.8	15.8	15.8	15.8	15.2	14.4	13.6	12.8	12.0	18.3
97.5°	15.8	15.8	15.8	15.8	15.8	18.1	22.7	27.5	32.1	36.9	49.3
100°	15.8	16.4	17.1	17.7	18.4	31.1	55.8	80.7	105.4	130.2	129.6
102.5°	94.1	105.4	116.7	128.1	139.4	147.3	152.1	156.7	161.5	166.1	165.7
105°	222.3	222.4	222.6	222.8	222.9	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.1	280.6	281.1	281.7	282.2	282.4	282.4	282.4	282.3	282.3	282.0
110°	320.2	320.1	319.9	319.7	319.6	319.7	320.2	320.7	321.2	321.7	321.4



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.2	356.4	356.7	356.9	357.1	357.5	358.2	358.8	359.4	360.1	359.9
115°	410.0	411.0	412.0	413.0	414.0	414.9	415.6	416.2	416.9	417.6	417.4
117.5°	467.6	468.0	468.4	468.8	469.3	469.9	470.8	471.6	472.5	473.3	472.7
120°	502.8	503.7	504.5	505.3	506.1	506.8	507.1	507.5	507.8	508.1	507.6
122.5°	536.3	537.3	538.3	539.3	540.2	540.9	541.2	541.5	541.9	542.2	542.0
125°	587.4	587.9	588.3	588.9	589.4	590.0	590.7	591.3	592.0	592.6	592.6
127.5°	630.4	631.6	632.8	634.0	635.3	636.1	636.4	636.8	637.1	637.5	637.6
130°	661.5	662.3	663.2	664.0	664.8	665.5	666.0	666.5	666.9	667.4	667.3
132.5°	690.2	691.1	691.9	692.7	693.6	694.0	694.1	694.2	694.3	694.4	694.8
135°	729.5	730.5	731.5	732.6	733.6	734.3	734.6	734.9	735.2	735.6	735.9
137.5°	769.1	769.9	770.8	771.6	772.5	773.0	772.8	772.8	772.7	772.6	773.0
140°	792.4	793.5	794.5	795.4	796.4	796.8	796.4	796.1	795.8	795.4	795.6
142.5°	814.6	815.6	816.6	817.6	818.6	819.0	819.0	818.9	818.8	818.8	818.5
145°	847.1	848.1	849.0	850.0	851.0	851.4	851.3	851.1	850.9	850.8	850.8
147.5°	873.8	875.0	876.3	877.5	878.6	879.1	878.9	878.7	878.5	878.3	878.1
150°	891.2	892.5	893.8	895.1	896.6	897.1	896.7	896.4	896.1	895.6	895.3
152.5°	907.4	908.6	909.8	910.9	912.1	912.6	912.2	911.9	911.6	911.2	910.9
155°	928.6	930.0	931.3	932.6	933.9	934.3	933.8	933.3	932.8	932.3	932.0
157.5°	946.4	947.8	949.1	950.4	951.7	952.1	951.6	951.1	950.6	950.0	950.0
160°	957.8	959.2	960.5	961.8	963.1	963.4	962.8	962.1	961.5	960.8	960.6
162.5°	968.0	969.5	970.9	972.4	973.8	974.1	973.1	972.2	971.3	970.4	970.2
165°	981.7	983.1	984.4	985.7	987.0	987.2	986.2	985.2	984.2	983.2	983.1
167.5°	991.3	992.8	994.3	995.8	997.3	997.4	996.2	995.0	993.8	992.7	992.5
170°	996.7	998.2	999.7	1001.2	1002.7	1002.8	1001.5	1000.1	998.8	997.4	997.2
172.5°	1000.3	1001.8	1003.3	1004.8	1006.2	1006.4	1005.2	1004.0	1002.8	1001.7	1001.4
175°	1004.9	1006.4	1007.9	1009.5	1010.9	1011.0	1009.7	1008.4	1007.0	1005.7	1005.5
177.5°	1007.6	1008.7	1009.8	1010.8	1011.9	1012.0	1011.0	1010.1	1009.2	1008.2	1008.0
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	929.9	927.8	925.3	921.0	915.7	913.0	908.8	905.9	900.4	895.9	890.9
5°	977.0	967.1	958.0	946.0	933.0	924.5	914.5	903.4	891.9	880.0	867.0
7.5°	1025.9	1008.4	989.2	968.5	948.4	929.8	912.0	894.6	878.4	858.7	842.0
10°	1058.8	1036.5	1012.8	984.7	957.6	933.7	909.6	888.5	867.0	843.9	823.6
12.5°	1091.7	1062.0	1028.4	997.6	964.9	936.2	907.8	880.8	853.8	828.3	804.7
15°	1114.8	1088.7	1057.6	1013.9	977.0	937.6	900.0	865.1	832.4	804.1	774.2
17.5°	1130.0	1096.5	1063.1	1021.2	972.9	928.7	886.1	846.2	809.4	773.4	744.6
20°	1132.9	1098.3	1063.4	1022.4	972.9	922.2	879.7	831.7	792.1	755.0	719.6
22.5°	1132.0	1092.8	1054.8	1012.5	964.3	917.7	866.2	817.3	774.4	737.8	700.9
25°	1123.3	1081.5	1033.9	991.3	943.7	894.2	842.0	791.4	747.7	705.9	669.4
27.5°	1116.0	1061.8	1007.9	958.3	912.3	867.0	817.1	765.2	716.7	674.3	640.0
30°	1107.1	1047.6	987.0	935.2	888.1	843.9	796.8	746.2	695.5	654.1	617.2
32.5°	1099.1	1029.9	965.9	909.5	859.6	816.7	773.2	725.0	675.3	633.2	596.4
35°	1083.8	1003.6	930.3	866.6	813.2	769.2	732.8	687.8	642.2	601.5	566.2
37.5°	1064.2	969.1	890.4	823.6	765.2	718.7	684.8	650.4	606.5	567.3	535.4
40°	1048.8	944.5	861.2	792.9	732.4	684.0	652.6	620.0	583.5	547.0	513.3
42.5°	1029.5	922.4	831.7	758.3	698.3	651.2	618.1	590.5	558.4	524.3	493.0
45°	994.0	882.3	784.2	705.1	644.5	598.0	563.9	543.2	519.1	486.9	460.4
47.5°	941.7	834.2	732.7	651.1	588.5	545.5	513.5	493.6	476.7	452.7	428.7
50°	895.3	798.3	695.5	614.6	552.0	508.7	479.2	461.1	446.6	428.1	407.8
52.5°	843.5	753.2	659.0	579.0	517.1	474.3	445.4	429.5	417.4	404.1	384.2
55°	761.1	684.4	596.9	521.0	463.8	422.0	396.7	382.8	372.8	362.9	350.6
57.5°	670.3	610.4	532.8	463.4	410.8	372.7	349.1	335.7	327.9	322.8	315.6
60°	606.5	555.1	488.4	425.1	373.7	339.9	316.9	306.5	300.0	295.8	290.4
62.5°	547.2	505.0	443.2	385.5	340.5	308.6	288.0	278.0	271.8	269.7	265.2
65°	460.0	427.4	376.4	328.4	290.0	262.8	245.5	235.9	232.1	229.7	230.1
67.5°	374.0	354.1	313.2	272.3	241.6	218.7	204.9	197.5	195.6	192.6	192.5
70°	321.4	306.5	272.0	236.3	209.0	191.5	179.2	171.5	169.6	168.0	167.6
72.5°	275.1	262.1	232.1	203.5	179.0	163.5	153.4	148.8	145.6	144.7	144.6
75°	206.8	199.4	175.7	153.1	136.2	125.4	118.6	114.3	112.0	111.6	112.0
77.5°	147.0	140.7	125.5	109.5	98.9	90.7	84.8	83.4	80.8	80.9	80.5
80°	110.5	106.2	96.6	84.0	75.2	68.3	65.2	62.5	61.8	60.6	61.8
82.5°	80.1	75.5	69.1	61.0	53.7	49.6	46.5	45.6	45.1	44.6	44.8
85°	39.5	39.9	36.1	29.9	26.9	24.5	22.6	22.6	22.2	21.9	22.2
87.5°	15.5	14.5	13.1	11.9	10.2	9.0	8.4	8.5	7.8	7.8	8.3
90°	9.7	8.5	7.3	6.1	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	9.9	8.9	7.9	7.8	8.7	9.7	10.6	11.5	10.6	9.7	8.7
95°	24.6	30.9	37.3	40.7	41.2	41.6	42.1	42.6	42.1	41.6	41.2
97.5°	61.8	74.3	86.8	92.6	91.7	90.9	90.0	89.1	90.0	90.9	91.7
100°	128.9	128.3	127.5	126.9	126.4	125.9	125.4	124.9	125.4	125.9	126.4
102.5°	165.3	164.9	164.5	164.0	163.4	162.8	162.1	161.5	162.1	162.8	163.4
105°	223.0	223.0	223.0	222.7	222.0	221.4	220.7	219.9	220.7	221.4	222.0
107.5°	281.6	281.2	280.9	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7
110°	321.1	320.7	320.4	320.2	320.2	320.2	320.2	320.2	320.2	320.2	320.2



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	359.7	359.5	359.3	359.0	358.6	358.2	357.8	357.4	357.8	358.2	358.6
115°	417.2	417.1	416.9	416.4	415.6	414.8	413.8	413.0	413.8	414.8	415.6
117.5°	472.1	471.5	470.8	470.5	470.6	470.6	470.6	470.7	470.6	470.6	470.6
120°	507.1	506.5	506.0	505.9	506.0	506.2	506.4	506.5	506.4	506.2	506.0
122.5°	541.7	541.5	541.3	540.9	540.2	539.6	539.0	538.3	539.0	539.6	540.2
125°	592.6	592.6	592.6	592.1	590.9	589.8	588.5	587.4	588.5	589.8	590.9
127.5°	637.7	637.8	637.9	637.5	636.7	635.9	635.1	634.2	635.1	635.9	636.7
130°	667.1	666.9	666.8	666.3	665.5	664.6	663.8	663.0	663.8	664.6	665.5
132.5°	695.1	695.5	695.9	695.6	694.6	693.7	692.7	691.7	692.7	693.7	694.6
135°	736.2	736.6	736.9	736.6	735.6	734.6	733.6	732.6	733.6	734.6	735.6
137.5°	773.3	773.6	773.9	773.6	772.7	771.8	771.0	770.1	771.0	771.8	772.7
140°	795.8	795.9	796.1	796.0	795.7	795.4	795.0	794.7	795.0	795.4	795.7
142.5°	818.3	818.1	817.8	817.6	817.4	817.2	817.0	816.8	817.0	817.2	817.4
145°	850.8	850.8	850.8	850.6	850.3	850.0	849.6	849.3	849.6	850.0	850.3
147.5°	877.9	877.8	877.6	877.5	877.6	877.6	877.7	877.8	877.7	877.6	877.6
150°	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	895.3	895.0	894.6
152.5°	910.6	910.3	909.9	910.1	910.9	911.6	912.3	913.0	912.3	911.6	910.9
155°	931.7	931.4	931.0	931.4	932.3	933.3	934.3	935.3	934.3	933.3	932.3
157.5°	950.0	949.9	949.9	950.2	950.8	951.4	952.0	952.5	952.0	951.4	950.8
160°	960.5	960.3	960.1	960.6	961.5	962.5	963.5	964.5	963.5	962.5	961.5
162.5°	970.1	969.9	969.7	970.1	971.1	972.1	973.1	974.1	973.1	972.1	971.1
165°	982.9	982.7	982.6	983.0	984.0	985.0	985.9	986.9	985.9	985.0	984.0
167.5°	992.3	992.2	992.0	992.4	993.5	994.5	995.5	996.5	995.5	994.5	993.5
170°	997.1	996.9	996.7	997.2	998.5	999.6	1000.8	1002.0	1000.8	999.6	998.5
172.5°	1001.1	1000.8	1000.5	1000.9	1002.0	1003.2	1004.4	1005.5	1004.4	1003.2	1002.0
175°	1005.3	1005.2	1005.0	1005.4	1006.4	1007.4	1008.5	1009.5	1008.5	1007.4	1006.4
177.5°	1007.9	1007.8	1007.6	1008.0	1008.9	1009.7	1010.4	1011.2	1010.4	1009.7	1008.9
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	888.2	884.7	882.0	875.9	872.5	867.9	864.2	868.2	863.9	865.8	863.0
5°	860.5	849.7	842.0	830.9	821.3	812.5	806.0	804.9	801.7	800.2	795.7
7.5°	827.2	813.7	800.5	786.0	773.7	761.2	753.2	746.6	742.3	736.5	732.6
10°	807.5	789.5	774.2	756.5	741.1	727.7	717.0	711.7	706.6	699.3	696.7
12.5°	783.3	764.7	745.9	727.0	712.4	697.3	688.1	680.0	676.6	668.3	667.5
15°	754.2	726.2	707.8	688.6	668.2	656.0	648.3	639.5	635.7	630.0	625.7
17.5°	719.5	694.5	671.5	651.7	634.2	623.9	614.3	608.2	601.7	597.9	591.0
20°	694.4	670.6	647.5	626.4	613.0	601.2	593.5	587.7	580.8	578.9	572.0
22.5°	673.2	646.9	624.8	607.1	592.5	579.1	570.8	566.8	562.1	556.1	554.8
25°	638.7	611.5	592.7	575.0	562.0	549.8	544.0	539.0	534.4	530.2	528.7
27.5°	608.9	584.6	562.3	546.3	535.0	523.8	518.8	512.7	509.3	505.9	501.8
30°	588.1	563.2	543.6	528.3	515.9	506.0	500.6	496.4	493.3	490.3	488.0
32.5°	566.6	543.5	524.5	509.6	497.3	489.8	484.9	482.0	478.6	474.9	472.0
35°	538.3	512.9	494.5	481.4	471.8	466.1	460.7	458.1	454.2	454.2	451.1
37.5°	506.2	484.3	468.1	456.2	447.6	442.4	436.7	434.8	432.3	430.7	429.7
40°	487.2	466.9	451.5	439.6	430.4	426.2	421.6	418.5	417.0	415.1	414.3
42.5°	467.6	448.2	433.4	422.4	414.4	410.8	406.6	404.5	401.3	398.8	398.4
45°	437.7	418.9	405.5	396.7	389.8	385.6	382.8	378.3	376.7	373.7	373.2
47.5°	409.4	391.3	378.2	370.9	364.9	361.4	357.2	352.6	350.8	349.3	349.2
50°	388.2	371.7	359.4	352.5	346.8	341.8	337.6	334.6	333.4	333.4	334.2
52.5°	366.8	352.7	342.2	333.9	328.4	323.1	319.2	317.3	315.6	317.4	318.8
55°	335.3	321.1	313.5	305.4	300.0	293.9	292.0	291.1	290.0	293.1	294.6
57.5°	301.9	292.1	283.1	275.1	270.2	266.7	264.1	263.7	265.8	267.2	272.3
60°	280.8	269.3	261.3	255.1	249.3	247.0	246.3	245.5	247.0	251.3	257.8
62.5°	257.5	248.1	239.4	234.9	230.7	226.8	226.6	227.1	230.1	235.0	241.6
65°	223.3	215.2	209.4	204.1	200.7	198.3	199.1	200.7	204.1	210.7	217.9
67.5°	188.5	183.0	177.8	173.5	170.2	170.2	171.0	173.3	177.3	184.8	191.5
70°	166.1	160.0	155.7	153.8	151.2	149.7	151.9	155.7	159.2	166.1	171.9
72.5°	143.7	138.5	135.2	133.9	132.7	131.5	132.3	136.4	141.1	148.0	154.7
75°	110.5	108.6	106.2	104.7	103.6	104.3	105.1	109.0	112.8	120.1	127.7
77.5°	80.7	78.7	77.3	76.9	76.2	76.6	78.8	81.6	85.4	90.7	96.5
80°	61.0	60.2	59.5	59.1	59.1	59.5	62.5	64.4	67.9	72.9	77.5
82.5°	44.4	43.9	43.8	43.7	44.0	44.1	45.9	48.5	51.3	55.1	59.1
85°	23.4	22.6	23.8	24.1	23.4	24.5	25.3	26.9	28.0	29.9	31.8
87.5°	8.9	9.8	9.7	10.2	10.4	11.3	11.1	12.5	13.3	14.1	13.9
90°	6.1	7.3	8.5	9.7	10.8	12.0	12.8	13.6	14.4	15.2	16.0
92.5°	7.8	7.9	8.9	9.9	10.9	12.0	12.8	13.6	14.4	15.2	15.9
95°	40.7	37.3	30.9	24.6	18.3	12.0	12.8	13.6	14.4	15.2	15.8
97.5°	92.6	86.8	74.3	61.8	49.3	36.9	32.1	27.5	22.7	18.1	15.8
100°	126.9	127.5	128.3	128.9	129.6	130.2	105.4	80.7	55.8	31.1	18.4
102.5°	164.0	164.5	164.9	165.3	165.7	166.1	161.5	156.7	152.1	147.3	139.4
105°	222.7	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0	222.9
107.5°	280.7	280.9	281.2	281.6	282.0	282.3	282.3	282.4	282.4	282.4	282.2
110°	320.2	320.4	320.7	321.1	321.4	321.7	321.2	320.7	320.2	319.7	319.6



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	359.0	359.3	359.5	359.7	359.9	360.1	359.4	358.8	358.2	357.5	357.1
115°	416.4	416.9	417.1	417.2	417.4	417.6	416.9	416.2	415.6	414.9	414.0
117.5°	470.5	470.8	471.5	472.1	472.7	473.3	472.5	471.6	470.8	469.9	469.3
120°	505.9	506.0	506.5	507.1	507.6	508.1	507.8	507.5	507.1	506.8	506.1
122.5°	540.9	541.3	541.5	541.7	542.0	542.2	541.9	541.5	541.2	540.9	540.2
125°	592.1	592.6	592.6	592.6	592.6	592.6	592.0	591.3	590.7	590.0	589.4
127.5°	637.5	637.9	637.8	637.7	637.6	637.5	637.1	636.8	636.4	636.1	635.3
130°	666.3	666.8	666.9	667.1	667.3	667.4	666.9	666.5	666.0	665.5	664.8
132.5°	695.6	695.9	695.5	695.1	694.8	694.4	694.3	694.2	694.1	694.0	693.6
135°	736.6	736.9	736.6	736.2	735.9	735.6	735.2	734.9	734.6	734.3	733.6
137.5°	773.6	773.9	773.6	773.3	773.0	772.6	772.7	772.8	772.8	773.0	772.5
140°	796.0	796.1	795.9	795.8	795.6	795.4	795.8	796.1	796.4	796.8	796.4
142.5°	817.6	817.8	818.1	818.3	818.5	818.8	818.8	818.9	819.0	819.0	818.6
145°	850.6	850.8	850.8	850.8	850.8	850.8	850.9	851.1	851.3	851.4	851.0
147.5°	877.5	877.6	877.8	877.9	878.1	878.3	878.5	878.7	878.9	879.1	878.6
150°	894.3	894.3	894.6	895.0	895.3	895.6	896.1	896.4	896.7	897.1	896.6
152.5°	910.1	909.9	910.3	910.6	910.9	911.2	911.6	911.9	912.2	912.6	912.1
155°	931.4	931.0	931.4	931.7	932.0	932.3	932.8	933.3	933.8	934.3	933.9
157.5°	950.2	949.9	949.9	950.0	950.0	950.0	950.6	951.1	951.6	952.1	951.7
160°	960.6	960.1	960.3	960.5	960.6	960.8	961.5	962.1	962.8	963.4	963.1
162.5°	970.1	969.7	969.9	970.1	970.2	970.4	971.3	972.2	973.1	974.1	973.8
165°	983.0	982.6	982.7	982.9	983.1	983.2	984.2	985.2	986.2	987.2	987.0
167.5°	992.4	992.0	992.2	992.3	992.5	992.7	993.8	995.0	996.2	997.4	997.3
170°	997.2	996.7	996.9	997.1	997.2	997.4	998.8	1000.1	1001.5	1002.8	1002.7
172.5°	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8	1004.0	1005.2	1006.4	1006.2
175°	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0	1008.4	1009.7	1011.0	1010.9
177.5°	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2	1010.1	1011.0	1012.0	1011.9
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	861.1	863.3	861.5	863.9	861.5	863.3	861.1	863.0	865.8	863.9	868.2
5°	793.8	790.2	792.5	791.0	792.5	790.2	793.8	795.7	800.2	801.7	804.9
7.5°	731.4	728.1	724.4	722.6	724.4	728.1	731.4	732.6	736.5	742.3	746.6
10°	692.5	688.2	687.8	685.2	687.8	688.2	692.5	696.7	699.3	706.6	711.7
12.5°	663.9	659.9	655.6	654.5	655.6	659.9	663.9	667.5	668.3	676.6	680.0
15°	623.4	620.4	617.6	620.0	617.6	620.4	623.4	625.7	630.0	635.7	639.5
17.5°	589.7	587.1	586.7	583.9	586.7	587.1	589.7	591.0	597.9	601.7	608.2
20°	568.6	566.6	567.3	562.4	567.3	566.6	568.6	572.0	578.9	580.8	587.7
22.5°	551.7	547.9	547.4	546.4	547.4	547.9	551.7	554.8	556.1	562.1	566.8
25°	525.2	523.3	521.4	523.3	521.4	523.3	525.2	528.7	530.2	534.4	539.0
27.5°	502.1	499.8	499.3	499.5	499.3	499.8	502.1	501.8	505.9	509.3	512.7
30°	488.0	484.1	484.5	484.1	484.5	484.1	488.0	488.0	490.3	493.3	496.4
32.5°	472.6	470.0	469.5	468.8	469.5	470.0	472.6	472.0	474.9	478.6	482.0
35°	450.0	450.0	448.1	448.1	448.1	450.0	450.0	451.1	454.2	454.2	458.1
37.5°	428.7	428.4	427.2	427.4	427.2	428.4	428.7	429.7	430.7	432.3	434.8
40°	412.7	412.4	411.2	408.9	411.2	412.4	412.7	414.3	415.1	417.0	418.5
42.5°	397.5	396.2	395.6	394.9	395.6	396.2	397.5	398.4	398.8	401.3	404.5
45°	373.2	373.2	372.5	372.1	372.5	373.2	373.2	373.2	373.7	376.7	378.3
47.5°	349.8	350.5	351.9	351.7	351.9	350.5	349.8	349.2	349.3	350.8	352.6
50°	335.7	336.1	337.2	337.6	337.2	336.1	335.7	334.2	333.4	333.4	334.6
52.5°	320.0	322.2	323.7	323.5	323.7	322.2	320.0	318.8	317.4	315.6	317.3
55°	298.1	300.7	303.5	303.9	303.5	300.7	298.1	294.6	293.1	290.0	291.1
57.5°	276.4	280.1	283.0	283.9	283.0	280.1	276.4	272.3	267.2	265.8	263.7
60°	261.7	266.6	270.0	271.7	270.0	266.6	261.7	257.8	251.3	247.0	245.5
62.5°	247.5	253.1	256.6	256.9	256.6	253.1	247.5	241.6	235.0	230.1	227.1
65°	224.4	230.1	233.3	235.5	233.3	230.1	224.4	217.9	210.7	204.1	200.7
67.5°	199.5	205.3	208.7	210.6	208.7	205.3	199.5	191.5	184.8	177.3	173.3
70°	181.5	187.2	191.8	193.4	191.8	187.2	181.5	171.9	166.1	159.2	155.7
72.5°	163.7	168.7	172.5	174.3	172.5	168.7	163.7	154.7	148.0	141.1	136.4
75°	132.7	139.7	143.1	145.0	143.1	139.7	132.7	127.7	120.1	112.8	109.0
77.5°	102.4	108.7	110.7	111.7	110.7	108.7	102.4	96.5	90.7	85.4	81.6
80°	82.1	85.9	88.7	89.0	88.7	85.9	82.1	77.5	72.9	67.9	64.4
82.5°	63.1	66.2	67.2	68.2	67.2	66.2	63.1	59.1	55.1	51.3	48.5
85°	34.5	36.1	36.5	36.1	36.5	36.1	34.5	31.8	29.9	28.0	26.9
87.5°	14.6	14.4	14.5	15.2	14.5	14.4	14.6	13.9	14.1	13.3	12.5
90°	16.5	17.0	17.5	18.0	17.5	17.0	16.5	16.0	15.2	14.4	13.6
92.5°	16.1	16.3	16.6	16.8	16.6	16.3	16.1	15.9	15.2	14.4	13.6
95°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.2	14.4	13.6
97.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	18.1	22.7	27.5
100°	17.7	17.1	16.4	15.8	16.4	17.1	17.7	18.4	31.1	55.8	80.7
102.5°	128.1	116.7	105.4	94.1	105.4	116.7	128.1	139.4	147.3	152.1	156.7
105°	222.8	222.6	222.4	222.3	222.4	222.6	222.8	222.9	223.0	223.0	223.0
107.5°	281.7	281.1	280.6	280.1	280.6	281.1	281.7	282.2	282.4	282.4	282.4
110°	319.7	319.9	320.1	320.2	320.1	319.9	319.7	319.6	319.7	320.2	320.7



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	356.9	356.7	356.4	356.2	356.4	356.7	356.9	357.1	357.5	358.2	358.8
115°	413.0	412.0	411.0	410.0	411.0	412.0	413.0	414.0	414.9	415.6	416.2
117.5°	468.8	468.4	468.0	467.6	468.0	468.4	468.8	469.3	469.9	470.8	471.6
120°	505.3	504.5	503.7	502.8	503.7	504.5	505.3	506.1	506.8	507.1	507.5
122.5°	539.3	538.3	537.3	536.3	537.3	538.3	539.3	540.2	540.9	541.2	541.5
125°	588.9	588.3	587.9	587.4	587.9	588.3	588.9	589.4	590.0	590.7	591.3
127.5°	634.0	632.8	631.6	630.4	631.6	632.8	634.0	635.3	636.1	636.4	636.8
130°	664.0	663.2	662.3	661.5	662.3	663.2	664.0	664.8	665.5	666.0	666.5
132.5°	692.7	691.9	691.1	690.2	691.1	691.9	692.7	693.6	694.0	694.1	694.2
135°	732.6	731.5	730.5	729.5	730.5	731.5	732.6	733.6	734.3	734.6	734.9
137.5°	771.6	770.8	769.9	769.1	769.9	770.8	771.6	772.5	773.0	772.8	772.8
140°	795.4	794.5	793.5	792.4	793.5	794.5	795.4	796.4	796.8	796.4	796.1
142.5°	817.6	816.6	815.6	814.6	815.6	816.6	817.6	818.6	819.0	819.0	818.9
145°	850.0	849.0	848.1	847.1	848.1	849.0	850.0	851.0	851.4	851.3	851.1
147.5°	877.5	876.3	875.0	873.8	875.0	876.3	877.5	878.6	879.1	878.9	878.7
150°	895.1	893.8	892.5	891.2	892.5	893.8	895.1	896.6	897.1	896.7	896.4
152.5°	910.9	909.8	908.6	907.4	908.6	909.8	910.9	912.1	912.6	912.2	911.9
155°	932.6	931.3	930.0	928.6	930.0	931.3	932.6	933.9	934.3	933.8	933.3
157.5°	950.4	949.1	947.8	946.4	947.8	949.1	950.4	951.7	952.1	951.6	951.1
160°	961.8	960.5	959.2	957.8	959.2	960.5	961.8	963.1	963.4	962.8	962.1
162.5°	972.4	970.9	969.5	968.0	969.5	970.9	972.4	973.8	974.1	973.1	972.2
165°	985.7	984.4	983.1	981.7	983.1	984.4	985.7	987.0	987.2	986.2	985.2
167.5°	995.8	994.3	992.8	991.3	992.8	994.3	995.8	997.3	997.4	996.2	995.0
170°	1001.2	999.7	998.2	996.7	998.2	999.7	1001.2	1002.7	1002.8	1001.5	1000.1
172.5°	1004.8	1003.3	1001.8	1000.3	1001.8	1003.3	1004.8	1006.2	1006.4	1005.2	1004.0
175°	1009.5	1007.9	1006.4	1004.9	1006.4	1007.9	1009.5	1010.9	1011.0	1009.7	1008.4
177.5°	1010.8	1009.8	1008.7	1007.6	1008.7	1009.8	1010.8	1011.9	1012.0	1011.0	1010.1
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	864.2	867.9	872.5	875.9	882.0	884.7	888.2	890.9	895.9	900.4	905.9
5°	806.0	812.5	821.3	830.9	842.0	849.7	860.5	867.0	880.0	891.9	903.4
7.5°	753.2	761.2	773.7	786.0	800.5	813.7	827.2	842.0	858.7	878.4	894.6
10°	717.0	727.7	741.1	756.5	774.2	789.5	807.5	823.6	843.9	867.0	888.5
12.5°	688.1	697.3	712.4	727.0	745.9	764.7	783.3	804.7	828.3	853.8	880.8
15°	648.3	656.0	668.2	688.6	707.8	726.2	754.2	774.2	804.1	832.4	865.1
17.5°	614.3	623.9	634.2	651.7	671.5	694.5	719.5	744.6	773.4	809.4	846.2
20°	593.5	601.2	613.0	626.4	647.5	670.6	694.4	719.6	755.0	792.1	831.7
22.5°	570.8	579.1	592.5	607.1	624.8	646.9	673.2	700.9	737.8	774.4	817.3
25°	544.0	549.8	562.0	575.0	592.7	611.5	638.7	669.4	705.9	747.7	791.4
27.5°	518.8	523.8	535.0	546.3	562.3	584.6	608.9	640.0	674.3	716.7	765.2
30°	500.6	506.0	515.9	528.3	543.6	563.2	588.1	617.2	654.1	695.5	746.2
32.5°	484.9	489.8	497.3	509.6	524.5	543.5	566.6	596.4	633.2	675.3	725.0
35°	460.7	466.1	471.8	481.4	494.5	512.9	538.3	566.2	601.5	642.2	687.8
37.5°	436.7	442.4	447.6	456.2	468.1	484.3	506.2	535.4	567.3	606.5	650.4
40°	421.6	426.2	430.4	439.6	451.5	466.9	487.2	513.3	547.0	583.5	620.0
42.5°	406.6	410.8	414.4	422.4	433.4	448.2	467.6	493.0	524.3	558.4	590.5
45°	382.8	385.6	389.8	396.7	405.5	418.9	437.7	460.4	486.9	519.1	543.2
47.5°	357.2	361.4	364.9	370.9	378.2	391.3	409.4	428.7	452.7	476.7	493.6
50°	337.6	341.8	346.8	352.5	359.4	371.7	388.2	407.8	428.1	446.6	461.1
52.5°	319.2	323.1	328.4	333.9	342.2	352.7	366.8	384.2	404.1	417.4	429.5
55°	292.0	293.9	300.0	305.4	313.5	321.1	335.3	350.6	362.9	372.8	382.8
57.5°	264.1	266.7	270.2	275.1	283.1	292.1	301.9	315.6	322.8	327.9	335.7
60°	246.3	247.0	249.3	255.1	261.3	269.3	280.8	290.4	295.8	300.0	306.5
62.5°	226.6	226.8	230.7	234.9	239.4	248.1	257.5	265.2	269.7	271.8	278.0
65°	199.1	198.3	200.7	204.1	209.4	215.2	223.3	230.1	229.7	232.1	235.9
67.5°	171.0	170.2	170.2	173.5	177.8	183.0	188.5	192.5	192.6	195.6	197.5
70°	151.9	149.7	151.2	153.8	155.7	160.0	166.1	167.6	168.0	169.6	171.5
72.5°	132.3	131.5	132.7	133.9	135.2	138.5	143.7	144.6	144.7	145.6	148.8
75°	105.1	104.3	103.6	104.7	106.2	108.6	110.5	112.0	111.6	112.0	114.3
77.5°	78.8	76.6	76.2	76.9	77.3	78.7	80.7	80.5	80.9	80.8	83.4
80°	62.5	59.5	59.1	59.1	59.5	60.2	61.0	61.8	60.6	61.8	62.5
82.5°	45.9	44.1	44.0	43.7	43.8	43.9	44.4	44.8	44.6	45.1	45.6
85°	25.3	24.5	23.4	24.1	23.8	22.6	23.4	22.2	21.9	22.2	22.6
87.5°	11.1	11.3	10.4	10.2	9.7	9.8	8.9	8.3	7.8	7.8	8.5
90°	12.8	12.0	10.8	9.7	8.5	7.3	6.1	4.7	3.4	2.1	0.7
92.5°	12.8	12.0	10.9	9.9	8.9	7.9	7.8	8.7	9.7	10.6	11.5
95°	12.8	12.0	18.3	24.6	30.9	37.3	40.7	41.2	41.6	42.1	42.6
97.5°	32.1	36.9	49.3	61.8	74.3	86.8	92.6	91.7	90.9	90.0	89.1
100°	105.4	130.2	129.6	128.9	128.3	127.5	126.9	126.4	125.9	125.4	124.9
102.5°	161.5	166.1	165.7	165.3	164.9	164.5	164.0	163.4	162.8	162.1	161.5
105°	223.0	223.0	223.0	223.0	223.0	223.0	222.7	222.0	221.4	220.7	219.9
107.5°	282.3	282.3	282.0	281.6	281.2	280.9	280.7	280.7	280.7	280.7	280.7
110°	321.2	321.7	321.4	321.1	320.7	320.4	320.2	320.2	320.2	320.2	320.2



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	359.4	360.1	359.9	359.7	359.5	359.3	359.0	358.6	358.2	357.8	357.4
115°	416.9	417.6	417.4	417.2	417.1	416.9	416.4	415.6	414.8	413.8	413.0
117.5°	472.5	473.3	472.7	472.1	471.5	470.8	470.5	470.6	470.6	470.6	470.7
120°	507.8	508.1	507.6	507.1	506.5	506.0	505.9	506.0	506.2	506.4	506.5
122.5°	541.9	542.2	542.0	541.7	541.5	541.3	540.9	540.2	539.6	539.0	538.3
125°	592.0	592.6	592.6	592.6	592.6	592.6	592.1	590.9	589.8	588.5	587.4
127.5°	637.1	637.5	637.6	637.7	637.8	637.9	637.5	636.7	635.9	635.1	634.2
130°	666.9	667.4	667.3	667.1	666.9	666.8	666.3	665.5	664.6	663.8	663.0
132.5°	694.3	694.4	694.8	695.1	695.5	695.9	695.6	694.6	693.7	692.7	691.7
135°	735.2	735.6	735.9	736.2	736.6	736.9	736.6	735.6	734.6	733.6	732.6
137.5°	772.7	772.6	773.0	773.3	773.6	773.9	773.6	772.7	771.8	771.0	770.1
140°	795.8	795.4	795.6	795.8	795.9	796.1	796.0	795.7	795.4	795.0	794.7
142.5°	818.8	818.8	818.5	818.3	818.1	817.8	817.6	817.4	817.2	817.0	816.8
145°	850.9	850.8	850.8	850.8	850.8	850.8	850.6	850.3	850.0	849.6	849.3
147.5°	878.5	878.3	878.1	877.9	877.8	877.6	877.5	877.6	877.6	877.7	877.8
150°	896.1	895.6	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6
152.5°	911.6	911.2	910.9	910.6	910.3	909.9	910.1	910.9	911.6	912.3	913.0
155°	932.8	932.3	932.0	931.7	931.4	931.0	931.4	932.3	933.3	934.3	935.3
157.5°	950.6	950.0	950.0	950.0	949.9	949.9	950.2	950.8	951.4	952.0	952.5
160°	961.5	960.8	960.6	960.5	960.3	960.1	960.6	961.5	962.5	963.5	964.5
162.5°	971.3	970.4	970.2	970.1	969.9	969.7	970.1	971.1	972.1	973.1	974.1
165°	984.2	983.2	983.1	982.9	982.7	982.6	983.0	984.0	985.0	985.9	986.9
167.5°	993.8	992.7	992.5	992.3	992.2	992.0	992.4	993.5	994.5	995.5	996.5
170°	998.8	997.4	997.2	997.1	996.9	996.7	997.2	998.5	999.6	1000.8	1002.0
172.5°	1002.8	1001.7	1001.4	1001.1	1000.8	1000.5	1000.9	1002.0	1003.2	1004.4	1005.5
175°	1007.0	1005.7	1005.5	1005.3	1005.2	1005.0	1005.4	1006.4	1007.4	1008.5	1009.5
177.5°	1009.2	1008.2	1008.0	1007.9	1007.8	1007.6	1008.0	1008.9	1009.7	1010.4	1011.2
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	908.8	913.0	915.7	921.0	925.3	927.8	929.9	931.7	933.9	935.7	941.0
5°	914.5	924.5	933.0	946.0	958.0	967.1	977.0	985.9	993.2	1003.6	1011.6
7.5°	912.0	929.8	948.4	968.5	989.2	1008.4	1025.9	1042.5	1057.4	1075.5	1091.4
10°	909.6	933.7	957.6	984.7	1012.8	1036.5	1058.8	1081.5	1097.9	1121.0	1140.5
12.5°	907.8	936.2	964.9	997.6	1028.4	1062.0	1091.7	1108.1	1133.3	1151.7	1174.9
15°	900.0	937.6	977.0	1013.9	1057.6	1088.7	1114.8	1147.0	1170.4	1193.9	1219.1
17.5°	886.1	928.7	972.9	1021.2	1063.1	1096.5	1130.0	1161.1	1189.1	1220.4	1252.0
20°	879.7	922.2	972.9	1022.4	1063.4	1098.3	1132.9	1167.0	1197.7	1238.0	1274.3
22.5°	866.2	917.7	964.3	1012.5	1054.8	1092.8	1132.0	1170.6	1211.4	1257.0	1302.6
25°	842.0	894.2	943.7	991.3	1033.9	1081.5	1123.3	1175.1	1227.2	1287.5	1344.2
27.5°	817.1	867.0	912.3	958.3	1007.9	1061.8	1116.0	1174.8	1243.1	1319.1	1399.3
30°	796.8	843.9	888.1	935.2	987.0	1047.6	1107.1	1177.0	1256.0	1341.5	1436.6
32.5°	773.2	816.7	859.6	909.5	965.9	1029.9	1099.1	1175.7	1270.7	1368.0	1465.8
35°	732.8	769.2	813.2	866.6	930.3	1003.6	1083.8	1174.3	1283.2	1394.8	1477.3
37.5°	684.8	718.7	765.2	823.6	890.4	969.1	1064.2	1171.5	1287.3	1376.2	1402.9
40°	652.6	684.0	732.4	792.9	861.2	944.5	1048.8	1162.4	1274.3	1331.2	1309.3
42.5°	618.1	651.2	698.3	758.3	831.7	922.4	1029.5	1143.1	1237.0	1258.4	1182.9
45°	563.9	598.0	644.5	705.1	784.2	882.3	994.0	1097.1	1151.2	1112.5	995.5
47.5°	513.5	545.5	588.5	651.1	732.7	834.2	941.7	1024.0	1028.3	935.8	810.9
50°	479.2	508.7	552.0	614.6	695.5	798.3	895.3	960.2	931.1	826.4	706.3
52.5°	445.4	474.3	517.1	579.0	659.0	753.2	843.5	889.0	834.0	726.6	624.0
55°	396.7	422.0	463.8	521.0	596.9	684.4	761.1	776.8	705.5	599.6	516.3
57.5°	349.1	372.7	410.8	463.4	532.8	610.4	670.3	667.0	591.6	500.7	434.6
60°	316.9	339.9	373.7	425.1	488.4	555.1	606.5	594.2	519.5	441.2	385.6
62.5°	288.0	308.6	340.5	385.5	443.2	505.0	547.2	529.2	455.9	387.5	343.5
65°	245.5	262.8	290.0	328.4	376.4	427.4	460.0	436.6	374.1	320.7	285.4
67.5°	204.9	218.7	241.6	272.3	313.2	354.1	374.0	350.4	300.3	261.5	235.3
70°	179.2	191.5	209.0	236.3	272.0	306.5	321.4	300.3	257.4	224.0	205.2
72.5°	153.4	163.5	179.0	203.5	232.1	262.1	275.1	255.0	219.6	191.5	173.9
75°	118.6	125.4	136.2	153.1	175.7	199.4	206.8	189.1	166.5	145.4	133.9
77.5°	84.8	90.7	98.9	109.5	125.5	140.7	147.0	136.8	119.3	105.9	96.5
80°	65.2	68.3	75.2	84.0	96.6	106.2	110.5	103.9	91.7	81.7	74.4
82.5°	46.5	49.6	53.7	61.0	69.1	75.5	80.1	75.7	66.9	59.0	54.7
85°	22.6	24.5	26.9	29.9	36.1	39.9	39.5	36.9	33.3	30.3	28.0
87.5°	8.4	9.0	10.2	11.9	13.1	14.5	15.5	15.0	14.0	13.3	12.5
90°	2.1	3.4	4.7	6.1	7.3	8.5	9.7	10.8	12.0	12.8	13.6
92.5°	10.6	9.7	8.7	7.8	7.9	8.9	9.9	10.9	12.0	12.8	13.6
95°	42.1	41.6	41.2	40.7	37.3	30.9	24.6	18.3	12.0	12.8	13.6
97.5°	90.0	90.9	91.7	92.6	86.8	74.3	61.8	49.3	36.9	32.1	27.5
100°	125.4	125.9	126.4	126.9	127.5	128.3	128.9	129.6	130.2	105.4	80.7
102.5°	162.1	162.8	163.4	164.0	164.5	164.9	165.3	165.7	166.1	161.5	156.7
105°	220.7	221.4	222.0	222.7	223.0	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.7	280.7	280.7	280.7	280.9	281.2	281.6	282.0	282.3	282.3	282.4
110°	320.2	320.2	320.2	320.2	320.4	320.7	321.1	321.4	321.7	321.2	320.7



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	357.8	358.2	358.6	359.0	359.3	359.5	359.7	359.9	360.1	359.4	358.8
115°	413.8	414.8	415.6	416.4	416.9	417.1	417.2	417.4	417.6	416.9	416.2
117.5°	470.6	470.6	470.6	470.5	470.8	471.5	472.1	472.7	473.3	472.5	471.6
120°	506.4	506.2	506.0	505.9	506.0	506.5	507.1	507.6	508.1	507.8	507.5
122.5°	539.0	539.6	540.2	540.9	541.3	541.5	541.7	542.0	542.2	541.9	541.5
125°	588.5	589.8	590.9	592.1	592.6	592.6	592.6	592.6	592.6	592.0	591.3
127.5°	635.1	635.9	636.7	637.5	637.9	637.8	637.7	637.6	637.5	637.1	636.8
130°	663.8	664.6	665.5	666.3	666.8	666.9	667.1	667.3	667.4	666.9	666.5
132.5°	692.7	693.7	694.6	695.6	695.9	695.5	695.1	694.8	694.4	694.3	694.2
135°	733.6	734.6	735.6	736.6	736.9	736.6	736.2	735.9	735.6	735.2	734.9
137.5°	771.0	771.8	772.7	773.6	773.9	773.6	773.3	773.0	772.6	772.7	772.8
140°	795.0	795.4	795.7	796.0	796.1	795.9	795.8	795.6	795.4	795.8	796.1
142.5°	817.0	817.2	817.4	817.6	817.8	818.1	818.3	818.5	818.8	818.8	818.9
145°	849.6	850.0	850.3	850.6	850.8	850.8	850.8	850.8	850.8	850.9	851.1
147.5°	877.7	877.6	877.6	877.5	877.6	877.8	877.9	878.1	878.3	878.5	878.7
150°	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	896.1	896.4
152.5°	912.3	911.6	910.9	910.1	909.9	910.3	910.6	910.9	911.2	911.6	911.9
155°	934.3	933.3	932.3	931.4	931.0	931.4	931.7	932.0	932.3	932.8	933.3
157.5°	952.0	951.4	950.8	950.2	949.9	949.9	950.0	950.0	950.0	950.6	951.1
160°	963.5	962.5	961.5	960.6	960.1	960.3	960.5	960.6	960.8	961.5	962.1
162.5°	973.1	972.1	971.1	970.1	969.7	969.9	970.1	970.2	970.4	971.3	972.2
165°	985.9	985.0	984.0	983.0	982.6	982.7	982.9	983.1	983.2	984.2	985.2
167.5°	995.5	994.5	993.5	992.4	992.0	992.2	992.3	992.5	992.7	993.8	995.0
170°	1000.8	999.6	998.5	997.2	996.7	996.9	997.1	997.2	997.4	998.8	1000.1
172.5°	1004.4	1003.2	1002.0	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8	1004.0
175°	1008.5	1007.4	1006.4	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0	1008.4
177.5°	1010.4	1009.7	1008.9	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2	1010.1
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	945.2	947.7	952.9	951.1	953.5	954.7	956.0
5°	1021.6	1033.9	1039.3	1038.4	1046.5	1044.6	1042.7
7.5°	1107.8	1120.7	1127.9	1136.9	1142.2	1142.5	1147.0
10°	1156.6	1173.5	1180.4	1190.0	1196.2	1199.6	1199.2
12.5°	1194.1	1207.3	1222.7	1227.5	1235.8	1240.1	1238.5
15°	1239.1	1260.2	1276.3	1284.3	1294.7	1297.8	1302.0
17.5°	1279.3	1307.6	1326.5	1351.4	1360.9	1366.7	1363.2
20°	1309.7	1346.9	1365.7	1395.6	1412.1	1421.0	1417.9
22.5°	1345.6	1385.8	1420.7	1446.5	1471.7	1483.6	1486.0
25°	1407.1	1462.4	1513.4	1547.5	1578.6	1585.9	1602.0
27.5°	1475.9	1541.1	1595.6	1631.4	1653.1	1661.2	1666.3
30°	1519.1	1584.0	1625.1	1648.0	1655.0	1654.2	1653.5
32.5°	1540.3	1580.9	1588.8	1582.4	1566.6	1553.2	1539.2
35°	1510.4	1480.1	1434.7	1376.4	1333.5	1290.1	1285.9
37.5°	1358.4	1261.4	1186.1	1102.0	1053.4	1023.4	1002.6
40°	1215.3	1105.2	1013.9	942.9	893.4	873.9	854.7
42.5°	1060.1	954.8	873.9	814.7	777.5	755.8	740.5
45°	861.2	768.4	705.1	662.2	632.6	615.7	606.1
47.5°	705.7	637.0	583.3	552.3	531.9	518.8	518.8
50°	622.3	556.6	521.0	496.4	478.8	468.4	470.3
52.5°	548.3	499.3	468.8	448.2	435.2	428.8	428.6
55°	458.5	423.1	403.2	388.2	379.4	372.1	373.7
57.5°	392.1	362.3	349.0	336.6	330.4	327.5	323.4
60°	351.0	328.0	316.5	306.5	300.3	298.1	293.9
62.5°	314.5	296.4	285.2	277.0	271.6	270.7	267.4
65°	264.3	250.5	240.5	236.7	231.0	229.4	229.4
67.5°	217.9	208.0	200.3	196.7	194.2	194.6	192.7
70°	188.7	180.7	175.7	171.9	170.0	170.4	168.7
72.5°	165.1	156.1	151.8	149.5	146.9	147.9	147.3
75°	125.0	120.5	118.2	115.8	114.3	113.5	112.8
77.5°	91.8	87.8	86.0	84.7	84.9	83.1	84.5
80°	71.0	67.6	66.3	64.4	64.0	64.0	63.7
82.5°	51.9	50.0	49.2	47.6	46.9	47.5	46.5
85°	26.9	25.3	24.9	24.9	24.1	23.4	25.3
87.5°	12.7	11.6	11.8	11.6	11.7	11.5	11.0
90°	14.4	15.2	16.0	16.5	17.0	17.5	18.0
92.5°	14.4	15.2	15.9	16.1	16.3	16.6	16.8
95°	14.4	15.2	15.8	15.8	15.8	15.8	15.8
97.5°	22.7	18.1	15.8	15.8	15.8	15.8	15.8
100°	55.8	31.1	18.4	17.7	17.1	16.4	15.8
102.5°	152.1	147.3	139.4	128.1	116.7	105.4	94.1
105°	223.0	223.0	222.9	222.8	222.6	222.4	222.3
107.5°	282.4	282.4	282.2	281.7	281.1	280.6	280.1
110°	320.2	319.7	319.6	319.7	319.9	320.1	320.2



TEST NUMBER: P333376-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	358.2	357.5	357.1	356.9	356.7	356.4	356.2
115°	415.6	414.9	414.0	413.0	412.0	411.0	410.0
117.5°	470.8	469.9	469.3	468.8	468.4	468.0	467.6
120°	507.1	506.8	506.1	505.3	504.5	503.7	502.8
122.5°	541.2	540.9	540.2	539.3	538.3	537.3	536.3
125°	590.7	590.0	589.4	588.9	588.3	587.9	587.4
127.5°	636.4	636.1	635.3	634.0	632.8	631.6	630.4
130°	666.0	665.5	664.8	664.0	663.2	662.3	661.5
132.5°	694.1	694.0	693.6	692.7	691.9	691.1	690.2
135°	734.6	734.3	733.6	732.6	731.5	730.5	729.5
137.5°	772.8	773.0	772.5	771.6	770.8	769.9	769.1
140°	796.4	796.8	796.4	795.4	794.5	793.5	792.4
142.5°	819.0	819.0	818.6	817.6	816.6	815.6	814.6
145°	851.3	851.4	851.0	850.0	849.0	848.1	847.1
147.5°	878.9	879.1	878.6	877.5	876.3	875.0	873.8
150°	896.7	897.1	896.6	895.1	893.8	892.5	891.2
152.5°	912.2	912.6	912.1	910.9	909.8	908.6	907.4
155°	933.8	934.3	933.9	932.6	931.3	930.0	928.6
157.5°	951.6	952.1	951.7	950.4	949.1	947.8	946.4
160°	962.8	963.4	963.1	961.8	960.5	959.2	957.8
162.5°	973.1	974.1	973.8	972.4	970.9	969.5	968.0
165°	986.2	987.2	987.0	985.7	984.4	983.1	981.7
167.5°	996.2	997.4	997.3	995.8	994.3	992.8	991.3
170°	1001.5	1002.8	1002.7	1001.2	999.7	998.2	996.7
172.5°	1005.2	1006.4	1006.2	1004.8	1003.3	1001.8	1000.3
175°	1009.7	1011.0	1010.9	1009.5	1007.9	1006.4	1004.9
177.5°	1011.0	1012.0	1011.9	1010.8	1009.8	1008.7	1007.6
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5

(END OF REPORT)