

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333412-840

Luminaire Tested: **S125DIW-S850D1050U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333412-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1050U840-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7720.0 lumens  
Efficiency: N/A  
Efficacy: 146.8 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	69	65	62	59	55	51	49	46	41	39	37	33
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	28	24
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	17	15	13
10	46	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.9	1.5
10°-20°	354.1	4.6
20°-30°	575.0	7.4
30°-40°	701.4	9.1
40°-50°	638.1	8.3
50°-60°	508.2	6.6
60°-70°	354.0	4.6
70°-80°	188.8	2.4
80°-90°	50.5	0.7
90°-100°	50.1	0.6
100°-110°	308.6	4.0
110°-120°	559.7	7.2
120°-130°	718.2	9.3
130°-140°	772.5	10.0
140°-150°	725.1	9.4
150°-160°	586.6	7.6
160°-170°	379.4	4.9
170°-180°	130.8	1.7
0°-30°	1048.1	13.6
0°-40°	1749.5	22.7
0°-60°	2895.8	37.5
0°-90°	3489.0	45.2
90°-120°	918.3	11.9
90°-150°	3134.2	40.6
90°-180°	4231.0	54.8
0°-180°	7720.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	41
90°	24	1	24	1	24	12
95°	21	58	21	58	21	18
105°	303	300	303	300	303	274
115°	560	564	560	564	560	556
125°	802	802	802	802	802	713
135°	996	1000	996	1000	996	769
145°	1156	1159	1156	1159	1156	722
155°	1268	1277	1268	1277	1268	584
165°	1340	1347	1340	1347	1340	378
175°	1372	1378	1372	1378	1372	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	14.9	15.7	16.0	15.9	16.1	16.0	17.4	17.2	18.2	19.2	20.6
90°	24.5	23.8	23.1	22.5	21.8	20.9	19.8	18.6	17.5	16.4	14.7
92.5°	22.9	22.5	22.2	21.9	21.6	20.9	19.8	18.6	17.5	16.4	14.9
95°	21.4	21.4	21.4	21.4	21.4	20.9	19.8	18.6	17.5	16.4	24.9
97.5°	21.4	21.4	21.4	21.4	21.4	24.6	31.0	37.5	43.8	50.3	67.4
100°	21.4	22.3	23.2	24.1	25.0	42.4	76.2	110.1	143.9	177.7	176.8
102.5°	128.5	143.9	159.4	174.8	190.3	201.2	207.5	213.9	220.4	226.7	226.2
105°	303.4	303.6	303.8	304.1	304.3	304.4	304.4	304.4	304.4	304.4	304.4
107.5°	382.4	383.0	383.7	384.5	385.2	385.5	385.4	385.4	385.3	385.3	384.8
110°	437.2	436.9	436.7	436.5	436.3	436.5	437.2	437.8	438.5	439.2	438.7



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	486.1	486.5	486.8	487.2	487.5	488.1	488.9	489.8	490.6	491.5	491.2
115°	559.7	561.1	562.4	563.8	565.1	566.2	567.1	568.0	569.0	569.9	569.7
117.5°	638.1	638.7	639.3	640.0	640.5	641.4	642.6	643.8	644.9	646.1	645.2
120°	686.3	687.5	688.6	689.7	690.8	691.7	692.2	692.6	693.1	693.5	692.8
122.5°	732.2	733.5	734.8	736.1	737.4	738.2	738.7	739.1	739.6	740.0	739.7
125°	801.7	802.4	803.1	803.9	804.5	805.3	806.2	807.1	808.0	808.9	808.9
127.5°	860.4	862.0	863.7	865.5	867.1	868.2	868.7	869.2	869.7	870.2	870.3
130°	902.9	904.0	905.1	906.3	907.4	908.3	909.0	909.7	910.4	911.0	910.8
132.5°	942.1	943.2	944.3	945.5	946.6	947.3	947.4	947.6	947.7	947.9	948.3
135°	995.8	997.1	998.6	999.9	1001.3	1002.2	1002.6	1003.1	1003.5	1004.0	1004.4
137.5°	1049.8	1051.0	1052.1	1053.3	1054.5	1055.0	1054.9	1054.8	1054.7	1054.6	1055.0
140°	1081.6	1083.0	1084.3	1085.7	1087.0	1087.5	1087.0	1086.6	1086.1	1085.7	1085.9
142.5°	1111.9	1113.2	1114.6	1115.9	1117.3	1117.9	1117.8	1117.7	1117.6	1117.5	1117.2
145°	1156.2	1157.5	1158.9	1160.2	1161.6	1162.2	1162.0	1161.7	1161.5	1161.2	1161.2
147.5°	1192.8	1194.4	1196.0	1197.6	1199.3	1199.9	1199.7	1199.4	1199.1	1198.8	1198.6
150°	1216.4	1218.2	1220.0	1221.8	1223.7	1224.4	1224.0	1223.5	1223.0	1222.5	1222.1
152.5°	1238.5	1240.1	1241.7	1243.3	1245.1	1245.6	1245.2	1244.7	1244.3	1243.7	1243.3
155°	1267.5	1269.3	1271.1	1272.9	1274.8	1275.4	1274.7	1273.9	1273.2	1272.6	1272.1
157.5°	1291.8	1293.6	1295.5	1297.3	1299.1	1299.6	1298.9	1298.2	1297.5	1296.7	1296.7
160°	1307.4	1309.2	1311.0	1312.8	1314.5	1315.0	1314.1	1313.2	1312.3	1311.4	1311.2
162.5°	1321.2	1323.2	1325.2	1327.2	1329.2	1329.6	1328.3	1327.1	1325.8	1324.4	1324.2
165°	1340.0	1341.8	1343.6	1345.4	1347.3	1347.5	1346.2	1344.7	1343.4	1342.0	1341.8
167.5°	1353.1	1355.1	1357.2	1359.2	1361.3	1361.5	1359.8	1358.2	1356.6	1354.9	1354.7
170°	1360.4	1362.5	1364.5	1366.5	1368.6	1368.8	1367.0	1365.1	1363.3	1361.5	1361.2
172.5°	1365.3	1367.4	1369.4	1371.5	1373.5	1373.7	1372.1	1370.5	1368.8	1367.2	1366.8
175°	1371.7	1373.7	1375.7	1377.8	1379.9	1380.0	1378.2	1376.3	1374.5	1372.7	1372.5
177.5°	1375.3	1376.8	1378.3	1379.7	1381.2	1381.3	1380.0	1378.7	1377.5	1376.1	1375.9
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	21.1	19.9	18.0	16.4	13.8	12.2	11.5	11.5	10.6	10.6	11.4
90°	13.1	11.6	10.0	8.3	6.5	4.6	2.8	1.0	2.8	4.6	6.5
92.5°	13.5	12.1	10.7	10.6	11.9	13.2	14.4	15.8	14.4	13.2	11.9
95°	33.6	42.2	50.8	55.5	56.1	56.9	57.6	58.2	57.6	56.9	56.1
97.5°	84.4	101.5	118.6	126.4	125.2	124.0	122.8	121.6	122.8	124.0	125.2
100°	175.9	175.0	174.1	173.3	172.6	171.9	171.3	170.6	171.3	171.9	172.6
102.5°	225.6	225.1	224.6	223.9	223.0	222.2	221.3	220.5	221.3	222.2	223.0
105°	304.4	304.4	304.4	303.9	303.0	302.1	301.1	300.2	301.1	302.1	303.0
107.5°	384.4	383.8	383.4	383.2	383.2	383.2	383.2	383.2	383.2	383.2	383.2
110°	438.3	437.8	437.4	437.2	437.2	437.2	437.2	437.2	437.2	437.2	437.2





TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.9	490.7	490.4	490.0	489.4	488.9	488.4	487.8	488.4	488.9	489.4
115°	569.5	569.3	569.0	568.4	567.1	566.0	564.9	563.8	564.9	566.0	567.1
117.5°	644.4	643.5	642.7	642.3	642.3	642.4	642.4	642.5	642.4	642.4	642.3
120°	692.2	691.5	690.7	690.5	690.7	690.9	691.3	691.5	691.3	690.9	690.7
122.5°	739.4	739.1	738.8	738.2	737.3	736.5	735.6	734.8	735.6	736.5	737.3
125°	808.9	808.9	808.9	808.1	806.5	805.0	803.3	801.7	803.3	805.0	806.5
127.5°	870.5	870.6	870.7	870.2	869.1	868.0	866.9	865.7	866.9	868.0	869.1
130°	910.6	910.4	910.1	909.5	908.3	907.2	906.1	904.9	906.1	907.2	908.3
132.5°	948.8	949.3	949.8	949.4	948.1	946.7	945.4	944.1	945.4	946.7	948.1
135°	1004.9	1005.3	1005.8	1005.3	1004.0	1002.6	1001.3	999.9	1001.3	1002.6	1004.0
137.5°	1055.5	1055.9	1056.3	1055.9	1054.7	1053.5	1052.4	1051.2	1052.4	1053.5	1054.7
140°	1086.1	1086.4	1086.6	1086.5	1086.0	1085.6	1085.1	1084.7	1085.1	1085.6	1086.0
142.5°	1116.9	1116.6	1116.3	1116.0	1115.7	1115.5	1115.2	1114.9	1115.2	1115.5	1115.7
145°	1161.2	1161.2	1161.2	1161.0	1160.6	1160.1	1159.7	1159.2	1159.7	1160.1	1160.6
147.5°	1198.3	1198.0	1197.8	1197.7	1197.8	1197.9	1198.0	1198.0	1198.0	1197.9	1197.8
150°	1221.6	1221.2	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5	1222.1	1221.6	1221.2
152.5°	1242.9	1242.4	1242.0	1242.2	1243.2	1244.3	1245.3	1246.3	1245.3	1244.3	1243.2
155°	1271.7	1271.2	1270.8	1271.2	1272.6	1273.9	1275.4	1276.7	1275.4	1273.9	1272.6
157.5°	1296.6	1296.6	1296.6	1296.9	1297.8	1298.6	1299.4	1300.2	1299.4	1298.6	1297.8
160°	1311.0	1310.7	1310.5	1311.1	1312.4	1313.8	1315.1	1316.6	1315.1	1313.8	1312.4
162.5°	1324.0	1323.8	1323.5	1324.1	1325.5	1326.9	1328.3	1329.6	1328.3	1326.9	1325.5
165°	1341.6	1341.4	1341.1	1341.7	1343.1	1344.4	1345.8	1347.2	1345.8	1344.4	1343.1
167.5°	1354.4	1354.2	1354.0	1354.6	1356.0	1357.5	1358.9	1360.2	1358.9	1357.5	1356.0
170°	1361.0	1360.8	1360.6	1361.2	1362.8	1364.4	1366.0	1367.6	1366.0	1364.4	1362.8
172.5°	1366.3	1365.9	1365.5	1366.1	1367.8	1369.3	1370.9	1372.5	1370.9	1369.3	1367.8
175°	1372.2	1372.0	1371.8	1372.3	1373.7	1375.0	1376.4	1377.8	1376.4	1375.0	1373.7
177.5°	1375.8	1375.6	1375.4	1375.9	1377.0	1378.1	1379.2	1380.3	1379.2	1378.1	1377.0
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	12.1	13.3	13.2	13.9	14.2	15.5	15.2	17.2	18.2	19.3	19.1
90°	8.3	10.0	11.6	13.1	14.7	16.4	17.5	18.6	19.8	20.9	21.8
92.5°	10.6	10.7	12.1	13.5	14.9	16.4	17.5	18.6	19.8	20.9	21.6
95°	55.5	50.8	42.2	33.6	24.9	16.4	17.5	18.6	19.8	20.9	21.4
97.5°	126.4	118.6	101.5	84.4	67.4	50.3	43.8	37.5	31.0	24.6	21.4
100°	173.3	174.1	175.0	175.9	176.8	177.7	143.9	110.1	76.2	42.4	25.0
102.5°	223.9	224.6	225.1	225.6	226.2	226.7	220.4	213.9	207.5	201.2	190.3
105°	303.9	304.4	304.4	304.4	304.4	304.4	304.4	304.4	304.4	304.4	304.3
107.5°	383.2	383.4	383.8	384.4	384.8	385.3	385.3	385.4	385.4	385.5	385.2
110°	437.2	437.4	437.8	438.3	438.7	439.2	438.5	437.8	437.2	436.5	436.3



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	490.0	490.4	490.7	490.9	491.2	491.5	490.6	489.8	488.9	488.1	487.5
115°	568.4	569.0	569.3	569.5	569.7	569.9	569.0	568.0	567.1	566.2	565.1
117.5°	642.3	642.7	643.5	644.4	645.2	646.1	644.9	643.8	642.6	641.4	640.5
120°	690.5	690.7	691.5	692.2	692.8	693.5	693.1	692.6	692.2	691.7	690.8
122.5°	738.2	738.8	739.1	739.4	739.7	740.0	739.6	739.1	738.7	738.2	737.4
125°	808.1	808.9	808.9	808.9	808.9	808.9	808.0	807.1	806.2	805.3	804.5
127.5°	870.2	870.7	870.6	870.5	870.3	870.2	869.7	869.2	868.7	868.2	867.1
130°	909.5	910.1	910.4	910.6	910.8	911.0	910.4	909.7	909.0	908.3	907.4
132.5°	949.4	949.8	949.3	948.8	948.3	947.9	947.7	947.6	947.4	947.3	946.6
135°	1005.3	1005.8	1005.3	1004.9	1004.4	1004.0	1003.5	1003.1	1002.6	1002.2	1001.3
137.5°	1055.9	1056.3	1055.9	1055.5	1055.0	1054.6	1054.7	1054.8	1054.9	1055.0	1054.5
140°	1086.5	1086.6	1086.4	1086.1	1085.9	1085.7	1086.1	1086.6	1087.0	1087.5	1087.0
142.5°	1116.0	1116.3	1116.6	1116.9	1117.2	1117.5	1117.6	1117.7	1117.8	1117.9	1117.3
145°	1161.0	1161.2	1161.2	1161.2	1161.2	1161.2	1161.5	1161.7	1162.0	1162.2	1161.6
147.5°	1197.7	1197.8	1198.0	1198.3	1198.6	1198.8	1199.1	1199.4	1199.7	1199.9	1199.3
150°	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5	1223.0	1223.5	1224.0	1224.4	1223.7
152.5°	1242.2	1242.0	1242.4	1242.9	1243.3	1243.7	1244.3	1244.7	1245.2	1245.6	1245.1
155°	1271.2	1270.8	1271.2	1271.7	1272.1	1272.6	1273.2	1273.9	1274.7	1275.4	1274.8
157.5°	1296.9	1296.6	1296.6	1296.6	1296.7	1296.7	1297.5	1298.2	1298.9	1299.6	1299.1
160°	1311.1	1310.5	1310.7	1311.0	1311.2	1311.4	1312.3	1313.2	1314.1	1315.0	1314.5
162.5°	1324.1	1323.5	1323.8	1324.0	1324.2	1324.4	1325.8	1327.1	1328.3	1329.6	1329.2
165°	1341.7	1341.1	1341.4	1341.6	1341.8	1342.0	1343.4	1344.7	1346.2	1347.5	1347.3
167.5°	1354.6	1354.0	1354.2	1354.4	1354.7	1354.9	1356.6	1358.2	1359.8	1361.5	1361.3
170°	1361.2	1360.6	1360.8	1361.0	1361.2	1361.5	1363.3	1365.1	1367.0	1368.8	1368.6
172.5°	1366.1	1365.5	1365.9	1366.3	1366.8	1367.2	1368.8	1370.5	1372.1	1373.7	1373.5
175°	1372.3	1371.8	1372.0	1372.2	1372.5	1372.7	1374.5	1376.3	1378.2	1380.0	1379.9
177.5°	1375.9	1375.4	1375.6	1375.8	1375.9	1376.1	1377.5	1378.7	1380.0	1381.3	1381.2
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	20.0	19.7	19.9	20.8	19.9	19.7	20.0	19.1	19.3	18.2	17.2
90°	22.5	23.1	23.8	24.5	23.8	23.1	22.5	21.8	20.9	19.8	18.6
92.5°	21.9	22.2	22.5	22.9	22.5	22.2	21.9	21.6	20.9	19.8	18.6
95°	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4	20.9	19.8	18.6
97.5°	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4	24.6	31.0	37.5
100°	24.1	23.2	22.3	21.4	22.3	23.2	24.1	25.0	42.4	76.2	110.1
102.5°	174.8	159.4	143.9	128.5	143.9	159.4	174.8	190.3	201.2	207.5	213.9
105°	304.1	303.8	303.6	303.4	303.6	303.8	304.1	304.3	304.4	304.4	304.4
107.5°	384.5	383.7	383.0	382.4	383.0	383.7	384.5	385.2	385.5	385.4	385.4
110°	436.5	436.7	436.9	437.2	436.9	436.7	436.5	436.3	436.5	437.2	437.8



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	487.2	486.8	486.5	486.1	486.5	486.8	487.2	487.5	488.1	488.9	489.8
115°	563.8	562.4	561.1	559.7	561.1	562.4	563.8	565.1	566.2	567.1	568.0
117.5°	640.0	639.3	638.7	638.1	638.7	639.3	640.0	640.5	641.4	642.6	643.8
120°	689.7	688.6	687.5	686.3	687.5	688.6	689.7	690.8	691.7	692.2	692.6
122.5°	736.1	734.8	733.5	732.2	733.5	734.8	736.1	737.4	738.2	738.7	739.1
125°	803.9	803.1	802.4	801.7	802.4	803.1	803.9	804.5	805.3	806.2	807.1
127.5°	865.5	863.7	862.0	860.4	862.0	863.7	865.5	867.1	868.2	868.7	869.2
130°	906.3	905.1	904.0	902.9	904.0	905.1	906.3	907.4	908.3	909.0	909.7
132.5°	945.5	944.3	943.2	942.1	943.2	944.3	945.5	946.6	947.3	947.4	947.6
135°	999.9	998.6	997.1	995.8	997.1	998.6	999.9	1001.3	1002.2	1002.6	1003.1
137.5°	1053.3	1052.1	1051.0	1049.8	1051.0	1052.1	1053.3	1054.5	1055.0	1054.9	1054.8
140°	1085.7	1084.3	1083.0	1081.6	1083.0	1084.3	1085.7	1087.0	1087.5	1087.0	1086.6
142.5°	1115.9	1114.6	1113.2	1111.9	1113.2	1114.6	1115.9	1117.3	1117.9	1117.8	1117.7
145°	1160.2	1158.9	1157.5	1156.2	1157.5	1158.9	1160.2	1161.6	1162.2	1162.0	1161.7
147.5°	1197.6	1196.0	1194.4	1192.8	1194.4	1196.0	1197.6	1199.3	1199.9	1199.7	1199.4
150°	1221.8	1220.0	1218.2	1216.4	1218.2	1220.0	1221.8	1223.7	1224.4	1224.0	1223.5
152.5°	1243.3	1241.7	1240.1	1238.5	1240.1	1241.7	1243.3	1245.1	1245.6	1245.2	1244.7
155°	1272.9	1271.1	1269.3	1267.5	1269.3	1271.1	1272.9	1274.8	1275.4	1274.7	1273.9
157.5°	1297.3	1295.5	1293.6	1291.8	1293.6	1295.5	1297.3	1299.1	1299.6	1298.9	1298.2
160°	1312.8	1311.0	1309.2	1307.4	1309.2	1311.0	1312.8	1314.5	1315.0	1314.1	1313.2
162.5°	1327.2	1325.2	1323.2	1321.2	1323.2	1325.2	1327.2	1329.2	1329.6	1328.3	1327.1
165°	1345.4	1343.6	1341.8	1340.0	1341.8	1343.6	1345.4	1347.3	1347.5	1346.2	1344.7
167.5°	1359.2	1357.2	1355.1	1353.1	1355.1	1357.2	1359.2	1361.3	1361.5	1359.8	1358.2
170°	1366.5	1364.5	1362.5	1360.4	1362.5	1364.5	1366.5	1368.6	1368.8	1367.0	1365.1
172.5°	1371.5	1369.4	1367.4	1365.3	1367.4	1369.4	1371.5	1373.5	1373.7	1372.1	1370.5
175°	1377.8	1375.7	1373.7	1371.7	1373.7	1375.7	1377.8	1379.9	1380.0	1378.2	1376.3
177.5°	1379.7	1378.3	1376.8	1375.3	1376.8	1378.3	1379.7	1381.2	1381.3	1380.0	1378.7
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	15.2	15.5	14.2	13.9	13.2	13.3	12.1	11.4	10.6	10.6	11.5
90°	17.5	16.4	14.7	13.1	11.6	10.0	8.3	6.5	4.6	2.8	1.0
92.5°	17.5	16.4	14.9	13.5	12.1	10.7	10.6	11.9	13.2	14.4	15.8
95°	17.5	16.4	24.9	33.6	42.2	50.8	55.5	56.1	56.9	57.6	58.2
97.5°	43.8	50.3	67.4	84.4	101.5	118.6	126.4	125.2	124.0	122.8	121.6
100°	143.9	177.7	176.8	175.9	175.0	174.1	173.3	172.6	171.9	171.3	170.6
102.5°	220.4	226.7	226.2	225.6	225.1	224.6	223.9	223.0	222.2	221.3	220.5
105°	304.4	304.4	304.4	304.4	304.4	304.4	303.9	303.0	302.1	301.1	300.2
107.5°	385.3	385.3	384.8	384.4	383.8	383.4	383.2	383.2	383.2	383.2	383.2
110°	438.5	439.2	438.7	438.3	437.8	437.4	437.2	437.2	437.2	437.2	437.2



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	490.6	491.5	491.2	490.9	490.7	490.4	490.0	489.4	488.9	488.4	487.8
115°	569.0	569.9	569.7	569.5	569.3	569.0	568.4	567.1	566.0	564.9	563.8
117.5°	644.9	646.1	645.2	644.4	643.5	642.7	642.3	642.3	642.4	642.4	642.5
120°	693.1	693.5	692.8	692.2	691.5	690.7	690.5	690.7	690.9	691.3	691.5
122.5°	739.6	740.0	739.7	739.4	739.1	738.8	738.2	737.3	736.5	735.6	734.8
125°	808.0	808.9	808.9	808.9	808.9	808.9	808.1	806.5	805.0	803.3	801.7
127.5°	869.7	870.2	870.3	870.5	870.6	870.7	870.2	869.1	868.0	866.9	865.7
130°	910.4	911.0	910.8	910.6	910.4	910.1	909.5	908.3	907.2	906.1	904.9
132.5°	947.7	947.9	948.3	948.8	949.3	949.8	949.4	948.1	946.7	945.4	944.1
135°	1003.5	1004.0	1004.4	1004.9	1005.3	1005.8	1005.3	1004.0	1002.6	1001.3	999.9
137.5°	1054.7	1054.6	1055.0	1055.5	1055.9	1056.3	1055.9	1054.7	1053.5	1052.4	1051.2
140°	1086.1	1085.7	1085.9	1086.1	1086.4	1086.6	1086.5	1086.0	1085.6	1085.1	1084.7
142.5°	1117.6	1117.5	1117.2	1116.9	1116.6	1116.3	1116.0	1115.7	1115.5	1115.2	1114.9
145°	1161.5	1161.2	1161.2	1161.2	1161.2	1161.2	1161.0	1160.6	1160.1	1159.7	1159.2
147.5°	1199.1	1198.8	1198.6	1198.3	1198.0	1197.8	1197.7	1197.8	1197.9	1198.0	1198.0
150°	1223.0	1222.5	1222.1	1221.6	1221.2	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5
152.5°	1244.3	1243.7	1243.3	1242.9	1242.4	1242.0	1242.2	1243.2	1244.3	1245.3	1246.3
155°	1273.2	1272.6	1272.1	1271.7	1271.2	1270.8	1271.2	1272.6	1273.9	1275.4	1276.7
157.5°	1297.5	1296.7	1296.7	1296.6	1296.6	1296.6	1296.9	1297.8	1298.6	1299.4	1300.2
160°	1312.3	1311.4	1311.2	1311.0	1310.7	1310.5	1311.1	1312.4	1313.8	1315.1	1316.6
162.5°	1325.8	1324.4	1324.2	1324.0	1323.8	1323.5	1324.1	1325.5	1326.9	1328.3	1329.6
165°	1343.4	1342.0	1341.8	1341.6	1341.4	1341.1	1341.7	1343.1	1344.4	1345.8	1347.2
167.5°	1356.6	1354.9	1354.7	1354.4	1354.2	1354.0	1354.6	1356.0	1357.5	1358.9	1360.2
170°	1363.3	1361.5	1361.2	1361.0	1360.8	1360.6	1361.2	1362.8	1364.4	1366.0	1367.6
172.5°	1368.8	1367.2	1366.8	1366.3	1365.9	1365.5	1366.1	1367.8	1369.3	1370.9	1372.5
175°	1374.5	1372.7	1372.5	1372.2	1372.0	1371.8	1372.3	1373.7	1375.0	1376.4	1377.8
177.5°	1377.5	1376.1	1375.9	1375.8	1375.6	1375.4	1375.9	1377.0	1378.1	1379.2	1380.3
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.5	12.2	13.8	16.4	18.0	19.9	21.1	20.6	19.2	18.2	17.2
90°	2.8	4.6	6.5	8.3	10.0	11.6	13.1	14.7	16.4	17.5	18.6
92.5°	14.4	13.2	11.9	10.6	10.7	12.1	13.5	14.9	16.4	17.5	18.6
95°	57.6	56.9	56.1	55.5	50.8	42.2	33.6	24.9	16.4	17.5	18.6
97.5°	122.8	124.0	125.2	126.4	118.6	101.5	84.4	67.4	50.3	43.8	37.5
100°	171.3	171.9	172.6	173.3	174.1	175.0	175.9	176.8	177.7	143.9	110.1
102.5°	221.3	222.2	223.0	223.9	224.6	225.1	225.6	226.2	226.7	220.4	213.9
105°	301.1	302.1	303.0	303.9	304.4	304.4	304.4	304.4	304.4	304.4	304.4
107.5°	383.2	383.2	383.2	383.2	383.4	383.8	384.4	384.8	385.3	385.3	385.4
110°	437.2	437.2	437.2	437.2	437.4	437.8	438.3	438.7	439.2	438.5	437.8





TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	488.4	488.9	489.4	490.0	490.4	490.7	490.9	491.2	491.5	490.6	489.8
115°	564.9	566.0	567.1	568.4	569.0	569.3	569.5	569.7	569.9	569.0	568.0
117.5°	642.4	642.4	642.3	642.3	642.7	643.5	644.4	645.2	646.1	644.9	643.8
120°	691.3	690.9	690.7	690.5	690.7	691.5	692.2	692.8	693.5	693.1	692.6
122.5°	735.6	736.5	737.3	738.2	738.8	739.1	739.4	739.7	740.0	739.6	739.1
125°	803.3	805.0	806.5	808.1	808.9	808.9	808.9	808.9	808.9	808.0	807.1
127.5°	866.9	868.0	869.1	870.2	870.7	870.6	870.5	870.3	870.2	869.7	869.2
130°	906.1	907.2	908.3	909.5	910.1	910.4	910.6	910.8	911.0	910.4	909.7
132.5°	945.4	946.7	948.1	949.4	949.8	949.3	948.8	948.3	947.9	947.7	947.6
135°	1001.3	1002.6	1004.0	1005.3	1005.8	1005.3	1004.9	1004.4	1004.0	1003.5	1003.1
137.5°	1052.4	1053.5	1054.7	1055.9	1056.3	1055.9	1055.5	1055.0	1054.6	1054.7	1054.8
140°	1085.1	1085.6	1086.0	1086.5	1086.6	1086.4	1086.1	1085.9	1085.7	1086.1	1086.6
142.5°	1115.2	1115.5	1115.7	1116.0	1116.3	1116.6	1116.9	1117.2	1117.5	1117.6	1117.7
145°	1159.7	1160.1	1160.6	1161.0	1161.2	1161.2	1161.2	1161.2	1161.2	1161.5	1161.7
147.5°	1198.0	1197.9	1197.8	1197.7	1197.8	1198.0	1198.3	1198.6	1198.8	1199.1	1199.4
150°	1222.1	1221.6	1221.2	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5	1223.0	1223.5
152.5°	1245.3	1244.3	1243.2	1242.2	1242.0	1242.4	1242.9	1243.3	1243.7	1244.3	1244.7
155°	1275.4	1273.9	1272.6	1271.2	1270.8	1271.2	1271.7	1272.1	1272.6	1273.2	1273.9
157.5°	1299.4	1298.6	1297.8	1296.9	1296.6	1296.6	1296.6	1296.7	1296.7	1297.5	1298.2
160°	1315.1	1313.8	1312.4	1311.1	1310.5	1310.7	1311.0	1311.2	1311.4	1312.3	1313.2
162.5°	1328.3	1326.9	1325.5	1324.1	1323.5	1323.8	1324.0	1324.2	1324.4	1325.8	1327.1
165°	1345.8	1344.4	1343.1	1341.7	1341.1	1341.4	1341.6	1341.8	1342.0	1343.4	1344.7
167.5°	1358.9	1357.5	1356.0	1354.6	1354.0	1354.2	1354.4	1354.7	1354.9	1356.6	1358.2
170°	1366.0	1364.4	1362.8	1361.2	1360.6	1360.8	1361.0	1361.2	1361.5	1363.3	1365.1
172.5°	1370.9	1369.3	1367.8	1366.1	1365.5	1365.9	1366.3	1366.8	1367.2	1368.8	1370.5
175°	1376.4	1375.0	1373.7	1372.3	1371.8	1372.0	1372.2	1372.5	1372.7	1374.5	1376.3
177.5°	1379.2	1378.1	1377.0	1375.9	1375.4	1375.6	1375.8	1375.9	1376.1	1377.5	1378.7
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	17.4	16.0	16.1	15.9	16.0	15.7	14.9
90°	19.8	20.9	21.8	22.5	23.1	23.8	24.5
92.5°	19.8	20.9	21.6	21.9	22.2	22.5	22.9
95°	19.8	20.9	21.4	21.4	21.4	21.4	21.4
97.5°	31.0	24.6	21.4	21.4	21.4	21.4	21.4
100°	76.2	42.4	25.0	24.1	23.2	22.3	21.4
102.5°	207.5	201.2	190.3	174.8	159.4	143.9	128.5
105°	304.4	304.4	304.3	304.1	303.8	303.6	303.4
107.5°	385.4	385.5	385.2	384.5	383.7	383.0	382.4
110°	437.2	436.5	436.3	436.5	436.7	436.9	437.2



TEST NUMBER: P333412-840

CATALOG NUMBER: S125DIW-S850D1050U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	488.9	488.1	487.5	487.2	486.8	486.5	486.1
115°	567.1	566.2	565.1	563.8	562.4	561.1	559.7
117.5°	642.6	641.4	640.5	640.0	639.3	638.7	638.1
120°	692.2	691.7	690.8	689.7	688.6	687.5	686.3
122.5°	738.7	738.2	737.4	736.1	734.8	733.5	732.2
125°	806.2	805.3	804.5	803.9	803.1	802.4	801.7
127.5°	868.7	868.2	867.1	865.5	863.7	862.0	860.4
130°	909.0	908.3	907.4	906.3	905.1	904.0	902.9
132.5°	947.4	947.3	946.6	945.5	944.3	943.2	942.1
135°	1002.6	1002.2	1001.3	999.9	998.6	997.1	995.8
137.5°	1054.9	1055.0	1054.5	1053.3	1052.1	1051.0	1049.8
140°	1087.0	1087.5	1087.0	1085.7	1084.3	1083.0	1081.6
142.5°	1117.8	1117.9	1117.3	1115.9	1114.6	1113.2	1111.9
145°	1162.0	1162.2	1161.6	1160.2	1158.9	1157.5	1156.2
147.5°	1199.7	1199.9	1199.3	1197.6	1196.0	1194.4	1192.8
150°	1224.0	1224.4	1223.7	1221.8	1220.0	1218.2	1216.4
152.5°	1245.2	1245.6	1245.1	1243.3	1241.7	1240.1	1238.5
155°	1274.7	1275.4	1274.8	1272.9	1271.1	1269.3	1267.5
157.5°	1298.9	1299.6	1299.1	1297.3	1295.5	1293.6	1291.8
160°	1314.1	1315.0	1314.5	1312.8	1311.0	1309.2	1307.4
162.5°	1328.3	1329.6	1329.2	1327.2	1325.2	1323.2	1321.2
165°	1346.2	1347.5	1347.3	1345.4	1343.6	1341.8	1340.0
167.5°	1359.8	1361.5	1361.3	1359.2	1357.2	1355.1	1353.1
170°	1367.0	1368.8	1368.6	1366.5	1364.5	1362.5	1360.4
172.5°	1372.1	1373.7	1373.5	1371.5	1369.4	1367.4	1365.3
175°	1378.2	1380.0	1379.9	1377.8	1375.7	1373.7	1371.7
177.5°	1380.0	1381.3	1381.2	1379.7	1378.3	1376.8	1375.3
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8

(END OF REPORT)