

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334429

Luminaire Tested: **S125RDW-S1270D930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P334429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDW-S1270D930-4F0-1E-UDD-F
Description: DEFINE 5 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 1270 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3779.9 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 41.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334429

CATALOG NUMBER: S125RDW-S1270D930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P334429

CATALOG NUMBER: S125RDW-S1270D930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93		95	92	90		91	89	87	85
2	100	92	86	80	98	90	84	79	87	82	78		84	79	76		81	77	74	72
3	92	82	74	68	89	80	73	67	77	71	66		74	69	65		72	67	64	61
4	84	73	64	58	82	71	64	57	69	62	57		67	61	56		64	59	55	53
5	78	65	57	50	76	64	56	50	62	55	49		60	54	49		58	53	48	46
6	72	59	50	44	70	58	50	44	56	49	44		55	48	43		53	47	43	41
7	67	54	45	39	65	53	45	39	51	44	39		50	43	39		49	43	38	36
8	62	49	41	35	61	48	41	35	47	40	35		46	39	35		45	39	34	33
9	58	45	37	32	57	45	37	32	44	37	32		42	36	31		41	36	31	29
10	55	42	34	29	54	41	34	29	40	34	29		39	33	29		39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10332	10332	10332
5°	10356	10239	10302
10°	10278	10143	10143
15°	10156	9938	9857
20°	9999	9650	9534
25°	9816	9369	9162
30°	9588	9038	8750
35°	9355	8698	8289
40°	9138	8343	7834
45°	8873	7946	7339
50°	8608	7515	6823
55°	8300	7103	6272
60°	7992	6602	5681
65°	7626	6019	5005
70°	7210	5293	4313
75°	6633	4462	3588
80°	5843	3507	3013
85°	4928	2868	2690



TEST NUMBER: P334429

CATALOG NUMBER: S125RDW-S1270D930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	4.0
10°-20°	420.8	11.1
20°-30°	610.1	16.1
30°-40°	695.1	18.4
40°-50°	677.5	17.9
50°-60°	570.2	15.1
60°-70°	399.6	10.6
70°-80°	204.8	5.4
80°-90°	51.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1181.5	31.3
0°-40°	1876.6	49.6
0°-60°	3124.4	82.7
0°-90°	3779.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3779.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1600	1600	1600	1600	1600	
5°	1597	1593	1579	1591	1589	151
15°	1519	1512	1486	1485	1474	428
25°	1378	1359	1315	1299	1286	634
35°	1187	1158	1103	1068	1051	743
45°	972	936	870	822	804	749
55°	737	698	631	576	557	659
65°	499	458	394	346	328	494
75°	266	230	179	152	144	281
85°	66	45	39	38	36	77
90°	0	0	0	0	0	



TEST NUMBER: P334429

CATALOG NUMBER: S125RDW-S1270D930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1599.8	1599.8	1599.8	1599.8	1599.8
2.5°	1603.5	1599.8	1587.8	1599.8	1598.6
5°	1597.4	1592.6	1579.3	1591.4	1589.0
7.5°	1585.3	1580.5	1564.8	1574.5	1572.0
10°	1567.2	1563.6	1546.7	1550.3	1546.7
12.5°	1546.7	1541.8	1517.7	1520.1	1514.0
15°	1518.9	1511.6	1486.3	1485.0	1474.2
17.5°	1489.9	1479.0	1448.8	1442.8	1434.3
20°	1454.8	1442.8	1404.1	1398.0	1387.2
22.5°	1416.2	1404.1	1363.0	1349.7	1341.3
25°	1377.5	1359.4	1314.7	1299.0	1285.7
27.5°	1334.0	1312.3	1265.1	1244.6	1231.3
30°	1285.7	1262.7	1212.0	1184.2	1173.3
32.5°	1238.5	1210.8	1158.8	1127.4	1112.9
35°	1186.6	1157.6	1103.2	1068.2	1051.3
37.5°	1137.0	1102.0	1046.4	1005.3	988.4
40°	1083.9	1047.6	989.6	943.7	929.2
42.5°	1028.3	990.8	930.4	886.9	864.0
45°	971.5	936.5	870.0	821.7	803.5
47.5°	912.3	876.0	809.6	760.0	739.5
50°	856.7	816.8	748.0	697.2	679.1
52.5°	796.3	755.2	691.2	635.6	617.5
55°	737.1	698.4	630.8	576.4	557.0
57.5°	676.7	635.6	570.3	517.2	500.3
60°	618.7	576.4	511.1	458.0	439.8
62.5°	557.0	517.2	450.7	402.4	384.3
65°	499.0	458.0	393.9	345.6	327.5
67.5°	441.0	400.0	338.3	292.4	277.9
70°	381.8	340.8	280.3	242.9	228.4
72.5°	323.8	284.0	228.4	194.5	186.1
75°	265.8	229.6	178.8	152.3	143.8
77.5°	206.6	177.6	135.3	114.8	107.5
80°	157.1	128.1	94.3	83.4	81.0
82.5°	108.8	83.4	62.8	59.2	58.0
85°	66.5	44.7	38.7	37.5	36.3
87.5°	27.8	19.3	18.1	18.1	16.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)