

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333419-840

Luminaire Tested: **S125DIW-S850D1340U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333419-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1340U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8187.0 lumens
Efficiency: N/A
Efficacy: 133.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																				
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36																				
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36	31																				
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	32	31	26																				
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26	23																				
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20																				
6	62	50	42	37	57	46	39	34	39	33	29	32	28	25	25	22	20	17																				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	33	28	48	38	31	26	32	27	23	26	22	20	21	18	16	14																				
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12																				
10	46	34	27	22	42	32	25	21	27	22	18	22	19	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.9	1.5
10°-20°	354.1	4.3
20°-30°	575.0	7.0
30°-40°	701.4	8.6
40°-50°	638.1	7.8
50°-60°	508.2	6.2
60°-70°	354.0	4.3
70°-80°	188.8	2.3
80°-90°	51.3	0.6
90°-100°	112.7	1.4
100°-110°	332.9	4.1
110°-120°	563.9	6.9
120°-130°	742.1	9.1
130°-140°	831.6	10.2
140°-150°	815.0	10.0
150°-160°	684.5	8.4
160°-170°	455.0	5.6
170°-180°	159.2	1.9
0°-30°	1048.1	12.8
0°-40°	1749.5	21.4
0°-60°	2895.8	35.4
0°-90°	3489.8	42.6
90°-120°	1009.6	12.3
90°-150°	3398.3	41.5
90°-180°	4697.0	57.4
0°-180°	8187.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	41
90°	31	1	31	1	31	19
95°	113	85	113	85	113	115
105°	325	299	325	299	325	344
115°	570	565	570	565	570	564
125°	829	824	829	824	829	740
135°	1076	1072	1076	1072	1076	830
145°	1303	1298	1303	1298	1303	814
155°	1486	1486	1486	1486	1486	684
165°	1611	1615	1611	1615	1611	454
175°	1673	1679	1673	1679	1673	159
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	16.4	17.1	17.3	17.1	17.4	17.1	18.5	18.2	19.2	20.1	21.4
90°	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8	22.4	21.0	18.9
92.5°	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1	52.2	50.3	47.8
95°	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9	102.9	100.9	98.0
97.5°	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4	162.5	160.6	156.6
100°	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7	203.1	200.5	196.6
102.5°	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0	245.2	242.4	240.4
105°	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6	314.9	313.1	311.3
107.5°	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5	389.7	388.8	387.5
110°	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9	441.0	440.1	439.3



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3	492.9	492.5	491.4
115°	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9	572.2	572.5	571.9
117.5°	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5	650.3	650.1	649.4
120°	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5	703.5	703.5	703.2
122.5°	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4	755.6	755.9	755.1
125°	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9	832.5	833.1	832.8
127.5°	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0	908.3	908.6	908.3
130°	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3	958.6	958.9	958.3
132.5°	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5	1006.8	1007.1	1007.2
135°	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8	1080.8	1080.8	1080.5
137.5°	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0	1152.6	1152.3	1151.7
140°	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5	1197.9	1197.3	1196.4
142.5°	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0	1242.7	1242.3	1241.2
145°	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4	1307.4	1307.4	1306.5
147.5°	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9	1366.2	1365.5	1364.8
150°	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3	1404.3	1404.3	1403.1
152.5°	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2	1438.6	1437.8	1437.3
155°	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1	1487.9	1486.8	1486.5
157.5°	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4	1531.2	1530.0	1529.7
160°	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5	1557.4	1556.2	1555.9
162.5°	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2	1581.8	1580.3	1580.2
165°	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2	1615.1	1613.9	1613.6
167.5°	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7	1638.9	1637.2	1637.2
170°	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4	1653.7	1651.8	1651.8
172.5°	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9	1664.1	1662.3	1662.3
175°	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6	1675.9	1674.2	1674.2
177.5°	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9	1681.5	1680.1	1680.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	21.8	20.6	18.5	16.8	14.2	12.5	11.6	11.6	10.8	10.8	11.7
90°	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3	3.6	6.0	8.3
92.5°	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7	33.3	34.9	36.6
95°	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1	85.7	86.3	86.8
97.5°	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5	141.7	142.0	142.2
100°	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.4
102.5°	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4	229.6	230.8	232.0
105°	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7	300.1	301.5	303.1
107.5°	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2	377.7	379.1	380.6
110°	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7	431.1	432.6	434.0



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1	484.9	485.6	486.5
115°	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6	565.7	566.9	568.0
117.5°	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3	645.8	646.3	646.8
120°	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6	697.0	698.5	699.9
122.5°	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1	750.6	751.1	751.6
125°	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9	825.7	827.5	829.2
127.5°	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5	903.5	904.5	905.5
130°	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7	951.2	952.6	954.1
132.5°	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8	999.3	1001.7	1004.0
135°	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6	1073.3	1075.0	1076.8
137.5°	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8	1143.5	1145.2	1146.8
140°	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8	1188.3	1189.7	1191.2
142.5°	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9	1233.1	1234.4	1235.6
145°	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2	1299.3	1300.5	1301.6
147.5°	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5	1360.1	1360.8	1361.4
150°	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4	1400.1	1399.8	1399.5
152.5°	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9	1434.3	1434.7	1435.1
155°	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6	1531.0	1530.3	1529.6
160°	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8	1558.0	1557.1	1556.2
162.5°	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0	1582.4	1581.7	1581.0
165°	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2	1614.6	1614.0	1613.5
167.5°	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4	1641.2	1640.1	1638.9
170°	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1	1656.0	1654.8	1653.7
172.5°	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6	1666.4	1665.3	1664.1
175°	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4	1678.2	1677.1	1675.9
177.5°	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4	1684.5	1683.5	1682.6
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	12.6	13.9	13.8	14.7	15.1	16.4	16.3	18.2	19.3	20.5	20.3
90°	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8	25.3	26.8	28.0
92.5°	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1	56.0	58.0	59.3
95°	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9	106.9	109.1	110.3
97.5°	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4	166.3	168.2	169.5
100°	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7	208.2	210.9	212.5
102.5°	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0	250.9	253.8	255.6
105°	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6	318.3	320.0	321.3
107.5°	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5	391.4	392.3	392.7
110°	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9	442.7	443.6	443.9



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3	493.7	494.1	494.1
115°	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9	571.6	571.3	571.0
117.5°	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5	650.7	651.0	650.5
120°	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5	703.5	703.5	702.9
122.5°	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4	755.2	754.9	754.4
125°	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9	831.4	830.8	830.4
127.5°	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0	907.7	907.5	907.0
130°	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3	958.1	957.8	957.3
132.5°	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5	1006.2	1005.9	1005.4
135°	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8	1080.8	1080.8	1080.2
137.5°	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0	1153.3	1153.7	1153.1
140°	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5	1199.0	1199.6	1199.2
142.5°	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0	1243.4	1243.7	1243.2
145°	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4	1307.4	1307.4	1306.9
147.5°	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9	1367.6	1368.3	1367.7
150°	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3	1404.3	1404.3	1404.0
152.5°	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2	1439.9	1440.6	1440.5
155°	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1	1490.3	1491.5	1491.3
157.5°	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4	1533.5	1534.7	1534.3
160°	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5	1559.7	1560.8	1560.7
162.5°	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2	1584.5	1585.9	1585.8
165°	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2	1617.4	1618.5	1618.2
167.5°	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7	1642.4	1644.2	1644.2
170°	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4	1657.1	1658.8	1658.7
172.5°	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9	1667.6	1669.3	1669.3
175°	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6	1679.4	1681.1	1680.9
177.5°	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9	1684.4	1685.8	1685.7
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	21.3	21.0	21.2	22.2	21.2	21.0	21.3	20.3	20.5	19.3	18.2
90°	28.8	29.7	30.6	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8
92.5°	59.9	60.6	61.2	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1
95°	110.9	111.5	112.1	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9
97.5°	169.8	170.2	170.5	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4
100°	213.1	213.7	214.3	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7
102.5°	256.4	257.2	258.0	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0
105°	322.2	323.2	324.0	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6
107.5°	392.6	392.5	392.5	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5
110°	443.6	443.3	443.0	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	493.6	493.1	492.5	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3
115°	570.7	570.4	570.2	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9
117.5°	649.3	648.1	647.0	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5
120°	701.7	700.5	699.3	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5
122.5°	753.4	752.5	751.5	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4
125°	830.1	829.8	829.5	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9
127.5°	906.5	905.8	905.2	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0
130°	956.7	956.1	955.5	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3
132.5°	1004.6	1003.7	1002.9	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5
135°	1078.9	1077.8	1076.6	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8
137.5°	1151.7	1150.1	1148.7	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0
140°	1197.7	1196.3	1194.9	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5
142.5°	1241.7	1240.3	1238.8	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0
145°	1306.1	1305.1	1304.2	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4
147.5°	1365.6	1363.7	1361.7	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9
150°	1403.4	1402.8	1402.2	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3
152.5°	1439.4	1438.4	1437.2	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2
155°	1489.9	1488.4	1486.9	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1
157.5°	1532.4	1530.5	1528.5	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4
160°	1559.3	1557.8	1556.4	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5
162.5°	1584.1	1582.4	1580.7	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2
165°	1616.5	1614.8	1613.0	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2
167.5°	1642.3	1640.5	1638.7	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7
170°	1656.7	1654.7	1652.5	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4
172.5°	1667.5	1665.7	1663.9	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9
175°	1678.9	1676.9	1674.9	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6
177.5°	1683.9	1682.3	1680.7	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	16.3	16.4	15.1	14.7	13.8	13.9	12.6	11.7	10.8	10.8	11.6
90°	22.4	21.0	18.9	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3
92.5°	52.2	50.3	47.8	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7
95°	102.9	100.9	98.0	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1
97.5°	162.5	160.6	156.6	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5
100°	203.1	200.5	196.6	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4
102.5°	245.2	242.4	240.4	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4
105°	314.9	313.1	311.3	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7
107.5°	389.7	388.8	387.5	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2
110°	441.0	440.1	439.3	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	492.9	492.5	491.4	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1
115°	572.2	572.5	571.9	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6
117.5°	650.3	650.1	649.4	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3
120°	703.5	703.5	703.2	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6
122.5°	755.6	755.9	755.1	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1
125°	832.5	833.1	832.8	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9
127.5°	908.3	908.6	908.3	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5
130°	958.6	958.9	958.3	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7
132.5°	1006.8	1007.1	1007.2	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8
135°	1080.8	1080.8	1080.5	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6
137.5°	1152.6	1152.3	1151.7	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8
140°	1197.9	1197.3	1196.4	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8
142.5°	1242.7	1242.3	1241.2	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9
145°	1307.4	1307.4	1306.5	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2
147.5°	1366.2	1365.5	1364.8	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5
150°	1404.3	1404.3	1403.1	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4
152.5°	1438.6	1437.8	1437.3	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9
155°	1487.9	1486.8	1486.5	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1531.2	1530.0	1529.7	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6
160°	1557.4	1556.2	1555.9	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8
162.5°	1581.8	1580.3	1580.2	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0
165°	1615.1	1613.9	1613.6	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2
167.5°	1638.9	1637.2	1637.2	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4
170°	1653.7	1651.8	1651.8	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1
172.5°	1664.1	1662.3	1662.3	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6
175°	1675.9	1674.2	1674.2	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4
177.5°	1681.5	1680.1	1680.4	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.6	12.5	14.2	16.8	18.5	20.6	21.8	21.4	20.1	19.2	18.2
90°	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8
92.5°	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1
95°	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9
97.5°	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4
100°	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7
102.5°	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0
105°	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6
107.5°	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5
110°	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3
115°	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9
117.5°	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5
120°	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5
122.5°	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4
125°	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9
127.5°	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0
130°	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3
132.5°	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5
135°	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8
137.5°	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0
140°	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5
142.5°	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0
145°	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4
147.5°	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9
150°	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3
152.5°	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2
155°	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1
157.5°	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4
160°	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5
162.5°	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2
165°	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2
167.5°	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7
170°	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4
172.5°	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9
175°	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6
177.5°	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	18.5	17.1	17.4	17.1	17.3	17.1	16.4
90°	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	442.7	443.6	443.9	443.6	443.3	443.0	442.7



TEST NUMBER: P333419-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)