

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333404-840

Luminaire Tested: **S125DIW-S850D470U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333404-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5343.5 lumens
Efficiency: N/A
Efficacy: 141.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333404-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333404-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	92	89	95	91	87	84	80	78	75	70	68	67	61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45
3	84	74	67	60	78	70	63	58	62	57	52	55	50	47	48	45	42	38
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	38	44	39	35	38	35	31	29
6	65	53	44	38	61	50	42	37	44	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333404-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	2.3
10°-20°	353.1	6.6
20°-30°	521.3	9.8
30°-40°	608.3	11.4
40°-50°	611.0	11.4
50°-60°	536.3	10.0
60°-70°	399.6	7.5
70°-80°	228.5	4.3
80°-90°	67.8	1.3
90°-100°	22.4	0.4
100°-110°	138.0	2.6
110°-120°	250.3	4.7
120°-130°	321.3	6.0
130°-140°	345.6	6.5
140°-150°	324.4	6.1
150°-160°	262.4	4.9
160°-170°	169.7	3.2
170°-180°	58.5	1.1
0°-30°	999.4	18.7
0°-40°	1607.8	30.1
0°-60°	2755.1	51.6
0°-90°	3451.0	64.6
90°-120°	410.7	7.7
90°-150°	1401.9	26.2
90°-180°	1893.0	35.4
0°-180°	5343.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	0	4	7	10	11	4
95°	26	24	7	9	10	33
105°	134	136	136	136	136	142
115°	252	254	255	253	250	250
125°	359	362	362	360	359	320
135°	447	450	449	448	446	345
145°	519	519	520	520	517	324
155°	571	569	569	570	567	263
165°	603	600	600	603	599	170
175°	616	614	614	617	614	59
180°	616	616	616	616	616	



TEST NUMBER: P333404-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.7	22.9	23.0	23.2	23.4	23.4	23.4	23.3	23.3	23.2	23.4
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.3	7.8
92.5°	7.1	6.5	5.9	5.4	4.7	4.7	5.5	6.1	6.7	7.3	7.8
95°	26.1	25.8	25.4	25.1	24.8	22.7	18.9	15.0	11.2	7.3	7.8
97.5°	54.3	54.9	55.4	56.0	56.6	53.0	45.3	37.8	30.1	22.5	19.6
100°	76.2	76.6	77.0	77.3	77.6	77.9	78.3	78.7	79.1	79.5	64.3
102.5°	98.6	99.0	99.4	99.8	100.2	100.5	100.7	100.9	101.2	101.4	98.6
105°	134.3	134.7	135.1	135.5	135.9	136.1	136.1	136.1	136.1	136.1	136.1
107.5°	171.4	171.4	171.4	171.4	171.4	171.5	171.7	171.9	172.1	172.3	172.4
110°	195.5	195.5	195.5	195.5	195.5	195.6	195.8	196.0	196.2	196.4	196.1



TEST NUMBER: P333404-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.2	218.4	218.6	218.9	219.1	219.3	219.4	219.6	219.7	219.8	219.4
115°	252.2	252.7	253.2	253.7	254.2	254.5	254.6	254.7	254.8	254.9	254.5
117.5°	287.4	287.3	287.3	287.3	287.3	287.5	287.8	288.2	288.6	289.0	288.5
120°	309.3	309.2	309.1	309.0	308.9	309.0	309.3	309.6	309.9	310.2	310.0
122.5°	328.7	329.0	329.4	329.8	330.2	330.4	330.6	330.7	330.9	331.0	330.8
125°	358.6	359.3	360.0	360.7	361.4	361.8	361.8	361.8	361.8	361.8	361.4
127.5°	387.2	387.8	388.3	388.8	389.3	389.5	389.4	389.4	389.3	389.2	389.0
130°	404.8	405.3	405.8	406.3	406.8	407.1	407.2	407.3	407.4	407.5	407.2
132.5°	422.3	422.9	423.5	424.0	424.6	424.9	424.6	424.4	424.1	423.9	423.9
135°	447.3	447.9	448.5	449.1	449.7	449.9	449.7	449.5	449.3	449.1	448.9
137.5°	470.2	470.7	471.2	471.8	472.3	472.5	472.3	472.1	471.9	471.7	471.8
140°	485.1	485.3	485.5	485.7	485.9	486.0	485.9	485.8	485.7	485.6	485.8
142.5°	498.7	498.9	499.0	499.1	499.2	499.3	499.5	499.6	499.8	499.9	499.9
145°	518.6	518.8	519.0	519.2	519.4	519.5	519.5	519.5	519.5	519.5	519.6
147.5°	535.9	535.8	535.8	535.7	535.7	535.7	535.9	536.0	536.1	536.2	536.3
150°	546.8	546.6	546.4	546.2	546.0	546.0	546.2	546.4	546.6	546.8	547.0
152.5°	557.4	557.0	556.5	556.1	555.6	555.5	555.7	555.9	556.1	556.3	556.5
155°	571.1	570.5	569.9	569.3	568.7	568.5	568.7	568.9	569.1	569.3	569.6
157.5°	581.6	581.2	580.9	580.5	580.1	580.0	580.0	580.0	580.0	580.1	580.4
160°	588.9	588.2	587.6	587.0	586.4	586.2	586.3	586.4	586.5	586.6	587.0
162.5°	594.7	594.1	593.5	592.9	592.3	592.1	592.2	592.3	592.4	592.5	593.0
165°	602.6	602.0	601.4	600.8	600.2	599.9	600.0	600.1	600.2	600.3	600.9
167.5°	608.4	607.8	607.2	606.5	605.9	605.6	605.7	605.8	605.9	606.0	606.8
170°	611.8	611.1	610.3	609.6	608.8	608.5	608.6	608.7	608.8	608.9	609.8
172.5°	613.9	613.2	612.5	611.8	611.1	610.9	611.0	611.2	611.4	611.6	612.3
175°	616.3	615.7	615.1	614.5	613.9	613.6	613.7	613.8	613.9	614.0	614.8
177.5°	617.4	616.9	616.4	615.9	615.4	615.2	615.3	615.4	615.5	615.6	616.1
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3



TEST NUMBER: P333404-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	23.5	23.6	23.7	23.5	23.2	22.9	22.6	22.3
90°	8.3	8.8	9.3	9.8	10.1	10.4	10.7	11.0
92.5°	8.3	8.8	9.3	9.7	9.8	10.0	10.1	10.2
95°	8.3	8.8	9.3	9.6	9.6	9.6	9.6	9.6
97.5°	16.8	13.9	11.0	9.6	9.6	9.6	9.6	9.6
100°	49.3	34.1	19.0	11.2	10.8	10.4	10.0	9.6
102.5°	95.7	92.8	90.0	85.1	78.2	71.3	64.3	57.5
105°	136.1	136.1	136.1	136.1	136.0	135.9	135.8	135.7
107.5°	172.4	172.4	172.4	172.3	172.0	171.7	171.4	171.1
110°	195.8	195.5	195.2	195.1	195.2	195.3	195.4	195.5



TEST NUMBER: P333404-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	219.0	218.6	218.3	218.0	217.9	217.7	217.6	217.4
115°	254.1	253.7	253.3	252.8	252.2	251.6	251.0	250.3
117.5°	287.9	287.4	286.9	286.5	286.2	286.0	285.7	285.5
120°	309.8	309.6	309.4	309.0	308.5	308.0	307.5	307.0
122.5°	330.6	330.4	330.2	329.8	329.2	328.6	328.1	327.5
125°	361.0	360.6	360.2	359.8	359.5	359.2	358.9	358.6
127.5°	388.8	388.6	388.4	387.9	387.1	386.4	385.6	384.9
130°	406.9	406.6	406.3	405.9	405.4	404.9	404.3	403.8
132.5°	423.8	423.7	423.7	423.4	422.9	422.4	421.9	421.4
135°	448.7	448.5	448.3	447.9	447.3	446.7	446.1	445.5
137.5°	471.8	471.9	471.9	471.7	471.1	470.6	470.1	469.6
140°	486.0	486.3	486.5	486.3	485.6	485.0	484.4	483.8
142.5°	500.0	500.0	500.1	499.8	499.2	498.6	498.0	497.4
145°	519.7	519.8	519.9	519.6	519.0	518.4	517.8	517.2
147.5°	536.5	536.6	536.7	536.4	535.7	535.0	534.2	533.5
150°	547.2	547.4	547.6	547.3	546.5	545.7	544.9	544.1
152.5°	556.7	556.9	557.1	556.9	556.1	555.4	554.7	554.0
155°	569.9	570.2	570.5	570.2	569.4	568.6	567.7	566.9
157.5°	580.7	581.0	581.3	581.1	580.3	579.5	578.7	577.8
160°	587.4	587.8	588.2	588.0	587.2	586.4	585.6	584.8
162.5°	593.6	594.2	594.7	594.6	593.7	592.8	591.9	591.0
165°	601.6	602.2	602.8	602.7	601.9	601.0	600.2	599.4
167.5°	607.5	608.2	608.9	608.9	607.9	607.0	606.1	605.2
170°	610.6	611.5	612.3	612.2	611.3	610.4	609.5	608.5
172.5°	613.0	613.7	614.5	614.4	613.5	612.6	611.7	610.8
175°	615.6	616.4	617.2	617.2	616.3	615.4	614.5	613.6
177.5°	616.7	617.2	617.8	617.8	617.1	616.5	615.8	615.2
180°	616.3	616.3	616.3	616.3	616.3	616.3	616.3	616.3

(END OF REPORT)