

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333405-840

Luminaire Tested: **S125DIW-S850D470U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333405-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5092.2 lumens
Efficiency: N/A
Efficacy: 135.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333405-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333405-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	97	93	90	96	92	88	85	82	79	77	72	70	69	64	62	61	57
2	93	85	78	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	50	47	44	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	45	41	38	35
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333405-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	2.5
10°-20°	353.1	6.9
20°-30°	521.3	10.2
30°-40°	608.3	11.9
40°-50°	611.0	12.0
50°-60°	536.3	10.5
60°-70°	399.6	7.8
70°-80°	228.5	4.5
80°-90°	67.8	1.3
90°-100°	39.4	0.8
100°-110°	116.3	2.3
110°-120°	197.1	3.9
120°-130°	259.3	5.1
130°-140°	290.6	5.7
140°-150°	284.8	5.6
150°-160°	239.2	4.7
160°-170°	159.0	3.1
170°-180°	55.6	1.1
0°-30°	999.4	19.6
0°-40°	1607.8	31.6
0°-60°	2755.1	54.1
0°-90°	3451.0	67.8
90°-120°	352.8	6.9
90°-150°	1187.4	23.3
90°-180°	1641.0	32.2
0°-180°	5092.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	0	4	7	10	11	5
95°	30	31	35	38	39	32
105°	104	107	109	112	114	111
115°	197	199	200	200	199	195
125°	288	290	291	290	290	258
135°	374	377	378	378	376	288
145°	454	455	457	457	455	283
155°	519	519	520	521	519	239
165°	564	564	564	565	563	159
175°	587	585	585	587	584	56
180°	588	588	588	588	588	



TEST NUMBER: P333405-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.7	22.9	23.0	23.2	23.4	23.4	23.4	23.3	23.3	23.3	23.4
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.4	7.9
92.5°	11.1	11.6	12.2	12.8	13.3	14.0	14.9	15.9	16.7	17.6	18.3
95°	29.8	30.0	30.2	30.4	30.6	31.2	32.2	33.2	34.2	35.2	36.0
97.5°	49.4	49.5	49.6	49.7	49.8	50.5	51.9	53.3	54.7	56.1	56.8
100°	64.1	64.1	64.1	64.1	64.1	64.7	66.0	67.4	68.7	70.0	71.0
102.5°	79.8	80.2	80.7	81.1	81.5	82.0	82.7	83.3	84.0	84.6	85.6
105°	104.3	104.8	105.3	105.8	106.4	106.9	107.6	108.2	108.8	109.4	110.0
107.5°	131.5	132.0	132.5	133.0	133.5	134.0	134.4	134.9	135.4	135.8	136.1
110°	150.2	150.7	151.2	151.7	152.2	152.6	152.9	153.2	153.5	153.8	154.1



TEST NUMBER: P333405-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.2	169.5	169.7	170.0	170.3	170.6	171.0	171.4	171.7	172.1	172.3
115°	197.2	197.6	198.1	198.5	198.9	199.2	199.4	199.7	199.9	200.1	200.0
117.5°	225.5	225.6	225.8	226.0	226.2	226.4	226.6	226.7	226.9	227.1	227.2
120°	243.1	243.6	244.1	244.6	245.1	245.4	245.5	245.6	245.7	245.8	245.8
122.5°	262.1	262.3	262.5	262.7	262.8	263.1	263.3	263.6	263.9	264.1	264.0
125°	287.9	288.5	289.1	289.7	290.3	290.7	290.8	290.9	291.0	291.1	290.9
127.5°	315.4	315.7	316.1	316.4	316.8	317.0	317.1	317.2	317.3	317.5	317.4
130°	331.8	332.3	332.9	333.4	333.9	334.3	334.5	334.7	334.9	335.1	335.0
132.5°	348.3	349.1	350.0	350.8	351.6	352.0	352.0	351.9	351.9	351.8	351.7
135°	374.4	375.1	375.7	376.3	376.9	377.2	377.3	377.4	377.5	377.6	377.6
137.5°	398.9	399.5	400.1	400.7	401.3	401.7	401.9	402.1	402.3	402.6	402.7
140°	414.7	415.2	415.7	416.2	416.7	417.2	417.5	417.8	418.1	418.4	418.6
142.5°	430.4	430.8	431.3	431.7	432.1	432.5	432.9	433.3	433.7	434.1	434.2
145°	453.6	454.0	454.4	454.8	455.2	455.6	455.9	456.2	456.5	456.8	456.8
147.5°	475.0	475.2	475.4	475.6	475.9	476.2	476.4	476.7	476.9	477.2	477.4
150°	489.3	489.2	489.1	489.0	488.9	489.1	489.5	489.9	490.3	490.7	490.7
152.5°	501.0	501.2	501.3	501.4	501.6	501.7	501.9	502.1	502.2	502.4	502.6
155°	519.1	519.1	519.1	519.1	519.1	519.1	519.2	519.3	519.4	519.5	519.9
157.5°	535.1	534.9	534.7	534.5	534.2	534.2	534.3	534.4	534.5	534.6	535.0
160°	544.7	544.4	544.0	543.7	543.4	543.3	543.4	543.5	543.6	543.7	544.2
162.5°	553.1	552.9	552.7	552.4	552.2	552.1	552.1	552.1	552.2	552.2	552.7
165°	564.3	564.1	563.9	563.7	563.5	563.5	563.6	563.7	563.8	563.9	564.3
167.5°	573.9	573.5	573.1	572.7	572.3	572.1	572.1	572.1	572.1	572.1	572.7
170°	579.0	578.6	578.1	577.7	577.3	577.1	577.1	577.1	577.1	577.1	577.7
172.5°	582.7	582.3	581.9	581.5	581.1	580.9	580.9	580.9	580.9	580.9	581.5
175°	586.8	586.3	585.9	585.5	585.1	584.9	584.9	584.9	584.9	584.9	585.5
177.5°	588.9	588.5	588.2	587.9	587.5	587.3	587.3	587.2	587.1	587.0	587.5
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333405-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	23.5	23.6	23.7	23.6	23.2	22.9	22.6	22.3
90°	8.4	8.9	9.4	9.8	10.1	10.4	10.7	11.0
92.5°	18.9	19.6	20.3	20.7	20.9	21.1	21.4	21.6
95°	36.7	37.4	38.1	38.6	38.8	39.0	39.2	39.4
97.5°	57.5	58.2	58.8	59.2	59.3	59.5	59.6	59.7
100°	71.9	72.8	73.7	74.2	74.4	74.6	74.8	75.0
102.5°	86.6	87.7	88.7	89.3	89.6	89.9	90.2	90.5
105°	110.6	111.2	111.8	112.3	112.6	112.9	113.2	113.5
107.5°	136.4	136.7	137.0	137.2	137.2	137.1	137.1	137.1
110°	154.4	154.7	155.0	155.1	155.0	154.9	154.8	154.7



TEST NUMBER: P333405-840

CATALOG NUMBER: S125DIW-S850D470U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	172.4	172.5	172.7	172.7	172.5	172.3	172.1	171.9
115°	199.9	199.8	199.7	199.5	199.4	199.3	199.2	199.1
117.5°	227.3	227.3	227.4	227.3	226.9	226.5	226.0	225.6
120°	245.8	245.8	245.8	245.6	245.2	244.8	244.4	244.0
122.5°	264.0	263.9	263.8	263.6	263.3	263.0	262.6	262.3
125°	290.7	290.5	290.3	290.1	290.0	289.9	289.8	289.7
127.5°	317.3	317.2	317.1	316.9	316.7	316.5	316.3	316.1
130°	334.9	334.8	334.7	334.5	334.3	334.1	333.9	333.7
132.5°	351.6	351.5	351.4	351.3	351.0	350.7	350.4	350.1
135°	377.6	377.6	377.6	377.4	377.0	376.6	376.2	375.8
137.5°	402.8	402.9	403.1	402.9	402.4	401.9	401.3	400.8
140°	418.8	419.0	419.2	419.0	418.5	418.0	417.5	417.0
142.5°	434.3	434.4	434.5	434.3	433.8	433.3	432.8	432.3
145°	456.8	456.8	456.8	456.7	456.4	456.1	455.8	455.4
147.5°	477.6	477.9	478.1	477.9	477.2	476.5	475.7	475.1
150°	490.7	490.7	490.7	490.6	490.4	490.2	490.0	489.8
152.5°	502.9	503.1	503.3	503.3	502.9	502.6	502.2	501.8
155°	520.3	520.7	521.1	521.1	520.6	520.1	519.6	519.1
157.5°	535.4	535.8	536.2	536.1	535.4	534.7	534.1	533.4
160°	544.6	545.0	545.4	545.3	544.8	544.3	543.8	543.3
162.5°	553.2	553.6	554.1	554.1	553.5	552.9	552.3	551.7
165°	564.7	565.1	565.5	565.4	564.8	564.2	563.6	563.0
167.5°	573.3	573.9	574.5	574.5	573.8	573.2	572.6	572.0
170°	578.3	579.0	579.7	579.6	578.9	578.1	577.4	576.7
172.5°	582.1	582.7	583.3	583.3	582.6	582.0	581.4	580.8
175°	586.1	586.8	587.4	587.3	586.6	585.9	585.2	584.5
177.5°	588.0	588.5	589.1	589.0	588.4	587.8	587.2	586.7
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1

(END OF REPORT)