

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333410-840

Luminaire Tested: **S125DIW-S850D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333410-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D770U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6551.6 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333410-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333410-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333410-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.9
10°-20°	353.1	5.4
20°-30°	521.3	8.0
30°-40°	608.3	9.3
40°-50°	611.0	9.3
50°-60°	536.3	8.2
60°-70°	399.6	6.1
70°-80°	228.5	3.5
80°-90°	68.6	1.0
90°-100°	36.7	0.6
100°-110°	226.1	3.5
110°-120°	410.0	6.3
120°-130°	526.2	8.0
130°-140°	566.0	8.6
140°-150°	531.3	8.1
150°-160°	429.7	6.6
160°-170°	277.9	4.2
170°-180°	95.9	1.5
0°-30°	999.4	15.3
0°-40°	1607.8	24.5
0°-60°	2755.1	42.1
0°-90°	3451.8	52.7
90°-120°	672.8	10.3
90°-150°	2296.2	35.0
90°-180°	3100.0	47.3
0°-180°	6551.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	1	7	12	16	18	5
95°	43	39	12	16	16	54
105°	220	223	223	223	222	233
115°	413	417	418	414	410	409
125°	587	592	593	590	587	524
135°	733	737	736	734	730	564
145°	849	851	851	851	847	531
155°	935	931	932	934	929	431
165°	987	983	983	987	982	279
175°	1010	1005	1006	1011	1005	96
180°	1010	1010	1010	1010	1010	



TEST NUMBER: P333410-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.8	23.0	23.3	23.6	23.8	24.0	24.0	24.1	24.1	24.2	24.3
90°	0.7	2.1	3.4	4.7	6.1	7.3	8.5	9.7	10.8	12.0	12.8
92.5°	11.5	10.6	9.7	8.7	7.8	7.9	8.9	9.9	10.9	12.0	12.8
95°	42.6	42.1	41.6	41.2	40.7	37.3	30.9	24.6	18.3	12.0	12.8
97.5°	89.1	90.0	90.9	91.7	92.6	86.8	74.3	61.8	49.3	36.9	32.1
100°	124.9	125.4	125.9	126.4	126.9	127.5	128.3	128.9	129.6	130.2	105.4
102.5°	161.5	162.1	162.8	163.4	164.0	164.5	164.9	165.3	165.7	166.1	161.5
105°	219.9	220.7	221.4	222.0	222.7	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.7	280.7	280.7	280.7	280.7	280.9	281.2	281.6	282.0	282.3	282.3
110°	320.2	320.2	320.2	320.2	320.2	320.4	320.7	321.1	321.4	321.7	321.2



TEST NUMBER: P333410-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.4	357.8	358.2	358.6	359.0	359.3	359.5	359.7	359.9	360.1	359.4
115°	413.0	413.8	414.8	415.6	416.4	416.9	417.1	417.2	417.4	417.6	416.9
117.5°	470.7	470.6	470.6	470.6	470.5	470.8	471.5	472.1	472.7	473.3	472.5
120°	506.5	506.4	506.2	506.0	505.9	506.0	506.5	507.1	507.6	508.1	507.8
122.5°	538.3	539.0	539.6	540.2	540.9	541.3	541.5	541.7	542.0	542.2	541.9
125°	587.4	588.5	589.8	590.9	592.1	592.6	592.6	592.6	592.6	592.6	592.0
127.5°	634.2	635.1	635.9	636.7	637.5	637.9	637.8	637.7	637.6	637.5	637.1
130°	663.0	663.8	664.6	665.5	666.3	666.8	666.9	667.1	667.3	667.4	666.9
132.5°	691.7	692.7	693.7	694.6	695.6	695.9	695.5	695.1	694.8	694.4	694.3
135°	732.6	733.6	734.6	735.6	736.6	736.9	736.6	736.2	735.9	735.6	735.2
137.5°	770.1	771.0	771.8	772.7	773.6	773.9	773.6	773.3	773.0	772.6	772.7
140°	794.7	795.0	795.4	795.7	796.0	796.1	795.9	795.8	795.6	795.4	795.8
142.5°	816.8	817.0	817.2	817.4	817.6	817.8	818.1	818.3	818.5	818.8	818.8
145°	849.3	849.6	850.0	850.3	850.6	850.8	850.8	850.8	850.8	850.8	850.9
147.5°	877.8	877.7	877.6	877.6	877.5	877.6	877.8	877.9	878.1	878.3	878.5
150°	895.6	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	896.1
152.5°	913.0	912.3	911.6	910.9	910.1	909.9	910.3	910.6	910.9	911.2	911.6
155°	935.3	934.3	933.3	932.3	931.4	931.0	931.4	931.7	932.0	932.3	932.8
157.5°	952.5	952.0	951.4	950.8	950.2	949.9	949.9	950.0	950.0	950.0	950.6
160°	964.5	963.5	962.5	961.5	960.6	960.1	960.3	960.5	960.6	960.8	961.5
162.5°	974.1	973.1	972.1	971.1	970.1	969.7	969.9	970.1	970.2	970.4	971.3
165°	986.9	985.9	985.0	984.0	983.0	982.6	982.7	982.9	983.1	983.2	984.2
167.5°	996.5	995.5	994.5	993.5	992.4	992.0	992.2	992.3	992.5	992.7	993.8
170°	1002.0	1000.8	999.6	998.5	997.2	996.7	996.9	997.1	997.2	997.4	998.8
172.5°	1005.5	1004.4	1003.2	1002.0	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8
175°	1009.5	1008.5	1007.4	1006.4	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0
177.5°	1011.2	1010.4	1009.7	1008.9	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333410-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	24.5	24.7	24.8	24.8	24.5	24.2	24.0	23.7
90°	13.6	14.4	15.2	16.0	16.5	17.0	17.5	18.0
92.5°	13.6	14.4	15.2	15.9	16.1	16.3	16.6	16.8
95°	13.6	14.4	15.2	15.8	15.8	15.8	15.8	15.8
97.5°	27.5	22.7	18.1	15.8	15.8	15.8	15.8	15.8
100°	80.7	55.8	31.1	18.4	17.7	17.1	16.4	15.8
102.5°	156.7	152.1	147.3	139.4	128.1	116.7	105.4	94.1
105°	223.0	223.0	223.0	222.9	222.8	222.6	222.4	222.3
107.5°	282.4	282.4	282.4	282.2	281.7	281.1	280.6	280.1
110°	320.7	320.2	319.7	319.6	319.7	319.9	320.1	320.2



TEST NUMBER: P333410-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.8	358.2	357.5	357.1	356.9	356.7	356.4	356.2
115°	416.2	415.6	414.9	414.0	413.0	412.0	411.0	410.0
117.5°	471.6	470.8	469.9	469.3	468.8	468.4	468.0	467.6
120°	507.5	507.1	506.8	506.1	505.3	504.5	503.7	502.8
122.5°	541.5	541.2	540.9	540.2	539.3	538.3	537.3	536.3
125°	591.3	590.7	590.0	589.4	588.9	588.3	587.9	587.4
127.5°	636.8	636.4	636.1	635.3	634.0	632.8	631.6	630.4
130°	666.5	666.0	665.5	664.8	664.0	663.2	662.3	661.5
132.5°	694.2	694.1	694.0	693.6	692.7	691.9	691.1	690.2
135°	734.9	734.6	734.3	733.6	732.6	731.5	730.5	729.5
137.5°	772.8	772.8	773.0	772.5	771.6	770.8	769.9	769.1
140°	796.1	796.4	796.8	796.4	795.4	794.5	793.5	792.4
142.5°	818.9	819.0	819.0	818.6	817.6	816.6	815.6	814.6
145°	851.1	851.3	851.4	851.0	850.0	849.0	848.1	847.1
147.5°	878.7	878.9	879.1	878.6	877.5	876.3	875.0	873.8
150°	896.4	896.7	897.1	896.6	895.1	893.8	892.5	891.2
152.5°	911.9	912.2	912.6	912.1	910.9	909.8	908.6	907.4
155°	933.3	933.8	934.3	933.9	932.6	931.3	930.0	928.6
157.5°	951.1	951.6	952.1	951.7	950.4	949.1	947.8	946.4
160°	962.1	962.8	963.4	963.1	961.8	960.5	959.2	957.8
162.5°	972.2	973.1	974.1	973.8	972.4	970.9	969.5	968.0
165°	985.2	986.2	987.2	987.0	985.7	984.4	983.1	981.7
167.5°	995.0	996.2	997.4	997.3	995.8	994.3	992.8	991.3
170°	1000.1	1001.5	1002.8	1002.7	1001.2	999.7	998.2	996.7
172.5°	1004.0	1005.2	1006.4	1006.2	1004.8	1003.3	1001.8	1000.3
175°	1008.4	1009.7	1011.0	1010.9	1009.5	1007.9	1006.4	1004.9
177.5°	1010.1	1011.0	1012.0	1011.9	1010.8	1009.8	1008.7	1007.6
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5

(END OF REPORT)