

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333411-840

Luminaire Tested: **S125DIW-S850D770U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333411-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D770U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6139.9 lumens  
Efficiency: N/A  
Efficacy: 136.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333411-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333411-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333411-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.0	2.0
10°-20°	353.1	5.8
20°-30°	521.3	8.5
30°-40°	608.3	9.9
40°-50°	611.0	10.0
50°-60°	536.3	8.7
60°-70°	399.6	6.5
70°-80°	228.5	3.7
80°-90°	68.6	1.1
90°-100°	64.5	1.1
100°-110°	190.5	3.1
110°-120°	322.7	5.3
120°-130°	424.7	6.9
130°-140°	475.9	7.8
140°-150°	466.4	7.6
150°-160°	391.7	6.4
160°-170°	260.4	4.2
170°-180°	91.1	1.5
0°-30°	999.4	16.3
0°-40°	1607.8	26.2
0°-60°	2755.1	44.9
0°-90°	3451.8	56.2
90°-120°	577.8	9.4
90°-150°	1944.8	31.7
90°-180°	2688.0	43.8
0°-180°	6139.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	1	7	12	16	18	6
95°	49	51	58	63	64	52
105°	171	175	179	184	186	183
115°	323	326	328	327	326	319
125°	472	476	477	475	474	422
135°	613	618	618	618	616	472
145°	743	746	748	748	746	464
155°	850	850	851	853	850	391
165°	924	923	924	926	922	261
175°	961	958	958	962	957	91
180°	963	963	963	963	963	



TEST NUMBER: P333411-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.8	23.0	23.3	23.6	23.8	24.0	24.0	24.1	24.1	24.2	24.3
90°	0.7	2.1	3.4	4.7	6.1	7.4	8.5	9.7	10.8	12.0	12.8
92.5°	18.2	19.1	20.0	20.9	21.9	23.0	24.5	26.0	27.4	28.8	29.9
95°	48.8	49.1	49.4	49.7	50.1	51.1	52.7	54.4	56.0	57.8	58.9
97.5°	81.0	81.1	81.2	81.4	81.5	82.7	85.0	87.4	89.6	91.9	93.0
100°	104.9	104.9	104.9	104.9	104.9	106.0	108.2	110.4	112.5	114.7	116.2
102.5°	130.8	131.4	132.1	132.7	133.4	134.3	135.4	136.5	137.5	138.7	140.4
105°	171.0	171.8	172.6	173.4	174.3	175.2	176.2	177.1	178.1	179.2	180.2
107.5°	215.3	216.1	217.0	217.8	218.6	219.4	220.3	221.0	221.8	222.5	223.0
110°	245.9	246.7	247.5	248.4	249.2	249.8	250.3	250.9	251.4	251.9	252.4



TEST NUMBER: P333411-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.1	277.5	277.9	278.4	278.8	279.3	279.9	280.6	281.2	281.9	282.2
115°	323.2	323.8	324.5	325.1	325.8	326.3	326.6	326.9	327.3	327.6	327.4
117.5°	369.3	369.6	369.9	370.2	370.5	370.8	371.1	371.4	371.7	372.0	372.1
120°	398.1	398.9	399.7	400.6	401.4	401.9	402.0	402.2	402.4	402.5	402.5
122.5°	429.3	429.6	429.9	430.2	430.5	430.8	431.2	431.7	432.1	432.5	432.4
125°	471.5	472.5	473.5	474.5	475.5	476.2	476.3	476.5	476.7	476.8	476.5
127.5°	516.5	517.1	517.7	518.3	518.8	519.2	519.4	519.6	519.8	520.0	519.8
130°	543.5	544.3	545.2	546.0	546.8	547.4	547.8	548.1	548.5	548.8	548.6
132.5°	570.5	571.9	573.2	574.6	575.9	576.6	576.5	576.4	576.4	576.3	576.2
135°	613.2	614.2	615.2	616.2	617.2	617.8	617.9	618.1	618.3	618.4	618.4
137.5°	653.4	654.4	655.3	656.3	657.3	657.9	658.3	658.6	659.0	659.4	659.6
140°	679.2	680.0	680.9	681.7	682.6	683.2	683.7	684.2	684.7	685.2	685.5
142.5°	705.0	705.7	706.4	707.1	707.8	708.4	709.1	709.7	710.3	710.9	711.1
145°	743.0	743.6	744.3	744.9	745.6	746.2	746.7	747.2	747.7	748.2	748.2
147.5°	778.0	778.4	778.7	779.1	779.5	779.8	780.2	780.6	781.0	781.4	781.8
150°	801.4	801.2	801.0	800.9	800.7	801.0	801.6	802.3	802.9	803.7	803.7
152.5°	820.6	820.8	821.0	821.3	821.5	821.7	822.0	822.3	822.5	822.8	823.2
155°	850.1	850.1	850.1	850.1	850.1	850.2	850.4	850.5	850.7	850.9	851.5
157.5°	876.6	876.2	875.8	875.5	875.0	874.9	875.1	875.3	875.5	875.7	876.3
160°	892.1	891.6	891.1	890.6	890.1	889.9	890.1	890.3	890.4	890.6	891.3
162.5°	905.9	905.5	905.1	904.8	904.4	904.2	904.3	904.3	904.3	904.4	905.2
165°	924.3	924.0	923.7	923.3	923.0	922.9	923.1	923.2	923.4	923.6	924.2
167.5°	940.0	939.3	938.6	938.0	937.3	937.0	937.0	937.0	937.0	937.0	938.0
170°	948.4	947.7	947.0	946.3	945.6	945.3	945.3	945.3	945.3	945.3	946.3
172.5°	954.3	953.6	953.0	952.3	951.7	951.3	951.3	951.3	951.3	951.3	952.3
175°	961.1	960.4	959.8	959.1	958.4	958.1	958.1	958.1	958.1	958.1	959.1
177.5°	964.5	964.0	963.4	962.9	962.4	962.1	961.9	961.8	961.7	961.5	962.3
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333411-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	24.5	24.7	24.8	24.8	24.5	24.2	24.0	23.7
90°	13.6	14.5	15.3	16.0	16.5	17.0	17.5	18.0
92.5°	31.0	32.1	33.2	33.9	34.3	34.6	35.0	35.3
95°	60.1	61.2	62.4	63.1	63.5	63.8	64.1	64.4
97.5°	94.1	95.2	96.3	96.9	97.1	97.4	97.6	97.8
100°	117.6	119.2	120.7	121.6	122.0	122.3	122.6	122.9
102.5°	142.0	143.6	145.2	146.2	146.7	147.2	147.6	148.1
105°	181.2	182.2	183.2	183.9	184.4	184.9	185.4	185.9
107.5°	223.5	224.0	224.5	224.7	224.7	224.7	224.6	224.6
110°	252.9	253.4	253.9	254.1	253.9	253.7	253.6	253.4





TEST NUMBER: P333411-840

CATALOG NUMBER: S125DIW-S850D770U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	282.4	282.6	282.8	282.8	282.5	282.2	281.9	281.6
115°	327.3	327.1	326.9	326.8	326.6	326.5	326.3	326.1
117.5°	372.2	372.3	372.5	372.2	371.6	370.9	370.2	369.6
120°	402.5	402.5	402.5	402.2	401.6	400.9	400.2	399.6
122.5°	432.3	432.1	432.0	431.7	431.1	430.6	430.1	429.6
125°	476.2	475.7	475.4	475.2	475.0	474.8	474.7	474.5
127.5°	519.7	519.5	519.3	519.1	518.8	518.4	518.1	517.8
130°	548.5	548.3	548.1	547.9	547.5	547.1	546.8	546.5
132.5°	576.0	575.8	575.7	575.3	574.9	574.4	574.0	573.5
135°	618.4	618.4	618.4	618.1	617.4	616.8	616.1	615.5
137.5°	659.8	660.0	660.2	659.8	659.0	658.2	657.4	656.5
140°	685.9	686.2	686.5	686.3	685.5	684.6	683.8	683.0
142.5°	711.3	711.6	711.8	711.4	710.6	709.8	708.9	708.1
145°	748.2	748.2	748.2	747.9	747.4	746.9	746.4	745.9
147.5°	782.2	782.6	783.0	782.6	781.5	780.4	779.3	778.2
150°	803.7	803.7	803.7	803.4	803.1	802.8	802.4	802.1
152.5°	823.6	824.0	824.5	824.4	823.7	823.1	822.5	821.9
155°	852.2	852.8	853.5	853.4	852.6	851.8	850.9	850.1
157.5°	877.0	877.6	878.3	878.1	877.0	875.9	874.7	873.6
160°	891.9	892.6	893.2	893.2	892.3	891.5	890.7	889.9
162.5°	906.1	906.8	907.6	907.6	906.6	905.5	904.6	903.6
165°	924.9	925.6	926.2	926.0	925.1	924.1	923.1	922.1
167.5°	939.0	940.0	940.9	940.9	939.9	938.9	937.9	936.8
170°	947.4	948.4	949.4	949.3	948.1	947.0	945.7	944.6
172.5°	953.3	954.3	955.3	955.3	954.3	953.2	952.2	951.2
175°	960.1	961.1	962.1	962.0	960.8	959.7	958.5	957.4
177.5°	963.1	963.9	964.7	964.6	963.7	962.8	961.9	960.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3

(END OF REPORT)