

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333709-840

Luminaire Tested: **S125RDIW-S1090D1050U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333709-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7973.8 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	52	51	46
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29
5	70	58	50	45	65	55	48	42	48	42	38	41	37	33	35	31	29	26
6	64	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	23
7	60	48	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10723	10723	10723	10723
5°	12337	10738	9483	10738
10°	14152	10683	8368	10683
15°	15285	10573	7438	10573
20°	16855	10446	6868	10446
25°	19506	10278	6372	10278
30°	21227	10100	6049	10100
35°	17906	9894	5750	9894
40°	12505	9522	5493	9522
45°	9276	9020	5242	9020
50°	7396	8499	5027	8499
55°	6277	7851	4835	7851
60°	5424	7272	4525	7272
65°	4834	6645	3895	6645
70°	4247	6086	3552	6086
75°	3673	5273	3334	5273
80°	2786	4437	2786	4437
85°	2319	3490	2623	3490



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	2.0
10°-20°	466.6	5.9
20°-30°	739.8	9.3
30°-40°	892.2	11.2
40°-50°	796.7	10.0
50°-60°	611.0	7.7
60°-70°	397.1	5.0
70°-80°	193.0	2.4
80°-90°	49.0	0.6
90°-100°	88.1	1.1
100°-110°	260.1	3.3
110°-120°	440.5	5.5
120°-130°	579.7	7.3
130°-140°	649.6	8.1
140°-150°	636.6	8.0
150°-160°	534.7	6.7
160°-170°	355.4	4.5
170°-180°	124.4	1.6
0°-30°	1365.7	17.1
0°-40°	2257.9	28.3
0°-60°	3665.6	46.0
0°-90°	4304.6	54.0
90°-120°	788.6	9.9
90°-150°	2654.6	33.3
90°-180°	3669.0	46.0
0°-180°	7973.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1660	1660	1660	1660	1660	
5°	1903	1656	1463	1656	1903	190
15°	2286	1581	1112	1581	2286	655
25°	2737	1442	894	1442	2737	1257
35°	2271	1255	729	1255	2271	1372
45°	1016	988	574	988	1016	810
55°	558	697	429	697	558	506
65°	316	435	255	435	316	315
75°	147	211	134	211	147	157
85°	31	47	35	47	31	37
90°	24	1	24	1	24	16
95°	88	67	88	67	88	90
105°	254	233	254	233	254	269
115°	445	441	445	441	445	440
125°	648	644	648	644	648	578
135°	840	837	840	837	840	648
145°	1018	1014	1018	1014	1018	636
155°	1160	1160	1160	1160	1160	534
165°	1259	1262	1259	1262	1259	355
175°	1307	1312	1307	1312	1307	124
180°	1315	1315	1315	1315	1315	



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1746.6	1745.5	1747.7	1741.6	1742.2	1732.9	1732.9	1725.9	1716.6	1709.5	1706.2
5°	1903.0	1904.4	1901.7	1891.5	1884.6	1874.4	1862.8	1842.4	1825.3	1809.0	1796.0
7.5°	2064.2	2065.1	2056.1	2053.0	2035.8	2023.3	1997.5	1969.6	1945.0	1913.7	1889.7
10°	2158.0	2157.3	2147.7	2140.2	2125.3	2106.2	2080.9	2048.2	2017.5	1983.5	1950.8
12.5°	2212.5	2210.7	2207.7	2198.6	2184.6	2167.8	2146.4	2114.2	2076.4	2039.1	2000.9
15°	2286.1	2281.3	2272.5	2260.9	2241.1	2221.3	2197.5	2168.9	2132.7	2090.4	2055.1
17.5°	2377.1	2377.3	2363.7	2347.5	2320.7	2285.8	2249.0	2202.8	2153.7	2107.3	2069.5
20°	2452.4	2450.3	2436.7	2405.4	2374.7	2331.1	2288.9	2232.2	2172.2	2111.6	2064.6
22.5°	2560.4	2555.1	2540.8	2499.7	2452.2	2396.0	2331.4	2262.2	2189.7	2120.8	2059.1
25°	2737.3	2733.2	2705.2	2657.6	2590.8	2504.2	2419.6	2324.9	2220.7	2130.0	2055.1
27.5°	2858.3	2853.9	2833.2	2793.5	2731.9	2640.8	2526.4	2399.7	2269.6	2144.9	2036.8
30°	2846.4	2856.6	2853.9	2835.5	2789.1	2707.3	2601.7	2459.2	2304.5	2158.0	2029.1
32.5°	2675.1	2684.3	2708.3	2744.4	2747.1	2714.4	2635.4	2504.0	2343.8	2177.1	2023.2
35°	2271.1	2283.4	2329.8	2402.7	2498.1	2577.8	2594.1	2523.2	2379.4	2200.2	2014.2
37.5°	1746.0	1813.0	1852.1	1928.8	2073.1	2219.7	2360.8	2412.8	2351.5	2190.7	1999.5
40°	1483.2	1499.5	1569.0	1655.6	1777.0	1929.7	2130.7	2275.8	2280.7	2168.9	1976.6
42.5°	1269.4	1290.1	1337.9	1406.9	1510.9	1663.6	1871.2	2062.6	2151.4	2108.9	1946.6
45°	1015.6	1031.3	1066.0	1119.2	1198.9	1325.0	1503.6	1725.2	1901.0	1969.8	1866.2
47.5°	834.2	842.7	873.0	913.5	972.5	1064.4	1202.6	1394.9	1605.9	1753.7	1739.2
50°	736.1	745.7	768.8	799.5	849.3	927.0	1037.4	1197.6	1415.0	1595.6	1631.7
52.5°	659.7	667.7	682.2	711.1	752.2	811.9	901.1	1046.0	1241.6	1433.7	1517.2
55°	557.5	563.0	574.6	591.0	623.7	666.6	743.7	843.8	1002.0	1195.5	1318.2
57.5°	473.3	476.1	483.4	498.6	521.2	552.5	608.1	693.1	806.5	980.8	1116.2
60°	419.9	422.6	432.1	442.3	460.1	488.7	532.3	591.6	700.6	844.6	981.5
62.5°	377.3	379.0	383.0	393.2	408.8	430.9	465.2	513.6	600.4	726.7	856.1
65°	316.3	316.9	318.3	326.5	336.0	352.3	374.9	409.0	474.4	569.9	684.3
67.5°	257.6	258.6	263.4	266.2	276.2	284.8	298.0	324.1	370.1	434.4	523.5
70°	224.9	224.3	229.0	232.5	235.8	246.1	254.9	276.1	304.7	353.8	428.1
72.5°	194.4	192.6	194.7	195.9	200.4	207.3	216.2	229.1	251.3	285.1	341.9
75°	147.2	147.9	147.9	149.3	152.7	155.4	158.1	164.9	177.2	199.8	230.4
77.5°	103.3	102.2	105.1	105.5	107.6	110.6	112.9	115.6	120.7	129.9	145.7
80°	74.9	74.9	75.6	77.7	77.1	78.4	81.8	84.5	90.7	96.1	101.6
82.5°	57.6	57.0	57.7	58.1	58.0	59.3	60.5	61.1	63.4	66.1	69.9
85°	31.3	31.3	32.0	32.0	32.7	32.7	33.4	33.4	33.4	34.0	34.7
87.5°	16.9	16.3	15.6	15.5	15.9	16.8	16.0	15.1	14.9	14.7	14.9
90°	24.5	23.8	23.2	22.5	21.8	20.9	19.8	18.7	17.5	16.4	14.7
92.5°	48.3	47.8	47.3	46.8	46.3	45.3	43.8	42.3	40.8	39.3	37.4
95°	88.0	87.6	87.1	86.6	86.1	85.1	83.5	82.0	80.4	78.8	76.5
97.5°	133.4	133.2	132.9	132.6	132.3	131.5	130.0	128.5	126.9	125.4	122.3
100°	167.8	167.3	166.9	166.4	166.0	164.7	162.7	160.7	158.6	156.5	153.6
102.5°	202.2	201.6	201.0	200.3	199.7	198.2	196.0	193.8	191.6	189.3	187.8
105°	253.8	253.1	252.4	251.8	251.1	250.0	248.6	247.3	245.9	244.6	243.2
107.5°	306.6	306.6	306.7	306.7	306.8	306.4	305.8	305.1	304.4	303.7	302.7
110°	345.9	346.1	346.3	346.6	346.8	346.6	345.9	345.2	344.5	343.9	343.2



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	384.4	384.8	385.2	385.6	386.0	386.0	385.7	385.4	385.1	384.8	383.8
115°	445.1	445.4	445.6	445.8	446.1	446.3	446.5	446.7	447.0	447.2	446.7
117.5°	504.4	505.3	506.2	507.2	508.1	508.5	508.3	508.1	508.0	507.8	507.4
120°	545.4	546.3	547.2	548.2	549.1	549.5	549.5	549.5	549.5	549.5	549.3
122.5°	586.3	587.0	587.7	588.5	589.3	589.7	589.9	590.1	590.3	590.5	589.9
125°	647.7	647.9	648.1	648.4	648.6	648.9	649.4	649.8	650.4	650.8	650.6
127.5°	706.7	707.1	707.6	708.0	708.5	708.8	709.0	709.2	709.5	709.7	709.4
130°	746.0	746.4	746.9	747.3	747.8	748.1	748.3	748.6	748.8	749.0	748.6
132.5°	782.7	783.5	784.1	784.7	785.4	785.8	786.0	786.2	786.5	786.7	786.8
135°	840.1	841.0	841.9	842.8	843.7	844.1	844.1	844.1	844.1	844.1	843.9
137.5°	896.2	897.3	898.5	899.6	900.7	901.1	900.9	900.6	900.3	900.1	899.6
140°	932.2	933.3	934.4	935.6	936.8	937.1	936.6	936.1	935.7	935.2	934.5
142.5°	966.5	967.8	968.9	970.0	971.1	971.6	971.3	971.0	970.7	970.5	969.6
145°	1018.1	1018.9	1019.5	1020.2	1020.9	1021.2	1021.2	1021.2	1021.2	1021.2	1020.6
147.5°	1062.2	1063.7	1065.2	1066.8	1068.3	1068.8	1068.2	1067.7	1067.2	1066.6	1066.1
150°	1094.9	1095.3	1095.8	1096.2	1096.7	1096.9	1096.9	1096.9	1096.9	1096.9	1096.0
152.5°	1121.9	1122.7	1123.6	1124.4	1125.2	1125.3	1124.8	1124.2	1123.7	1123.2	1122.8
155°	1160.3	1161.5	1162.7	1163.8	1164.9	1165.1	1164.2	1163.3	1162.4	1161.4	1161.1
157.5°	1192.5	1194.0	1195.5	1197.0	1198.5	1198.8	1197.9	1197.0	1196.1	1195.2	1195.0
160°	1214.6	1215.8	1216.9	1218.0	1219.1	1219.3	1218.4	1217.5	1216.6	1215.7	1215.4
162.5°	1233.4	1234.8	1236.1	1237.4	1238.7	1238.8	1237.7	1236.7	1235.6	1234.5	1234.5
165°	1258.6	1260.0	1261.3	1262.7	1264.0	1264.3	1263.3	1262.4	1261.5	1260.6	1260.4
167.5°	1278.7	1280.1	1281.5	1282.9	1284.3	1284.3	1282.9	1281.6	1280.2	1278.9	1278.9
170°	1289.3	1290.9	1292.5	1294.0	1295.7	1295.8	1294.4	1293.0	1291.7	1290.3	1290.3
172.5°	1298.3	1299.7	1301.1	1302.5	1303.9	1303.9	1302.6	1301.2	1299.9	1298.5	1298.5
175°	1306.7	1308.3	1309.9	1311.5	1313.0	1313.2	1311.8	1310.4	1309.1	1307.7	1307.7
177.5°	1311.6	1312.9	1314.1	1315.5	1316.7	1316.8	1315.8	1314.6	1313.5	1312.4	1312.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1706.2	1702.3	1695.3	1688.7	1680.5	1673.4	1668.6	1662.5	1655.0	1645.7	1638.0
5°	1781.7	1766.7	1747.0	1729.9	1708.1	1691.0	1673.3	1656.3	1639.2	1617.4	1598.3
7.5°	1865.4	1834.4	1804.3	1766.5	1732.1	1701.4	1671.9	1642.1	1613.0	1582.0	1552.2
10°	1916.6	1879.2	1837.6	1789.9	1746.3	1704.7	1666.5	1629.0	1589.5	1554.7	1517.2
12.5°	1964.7	1916.2	1868.7	1808.5	1756.1	1705.3	1656.7	1609.9	1567.7	1522.6	1482.4
15°	2008.0	1960.2	1907.1	1833.5	1760.6	1699.2	1641.9	1581.3	1528.8	1478.3	1433.4
17.5°	2024.8	1974.7	1913.0	1842.2	1762.5	1685.4	1611.5	1545.1	1483.3	1424.5	1373.9
20°	2018.2	1969.8	1906.4	1839.0	1753.7	1673.3	1593.6	1519.9	1451.2	1389.1	1335.2
22.5°	2002.4	1952.4	1891.2	1819.9	1739.0	1653.7	1568.5	1490.0	1417.9	1353.6	1294.9
25°	1978.7	1910.6	1847.9	1778.3	1701.3	1616.8	1528.8	1442.3	1365.2	1299.8	1235.8
27.5°	1954.0	1869.0	1789.2	1720.1	1638.7	1563.3	1478.5	1389.8	1308.8	1242.1	1176.4
30°	1931.7	1836.2	1748.3	1669.9	1592.9	1521.4	1440.9	1354.3	1271.2	1202.3	1135.6
32.5°	1903.8	1802.4	1705.8	1615.4	1541.1	1470.1	1397.2	1314.5	1233.6	1162.6	1094.7
35°	1869.0	1739.5	1634.5	1538.3	1455.9	1387.0	1321.6	1254.9	1173.8	1100.1	1034.0
37.5°	1823.1	1676.2	1554.7	1450.1	1363.0	1293.9	1242.2	1181.2	1107.2	1036.7	975.3
40°	1795.3	1630.4	1497.4	1393.9	1302.5	1229.6	1181.2	1129.4	1062.0	995.8	934.4
42.5°	1758.3	1588.4	1439.7	1331.7	1239.8	1169.6	1120.6	1075.4	1018.9	956.5	890.8
45°	1685.6	1507.0	1350.9	1235.1	1142.4	1073.5	1027.8	987.6	944.7	887.5	830.2
47.5°	1590.9	1422.1	1258.8	1132.3	1041.5	977.5	933.2	901.5	870.8	822.1	766.5
50°	1515.2	1352.3	1192.8	1070.2	973.3	912.6	871.1	845.9	817.9	773.7	727.3
52.5°	1425.7	1280.3	1124.1	998.7	907.4	850.5	810.5	785.4	762.3	726.2	682.0
55°	1284.9	1157.4	1014.2	900.4	816.6	759.3	721.1	697.3	683.7	653.0	618.2
57.5°	1122.2	1030.9	904.6	794.9	720.7	664.2	636.2	615.9	600.5	578.9	554.3
60°	1008.8	944.7	831.5	727.3	659.1	605.2	580.1	563.0	548.7	530.3	511.2
62.5°	893.7	847.1	748.7	659.1	596.4	551.3	527.7	512.3	495.8	483.4	464.8
65°	739.5	697.9	629.8	559.6	501.7	465.5	448.5	434.8	424.6	411.0	398.1
67.5°	575.3	558.4	511.3	462.9	421.3	389.2	374.5	365.0	352.6	344.5	335.6
70°	474.4	466.3	432.8	400.8	361.9	340.1	326.5	322.3	307.4	299.2	293.1
72.5°	385.0	381.1	361.9	339.7	312.4	293.3	280.6	276.1	266.5	259.9	256.0
75°	263.8	265.2	261.8	247.4	237.2	224.9	214.0	211.3	204.5	199.0	195.6
77.5°	166.8	173.8	174.1	173.4	169.4	161.8	157.3	155.3	148.6	146.5	145.7
80°	114.5	122.0	128.9	128.2	126.7	124.7	121.3	119.3	115.8	113.8	112.5
82.5°	76.3	83.3	89.0	92.7	92.4	90.4	88.1	87.2	86.4	84.9	84.6
85°	36.2	37.5	39.5	44.3	47.7	48.4	47.7	47.1	44.9	45.6	46.4
87.5°	15.1	14.8	15.0	14.7	13.8	16.2	17.5	17.7	17.0	16.2	15.5
90°	13.2	11.6	10.0	8.3	6.5	4.6	2.8	1.0	2.8	4.6	6.5
92.5°	35.3	33.4	31.5	29.9	28.6	27.3	26.1	24.7	26.1	27.3	28.6
95°	74.2	72.0	69.7	68.4	67.9	67.5	67.0	66.6	67.0	67.5	67.9
97.5°	119.2	116.0	112.9	111.3	111.1	110.9	110.7	110.5	110.7	110.9	111.1
100°	150.7	147.6	144.7	143.3	143.3	143.3	143.3	143.3	143.3	143.3	143.3
102.5°	186.3	184.8	183.3	182.1	181.2	180.3	179.4	178.4	179.4	180.3	181.2
105°	241.9	240.4	239.1	237.8	236.7	235.6	234.4	233.3	234.4	235.6	236.7
107.5°	301.6	300.5	299.5	298.4	297.3	296.2	295.0	293.9	295.0	296.2	297.3
110°	342.4	341.7	341.1	340.2	339.0	337.9	336.8	335.6	336.8	337.9	339.0



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	383.0	382.1	381.3	380.5	380.0	379.4	378.8	378.2	378.8	379.4	380.0
115°	446.3	445.8	445.4	444.6	443.7	442.8	441.9	441.0	441.9	442.8	443.7
117.5°	507.0	506.5	506.1	505.7	505.2	504.8	504.4	504.0	504.4	504.8	505.2
120°	549.1	548.8	548.6	547.9	546.7	545.6	544.5	543.3	544.5	545.6	546.7
122.5°	589.3	588.7	588.0	587.5	587.1	586.7	586.3	585.9	586.3	586.7	587.1
125°	650.4	650.2	649.8	649.0	647.7	646.3	645.0	643.6	645.0	646.3	647.7
127.5°	709.2	708.9	708.6	708.1	707.3	706.6	705.8	705.0	705.8	706.6	707.3
130°	748.1	747.7	747.2	746.4	745.3	744.2	743.0	741.8	743.0	744.2	745.3
132.5°	786.9	787.0	787.1	786.2	784.3	782.4	780.5	778.7	780.5	782.4	784.3
135°	843.7	843.5	843.2	842.5	841.1	839.7	838.4	837.0	838.4	839.7	841.1
137.5°	899.1	898.6	898.1	897.2	895.9	894.5	893.2	891.9	893.2	894.5	895.9
140°	933.9	933.2	932.5	931.6	930.5	929.4	928.2	927.1	928.2	929.4	930.5
142.5°	968.8	967.9	967.0	966.1	965.1	964.2	963.2	962.3	963.2	964.2	965.1
145°	1019.9	1019.2	1018.4	1017.6	1016.7	1015.8	1014.9	1014.0	1014.9	1015.8	1016.7
147.5°	1065.5	1065.0	1064.5	1063.9	1063.4	1063.0	1062.5	1062.0	1062.5	1063.0	1063.4
150°	1095.1	1094.2	1093.3	1093.0	1093.2	1093.4	1093.7	1093.9	1093.7	1093.4	1093.2
152.5°	1122.4	1122.1	1121.7	1121.4	1121.1	1120.6	1120.3	1120.0	1120.3	1120.6	1121.1
155°	1160.9	1160.7	1160.4	1160.3	1160.3	1160.3	1160.3	1160.3	1160.3	1160.3	1160.3
157.5°	1194.7	1194.5	1194.3	1194.4	1194.9	1195.4	1195.9	1196.4	1195.9	1195.4	1194.9
160°	1215.2	1215.0	1214.8	1215.0	1215.7	1216.3	1217.0	1217.7	1217.0	1216.3	1215.7
162.5°	1234.4	1234.4	1234.3	1234.5	1235.0	1235.5	1236.0	1236.5	1236.0	1235.5	1235.0
165°	1260.2	1260.0	1259.7	1259.8	1260.3	1260.7	1261.2	1261.7	1261.2	1260.7	1260.3
167.5°	1278.9	1278.9	1278.9	1279.3	1280.2	1281.1	1282.0	1282.9	1282.0	1281.1	1280.2
170°	1290.3	1290.3	1290.3	1290.8	1291.7	1292.6	1293.5	1294.4	1293.5	1292.6	1291.7
172.5°	1298.5	1298.5	1298.5	1299.0	1299.9	1300.8	1301.7	1302.6	1301.7	1300.8	1299.9
175°	1307.7	1307.7	1307.7	1308.2	1309.1	1310.0	1310.9	1311.8	1310.9	1310.0	1309.1
177.5°	1312.8	1312.9	1313.1	1313.6	1314.3	1315.0	1315.8	1316.6	1315.8	1315.0	1314.3
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1632.5	1625.0	1619.5	1608.6	1600.9	1597.7	1591.6	1590.0	1596.0	1591.6	1591.1
5°	1584.1	1564.3	1548.6	1532.9	1515.9	1505.0	1488.6	1485.9	1481.8	1475.6	1474.3
7.5°	1525.8	1500.1	1479.9	1454.0	1431.5	1413.4	1392.9	1383.2	1378.0	1370.0	1359.4
10°	1486.5	1455.9	1428.7	1402.7	1374.8	1352.3	1331.8	1316.2	1306.0	1296.4	1292.3
12.5°	1447.8	1416.6	1381.7	1350.4	1319.2	1293.9	1271.3	1261.1	1249.8	1238.6	1229.1
15°	1387.8	1346.2	1308.0	1271.8	1245.3	1218.0	1196.2	1181.2	1164.2	1159.4	1141.0
17.5°	1323.9	1283.1	1238.5	1200.4	1169.6	1139.6	1115.6	1098.6	1085.8	1068.2	1059.8
20°	1284.1	1235.8	1192.1	1157.4	1123.3	1087.8	1063.3	1048.9	1036.7	1022.4	1015.6
22.5°	1241.6	1194.3	1149.6	1108.8	1074.2	1039.4	1021.9	1007.0	993.1	979.9	970.9
25°	1179.1	1131.5	1084.4	1042.2	1006.0	980.8	960.4	943.3	935.8	922.9	913.3
27.5°	1117.4	1066.7	1017.9	975.7	947.5	922.5	905.7	892.2	878.7	867.4	859.1
30°	1077.6	1025.8	972.6	939.3	909.3	885.3	867.0	854.0	843.8	833.6	827.5
32.5°	1037.8	984.4	937.2	901.1	872.7	852.1	833.1	820.8	810.0	798.7	791.4
35°	974.0	919.5	881.3	845.9	817.9	798.8	785.9	768.2	759.3	751.1	743.7
37.5°	914.7	864.0	822.7	791.6	767.3	748.4	731.6	722.1	711.1	703.8	697.5
40°	871.1	824.8	787.3	754.6	736.8	715.7	700.0	687.7	679.5	670.0	663.2
42.5°	831.8	788.7	752.3	722.9	700.8	683.0	667.8	655.6	645.2	638.4	632.7
45°	776.4	733.4	697.9	670.7	650.3	633.2	617.5	611.4	597.7	589.6	586.8
47.5°	718.9	680.5	646.3	621.2	600.3	584.1	569.4	556.8	549.4	541.3	536.9
50°	680.2	643.4	611.4	586.8	566.4	548.7	535.0	526.8	516.6	509.2	503.7
52.5°	641.6	607.4	575.4	552.0	534.2	516.5	501.3	493.1	483.4	478.6	474.8
55°	586.2	550.1	522.8	499.6	481.2	464.8	450.5	442.3	436.3	431.4	430.1
57.5°	523.5	494.8	469.5	448.6	429.5	414.1	401.6	393.8	388.4	387.7	383.6
60°	482.6	456.7	433.5	411.0	394.7	380.3	369.4	360.5	355.1	354.5	353.0
62.5°	441.7	416.9	395.4	375.6	360.8	347.1	336.7	326.8	323.5	320.1	317.1
65°	381.0	358.5	340.8	325.1	309.4	297.8	287.6	281.6	274.0	269.9	262.5
67.5°	321.4	304.0	287.0	273.8	261.5	250.4	242.0	232.9	227.8	224.5	219.0
70°	282.2	268.5	251.6	237.2	227.6	218.8	212.0	201.8	198.3	195.6	192.9
72.5°	245.1	233.1	218.8	207.2	197.6	189.3	181.5	176.6	173.3	170.6	169.0
75°	192.9	181.3	169.1	160.9	154.0	147.2	143.1	139.8	138.4	137.6	134.9
77.5°	141.7	135.5	125.7	119.2	114.6	111.9	108.3	106.4	106.3	103.3	102.4
80°	108.4	104.9	96.7	94.0	90.7	88.0	85.8	82.5	79.1	77.7	75.6
82.5°	80.6	77.2	73.9	69.5	66.7	65.0	63.0	61.7	62.2	60.3	59.3
85°	42.9	39.5	38.2	37.5	36.2	37.5	36.8	36.2	35.4	34.7	35.4
87.5°	15.2	15.7	15.5	16.9	15.5	16.4	16.6	16.3	16.5	16.8	16.4
90°	8.3	10.0	11.6	13.2	14.7	16.4	17.5	18.7	19.8	20.9	21.8
92.5°	29.9	31.5	33.4	35.3	37.4	39.3	40.8	42.3	43.8	45.3	46.3
95°	68.4	69.7	72.0	74.2	76.5	78.8	80.4	82.0	83.5	85.1	86.1
97.5°	111.3	112.9	116.0	119.2	122.3	125.4	126.9	128.5	130.0	131.5	132.3
100°	143.3	144.7	147.6	150.7	153.6	156.5	158.6	160.7	162.7	164.7	166.0
102.5°	182.1	183.3	184.8	186.3	187.8	189.3	191.6	193.8	196.0	198.2	199.7
105°	237.8	239.1	240.4	241.9	243.2	244.6	245.9	247.3	248.6	250.0	251.1
107.5°	298.4	299.5	300.5	301.6	302.7	303.7	304.4	305.1	305.8	306.4	306.8
110°	340.2	341.1	341.7	342.4	343.2	343.9	344.5	345.2	345.9	346.6	346.8



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	380.5	381.3	382.1	383.0	383.8	384.8	385.1	385.4	385.7	386.0	386.0
115°	444.6	445.4	445.8	446.3	446.7	447.2	447.0	446.7	446.5	446.3	446.1
117.5°	505.7	506.1	506.5	507.0	507.4	507.8	508.0	508.1	508.3	508.5	508.1
120°	547.9	548.6	548.8	549.1	549.3	549.5	549.5	549.5	549.5	549.5	549.1
122.5°	587.5	588.0	588.7	589.3	589.9	590.5	590.3	590.1	589.9	589.7	589.3
125°	649.0	649.8	650.2	650.4	650.6	650.8	650.4	649.8	649.4	648.9	648.6
127.5°	708.1	708.6	708.9	709.2	709.4	709.7	709.5	709.2	709.0	708.8	708.5
130°	746.4	747.2	747.7	748.1	748.6	749.0	748.8	748.6	748.3	748.1	747.8
132.5°	786.2	787.1	787.0	786.9	786.8	786.7	786.5	786.2	786.0	785.8	785.4
135°	842.5	843.2	843.5	843.7	843.9	844.1	844.1	844.1	844.1	844.1	843.7
137.5°	897.2	898.1	898.6	899.1	899.6	900.1	900.3	900.6	900.9	901.1	900.7
140°	931.6	932.5	933.2	933.9	934.5	935.2	935.7	936.1	936.6	937.1	936.8
142.5°	966.1	967.0	967.9	968.8	969.6	970.5	970.7	971.0	971.3	971.6	971.1
145°	1017.6	1018.4	1019.2	1019.9	1020.6	1021.2	1021.2	1021.2	1021.2	1021.2	1020.9
147.5°	1063.9	1064.5	1065.0	1065.5	1066.1	1066.6	1067.2	1067.7	1068.2	1068.8	1068.3
150°	1093.0	1093.3	1094.2	1095.1	1096.0	1096.9	1096.9	1096.9	1096.9	1096.9	1096.7
152.5°	1121.4	1121.7	1122.1	1122.4	1122.8	1123.2	1123.7	1124.2	1124.8	1125.3	1125.2
155°	1160.3	1160.4	1160.7	1160.9	1161.1	1161.4	1162.4	1163.3	1164.2	1165.1	1164.9
157.5°	1194.4	1194.3	1194.5	1194.7	1195.0	1195.2	1196.1	1197.0	1197.9	1198.8	1198.5
160°	1215.0	1214.8	1215.0	1215.2	1215.4	1215.7	1216.6	1217.5	1218.4	1219.3	1219.1
162.5°	1234.5	1234.3	1234.4	1234.4	1234.5	1234.5	1235.6	1236.7	1237.7	1238.8	1238.7
165°	1259.8	1259.7	1260.0	1260.2	1260.4	1260.6	1261.5	1262.4	1263.3	1264.3	1264.0
167.5°	1279.3	1278.9	1278.9	1278.9	1278.9	1278.9	1280.2	1281.6	1282.9	1284.3	1284.3
170°	1290.8	1290.3	1290.3	1290.3	1290.3	1290.3	1291.7	1293.0	1294.4	1295.8	1295.7
172.5°	1299.0	1298.5	1298.5	1298.5	1298.5	1298.5	1299.9	1301.2	1302.6	1303.9	1303.9
175°	1308.2	1307.7	1307.7	1307.7	1307.7	1307.7	1309.1	1310.4	1311.8	1313.2	1313.0
177.5°	1313.6	1313.1	1312.9	1312.8	1312.6	1312.4	1313.5	1314.6	1315.8	1316.8	1316.7
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1590.5	1584.6	1583.0	1585.1	1583.0	1584.6	1590.5	1591.1	1591.6	1596.0	1590.0
5°	1467.5	1460.7	1464.1	1462.7	1464.1	1460.7	1467.5	1474.3	1475.6	1481.8	1485.9
7.5°	1359.3	1350.8	1341.8	1344.6	1341.8	1350.8	1359.3	1359.4	1370.0	1378.0	1383.2
10°	1283.4	1276.7	1272.5	1276.0	1272.5	1276.7	1283.4	1292.3	1296.4	1306.0	1316.2
12.5°	1219.6	1215.6	1212.0	1210.5	1212.0	1215.6	1219.6	1229.1	1238.6	1249.8	1261.1
15°	1132.9	1124.7	1121.3	1112.4	1121.3	1124.7	1132.9	1141.0	1159.4	1164.2	1181.2
17.5°	1052.8	1050.1	1041.2	1037.4	1041.2	1050.1	1052.8	1059.8	1068.2	1085.8	1098.6
20°	1005.3	1002.6	993.8	999.3	993.8	1002.6	1005.3	1015.6	1022.4	1036.7	1048.9
22.5°	966.1	960.1	957.3	955.6	957.3	960.1	966.1	970.9	979.9	993.1	1007.0
25°	910.6	901.7	898.4	894.2	898.4	901.7	910.6	913.3	922.9	935.8	943.3
27.5°	855.3	850.5	846.0	845.0	846.0	850.5	855.3	859.1	867.4	878.7	892.2
30°	819.3	814.6	811.1	811.1	811.1	814.6	819.3	827.5	833.6	843.8	854.0
32.5°	787.1	783.5	780.0	779.5	780.0	783.5	787.1	791.4	798.7	810.0	820.8
35°	740.2	734.8	733.4	729.3	733.4	734.8	740.2	743.7	751.1	759.3	768.2
37.5°	691.6	687.0	686.9	686.5	686.9	687.0	691.6	697.5	703.8	711.1	722.1
40°	660.5	657.0	656.4	651.6	656.4	657.0	660.5	663.2	670.0	679.5	687.7
42.5°	627.2	625.4	623.1	621.1	623.1	625.4	627.2	632.7	638.4	645.2	655.6
45°	582.1	577.3	577.3	573.9	577.3	577.3	582.1	586.8	589.6	597.7	611.4
47.5°	535.4	531.8	532.2	528.7	532.2	531.8	535.4	536.9	541.3	549.4	556.8
50°	504.4	502.3	501.7	500.3	501.7	502.3	504.4	503.7	509.2	516.6	526.8
52.5°	473.3	472.3	474.9	471.9	474.9	472.3	473.3	474.8	478.6	483.4	493.1
55°	431.4	429.4	433.5	429.4	433.5	429.4	431.4	430.1	431.4	436.3	442.3
57.5°	383.3	381.4	385.1	383.0	385.1	381.4	383.3	383.6	387.7	388.4	393.8
60°	351.7	347.6	349.6	350.3	349.6	347.6	351.7	353.0	354.5	355.1	360.5
62.5°	314.1	311.6	313.2	310.0	313.2	311.6	314.1	317.1	320.1	323.5	326.8
65°	261.1	259.0	256.3	254.9	256.3	259.0	261.1	262.5	269.9	274.0	281.6
67.5°	219.3	214.4	214.3	215.4	214.3	214.4	219.3	219.0	224.5	227.8	232.9
70°	188.8	188.8	188.1	188.1	188.1	188.8	188.8	192.9	195.6	198.3	201.8
72.5°	167.5	167.0	165.7	165.2	165.7	167.0	167.5	169.0	170.6	173.3	176.6
75°	134.9	135.6	134.3	133.6	134.3	135.6	134.9	134.9	137.6	138.4	139.8
77.5°	99.7	96.7	98.3	96.7	98.3	96.7	99.7	102.4	103.3	106.3	106.4
80°	75.6	74.9	77.1	74.9	77.1	74.9	75.6	75.6	77.7	79.1	82.5
82.5°	59.9	59.2	60.1	58.6	60.1	59.2	59.9	59.3	60.3	62.2	61.7
85°	36.2	35.4	34.7	35.4	34.7	35.4	36.2	35.4	34.7	35.4	36.2
87.5°	17.1	16.7	16.8	16.9	16.8	16.7	17.1	16.4	16.8	16.5	16.3
90°	22.5	23.2	23.8	24.5	23.8	23.2	22.5	21.8	20.9	19.8	18.7
92.5°	46.8	47.3	47.8	48.3	47.8	47.3	46.8	46.3	45.3	43.8	42.3
95°	86.6	87.1	87.6	88.0	87.6	87.1	86.6	86.1	85.1	83.5	82.0
97.5°	132.6	132.9	133.2	133.4	133.2	132.9	132.6	132.3	131.5	130.0	128.5
100°	166.4	166.9	167.3	167.8	167.3	166.9	166.4	166.0	164.7	162.7	160.7
102.5°	200.3	201.0	201.6	202.2	201.6	201.0	200.3	199.7	198.2	196.0	193.8
105°	251.8	252.4	253.1	253.8	253.1	252.4	251.8	251.1	250.0	248.6	247.3
107.5°	306.7	306.7	306.6	306.6	306.6	306.7	306.7	306.8	306.4	305.8	305.1
110°	346.6	346.3	346.1	345.9	346.1	346.3	346.6	346.8	346.6	345.9	345.2



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	385.6	385.2	384.8	384.4	384.8	385.2	385.6	386.0	386.0	385.7	385.4
115°	445.8	445.6	445.4	445.1	445.4	445.6	445.8	446.1	446.3	446.5	446.7
117.5°	507.2	506.2	505.3	504.4	505.3	506.2	507.2	508.1	508.5	508.3	508.1
120°	548.2	547.2	546.3	545.4	546.3	547.2	548.2	549.1	549.5	549.5	549.5
122.5°	588.5	587.7	587.0	586.3	587.0	587.7	588.5	589.3	589.7	589.9	590.1
125°	648.4	648.1	647.9	647.7	647.9	648.1	648.4	648.6	648.9	649.4	649.8
127.5°	708.0	707.6	707.1	706.7	707.1	707.6	708.0	708.5	708.8	709.0	709.2
130°	747.3	746.9	746.4	746.0	746.4	746.9	747.3	747.8	748.1	748.3	748.6
132.5°	784.7	784.1	783.5	782.7	783.5	784.1	784.7	785.4	785.8	786.0	786.2
135°	842.8	841.9	841.0	840.1	841.0	841.9	842.8	843.7	844.1	844.1	844.1
137.5°	899.6	898.5	897.3	896.2	897.3	898.5	899.6	900.7	901.1	900.9	900.6
140°	935.6	934.4	933.3	932.2	933.3	934.4	935.6	936.8	937.1	936.6	936.1
142.5°	970.0	968.9	967.8	966.5	967.8	968.9	970.0	971.1	971.6	971.3	971.0
145°	1020.2	1019.5	1018.9	1018.1	1018.9	1019.5	1020.2	1020.9	1021.2	1021.2	1021.2
147.5°	1066.8	1065.2	1063.7	1062.2	1063.7	1065.2	1066.8	1068.3	1068.8	1068.2	1067.7
150°	1096.2	1095.8	1095.3	1094.9	1095.3	1095.8	1096.2	1096.7	1096.9	1096.9	1096.9
152.5°	1124.4	1123.6	1122.7	1121.9	1122.7	1123.6	1124.4	1125.2	1125.3	1124.8	1124.2
155°	1163.8	1162.7	1161.5	1160.3	1161.5	1162.7	1163.8	1164.9	1165.1	1164.2	1163.3
157.5°	1197.0	1195.5	1194.0	1192.5	1194.0	1195.5	1197.0	1198.5	1198.8	1197.9	1197.0
160°	1218.0	1216.9	1215.8	1214.6	1215.8	1216.9	1218.0	1219.1	1219.3	1218.4	1217.5
162.5°	1237.4	1236.1	1234.8	1233.4	1234.8	1236.1	1237.4	1238.7	1238.8	1237.7	1236.7
165°	1262.7	1261.3	1260.0	1258.6	1260.0	1261.3	1262.7	1264.0	1264.3	1263.3	1262.4
167.5°	1282.9	1281.5	1280.1	1278.7	1280.1	1281.5	1282.9	1284.3	1284.3	1282.9	1281.6
170°	1294.0	1292.5	1290.9	1289.3	1290.9	1292.5	1294.0	1295.7	1295.8	1294.4	1293.0
172.5°	1302.5	1301.1	1299.7	1298.3	1299.7	1301.1	1302.5	1303.9	1303.9	1302.6	1301.2
175°	1311.5	1309.9	1308.3	1306.7	1308.3	1309.9	1311.5	1313.0	1313.2	1311.8	1310.4
177.5°	1315.5	1314.1	1312.9	1311.6	1312.9	1314.1	1315.5	1316.7	1316.8	1315.8	1314.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1591.6	1597.7	1600.9	1608.6	1619.5	1625.0	1632.5	1638.0	1645.7	1655.0	1662.5
5°	1488.6	1505.0	1515.9	1532.9	1548.6	1564.3	1584.1	1598.3	1617.4	1639.2	1656.3
7.5°	1392.9	1413.4	1431.5	1454.0	1479.9	1500.1	1525.8	1552.2	1582.0	1613.0	1642.1
10°	1331.8	1352.3	1374.8	1402.7	1428.7	1455.9	1486.5	1517.2	1554.7	1589.5	1629.0
12.5°	1271.3	1293.9	1319.2	1350.4	1381.7	1416.6	1447.8	1482.4	1522.6	1567.7	1609.9
15°	1196.2	1218.0	1245.3	1271.8	1308.0	1346.2	1387.8	1433.4	1478.3	1528.8	1581.3
17.5°	1115.6	1139.6	1169.6	1200.4	1238.5	1283.1	1323.9	1373.9	1424.5	1483.3	1545.1
20°	1063.3	1087.8	1123.3	1157.4	1192.1	1235.8	1284.1	1335.2	1389.1	1451.2	1519.9
22.5°	1021.9	1039.4	1074.2	1108.8	1149.6	1194.3	1241.6	1294.9	1353.6	1417.9	1490.0
25°	960.4	980.8	1006.0	1042.2	1084.4	1131.5	1179.1	1235.8	1299.8	1365.2	1442.3
27.5°	905.7	922.5	947.5	975.7	1017.9	1066.7	1117.4	1176.4	1242.1	1308.8	1389.8
30°	867.0	885.3	909.3	939.3	972.6	1025.8	1077.6	1135.6	1202.3	1271.2	1354.3
32.5°	833.1	852.1	872.7	901.1	937.2	984.4	1037.8	1094.7	1162.6	1233.6	1314.5
35°	785.9	798.8	817.9	845.9	881.3	919.5	974.0	1034.0	1100.1	1173.8	1254.9
37.5°	731.6	748.4	767.3	791.6	822.7	864.0	914.7	975.3	1036.7	1107.2	1181.2
40°	700.0	715.7	736.8	754.6	787.3	824.8	871.1	934.4	995.8	1062.0	1129.4
42.5°	667.8	683.0	700.8	722.9	752.3	788.7	831.8	890.8	956.5	1018.9	1075.4
45°	617.5	633.2	650.3	670.7	697.9	733.4	776.4	830.2	887.5	944.7	987.6
47.5°	569.4	584.1	600.3	621.2	646.3	680.5	718.9	766.5	822.1	870.8	901.5
50°	535.0	548.7	566.4	586.8	611.4	643.4	680.2	727.3	773.7	817.9	845.9
52.5°	501.3	516.5	534.2	552.0	575.4	607.4	641.6	682.0	726.2	762.3	785.4
55°	450.5	464.8	481.2	499.6	522.8	550.1	586.2	618.2	653.0	683.7	697.3
57.5°	401.6	414.1	429.5	448.6	469.5	494.8	523.5	554.3	578.9	600.5	615.9
60°	369.4	380.3	394.7	411.0	433.5	456.7	482.6	511.2	530.3	548.7	563.0
62.5°	336.7	347.1	360.8	375.6	395.4	416.9	441.7	464.8	483.4	495.8	512.3
65°	287.6	297.8	309.4	325.1	340.8	358.5	381.0	398.1	411.0	424.6	434.8
67.5°	242.0	250.4	261.5	273.8	287.0	304.0	321.4	335.6	344.5	352.6	365.0
70°	212.0	218.8	227.6	237.2	251.6	268.5	282.2	293.1	299.2	307.4	322.3
72.5°	181.5	189.3	197.6	207.2	218.8	233.1	245.1	256.0	259.9	266.5	276.1
75°	143.1	147.2	154.0	160.9	169.1	181.3	192.9	195.6	199.0	204.5	211.3
77.5°	108.3	111.9	114.6	119.2	125.7	135.5	141.7	145.7	146.5	148.6	155.3
80°	85.8	88.0	90.7	94.0	96.7	104.9	108.4	112.5	113.8	115.8	119.3
82.5°	63.0	65.0	66.7	69.5	73.9	77.2	80.6	84.6	84.9	86.4	87.2
85°	36.8	37.5	36.2	37.5	38.2	39.5	42.9	46.4	45.6	44.9	47.1
87.5°	16.6	16.4	15.5	16.9	15.5	15.7	15.2	15.5	16.2	17.0	17.7
90°	17.5	16.4	14.7	13.2	11.6	10.0	8.3	6.5	4.6	2.8	1.0
92.5°	40.8	39.3	37.4	35.3	33.4	31.5	29.9	28.6	27.3	26.1	24.7
95°	80.4	78.8	76.5	74.2	72.0	69.7	68.4	67.9	67.5	67.0	66.6
97.5°	126.9	125.4	122.3	119.2	116.0	112.9	111.3	111.1	110.9	110.7	110.5
100°	158.6	156.5	153.6	150.7	147.6	144.7	143.3	143.3	143.3	143.3	143.3
102.5°	191.6	189.3	187.8	186.3	184.8	183.3	182.1	181.2	180.3	179.4	178.4
105°	245.9	244.6	243.2	241.9	240.4	239.1	237.8	236.7	235.6	234.4	233.3
107.5°	304.4	303.7	302.7	301.6	300.5	299.5	298.4	297.3	296.2	295.0	293.9
110°	344.5	343.9	343.2	342.4	341.7	341.1	340.2	339.0	337.9	336.8	335.6



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	385.1	384.8	383.8	383.0	382.1	381.3	380.5	380.0	379.4	378.8	378.2
115°	447.0	447.2	446.7	446.3	445.8	445.4	444.6	443.7	442.8	441.9	441.0
117.5°	508.0	507.8	507.4	507.0	506.5	506.1	505.7	505.2	504.8	504.4	504.0
120°	549.5	549.5	549.3	549.1	548.8	548.6	547.9	546.7	545.6	544.5	543.3
122.5°	590.3	590.5	589.9	589.3	588.7	588.0	587.5	587.1	586.7	586.3	585.9
125°	650.4	650.8	650.6	650.4	650.2	649.8	649.0	647.7	646.3	645.0	643.6
127.5°	709.5	709.7	709.4	709.2	708.9	708.6	708.1	707.3	706.6	705.8	705.0
130°	748.8	749.0	748.6	748.1	747.7	747.2	746.4	745.3	744.2	743.0	741.8
132.5°	786.5	786.7	786.8	786.9	787.0	787.1	786.2	784.3	782.4	780.5	778.7
135°	844.1	844.1	843.9	843.7	843.5	843.2	842.5	841.1	839.7	838.4	837.0
137.5°	900.3	900.1	899.6	899.1	898.6	898.1	897.2	895.9	894.5	893.2	891.9
140°	935.7	935.2	934.5	933.9	933.2	932.5	931.6	930.5	929.4	928.2	927.1
142.5°	970.7	970.5	969.6	968.8	967.9	967.0	966.1	965.1	964.2	963.2	962.3
145°	1021.2	1021.2	1020.6	1019.9	1019.2	1018.4	1017.6	1016.7	1015.8	1014.9	1014.0
147.5°	1067.2	1066.6	1066.1	1065.5	1065.0	1064.5	1063.9	1063.4	1063.0	1062.5	1062.0
150°	1096.9	1096.9	1096.0	1095.1	1094.2	1093.3	1093.0	1093.2	1093.4	1093.7	1093.9
152.5°	1123.7	1123.2	1122.8	1122.4	1122.1	1121.7	1121.4	1121.1	1120.6	1120.3	1120.0
155°	1162.4	1161.4	1161.1	1160.9	1160.7	1160.4	1160.3	1160.3	1160.3	1160.3	1160.3
157.5°	1196.1	1195.2	1195.0	1194.7	1194.5	1194.3	1194.4	1194.9	1195.4	1195.9	1196.4
160°	1216.6	1215.7	1215.4	1215.2	1215.0	1214.8	1215.0	1215.7	1216.3	1217.0	1217.7
162.5°	1235.6	1234.5	1234.5	1234.4	1234.4	1234.3	1234.5	1235.0	1235.5	1236.0	1236.5
165°	1261.5	1260.6	1260.4	1260.2	1260.0	1259.7	1259.8	1260.3	1260.7	1261.2	1261.7
167.5°	1280.2	1278.9	1278.9	1278.9	1278.9	1278.9	1279.3	1280.2	1281.1	1282.0	1282.9
170°	1291.7	1290.3	1290.3	1290.3	1290.3	1290.3	1290.8	1291.7	1292.6	1293.5	1294.4
172.5°	1299.9	1298.5	1298.5	1298.5	1298.5	1298.5	1299.0	1299.9	1300.8	1301.7	1302.6
175°	1309.1	1307.7	1307.7	1307.7	1307.7	1307.7	1308.2	1309.1	1310.0	1310.9	1311.8
177.5°	1313.5	1312.4	1312.6	1312.8	1312.9	1313.1	1313.6	1314.3	1315.0	1315.8	1316.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1668.6	1673.4	1680.5	1688.7	1695.3	1702.3	1706.2	1706.2	1709.5	1716.6	1725.9
5°	1673.3	1691.0	1708.1	1729.9	1747.0	1766.7	1781.7	1796.0	1809.0	1825.3	1842.4
7.5°	1671.9	1701.4	1732.1	1766.5	1804.3	1834.4	1865.4	1889.7	1913.7	1945.0	1969.6
10°	1666.5	1704.7	1746.3	1789.9	1837.6	1879.2	1916.6	1950.8	1983.5	2017.5	2048.2
12.5°	1656.7	1705.3	1756.1	1808.5	1868.7	1916.2	1964.7	2000.9	2039.1	2076.4	2114.2
15°	1641.9	1699.2	1760.6	1833.5	1907.1	1960.2	2008.0	2055.1	2090.4	2132.7	2168.9
17.5°	1611.5	1685.4	1762.5	1842.2	1913.0	1974.7	2024.8	2069.5	2107.3	2153.7	2202.8
20°	1593.6	1673.3	1753.7	1839.0	1906.4	1969.8	2018.2	2064.6	2111.6	2172.2	2232.2
22.5°	1568.5	1653.7	1739.0	1819.9	1891.2	1952.4	2002.4	2059.1	2120.8	2189.7	2262.2
25°	1528.8	1616.8	1701.3	1778.3	1847.9	1910.6	1978.7	2055.1	2130.0	2220.7	2324.9
27.5°	1478.5	1563.3	1638.7	1720.1	1789.2	1869.0	1954.0	2036.8	2144.9	2269.6	2399.7
30°	1440.9	1521.4	1592.9	1669.9	1748.3	1836.2	1931.7	2029.1	2158.0	2304.5	2459.2
32.5°	1397.2	1470.1	1541.1	1615.4	1705.8	1802.4	1903.8	2023.2	2177.1	2343.8	2504.0
35°	1321.6	1387.0	1455.9	1538.3	1634.5	1739.5	1869.0	2014.2	2200.2	2379.4	2523.2
37.5°	1242.2	1293.9	1363.0	1450.1	1554.7	1676.2	1823.1	1999.5	2190.7	2351.5	2412.8
40°	1181.2	1229.6	1302.5	1393.9	1497.4	1630.4	1795.3	1976.6	2168.9	2280.7	2275.8
42.5°	1120.6	1169.6	1239.8	1331.7	1439.7	1588.4	1758.3	1946.6	2108.9	2151.4	2062.6
45°	1027.8	1073.5	1142.4	1235.1	1350.9	1507.0	1685.6	1866.2	1969.8	1901.0	1725.2
47.5°	933.2	977.5	1041.5	1132.3	1258.8	1422.1	1590.9	1739.2	1753.7	1605.9	1394.9
50°	871.1	912.6	973.3	1070.2	1192.8	1352.3	1515.2	1631.7	1595.6	1415.0	1197.6
52.5°	810.5	850.5	907.4	998.7	1124.1	1280.3	1425.7	1517.2	1433.7	1241.6	1046.0
55°	721.1	759.3	816.6	900.4	1014.2	1157.4	1284.9	1318.2	1195.5	1002.0	843.8
57.5°	636.2	664.2	720.7	794.9	904.6	1030.9	1122.2	1116.2	980.8	806.5	693.1
60°	580.1	605.2	659.1	727.3	831.5	944.7	1008.8	981.5	844.6	700.6	591.6
62.5°	527.7	551.3	596.4	659.1	748.7	847.1	893.7	856.1	726.7	600.4	513.6
65°	448.5	465.5	501.7	559.6	629.8	697.9	739.5	684.3	569.9	474.4	409.0
67.5°	374.5	389.2	421.3	462.9	511.3	558.4	575.3	523.5	434.4	370.1	324.1
70°	326.5	340.1	361.9	400.8	432.8	466.3	474.4	428.1	353.8	304.7	276.1
72.5°	280.6	293.3	312.4	339.7	361.9	381.1	385.0	341.9	285.1	251.3	229.1
75°	214.0	224.9	237.2	247.4	261.8	265.2	263.8	230.4	199.8	177.2	164.9
77.5°	157.3	161.8	169.4	173.4	174.1	173.8	166.8	145.7	129.9	120.7	115.6
80°	121.3	124.7	126.7	128.2	128.9	122.0	114.5	101.6	96.1	90.7	84.5
82.5°	88.1	90.4	92.4	92.7	89.0	83.3	76.3	69.9	66.1	63.4	61.1
85°	47.7	48.4	47.7	44.3	39.5	37.5	36.2	34.7	34.0	33.4	33.4
87.5°	17.5	16.2	13.8	14.7	15.0	14.8	15.1	14.9	14.7	14.9	15.1
90°	2.8	4.6	6.5	8.3	10.0	11.6	13.2	14.7	16.4	17.5	18.7
92.5°	26.1	27.3	28.6	29.9	31.5	33.4	35.3	37.4	39.3	40.8	42.3
95°	67.0	67.5	67.9	68.4	69.7	72.0	74.2	76.5	78.8	80.4	82.0
97.5°	110.7	110.9	111.1	111.3	112.9	116.0	119.2	122.3	125.4	126.9	128.5
100°	143.3	143.3	143.3	143.3	144.7	147.6	150.7	153.6	156.5	158.6	160.7
102.5°	179.4	180.3	181.2	182.1	183.3	184.8	186.3	187.8	189.3	191.6	193.8
105°	234.4	235.6	236.7	237.8	239.1	240.4	241.9	243.2	244.6	245.9	247.3
107.5°	295.0	296.2	297.3	298.4	299.5	300.5	301.6	302.7	303.7	304.4	305.1
110°	336.8	337.9	339.0	340.2	341.1	341.7	342.4	343.2	343.9	344.5	345.2



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	378.8	379.4	380.0	380.5	381.3	382.1	383.0	383.8	384.8	385.1	385.4
115°	441.9	442.8	443.7	444.6	445.4	445.8	446.3	446.7	447.2	447.0	446.7
117.5°	504.4	504.8	505.2	505.7	506.1	506.5	507.0	507.4	507.8	508.0	508.1
120°	544.5	545.6	546.7	547.9	548.6	548.8	549.1	549.3	549.5	549.5	549.5
122.5°	586.3	586.7	587.1	587.5	588.0	588.7	589.3	589.9	590.5	590.3	590.1
125°	645.0	646.3	647.7	649.0	649.8	650.2	650.4	650.6	650.8	650.4	649.8
127.5°	705.8	706.6	707.3	708.1	708.6	708.9	709.2	709.4	709.7	709.5	709.2
130°	743.0	744.2	745.3	746.4	747.2	747.7	748.1	748.6	749.0	748.8	748.6
132.5°	780.5	782.4	784.3	786.2	787.1	787.0	786.9	786.8	786.7	786.5	786.2
135°	838.4	839.7	841.1	842.5	843.2	843.5	843.7	843.9	844.1	844.1	844.1
137.5°	893.2	894.5	895.9	897.2	898.1	898.6	899.1	899.6	900.1	900.3	900.6
140°	928.2	929.4	930.5	931.6	932.5	933.2	933.9	934.5	935.2	935.7	936.1
142.5°	963.2	964.2	965.1	966.1	967.0	967.9	968.8	969.6	970.5	970.7	971.0
145°	1014.9	1015.8	1016.7	1017.6	1018.4	1019.2	1019.9	1020.6	1021.2	1021.2	1021.2
147.5°	1062.5	1063.0	1063.4	1063.9	1064.5	1065.0	1065.5	1066.1	1066.6	1067.2	1067.7
150°	1093.7	1093.4	1093.2	1093.0	1093.3	1094.2	1095.1	1096.0	1096.9	1096.9	1096.9
152.5°	1120.3	1120.6	1121.1	1121.4	1121.7	1122.1	1122.4	1122.8	1123.2	1123.7	1124.2
155°	1160.3	1160.3	1160.3	1160.3	1160.4	1160.7	1160.9	1161.1	1161.4	1162.4	1163.3
157.5°	1195.9	1195.4	1194.9	1194.4	1194.3	1194.5	1194.7	1195.0	1195.2	1196.1	1197.0
160°	1217.0	1216.3	1215.7	1215.0	1214.8	1215.0	1215.2	1215.4	1215.7	1216.6	1217.5
162.5°	1236.0	1235.5	1235.0	1234.5	1234.3	1234.4	1234.4	1234.5	1234.5	1235.6	1236.7
165°	1261.2	1260.7	1260.3	1259.8	1259.7	1260.0	1260.2	1260.4	1260.6	1261.5	1262.4
167.5°	1282.0	1281.1	1280.2	1279.3	1278.9	1278.9	1278.9	1278.9	1278.9	1280.2	1281.6
170°	1293.5	1292.6	1291.7	1290.8	1290.3	1290.3	1290.3	1290.3	1290.3	1291.7	1293.0
172.5°	1301.7	1300.8	1299.9	1299.0	1298.5	1298.5	1298.5	1298.5	1298.5	1299.9	1301.2
175°	1310.9	1310.0	1309.1	1308.2	1307.7	1307.7	1307.7	1307.7	1307.7	1309.1	1310.4
177.5°	1315.8	1315.0	1314.3	1313.6	1313.1	1312.9	1312.8	1312.6	1312.4	1313.5	1314.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1732.9	1732.9	1742.2	1741.6	1747.7	1745.5	1746.6
5°	1862.8	1874.4	1884.6	1891.5	1901.7	1904.4	1903.0
7.5°	1997.5	2023.3	2035.8	2053.0	2056.1	2065.1	2064.2
10°	2080.9	2106.2	2125.3	2140.2	2147.7	2157.3	2158.0
12.5°	2146.4	2167.8	2184.6	2198.6	2207.7	2210.7	2212.5
15°	2197.5	2221.3	2241.1	2260.9	2272.5	2281.3	2286.1
17.5°	2249.0	2285.8	2320.7	2347.5	2363.7	2377.3	2377.1
20°	2288.9	2331.1	2374.7	2405.4	2436.7	2450.3	2452.4
22.5°	2331.4	2396.0	2452.2	2499.7	2540.8	2555.1	2560.4
25°	2419.6	2504.2	2590.8	2657.6	2705.2	2733.2	2737.3
27.5°	2526.4	2640.8	2731.9	2793.5	2833.2	2853.9	2858.3
30°	2601.7	2707.3	2789.1	2835.5	2853.9	2856.6	2846.4
32.5°	2635.4	2714.4	2747.1	2744.4	2708.3	2684.3	2675.1
35°	2594.1	2577.8	2498.1	2402.7	2329.8	2283.4	2271.1
37.5°	2360.8	2219.7	2073.1	1928.8	1852.1	1813.0	1746.0
40°	2130.7	1929.7	1777.0	1655.6	1569.0	1499.5	1483.2
42.5°	1871.2	1663.6	1510.9	1406.9	1337.9	1290.1	1269.4
45°	1503.6	1325.0	1198.9	1119.2	1066.0	1031.3	1015.6
47.5°	1202.6	1064.4	972.5	913.5	873.0	842.7	834.2
50°	1037.4	927.0	849.3	799.5	768.8	745.7	736.1
52.5°	901.1	811.9	752.2	711.1	682.2	667.7	659.7
55°	743.7	666.6	623.7	591.0	574.6	563.0	557.5
57.5°	608.1	552.5	521.2	498.6	483.4	476.1	473.3
60°	532.3	488.7	460.1	442.3	432.1	422.6	419.9
62.5°	465.2	430.9	408.8	393.2	383.0	379.0	377.3
65°	374.9	352.3	336.0	326.5	318.3	316.9	316.3
67.5°	298.0	284.8	276.2	266.2	263.4	258.6	257.6
70°	254.9	246.1	235.8	232.5	229.0	224.3	224.9
72.5°	216.2	207.3	200.4	195.9	194.7	192.6	194.4
75°	158.1	155.4	152.7	149.3	147.9	147.9	147.2
77.5°	112.9	110.6	107.6	105.5	105.1	102.2	103.3
80°	81.8	78.4	77.1	77.7	75.6	74.9	74.9
82.5°	60.5	59.3	58.0	58.1	57.7	57.0	57.6
85°	33.4	32.7	32.7	32.0	32.0	31.3	31.3
87.5°	16.0	16.8	15.9	15.5	15.6	16.3	16.9
90°	19.8	20.9	21.8	22.5	23.2	23.8	24.5
92.5°	43.8	45.3	46.3	46.8	47.3	47.8	48.3
95°	83.5	85.1	86.1	86.6	87.1	87.6	88.0
97.5°	130.0	131.5	132.3	132.6	132.9	133.2	133.4
100°	162.7	164.7	166.0	166.4	166.9	167.3	167.8
102.5°	196.0	198.2	199.7	200.3	201.0	201.6	202.2
105°	248.6	250.0	251.1	251.8	252.4	253.1	253.8
107.5°	305.8	306.4	306.8	306.7	306.7	306.6	306.6
110°	345.9	346.6	346.8	346.6	346.3	346.1	345.9



TEST NUMBER: P333709-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	385.7	386.0	386.0	385.6	385.2	384.8	384.4
115°	446.5	446.3	446.1	445.8	445.6	445.4	445.1
117.5°	508.3	508.5	508.1	507.2	506.2	505.3	504.4
120°	549.5	549.5	549.1	548.2	547.2	546.3	545.4
122.5°	589.9	589.7	589.3	588.5	587.7	587.0	586.3
125°	649.4	648.9	648.6	648.4	648.1	647.9	647.7
127.5°	709.0	708.8	708.5	708.0	707.6	707.1	706.7
130°	748.3	748.1	747.8	747.3	746.9	746.4	746.0
132.5°	786.0	785.8	785.4	784.7	784.1	783.5	782.7
135°	844.1	844.1	843.7	842.8	841.9	841.0	840.1
137.5°	900.9	901.1	900.7	899.6	898.5	897.3	896.2
140°	936.6	937.1	936.8	935.6	934.4	933.3	932.2
142.5°	971.3	971.6	971.1	970.0	968.9	967.8	966.5
145°	1021.2	1021.2	1020.9	1020.2	1019.5	1018.9	1018.1
147.5°	1068.2	1068.8	1068.3	1066.8	1065.2	1063.7	1062.2
150°	1096.9	1096.9	1096.7	1096.2	1095.8	1095.3	1094.9
152.5°	1124.8	1125.3	1125.2	1124.4	1123.6	1122.7	1121.9
155°	1164.2	1165.1	1164.9	1163.8	1162.7	1161.5	1160.3
157.5°	1197.9	1198.8	1198.5	1197.0	1195.5	1194.0	1192.5
160°	1218.4	1219.3	1219.1	1218.0	1216.9	1215.8	1214.6
162.5°	1237.7	1238.8	1238.7	1237.4	1236.1	1234.8	1233.4
165°	1263.3	1264.3	1264.0	1262.7	1261.3	1260.0	1258.6
167.5°	1282.9	1284.3	1284.3	1282.9	1281.5	1280.1	1278.7
170°	1294.4	1295.8	1295.7	1294.0	1292.5	1290.9	1289.3
172.5°	1302.6	1303.9	1303.9	1302.5	1301.1	1299.7	1298.3
175°	1311.8	1313.2	1313.0	1311.5	1309.9	1308.3	1306.7
177.5°	1315.8	1316.8	1316.7	1315.5	1314.1	1312.9	1311.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8

(END OF REPORT)