

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333711-840

Luminaire Tested: **S125RDIW-S1090D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333711-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7936.2 lumens  
Efficiency: N/A  
Efficacy: 129.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333711-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333711-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333711-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.7	2.1
10°-20°	474.3	6.0
20°-30°	687.8	8.7
30°-40°	783.9	9.9
40°-50°	764.1	9.6
50°-60°	643.2	8.1
60°-70°	450.9	5.7
70°-80°	231.8	2.9
80°-90°	61.4	0.8
90°-100°	88.1	1.1
100°-110°	260.1	3.3
110°-120°	440.5	5.6
120°-130°	579.7	7.3
130°-140°	649.6	8.2
140°-150°	636.6	8.0
150°-160°	534.7	6.7
160°-170°	355.4	4.5
170°-180°	124.4	1.6
0°-30°	1331.9	16.8
0°-40°	2115.8	26.7
0°-60°	3523.1	44.4
0°-90°	4267.1	53.8
90°-120°	788.6	9.9
90°-150°	2654.6	33.4
90°-180°	3669.0	46.2
0°-180°	7936.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	1	9	16	21	24	7
95°	67	69	79	86	88	71
105°	233	238	245	251	254	249
115°	441	445	447	446	445	436
125°	644	649	651	649	648	576
135°	837	843	844	844	840	645
145°	1014	1018	1021	1021	1018	634
155°	1160	1160	1161	1165	1160	534
165°	1262	1260	1261	1264	1259	356
175°	1312	1308	1308	1313	1307	125
180°	1315	1315	1315	1315	1315	



TEST NUMBER: P333711-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.2	23.9	22.6	21.3	20.0	19.3	19.4	19.5	19.6	19.6	19.9
90°	1.0	2.8	4.6	6.5	8.3	10.0	11.6	13.2	14.7	16.4	17.5
92.5°	24.7	26.1	27.3	28.6	29.9	31.5	33.4	35.3	37.4	39.3	40.8
95°	66.6	67.0	67.5	67.9	68.4	69.7	72.0	74.2	76.5	78.8	80.4
97.5°	110.5	110.7	110.9	111.1	111.3	112.9	116.0	119.2	122.3	125.4	126.9
100°	143.3	143.3	143.3	143.3	143.3	144.7	147.6	150.7	153.6	156.5	158.6
102.5°	178.4	179.4	180.3	181.2	182.1	183.3	184.8	186.3	187.8	189.3	191.6
105°	233.3	234.4	235.6	236.7	237.8	239.1	240.4	241.9	243.2	244.6	245.9
107.5°	293.9	295.0	296.2	297.3	298.4	299.5	300.5	301.6	302.7	303.7	304.4
110°	335.6	336.8	337.9	339.0	340.2	341.1	341.7	342.4	343.2	343.9	344.5



TEST NUMBER: P333711-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.2	378.8	379.4	380.0	380.5	381.3	382.1	383.0	383.8	384.8	385.1
115°	441.0	441.9	442.8	443.7	444.6	445.4	445.8	446.3	446.7	447.2	447.0
117.5°	504.0	504.4	504.8	505.2	505.7	506.1	506.5	507.0	507.4	507.8	508.0
120°	543.3	544.5	545.6	546.7	547.9	548.6	548.8	549.1	549.3	549.5	549.5
122.5°	585.9	586.3	586.7	587.1	587.5	588.0	588.7	589.3	589.9	590.5	590.3
125°	643.6	645.0	646.3	647.7	649.0	649.8	650.2	650.4	650.6	650.8	650.4
127.5°	705.0	705.8	706.6	707.3	708.1	708.6	708.9	709.2	709.4	709.7	709.5
130°	741.8	743.0	744.2	745.3	746.4	747.2	747.7	748.1	748.6	749.0	748.8
132.5°	778.7	780.5	782.4	784.3	786.2	787.1	787.0	786.9	786.8	786.7	786.5
135°	837.0	838.4	839.7	841.1	842.5	843.2	843.5	843.7	843.9	844.1	844.1
137.5°	891.9	893.2	894.5	895.9	897.2	898.1	898.6	899.1	899.6	900.1	900.3
140°	927.1	928.2	929.4	930.5	931.6	932.5	933.2	933.9	934.5	935.2	935.7
142.5°	962.3	963.2	964.2	965.1	966.1	967.0	967.9	968.8	969.6	970.5	970.7
145°	1014.0	1014.9	1015.8	1016.7	1017.6	1018.4	1019.2	1019.9	1020.6	1021.2	1021.2
147.5°	1062.0	1062.5	1063.0	1063.4	1063.9	1064.5	1065.0	1065.5	1066.1	1066.6	1067.2
150°	1093.9	1093.7	1093.4	1093.2	1093.0	1093.3	1094.2	1095.1	1096.0	1096.9	1096.9
152.5°	1120.0	1120.3	1120.6	1121.1	1121.4	1121.7	1122.1	1122.4	1122.8	1123.2	1123.7
155°	1160.3	1160.3	1160.3	1160.3	1160.3	1160.4	1160.7	1160.9	1161.1	1161.4	1162.4
157.5°	1196.4	1195.9	1195.4	1194.9	1194.4	1194.3	1194.5	1194.7	1195.0	1195.2	1196.1
160°	1217.7	1217.0	1216.3	1215.7	1215.0	1214.8	1215.0	1215.2	1215.4	1215.7	1216.6
162.5°	1236.5	1236.0	1235.5	1235.0	1234.5	1234.3	1234.4	1234.4	1234.5	1234.5	1235.6
165°	1261.7	1261.2	1260.7	1260.3	1259.8	1259.7	1260.0	1260.2	1260.4	1260.6	1261.5
167.5°	1282.9	1282.0	1281.1	1280.2	1279.3	1278.9	1278.9	1278.9	1278.9	1278.9	1280.2
170°	1294.4	1293.5	1292.6	1291.7	1290.8	1290.3	1290.3	1290.3	1290.3	1290.3	1291.7
172.5°	1302.6	1301.7	1300.8	1299.9	1299.0	1298.5	1298.5	1298.5	1298.5	1298.5	1299.9
175°	1311.8	1310.9	1310.0	1309.1	1308.2	1307.7	1307.7	1307.7	1307.7	1307.7	1309.1
177.5°	1316.6	1315.8	1315.0	1314.3	1313.6	1313.1	1312.9	1312.8	1312.6	1312.4	1313.5
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333711-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	20.1	20.3	20.5	20.6	20.5	20.4	20.3	20.2
90°	18.7	19.8	20.9	21.8	22.5	23.2	23.8	24.5
92.5°	42.3	43.8	45.3	46.3	46.8	47.3	47.8	48.3
95°	82.0	83.5	85.1	86.1	86.6	87.1	87.6	88.0
97.5°	128.5	130.0	131.5	132.3	132.6	132.9	133.2	133.4
100°	160.7	162.7	164.7	166.0	166.4	166.9	167.3	167.8
102.5°	193.8	196.0	198.2	199.7	200.3	201.0	201.6	202.2
105°	247.3	248.6	250.0	251.1	251.8	252.4	253.1	253.8
107.5°	305.1	305.8	306.4	306.8	306.7	306.7	306.6	306.6
110°	345.2	345.9	346.6	346.8	346.6	346.3	346.1	345.9





TEST NUMBER: P333711-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	385.4	385.7	386.0	386.0	385.6	385.2	384.8	384.4
115°	446.7	446.5	446.3	446.1	445.8	445.6	445.4	445.1
117.5°	508.1	508.3	508.5	508.1	507.2	506.2	505.3	504.4
120°	549.5	549.5	549.5	549.1	548.2	547.2	546.3	545.4
122.5°	590.1	589.9	589.7	589.3	588.5	587.7	587.0	586.3
125°	649.8	649.4	648.9	648.6	648.4	648.1	647.9	647.7
127.5°	709.2	709.0	708.8	708.5	708.0	707.6	707.1	706.7
130°	748.6	748.3	748.1	747.8	747.3	746.9	746.4	746.0
132.5°	786.2	786.0	785.8	785.4	784.7	784.1	783.5	782.7
135°	844.1	844.1	844.1	843.7	842.8	841.9	841.0	840.1
137.5°	900.6	900.9	901.1	900.7	899.6	898.5	897.3	896.2
140°	936.1	936.6	937.1	936.8	935.6	934.4	933.3	932.2
142.5°	971.0	971.3	971.6	971.1	970.0	968.9	967.8	966.5
145°	1021.2	1021.2	1021.2	1020.9	1020.2	1019.5	1018.9	1018.1
147.5°	1067.7	1068.2	1068.8	1068.3	1066.8	1065.2	1063.7	1062.2
150°	1096.9	1096.9	1096.9	1096.7	1096.2	1095.8	1095.3	1094.9
152.5°	1124.2	1124.8	1125.3	1125.2	1124.4	1123.6	1122.7	1121.9
155°	1163.3	1164.2	1165.1	1164.9	1163.8	1162.7	1161.5	1160.3
157.5°	1197.0	1197.9	1198.8	1198.5	1197.0	1195.5	1194.0	1192.5
160°	1217.5	1218.4	1219.3	1219.1	1218.0	1216.9	1215.8	1214.6
162.5°	1236.7	1237.7	1238.8	1238.7	1237.4	1236.1	1234.8	1233.4
165°	1262.4	1263.3	1264.3	1264.0	1262.7	1261.3	1260.0	1258.6
167.5°	1281.6	1282.9	1284.3	1284.3	1282.9	1281.5	1280.1	1278.7
170°	1293.0	1294.4	1295.8	1295.7	1294.0	1292.5	1290.9	1289.3
172.5°	1301.2	1302.6	1303.9	1303.9	1302.5	1301.1	1299.7	1298.3
175°	1310.4	1311.8	1313.2	1313.0	1311.5	1309.9	1308.3	1306.7
177.5°	1314.6	1315.8	1316.8	1316.7	1315.5	1314.1	1312.9	1311.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8

(END OF REPORT)