

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333739-840

Luminaire Tested: **S125RDIW-S1270D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333739-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10390.3 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333739-840

CATALOG NUMBER: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333739-840

CATALOG NUMBER: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47					47			
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46					40				
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39					34				
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33					29				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29					25				
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25					22				
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22					19				
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20					17				
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18					15				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16					14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15					13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13464	13464	13464
5°	13494	13341	13422
10°	13392	13217	13217
15°	13233	12948	12843
20°	13029	12575	12423
25°	12790	12207	11938
30°	12493	11777	11401
35°	12191	11334	10800
40°	11907	10871	10208
45°	11562	10355	9563
50°	11216	9792	8890
55°	10815	9254	8173
60°	10413	8603	7403
65°	9938	7844	6521
70°	9396	6898	5620
75°	8644	5814	4674
80°	7613	4567	3924
85°	6417	3735	3505



TEST NUMBER: P333739-840

CATALOG NUMBER: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	1.9
10°-20°	547.8	5.3
20°-30°	794.4	7.6
30°-40°	905.3	8.7
40°-50°	882.5	8.5
50°-60°	742.8	7.1
60°-70°	520.7	5.0
70°-80°	267.7	2.6
80°-90°	71.9	0.7
90°-100°	131.1	1.3
100°-110°	387.1	3.7
110°-120°	655.6	6.3
120°-130°	862.9	8.3
130°-140°	966.8	9.3
140°-150°	947.6	9.1
150°-160°	795.9	7.7
160°-170°	529.1	5.1
170°-180°	185.2	1.8
0°-30°	1538.2	14.8
0°-40°	2443.5	23.5
0°-60°	4068.9	39.2
0°-90°	4929.1	47.4
90°-120°	1173.8	11.3
90°-150°	3951.1	38.0
90°-180°	5461.0	52.6
0°-180°	10390.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2058	2073	2070	197
15°	1979	1968	1937	1934	1921	558
25°	1795	1769	1713	1693	1675	826
35°	1546	1507	1438	1393	1370	968
45°	1266	1218	1134	1073	1047	976
55°	960	908	822	754	726	859
65°	650	595	513	452	427	644
75°	346	298	233	200	187	367
85°	87	59	50	49	47	97
90°	2	14	24	32	37	9
95°	99	103	117	128	131	106
105°	347	355	364	373	378	371
115°	656	662	666	664	663	649
125°	958	967	969	966	964	858
135°	1246	1255	1256	1256	1250	960
145°	1509	1515	1520	1520	1515	943
155°	1727	1727	1729	1734	1727	795
165°	1878	1875	1876	1882	1873	530
175°	1953	1947	1946	1954	1945	185
180°	1957	1957	1957	1957	1957	



TEST NUMBER: P333739-840

CATALOG NUMBER: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2088.4	2087.6	2086.7	2085.9	2085.1	2083.3	2080.4	2077.6	2074.9	2072.0	2074.9
5°	2081.5	2080.1	2078.7	2077.3	2075.9	2073.3	2069.4	2065.6	2061.7	2057.9	2061.3
7.5°	2061.0	2059.7	2058.4	2057.0	2055.7	2052.8	2048.1	2043.5	2038.9	2034.3	2036.7
10°	2042.1	2041.0	2040.0	2039.0	2037.9	2035.0	2030.0	2025.2	2020.2	2015.4	2016.4
12.5°	2020.7	2019.4	2018.0	2016.7	2015.4	2011.4	2004.9	1998.3	1991.7	1985.1	1985.9
15°	1979.1	1977.0	1975.0	1972.9	1970.8	1966.0	1958.6	1951.4	1944.0	1936.6	1936.3
17.5°	1932.2	1929.0	1925.8	1922.6	1919.3	1913.1	1903.9	1894.6	1885.4	1876.1	1874.4
20°	1895.7	1892.2	1888.6	1885.2	1881.7	1874.3	1863.2	1852.0	1840.8	1829.6	1827.9
22.5°	1855.4	1851.9	1848.4	1844.9	1841.4	1833.8	1822.0	1810.3	1798.5	1786.8	1783.3
25°	1794.9	1789.7	1784.4	1779.2	1773.9	1764.8	1751.9	1739.0	1726.0	1713.0	1708.5
27.5°	1725.7	1719.3	1712.9	1706.6	1700.2	1690.1	1676.2	1662.3	1648.5	1634.7	1628.3
30°	1675.3	1668.6	1661.9	1655.4	1648.7	1638.0	1623.3	1608.6	1593.9	1579.2	1571.1
32.5°	1626.2	1618.4	1610.6	1602.9	1595.1	1583.7	1568.7	1553.8	1538.7	1523.8	1514.9
35°	1546.2	1537.7	1529.3	1521.0	1512.6	1500.5	1484.7	1469.1	1453.3	1437.5	1427.3
37.5°	1467.7	1457.5	1447.3	1437.1	1426.8	1413.6	1397.5	1381.2	1364.9	1348.7	1336.6
40°	1412.3	1401.8	1391.3	1380.8	1370.4	1356.7	1339.9	1323.1	1306.3	1289.5	1276.3
42.5°	1354.4	1343.6	1332.8	1322.0	1311.3	1297.2	1279.9	1262.5	1245.2	1227.8	1215.1
45°	1265.9	1255.8	1245.6	1235.5	1225.3	1210.6	1191.3	1172.2	1152.9	1133.7	1119.6
47.5°	1174.3	1163.6	1152.9	1142.2	1131.5	1116.4	1097.0	1077.6	1058.2	1038.8	1024.4
50°	1116.3	1104.8	1093.2	1081.7	1070.2	1054.4	1034.4	1014.5	994.5	974.6	959.9
52.5°	1053.3	1041.5	1029.7	1017.8	1006.0	990.7	971.9	953.1	934.2	915.4	899.6
55°	960.5	949.3	938.1	926.9	915.6	900.3	880.7	861.1	841.5	821.9	806.2
57.5°	866.6	854.6	842.6	830.7	818.7	803.3	784.5	765.5	746.6	727.7	712.4
60°	806.2	793.9	781.6	769.4	757.2	741.5	722.7	703.8	684.9	666.0	650.7
62.5°	741.9	730.2	718.5	706.8	695.2	679.7	660.6	641.4	622.2	603.0	588.8
65°	650.3	638.3	626.5	614.6	602.7	587.4	569.0	550.4	531.8	513.3	499.3
67.5°	559.3	547.3	535.4	523.6	511.7	496.9	479.1	461.3	443.5	425.8	412.9
70°	497.6	485.6	473.7	461.8	450.0	435.3	417.8	400.3	382.7	365.3	354.5
72.5°	437.1	425.5	413.8	402.2	390.6	376.6	360.2	343.9	327.5	311.1	301.1
75°	346.4	335.9	325.4	314.9	304.4	291.9	277.1	262.5	247.7	233.0	225.3
77.5°	256.3	247.9	239.5	231.2	222.8	212.7	200.9	189.1	177.4	165.6	160.3
80°	204.7	196.3	187.9	179.5	171.1	162.0	152.2	142.4	132.6	122.8	119.7
82.5°	154.3	146.7	139.2	131.6	124.1	116.9	110.2	103.5	96.7	90.1	88.6
85°	86.6	80.3	74.0	67.7	61.4	57.4	55.6	53.9	52.1	50.4	50.0
87.5°	29.3	27.9	26.5	25.0	23.6	23.0	23.2	23.4	23.5	23.7	24.1
90°	1.5	4.2	7.0	9.7	12.3	14.8	17.3	19.6	22.0	24.3	26.1
92.5°	36.9	38.8	40.7	42.5	44.4	46.9	49.8	52.6	55.5	58.5	60.7
95°	99.0	99.7	100.4	101.0	101.7	103.7	107.1	110.5	113.9	117.2	119.7
97.5°	164.5	164.7	165.0	165.3	165.6	168.0	172.7	177.4	182.1	186.7	188.9
100°	213.2	213.2	213.2	213.2	213.2	215.4	219.8	224.2	228.6	233.0	236.1
102.5°	265.6	267.0	268.3	269.6	271.0	272.9	275.1	277.3	279.5	281.8	285.1
105°	347.3	348.9	350.6	352.3	354.1	355.9	357.9	359.9	361.9	364.1	366.1
107.5°	437.4	439.1	440.8	442.5	444.1	445.9	447.4	448.9	450.5	452.0	453.0
110°	499.6	501.3	502.9	504.6	506.3	507.7	508.7	509.7	510.7	511.7	512.7



TEST NUMBER: P333739-840

CATALOG NUMBER: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	562.9	563.8	564.7	565.5	566.4	567.5	568.8	570.1	571.4	572.7	573.1
115°	656.4	657.8	659.1	660.5	661.9	662.9	663.6	664.2	664.9	665.6	665.2
117.5°	750.2	750.8	751.4	752.0	752.7	753.3	753.9	754.5	755.1	755.8	756.0
120°	808.7	810.4	812.1	813.9	815.5	816.5	816.9	817.2	817.5	817.9	817.9
122.5°	872.1	872.7	873.3	873.9	874.5	875.3	876.2	877.1	877.9	878.8	878.5
125°	958.0	960.0	962.1	964.1	966.1	967.3	967.7	968.0	968.4	968.7	968.0
127.5°	1049.4	1050.6	1051.7	1052.8	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0
130°	1104.2	1105.9	1107.6	1109.2	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5
132.5°	1159.0	1161.8	1164.6	1167.4	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5
135°	1245.9	1247.9	1249.9	1251.9	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5
137.5°	1327.5	1329.5	1331.4	1333.3	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1
140°	1379.9	1381.6	1383.2	1384.9	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7
142.5°	1432.3	1433.7	1435.1	1436.5	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8
145°	1509.3	1510.7	1512.1	1513.4	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9
147.5°	1580.6	1581.3	1582.1	1582.9	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4
150°	1628.1	1627.8	1627.5	1627.1	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7
152.5°	1667.1	1667.6	1668.1	1668.5	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5
155°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0
157.5°	1780.7	1780.0	1779.3	1778.5	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3
160°	1812.4	1811.4	1810.4	1809.4	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7
162.5°	1840.5	1839.7	1839.0	1838.3	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1
165°	1877.9	1877.2	1876.5	1875.9	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7
167.5°	1909.6	1908.2	1906.9	1905.5	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5
170°	1926.6	1925.3	1923.9	1922.6	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6
172.5°	1938.8	1937.5	1936.1	1934.8	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8
175°	1952.6	1951.2	1949.8	1948.4	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4
177.5°	1959.5	1958.4	1957.4	1956.3	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333739-840

CATALOG NUMBER: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2077.6	2080.4	2083.3	2084.5	2084.3	2084.0	2083.7	2083.4
5°	2064.9	2068.4	2071.8	2073.3	2072.5	2071.8	2071.1	2070.4
7.5°	2039.1	2041.6	2044.1	2044.9	2044.1	2043.4	2042.6	2041.8
10°	2017.4	2018.5	2019.5	2019.5	2018.5	2017.4	2016.4	2015.4
12.5°	1986.7	1987.4	1988.2	1987.8	1986.2	1984.6	1983.0	1981.4
15°	1935.9	1935.6	1935.2	1933.5	1930.4	1927.2	1924.0	1920.9
17.5°	1872.7	1870.9	1869.2	1867.0	1864.4	1861.8	1859.3	1856.6
20°	1826.0	1824.3	1822.6	1820.1	1816.9	1813.8	1810.7	1807.6
22.5°	1779.9	1776.5	1773.0	1770.0	1767.5	1764.8	1762.2	1759.7
25°	1703.9	1699.4	1694.9	1690.6	1686.8	1682.9	1679.1	1675.3
27.5°	1621.9	1615.6	1609.2	1604.2	1600.4	1596.7	1593.0	1589.3
30°	1563.2	1555.1	1547.0	1541.5	1538.3	1535.1	1532.0	1528.8
32.5°	1506.0	1497.1	1488.2	1481.8	1477.8	1473.8	1469.9	1465.8
35°	1417.2	1407.0	1396.9	1389.4	1384.5	1379.6	1374.7	1369.8
37.5°	1324.3	1312.2	1300.0	1291.5	1286.8	1282.0	1277.3	1272.5
40°	1262.9	1249.6	1236.4	1227.6	1223.4	1219.2	1215.0	1210.8
42.5°	1202.3	1189.6	1176.9	1167.4	1161.2	1155.1	1148.9	1142.8
45°	1105.6	1091.7	1077.6	1068.0	1062.8	1057.5	1052.3	1047.0
47.5°	1010.1	995.6	981.2	971.1	965.2	959.5	953.6	947.9
50°	945.2	930.5	915.8	905.8	900.6	895.3	890.1	884.8
52.5°	883.7	868.0	852.1	841.6	836.4	831.1	825.9	820.6
55°	790.4	774.7	758.9	748.2	742.7	737.0	731.4	725.9
57.5°	696.9	681.6	666.1	656.0	651.0	646.0	641.1	636.1
60°	635.2	619.9	604.4	594.1	588.9	583.6	578.3	573.1
62.5°	574.5	560.2	545.9	536.1	530.9	525.6	520.4	515.1
65°	485.3	471.3	457.3	447.7	442.4	437.2	431.9	426.7
67.5°	400.1	387.3	374.6	366.0	361.8	357.6	353.5	349.2
70°	343.6	332.8	321.9	314.4	310.1	306.0	301.7	297.6
72.5°	291.1	281.1	271.0	264.7	261.9	259.1	256.3	253.5
75°	217.6	210.0	202.3	197.1	194.7	192.3	189.9	187.3
77.5°	154.8	149.5	144.1	140.5	138.7	136.8	135.0	133.2
80°	116.5	113.4	110.2	108.3	107.6	106.8	106.2	105.5
82.5°	87.2	85.6	84.2	83.2	82.8	82.4	82.0	81.6
85°	49.7	49.4	49.0	48.7	48.3	48.0	47.6	47.3
87.5°	24.4	24.7	25.1	25.2	25.1	25.1	25.0	24.9
90°	27.8	29.5	31.1	32.5	33.5	34.5	35.5	36.6
92.5°	62.9	65.1	67.5	68.9	69.7	70.4	71.1	71.9
95°	122.0	124.4	126.7	128.3	129.0	129.7	130.3	131.0
97.5°	191.2	193.4	195.6	197.0	197.4	197.8	198.2	198.6
100°	239.1	242.2	245.2	247.1	247.7	248.4	249.1	249.7
102.5°	288.4	291.8	295.0	297.2	298.1	299.0	300.0	300.9
105°	368.1	370.1	372.1	373.7	374.7	375.7	376.7	377.7
107.5°	454.0	455.0	456.1	456.6	456.5	456.5	456.4	456.3
110°	513.8	514.8	515.8	516.1	515.8	515.4	515.1	514.8



TEST NUMBER: P333739-840

CATALOG NUMBER: S125RDIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	573.6	574.1	574.5	574.5	573.9	573.3	572.7	572.1
115°	664.9	664.6	664.2	663.9	663.6	663.2	662.9	662.6
117.5°	756.3	756.6	756.8	756.3	754.9	753.6	752.2	750.8
120°	817.9	817.9	817.9	817.2	815.9	814.5	813.1	811.8
122.5°	878.3	878.0	877.7	877.1	876.0	874.8	873.7	872.7
125°	967.3	966.6	965.9	965.4	965.1	964.7	964.4	964.1
127.5°	1055.7	1055.4	1055.0	1054.5	1053.8	1053.2	1052.5	1051.8
130°	1114.2	1113.9	1113.5	1113.0	1112.4	1111.7	1111.0	1110.3
132.5°	1170.2	1169.9	1169.5	1168.9	1168.0	1167.0	1166.1	1165.1
135°	1256.5	1256.5	1256.5	1255.9	1254.5	1253.1	1251.7	1250.4
137.5°	1340.5	1340.9	1341.3	1340.7	1339.0	1337.3	1335.5	1333.8
140°	1393.4	1394.1	1394.7	1394.2	1392.6	1390.9	1389.2	1387.5
142.5°	1445.2	1445.6	1446.1	1445.4	1443.7	1442.1	1440.4	1438.7
145°	1519.9	1519.9	1519.9	1519.4	1518.4	1517.4	1516.4	1515.4
147.5°	1589.2	1590.0	1590.8	1590.1	1587.8	1585.5	1583.3	1580.9
150°	1632.7	1632.7	1632.7	1632.3	1631.6	1631.0	1630.3	1629.6
152.5°	1673.3	1674.2	1675.0	1674.8	1673.5	1672.3	1671.1	1669.9
155°	1731.3	1732.7	1734.0	1733.9	1732.2	1730.5	1728.8	1727.2
157.5°	1781.6	1783.0	1784.3	1783.9	1781.6	1779.4	1777.2	1774.9
160°	1812.1	1813.4	1814.8	1814.6	1812.9	1811.2	1809.6	1807.9
162.5°	1840.7	1842.3	1843.9	1843.7	1841.8	1839.8	1837.9	1835.8
165°	1879.1	1880.5	1881.8	1881.5	1879.5	1877.4	1875.4	1873.3
167.5°	1907.5	1909.6	1911.6	1911.6	1909.5	1907.4	1905.3	1903.2
170°	1924.6	1926.6	1928.6	1928.5	1926.1	1923.8	1921.4	1919.0
172.5°	1936.8	1938.8	1940.9	1940.9	1938.7	1936.6	1934.5	1932.5
175°	1950.6	1952.6	1954.6	1954.4	1952.1	1949.6	1947.3	1944.9
177.5°	1956.7	1958.3	1959.9	1959.8	1957.9	1956.0	1954.1	1952.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1

(END OF REPORT)