

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333726-840

Luminaire Tested: **S125RDIW-S1270D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333726-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D770U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8026.7 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333726-840

CATALOG NUMBER: S125RDIW-S1270D770U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333726-840

CATALOG NUMBER: S125RDIW-S1270D770U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48	44
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	34	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13464	13464	13464
5°	13494	13341	13422
10°	13392	13217	13217
15°	13233	12948	12843
20°	13029	12575	12423
25°	12790	12207	11938
30°	12493	11777	11401
35°	12191	11334	10800
40°	11907	10871	10208
45°	11562	10355	9563
50°	11216	9792	8890
55°	10815	9254	8173
60°	10413	8603	7403
65°	9938	7844	6521
70°	9396	6898	5620
75°	8644	5814	4674
80°	7613	4567	3924
85°	6417	3735	3505



TEST NUMBER: P333726-840

CATALOG NUMBER: S125RDIW-S1270D770U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	2.4
10°-20°	547.8	6.8
20°-30°	794.4	9.9
30°-40°	905.3	11.3
40°-50°	882.5	11.0
50°-60°	742.8	9.3
60°-70°	520.7	6.5
70°-80°	267.7	3.3
80°-90°	69.7	0.9
90°-100°	36.7	0.5
100°-110°	226.1	2.8
110°-120°	410.0	5.1
120°-130°	526.2	6.6
130°-140°	566.0	7.1
140°-150°	531.3	6.6
150°-160°	429.7	5.4
160°-170°	277.9	3.5
170°-180°	95.9	1.2
0°-30°	1538.2	19.2
0°-40°	2443.5	30.4
0°-60°	4068.9	50.7
0°-90°	4927.0	61.4
90°-120°	672.8	8.4
90°-150°	2296.2	28.6
90°-180°	3100.0	38.6
0°-180°	8026.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2058	2073	2070	197
15°	1979	1968	1937	1934	1921	558
25°	1795	1769	1713	1693	1675	826
35°	1546	1507	1438	1393	1370	968
45°	1266	1218	1134	1073	1047	976
55°	960	908	822	754	726	859
65°	650	595	513	452	427	644
75°	346	298	233	200	187	367
85°	87	59	50	49	47	97
90°	1	7	12	16	18	6
95°	43	39	12	16	16	54
105°	220	223	223	223	222	233
115°	413	417	418	414	410	409
125°	587	592	593	590	587	524
135°	733	737	736	734	730	564
145°	849	851	851	851	847	531
155°	935	931	932	934	929	431
165°	987	983	983	987	982	279
175°	1010	1005	1006	1011	1005	96
180°	1010	1010	1010	1010	1010	



TEST NUMBER: P333726-840

CATALOG NUMBER: S125RDIW-S1270D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2088.4	2087.6	2086.7	2085.9	2085.1	2083.3	2080.4	2077.6	2074.9	2072.0	2074.9
5°	2081.5	2080.1	2078.7	2077.3	2075.9	2073.3	2069.4	2065.6	2061.7	2057.9	2061.3
7.5°	2061.0	2059.7	2058.4	2057.0	2055.7	2052.8	2048.1	2043.5	2038.9	2034.3	2036.7
10°	2042.1	2041.0	2040.0	2039.0	2037.9	2035.0	2030.0	2025.2	2020.2	2015.4	2016.4
12.5°	2020.7	2019.4	2018.0	2016.7	2015.4	2011.4	2004.9	1998.3	1991.7	1985.1	1985.9
15°	1979.1	1977.0	1975.0	1972.9	1970.8	1966.0	1958.6	1951.4	1944.0	1936.6	1936.3
17.5°	1932.2	1929.0	1925.8	1922.6	1919.3	1913.1	1903.9	1894.6	1885.4	1876.1	1874.4
20°	1895.7	1892.2	1888.6	1885.2	1881.7	1874.3	1863.2	1852.0	1840.8	1829.6	1827.9
22.5°	1855.4	1851.9	1848.4	1844.9	1841.4	1833.8	1822.0	1810.3	1798.5	1786.8	1783.3
25°	1794.9	1789.7	1784.4	1779.2	1773.9	1764.8	1751.9	1739.0	1726.0	1713.0	1708.5
27.5°	1725.7	1719.3	1712.9	1706.6	1700.2	1690.1	1676.2	1662.3	1648.5	1634.7	1628.3
30°	1675.3	1668.6	1661.9	1655.4	1648.7	1638.0	1623.3	1608.6	1593.9	1579.2	1571.1
32.5°	1626.2	1618.4	1610.6	1602.9	1595.1	1583.7	1568.7	1553.8	1538.7	1523.8	1514.9
35°	1546.2	1537.7	1529.3	1521.0	1512.6	1500.5	1484.7	1469.1	1453.3	1437.5	1427.3
37.5°	1467.7	1457.5	1447.3	1437.1	1426.8	1413.6	1397.5	1381.2	1364.9	1348.7	1336.6
40°	1412.3	1401.8	1391.3	1380.8	1370.4	1356.7	1339.9	1323.1	1306.3	1289.5	1276.3
42.5°	1354.4	1343.6	1332.8	1322.0	1311.3	1297.2	1279.9	1262.5	1245.2	1227.8	1215.1
45°	1265.9	1255.8	1245.6	1235.5	1225.3	1210.6	1191.3	1172.2	1152.9	1133.7	1119.6
47.5°	1174.3	1163.6	1152.9	1142.2	1131.5	1116.4	1097.0	1077.6	1058.2	1038.8	1024.4
50°	1116.3	1104.8	1093.2	1081.7	1070.2	1054.4	1034.4	1014.5	994.5	974.6	959.9
52.5°	1053.3	1041.5	1029.7	1017.8	1006.0	990.7	971.9	953.1	934.2	915.4	899.6
55°	960.5	949.3	938.1	926.9	915.6	900.3	880.7	861.1	841.5	821.9	806.2
57.5°	866.6	854.6	842.6	830.7	818.7	803.3	784.5	765.5	746.6	727.7	712.4
60°	806.2	793.9	781.6	769.4	757.2	741.5	722.7	703.8	684.9	666.0	650.7
62.5°	741.9	730.2	718.5	706.8	695.2	679.7	660.6	641.4	622.2	603.0	588.8
65°	650.3	638.3	626.5	614.6	602.7	587.4	569.0	550.4	531.8	513.3	499.3
67.5°	559.3	547.3	535.4	523.6	511.7	496.9	479.1	461.3	443.5	425.8	412.9
70°	497.6	485.6	473.7	461.8	450.0	435.3	417.8	400.3	382.7	365.3	354.5
72.5°	437.1	425.5	413.8	402.2	390.6	376.6	360.2	343.9	327.5	311.1	301.1
75°	346.4	335.9	325.4	314.9	304.4	291.9	277.1	262.5	247.7	233.0	225.3
77.5°	256.3	247.9	239.5	231.2	222.8	212.7	200.9	189.1	177.4	165.6	160.3
80°	204.7	196.3	187.9	179.5	171.1	162.0	152.2	142.4	132.6	122.8	119.7
82.5°	154.3	146.7	139.2	131.6	124.1	116.9	110.2	103.5	96.7	90.1	88.6
85°	86.6	80.3	74.0	67.7	61.4	57.4	55.6	53.9	52.1	50.4	50.0
87.5°	29.1	27.5	25.8	24.0	22.3	21.5	21.4	21.4	21.3	21.3	21.4
90°	0.7	2.1	3.4	4.7	6.1	7.3	8.5	9.7	10.8	12.0	12.8
92.5°	11.5	10.6	9.7	8.7	7.8	7.9	8.9	9.9	10.9	12.0	12.8
95°	42.6	42.1	41.6	41.2	40.7	37.3	30.9	24.6	18.3	12.0	12.8
97.5°	89.1	90.0	90.9	91.7	92.6	86.8	74.3	61.8	49.3	36.9	32.1
100°	124.9	125.4	125.9	126.4	126.9	127.5	128.3	128.9	129.6	130.2	105.4
102.5°	161.5	162.1	162.8	163.4	164.0	164.5	164.9	165.3	165.7	166.1	161.5
105°	219.9	220.7	221.4	222.0	222.7	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.7	280.7	280.7	280.7	280.7	280.9	281.2	281.6	282.0	282.3	282.3
110°	320.2	320.2	320.2	320.2	320.2	320.4	320.7	321.1	321.4	321.7	321.2



TEST NUMBER: P333726-840

CATALOG NUMBER: S125RDIW-S1270D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.4	357.8	358.2	358.6	359.0	359.3	359.5	359.7	359.9	360.1	359.4
115°	413.0	413.8	414.8	415.6	416.4	416.9	417.1	417.2	417.4	417.6	416.9
117.5°	470.7	470.6	470.6	470.6	470.5	470.8	471.5	472.1	472.7	473.3	472.5
120°	506.5	506.4	506.2	506.0	505.9	506.0	506.5	507.1	507.6	508.1	507.8
122.5°	538.3	539.0	539.6	540.2	540.9	541.3	541.5	541.7	542.0	542.2	541.9
125°	587.4	588.5	589.8	590.9	592.1	592.6	592.6	592.6	592.6	592.6	592.0
127.5°	634.2	635.1	635.9	636.7	637.5	637.9	637.8	637.7	637.6	637.5	637.1
130°	663.0	663.8	664.6	665.5	666.3	666.8	666.9	667.1	667.3	667.4	666.9
132.5°	691.7	692.7	693.7	694.6	695.6	695.9	695.5	695.1	694.8	694.4	694.3
135°	732.6	733.6	734.6	735.6	736.6	736.9	736.6	736.2	735.9	735.6	735.2
137.5°	770.1	771.0	771.8	772.7	773.6	773.9	773.6	773.3	773.0	772.6	772.7
140°	794.7	795.0	795.4	795.7	796.0	796.1	795.9	795.8	795.6	795.4	795.8
142.5°	816.8	817.0	817.2	817.4	817.6	817.8	818.1	818.3	818.5	818.8	818.8
145°	849.3	849.6	850.0	850.3	850.6	850.8	850.8	850.8	850.8	850.8	850.9
147.5°	877.8	877.7	877.6	877.6	877.5	877.6	877.8	877.9	878.1	878.3	878.5
150°	895.6	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	896.1
152.5°	913.0	912.3	911.6	910.9	910.1	909.9	910.3	910.6	910.9	911.2	911.6
155°	935.3	934.3	933.3	932.3	931.4	931.0	931.4	931.7	932.0	932.3	932.8
157.5°	952.5	952.0	951.4	950.8	950.2	949.9	949.9	950.0	950.0	950.0	950.6
160°	964.5	963.5	962.5	961.5	960.6	960.1	960.3	960.5	960.6	960.8	961.5
162.5°	974.1	973.1	972.1	971.1	970.1	969.7	969.9	970.1	970.2	970.4	971.3
165°	986.9	985.9	985.0	984.0	983.0	982.6	982.7	982.9	983.1	983.2	984.2
167.5°	996.5	995.5	994.5	993.5	992.4	992.0	992.2	992.3	992.5	992.7	993.8
170°	1002.0	1000.8	999.6	998.5	997.2	996.7	996.9	997.1	997.2	997.4	998.8
172.5°	1005.5	1004.4	1003.2	1002.0	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8
175°	1009.5	1008.5	1007.4	1006.4	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0
177.5°	1011.2	1010.4	1009.7	1008.9	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333726-840

CATALOG NUMBER: S125RDIW-S1270D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2077.6	2080.4	2083.3	2084.5	2084.3	2084.0	2083.7	2083.4
5°	2064.9	2068.4	2071.8	2073.3	2072.5	2071.8	2071.1	2070.4
7.5°	2039.1	2041.6	2044.1	2044.9	2044.1	2043.4	2042.6	2041.8
10°	2017.4	2018.5	2019.5	2019.5	2018.5	2017.4	2016.4	2015.4
12.5°	1986.7	1987.4	1988.2	1987.8	1986.2	1984.6	1983.0	1981.4
15°	1935.9	1935.6	1935.2	1933.5	1930.4	1927.2	1924.0	1920.9
17.5°	1872.7	1870.9	1869.2	1867.0	1864.4	1861.8	1859.3	1856.6
20°	1826.0	1824.3	1822.6	1820.1	1816.9	1813.8	1810.7	1807.6
22.5°	1779.9	1776.5	1773.0	1770.0	1767.5	1764.8	1762.2	1759.7
25°	1703.9	1699.4	1694.9	1690.6	1686.8	1682.9	1679.1	1675.3
27.5°	1621.9	1615.6	1609.2	1604.2	1600.4	1596.7	1593.0	1589.3
30°	1563.2	1555.1	1547.0	1541.5	1538.3	1535.1	1532.0	1528.8
32.5°	1506.0	1497.1	1488.2	1481.8	1477.8	1473.8	1469.9	1465.8
35°	1417.2	1407.0	1396.9	1389.4	1384.5	1379.6	1374.7	1369.8
37.5°	1324.3	1312.2	1300.0	1291.5	1286.8	1282.0	1277.3	1272.5
40°	1262.9	1249.6	1236.4	1227.6	1223.4	1219.2	1215.0	1210.8
42.5°	1202.3	1189.6	1176.9	1167.4	1161.2	1155.1	1148.9	1142.8
45°	1105.6	1091.7	1077.6	1068.0	1062.8	1057.5	1052.3	1047.0
47.5°	1010.1	995.6	981.2	971.1	965.2	959.5	953.6	947.9
50°	945.2	930.5	915.8	905.8	900.6	895.3	890.1	884.8
52.5°	883.7	868.0	852.1	841.6	836.4	831.1	825.9	820.6
55°	790.4	774.7	758.9	748.2	742.7	737.0	731.4	725.9
57.5°	696.9	681.6	666.1	656.0	651.0	646.0	641.1	636.1
60°	635.2	619.9	604.4	594.1	588.9	583.6	578.3	573.1
62.5°	574.5	560.2	545.9	536.1	530.9	525.6	520.4	515.1
65°	485.3	471.3	457.3	447.7	442.4	437.2	431.9	426.7
67.5°	400.1	387.3	374.6	366.0	361.8	357.6	353.5	349.2
70°	343.6	332.8	321.9	314.4	310.1	306.0	301.7	297.6
72.5°	291.1	281.1	271.0	264.7	261.9	259.1	256.3	253.5
75°	217.6	210.0	202.3	197.1	194.7	192.3	189.9	187.3
77.5°	154.8	149.5	144.1	140.5	138.7	136.8	135.0	133.2
80°	116.5	113.4	110.2	108.3	107.6	106.8	106.2	105.5
82.5°	87.2	85.6	84.2	83.2	82.8	82.4	82.0	81.6
85°	49.7	49.4	49.0	48.7	48.3	48.0	47.6	47.3
87.5°	21.6	21.8	21.9	21.9	21.8	21.6	21.4	21.2
90°	13.6	14.4	15.2	16.0	16.5	17.0	17.5	18.0
92.5°	13.6	14.4	15.2	15.9	16.1	16.3	16.6	16.8
95°	13.6	14.4	15.2	15.8	15.8	15.8	15.8	15.8
97.5°	27.5	22.7	18.1	15.8	15.8	15.8	15.8	15.8
100°	80.7	55.8	31.1	18.4	17.7	17.1	16.4	15.8
102.5°	156.7	152.1	147.3	139.4	128.1	116.7	105.4	94.1
105°	223.0	223.0	223.0	222.9	222.8	222.6	222.4	222.3
107.5°	282.4	282.4	282.4	282.2	281.7	281.1	280.6	280.1
110°	320.7	320.2	319.7	319.6	319.7	319.9	320.1	320.2



TEST NUMBER: P333726-840

CATALOG NUMBER: S125RDIW-S1270D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.8	358.2	357.5	357.1	356.9	356.7	356.4	356.2
115°	416.2	415.6	414.9	414.0	413.0	412.0	411.0	410.0
117.5°	471.6	470.8	469.9	469.3	468.8	468.4	468.0	467.6
120°	507.5	507.1	506.8	506.1	505.3	504.5	503.7	502.8
122.5°	541.5	541.2	540.9	540.2	539.3	538.3	537.3	536.3
125°	591.3	590.7	590.0	589.4	588.9	588.3	587.9	587.4
127.5°	636.8	636.4	636.1	635.3	634.0	632.8	631.6	630.4
130°	666.5	666.0	665.5	664.8	664.0	663.2	662.3	661.5
132.5°	694.2	694.1	694.0	693.6	692.7	691.9	691.1	690.2
135°	734.9	734.6	734.3	733.6	732.6	731.5	730.5	729.5
137.5°	772.8	772.8	773.0	772.5	771.6	770.8	769.9	769.1
140°	796.1	796.4	796.8	796.4	795.4	794.5	793.5	792.4
142.5°	818.9	819.0	819.0	818.6	817.6	816.6	815.6	814.6
145°	851.1	851.3	851.4	851.0	850.0	849.0	848.1	847.1
147.5°	878.7	878.9	879.1	878.6	877.5	876.3	875.0	873.8
150°	896.4	896.7	897.1	896.6	895.1	893.8	892.5	891.2
152.5°	911.9	912.2	912.6	912.1	910.9	909.8	908.6	907.4
155°	933.3	933.8	934.3	933.9	932.6	931.3	930.0	928.6
157.5°	951.1	951.6	952.1	951.7	950.4	949.1	947.8	946.4
160°	962.1	962.8	963.4	963.1	961.8	960.5	959.2	957.8
162.5°	972.2	973.1	974.1	973.8	972.4	970.9	969.5	968.0
165°	985.2	986.2	987.2	987.0	985.7	984.4	983.1	981.7
167.5°	995.0	996.2	997.4	997.3	995.8	994.3	992.8	991.3
170°	1000.1	1001.5	1002.8	1002.7	1001.2	999.7	998.2	996.7
172.5°	1004.0	1005.2	1006.4	1006.2	1004.8	1003.3	1001.8	1000.3
175°	1008.4	1009.7	1011.0	1010.9	1009.5	1007.9	1006.4	1004.9
177.5°	1010.1	1011.0	1012.0	1011.9	1010.8	1009.8	1008.7	1007.6
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5

(END OF REPORT)