

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333651-840

Luminaire Tested: **S125RDIW-S375D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333651-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1050U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5131.8 lumens  
Efficiency: N/A  
Efficacy: 135.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333651-840

CATALOG NUMBER: S125RDIW-S375D1050U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333651-840

CATALOG NUMBER: S125RDIW-S375D1050U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	77	68	61	56	69	61	56	51	49	44	41	37	34	32	25	24	22
4	71	60	53	47	63	54	48	43	43	39	35	33	29	27	23	21	19
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	19	17	15
7	55	43	36	30	49	39	33	28	31	26	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	16	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	19	24	19	16	18	15	13	13	11	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3991	3991	3991
5°	4000	3955	3979
10°	3970	3918	3918
15°	3922	3839	3807
20°	3862	3727	3682
25°	3792	3619	3539
30°	3703	3491	3380
35°	3613	3360	3202
40°	3530	3222	3026
45°	3428	3070	2834
50°	3325	2903	2635
55°	3206	2743	2423
60°	3086	2550	2195
65°	2946	2326	1932
70°	2783	2045	1665
75°	2563	1724	1385
80°	2258	1354	1164
85°	1904	1104	1037



TEST NUMBER: P333651-840

CATALOG NUMBER: S125RDIW-S375D1050U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.1	1.1
10°-20°	162.4	3.2
20°-30°	235.5	4.6
30°-40°	268.4	5.2
40°-50°	261.6	5.1
50°-60°	220.2	4.3
60°-70°	154.3	3.0
70°-80°	79.3	1.5
80°-90°	22.9	0.4
90°-100°	88.1	1.7
100°-110°	260.1	5.1
110°-120°	440.5	8.6
120°-130°	579.7	11.3
130°-140°	649.6	12.7
140°-150°	636.6	12.4
150°-160°	534.7	10.4
160°-170°	355.4	6.9
170°-180°	124.4	2.4
0°-30°	456.0	8.9
0°-40°	724.3	14.1
0°-60°	1206.1	23.5
0°-90°	1462.7	28.5
90°-120°	788.6	15.4
90°-150°	2654.6	51.7
90°-180°	3669.0	71.5
0°-180°	5131.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	614	58
15°	587	584	574	573	569	165
25°	532	524	508	502	497	245
35°	458	447	426	413	406	287
45°	375	361	336	318	310	289
55°	285	269	244	223	215	255
65°	193	176	152	134	126	191
75°	103	88	69	59	56	109
85°	26	18	15	14	14	29
90°	1	9	16	21	24	5
95°	67	69	79	86	88	71
105°	233	238	245	251	254	249
115°	441	445	447	446	445	436
125°	644	649	651	649	648	576
135°	837	843	844	844	840	645
145°	1014	1018	1021	1021	1018	634
155°	1160	1160	1161	1165	1160	534
165°	1262	1260	1261	1264	1259	356
175°	1312	1308	1308	1313	1307	125
180°	1315	1315	1315	1315	1315	



TEST NUMBER: P333651-840

CATALOG NUMBER: S125RDIW-S375D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	619.0	618.8	618.5	618.3	618.0	617.5	616.7	615.8	615.0	614.2	615.0
5°	617.0	616.6	616.2	615.7	615.3	614.6	613.4	612.3	611.2	610.0	611.1
7.5°	611.0	610.6	610.2	609.8	609.4	608.4	607.1	605.7	604.4	603.0	603.7
10°	605.3	605.0	604.7	604.4	604.1	603.2	601.8	600.3	598.8	597.4	597.7
12.5°	599.0	598.5	598.2	597.8	597.4	596.2	594.3	592.4	590.4	588.4	588.7
15°	586.6	586.0	585.4	584.8	584.2	582.8	580.6	578.5	576.2	574.1	574.0
17.5°	572.8	571.8	570.9	569.9	569.0	567.1	564.3	561.6	558.9	556.1	555.6
20°	561.9	560.9	559.9	558.9	557.7	555.6	552.3	549.0	545.6	542.3	541.8
22.5°	550.0	549.0	548.0	546.8	545.8	543.6	540.1	536.6	533.1	529.7	528.7
25°	532.1	530.5	529.0	527.4	525.8	523.1	519.3	515.4	511.6	507.8	506.4
27.5°	511.5	509.7	507.8	505.8	503.9	501.0	496.9	492.7	488.7	484.5	482.6
30°	496.6	494.6	492.6	490.7	488.7	485.5	481.2	476.9	472.5	468.1	465.7
32.5°	482.0	479.7	477.5	475.1	472.8	469.5	465.0	460.6	456.2	451.7	449.1
35°	458.3	455.9	453.3	450.8	448.4	444.7	440.1	435.5	430.8	426.2	423.1
37.5°	435.0	432.0	429.0	426.0	422.9	419.0	414.2	409.4	404.7	399.8	396.2
40°	418.7	415.6	412.4	409.3	406.2	402.1	397.2	392.2	387.2	382.2	378.3
42.5°	401.4	398.3	395.1	391.9	388.7	384.6	379.4	374.3	369.1	364.0	360.2
45°	375.3	372.2	369.2	366.2	363.2	358.8	353.1	347.5	341.7	336.1	331.8
47.5°	348.1	344.9	341.7	338.5	335.4	330.9	325.2	319.4	313.7	307.9	303.7
50°	330.9	327.5	324.1	320.6	317.2	312.6	306.6	300.7	294.8	288.9	284.6
52.5°	312.3	308.7	305.2	301.7	298.2	293.7	288.1	282.5	276.9	271.4	266.7
55°	284.7	281.3	278.0	274.8	271.5	266.9	261.1	255.2	249.4	243.6	238.9
57.5°	256.9	253.4	249.7	246.2	242.7	238.1	232.5	226.9	221.4	215.7	211.2
60°	238.9	235.3	231.7	228.0	224.4	219.8	214.2	208.6	203.0	197.4	192.9
62.5°	219.9	216.4	213.0	209.5	206.0	201.5	195.8	190.2	184.4	178.7	174.5
65°	192.8	189.2	185.7	182.2	178.6	174.1	168.6	163.2	157.6	152.2	148.0
67.5°	165.8	162.3	158.8	155.2	151.7	147.2	142.0	136.7	131.5	126.2	122.4
70°	147.4	144.0	140.5	136.9	133.4	129.1	123.8	118.7	113.5	108.3	105.0
72.5°	129.6	126.1	122.7	119.3	115.8	111.6	106.7	101.9	97.0	92.2	89.3
75°	102.7	99.6	96.4	93.3	90.3	86.5	82.1	77.8	73.4	69.1	66.8
77.5°	75.9	73.5	71.0	68.5	66.0	63.0	59.6	56.0	52.6	49.1	47.5
80°	60.7	58.2	55.7	53.2	50.7	48.1	45.1	42.2	39.3	36.4	35.4
82.5°	45.7	43.5	41.3	39.0	36.8	34.6	32.7	30.7	28.7	26.7	26.3
85°	25.7	23.8	21.9	20.1	18.2	17.0	16.5	16.0	15.5	14.9	14.8
87.5°	8.8	8.6	8.4	8.2	7.9	8.0	8.2	8.4	8.7	8.9	9.1
90°	1.0	2.8	4.6	6.5	8.3	10.0	11.6	13.2	14.7	16.4	17.5
92.5°	24.7	26.1	27.3	28.6	29.9	31.5	33.4	35.3	37.4	39.3	40.8
95°	66.6	67.0	67.5	67.9	68.4	69.7	72.0	74.2	76.5	78.8	80.4
97.5°	110.5	110.7	110.9	111.1	111.3	112.9	116.0	119.2	122.3	125.4	126.9
100°	143.3	143.3	143.3	143.3	143.3	144.7	147.6	150.7	153.6	156.5	158.6
102.5°	178.4	179.4	180.3	181.2	182.1	183.3	184.8	186.3	187.8	189.3	191.6
105°	233.3	234.4	235.6	236.7	237.8	239.1	240.4	241.9	243.2	244.6	245.9
107.5°	293.9	295.0	296.2	297.3	298.4	299.5	300.5	301.6	302.7	303.7	304.4
110°	335.6	336.8	337.9	339.0	340.2	341.1	341.7	342.4	343.2	343.9	344.5



TEST NUMBER: P333651-840

CATALOG NUMBER: S125RDIW-S375D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.2	378.8	379.4	380.0	380.5	381.3	382.1	383.0	383.8	384.8	385.1
115°	441.0	441.9	442.8	443.7	444.6	445.4	445.8	446.3	446.7	447.2	447.0
117.5°	504.0	504.4	504.8	505.2	505.7	506.1	506.5	507.0	507.4	507.8	508.0
120°	543.3	544.5	545.6	546.7	547.9	548.6	548.8	549.1	549.3	549.5	549.5
122.5°	585.9	586.3	586.7	587.1	587.5	588.0	588.7	589.3	589.9	590.5	590.3
125°	643.6	645.0	646.3	647.7	649.0	649.8	650.2	650.4	650.6	650.8	650.4
127.5°	705.0	705.8	706.6	707.3	708.1	708.6	708.9	709.2	709.4	709.7	709.5
130°	741.8	743.0	744.2	745.3	746.4	747.2	747.7	748.1	748.6	749.0	748.8
132.5°	778.7	780.5	782.4	784.3	786.2	787.1	787.0	786.9	786.8	786.7	786.5
135°	837.0	838.4	839.7	841.1	842.5	843.2	843.5	843.7	843.9	844.1	844.1
137.5°	891.9	893.2	894.5	895.9	897.2	898.1	898.6	899.1	899.6	900.1	900.3
140°	927.1	928.2	929.4	930.5	931.6	932.5	933.2	933.9	934.5	935.2	935.7
142.5°	962.3	963.2	964.2	965.1	966.1	967.0	967.9	968.8	969.6	970.5	970.7
145°	1014.0	1014.9	1015.8	1016.7	1017.6	1018.4	1019.2	1019.9	1020.6	1021.2	1021.2
147.5°	1062.0	1062.5	1063.0	1063.4	1063.9	1064.5	1065.0	1065.5	1066.1	1066.6	1067.2
150°	1093.9	1093.7	1093.4	1093.2	1093.0	1093.3	1094.2	1095.1	1096.0	1096.9	1096.9
152.5°	1120.0	1120.3	1120.6	1121.1	1121.4	1121.7	1122.1	1122.4	1122.8	1123.2	1123.7
155°	1160.3	1160.3	1160.3	1160.3	1160.3	1160.4	1160.7	1160.9	1161.1	1161.4	1162.4
157.5°	1196.4	1195.9	1195.4	1194.9	1194.4	1194.3	1194.5	1194.7	1195.0	1195.2	1196.1
160°	1217.7	1217.0	1216.3	1215.7	1215.0	1214.8	1215.0	1215.2	1215.4	1215.7	1216.6
162.5°	1236.5	1236.0	1235.5	1235.0	1234.5	1234.3	1234.4	1234.4	1234.5	1234.5	1235.6
165°	1261.7	1261.2	1260.7	1260.3	1259.8	1259.7	1260.0	1260.2	1260.4	1260.6	1261.5
167.5°	1282.9	1282.0	1281.1	1280.2	1279.3	1278.9	1278.9	1278.9	1278.9	1278.9	1280.2
170°	1294.4	1293.5	1292.6	1291.7	1290.8	1290.3	1290.3	1290.3	1290.3	1290.3	1291.7
172.5°	1302.6	1301.7	1300.8	1299.9	1299.0	1298.5	1298.5	1298.5	1298.5	1298.5	1299.9
175°	1311.8	1310.9	1310.0	1309.1	1308.2	1307.7	1307.7	1307.7	1307.7	1307.7	1309.1
177.5°	1316.6	1315.8	1315.0	1314.3	1313.6	1313.1	1312.9	1312.8	1312.6	1312.4	1313.5
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333651-840

CATALOG NUMBER: S125RDIW-S375D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	615.8	616.7	617.5	617.9	617.8	617.7	617.6	617.5
5°	612.1	613.1	614.1	614.6	614.4	614.1	613.9	613.7
7.5°	604.4	605.2	605.9	606.1	605.9	605.7	605.5	605.2
10°	598.0	598.3	598.6	598.6	598.3	598.0	597.7	597.4
12.5°	588.9	589.2	589.4	589.3	588.8	588.2	587.8	587.3
15°	573.8	573.7	573.6	573.1	572.2	571.3	570.4	569.4
17.5°	555.1	554.6	554.1	553.4	552.7	551.9	551.1	550.4
20°	541.3	540.8	540.3	539.6	538.6	537.7	536.7	535.8
22.5°	527.6	526.5	525.5	524.6	523.9	523.1	522.4	521.6
25°	505.1	503.7	502.4	501.2	500.0	498.9	497.8	496.6
27.5°	480.8	478.9	477.0	475.5	474.4	473.3	472.2	471.1
30°	463.3	461.0	458.6	457.0	456.0	455.0	454.1	453.2
32.5°	446.5	443.8	441.1	439.3	438.1	436.9	435.7	434.5
35°	420.1	417.1	414.0	411.8	410.4	409.0	407.5	406.1
37.5°	392.5	389.0	385.4	382.8	381.4	380.0	378.6	377.2
40°	374.4	370.4	366.5	363.9	362.6	361.4	360.1	358.9
42.5°	356.4	352.6	348.8	346.1	344.3	342.3	340.5	338.7
45°	327.7	323.6	319.4	316.6	315.1	313.5	311.9	310.3
47.5°	299.4	295.1	290.8	287.8	286.1	284.4	282.7	280.9
50°	280.1	275.8	271.5	268.5	267.0	265.4	263.9	262.3
52.5°	262.0	257.3	252.6	249.4	247.9	246.4	244.8	243.3
55°	234.3	229.6	225.0	221.8	220.2	218.4	216.8	215.2
57.5°	206.6	202.1	197.4	194.4	193.0	191.5	190.1	188.5
60°	188.3	183.7	179.2	176.1	174.5	173.0	171.5	169.9
62.5°	170.3	166.0	161.8	159.0	157.3	155.8	154.3	152.7
65°	143.8	139.7	135.5	132.7	131.2	129.6	128.1	126.4
67.5°	118.6	114.8	111.0	108.5	107.2	106.0	104.7	103.5
70°	101.9	98.7	95.4	93.2	91.9	90.7	89.5	88.2
72.5°	86.2	83.3	80.4	78.5	77.7	76.9	75.9	75.1
75°	64.5	62.2	60.0	58.5	57.8	57.0	56.2	55.5
77.5°	45.9	44.3	42.7	41.6	41.1	40.6	40.0	39.5
80°	34.5	33.6	32.7	32.1	31.9	31.7	31.5	31.3
82.5°	25.9	25.3	24.9	24.6	24.5	24.4	24.3	24.1
85°	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.0
87.5°	9.3	9.6	9.8	9.9	10.0	10.0	10.1	10.1
90°	18.7	19.8	20.9	21.8	22.5	23.2	23.8	24.5
92.5°	42.3	43.8	45.3	46.3	46.8	47.3	47.8	48.3
95°	82.0	83.5	85.1	86.1	86.6	87.1	87.6	88.0
97.5°	128.5	130.0	131.5	132.3	132.6	132.9	133.2	133.4
100°	160.7	162.7	164.7	166.0	166.4	166.9	167.3	167.8
102.5°	193.8	196.0	198.2	199.7	200.3	201.0	201.6	202.2
105°	247.3	248.6	250.0	251.1	251.8	252.4	253.1	253.8
107.5°	305.1	305.8	306.4	306.8	306.7	306.7	306.6	306.6
110°	345.2	345.9	346.6	346.8	346.6	346.3	346.1	345.9





TEST NUMBER: P333651-840

CATALOG NUMBER: S125RDIW-S375D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	385.4	385.7	386.0	386.0	385.6	385.2	384.8	384.4
115°	446.7	446.5	446.3	446.1	445.8	445.6	445.4	445.1
117.5°	508.1	508.3	508.5	508.1	507.2	506.2	505.3	504.4
120°	549.5	549.5	549.5	549.1	548.2	547.2	546.3	545.4
122.5°	590.1	589.9	589.7	589.3	588.5	587.7	587.0	586.3
125°	649.8	649.4	648.9	648.6	648.4	648.1	647.9	647.7
127.5°	709.2	709.0	708.8	708.5	708.0	707.6	707.1	706.7
130°	748.6	748.3	748.1	747.8	747.3	746.9	746.4	746.0
132.5°	786.2	786.0	785.8	785.4	784.7	784.1	783.5	782.7
135°	844.1	844.1	844.1	843.7	842.8	841.9	841.0	840.1
137.5°	900.6	900.9	901.1	900.7	899.6	898.5	897.3	896.2
140°	936.1	936.6	937.1	936.8	935.6	934.4	933.3	932.2
142.5°	971.0	971.3	971.6	971.1	970.0	968.9	967.8	966.5
145°	1021.2	1021.2	1021.2	1020.9	1020.2	1019.5	1018.9	1018.1
147.5°	1067.7	1068.2	1068.8	1068.3	1066.8	1065.2	1063.7	1062.2
150°	1096.9	1096.9	1096.9	1096.7	1096.2	1095.8	1095.3	1094.9
152.5°	1124.2	1124.8	1125.3	1125.2	1124.4	1123.6	1122.7	1121.9
155°	1163.3	1164.2	1165.1	1164.9	1163.8	1162.7	1161.5	1160.3
157.5°	1197.0	1197.9	1198.8	1198.5	1197.0	1195.5	1194.0	1192.5
160°	1217.5	1218.4	1219.3	1219.1	1218.0	1216.9	1215.8	1214.6
162.5°	1236.7	1237.7	1238.8	1238.7	1237.4	1236.1	1234.8	1233.4
165°	1262.4	1263.3	1264.3	1264.0	1262.7	1261.3	1260.0	1258.6
167.5°	1281.6	1282.9	1284.3	1284.3	1282.9	1281.5	1280.1	1278.7
170°	1293.0	1294.4	1295.8	1295.7	1294.0	1292.5	1290.9	1289.3
172.5°	1301.2	1302.6	1303.9	1303.9	1302.5	1301.1	1299.7	1298.3
175°	1310.4	1311.8	1313.2	1313.0	1311.5	1309.9	1308.3	1306.7
177.5°	1314.6	1315.8	1316.8	1316.7	1315.5	1314.1	1312.9	1311.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8

(END OF REPORT)