

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333654-840

Luminaire Tested: **S125RDIW-S375D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333654-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1340U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6880.0 lumens
Efficiency: N/A
Efficacy: 147.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333654-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333654-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	19	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3991	3991	3991
5°	4000	3955	3979
10°	3970	3918	3918
15°	3922	3839	3807
20°	3862	3727	3682
25°	3792	3619	3539
30°	3703	3491	3380
35°	3613	3360	3202
40°	3530	3222	3026
45°	3428	3070	2834
50°	3325	2903	2635
55°	3206	2743	2423
60°	3086	2550	2195
65°	2946	2326	1932
70°	2783	2045	1665
75°	2563	1724	1385
80°	2258	1354	1164
85°	1904	1104	1037



TEST NUMBER: P333654-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	0.8
10°-20°	162.4	2.4
20°-30°	235.5	3.4
30°-40°	268.4	3.9
40°-50°	261.6	3.8
50°-60°	220.2	3.2
60°-70°	154.3	2.2
70°-80°	79.3	1.2
80°-90°	23.7	0.3
90°-100°	64.1	0.9
100°-110°	395.0	5.7
110°-120°	716.5	10.4
120°-130°	919.5	13.4
130°-140°	989.0	14.4
140°-150°	928.3	13.5
150°-160°	750.9	10.9
160°-170°	485.7	7.1
170°-180°	167.5	2.4
0°-30°	456.0	6.6
0°-40°	724.3	10.5
0°-60°	1206.1	17.5
0°-90°	1463.5	21.3
90°-120°	1175.6	17.1
90°-150°	4012.4	58.3
90°-180°	5416.0	78.7
0°-180°	6880.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	614	58
15°	587	584	574	573	569	165
25°	532	524	508	502	497	245
35°	458	447	426	413	406	287
45°	375	361	336	318	310	289
55°	285	269	244	223	215	255
65°	193	176	152	134	126	191
75°	103	88	69	59	56	109
85°	26	18	15	14	14	29
90°	1	12	21	27	31	4
95°	74	68	21	27	28	95
105°	384	389	390	390	388	408
115°	722	728	730	724	716	715
125°	1026	1035	1036	1030	1026	916
135°	1280	1287	1285	1282	1275	986
145°	1484	1486	1487	1487	1480	928
155°	1634	1627	1629	1632	1623	753
165°	1725	1717	1718	1725	1716	487
175°	1764	1757	1757	1767	1756	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P333654-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	619.0	618.8	618.5	618.3	618.0	617.5	616.7	615.8	615.0	614.2	615.0
5°	617.0	616.6	616.2	615.7	615.3	614.6	613.4	612.3	611.2	610.0	611.1
7.5°	611.0	610.6	610.2	609.8	609.4	608.4	607.1	605.7	604.4	603.0	603.7
10°	605.3	605.0	604.7	604.4	604.1	603.2	601.8	600.3	598.8	597.4	597.7
12.5°	599.0	598.5	598.2	597.8	597.4	596.2	594.3	592.4	590.4	588.4	588.7
15°	586.6	586.0	585.4	584.8	584.2	582.8	580.6	578.5	576.2	574.1	574.0
17.5°	572.8	571.8	570.9	569.9	569.0	567.1	564.3	561.6	558.9	556.1	555.6
20°	561.9	560.9	559.9	558.9	557.7	555.6	552.3	549.0	545.6	542.3	541.8
22.5°	550.0	549.0	548.0	546.8	545.8	543.6	540.1	536.6	533.1	529.7	528.7
25°	532.1	530.5	529.0	527.4	525.8	523.1	519.3	515.4	511.6	507.8	506.4
27.5°	511.5	509.7	507.8	505.8	503.9	501.0	496.9	492.7	488.7	484.5	482.6
30°	496.6	494.6	492.6	490.7	488.7	485.5	481.2	476.9	472.5	468.1	465.7
32.5°	482.0	479.7	477.5	475.1	472.8	469.5	465.0	460.6	456.2	451.7	449.1
35°	458.3	455.9	453.3	450.8	448.4	444.7	440.1	435.5	430.8	426.2	423.1
37.5°	435.0	432.0	429.0	426.0	422.9	419.0	414.2	409.4	404.7	399.8	396.2
40°	418.7	415.6	412.4	409.3	406.2	402.1	397.2	392.2	387.2	382.2	378.3
42.5°	401.4	398.3	395.1	391.9	388.7	384.6	379.4	374.3	369.1	364.0	360.2
45°	375.3	372.2	369.2	366.2	363.2	358.8	353.1	347.5	341.7	336.1	331.8
47.5°	348.1	344.9	341.7	338.5	335.4	330.9	325.2	319.4	313.7	307.9	303.7
50°	330.9	327.5	324.1	320.6	317.2	312.6	306.6	300.7	294.8	288.9	284.6
52.5°	312.3	308.7	305.2	301.7	298.2	293.7	288.1	282.5	276.9	271.4	266.7
55°	284.7	281.3	278.0	274.8	271.5	266.9	261.1	255.2	249.4	243.6	238.9
57.5°	256.9	253.4	249.7	246.2	242.7	238.1	232.5	226.9	221.4	215.7	211.2
60°	238.9	235.3	231.7	228.0	224.4	219.8	214.2	208.6	203.0	197.4	192.9
62.5°	219.9	216.4	213.0	209.5	206.0	201.5	195.8	190.2	184.4	178.7	174.5
65°	192.8	189.2	185.7	182.2	178.6	174.1	168.6	163.2	157.6	152.2	148.0
67.5°	165.8	162.3	158.8	155.2	151.7	147.2	142.0	136.7	131.5	126.2	122.4
70°	147.4	144.0	140.5	136.9	133.4	129.1	123.8	118.7	113.5	108.3	105.0
72.5°	129.6	126.1	122.7	119.3	115.8	111.6	106.7	101.9	97.0	92.2	89.3
75°	102.7	99.6	96.4	93.3	90.3	86.5	82.1	77.8	73.4	69.1	66.8
77.5°	75.9	73.5	71.0	68.5	66.0	63.0	59.6	56.0	52.6	49.1	47.5
80°	60.7	58.2	55.7	53.2	50.7	48.1	45.1	42.2	39.3	36.4	35.4
82.5°	45.7	43.5	41.3	39.0	36.8	34.6	32.7	30.7	28.7	26.7	26.3
85°	25.7	23.8	21.9	20.1	18.2	17.0	16.5	16.0	15.5	14.9	14.8
87.5°	8.9	8.7	8.6	8.5	8.4	8.5	8.8	9.1	9.5	9.8	10.1
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	20.9	22.4
92.5°	20.1	18.5	16.9	15.2	13.6	13.7	15.6	17.3	19.1	20.9	22.4
95°	74.5	73.6	72.8	71.9	71.0	65.0	54.0	43.0	31.9	20.9	22.4
97.5°	155.6	157.1	158.8	160.3	161.9	151.7	129.9	108.1	86.1	64.3	56.1
100°	218.3	219.2	220.0	221.0	221.9	222.9	224.0	225.2	226.3	227.5	184.2
102.5°	282.2	283.3	284.4	285.5	286.6	287.5	288.2	288.9	289.5	290.2	282.1
105°	384.5	385.6	386.8	387.9	389.1	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	490.6	490.6	490.6	490.6	490.6	490.9	491.5	492.0	492.6	493.2	493.2
110°	559.7	559.7	559.7	559.7	559.7	559.9	560.5	561.1	561.7	562.2	561.4



TEST NUMBER: P333654-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	624.5	625.2	625.9	626.5	627.2	627.8	628.1	628.4	628.8	629.1	628.0
115°	721.8	723.2	724.7	726.1	727.6	728.4	728.7	729.0	729.3	729.6	728.4
117.5°	822.4	822.3	822.3	822.2	822.2	822.7	823.8	825.0	826.1	827.2	825.7
120°	885.1	884.9	884.6	884.3	884.0	884.3	885.1	886.1	887.0	887.8	887.3
122.5°	940.6	941.7	942.8	943.9	945.0	945.8	946.2	946.6	947.1	947.5	946.8
125°	1026.4	1028.4	1030.5	1032.5	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4
127.5°	1108.2	1109.7	1111.2	1112.6	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4
130°	1158.4	1159.9	1161.3	1162.9	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5
132.5°	1208.7	1210.3	1212.0	1213.8	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3
135°	1280.1	1281.8	1283.5	1285.3	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8
137.5°	1345.7	1347.2	1348.7	1350.2	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3
140°	1388.6	1389.2	1389.8	1390.3	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5
142.5°	1427.2	1427.6	1427.9	1428.4	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8
145°	1484.0	1484.6	1485.2	1485.8	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9
147.5°	1533.7	1533.6	1533.5	1533.4	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1
150°	1565.1	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7
152.5°	1595.4	1594.2	1592.9	1591.6	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9
155°	1634.4	1632.6	1630.9	1629.2	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0
157.5°	1664.5	1663.4	1662.3	1661.3	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9
160°	1685.4	1683.6	1681.9	1680.1	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0
162.5°	1702.1	1700.4	1698.6	1696.9	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2
165°	1724.6	1722.8	1721.1	1719.4	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8
167.5°	1741.3	1739.6	1737.8	1736.0	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7
170°	1750.8	1748.8	1746.7	1744.6	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2
172.5°	1757.1	1755.0	1753.0	1750.9	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3
175°	1763.8	1762.1	1760.4	1758.6	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6
177.5°	1767.0	1765.5	1764.2	1762.8	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333654-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	615.8	616.7	617.5	617.9	617.8	617.7	617.6	617.5
5°	612.1	613.1	614.1	614.6	614.4	614.1	613.9	613.7
7.5°	604.4	605.2	605.9	606.1	605.9	605.7	605.5	605.2
10°	598.0	598.3	598.6	598.6	598.3	598.0	597.7	597.4
12.5°	588.9	589.2	589.4	589.3	588.8	588.2	587.8	587.3
15°	573.8	573.7	573.6	573.1	572.2	571.3	570.4	569.4
17.5°	555.1	554.6	554.1	553.4	552.7	551.9	551.1	550.4
20°	541.3	540.8	540.3	539.6	538.6	537.7	536.7	535.8
22.5°	527.6	526.5	525.5	524.6	523.9	523.1	522.4	521.6
25°	505.1	503.7	502.4	501.2	500.0	498.9	497.8	496.6
27.5°	480.8	478.9	477.0	475.5	474.4	473.3	472.2	471.1
30°	463.3	461.0	458.6	457.0	456.0	455.0	454.1	453.2
32.5°	446.5	443.8	441.1	439.3	438.1	436.9	435.7	434.5
35°	420.1	417.1	414.0	411.8	410.4	409.0	407.5	406.1
37.5°	392.5	389.0	385.4	382.8	381.4	380.0	378.6	377.2
40°	374.4	370.4	366.5	363.9	362.6	361.4	360.1	358.9
42.5°	356.4	352.6	348.8	346.1	344.3	342.3	340.5	338.7
45°	327.7	323.6	319.4	316.6	315.1	313.5	311.9	310.3
47.5°	299.4	295.1	290.8	287.8	286.1	284.4	282.7	280.9
50°	280.1	275.8	271.5	268.5	267.0	265.4	263.9	262.3
52.5°	262.0	257.3	252.6	249.4	247.9	246.4	244.8	243.3
55°	234.3	229.6	225.0	221.8	220.2	218.4	216.8	215.2
57.5°	206.6	202.1	197.4	194.4	193.0	191.5	190.1	188.5
60°	188.3	183.7	179.2	176.1	174.5	173.0	171.5	169.9
62.5°	170.3	166.0	161.8	159.0	157.3	155.8	154.3	152.7
65°	143.8	139.7	135.5	132.7	131.2	129.6	128.1	126.4
67.5°	118.6	114.8	111.0	108.5	107.2	106.0	104.7	103.5
70°	101.9	98.7	95.4	93.2	91.9	90.7	89.5	88.2
72.5°	86.2	83.3	80.4	78.5	77.7	76.9	75.9	75.1
75°	64.5	62.2	60.0	58.5	57.8	57.0	56.2	55.5
77.5°	45.9	44.3	42.7	41.6	41.1	40.6	40.0	39.5
80°	34.5	33.6	32.7	32.1	31.9	31.7	31.5	31.3
82.5°	25.9	25.3	24.9	24.6	24.5	24.4	24.3	24.1
85°	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.0
87.5°	10.4	10.7	10.9	11.1	11.2	11.3	11.4	11.5
90°	23.8	25.2	26.8	27.9	28.8	29.6	30.5	31.4
92.5°	23.8	25.2	26.8	27.7	28.1	28.5	28.9	29.3
95°	23.8	25.2	26.8	27.5	27.5	27.5	27.5	27.5
97.5°	48.0	39.8	31.5	27.5	27.5	27.5	27.5	27.5
100°	140.9	97.7	54.3	32.1	30.9	29.8	28.6	27.5
102.5°	273.9	265.7	257.5	243.5	223.8	204.0	184.2	164.5
105°	389.6	389.6	389.6	389.5	389.2	388.9	388.6	388.3
107.5°	493.3	493.4	493.4	493.0	492.1	491.3	490.4	489.6
110°	560.5	559.7	558.8	558.5	558.8	559.1	559.4	559.7



TEST NUMBER: P333654-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	626.9	625.9	624.8	624.0	623.6	623.2	622.8	622.4
115°	727.3	726.1	725.0	723.5	721.8	720.0	718.2	716.5
117.5°	824.2	822.6	821.1	819.9	819.2	818.5	817.7	817.0
120°	886.7	886.1	885.4	884.4	883.0	881.5	880.1	878.7
122.5°	946.2	945.6	945.1	943.9	942.3	940.6	938.9	937.3
125°	1033.2	1032.1	1030.9	1029.9	1029.1	1028.1	1027.2	1026.4
127.5°	1112.8	1112.1	1111.5	1110.0	1107.9	1105.8	1103.6	1101.5
130°	1164.6	1163.7	1162.9	1161.6	1160.2	1158.7	1157.3	1155.9
132.5°	1213.0	1212.8	1212.6	1211.8	1210.4	1209.0	1207.5	1206.1
135°	1284.1	1283.5	1282.9	1281.8	1280.1	1278.3	1276.6	1274.9
137.5°	1350.4	1350.5	1350.6	1349.9	1348.4	1346.9	1345.3	1343.8
140°	1391.1	1391.6	1392.2	1391.6	1389.9	1388.2	1386.4	1384.6
142.5°	1430.9	1431.1	1431.2	1430.4	1428.6	1426.8	1425.1	1423.4
145°	1487.2	1487.5	1487.8	1487.1	1485.3	1483.6	1481.9	1480.2
147.5°	1535.5	1535.8	1536.2	1535.3	1533.2	1531.1	1529.0	1526.9
150°	1566.3	1566.8	1567.4	1566.5	1564.2	1561.9	1559.5	1557.2
152.5°	1593.5	1594.1	1594.6	1593.9	1591.7	1589.7	1587.6	1585.5
155°	1630.9	1631.7	1632.6	1631.9	1629.6	1627.3	1625.0	1622.7
157.5°	1661.9	1662.8	1663.8	1663.0	1660.7	1658.4	1656.1	1653.8
160°	1681.2	1682.3	1683.5	1682.9	1680.6	1678.3	1676.0	1673.6
162.5°	1698.8	1700.5	1702.1	1701.6	1699.1	1696.5	1693.9	1691.4
165°	1721.5	1723.3	1725.1	1724.7	1722.4	1720.1	1717.8	1715.5
167.5°	1738.8	1740.8	1742.9	1742.6	1740.0	1737.5	1734.8	1732.2
170°	1747.6	1749.9	1752.2	1752.1	1749.5	1746.9	1744.2	1741.6
172.5°	1754.4	1756.6	1758.6	1758.4	1755.8	1753.1	1750.5	1747.9
175°	1761.9	1764.2	1766.6	1766.5	1763.8	1761.2	1758.6	1756.0
177.5°	1765.0	1766.7	1768.3	1768.2	1766.3	1764.4	1762.5	1760.7
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)