

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333655-840

Luminaire Tested: **S125RDIW-S375D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333655-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1340U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6160.6 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333655-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333655-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23	17
3	76	67	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	15
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3991	3991	3991
5°	4000	3955	3979
10°	3970	3918	3918
15°	3922	3839	3807
20°	3862	3727	3682
25°	3792	3619	3539
30°	3703	3491	3380
35°	3613	3360	3202
40°	3530	3222	3026
45°	3428	3070	2834
50°	3325	2903	2635
55°	3206	2743	2423
60°	3086	2550	2195
65°	2946	2326	1932
70°	2783	2045	1665
75°	2563	1724	1385
80°	2258	1354	1164
85°	1904	1104	1037



TEST NUMBER: P333655-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	0.9
10°-20°	162.4	2.6
20°-30°	235.5	3.8
30°-40°	268.4	4.4
40°-50°	261.6	4.2
50°-60°	220.2	3.6
60°-70°	154.3	2.5
70°-80°	79.3	1.3
80°-90°	23.7	0.4
90°-100°	112.7	1.8
100°-110°	332.9	5.4
110°-120°	563.9	9.2
120°-130°	742.1	12.0
130°-140°	831.6	13.5
140°-150°	815.0	13.2
150°-160°	684.5	11.1
160°-170°	455.0	7.4
170°-180°	159.2	2.6
0°-30°	456.0	7.4
0°-40°	724.3	11.8
0°-60°	1206.1	19.6
0°-90°	1463.5	23.8
90°-120°	1009.6	16.4
90°-150°	3398.3	55.2
90°-180°	4697.0	76.2
0°-180°	6160.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	614	58
15°	587	584	574	573	569	165
25°	532	524	508	502	497	245
35°	458	447	426	413	406	287
45°	375	361	336	318	310	289
55°	285	269	244	223	215	255
65°	193	176	152	134	126	191
75°	103	88	69	59	56	109
85°	26	18	15	14	14	29
90°	1	12	21	27	31	6
95°	85	88	101	110	113	91
105°	299	305	313	321	325	319
115°	565	570	572	571	570	558
125°	824	831	833	831	829	738
135°	1072	1079	1081	1080	1076	826
145°	1298	1303	1307	1307	1303	811
155°	1486	1486	1487	1491	1486	684
165°	1615	1613	1614	1618	1611	455
175°	1679	1674	1674	1681	1673	160
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333655-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	619.0	618.8	618.5	618.3	618.0	617.5	616.7	615.8	615.0	614.2	615.0
5°	617.0	616.6	616.2	615.7	615.3	614.6	613.4	612.3	611.2	610.0	611.1
7.5°	611.0	610.6	610.2	609.8	609.4	608.4	607.1	605.7	604.4	603.0	603.7
10°	605.3	605.0	604.7	604.4	604.1	603.2	601.8	600.3	598.8	597.4	597.7
12.5°	599.0	598.5	598.2	597.8	597.4	596.2	594.3	592.4	590.4	588.4	588.7
15°	586.6	586.0	585.4	584.8	584.2	582.8	580.6	578.5	576.2	574.1	574.0
17.5°	572.8	571.8	570.9	569.9	569.0	567.1	564.3	561.6	558.9	556.1	555.6
20°	561.9	560.9	559.9	558.9	557.7	555.6	552.3	549.0	545.6	542.3	541.8
22.5°	550.0	549.0	548.0	546.8	545.8	543.6	540.1	536.6	533.1	529.7	528.7
25°	532.1	530.5	529.0	527.4	525.8	523.1	519.3	515.4	511.6	507.8	506.4
27.5°	511.5	509.7	507.8	505.8	503.9	501.0	496.9	492.7	488.7	484.5	482.6
30°	496.6	494.6	492.6	490.7	488.7	485.5	481.2	476.9	472.5	468.1	465.7
32.5°	482.0	479.7	477.5	475.1	472.8	469.5	465.0	460.6	456.2	451.7	449.1
35°	458.3	455.9	453.3	450.8	448.4	444.7	440.1	435.5	430.8	426.2	423.1
37.5°	435.0	432.0	429.0	426.0	422.9	419.0	414.2	409.4	404.7	399.8	396.2
40°	418.7	415.6	412.4	409.3	406.2	402.1	397.2	392.2	387.2	382.2	378.3
42.5°	401.4	398.3	395.1	391.9	388.7	384.6	379.4	374.3	369.1	364.0	360.2
45°	375.3	372.2	369.2	366.2	363.2	358.8	353.1	347.5	341.7	336.1	331.8
47.5°	348.1	344.9	341.7	338.5	335.4	330.9	325.2	319.4	313.7	307.9	303.7
50°	330.9	327.5	324.1	320.6	317.2	312.6	306.6	300.7	294.8	288.9	284.6
52.5°	312.3	308.7	305.2	301.7	298.2	293.7	288.1	282.5	276.9	271.4	266.7
55°	284.7	281.3	278.0	274.8	271.5	266.9	261.1	255.2	249.4	243.6	238.9
57.5°	256.9	253.4	249.7	246.2	242.7	238.1	232.5	226.9	221.4	215.7	211.2
60°	238.9	235.3	231.7	228.0	224.4	219.8	214.2	208.6	203.0	197.4	192.9
62.5°	219.9	216.4	213.0	209.5	206.0	201.5	195.8	190.2	184.4	178.7	174.5
65°	192.8	189.2	185.7	182.2	178.6	174.1	168.6	163.2	157.6	152.2	148.0
67.5°	165.8	162.3	158.8	155.2	151.7	147.2	142.0	136.7	131.5	126.2	122.4
70°	147.4	144.0	140.5	136.9	133.4	129.1	123.8	118.7	113.5	108.3	105.0
72.5°	129.6	126.1	122.7	119.3	115.8	111.6	106.7	101.9	97.0	92.2	89.3
75°	102.7	99.6	96.4	93.3	90.3	86.5	82.1	77.8	73.4	69.1	66.8
77.5°	75.9	73.5	71.0	68.5	66.0	63.0	59.6	56.0	52.6	49.1	47.5
80°	60.7	58.2	55.7	53.2	50.7	48.1	45.1	42.2	39.3	36.4	35.4
82.5°	45.7	43.5	41.3	39.0	36.8	34.6	32.7	30.7	28.7	26.7	26.3
85°	25.7	23.8	21.9	20.1	18.2	17.0	16.5	16.0	15.5	14.9	14.8
87.5°	8.9	8.7	8.6	8.5	8.4	8.5	8.8	9.2	9.5	9.8	10.1
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4
92.5°	31.7	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2
95°	85.1	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9
97.5°	141.5	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5
100°	183.4	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1
102.5°	228.4	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2
105°	298.7	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9
107.5°	376.2	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7
110°	429.7	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0



TEST NUMBER: P333655-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.1	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9
115°	564.6	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2
117.5°	645.3	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3
120°	695.6	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5
122.5°	750.1	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6
125°	823.9	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5
127.5°	902.5	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3
130°	949.7	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6
132.5°	996.8	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8
135°	1071.6	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8
137.5°	1141.8	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6
140°	1186.8	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9
142.5°	1231.9	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7
145°	1298.2	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4
147.5°	1359.5	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2
150°	1400.4	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3
152.5°	1433.9	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6
155°	1485.5	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9
157.5°	1531.6	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2
160°	1558.8	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4
162.5°	1583.0	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8
165°	1615.2	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1
167.5°	1642.4	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9
170°	1657.1	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7
172.5°	1667.6	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1
175°	1679.4	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9
177.5°	1685.4	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333655-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	615.8	616.7	617.5	617.9	617.8	617.7	617.6	617.5
5°	612.1	613.1	614.1	614.6	614.4	614.1	613.9	613.7
7.5°	604.4	605.2	605.9	606.1	605.9	605.7	605.5	605.2
10°	598.0	598.3	598.6	598.6	598.3	598.0	597.7	597.4
12.5°	588.9	589.2	589.4	589.3	588.8	588.2	587.8	587.3
15°	573.8	573.7	573.6	573.1	572.2	571.3	570.4	569.4
17.5°	555.1	554.6	554.1	553.4	552.7	551.9	551.1	550.4
20°	541.3	540.8	540.3	539.6	538.6	537.7	536.7	535.8
22.5°	527.6	526.5	525.5	524.6	523.9	523.1	522.4	521.6
25°	505.1	503.7	502.4	501.2	500.0	498.9	497.8	496.6
27.5°	480.8	478.9	477.0	475.5	474.4	473.3	472.2	471.1
30°	463.3	461.0	458.6	457.0	456.0	455.0	454.1	453.2
32.5°	446.5	443.8	441.1	439.3	438.1	436.9	435.7	434.5
35°	420.1	417.1	414.0	411.8	410.4	409.0	407.5	406.1
37.5°	392.5	389.0	385.4	382.8	381.4	380.0	378.6	377.2
40°	374.4	370.4	366.5	363.9	362.6	361.4	360.1	358.9
42.5°	356.4	352.6	348.8	346.1	344.3	342.3	340.5	338.7
45°	327.7	323.6	319.4	316.6	315.1	313.5	311.9	310.3
47.5°	299.4	295.1	290.8	287.8	286.1	284.4	282.7	280.9
50°	280.1	275.8	271.5	268.5	267.0	265.4	263.9	262.3
52.5°	262.0	257.3	252.6	249.4	247.9	246.4	244.8	243.3
55°	234.3	229.6	225.0	221.8	220.2	218.4	216.8	215.2
57.5°	206.6	202.1	197.4	194.4	193.0	191.5	190.1	188.5
60°	188.3	183.7	179.2	176.1	174.5	173.0	171.5	169.9
62.5°	170.3	166.0	161.8	159.0	157.3	155.8	154.3	152.7
65°	143.8	139.7	135.5	132.7	131.2	129.6	128.1	126.4
67.5°	118.6	114.8	111.0	108.5	107.2	106.0	104.7	103.5
70°	101.9	98.7	95.4	93.2	91.9	90.7	89.5	88.2
72.5°	86.2	83.3	80.4	78.5	77.7	76.9	75.9	75.1
75°	64.5	62.2	60.0	58.5	57.8	57.0	56.2	55.5
77.5°	45.9	44.3	42.7	41.6	41.1	40.6	40.0	39.5
80°	34.5	33.6	32.7	32.1	31.9	31.7	31.5	31.3
82.5°	25.9	25.3	24.9	24.6	24.5	24.4	24.3	24.1
85°	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.0
87.5°	10.4	10.7	10.9	11.1	11.2	11.3	11.4	11.5
90°	23.8	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	54.1	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	104.9	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	164.4	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	205.7	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	248.0	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	316.6	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	390.5	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	441.9	442.7	443.6	443.9	443.6	443.3	443.0	442.7



TEST NUMBER: P333655-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.3	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.9	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.5	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.4	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.9	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	908.0	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.3	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.5	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.0	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1198.5	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.0	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1366.9	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.2	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1489.1	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1532.4	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1558.5	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1583.2	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1616.2	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1640.7	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1655.4	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1665.9	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1677.6	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1682.9	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)