

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333658-840

Luminaire Tested: **S125RDIW-S375D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333658-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1560U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7761.6 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333658-840

CATALOG NUMBER: S125RDIW-S375D1560U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333658-840

CATALOG NUMBER: S125RDIW-S375D1560U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14				
3	75	67	60	54	66	59	53	49	45	41	38	31	29	27	19	18	17	12				
4	69	59	51	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10				
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9				
6	58	47	39	34	51	41	35	30	32	27	24	23	20	17	14	12	11	8				
7	54	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7				
8	49	38	31	26	44	34	27	23	26	21	18	19	16	14	12	10	9	6				
9	46	34	27	23	40	31	25	20	24	19	16	17	14	12	11	9	8	6				
10	43	31	25	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3991	3991	3991
5°	4000	3955	3979
10°	3970	3918	3918
15°	3922	3839	3807
20°	3862	3727	3682
25°	3792	3619	3539
30°	3703	3491	3380
35°	3613	3360	3202
40°	3530	3222	3026
45°	3428	3070	2834
50°	3325	2903	2635
55°	3206	2743	2423
60°	3086	2550	2195
65°	2946	2326	1932
70°	2783	2045	1665
75°	2563	1724	1385
80°	2258	1354	1164
85°	1904	1104	1037



TEST NUMBER: P333658-840

CATALOG NUMBER: S125RDIW-S375D1560U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	0.7
10°-20°	162.4	2.1
20°-30°	235.5	3.0
30°-40°	268.4	3.5
40°-50°	261.6	3.4
50°-60°	220.2	2.8
60°-70°	154.3	2.0
70°-80°	79.3	1.0
80°-90°	24.3	0.3
90°-100°	74.5	1.0
100°-110°	459.3	5.9
110°-120°	833.0	10.7
120°-130°	1069.1	13.8
130°-140°	1149.9	14.8
140°-150°	1079.3	13.9
150°-160°	873.1	11.2
160°-170°	564.7	7.3
170°-180°	194.8	2.5
0°-30°	456.0	5.9
0°-40°	724.3	9.3
0°-60°	1206.1	15.5
0°-90°	1464.1	18.9
90°-120°	1366.8	17.6
90°-150°	4665.0	60.1
90°-180°	6298.0	81.1
0°-180°	7761.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	614	58
15°	587	584	574	573	569	165
25°	532	524	508	502	497	245
35°	458	447	426	413	406	287
45°	375	361	336	318	310	289
55°	285	269	244	223	215	255
65°	193	176	152	134	126	191
75°	103	88	69	59	56	109
85°	26	18	15	14	14	29
90°	2	14	24	32	36	5
95°	87	79	24	32	32	110
105°	447	453	453	453	452	474
115°	839	846	848	842	833	832
125°	1193	1203	1204	1198	1193	1065
135°	1488	1497	1494	1491	1482	1147
145°	1726	1728	1728	1729	1721	1079
155°	1900	1892	1894	1898	1886	875
165°	2005	1997	1998	2006	1994	566
175°	2051	2042	2043	2054	2042	195
180°	2051	2051	2051	2051	2051	



TEST NUMBER: P333658-840

CATALOG NUMBER: S125RDIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	619.0	618.8	618.5	618.3	618.0	617.5	616.7	615.8	615.0	614.2	615.0
5°	617.0	616.6	616.2	615.7	615.3	614.6	613.4	612.3	611.2	610.0	611.1
7.5°	611.0	610.6	610.2	609.8	609.4	608.4	607.1	605.7	604.4	603.0	603.7
10°	605.3	605.0	604.7	604.4	604.1	603.2	601.8	600.3	598.8	597.4	597.7
12.5°	599.0	598.5	598.2	597.8	597.4	596.2	594.3	592.4	590.4	588.4	588.7
15°	586.6	586.0	585.4	584.8	584.2	582.8	580.6	578.5	576.2	574.1	574.0
17.5°	572.8	571.8	570.9	569.9	569.0	567.1	564.3	561.6	558.9	556.1	555.6
20°	561.9	560.9	559.9	558.9	557.7	555.6	552.3	549.0	545.6	542.3	541.8
22.5°	550.0	549.0	548.0	546.8	545.8	543.6	540.1	536.6	533.1	529.7	528.7
25°	532.1	530.5	529.0	527.4	525.8	523.1	519.3	515.4	511.6	507.8	506.4
27.5°	511.5	509.7	507.8	505.8	503.9	501.0	496.9	492.7	488.7	484.5	482.6
30°	496.6	494.6	492.6	490.7	488.7	485.5	481.2	476.9	472.5	468.1	465.7
32.5°	482.0	479.7	477.5	475.1	472.8	469.5	465.0	460.6	456.2	451.7	449.1
35°	458.3	455.9	453.3	450.8	448.4	444.7	440.1	435.5	430.8	426.2	423.1
37.5°	435.0	432.0	429.0	426.0	422.9	419.0	414.2	409.4	404.7	399.8	396.2
40°	418.7	415.6	412.4	409.3	406.2	402.1	397.2	392.2	387.2	382.2	378.3
42.5°	401.4	398.3	395.1	391.9	388.7	384.6	379.4	374.3	369.1	364.0	360.2
45°	375.3	372.2	369.2	366.2	363.2	358.8	353.1	347.5	341.7	336.1	331.8
47.5°	348.1	344.9	341.7	338.5	335.4	330.9	325.2	319.4	313.7	307.9	303.7
50°	330.9	327.5	324.1	320.6	317.2	312.6	306.6	300.7	294.8	288.9	284.6
52.5°	312.3	308.7	305.2	301.7	298.2	293.7	288.1	282.5	276.9	271.4	266.7
55°	284.7	281.3	278.0	274.8	271.5	266.9	261.1	255.2	249.4	243.6	238.9
57.5°	256.9	253.4	249.7	246.2	242.7	238.1	232.5	226.9	221.4	215.7	211.2
60°	238.9	235.3	231.7	228.0	224.4	219.8	214.2	208.6	203.0	197.4	192.9
62.5°	219.9	216.4	213.0	209.5	206.0	201.5	195.8	190.2	184.4	178.7	174.5
65°	192.8	189.2	185.7	182.2	178.6	174.1	168.6	163.2	157.6	152.2	148.0
67.5°	165.8	162.3	158.8	155.2	151.7	147.2	142.0	136.7	131.5	126.2	122.4
70°	147.4	144.0	140.5	136.9	133.4	129.1	123.8	118.7	113.5	108.3	105.0
72.5°	129.6	126.1	122.7	119.3	115.8	111.6	106.7	101.9	97.0	92.2	89.3
75°	102.7	99.6	96.4	93.3	90.3	86.5	82.1	77.8	73.4	69.1	66.8
77.5°	75.9	73.5	71.0	68.5	66.0	63.0	59.6	56.0	52.6	49.1	47.5
80°	60.7	58.2	55.7	53.2	50.7	48.1	45.1	42.2	39.3	36.4	35.4
82.5°	45.7	43.5	41.3	39.0	36.8	34.6	32.7	30.7	28.7	26.7	26.3
85°	25.7	23.8	21.9	20.1	18.2	17.0	16.5	16.0	15.5	14.9	14.8
87.5°	8.9	8.9	8.8	8.8	8.7	8.9	9.3	9.7	10.1	10.5	10.8
90°	1.5	4.2	7.0	9.6	12.3	14.8	17.3	19.6	21.9	24.3	26.1
92.5°	23.4	21.5	19.6	17.8	15.9	16.0	18.1	20.1	22.2	24.3	26.1
95°	86.6	85.6	84.6	83.6	82.6	75.6	62.8	50.0	37.2	24.3	26.1
97.5°	180.9	182.7	184.5	186.4	188.2	176.4	151.0	125.6	100.2	74.8	65.2
100°	253.9	254.9	255.9	256.9	257.9	259.1	260.4	261.9	263.2	264.5	214.2
102.5°	328.1	329.3	330.6	331.9	333.2	334.3	335.1	335.9	336.7	337.5	328.0
105°	447.0	448.3	449.7	451.0	452.3	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	570.4	570.4	570.4	570.4	570.4	570.7	571.4	572.1	572.8	573.4	573.5
110°	650.7	650.7	650.7	650.7	650.7	651.0	651.7	652.4	653.0	653.7	652.7



TEST NUMBER: P333658-840

CATALOG NUMBER: S125RDIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	726.1	726.9	727.7	728.5	729.3	729.9	730.3	730.7	731.1	731.5	730.2
115°	839.2	840.8	842.5	844.2	845.9	846.9	847.3	847.6	848.0	848.3	846.9
117.5°	956.2	956.1	956.0	956.0	955.9	956.5	957.9	959.1	960.4	961.7	959.9
120°	1029.2	1028.9	1028.5	1028.1	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6
122.5°	1093.7	1094.9	1096.2	1097.5	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9
125°	1193.4	1195.7	1198.1	1200.4	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6
127.5°	1288.5	1290.2	1291.9	1293.6	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4
130°	1346.9	1348.6	1350.3	1352.0	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0
132.5°	1405.2	1407.2	1409.2	1411.2	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6
135°	1488.2	1490.3	1492.4	1494.4	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7
137.5°	1564.6	1566.3	1568.1	1569.8	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9
140°	1614.5	1615.2	1615.8	1616.5	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7
142.5°	1659.4	1659.8	1660.2	1660.6	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6
145°	1725.5	1726.1	1726.8	1727.5	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8
147.5°	1783.2	1783.0	1782.9	1782.8	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8
150°	1819.7	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4
152.5°	1854.9	1853.5	1852.0	1850.5	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0
155°	1900.3	1898.2	1896.2	1894.2	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2
157.5°	1935.2	1934.0	1932.8	1931.6	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2
160°	1959.5	1957.5	1955.5	1953.5	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3
162.5°	1979.0	1977.0	1975.0	1972.9	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3
165°	2005.2	2003.2	2001.0	1999.0	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5
167.5°	2024.6	2022.6	2020.4	2018.3	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1
170°	2035.6	2033.2	2030.8	2028.4	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1
172.5°	2042.9	2040.5	2038.1	2035.8	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4
175°	2050.7	2048.7	2046.7	2044.7	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9
177.5°	2054.4	2052.8	2051.1	2049.5	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333658-840

CATALOG NUMBER: S125RDIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	615.8	616.7	617.5	617.9	617.8	617.7	617.6	617.5
5°	612.1	613.1	614.1	614.6	614.4	614.1	613.9	613.7
7.5°	604.4	605.2	605.9	606.1	605.9	605.7	605.5	605.2
10°	598.0	598.3	598.6	598.6	598.3	598.0	597.7	597.4
12.5°	588.9	589.2	589.4	589.3	588.8	588.2	587.8	587.3
15°	573.8	573.7	573.6	573.1	572.2	571.3	570.4	569.4
17.5°	555.1	554.6	554.1	553.4	552.7	551.9	551.1	550.4
20°	541.3	540.8	540.3	539.6	538.6	537.7	536.7	535.8
22.5°	527.6	526.5	525.5	524.6	523.9	523.1	522.4	521.6
25°	505.1	503.7	502.4	501.2	500.0	498.9	497.8	496.6
27.5°	480.8	478.9	477.0	475.5	474.4	473.3	472.2	471.1
30°	463.3	461.0	458.6	457.0	456.0	455.0	454.1	453.2
32.5°	446.5	443.8	441.1	439.3	438.1	436.9	435.7	434.5
35°	420.1	417.1	414.0	411.8	410.4	409.0	407.5	406.1
37.5°	392.5	389.0	385.4	382.8	381.4	380.0	378.6	377.2
40°	374.4	370.4	366.5	363.9	362.6	361.4	360.1	358.9
42.5°	356.4	352.6	348.8	346.1	344.3	342.3	340.5	338.7
45°	327.7	323.6	319.4	316.6	315.1	313.5	311.9	310.3
47.5°	299.4	295.1	290.8	287.8	286.1	284.4	282.7	280.9
50°	280.1	275.8	271.5	268.5	267.0	265.4	263.9	262.3
52.5°	262.0	257.3	252.6	249.4	247.9	246.4	244.8	243.3
55°	234.3	229.6	225.0	221.8	220.2	218.4	216.8	215.2
57.5°	206.6	202.1	197.4	194.4	193.0	191.5	190.1	188.5
60°	188.3	183.7	179.2	176.1	174.5	173.0	171.5	169.9
62.5°	170.3	166.0	161.8	159.0	157.3	155.8	154.3	152.7
65°	143.8	139.7	135.5	132.7	131.2	129.6	128.1	126.4
67.5°	118.6	114.8	111.0	108.5	107.2	106.0	104.7	103.5
70°	101.9	98.7	95.4	93.2	91.9	90.7	89.5	88.2
72.5°	86.2	83.3	80.4	78.5	77.7	76.9	75.9	75.1
75°	64.5	62.2	60.0	58.5	57.8	57.0	56.2	55.5
77.5°	45.9	44.3	42.7	41.6	41.1	40.6	40.0	39.5
80°	34.5	33.6	32.7	32.1	31.9	31.7	31.5	31.3
82.5°	25.9	25.3	24.9	24.6	24.5	24.4	24.3	24.1
85°	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.0
87.5°	11.1	11.5	11.8	12.0	12.1	12.3	12.4	12.5
90°	27.7	29.4	31.1	32.4	33.4	34.4	35.4	36.5
92.5°	27.7	29.4	31.1	32.1	32.6	33.1	33.6	34.0
95°	27.7	29.4	31.1	31.9	31.9	31.9	31.9	31.9
97.5°	55.7	46.3	36.7	31.9	31.9	31.9	31.9	31.9
100°	163.8	113.5	63.2	37.4	36.0	34.6	33.3	31.9
102.5°	318.4	308.9	299.4	283.2	260.1	237.2	214.2	191.3
105°	453.0	453.0	453.0	452.8	452.5	452.2	451.8	451.5
107.5°	573.6	573.6	573.7	573.2	572.2	571.2	570.2	569.2
110°	651.7	650.7	649.6	649.3	649.6	649.9	650.4	650.7



TEST NUMBER: P333658-840

CATALOG NUMBER: S125RDIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	728.9	727.7	726.4	725.5	725.1	724.6	724.1	723.6
115°	845.6	844.2	842.8	841.2	839.2	837.1	835.1	833.0
117.5°	958.2	956.4	954.6	953.3	952.5	951.6	950.7	949.8
120°	1030.9	1030.2	1029.6	1028.3	1026.6	1024.9	1023.3	1021.6
122.5°	1100.1	1099.5	1098.8	1097.5	1095.6	1093.6	1091.7	1089.6
125°	1201.3	1199.9	1198.6	1197.4	1196.4	1195.4	1194.4	1193.4
127.5°	1293.7	1293.0	1292.2	1290.6	1288.1	1285.7	1283.1	1280.6
130°	1354.0	1353.0	1352.0	1350.6	1349.0	1347.3	1345.5	1343.8
132.5°	1410.4	1410.2	1410.0	1409.0	1407.3	1405.6	1403.9	1402.2
135°	1493.0	1492.4	1491.7	1490.3	1488.2	1486.2	1484.2	1482.2
137.5°	1570.0	1570.1	1570.3	1569.5	1567.7	1566.0	1564.2	1562.5
140°	1617.3	1618.0	1618.7	1618.0	1616.0	1614.0	1611.9	1609.9
142.5°	1663.7	1663.9	1664.0	1663.0	1660.9	1658.9	1656.9	1654.9
145°	1729.2	1729.5	1729.8	1729.0	1727.0	1725.0	1722.9	1720.9
147.5°	1785.2	1785.6	1786.0	1785.0	1782.6	1780.2	1777.8	1775.3
150°	1821.0	1821.7	1822.4	1821.4	1818.7	1815.9	1813.3	1810.6
152.5°	1852.7	1853.3	1854.0	1853.1	1850.7	1848.3	1845.8	1843.4
155°	1896.2	1897.2	1898.2	1897.3	1894.7	1892.0	1889.3	1886.5
157.5°	1932.2	1933.3	1934.4	1933.6	1930.9	1928.1	1925.4	1922.8
160°	1954.6	1956.0	1957.3	1956.7	1954.0	1951.3	1948.5	1945.9
162.5°	1975.2	1977.1	1978.9	1978.4	1975.5	1972.5	1969.5	1966.5
165°	2001.6	2003.7	2005.7	2005.3	2002.7	1999.9	1997.2	1994.5
167.5°	2021.5	2024.0	2026.4	2026.1	2023.1	2020.0	2017.0	2014.0
170°	2031.8	2034.6	2037.2	2037.1	2034.1	2031.0	2027.9	2024.9
172.5°	2039.8	2042.3	2044.7	2044.4	2041.3	2038.3	2035.3	2032.3
175°	2048.5	2051.2	2054.0	2053.8	2050.7	2047.7	2044.7	2041.6
177.5°	2052.1	2054.0	2055.9	2055.8	2053.6	2051.4	2049.2	2047.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7

(END OF REPORT)