

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333675-840

Luminaire Tested: **S125RDIW-S610D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333675-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D1340U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7100.8 lumens  
Efficiency: N/A  
Efficacy: 132.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333675-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333675-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	76	65	63	61	50	49	48	37	36	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19
6	61	49	41	36	55	45	38	33	36	31	27	28	25	22	21	19	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	20	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14
9	48	36	29	24	44	33	27	23	27	22	19	22	18	16	16	14	12
10	45	33	26	22	41	30	24	20	25	20	17	20	17	14	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333675-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	1.3
10°-20°	267.0	3.8
20°-30°	387.1	5.5
30°-40°	441.2	6.2
40°-50°	430.0	6.1
50°-60°	362.0	5.1
60°-70°	253.8	3.6
70°-80°	130.4	1.8
80°-90°	36.6	0.5
90°-100°	112.7	1.6
100°-110°	332.9	4.7
110°-120°	563.9	7.9
120°-130°	742.1	10.5
130°-140°	831.6	11.7
140°-150°	815.0	11.5
150°-160°	684.5	9.6
160°-170°	455.0	6.4
170°-180°	159.2	2.2
0°-30°	749.6	10.6
0°-40°	1190.8	16.8
0°-60°	1982.8	27.9
0°-90°	2403.6	33.9
90°-120°	1009.6	14.2
90°-150°	3398.3	47.9
90°-180°	4697.0	66.1
0°-180°	7100.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	12	21	27	31	7
95°	85	88	101	110	113	91
105°	299	305	313	321	325	319
115°	565	570	572	571	570	558
125°	824	831	833	831	829	738
135°	1072	1079	1081	1080	1076	826
145°	1298	1303	1307	1307	1303	811
155°	1486	1486	1487	1491	1486	684
165°	1615	1613	1614	1618	1611	455
175°	1679	1674	1674	1681	1673	160
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333675-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.3	13.9	13.4	12.9	12.4	12.3	12.6	12.8	13.1	13.4	13.7
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4
92.5°	31.7	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2
95°	85.1	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9
97.5°	141.5	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5
100°	183.4	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1
102.5°	228.4	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2
105°	298.7	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9
107.5°	376.2	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7
110°	429.7	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0



TEST NUMBER: P333675-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.1	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9
115°	564.6	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2
117.5°	645.3	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3
120°	695.6	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5
122.5°	750.1	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6
125°	823.9	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5
127.5°	902.5	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3
130°	949.7	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6
132.5°	996.8	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8
135°	1071.6	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8
137.5°	1141.8	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6
140°	1186.8	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9
142.5°	1231.9	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7
145°	1298.2	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4
147.5°	1359.5	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2
150°	1400.4	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3
152.5°	1433.9	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6
155°	1485.5	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9
157.5°	1531.6	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2
160°	1558.8	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4
162.5°	1583.0	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8
165°	1615.2	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1
167.5°	1642.4	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9
170°	1657.1	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7
172.5°	1667.6	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1
175°	1679.4	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9
177.5°	1685.4	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333675-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	13.9	14.2	14.5	14.7	14.7	14.8	14.8	14.8
90°	23.8	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	54.1	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	104.9	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	164.4	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	205.7	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	248.0	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	316.6	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	390.5	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	441.9	442.7	443.6	443.9	443.6	443.3	443.0	442.7





TEST NUMBER: P333675-840

CATALOG NUMBER: S125RDIW-S610D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.3	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.9	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.5	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.4	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.9	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	908.0	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.3	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.5	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.0	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1198.5	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.0	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1366.9	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.2	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1489.1	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1532.4	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1558.5	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1583.2	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1616.2	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1640.7	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1655.4	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1665.9	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1677.6	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1682.9	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)