

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333676-840

Luminaire Tested: **S125RDIW-S610D1560U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333676-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D1560U840-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8722.9 lumens  
Efficiency: N/A  
Efficacy: 143.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	20
3	77	69	62	56	69	62	56	51	49	45	41	36	34	32	25	24	22	17
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	19	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	20	19	17	13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	19	17	15	12
7	55	43	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6035	6035	6035	6035
5°	6944	6043	5337	6043
10°	7965	6013	4709	6013
15°	8603	5951	4186	5951
20°	9487	5880	3865	5880
25°	10979	5784	3587	5784
30°	11946	5684	3404	5684
35°	10078	5568	3236	5568
40°	7038	5359	3092	5359
45°	5221	5076	2951	5076
50°	4163	4784	2829	4784
55°	3533	4418	2721	4418
60°	3052	4093	2547	4093
65°	2720	3741	2193	3741
70°	2391	3427	1998	3427
75°	2069	2969	1876	2969
80°	1570	2499	1570	2499
85°	1312	1964	1482	1964



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.6	1.0
10°-20°	262.6	3.0
20°-30°	416.4	4.8
30°-40°	502.1	5.8
40°-50°	448.4	5.1
50°-60°	343.9	3.9
60°-70°	223.5	2.6
70°-80°	108.6	1.2
80°-90°	30.2	0.3
90°-100°	74.5	0.9
100°-110°	459.3	5.3
110°-120°	833.0	9.5
120°-130°	1069.1	12.3
130°-140°	1149.9	13.2
140°-150°	1079.3	12.4
150°-160°	873.1	10.0
160°-170°	564.7	6.5
170°-180°	194.8	2.2
0°-30°	768.6	8.8
0°-40°	1270.8	14.6
0°-60°	2063.1	23.7
0°-90°	2425.4	27.8
90°-120°	1366.8	15.7
90°-150°	4665.0	53.5
90°-180°	6298.0	72.2
0°-180°	8722.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	934	934	934	934	934	
5°	1071	932	823	932	1071	107
15°	1287	890	626	890	1287	369
25°	1541	812	503	812	1541	707
35°	1278	706	410	706	1278	772
45°	572	556	323	556	572	456
55°	314	392	242	392	314	285
65°	178	245	144	245	178	177
75°	83	119	75	119	83	88
85°	18	26	20	26	18	21
90°	36	2	36	2	36	17
95°	32	87	32	87	32	26
105°	452	447	452	447	452	408
115°	833	839	833	839	833	827
125°	1193	1193	1193	1193	1193	1062
135°	1482	1488	1482	1488	1482	1144
145°	1721	1726	1721	1726	1721	1075
155°	1886	1900	1886	1900	1886	869
165°	1994	2005	1994	2005	1994	563
175°	2042	2051	2042	2051	2042	194
180°	2051	2051	2051	2051	2051	



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	983.0	982.4	983.6	980.2	980.6	975.3	975.3	971.3	966.1	962.1	960.3
5°	1071.1	1071.9	1070.3	1064.5	1060.7	1054.9	1048.4	1036.9	1027.3	1018.1	1010.9
7.5°	1161.7	1162.3	1157.2	1155.5	1145.8	1138.7	1124.3	1108.6	1094.7	1077.0	1063.6
10°	1214.6	1214.2	1208.8	1204.6	1196.1	1185.4	1171.1	1152.8	1135.5	1116.3	1097.9
12.5°	1245.3	1244.3	1242.5	1237.4	1229.6	1220.0	1208.0	1189.9	1168.6	1147.6	1126.2
15°	1286.7	1283.9	1279.0	1272.4	1261.3	1250.2	1236.8	1220.7	1200.3	1176.6	1156.6
17.5°	1337.9	1338.0	1330.3	1321.3	1306.2	1286.5	1265.8	1239.8	1212.1	1186.0	1164.8
20°	1380.3	1379.1	1371.4	1353.8	1336.6	1312.0	1288.2	1256.4	1222.6	1188.4	1162.0
22.5°	1441.0	1438.0	1430.1	1406.8	1380.1	1348.5	1312.1	1273.2	1232.4	1193.7	1158.9
25°	1540.7	1538.3	1522.6	1495.7	1458.1	1409.4	1361.8	1308.5	1249.8	1198.8	1156.6
27.5°	1608.7	1606.2	1594.6	1572.3	1537.5	1486.3	1421.9	1350.7	1277.4	1207.2	1146.3
30°	1601.9	1607.7	1606.2	1595.9	1569.7	1523.7	1464.3	1384.1	1297.0	1214.6	1142.1
32.5°	1505.6	1510.8	1524.3	1544.6	1546.1	1527.7	1483.3	1409.3	1319.1	1225.3	1138.6
35°	1278.2	1285.2	1311.2	1352.2	1405.9	1450.9	1460.1	1420.2	1339.2	1238.3	1133.6
37.5°	982.7	1020.5	1042.4	1085.6	1166.7	1249.3	1328.7	1358.0	1323.5	1232.9	1125.4
40°	834.8	843.9	883.1	931.8	1000.1	1086.0	1199.2	1280.9	1283.5	1220.7	1112.5
42.5°	714.5	726.1	753.0	791.8	850.3	936.2	1053.1	1160.9	1210.8	1186.9	1095.6
45°	571.6	580.4	600.0	629.9	674.8	745.8	846.3	971.0	1070.0	1108.6	1050.4
47.5°	469.6	474.3	491.3	514.1	547.3	599.1	676.8	785.1	903.8	987.0	978.9
50°	414.3	419.7	432.7	450.0	478.0	521.7	583.9	674.0	796.4	898.1	918.4
52.5°	371.3	375.8	384.0	400.3	423.3	457.0	507.2	588.8	698.8	806.9	853.9
55°	313.8	316.9	323.4	332.5	351.0	375.2	418.5	474.9	563.9	672.9	741.9
57.5°	266.4	267.9	272.1	280.5	293.3	310.9	342.2	390.1	453.9	552.0	628.2
60°	236.3	237.8	243.2	248.9	258.9	275.1	299.6	333.0	394.4	475.3	552.4
62.5°	212.4	213.3	215.6	221.4	230.0	242.6	261.9	289.1	337.9	409.0	481.8
65°	178.0	178.3	179.2	183.8	189.1	198.3	211.0	230.1	267.0	320.7	385.2
67.5°	145.0	145.5	148.2	149.9	155.4	160.3	167.7	182.4	208.3	244.5	294.6
70°	126.6	126.2	128.9	130.8	132.7	138.5	143.5	155.3	171.5	199.1	241.0
72.5°	109.4	108.5	109.6	110.3	112.8	116.7	121.7	129.0	141.4	160.5	192.4
75°	82.9	83.2	83.2	84.0	85.9	87.5	89.0	92.8	99.8	112.4	129.7
77.5°	58.2	57.6	59.2	59.4	60.5	62.2	63.5	65.0	67.9	73.1	82.0
80°	42.2	42.2	42.6	43.7	43.3	44.1	46.0	47.6	51.0	54.1	57.2
82.5°	32.4	32.1	32.4	32.7	32.6	33.3	34.0	34.3	35.6	37.2	39.4
85°	17.7	17.7	18.1	18.1	18.4	18.4	18.8	18.8	18.8	19.2	19.6
87.5°	14.0	13.5	13.0	12.8	12.9	13.2	12.6	12.0	11.6	11.3	11.1
90°	36.5	35.4	34.4	33.4	32.4	31.1	29.4	27.7	26.1	24.3	21.9
92.5°	34.0	33.6	33.1	32.6	32.1	31.1	29.4	27.7	26.1	24.3	22.2
95°	31.9	31.9	31.9	31.9	31.9	31.1	29.4	27.7	26.1	24.3	37.2
97.5°	31.9	31.9	31.9	31.9	31.9	36.7	46.3	55.7	65.2	74.8	100.2
100°	31.9	33.3	34.6	36.0	37.4	63.2	113.5	163.8	214.2	264.5	263.2
102.5°	191.3	214.2	237.2	260.1	283.2	299.4	308.9	318.4	328.0	337.5	336.7
105°	451.5	451.8	452.2	452.5	452.8	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	569.2	570.2	571.2	572.2	573.2	573.7	573.6	573.6	573.5	573.4	572.8
110°	650.7	650.4	649.9	649.6	649.3	649.6	650.7	651.7	652.7	653.7	653.0



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	723.6	724.1	724.6	725.1	725.5	726.4	727.7	728.9	730.2	731.5	731.1
115°	833.0	835.1	837.1	839.2	841.2	842.8	844.2	845.6	846.9	848.3	848.0
117.5°	949.8	950.7	951.6	952.5	953.3	954.6	956.4	958.2	959.9	961.7	960.4
120°	1021.6	1023.3	1024.9	1026.6	1028.3	1029.6	1030.2	1030.9	1031.6	1032.2	1031.2
122.5°	1089.6	1091.7	1093.6	1095.6	1097.5	1098.8	1099.5	1100.1	1100.9	1101.6	1101.1
125°	1193.4	1194.4	1195.4	1196.4	1197.4	1198.6	1199.9	1201.3	1202.6	1204.0	1204.0
127.5°	1280.6	1283.1	1285.7	1288.1	1290.6	1292.2	1293.0	1293.7	1294.4	1295.3	1295.5
130°	1343.8	1345.5	1347.3	1349.0	1350.6	1352.0	1353.0	1354.0	1355.0	1356.0	1355.6
132.5°	1402.2	1403.9	1405.6	1407.3	1409.0	1410.0	1410.2	1410.4	1410.6	1410.8	1411.5
135°	1482.2	1484.2	1486.2	1488.2	1490.3	1491.7	1492.4	1493.0	1493.7	1494.4	1495.0
137.5°	1562.5	1564.2	1566.0	1567.7	1569.5	1570.3	1570.1	1570.0	1569.9	1569.7	1570.3
140°	1609.9	1611.9	1614.0	1616.0	1618.0	1618.7	1618.0	1617.3	1616.7	1616.0	1616.3
142.5°	1654.9	1656.9	1658.9	1660.9	1663.0	1664.0	1663.9	1663.7	1663.6	1663.4	1662.9
145°	1720.9	1722.9	1725.0	1727.0	1729.0	1729.8	1729.5	1729.2	1728.8	1728.5	1728.5
147.5°	1775.3	1777.8	1780.2	1782.6	1785.0	1786.0	1785.6	1785.2	1784.8	1784.4	1784.0
150°	1810.6	1813.3	1815.9	1818.7	1821.4	1822.4	1821.7	1821.0	1820.4	1819.7	1819.0
152.5°	1843.4	1845.8	1848.3	1850.7	1853.1	1854.0	1853.3	1852.7	1852.0	1851.3	1850.7
155°	1886.5	1889.3	1892.0	1894.7	1897.3	1898.2	1897.2	1896.2	1895.2	1894.2	1893.5
157.5°	1922.8	1925.4	1928.1	1930.9	1933.6	1934.4	1933.3	1932.2	1931.2	1930.1	1930.0
160°	1945.9	1948.5	1951.3	1954.0	1956.7	1957.3	1956.0	1954.6	1953.3	1952.0	1951.6
162.5°	1966.5	1969.5	1972.5	1975.5	1978.4	1978.9	1977.1	1975.2	1973.3	1971.4	1971.1
165°	1994.5	1997.2	1999.9	2002.7	2005.3	2005.7	2003.7	2001.6	1999.5	1997.5	1997.2
167.5°	2014.0	2017.0	2020.0	2023.1	2026.1	2026.4	2024.0	2021.5	2019.1	2016.7	2016.4
170°	2024.9	2027.9	2031.0	2034.1	2037.1	2037.2	2034.6	2031.8	2029.1	2026.4	2026.1
172.5°	2032.3	2035.3	2038.3	2041.3	2044.4	2044.7	2042.3	2039.8	2037.4	2035.0	2034.4
175°	2041.6	2044.7	2047.7	2050.7	2053.8	2054.0	2051.2	2048.5	2045.9	2043.2	2042.9
177.5°	2047.1	2049.2	2051.4	2053.6	2055.8	2055.9	2054.0	2052.1	2050.2	2048.3	2048.0
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	960.3	958.2	954.1	950.5	945.8	941.9	939.1	935.7	931.4	926.2	921.9
5°	1002.8	994.3	983.2	973.6	961.4	951.8	941.8	932.2	922.6	910.3	899.6
7.5°	1049.9	1032.5	1015.5	994.2	974.8	957.6	941.0	924.2	907.8	890.4	873.5
10°	1078.7	1057.6	1034.2	1007.3	982.8	959.5	938.0	916.9	894.6	875.0	853.9
12.5°	1105.7	1078.5	1051.8	1017.8	988.4	959.8	932.4	906.2	882.3	857.0	834.2
15°	1130.1	1103.3	1073.4	1032.0	990.9	956.3	924.1	890.0	860.5	832.0	806.8
17.5°	1139.5	1111.5	1076.6	1036.8	992.0	948.6	907.1	869.6	834.9	801.7	773.3
20°	1135.9	1108.6	1073.0	1035.0	987.0	941.8	896.9	855.5	816.7	781.8	751.5
22.5°	1127.0	1098.8	1064.4	1024.3	978.8	930.7	882.8	838.6	798.0	761.8	728.8
25°	1113.7	1075.3	1040.0	1000.9	957.6	910.0	860.5	811.7	768.4	731.5	695.5
27.5°	1099.7	1051.9	1007.0	968.1	922.3	879.9	832.1	782.2	736.6	699.1	662.2
30°	1087.2	1033.5	984.0	939.9	896.6	856.3	810.9	762.2	715.5	676.7	639.1
32.5°	1071.6	1014.4	960.1	909.2	867.4	827.4	786.4	739.8	694.3	654.3	616.1
35°	1051.9	979.0	919.9	865.9	819.4	780.6	743.9	706.2	660.6	619.1	582.0
37.5°	1026.1	943.4	875.0	816.1	767.2	728.2	699.2	664.8	623.2	583.5	549.0
40°	1010.5	917.7	842.8	784.5	733.1	692.1	664.8	635.6	597.6	560.5	525.9
42.5°	989.6	894.0	810.3	749.5	697.8	658.3	630.8	605.3	573.4	538.4	501.4
45°	948.7	848.2	760.3	695.1	643.0	604.2	578.5	555.8	531.7	499.5	467.3
47.5°	895.4	800.4	708.4	637.2	586.1	550.2	525.2	507.4	490.1	462.7	431.4
50°	852.8	761.1	671.4	602.3	547.9	513.6	490.3	476.1	460.3	435.5	409.3
52.5°	802.4	720.6	632.7	562.1	510.7	478.7	456.2	442.0	429.0	408.7	383.8
55°	723.2	651.4	570.8	506.8	459.6	427.4	405.9	392.4	384.8	367.5	347.9
57.5°	631.6	580.2	509.2	447.4	405.7	373.8	358.1	346.7	338.0	325.8	311.9
60°	567.7	531.7	468.0	409.3	370.9	340.6	326.5	316.9	308.8	298.4	287.7
62.5°	503.0	476.8	421.4	370.9	335.7	310.2	297.0	288.3	279.0	272.1	261.7
65°	416.3	392.8	354.5	315.0	282.4	262.1	252.5	244.8	239.0	231.4	224.0
67.5°	323.8	314.3	287.8	260.5	237.1	219.0	210.8	205.4	198.4	193.9	188.8
70°	267.0	262.4	243.6	225.6	203.7	191.5	183.8	181.5	173.0	168.4	164.9
72.5°	216.7	214.5	203.7	191.2	175.8	165.0	157.9	155.3	150.0	146.3	144.1
75°	148.5	149.3	147.3	139.3	133.5	126.6	120.5	119.0	115.1	112.0	110.1
77.5°	93.9	97.9	98.0	97.6	95.3	91.1	88.6	87.4	83.6	82.5	82.0
80°	64.4	68.7	72.5	72.1	71.4	70.2	68.3	67.2	65.2	64.0	63.3
82.5°	42.9	46.9	50.1	52.2	52.0	50.9	49.6	49.0	48.7	47.8	47.7
85°	20.3	21.1	22.2	24.9	26.9	27.3	26.9	26.5	25.3	25.8	26.1
87.5°	11.0	10.5	10.3	9.8	9.0	10.0	10.4	10.1	10.1	10.0	9.9
90°	19.6	17.3	14.8	12.3	9.6	7.0	4.2	1.5	4.2	7.0	9.6
92.5°	20.1	18.1	16.0	15.9	17.8	19.6	21.5	23.4	21.5	19.6	17.8
95°	50.0	62.8	75.6	82.6	83.6	84.6	85.6	86.6	85.6	84.6	83.6
97.5°	125.6	151.0	176.4	188.2	186.4	184.5	182.7	180.9	182.7	184.5	186.4
100°	261.9	260.4	259.1	257.9	256.9	255.9	254.9	253.9	254.9	255.9	256.9
102.5°	335.9	335.1	334.3	333.2	331.9	330.6	329.3	328.1	329.3	330.6	331.9
105°	453.0	453.0	453.0	452.3	451.0	449.7	448.3	447.0	448.3	449.7	451.0
107.5°	572.1	571.4	570.7	570.4	570.4	570.4	570.4	570.4	570.4	570.4	570.4
110°	652.4	651.7	651.0	650.7	650.7	650.7	650.7	650.7	650.7	650.7	650.7





TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	730.7	730.3	729.9	729.3	728.5	727.7	726.9	726.1	726.9	727.7	728.5
115°	847.6	847.3	846.9	845.9	844.2	842.5	840.8	839.2	840.8	842.5	844.2
117.5°	959.1	957.9	956.5	955.9	956.0	956.0	956.1	956.2	956.1	956.0	956.0
120°	1030.2	1029.2	1028.1	1027.8	1028.1	1028.5	1028.9	1029.2	1028.9	1028.5	1028.1
122.5°	1100.6	1100.1	1099.6	1098.7	1097.5	1096.2	1094.9	1093.7	1094.9	1096.2	1097.5
125°	1204.0	1204.0	1204.0	1202.9	1200.4	1198.1	1195.7	1193.4	1195.7	1198.1	1200.4
127.5°	1295.7	1295.9	1296.1	1295.3	1293.6	1291.9	1290.2	1288.5	1290.2	1291.9	1293.6
130°	1355.3	1355.0	1354.6	1353.6	1352.0	1350.3	1348.6	1346.9	1348.6	1350.3	1352.0
132.5°	1412.2	1413.0	1413.7	1413.1	1411.2	1409.2	1407.2	1405.2	1407.2	1409.2	1411.2
135°	1495.7	1496.4	1497.0	1496.4	1494.4	1492.4	1490.3	1488.2	1490.3	1492.4	1494.4
137.5°	1570.9	1571.6	1572.2	1571.7	1569.8	1568.1	1566.3	1564.6	1566.3	1568.1	1569.8
140°	1616.7	1617.0	1617.3	1617.2	1616.5	1615.8	1615.2	1614.5	1615.2	1615.8	1616.5
142.5°	1662.4	1662.0	1661.5	1661.0	1660.6	1660.2	1659.8	1659.4	1659.8	1660.2	1660.6
145°	1728.5	1728.5	1728.5	1728.2	1727.5	1726.8	1726.1	1725.5	1726.1	1726.8	1727.5
147.5°	1783.6	1783.2	1782.8	1782.6	1782.8	1782.9	1783.0	1783.2	1783.0	1782.9	1782.8
150°	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1819.0	1818.4	1817.7
152.5°	1850.0	1849.3	1848.6	1849.0	1850.5	1852.0	1853.5	1854.9	1853.5	1852.0	1850.5
155°	1892.8	1892.2	1891.5	1892.2	1894.2	1896.2	1898.2	1900.3	1898.2	1896.2	1894.2
157.5°	1930.0	1929.9	1929.8	1930.4	1931.6	1932.8	1934.0	1935.2	1934.0	1932.8	1931.6
160°	1951.3	1951.0	1950.6	1951.5	1953.5	1955.5	1957.5	1959.5	1957.5	1955.5	1953.5
162.5°	1970.8	1970.3	1970.0	1970.9	1972.9	1975.0	1977.0	1979.0	1977.0	1975.0	1972.9
165°	1996.9	1996.5	1996.2	1997.0	1999.0	2001.0	2003.2	2005.2	2003.2	2001.0	1999.0
167.5°	2016.0	2015.7	2015.4	2016.2	2018.3	2020.4	2022.6	2024.6	2022.6	2020.4	2018.3
170°	2025.8	2025.4	2025.1	2026.1	2028.4	2030.8	2033.2	2035.6	2033.2	2030.8	2028.4
172.5°	2033.8	2033.2	2032.6	2033.4	2035.8	2038.1	2040.5	2042.9	2040.5	2038.1	2035.8
175°	2042.5	2042.1	2041.8	2042.7	2044.7	2046.7	2048.7	2050.7	2048.7	2046.7	2044.7
177.5°	2047.8	2047.5	2047.2	2047.9	2049.5	2051.1	2052.8	2054.4	2052.8	2051.1	2049.5
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	918.9	914.5	911.5	905.3	901.0	899.2	895.9	894.9	898.3	895.9	895.5
5°	891.5	880.4	871.6	862.7	853.1	847.1	837.8	836.3	833.9	830.5	829.8
7.5°	858.8	844.2	832.9	818.3	805.7	795.5	784.0	778.5	775.5	771.0	765.1
10°	836.7	819.4	804.1	789.5	773.8	761.1	749.6	740.7	735.0	729.6	727.3
12.5°	814.9	797.3	777.7	760.0	742.5	728.2	715.5	709.7	703.4	697.1	691.8
15°	781.0	757.6	736.2	715.8	700.8	685.5	673.3	664.8	655.2	652.6	642.2
17.5°	745.2	722.2	697.0	675.6	658.3	641.4	627.9	618.3	611.1	601.2	596.4
20°	722.8	695.5	671.0	651.4	632.2	612.3	598.4	590.4	583.5	575.4	571.6
22.5°	698.8	672.2	647.0	624.1	604.6	584.9	575.1	566.7	559.0	551.5	546.4
25°	663.7	636.8	610.4	586.5	566.2	552.0	540.5	530.9	526.7	519.4	514.0
27.5°	628.9	600.4	572.9	549.2	533.2	519.2	509.8	502.2	494.5	488.2	483.5
30°	606.5	577.3	547.4	528.7	511.7	498.4	488.0	480.7	474.9	469.2	465.7
32.5°	584.1	554.0	527.5	507.2	491.2	479.6	469.0	461.9	455.9	449.5	445.5
35°	548.2	517.5	496.0	476.1	460.3	449.6	442.3	432.3	427.4	422.7	418.5
37.5°	514.8	486.3	463.0	445.6	431.9	421.2	411.8	406.4	400.3	396.2	392.6
40°	490.3	464.1	443.1	424.6	414.7	402.8	393.9	387.1	382.4	377.1	373.2
42.5°	468.2	443.9	423.4	406.9	394.5	384.4	375.9	369.0	363.1	359.3	356.1
45°	437.0	412.7	392.8	377.5	366.0	356.4	347.6	344.1	336.4	331.8	330.3
47.5°	404.7	383.0	363.8	349.6	337.8	328.7	320.4	313.5	309.2	304.7	302.3
50°	382.8	362.1	344.1	330.3	318.8	308.8	301.1	296.5	290.7	286.6	283.5
52.5°	361.0	341.8	323.9	310.6	300.6	290.7	282.2	277.5	272.1	269.3	267.2
55°	329.9	309.6	294.3	281.1	270.8	261.7	253.6	248.9	245.5	242.9	242.1
57.5°	294.6	278.5	264.3	252.5	241.8	233.1	226.0	221.7	218.6	218.2	215.9
60°	271.6	257.0	244.0	231.4	222.1	214.1	207.9	203.0	199.9	199.4	198.7
62.5°	248.6	234.6	222.5	211.4	203.1	195.3	189.6	183.9	182.1	180.2	178.4
65°	214.4	201.8	191.8	183.0	174.2	167.6	161.9	158.4	154.2	151.9	147.7
67.5°	180.9	171.1	161.5	154.1	147.1	141.0	136.2	131.1	128.3	126.3	123.3
70°	158.9	151.2	141.6	133.5	128.2	123.1	119.3	113.5	111.6	110.1	108.6
72.5°	137.9	131.2	123.1	116.6	111.3	106.5	102.1	99.5	97.6	95.9	95.0
75°	108.6	102.0	95.1	90.5	86.7	82.9	80.6	78.7	77.9	77.5	75.9
77.5°	79.7	76.2	70.7	67.1	64.5	63.0	60.9	59.9	59.9	58.2	57.7
80°	61.0	59.1	54.4	52.9	51.0	49.5	48.4	46.5	44.5	43.7	42.6
82.5°	45.3	43.4	41.6	39.1	37.6	36.6	35.4	34.7	34.9	33.9	33.3
85°	24.1	22.2	21.5	21.1	20.3	21.1	20.7	20.3	20.0	19.6	20.0
87.5°	10.1	10.6	10.8	11.9	11.4	12.2	12.5	12.6	12.9	13.2	13.2
90°	12.3	14.8	17.3	19.6	21.9	24.3	26.1	27.7	29.4	31.1	32.4
92.5°	15.9	16.0	18.1	20.1	22.2	24.3	26.1	27.7	29.4	31.1	32.1
95°	82.6	75.6	62.8	50.0	37.2	24.3	26.1	27.7	29.4	31.1	31.9
97.5°	188.2	176.4	151.0	125.6	100.2	74.8	65.2	55.7	46.3	36.7	31.9
100°	257.9	259.1	260.4	261.9	263.2	264.5	214.2	163.8	113.5	63.2	37.4
102.5°	333.2	334.3	335.1	335.9	336.7	337.5	328.0	318.4	308.9	299.4	283.2
105°	452.3	453.0	453.0	453.0	453.0	453.0	453.0	453.0	453.0	453.0	452.8
107.5°	570.4	570.7	571.4	572.1	572.8	573.4	573.5	573.6	573.6	573.7	573.2
110°	650.7	651.0	651.7	652.4	653.0	653.7	652.7	651.7	650.7	649.6	649.3



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	729.3	729.9	730.3	730.7	731.1	731.5	730.2	728.9	727.7	726.4	725.5
115°	845.9	846.9	847.3	847.6	848.0	848.3	846.9	845.6	844.2	842.8	841.2
117.5°	955.9	956.5	957.9	959.1	960.4	961.7	959.9	958.2	956.4	954.6	953.3
120°	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6	1030.9	1030.2	1029.6	1028.3
122.5°	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9	1100.1	1099.5	1098.8	1097.5
125°	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6	1201.3	1199.9	1198.6	1197.4
127.5°	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4	1293.7	1293.0	1292.2	1290.6
130°	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0	1354.0	1353.0	1352.0	1350.6
132.5°	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6	1410.4	1410.2	1410.0	1409.0
135°	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7	1493.0	1492.4	1491.7	1490.3
137.5°	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9	1570.0	1570.1	1570.3	1569.5
140°	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7	1617.3	1618.0	1618.7	1618.0
142.5°	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6	1663.7	1663.9	1664.0	1663.0
145°	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8	1729.2	1729.5	1729.8	1729.0
147.5°	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8	1785.2	1785.6	1786.0	1785.0
150°	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4	1821.0	1821.7	1822.4	1821.4
152.5°	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0	1852.7	1853.3	1854.0	1853.1
155°	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2	1896.2	1897.2	1898.2	1897.3
157.5°	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2	1932.2	1933.3	1934.4	1933.6
160°	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3	1954.6	1956.0	1957.3	1956.7
162.5°	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3	1975.2	1977.1	1978.9	1978.4
165°	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5	2001.6	2003.7	2005.7	2005.3
167.5°	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1	2021.5	2024.0	2026.4	2026.1
170°	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1	2031.8	2034.6	2037.2	2037.1
172.5°	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4	2039.8	2042.3	2044.7	2044.4
175°	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9	2048.5	2051.2	2054.0	2053.8
177.5°	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2	2052.1	2054.0	2055.9	2055.8
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.2	891.8	890.9	892.1	890.9	891.8	895.2	895.5	895.9	898.3	894.9
5°	826.0	822.1	824.0	823.2	824.0	822.1	826.0	829.8	830.5	833.9	836.3
7.5°	765.0	760.2	755.2	756.8	755.2	760.2	765.0	765.1	771.0	775.5	778.5
10°	722.4	718.5	716.2	718.1	716.2	718.5	722.4	727.3	729.6	735.0	740.7
12.5°	686.4	684.2	682.2	681.4	682.2	684.2	686.4	691.8	697.1	703.4	709.7
15°	637.5	633.0	631.1	626.1	631.1	633.0	637.5	642.2	652.6	655.2	664.8
17.5°	592.5	591.0	586.0	583.9	586.0	591.0	592.5	596.4	601.2	611.1	618.3
20°	565.8	564.3	559.4	562.4	559.4	564.3	565.8	571.6	575.4	583.5	590.4
22.5°	543.7	540.4	538.8	537.9	538.8	540.4	543.7	546.4	551.5	559.0	566.7
25°	512.5	507.6	505.6	503.3	505.6	507.6	512.5	514.0	519.4	526.7	530.9
27.5°	481.4	478.7	476.2	475.5	476.2	478.7	481.4	483.5	488.2	494.5	502.2
30°	461.1	458.4	456.5	456.5	456.5	458.4	461.1	465.7	469.2	474.9	480.7
32.5°	443.0	440.9	439.0	438.7	439.0	440.9	443.0	445.5	449.5	455.9	461.9
35°	416.6	413.5	412.7	410.5	412.7	413.5	416.6	418.5	422.7	427.4	432.3
37.5°	389.2	386.7	386.6	386.4	386.6	386.7	389.2	392.6	396.2	400.3	406.4
40°	371.7	369.8	369.4	366.8	369.4	369.8	371.7	373.2	377.1	382.4	387.1
42.5°	353.0	352.0	350.7	349.5	350.7	352.0	353.0	356.1	359.3	363.1	369.0
45°	327.6	325.0	325.0	323.1	325.0	325.0	327.6	330.3	331.8	336.4	344.1
47.5°	301.3	299.3	299.5	297.5	299.5	299.3	301.3	302.3	304.7	309.2	313.5
50°	283.9	282.8	282.4	281.6	282.4	282.8	283.9	283.5	286.6	290.7	296.5
52.5°	266.4	265.9	267.3	265.6	267.3	265.9	266.4	267.2	269.3	272.1	277.5
55°	242.9	241.7	244.0	241.7	244.0	241.7	242.9	242.1	242.9	245.5	248.9
57.5°	215.7	214.7	216.7	215.6	216.7	214.7	215.7	215.9	218.2	218.6	221.7
60°	197.9	195.6	196.8	197.2	196.8	195.6	197.9	198.7	199.4	199.9	203.0
62.5°	176.7	175.4	176.2	174.5	176.2	175.4	176.7	178.4	180.2	182.1	183.9
65°	146.9	145.8	144.2	143.5	144.2	145.8	146.9	147.7	151.9	154.2	158.4
67.5°	123.4	120.7	120.6	121.2	120.6	120.7	123.4	123.3	126.3	128.3	131.1
70°	106.2	106.2	105.8	105.8	105.8	106.2	106.2	108.6	110.1	111.6	113.5
72.5°	94.3	94.0	93.3	93.0	93.3	94.0	94.3	95.0	95.9	97.6	99.5
75°	75.9	76.3	75.5	75.2	75.5	76.3	75.9	75.9	77.5	77.9	78.7
77.5°	56.0	54.4	55.3	54.4	55.3	54.4	56.0	57.7	58.2	59.9	59.9
80°	42.6	42.2	43.3	42.2	43.3	42.2	42.6	42.6	43.7	44.5	46.5
82.5°	33.7	33.3	33.8	33.0	33.8	33.3	33.7	33.3	33.9	34.9	34.7
85°	20.3	20.0	19.6	20.0	19.6	20.0	20.3	20.0	19.6	20.0	20.3
87.5°	13.7	13.6	13.8	14.0	13.8	13.6	13.7	13.2	13.2	12.9	12.6
90°	33.4	34.4	35.4	36.5	35.4	34.4	33.4	32.4	31.1	29.4	27.7
92.5°	32.6	33.1	33.6	34.0	33.6	33.1	32.6	32.1	31.1	29.4	27.7
95°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.1	29.4	27.7
97.5°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	36.7	46.3	55.7
100°	36.0	34.6	33.3	31.9	33.3	34.6	36.0	37.4	63.2	113.5	163.8
102.5°	260.1	237.2	214.2	191.3	214.2	237.2	260.1	283.2	299.4	308.9	318.4
105°	452.5	452.2	451.8	451.5	451.8	452.2	452.5	452.8	453.0	453.0	453.0
107.5°	572.2	571.2	570.2	569.2	570.2	571.2	572.2	573.2	573.7	573.6	573.6
110°	649.6	649.9	650.4	650.7	650.4	649.9	649.6	649.3	649.6	650.7	651.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	725.1	724.6	724.1	723.6	724.1	724.6	725.1	725.5	726.4	727.7	728.9
115°	839.2	837.1	835.1	833.0	835.1	837.1	839.2	841.2	842.8	844.2	845.6
117.5°	952.5	951.6	950.7	949.8	950.7	951.6	952.5	953.3	954.6	956.4	958.2
120°	1026.6	1024.9	1023.3	1021.6	1023.3	1024.9	1026.6	1028.3	1029.6	1030.2	1030.9
122.5°	1095.6	1093.6	1091.7	1089.6	1091.7	1093.6	1095.6	1097.5	1098.8	1099.5	1100.1
125°	1196.4	1195.4	1194.4	1193.4	1194.4	1195.4	1196.4	1197.4	1198.6	1199.9	1201.3
127.5°	1288.1	1285.7	1283.1	1280.6	1283.1	1285.7	1288.1	1290.6	1292.2	1293.0	1293.7
130°	1349.0	1347.3	1345.5	1343.8	1345.5	1347.3	1349.0	1350.6	1352.0	1353.0	1354.0
132.5°	1407.3	1405.6	1403.9	1402.2	1403.9	1405.6	1407.3	1409.0	1410.0	1410.2	1410.4
135°	1488.2	1486.2	1484.2	1482.2	1484.2	1486.2	1488.2	1490.3	1491.7	1492.4	1493.0
137.5°	1567.7	1566.0	1564.2	1562.5	1564.2	1566.0	1567.7	1569.5	1570.3	1570.1	1570.0
140°	1616.0	1614.0	1611.9	1609.9	1611.9	1614.0	1616.0	1618.0	1618.7	1618.0	1617.3
142.5°	1660.9	1658.9	1656.9	1654.9	1656.9	1658.9	1660.9	1663.0	1664.0	1663.9	1663.7
145°	1727.0	1725.0	1722.9	1720.9	1722.9	1725.0	1727.0	1729.0	1729.8	1729.5	1729.2
147.5°	1782.6	1780.2	1777.8	1775.3	1777.8	1780.2	1782.6	1785.0	1786.0	1785.6	1785.2
150°	1818.7	1815.9	1813.3	1810.6	1813.3	1815.9	1818.7	1821.4	1822.4	1821.7	1821.0
152.5°	1850.7	1848.3	1845.8	1843.4	1845.8	1848.3	1850.7	1853.1	1854.0	1853.3	1852.7
155°	1894.7	1892.0	1889.3	1886.5	1889.3	1892.0	1894.7	1897.3	1898.2	1897.2	1896.2
157.5°	1930.9	1928.1	1925.4	1922.8	1925.4	1928.1	1930.9	1933.6	1934.4	1933.3	1932.2
160°	1954.0	1951.3	1948.5	1945.9	1948.5	1951.3	1954.0	1956.7	1957.3	1956.0	1954.6
162.5°	1975.5	1972.5	1969.5	1966.5	1969.5	1972.5	1975.5	1978.4	1978.9	1977.1	1975.2
165°	2002.7	1999.9	1997.2	1994.5	1997.2	1999.9	2002.7	2005.3	2005.7	2003.7	2001.6
167.5°	2023.1	2020.0	2017.0	2014.0	2017.0	2020.0	2023.1	2026.1	2026.4	2024.0	2021.5
170°	2034.1	2031.0	2027.9	2024.9	2027.9	2031.0	2034.1	2037.1	2037.2	2034.6	2031.8
172.5°	2041.3	2038.3	2035.3	2032.3	2035.3	2038.3	2041.3	2044.4	2044.7	2042.3	2039.8
175°	2050.7	2047.7	2044.7	2041.6	2044.7	2047.7	2050.7	2053.8	2054.0	2051.2	2048.5
177.5°	2053.6	2051.4	2049.2	2047.1	2049.2	2051.4	2053.6	2055.8	2055.9	2054.0	2052.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.9	899.2	901.0	905.3	911.5	914.5	918.9	921.9	926.2	931.4	935.7
5°	837.8	847.1	853.1	862.7	871.6	880.4	891.5	899.6	910.3	922.6	932.2
7.5°	784.0	795.5	805.7	818.3	832.9	844.2	858.8	873.5	890.4	907.8	924.2
10°	749.6	761.1	773.8	789.5	804.1	819.4	836.7	853.9	875.0	894.6	916.9
12.5°	715.5	728.2	742.5	760.0	777.7	797.3	814.9	834.2	857.0	882.3	906.2
15°	673.3	685.5	700.8	715.8	736.2	757.6	781.0	806.8	832.0	860.5	890.0
17.5°	627.9	641.4	658.3	675.6	697.0	722.2	745.2	773.3	801.7	834.9	869.6
20°	598.4	612.3	632.2	651.4	671.0	695.5	722.8	751.5	781.8	816.7	855.5
22.5°	575.1	584.9	604.6	624.1	647.0	672.2	698.8	728.8	761.8	798.0	838.6
25°	540.5	552.0	566.2	586.5	610.4	636.8	663.7	695.5	731.5	768.4	811.7
27.5°	509.8	519.2	533.2	549.2	572.9	600.4	628.9	662.2	699.1	736.6	782.2
30°	488.0	498.4	511.7	528.7	547.4	577.3	606.5	639.1	676.7	715.5	762.2
32.5°	469.0	479.6	491.2	507.2	527.5	554.0	584.1	616.1	654.3	694.3	739.8
35°	442.3	449.6	460.3	476.1	496.0	517.5	548.2	582.0	619.1	660.6	706.2
37.5°	411.8	421.2	431.9	445.6	463.0	486.3	514.8	549.0	583.5	623.2	664.8
40°	393.9	402.8	414.7	424.6	443.1	464.1	490.3	525.9	560.5	597.6	635.6
42.5°	375.9	384.4	394.5	406.9	423.4	443.9	468.2	501.4	538.4	573.4	605.3
45°	347.6	356.4	366.0	377.5	392.8	412.7	437.0	467.3	499.5	531.7	555.8
47.5°	320.4	328.7	337.8	349.6	363.8	383.0	404.7	431.4	462.7	490.1	507.4
50°	301.1	308.8	318.8	330.3	344.1	362.1	382.8	409.3	435.5	460.3	476.1
52.5°	282.2	290.7	300.6	310.6	323.9	341.8	361.0	383.8	408.7	429.0	442.0
55°	253.6	261.7	270.8	281.1	294.3	309.6	329.9	347.9	367.5	384.8	392.4
57.5°	226.0	233.1	241.8	252.5	264.3	278.5	294.6	311.9	325.8	338.0	346.7
60°	207.9	214.1	222.1	231.4	244.0	257.0	271.6	287.7	298.4	308.8	316.9
62.5°	189.6	195.3	203.1	211.4	222.5	234.6	248.6	261.7	272.1	279.0	288.3
65°	161.9	167.6	174.2	183.0	191.8	201.8	214.4	224.0	231.4	239.0	244.8
67.5°	136.2	141.0	147.1	154.1	161.5	171.1	180.9	188.8	193.9	198.4	205.4
70°	119.3	123.1	128.2	133.5	141.6	151.2	158.9	164.9	168.4	173.0	181.5
72.5°	102.1	106.5	111.3	116.6	123.1	131.2	137.9	144.1	146.3	150.0	155.3
75°	80.6	82.9	86.7	90.5	95.1	102.0	108.6	110.1	112.0	115.1	119.0
77.5°	60.9	63.0	64.5	67.1	70.7	76.2	79.7	82.0	82.5	83.6	87.4
80°	48.4	49.5	51.0	52.9	54.4	59.1	61.0	63.3	64.0	65.2	67.2
82.5°	35.4	36.6	37.6	39.1	41.6	43.4	45.3	47.7	47.8	48.7	49.0
85°	20.7	21.1	20.3	21.1	21.5	22.2	24.1	26.1	25.8	25.3	26.5
87.5°	12.5	12.2	11.4	11.9	10.8	10.6	10.1	9.9	10.0	10.1	10.1
90°	26.1	24.3	21.9	19.6	17.3	14.8	12.3	9.6	7.0	4.2	1.5
92.5°	26.1	24.3	22.2	20.1	18.1	16.0	15.9	17.8	19.6	21.5	23.4
95°	26.1	24.3	37.2	50.0	62.8	75.6	82.6	83.6	84.6	85.6	86.6
97.5°	65.2	74.8	100.2	125.6	151.0	176.4	188.2	186.4	184.5	182.7	180.9
100°	214.2	264.5	263.2	261.9	260.4	259.1	257.9	256.9	255.9	254.9	253.9
102.5°	328.0	337.5	336.7	335.9	335.1	334.3	333.2	331.9	330.6	329.3	328.1
105°	453.0	453.0	453.0	453.0	453.0	453.0	452.3	451.0	449.7	448.3	447.0
107.5°	573.5	573.4	572.8	572.1	571.4	570.7	570.4	570.4	570.4	570.4	570.4
110°	652.7	653.7	653.0	652.4	651.7	651.0	650.7	650.7	650.7	650.7	650.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	730.2	731.5	731.1	730.7	730.3	729.9	729.3	728.5	727.7	726.9	726.1
115°	846.9	848.3	848.0	847.6	847.3	846.9	845.9	844.2	842.5	840.8	839.2
117.5°	959.9	961.7	960.4	959.1	957.9	956.5	955.9	956.0	956.0	956.1	956.2
120°	1031.6	1032.2	1031.2	1030.2	1029.2	1028.1	1027.8	1028.1	1028.5	1028.9	1029.2
122.5°	1100.9	1101.6	1101.1	1100.6	1100.1	1099.6	1098.7	1097.5	1096.2	1094.9	1093.7
125°	1202.6	1204.0	1204.0	1204.0	1204.0	1204.0	1202.9	1200.4	1198.1	1195.7	1193.4
127.5°	1294.4	1295.3	1295.5	1295.7	1295.9	1296.1	1295.3	1293.6	1291.9	1290.2	1288.5
130°	1355.0	1356.0	1355.6	1355.3	1355.0	1354.6	1353.6	1352.0	1350.3	1348.6	1346.9
132.5°	1410.6	1410.8	1411.5	1412.2	1413.0	1413.7	1413.1	1411.2	1409.2	1407.2	1405.2
135°	1493.7	1494.4	1495.0	1495.7	1496.4	1497.0	1496.4	1494.4	1492.4	1490.3	1488.2
137.5°	1569.9	1569.7	1570.3	1570.9	1571.6	1572.2	1571.7	1569.8	1568.1	1566.3	1564.6
140°	1616.7	1616.0	1616.3	1616.7	1617.0	1617.3	1617.2	1616.5	1615.8	1615.2	1614.5
142.5°	1663.6	1663.4	1662.9	1662.4	1662.0	1661.5	1661.0	1660.6	1660.2	1659.8	1659.4
145°	1728.8	1728.5	1728.5	1728.5	1728.5	1728.5	1728.2	1727.5	1726.8	1726.1	1725.5
147.5°	1784.8	1784.4	1784.0	1783.6	1783.2	1782.8	1782.6	1782.8	1782.9	1783.0	1783.2
150°	1820.4	1819.7	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7
152.5°	1852.0	1851.3	1850.7	1850.0	1849.3	1848.6	1849.0	1850.5	1852.0	1853.5	1854.9
155°	1895.2	1894.2	1893.5	1892.8	1892.2	1891.5	1892.2	1894.2	1896.2	1898.2	1900.3
157.5°	1931.2	1930.1	1930.0	1930.0	1929.9	1929.8	1930.4	1931.6	1932.8	1934.0	1935.2
160°	1953.3	1952.0	1951.6	1951.3	1951.0	1950.6	1951.5	1953.5	1955.5	1957.5	1959.5
162.5°	1973.3	1971.4	1971.1	1970.8	1970.3	1970.0	1970.9	1972.9	1975.0	1977.0	1979.0
165°	1999.5	1997.5	1997.2	1996.9	1996.5	1996.2	1997.0	1999.0	2001.0	2003.2	2005.2
167.5°	2019.1	2016.7	2016.4	2016.0	2015.7	2015.4	2016.2	2018.3	2020.4	2022.6	2024.6
170°	2029.1	2026.4	2026.1	2025.8	2025.4	2025.1	2026.1	2028.4	2030.8	2033.2	2035.6
172.5°	2037.4	2035.0	2034.4	2033.8	2033.2	2032.6	2033.4	2035.8	2038.1	2040.5	2042.9
175°	2045.9	2043.2	2042.9	2042.5	2042.1	2041.8	2042.7	2044.7	2046.7	2048.7	2050.7
177.5°	2050.2	2048.3	2048.0	2047.8	2047.5	2047.2	2047.9	2049.5	2051.1	2052.8	2054.4
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	939.1	941.9	945.8	950.5	954.1	958.2	960.3	960.3	962.1	966.1	971.3
5°	941.8	951.8	961.4	973.6	983.2	994.3	1002.8	1010.9	1018.1	1027.3	1036.9
7.5°	941.0	957.6	974.8	994.2	1015.5	1032.5	1049.9	1063.6	1077.0	1094.7	1108.6
10°	938.0	959.5	982.8	1007.3	1034.2	1057.6	1078.7	1097.9	1116.3	1135.5	1152.8
12.5°	932.4	959.8	988.4	1017.8	1051.8	1078.5	1105.7	1126.2	1147.6	1168.6	1189.9
15°	924.1	956.3	990.9	1032.0	1073.4	1103.3	1130.1	1156.6	1176.6	1200.3	1220.7
17.5°	907.1	948.6	992.0	1036.8	1076.6	1111.5	1139.5	1164.8	1186.0	1212.1	1239.8
20°	896.9	941.8	987.0	1035.0	1073.0	1108.6	1135.9	1162.0	1188.4	1222.6	1256.4
22.5°	882.8	930.7	978.8	1024.3	1064.4	1098.8	1127.0	1158.9	1193.7	1232.4	1273.2
25°	860.5	910.0	957.6	1000.9	1040.0	1075.3	1113.7	1156.6	1198.8	1249.8	1308.5
27.5°	832.1	879.9	922.3	968.1	1007.0	1051.9	1099.7	1146.3	1207.2	1277.4	1350.7
30°	810.9	856.3	896.6	939.9	984.0	1033.5	1087.2	1142.1	1214.6	1297.0	1384.1
32.5°	786.4	827.4	867.4	909.2	960.1	1014.4	1071.6	1138.6	1225.3	1319.1	1409.3
35°	743.9	780.6	819.4	865.9	919.9	979.0	1051.9	1133.6	1238.3	1339.2	1420.2
37.5°	699.2	728.2	767.2	816.1	875.0	943.4	1026.1	1125.4	1232.9	1323.5	1358.0
40°	664.8	692.1	733.1	784.5	842.8	917.7	1010.5	1112.5	1220.7	1283.5	1280.9
42.5°	630.8	658.3	697.8	749.5	810.3	894.0	989.6	1095.6	1186.9	1210.8	1160.9
45°	578.5	604.2	643.0	695.1	760.3	848.2	948.7	1050.4	1108.6	1070.0	971.0
47.5°	525.2	550.2	586.1	637.2	708.4	800.4	895.4	978.9	987.0	903.8	785.1
50°	490.3	513.6	547.9	602.3	671.4	761.1	852.8	918.4	898.1	796.4	674.0
52.5°	456.2	478.7	510.7	562.1	632.7	720.6	802.4	853.9	806.9	698.8	588.8
55°	405.9	427.4	459.6	506.8	570.8	651.4	723.2	741.9	672.9	563.9	474.9
57.5°	358.1	373.8	405.7	447.4	509.2	580.2	631.6	628.2	552.0	453.9	390.1
60°	326.5	340.6	370.9	409.3	468.0	531.7	567.7	552.4	475.3	394.4	333.0
62.5°	297.0	310.2	335.7	370.9	421.4	476.8	503.0	481.8	409.0	337.9	289.1
65°	252.5	262.1	282.4	315.0	354.5	392.8	416.3	385.2	320.7	267.0	230.1
67.5°	210.8	219.0	237.1	260.5	287.8	314.3	323.8	294.6	244.5	208.3	182.4
70°	183.8	191.5	203.7	225.6	243.6	262.4	267.0	241.0	199.1	171.5	155.3
72.5°	157.9	165.0	175.8	191.2	203.7	214.5	216.7	192.4	160.5	141.4	129.0
75°	120.5	126.6	133.5	139.3	147.3	149.3	148.5	129.7	112.4	99.8	92.8
77.5°	88.6	91.1	95.3	97.6	98.0	97.9	93.9	82.0	73.1	67.9	65.0
80°	68.3	70.2	71.4	72.1	72.5	68.7	64.4	57.2	54.1	51.0	47.6
82.5°	49.6	50.9	52.0	52.2	50.1	46.9	42.9	39.4	37.2	35.6	34.3
85°	26.9	27.3	26.9	24.9	22.2	21.1	20.3	19.6	19.2	18.8	18.8
87.5°	10.4	10.0	9.0	9.8	10.3	10.5	11.0	11.1	11.3	11.6	12.0
90°	4.2	7.0	9.6	12.3	14.8	17.3	19.6	21.9	24.3	26.1	27.7
92.5°	21.5	19.6	17.8	15.9	16.0	18.1	20.1	22.2	24.3	26.1	27.7
95°	85.6	84.6	83.6	82.6	75.6	62.8	50.0	37.2	24.3	26.1	27.7
97.5°	182.7	184.5	186.4	188.2	176.4	151.0	125.6	100.2	74.8	65.2	55.7
100°	254.9	255.9	256.9	257.9	259.1	260.4	261.9	263.2	264.5	214.2	163.8
102.5°	329.3	330.6	331.9	333.2	334.3	335.1	335.9	336.7	337.5	328.0	318.4
105°	448.3	449.7	451.0	452.3	453.0	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	570.4	570.4	570.4	570.4	570.7	571.4	572.1	572.8	573.4	573.5	573.6
110°	650.7	650.7	650.7	650.7	651.0	651.7	652.4	653.0	653.7	652.7	651.7





TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	726.9	727.7	728.5	729.3	729.9	730.3	730.7	731.1	731.5	730.2	728.9
115°	840.8	842.5	844.2	845.9	846.9	847.3	847.6	848.0	848.3	846.9	845.6
117.5°	956.1	956.0	956.0	955.9	956.5	957.9	959.1	960.4	961.7	959.9	958.2
120°	1028.9	1028.5	1028.1	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6	1030.9
122.5°	1094.9	1096.2	1097.5	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9	1100.1
125°	1195.7	1198.1	1200.4	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6	1201.3
127.5°	1290.2	1291.9	1293.6	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4	1293.7
130°	1348.6	1350.3	1352.0	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0	1354.0
132.5°	1407.2	1409.2	1411.2	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6	1410.4
135°	1490.3	1492.4	1494.4	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7	1493.0
137.5°	1566.3	1568.1	1569.8	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9	1570.0
140°	1615.2	1615.8	1616.5	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7	1617.3
142.5°	1659.8	1660.2	1660.6	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6	1663.7
145°	1726.1	1726.8	1727.5	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8	1729.2
147.5°	1783.0	1782.9	1782.8	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8	1785.2
150°	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4	1821.0
152.5°	1853.5	1852.0	1850.5	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0	1852.7
155°	1898.2	1896.2	1894.2	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2	1896.2
157.5°	1934.0	1932.8	1931.6	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2	1932.2
160°	1957.5	1955.5	1953.5	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3	1954.6
162.5°	1977.0	1975.0	1972.9	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3	1975.2
165°	2003.2	2001.0	1999.0	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5	2001.6
167.5°	2022.6	2020.4	2018.3	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1	2021.5
170°	2033.2	2030.8	2028.4	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1	2031.8
172.5°	2040.5	2038.1	2035.8	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4	2039.8
175°	2048.7	2046.7	2044.7	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9	2048.5
177.5°	2052.8	2051.1	2049.5	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2	2052.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	975.3	975.3	980.6	980.2	983.6	982.4	983.0
5°	1048.4	1054.9	1060.7	1064.5	1070.3	1071.9	1071.1
7.5°	1124.3	1138.7	1145.8	1155.5	1157.2	1162.3	1161.7
10°	1171.1	1185.4	1196.1	1204.6	1208.8	1214.2	1214.6
12.5°	1208.0	1220.0	1229.6	1237.4	1242.5	1244.3	1245.3
15°	1236.8	1250.2	1261.3	1272.4	1279.0	1283.9	1286.7
17.5°	1265.8	1286.5	1306.2	1321.3	1330.3	1338.0	1337.9
20°	1288.2	1312.0	1336.6	1353.8	1371.4	1379.1	1380.3
22.5°	1312.1	1348.5	1380.1	1406.8	1430.1	1438.0	1441.0
25°	1361.8	1409.4	1458.1	1495.7	1522.6	1538.3	1540.7
27.5°	1421.9	1486.3	1537.5	1572.3	1594.6	1606.2	1608.7
30°	1464.3	1523.7	1569.7	1595.9	1606.2	1607.7	1601.9
32.5°	1483.3	1527.7	1546.1	1544.6	1524.3	1510.8	1505.6
35°	1460.1	1450.9	1405.9	1352.2	1311.2	1285.2	1278.2
37.5°	1328.7	1249.3	1166.7	1085.6	1042.4	1020.5	982.7
40°	1199.2	1086.0	1000.1	931.8	883.1	843.9	834.8
42.5°	1053.1	936.2	850.3	791.8	753.0	726.1	714.5
45°	846.3	745.8	674.8	629.9	600.0	580.4	571.6
47.5°	676.8	599.1	547.3	514.1	491.3	474.3	469.6
50°	583.9	521.7	478.0	450.0	432.7	419.7	414.3
52.5°	507.2	457.0	423.3	400.3	384.0	375.8	371.3
55°	418.5	375.2	351.0	332.5	323.4	316.9	313.8
57.5°	342.2	310.9	293.3	280.5	272.1	267.9	266.4
60°	299.6	275.1	258.9	248.9	243.2	237.8	236.3
62.5°	261.9	242.6	230.0	221.4	215.6	213.3	212.4
65°	211.0	198.3	189.1	183.8	179.2	178.3	178.0
67.5°	167.7	160.3	155.4	149.9	148.2	145.5	145.0
70°	143.5	138.5	132.7	130.8	128.9	126.2	126.6
72.5°	121.7	116.7	112.8	110.3	109.6	108.5	109.4
75°	89.0	87.5	85.9	84.0	83.2	83.2	82.9
77.5°	63.5	62.2	60.5	59.4	59.2	57.6	58.2
80°	46.0	44.1	43.3	43.7	42.6	42.2	42.2
82.5°	34.0	33.3	32.6	32.7	32.4	32.1	32.4
85°	18.8	18.4	18.4	18.1	18.1	17.7	17.7
87.5°	12.6	13.2	12.9	12.8	13.0	13.5	14.0
90°	29.4	31.1	32.4	33.4	34.4	35.4	36.5
92.5°	29.4	31.1	32.1	32.6	33.1	33.6	34.0
95°	29.4	31.1	31.9	31.9	31.9	31.9	31.9
97.5°	46.3	36.7	31.9	31.9	31.9	31.9	31.9
100°	113.5	63.2	37.4	36.0	34.6	33.3	31.9
102.5°	308.9	299.4	283.2	260.1	237.2	214.2	191.3
105°	453.0	453.0	452.8	452.5	452.2	451.8	451.5
107.5°	573.6	573.7	573.2	572.2	571.2	570.2	569.2
110°	650.7	649.6	649.3	649.6	649.9	650.4	650.7



TEST NUMBER: P333676-840

CATALOG NUMBER: S125RDIW-S610D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	727.7	726.4	725.5	725.1	724.6	724.1	723.6
115°	844.2	842.8	841.2	839.2	837.1	835.1	833.0
117.5°	956.4	954.6	953.3	952.5	951.6	950.7	949.8
120°	1030.2	1029.6	1028.3	1026.6	1024.9	1023.3	1021.6
122.5°	1099.5	1098.8	1097.5	1095.6	1093.6	1091.7	1089.6
125°	1199.9	1198.6	1197.4	1196.4	1195.4	1194.4	1193.4
127.5°	1293.0	1292.2	1290.6	1288.1	1285.7	1283.1	1280.6
130°	1353.0	1352.0	1350.6	1349.0	1347.3	1345.5	1343.8
132.5°	1410.2	1410.0	1409.0	1407.3	1405.6	1403.9	1402.2
135°	1492.4	1491.7	1490.3	1488.2	1486.2	1484.2	1482.2
137.5°	1570.1	1570.3	1569.5	1567.7	1566.0	1564.2	1562.5
140°	1618.0	1618.7	1618.0	1616.0	1614.0	1611.9	1609.9
142.5°	1663.9	1664.0	1663.0	1660.9	1658.9	1656.9	1654.9
145°	1729.5	1729.8	1729.0	1727.0	1725.0	1722.9	1720.9
147.5°	1785.6	1786.0	1785.0	1782.6	1780.2	1777.8	1775.3
150°	1821.7	1822.4	1821.4	1818.7	1815.9	1813.3	1810.6
152.5°	1853.3	1854.0	1853.1	1850.7	1848.3	1845.8	1843.4
155°	1897.2	1898.2	1897.3	1894.7	1892.0	1889.3	1886.5
157.5°	1933.3	1934.4	1933.6	1930.9	1928.1	1925.4	1922.8
160°	1956.0	1957.3	1956.7	1954.0	1951.3	1948.5	1945.9
162.5°	1977.1	1978.9	1978.4	1975.5	1972.5	1969.5	1966.5
165°	2003.7	2005.7	2005.3	2002.7	1999.9	1997.2	1994.5
167.5°	2024.0	2026.4	2026.1	2023.1	2020.0	2017.0	2014.0
170°	2034.6	2037.2	2037.1	2034.1	2031.0	2027.9	2024.9
172.5°	2042.3	2044.7	2044.4	2041.3	2038.3	2035.3	2032.3
175°	2051.2	2054.0	2053.8	2050.7	2047.7	2044.7	2041.6
177.5°	2054.0	2055.9	2055.8	2053.6	2051.4	2049.2	2047.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7

(END OF REPORT)