

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333699-840

Luminaire Tested: **S125RDIW-S850D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333699-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8746.0 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333699-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333699-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	72	62	54	49	65	57	50	45	46	42	38	37	33	31	28	26	24	20
5	66	55	47	42	60	50	44	38	41	36	32	33	29	27	25	23	21	17
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333699-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	1.5
10°-20°	364.9	4.2
20°-30°	529.2	6.1
30°-40°	603.1	6.9
40°-50°	587.8	6.7
50°-60°	494.8	5.7
60°-70°	346.9	4.0
70°-80°	178.3	2.0
80°-90°	49.3	0.6
90°-100°	131.1	1.5
100°-110°	387.1	4.4
110°-120°	655.6	7.5
120°-130°	862.9	9.9
130°-140°	966.8	11.1
140°-150°	947.6	10.8
150°-160°	795.9	9.1
160°-170°	529.1	6.0
170°-180°	185.2	2.1
0°-30°	1024.6	11.7
0°-40°	1627.7	18.6
0°-60°	2710.4	31.0
0°-90°	3284.8	37.6
90°-120°	1173.8	13.4
90°-150°	3951.1	45.2
90°-180°	5461.0	62.4
0°-180°	8746.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	2	14	24	32	37	8
95°	99	103	117	128	131	106
105°	347	355	364	373	378	371
115°	656	662	666	664	663	649
125°	958	967	969	966	964	858
135°	1246	1255	1256	1256	1250	960
145°	1509	1515	1520	1520	1515	943
155°	1727	1727	1729	1734	1727	795
165°	1878	1875	1876	1882	1873	530
175°	1953	1947	1946	1954	1945	185
180°	1957	1957	1957	1957	1957	



TEST NUMBER: P333699-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.6	18.9	18.1	17.3	16.6	16.4	16.6	16.9	17.2	17.5	17.8
90°	1.5	4.2	7.0	9.7	12.3	14.8	17.3	19.6	22.0	24.3	26.1
92.5°	36.9	38.8	40.7	42.5	44.4	46.9	49.8	52.6	55.5	58.5	60.7
95°	99.0	99.7	100.4	101.0	101.7	103.7	107.1	110.5	113.9	117.2	119.7
97.5°	164.5	164.7	165.0	165.3	165.6	168.0	172.7	177.4	182.1	186.7	188.9
100°	213.2	213.2	213.2	213.2	213.2	215.4	219.8	224.2	228.6	233.0	236.1
102.5°	265.6	267.0	268.3	269.6	271.0	272.9	275.1	277.3	279.5	281.8	285.1
105°	347.3	348.9	350.6	352.3	354.1	355.9	357.9	359.9	361.9	364.1	366.1
107.5°	437.4	439.1	440.8	442.5	444.1	445.9	447.4	448.9	450.5	452.0	453.0
110°	499.6	501.3	502.9	504.6	506.3	507.7	508.7	509.7	510.7	511.7	512.7



TEST NUMBER: P333699-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	562.9	563.8	564.7	565.5	566.4	567.5	568.8	570.1	571.4	572.7	573.1
115°	656.4	657.8	659.1	660.5	661.9	662.9	663.6	664.2	664.9	665.6	665.2
117.5°	750.2	750.8	751.4	752.0	752.7	753.3	753.9	754.5	755.1	755.8	756.0
120°	808.7	810.4	812.1	813.9	815.5	816.5	816.9	817.2	817.5	817.9	817.9
122.5°	872.1	872.7	873.3	873.9	874.5	875.3	876.2	877.1	877.9	878.8	878.5
125°	958.0	960.0	962.1	964.1	966.1	967.3	967.7	968.0	968.4	968.7	968.0
127.5°	1049.4	1050.6	1051.7	1052.8	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0
130°	1104.2	1105.9	1107.6	1109.2	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5
132.5°	1159.0	1161.8	1164.6	1167.4	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5
135°	1245.9	1247.9	1249.9	1251.9	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5
137.5°	1327.5	1329.5	1331.4	1333.3	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1
140°	1379.9	1381.6	1383.2	1384.9	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7
142.5°	1432.3	1433.7	1435.1	1436.5	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8
145°	1509.3	1510.7	1512.1	1513.4	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9
147.5°	1580.6	1581.3	1582.1	1582.9	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4
150°	1628.1	1627.8	1627.5	1627.1	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7
152.5°	1667.1	1667.6	1668.1	1668.5	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5
155°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0
157.5°	1780.7	1780.0	1779.3	1778.5	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3
160°	1812.4	1811.4	1810.4	1809.4	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7
162.5°	1840.5	1839.7	1839.0	1838.3	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1
165°	1877.9	1877.2	1876.5	1875.9	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7
167.5°	1909.6	1908.2	1906.9	1905.5	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5
170°	1926.6	1925.3	1923.9	1922.6	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6
172.5°	1938.8	1937.5	1936.1	1934.8	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8
175°	1952.6	1951.2	1949.8	1948.4	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4
177.5°	1959.5	1958.4	1957.4	1956.3	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333699-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	18.2	18.5	18.8	19.0	19.0	19.0	19.1	19.1
90°	27.8	29.5	31.1	32.5	33.5	34.5	35.5	36.6
92.5°	62.9	65.1	67.5	68.9	69.7	70.4	71.1	71.9
95°	122.0	124.4	126.7	128.3	129.0	129.7	130.3	131.0
97.5°	191.2	193.4	195.6	197.0	197.4	197.8	198.2	198.6
100°	239.1	242.2	245.2	247.1	247.7	248.4	249.1	249.7
102.5°	288.4	291.8	295.0	297.2	298.1	299.0	300.0	300.9
105°	368.1	370.1	372.1	373.7	374.7	375.7	376.7	377.7
107.5°	454.0	455.0	456.1	456.6	456.5	456.5	456.4	456.3
110°	513.8	514.8	515.8	516.1	515.8	515.4	515.1	514.8



TEST NUMBER: P333699-840

CATALOG NUMBER: S125RDIW-S850D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	573.6	574.1	574.5	574.5	573.9	573.3	572.7	572.1
115°	664.9	664.6	664.2	663.9	663.6	663.2	662.9	662.6
117.5°	756.3	756.6	756.8	756.3	754.9	753.6	752.2	750.8
120°	817.9	817.9	817.9	817.2	815.9	814.5	813.1	811.8
122.5°	878.3	878.0	877.7	877.1	876.0	874.8	873.7	872.7
125°	967.3	966.6	965.9	965.4	965.1	964.7	964.4	964.1
127.5°	1055.7	1055.4	1055.0	1054.5	1053.8	1053.2	1052.5	1051.8
130°	1114.2	1113.9	1113.5	1113.0	1112.4	1111.7	1111.0	1110.3
132.5°	1170.2	1169.9	1169.5	1168.9	1168.0	1167.0	1166.1	1165.1
135°	1256.5	1256.5	1256.5	1255.9	1254.5	1253.1	1251.7	1250.4
137.5°	1340.5	1340.9	1341.3	1340.7	1339.0	1337.3	1335.5	1333.8
140°	1393.4	1394.1	1394.7	1394.2	1392.6	1390.9	1389.2	1387.5
142.5°	1445.2	1445.6	1446.1	1445.4	1443.7	1442.1	1440.4	1438.7
145°	1519.9	1519.9	1519.9	1519.4	1518.4	1517.4	1516.4	1515.4
147.5°	1589.2	1590.0	1590.8	1590.1	1587.8	1585.5	1583.3	1580.9
150°	1632.7	1632.7	1632.7	1632.3	1631.6	1631.0	1630.3	1629.6
152.5°	1673.3	1674.2	1675.0	1674.8	1673.5	1672.3	1671.1	1669.9
155°	1731.3	1732.7	1734.0	1733.9	1732.2	1730.5	1728.8	1727.2
157.5°	1781.6	1783.0	1784.3	1783.9	1781.6	1779.4	1777.2	1774.9
160°	1812.1	1813.4	1814.8	1814.6	1812.9	1811.2	1809.6	1807.9
162.5°	1840.7	1842.3	1843.9	1843.7	1841.8	1839.8	1837.9	1835.8
165°	1879.1	1880.5	1881.8	1881.5	1879.5	1877.4	1875.4	1873.3
167.5°	1907.5	1909.6	1911.6	1911.6	1909.5	1907.4	1905.3	1903.2
170°	1924.6	1926.6	1928.6	1928.5	1926.1	1923.8	1921.4	1919.0
172.5°	1936.8	1938.8	1940.9	1940.9	1938.7	1936.6	1934.5	1932.5
175°	1950.6	1952.6	1954.6	1954.4	1952.1	1949.6	1947.3	1944.9
177.5°	1956.7	1958.3	1959.9	1959.8	1957.9	1956.0	1954.1	1952.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1

(END OF REPORT)