

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333442-940

Luminaire Tested: **S125DIW-S1090D1050U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333442-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1050U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7739.8 lumens
Efficiency: N/A
Efficacy: 126.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	82	76	71	83	77	71	67	65	61	58	55	52	50	45	44	42	37
3	82	73	65	60	76	68	61	56	58	53	49	49	45	42	40	38	36	32
4	75	64	57	51	69	60	53	48	51	46	42	44	40	36	36	33	31	27
5	69	57	49	43	64	54	46	41	46	41	36	39	35	32	33	30	27	24
6	64	52	43	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	33	54	43	36	31	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	22	19	17
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9158	9158	9158	9158
5°	10605	9189	8045	9189
10°	12338	9141	7050	9141
15°	13658	9074	6503	9074
20°	15289	8968	6064	8968
25°	17910	8848	5850	8848
30°	19345	8730	5665	8730
35°	15906	8508	5542	8508
40°	11306	8200	5409	8200
45°	8685	7784	5332	7784
50°	7414	7268	5322	7268
55°	6600	6764	5368	6764
60°	5955	6212	5504	6212
65°	5500	5656	5647	5656
70°	5000	5080	5729	5080
75°	4414	4474	5677	4474
80°	3715	3649	5192	3649
85°	2942	2631	4187	2631



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	1.8
10°-20°	406.4	5.3
20°-30°	660.0	8.5
30°-40°	805.0	10.4
40°-50°	732.3	9.5
50°-60°	583.3	7.5
60°-70°	406.3	5.2
70°-80°	216.7	2.8
80°-90°	57.2	0.7
90°-100°	44.2	0.6
100°-110°	272.5	3.5
110°-120°	494.2	6.4
120°-130°	634.2	8.2
130°-140°	682.1	8.8
140°-150°	640.3	8.3
150°-160°	517.9	6.7
160°-170°	335.0	4.3
170°-180°	115.5	1.5
0°-30°	1202.9	15.5
0°-40°	2008.0	25.9
0°-60°	3323.6	42.9
0°-90°	4003.8	51.7
90°-120°	810.9	10.5
90°-150°	2767.5	35.8
90°-180°	3736.0	48.3
0°-180°	7739.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1636	1417	1241	1417	1636	165
15°	2043	1357	973	1357	2043	585
25°	2513	1242	821	1242	2513	1148
35°	2017	1079	703	1079	2017	1235
45°	951	852	584	852	951	761
55°	586	601	477	601	586	528
65°	360	370	370	370	360	357
75°	177	179	228	179	177	191
85°	40	36	56	36	40	46
90°	22	1	22	1	22	11
95°	19	51	19	51	19	16
105°	268	265	268	265	268	242
115°	494	498	494	498	494	491
125°	708	708	708	708	708	630
135°	879	883	879	883	879	679
145°	1021	1024	1021	1024	1021	638
155°	1119	1127	1119	1127	1119	516
165°	1183	1190	1183	1190	1183	334
175°	1211	1217	1211	1217	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1499.9	1497.9	1496.0	1492.1	1495.0	1486.8	1483.0	1476.2	1468.0	1465.2	1461.8
5°	1635.8	1638.9	1641.9	1629.2	1630.4	1622.0	1602.8	1587.1	1574.5	1558.2	1546.8
7.5°	1799.6	1792.4	1791.9	1783.7	1769.6	1758.3	1738.0	1712.3	1687.4	1658.9	1635.5
10°	1881.4	1882.0	1876.6	1867.0	1851.9	1841.1	1814.6	1789.3	1758.6	1722.5	1696.7
12.5°	1943.0	1945.5	1938.8	1925.7	1918.3	1894.1	1873.4	1843.3	1806.8	1777.9	1738.6
15°	2042.7	2036.1	2031.3	2015.0	2002.4	1977.1	1944.0	1912.7	1872.9	1836.3	1799.6
17.5°	2138.8	2144.0	2135.0	2120.2	2081.0	2051.5	2007.1	1964.3	1914.8	1865.5	1821.7
20°	2224.5	2229.3	2215.5	2189.6	2142.6	2113.2	2054.8	1999.4	1942.2	1879.0	1830.9
22.5°	2331.4	2327.5	2308.8	2269.5	2228.8	2174.3	2111.1	2043.7	1972.0	1900.7	1836.7
25°	2513.4	2488.1	2476.6	2428.0	2374.4	2294.3	2207.6	2108.9	2019.8	1925.4	1843.5
27.5°	2614.2	2606.3	2593.5	2559.6	2503.3	2417.7	2315.5	2195.2	2069.6	1950.3	1843.2
30°	2594.0	2595.2	2596.4	2585.6	2549.5	2485.1	2383.4	2254.0	2104.7	1970.5	1846.5
32.5°	2414.9	2436.8	2457.7	2482.5	2492.7	2480.3	2416.6	2299.7	2146.1	1993.6	1844.6
35°	2017.4	2024.1	2092.0	2159.5	2250.9	2322.0	2369.5	2317.7	2188.3	2013.2	1842.3
37.5°	1573.1	1605.5	1652.6	1728.8	1860.8	1979.1	2131.1	2201.0	2159.3	2019.6	1838.1
40°	1341.0	1371.0	1401.8	1479.3	1590.7	1733.9	1906.7	2054.1	2088.5	1999.4	1823.6
42.5°	1161.8	1185.7	1219.8	1278.1	1371.2	1498.1	1663.0	1855.7	1974.3	1940.6	1793.3
45°	950.9	966.0	992.5	1038.8	1106.3	1205.5	1351.2	1561.8	1745.4	1806.2	1721.4
47.5°	814.0	813.9	834.5	866.5	915.1	999.4	1107.1	1272.2	1468.3	1613.4	1606.6
50°	737.9	734.9	751.1	778.8	817.3	873.3	976.2	1108.0	1296.4	1460.7	1506.5
52.5°	672.4	672.8	682.8	703.2	735.5	783.3	860.1	979.0	1140.0	1308.6	1394.7
55°	586.2	583.8	595.2	609.1	632.6	663.9	719.3	810.1	940.7	1106.8	1218.8
57.5°	507.2	513.9	518.4	528.1	547.6	568.6	615.2	681.9	785.5	928.1	1046.4
60°	461.0	467.6	471.3	480.9	496.5	514.6	550.7	604.8	692.1	814.9	932.3
62.5°	419.6	424.8	426.0	434.6	447.5	465.0	493.4	539.0	607.9	715.2	830.2
65°	359.9	359.9	362.3	371.3	377.4	393.0	414.6	447.8	503.2	586.8	684.9
67.5°	302.4	305.2	304.7	308.6	314.1	326.4	341.9	369.2	410.2	471.3	549.7
70°	264.8	267.2	266.6	269.7	275.6	283.5	296.1	322.0	351.5	403.9	471.3
72.5°	231.1	232.1	230.5	234.5	238.1	245.0	259.0	272.9	300.4	344.6	400.0
75°	176.9	178.2	179.3	181.7	185.4	189.0	196.2	210.1	228.1	261.2	296.8
77.5°	132.7	130.4	133.2	132.9	134.9	137.7	144.1	151.4	166.2	187.2	214.6
80°	99.9	100.5	100.5	101.1	104.2	105.9	111.4	116.7	128.2	143.8	163.1
82.5°	72.9	74.5	73.6	74.6	77.1	78.5	81.5	86.0	92.6	104.9	118.8
85°	39.7	36.7	37.9	39.1	39.1	39.7	42.1	44.0	47.5	52.3	57.8
87.5°	15.9	16.8	17.1	16.9	17.3	17.2	18.9	18.7	20.0	21.2	22.8
90°	21.7	21.0	20.4	19.9	19.3	18.5	17.5	16.4	15.4	14.4	13.0
92.5°	20.2	19.9	19.6	19.4	19.1	18.5	17.5	16.4	15.4	14.4	13.2
95°	18.9	18.9	18.9	18.9	18.9	18.5	17.5	16.4	15.4	14.4	22.0
97.5°	18.9	18.9	18.9	18.9	18.9	21.8	27.4	33.1	38.7	44.4	59.5
100°	18.9	19.7	20.5	21.3	22.1	37.5	67.3	97.2	127.1	156.9	156.1
102.5°	113.4	127.1	140.7	154.4	168.0	177.6	183.2	188.9	194.6	200.2	199.7
105°	267.9	268.0	268.2	268.5	268.7	268.8	268.8	268.8	268.8	268.8	268.8
107.5°	337.7	338.2	338.9	339.5	340.1	340.4	340.3	340.3	340.2	340.2	339.7
110°	386.0	385.8	385.6	385.4	385.2	385.4	386.0	386.6	387.2	387.8	387.4



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	429.3	429.5	429.8	430.2	430.4	431.0	431.7	432.5	433.2	434.0	433.7
115°	494.2	495.4	496.6	497.8	499.0	500.0	500.8	501.6	502.4	503.2	503.0
117.5°	563.5	564.0	564.5	565.1	565.5	566.3	567.4	568.5	569.4	570.5	569.7
120°	606.0	607.1	608.1	609.0	610.0	610.7	611.2	611.5	612.0	612.3	611.7
122.5°	646.5	647.6	648.8	650.0	651.1	651.8	652.3	652.6	653.1	653.4	653.2
125°	707.9	708.6	709.2	709.8	710.3	711.1	711.9	712.7	713.5	714.3	714.3
127.5°	759.7	761.2	762.7	764.2	765.6	766.6	767.0	767.5	767.9	768.4	768.5
130°	797.3	798.3	799.2	800.2	801.2	802.0	802.6	803.3	803.9	804.4	804.2
132.5°	831.9	832.9	833.8	834.9	835.9	836.4	836.5	836.7	836.8	837.0	837.3
135°	879.3	880.5	881.7	882.9	884.1	884.9	885.3	885.7	886.1	886.5	886.9
137.5°	926.9	928.0	929.0	930.1	931.1	931.6	931.5	931.4	931.3	931.2	931.6
140°	955.0	956.3	957.4	958.7	959.8	960.3	959.8	959.5	959.0	958.7	958.9
142.5°	981.8	982.9	984.2	985.3	986.6	987.1	987.0	986.9	986.9	986.8	986.5
145°	1020.9	1022.1	1023.3	1024.5	1025.7	1026.2	1026.0	1025.8	1025.6	1025.4	1025.4
147.5°	1053.2	1054.6	1056.1	1057.5	1059.0	1059.5	1059.4	1059.1	1058.8	1058.5	1058.4
150°	1074.1	1075.7	1077.3	1078.9	1080.5	1081.1	1080.8	1080.3	1080.0	1079.5	1079.1
152.5°	1093.6	1095.0	1096.4	1097.9	1099.4	1099.8	1099.5	1099.0	1098.7	1098.2	1097.9
155°	1119.2	1120.8	1122.4	1124.0	1125.6	1126.1	1125.5	1124.9	1124.3	1123.7	1123.3
157.5°	1140.7	1142.3	1143.9	1145.5	1147.1	1147.5	1146.9	1146.3	1145.7	1145.0	1145.0
160°	1154.4	1156.0	1157.6	1159.2	1160.7	1161.2	1160.4	1159.6	1158.8	1158.0	1157.8
162.5°	1166.6	1168.4	1170.2	1171.9	1173.7	1174.0	1172.9	1171.8	1170.6	1169.5	1169.3
165°	1183.2	1184.8	1186.4	1188.0	1189.6	1189.8	1188.7	1187.4	1186.2	1185.0	1184.8
167.5°	1194.8	1196.6	1198.4	1200.2	1202.0	1202.2	1200.7	1199.3	1197.8	1196.4	1196.2
170°	1201.2	1203.1	1204.9	1206.7	1208.4	1208.6	1207.0	1205.4	1203.8	1202.2	1201.9
172.5°	1205.6	1207.4	1209.2	1211.0	1212.8	1213.0	1211.6	1210.1	1208.6	1207.2	1206.8
175°	1211.2	1213.0	1214.8	1216.6	1218.4	1218.5	1216.9	1215.3	1213.7	1212.1	1211.9
177.5°	1214.4	1215.8	1217.0	1218.3	1219.6	1219.7	1218.5	1217.4	1216.3	1215.1	1215.0
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1458.9	1455.5	1451.7	1444.9	1436.7	1432.4	1425.7	1421.4	1412.6	1405.4	1397.8
5°	1532.9	1517.3	1502.9	1484.2	1463.7	1450.5	1434.9	1417.4	1399.4	1380.6	1360.2
7.5°	1609.6	1581.9	1551.8	1519.5	1487.8	1458.7	1430.8	1403.6	1378.0	1347.2	1321.1
10°	1661.2	1626.2	1588.9	1545.0	1502.3	1464.9	1427.0	1393.9	1360.2	1324.1	1292.2
12.5°	1712.6	1666.2	1613.5	1565.2	1513.8	1468.7	1424.2	1381.9	1339.5	1299.6	1262.3
15°	1749.0	1708.1	1659.3	1590.7	1532.9	1471.0	1411.9	1357.2	1306.0	1261.5	1214.6
17.5°	1773.0	1720.2	1667.9	1602.0	1526.3	1457.0	1390.2	1327.5	1269.8	1213.4	1168.1
20°	1777.3	1723.1	1668.4	1603.9	1526.3	1446.9	1380.1	1304.8	1242.9	1184.5	1129.1
22.5°	1775.8	1714.5	1654.8	1588.6	1512.9	1439.7	1358.9	1282.2	1215.0	1157.5	1099.7
25°	1762.3	1696.7	1622.0	1555.2	1480.6	1402.9	1321.1	1241.6	1173.0	1107.4	1050.3
27.5°	1751.0	1665.8	1581.4	1503.4	1431.4	1360.2	1281.8	1200.5	1124.4	1057.9	1004.1
30°	1737.0	1643.7	1548.5	1467.3	1393.3	1324.1	1250.1	1170.6	1091.2	1026.2	968.4
32.5°	1724.5	1615.8	1515.4	1426.9	1348.5	1281.2	1213.0	1137.4	1059.4	993.5	935.7
35°	1700.2	1574.5	1459.6	1359.6	1275.9	1206.8	1149.6	1079.1	1007.5	943.7	888.3
37.5°	1669.6	1520.3	1397.0	1292.2	1200.5	1127.6	1074.3	1020.3	951.5	890.0	840.0
40°	1645.5	1481.8	1351.2	1244.0	1149.0	1073.1	1023.8	972.6	915.4	858.3	805.3
42.5°	1615.2	1447.2	1304.9	1189.6	1095.5	1021.6	969.8	926.4	875.9	822.6	773.5
45°	1559.4	1384.3	1230.2	1106.3	1011.1	938.3	884.8	852.2	814.3	763.8	722.2
47.5°	1477.5	1308.8	1149.4	1021.5	923.4	855.9	805.7	774.5	747.8	710.2	672.5
50°	1404.7	1252.5	1091.2	964.2	866.1	798.1	751.7	723.4	700.5	671.6	639.8
52.5°	1323.4	1181.7	1033.8	908.3	811.2	744.1	698.7	673.9	654.8	634.1	602.7
55°	1194.1	1073.7	936.5	817.3	727.6	662.0	622.3	600.7	585.1	569.4	550.1
57.5°	1051.7	957.5	836.0	727.0	644.4	584.8	547.7	526.6	514.4	506.4	495.1
60°	951.5	870.9	766.2	666.8	586.2	533.2	497.1	480.9	470.6	464.0	455.6
62.5°	858.6	792.4	695.4	604.8	534.2	484.1	451.9	436.1	426.3	423.1	416.2
65°	721.7	670.5	590.4	515.2	455.0	412.2	385.2	370.1	364.1	360.5	361.1
67.5°	586.7	555.5	491.2	427.0	379.1	343.2	321.6	310.0	306.9	302.1	302.0
70°	504.4	480.9	426.7	370.8	328.0	300.3	281.1	269.0	266.0	263.6	263.1
72.5°	431.7	411.1	364.1	319.2	280.8	256.5	240.6	233.4	228.5	227.0	226.9
75°	324.4	313.0	275.6	240.1	213.7	196.8	186.0	179.3	175.8	175.1	175.8
77.5°	230.6	220.6	196.9	171.7	155.1	142.3	133.1	130.8	126.7	126.9	126.3
80°	173.3	166.7	151.7	131.8	118.0	107.1	102.3	98.1	96.9	95.1	96.9
82.5°	125.6	118.6	108.3	95.7	84.3	77.8	72.9	71.6	70.9	70.1	70.4
85°	62.0	62.6	56.5	46.9	42.1	38.5	35.5	35.5	34.9	34.3	34.9
87.5°	23.5	22.3	20.1	18.3	15.6	13.8	13.0	13.2	12.0	11.9	12.7
90°	11.6	10.3	8.8	7.3	5.7	4.1	2.5	0.9	2.5	4.1	5.7
92.5°	11.9	10.7	9.5	9.4	10.5	11.7	12.8	13.9	12.8	11.7	10.5
95°	29.7	37.3	44.9	49.0	49.6	50.2	50.8	51.4	50.8	50.2	49.6
97.5°	74.5	89.6	104.7	111.6	110.6	109.5	108.4	107.4	108.4	109.5	110.6
100°	155.3	154.5	153.7	153.0	152.4	151.8	151.2	150.6	151.2	151.8	152.4
102.5°	199.2	198.8	198.3	197.7	196.9	196.2	195.4	194.7	195.4	196.2	196.9
105°	268.8	268.8	268.8	268.3	267.5	266.7	265.9	265.1	265.9	266.7	267.5
107.5°	339.4	338.9	338.6	338.4	338.4	338.4	338.4	338.4	338.4	338.4	338.4
110°	387.0	386.6	386.2	386.0	386.0	386.0	386.0	386.0	386.0	386.0	386.0



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	433.5	433.3	433.0	432.7	432.1	431.7	431.2	430.7	431.2	431.7	432.1
115°	502.8	502.7	502.4	501.9	500.8	499.8	498.8	497.8	498.8	499.8	500.8
117.5°	569.0	568.2	567.5	567.1	567.1	567.2	567.2	567.3	567.2	567.2	567.1
120°	611.2	610.6	609.9	609.8	609.9	610.1	610.4	610.6	610.4	610.1	609.9
122.5°	652.9	652.6	652.4	651.8	651.0	650.3	649.5	648.8	649.5	650.3	651.0
125°	714.3	714.3	714.3	713.5	712.1	710.8	709.4	707.9	709.4	710.8	712.1
127.5°	768.7	768.7	768.8	768.4	767.4	766.4	765.4	764.4	765.4	766.4	767.4
130°	804.1	803.9	803.6	803.1	802.0	801.0	800.0	799.1	800.0	801.0	802.0
132.5°	837.8	838.2	838.7	838.3	837.1	836.0	834.8	833.7	834.8	836.0	837.1
135°	887.3	887.7	888.1	887.7	886.5	885.3	884.1	882.9	884.1	885.3	886.5
137.5°	932.0	932.4	932.7	932.4	931.3	930.2	929.3	928.2	929.3	930.2	931.3
140°	959.0	959.3	959.5	959.4	958.9	958.6	958.1	957.8	958.1	958.6	958.9
142.5°	986.2	986.0	985.7	985.4	985.2	985.0	984.7	984.4	984.7	985.0	985.2
145°	1025.4	1025.4	1025.4	1025.2	1024.8	1024.4	1024.0	1023.6	1024.0	1024.4	1024.8
147.5°	1058.1	1057.8	1057.7	1057.6	1057.7	1057.7	1057.8	1057.8	1057.8	1057.7	1057.7
150°	1078.7	1078.3	1077.9	1077.9	1078.3	1078.7	1079.1	1079.5	1079.1	1078.7	1078.3
152.5°	1097.5	1097.1	1096.7	1096.9	1097.8	1098.7	1099.6	1100.5	1099.6	1098.7	1097.8
155°	1122.9	1122.5	1122.1	1122.5	1123.7	1124.9	1126.1	1127.3	1126.1	1124.9	1123.7
157.5°	1144.9	1144.9	1144.9	1145.1	1145.9	1146.7	1147.4	1148.1	1147.4	1146.7	1145.9
160°	1157.6	1157.4	1157.2	1157.7	1158.9	1160.1	1161.3	1162.5	1161.3	1160.1	1158.9
162.5°	1169.1	1168.9	1168.7	1169.2	1170.5	1171.6	1172.9	1174.0	1172.9	1171.6	1170.5
165°	1184.6	1184.5	1184.2	1184.7	1186.0	1187.1	1188.4	1189.5	1188.4	1187.1	1186.0
167.5°	1196.0	1195.8	1195.6	1196.1	1197.4	1198.6	1199.9	1201.0	1199.9	1198.6	1197.4
170°	1201.8	1201.6	1201.4	1201.9	1203.4	1204.8	1206.2	1207.6	1206.2	1204.8	1203.4
172.5°	1206.5	1206.1	1205.8	1206.3	1207.7	1209.1	1210.5	1211.9	1210.5	1209.1	1207.7
175°	1211.7	1211.5	1211.3	1211.7	1213.0	1214.2	1215.4	1216.6	1215.4	1214.2	1213.0
177.5°	1214.9	1214.7	1214.5	1215.0	1215.8	1216.8	1217.8	1218.8	1217.8	1216.8	1215.8
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1393.4	1388.1	1383.8	1374.1	1368.9	1361.6	1355.8	1362.1	1355.4	1358.3	1354.0
5°	1350.0	1333.1	1321.1	1303.6	1288.6	1274.7	1264.5	1262.7	1257.8	1255.4	1248.2
7.5°	1297.7	1276.7	1256.0	1233.1	1213.8	1194.2	1181.7	1171.4	1164.5	1155.5	1149.3
10°	1266.9	1238.6	1214.6	1186.9	1162.8	1141.7	1124.9	1116.4	1108.7	1097.2	1093.0
12.5°	1228.9	1199.6	1170.3	1140.7	1117.5	1094.0	1079.6	1066.8	1061.4	1048.6	1047.2
15°	1183.3	1139.3	1110.4	1080.3	1048.5	1029.2	1017.2	1003.3	997.3	988.3	981.6
17.5°	1128.8	1089.6	1053.5	1022.3	995.0	978.7	963.9	954.3	944.0	938.1	927.2
20°	1089.4	1052.0	1015.9	982.8	961.8	943.1	931.0	922.0	911.2	908.2	897.4
22.5°	1056.1	1014.9	980.3	952.5	929.5	908.5	895.5	889.3	881.8	872.5	870.4
25°	1002.1	959.4	929.9	902.2	881.7	862.5	853.5	845.6	838.4	831.8	829.4
27.5°	955.4	917.2	882.2	857.2	839.4	821.8	813.9	804.3	799.1	793.7	787.2
30°	922.7	883.5	852.8	828.8	809.5	793.9	785.4	778.8	774.0	769.2	765.5
32.5°	888.9	852.7	823.0	799.4	780.2	768.3	760.9	756.2	750.9	745.1	740.6
35°	844.5	804.7	775.8	755.4	740.3	731.3	722.8	718.6	712.6	712.6	707.8
37.5°	794.2	759.9	734.4	715.8	702.2	694.2	685.0	682.2	678.3	675.7	674.0
40°	764.4	732.5	708.4	689.7	675.3	668.7	661.5	656.7	654.2	651.2	650.0
42.5°	733.5	703.1	680.0	662.8	650.2	644.6	637.8	634.5	629.6	625.7	625.0
45°	686.7	657.2	636.1	622.3	611.4	604.8	600.7	593.4	591.0	586.2	585.6
47.5°	642.3	614.0	593.3	582.0	572.5	567.0	560.4	553.2	550.5	548.0	547.8
50°	609.1	583.2	563.9	553.1	544.1	536.3	529.7	524.9	523.0	523.0	524.2
52.5°	575.4	553.3	537.0	523.7	515.2	506.8	500.8	497.8	495.1	498.0	500.2
55°	526.0	503.7	491.7	479.1	470.6	461.0	458.0	456.8	455.0	459.9	462.3
57.5°	473.8	458.2	444.1	431.5	423.9	418.4	414.3	413.6	417.0	419.3	427.0
60°	440.6	422.5	409.8	400.2	391.2	387.6	386.4	385.2	387.6	394.2	404.5
62.5°	403.9	389.3	375.7	368.5	361.9	355.8	355.6	356.3	361.1	368.7	378.9
65°	350.3	337.6	328.6	320.2	314.8	311.1	312.4	314.8	320.2	330.4	341.9
67.5°	295.8	287.1	279.0	272.2	267.0	267.0	268.2	271.8	278.2	290.0	300.4
70°	260.6	251.0	244.3	241.4	237.1	234.7	238.4	244.3	249.8	260.6	269.7
72.5°	225.4	217.3	212.1	210.1	208.2	206.3	207.5	214.0	221.3	232.2	242.6
75°	173.3	170.3	166.7	164.3	162.5	163.7	164.9	170.9	176.9	188.4	200.5
77.5°	126.5	123.4	121.2	120.6	119.7	120.3	123.6	128.0	133.9	142.3	151.4
80°	95.7	94.5	93.3	92.6	92.6	93.3	98.1	101.1	106.6	114.3	121.5
82.5°	69.7	68.9	68.8	68.6	69.1	69.2	72.1	76.1	80.5	86.4	92.6
85°	36.7	35.5	37.3	37.9	36.7	38.5	39.7	42.1	44.0	46.9	49.9
87.5°	13.5	14.8	14.5	15.3	15.6	16.9	16.6	18.7	19.9	21.0	20.7
90°	7.3	8.8	10.3	11.6	13.0	14.4	15.4	16.4	17.5	18.5	19.3
92.5°	9.4	9.5	10.7	11.9	13.2	14.4	15.4	16.4	17.5	18.5	19.1
95°	49.0	44.9	37.3	29.7	22.0	14.4	15.4	16.4	17.5	18.5	18.9
97.5°	111.6	104.7	89.6	74.5	59.5	44.4	38.7	33.1	27.4	21.8	18.9
100°	153.0	153.7	154.5	155.3	156.1	156.9	127.1	97.2	67.3	37.5	22.1
102.5°	197.7	198.3	198.8	199.2	199.7	200.2	194.6	188.9	183.2	177.6	168.0
105°	268.3	268.8	268.8	268.8	268.8	268.8	268.8	268.8	268.8	268.8	268.7
107.5°	338.4	338.6	338.9	339.4	339.7	340.2	340.2	340.3	340.3	340.4	340.1
110°	386.0	386.2	386.6	387.0	387.4	387.8	387.2	386.6	386.0	385.4	385.2



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	432.7	433.0	433.3	433.5	433.7	434.0	433.2	432.5	431.7	431.0	430.4
115°	501.9	502.4	502.7	502.8	503.0	503.2	502.4	501.6	500.8	500.0	499.0
117.5°	567.1	567.5	568.2	569.0	569.7	570.5	569.4	568.5	567.4	566.3	565.5
120°	609.8	609.9	610.6	611.2	611.7	612.3	612.0	611.5	611.2	610.7	610.0
122.5°	651.8	652.4	652.6	652.9	653.2	653.4	653.1	652.6	652.3	651.8	651.1
125°	713.5	714.3	714.3	714.3	714.3	714.3	713.5	712.7	711.9	711.1	710.3
127.5°	768.4	768.8	768.7	768.7	768.5	768.4	767.9	767.5	767.0	766.6	765.6
130°	803.1	803.6	803.9	804.1	804.2	804.4	803.9	803.3	802.6	802.0	801.2
132.5°	838.3	838.7	838.2	837.8	837.3	837.0	836.8	836.7	836.5	836.4	835.9
135°	887.7	888.1	887.7	887.3	886.9	886.5	886.1	885.7	885.3	884.9	884.1
137.5°	932.4	932.7	932.4	932.0	931.6	931.2	931.3	931.4	931.5	931.6	931.1
140°	959.4	959.5	959.3	959.0	958.9	958.7	959.0	959.5	959.8	960.3	959.8
142.5°	985.4	985.7	986.0	986.2	986.5	986.8	986.9	986.9	987.0	987.1	986.6
145°	1025.2	1025.4	1025.4	1025.4	1025.4	1025.4	1025.6	1025.8	1026.0	1026.2	1025.7
147.5°	1057.6	1057.7	1057.8	1058.1	1058.4	1058.5	1058.8	1059.1	1059.4	1059.5	1059.0
150°	1077.9	1077.9	1078.3	1078.7	1079.1	1079.5	1080.0	1080.3	1080.8	1081.1	1080.5
152.5°	1096.9	1096.7	1097.1	1097.5	1097.9	1098.2	1098.7	1099.0	1099.5	1099.8	1099.4
155°	1122.5	1122.1	1122.5	1122.9	1123.3	1123.7	1124.3	1124.9	1125.5	1126.1	1125.6
157.5°	1145.1	1144.9	1144.9	1144.9	1145.0	1145.0	1145.7	1146.3	1146.9	1147.5	1147.1
160°	1157.7	1157.2	1157.4	1157.6	1157.8	1158.0	1158.8	1159.6	1160.4	1161.2	1160.7
162.5°	1169.2	1168.7	1168.9	1169.1	1169.3	1169.5	1170.6	1171.8	1172.9	1174.0	1173.7
165°	1184.7	1184.2	1184.5	1184.6	1184.8	1185.0	1186.2	1187.4	1188.7	1189.8	1189.6
167.5°	1196.1	1195.6	1195.8	1196.0	1196.2	1196.4	1197.8	1199.3	1200.7	1202.2	1202.0
170°	1201.9	1201.4	1201.6	1201.8	1201.9	1202.2	1203.8	1205.4	1207.0	1208.6	1208.4
172.5°	1206.3	1205.8	1206.1	1206.5	1206.8	1207.2	1208.6	1210.1	1211.6	1213.0	1212.8
175°	1211.7	1211.3	1211.5	1211.7	1211.9	1212.1	1213.7	1215.3	1216.9	1218.5	1218.4
177.5°	1215.0	1214.5	1214.7	1214.9	1215.0	1215.1	1216.3	1217.4	1218.5	1219.7	1219.6
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1351.0	1354.4	1351.6	1355.4	1351.6	1354.4	1351.0	1354.0	1358.3	1355.4	1362.1
5°	1245.3	1239.8	1243.4	1241.0	1243.4	1239.8	1245.3	1248.2	1255.4	1257.8	1262.7
7.5°	1147.5	1142.4	1136.4	1133.6	1136.4	1142.4	1147.5	1149.3	1155.5	1164.5	1171.4
10°	1086.4	1079.8	1079.1	1075.0	1079.1	1079.8	1086.4	1093.0	1097.2	1108.7	1116.4
12.5°	1041.6	1035.5	1028.6	1026.8	1028.6	1035.5	1041.6	1047.2	1048.6	1061.4	1066.8
15°	978.0	973.2	969.0	972.6	969.0	973.2	978.0	981.6	988.3	997.3	1003.3
17.5°	925.1	921.2	920.5	916.1	920.5	921.2	925.1	927.2	938.1	944.0	954.3
20°	892.0	888.9	890.2	882.3	890.2	888.9	892.0	897.4	908.2	911.2	922.0
22.5°	865.5	859.6	858.9	857.3	858.9	859.6	865.5	870.4	872.5	881.8	889.3
25°	823.9	820.9	818.0	820.9	818.0	820.9	823.9	829.4	831.8	838.4	845.6
27.5°	787.7	784.1	783.3	783.6	783.3	784.1	787.7	787.2	793.7	799.1	804.3
30°	765.5	759.6	760.2	759.6	760.2	759.6	765.5	765.5	769.2	774.0	778.8
32.5°	741.5	737.4	736.6	735.5	736.6	737.4	741.5	740.6	745.1	750.9	756.2
35°	706.0	706.0	702.9	702.9	702.9	706.0	706.0	707.8	712.6	712.6	718.6
37.5°	672.6	672.0	670.2	670.5	670.2	672.0	672.6	674.0	675.7	678.3	682.2
40°	647.6	647.0	645.2	641.6	645.2	647.0	647.6	650.0	651.2	654.2	656.7
42.5°	623.5	621.5	620.6	619.5	620.6	621.5	623.5	625.0	625.7	629.6	634.5
45°	585.6	585.6	584.4	583.8	584.4	585.6	585.6	585.6	586.2	591.0	593.4
47.5°	548.8	549.8	552.1	551.8	552.1	549.8	548.8	547.8	548.0	550.5	553.2
50°	526.6	527.3	529.1	529.7	529.1	527.3	526.6	524.2	523.0	523.0	524.9
52.5°	502.0	505.6	507.8	507.5	507.8	505.6	502.0	500.2	498.0	495.1	497.8
55°	467.6	471.9	476.1	476.7	476.1	471.9	467.6	462.3	459.9	455.0	456.8
57.5°	433.5	439.4	443.9	445.4	443.9	439.4	433.5	427.0	419.3	417.0	413.6
60°	410.5	418.3	423.7	426.1	423.7	418.3	410.5	404.5	394.2	387.6	385.2
62.5°	388.3	397.1	402.5	403.0	402.5	397.1	388.3	378.9	368.7	361.1	356.3
65°	352.0	361.1	366.0	369.5	366.0	361.1	352.0	341.9	330.4	320.2	314.8
67.5°	313.1	322.1	327.4	330.3	327.4	322.1	313.1	300.4	290.0	278.2	271.8
70°	284.7	293.7	301.0	303.4	301.0	293.7	284.7	269.7	260.6	249.8	244.3
72.5°	256.7	264.8	270.6	273.5	270.6	264.8	256.7	242.6	232.2	221.3	214.0
75°	208.2	219.1	224.5	227.5	224.5	219.1	208.2	200.5	188.4	176.9	170.9
77.5°	160.6	170.4	173.7	175.2	173.7	170.4	160.6	151.4	142.3	133.9	128.0
80°	128.8	134.8	139.0	139.6	139.0	134.8	128.8	121.5	114.3	106.6	101.1
82.5°	99.0	104.0	105.3	106.9	105.3	104.0	99.0	92.6	86.4	80.5	76.1
85°	54.1	56.5	57.2	56.5	57.2	56.5	54.1	49.9	46.9	44.0	42.1
87.5°	21.8	21.4	21.6	22.6	21.6	21.4	21.8	20.7	21.0	19.9	18.7
90°	19.9	20.4	21.0	21.7	21.0	20.4	19.9	19.3	18.5	17.5	16.4
92.5°	19.4	19.6	19.9	20.2	19.9	19.6	19.4	19.1	18.5	17.5	16.4
95°	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.5	17.5	16.4
97.5°	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	21.8	27.4	33.1
100°	21.3	20.5	19.7	18.9	19.7	20.5	21.3	22.1	37.5	67.3	97.2
102.5°	154.4	140.7	127.1	113.4	127.1	140.7	154.4	168.0	177.6	183.2	188.9
105°	268.5	268.2	268.0	267.9	268.0	268.2	268.5	268.7	268.8	268.8	268.8
107.5°	339.5	338.9	338.2	337.7	338.2	338.9	339.5	340.1	340.4	340.3	340.3
110°	385.4	385.6	385.8	386.0	385.8	385.6	385.4	385.2	385.4	386.0	386.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	430.2	429.8	429.5	429.3	429.5	429.8	430.2	430.4	431.0	431.7	432.5
115°	497.8	496.6	495.4	494.2	495.4	496.6	497.8	499.0	500.0	500.8	501.6
117.5°	565.1	564.5	564.0	563.5	564.0	564.5	565.1	565.5	566.3	567.4	568.5
120°	609.0	608.1	607.1	606.0	607.1	608.1	609.0	610.0	610.7	611.2	611.5
122.5°	650.0	648.8	647.6	646.5	647.6	648.8	650.0	651.1	651.8	652.3	652.6
125°	709.8	709.2	708.6	707.9	708.6	709.2	709.8	710.3	711.1	711.9	712.7
127.5°	764.2	762.7	761.2	759.7	761.2	762.7	764.2	765.6	766.6	767.0	767.5
130°	800.2	799.2	798.3	797.3	798.3	799.2	800.2	801.2	802.0	802.6	803.3
132.5°	834.9	833.8	832.9	831.9	832.9	833.8	834.9	835.9	836.4	836.5	836.7
135°	882.9	881.7	880.5	879.3	880.5	881.7	882.9	884.1	884.9	885.3	885.7
137.5°	930.1	929.0	928.0	926.9	928.0	929.0	930.1	931.1	931.6	931.5	931.4
140°	958.7	957.4	956.3	955.0	956.3	957.4	958.7	959.8	960.3	959.8	959.5
142.5°	985.3	984.2	982.9	981.8	982.9	984.2	985.3	986.6	987.1	987.0	986.9
145°	1024.5	1023.3	1022.1	1020.9	1022.1	1023.3	1024.5	1025.7	1026.2	1026.0	1025.8
147.5°	1057.5	1056.1	1054.6	1053.2	1054.6	1056.1	1057.5	1059.0	1059.5	1059.4	1059.1
150°	1078.9	1077.3	1075.7	1074.1	1075.7	1077.3	1078.9	1080.5	1081.1	1080.8	1080.3
152.5°	1097.9	1096.4	1095.0	1093.6	1095.0	1096.4	1097.9	1099.4	1099.8	1099.5	1099.0
155°	1124.0	1122.4	1120.8	1119.2	1120.8	1122.4	1124.0	1125.6	1126.1	1125.5	1124.9
157.5°	1145.5	1143.9	1142.3	1140.7	1142.3	1143.9	1145.5	1147.1	1147.5	1146.9	1146.3
160°	1159.2	1157.6	1156.0	1154.4	1156.0	1157.6	1159.2	1160.7	1161.2	1160.4	1159.6
162.5°	1171.9	1170.2	1168.4	1166.6	1168.4	1170.2	1171.9	1173.7	1174.0	1172.9	1171.8
165°	1188.0	1186.4	1184.8	1183.2	1184.8	1186.4	1188.0	1189.6	1189.8	1188.7	1187.4
167.5°	1200.2	1198.4	1196.6	1194.8	1196.6	1198.4	1200.2	1202.0	1202.2	1200.7	1199.3
170°	1206.7	1204.9	1203.1	1201.2	1203.1	1204.9	1206.7	1208.4	1208.6	1207.0	1205.4
172.5°	1211.0	1209.2	1207.4	1205.6	1207.4	1209.2	1211.0	1212.8	1213.0	1211.6	1210.1
175°	1216.6	1214.8	1213.0	1211.2	1213.0	1214.8	1216.6	1218.4	1218.5	1216.9	1215.3
177.5°	1218.3	1217.0	1215.8	1214.4	1215.8	1217.0	1218.3	1219.6	1219.7	1218.5	1217.4
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1355.8	1361.6	1368.9	1374.1	1383.8	1388.1	1393.4	1397.8	1405.4	1412.6	1421.4
5°	1264.5	1274.7	1288.6	1303.6	1321.1	1333.1	1350.0	1360.2	1380.6	1399.4	1417.4
7.5°	1181.7	1194.2	1213.8	1233.1	1256.0	1276.7	1297.7	1321.1	1347.2	1378.0	1403.6
10°	1124.9	1141.7	1162.8	1186.9	1214.6	1238.6	1266.9	1292.2	1324.1	1360.2	1393.9
12.5°	1079.6	1094.0	1117.5	1140.7	1170.3	1199.6	1228.9	1262.3	1299.6	1339.5	1381.9
15°	1017.2	1029.2	1048.5	1080.3	1110.4	1139.3	1183.3	1214.6	1261.5	1306.0	1357.2
17.5°	963.9	978.7	995.0	1022.3	1053.5	1089.6	1128.8	1168.1	1213.4	1269.8	1327.5
20°	931.0	943.1	961.8	982.8	1015.9	1052.0	1089.4	1129.1	1184.5	1242.9	1304.8
22.5°	895.5	908.5	929.5	952.5	980.3	1014.9	1056.1	1099.7	1157.5	1215.0	1282.2
25°	853.5	862.5	881.7	902.2	929.9	959.4	1002.1	1050.3	1107.4	1173.0	1241.6
27.5°	813.9	821.8	839.4	857.2	882.2	917.2	955.4	1004.1	1057.9	1124.4	1200.5
30°	785.4	793.9	809.5	828.8	852.8	883.5	922.7	968.4	1026.2	1091.2	1170.6
32.5°	760.9	768.3	780.2	799.4	823.0	852.7	888.9	935.7	993.5	1059.4	1137.4
35°	722.8	731.3	740.3	755.4	775.8	804.7	844.5	888.3	943.7	1007.5	1079.1
37.5°	685.0	694.2	702.2	715.8	734.4	759.9	794.2	840.0	890.0	951.5	1020.3
40°	661.5	668.7	675.3	689.7	708.4	732.5	764.4	805.3	858.3	915.4	972.6
42.5°	637.8	644.6	650.2	662.8	680.0	703.1	733.5	773.5	822.6	875.9	926.4
45°	600.7	604.8	611.4	622.3	636.1	657.2	686.7	722.2	763.8	814.3	852.2
47.5°	560.4	567.0	572.5	582.0	593.3	614.0	642.3	672.5	710.2	747.8	774.5
50°	529.7	536.3	544.1	553.1	563.9	583.2	609.1	639.8	671.6	700.5	723.4
52.5°	500.8	506.8	515.2	523.7	537.0	553.3	575.4	602.7	634.1	654.8	673.9
55°	458.0	461.0	470.6	479.1	491.7	503.7	526.0	550.1	569.4	585.1	600.7
57.5°	414.3	418.4	423.9	431.5	444.1	458.2	473.8	495.1	506.4	514.4	526.6
60°	386.4	387.6	391.2	400.2	409.8	422.5	440.6	455.6	464.0	470.6	480.9
62.5°	355.6	355.8	361.9	368.5	375.7	389.3	403.9	416.2	423.1	426.3	436.1
65°	312.4	311.1	314.8	320.2	328.6	337.6	350.3	361.1	360.5	364.1	370.1
67.5°	268.2	267.0	267.0	272.2	279.0	287.1	295.8	302.0	302.1	306.9	310.0
70°	238.4	234.7	237.1	241.4	244.3	251.0	260.6	263.1	263.6	266.0	269.0
72.5°	207.5	206.3	208.2	210.1	212.1	217.3	225.4	226.9	227.0	228.5	233.4
75°	164.9	163.7	162.5	164.3	166.7	170.3	173.3	175.8	175.1	175.8	179.3
77.5°	123.6	120.3	119.7	120.6	121.2	123.4	126.5	126.3	126.9	126.7	130.8
80°	98.1	93.3	92.6	92.6	93.3	94.5	95.7	96.9	95.1	96.9	98.1
82.5°	72.1	69.2	69.1	68.6	68.8	68.9	69.7	70.4	70.1	70.9	71.6
85°	39.7	38.5	36.7	37.9	37.3	35.5	36.7	34.9	34.3	34.9	35.5
87.5°	16.6	16.9	15.6	15.3	14.5	14.8	13.5	12.7	11.9	12.0	13.2
90°	15.4	14.4	13.0	11.6	10.3	8.8	7.3	5.7	4.1	2.5	0.9
92.5°	15.4	14.4	13.2	11.9	10.7	9.5	9.4	10.5	11.7	12.8	13.9
95°	15.4	14.4	22.0	29.7	37.3	44.9	49.0	49.6	50.2	50.8	51.4
97.5°	38.7	44.4	59.5	74.5	89.6	104.7	111.6	110.6	109.5	108.4	107.4
100°	127.1	156.9	156.1	155.3	154.5	153.7	153.0	152.4	151.8	151.2	150.6
102.5°	194.6	200.2	199.7	199.2	198.8	198.3	197.7	196.9	196.2	195.4	194.7
105°	268.8	268.8	268.8	268.8	268.8	268.8	268.3	267.5	266.7	265.9	265.1
107.5°	340.2	340.2	339.7	339.4	338.9	338.6	338.4	338.4	338.4	338.4	338.4
110°	387.2	387.8	387.4	387.0	386.6	386.2	386.0	386.0	386.0	386.0	386.0



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	433.2	434.0	433.7	433.5	433.3	433.0	432.7	432.1	431.7	431.2	430.7
115°	502.4	503.2	503.0	502.8	502.7	502.4	501.9	500.8	499.8	498.8	497.8
117.5°	569.4	570.5	569.7	569.0	568.2	567.5	567.1	567.1	567.2	567.2	567.3
120°	612.0	612.3	611.7	611.2	610.6	609.9	609.8	609.9	610.1	610.4	610.6
122.5°	653.1	653.4	653.2	652.9	652.6	652.4	651.8	651.0	650.3	649.5	648.8
125°	713.5	714.3	714.3	714.3	714.3	714.3	713.5	712.1	710.8	709.4	707.9
127.5°	767.9	768.4	768.5	768.7	768.7	768.8	768.4	767.4	766.4	765.4	764.4
130°	803.9	804.4	804.2	804.1	803.9	803.6	803.1	802.0	801.0	800.0	799.1
132.5°	836.8	837.0	837.3	837.8	838.2	838.7	838.3	837.1	836.0	834.8	833.7
135°	886.1	886.5	886.9	887.3	887.7	888.1	887.7	886.5	885.3	884.1	882.9
137.5°	931.3	931.2	931.6	932.0	932.4	932.7	932.4	931.3	930.2	929.3	928.2
140°	959.0	958.7	958.9	959.0	959.3	959.5	959.4	958.9	958.6	958.1	957.8
142.5°	986.9	986.8	986.5	986.2	986.0	985.7	985.4	985.2	985.0	984.7	984.4
145°	1025.6	1025.4	1025.4	1025.4	1025.4	1025.4	1025.2	1024.8	1024.4	1024.0	1023.6
147.5°	1058.8	1058.5	1058.4	1058.1	1057.8	1057.7	1057.6	1057.7	1057.7	1057.8	1057.8
150°	1080.0	1079.5	1079.1	1078.7	1078.3	1077.9	1077.9	1078.3	1078.7	1079.1	1079.5
152.5°	1098.7	1098.2	1097.9	1097.5	1097.1	1096.7	1096.9	1097.8	1098.7	1099.6	1100.5
155°	1124.3	1123.7	1123.3	1122.9	1122.5	1122.1	1122.5	1123.7	1124.9	1126.1	1127.3
157.5°	1145.7	1145.0	1145.0	1144.9	1144.9	1144.9	1145.1	1145.9	1146.7	1147.4	1148.1
160°	1158.8	1158.0	1157.8	1157.6	1157.4	1157.2	1157.7	1158.9	1160.1	1161.3	1162.5
162.5°	1170.6	1169.5	1169.3	1169.1	1168.9	1168.7	1169.2	1170.5	1171.6	1172.9	1174.0
165°	1186.2	1185.0	1184.8	1184.6	1184.5	1184.2	1184.7	1186.0	1187.1	1188.4	1189.5
167.5°	1197.8	1196.4	1196.2	1196.0	1195.8	1195.6	1196.1	1197.4	1198.6	1199.9	1201.0
170°	1203.8	1202.2	1201.9	1201.8	1201.6	1201.4	1201.9	1203.4	1204.8	1206.2	1207.6
172.5°	1208.6	1207.2	1206.8	1206.5	1206.1	1205.8	1206.3	1207.7	1209.1	1210.5	1211.9
175°	1213.7	1212.1	1211.9	1211.7	1211.5	1211.3	1211.7	1213.0	1214.2	1215.4	1216.6
177.5°	1216.3	1215.1	1215.0	1214.9	1214.7	1214.5	1215.0	1215.8	1216.8	1217.8	1218.8
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1425.7	1432.4	1436.7	1444.9	1451.7	1455.5	1458.9	1461.8	1465.2	1468.0	1476.2
5°	1434.9	1450.5	1463.7	1484.2	1502.9	1517.3	1532.9	1546.8	1558.2	1574.5	1587.1
7.5°	1430.8	1458.7	1487.8	1519.5	1551.8	1581.9	1609.6	1635.5	1658.9	1687.4	1712.3
10°	1427.0	1464.9	1502.3	1545.0	1588.9	1626.2	1661.2	1696.7	1722.5	1758.6	1789.3
12.5°	1424.2	1468.7	1513.8	1565.2	1613.5	1666.2	1712.6	1738.6	1777.9	1806.8	1843.3
15°	1411.9	1471.0	1532.9	1590.7	1659.3	1708.1	1749.0	1799.6	1836.3	1872.9	1912.7
17.5°	1390.2	1457.0	1526.3	1602.0	1667.9	1720.2	1773.0	1821.7	1865.5	1914.8	1964.3
20°	1380.1	1446.9	1526.3	1603.9	1668.4	1723.1	1777.3	1830.9	1879.0	1942.2	1999.4
22.5°	1358.9	1439.7	1512.9	1588.6	1654.8	1714.5	1775.8	1836.7	1900.7	1972.0	2043.7
25°	1321.1	1402.9	1480.6	1555.2	1622.0	1696.7	1762.3	1843.5	1925.4	2019.8	2108.9
27.5°	1281.8	1360.2	1431.4	1503.4	1581.4	1665.8	1751.0	1843.2	1950.3	2069.6	2195.2
30°	1250.1	1324.1	1393.3	1467.3	1548.5	1643.7	1737.0	1846.5	1970.5	2104.7	2254.0
32.5°	1213.0	1281.2	1348.5	1426.9	1515.4	1615.8	1724.5	1844.6	1993.6	2146.1	2299.7
35°	1149.6	1206.8	1275.9	1359.6	1459.6	1574.5	1700.2	1842.3	2013.2	2188.3	2317.7
37.5°	1074.3	1127.6	1200.5	1292.2	1397.0	1520.3	1669.6	1838.1	2019.6	2159.3	2201.0
40°	1023.8	1073.1	1149.0	1244.0	1351.2	1481.8	1645.5	1823.6	1999.4	2088.5	2054.1
42.5°	969.8	1021.6	1095.5	1189.6	1304.9	1447.2	1615.2	1793.3	1940.6	1974.3	1855.7
45°	884.8	938.3	1011.1	1106.3	1230.2	1384.3	1559.4	1721.4	1806.2	1745.4	1561.8
47.5°	805.7	855.9	923.4	1021.5	1149.4	1308.8	1477.5	1606.6	1613.4	1468.3	1272.2
50°	751.7	798.1	866.1	964.2	1091.2	1252.5	1404.7	1506.5	1460.7	1296.4	1108.0
52.5°	698.7	744.1	811.2	908.3	1033.8	1181.7	1323.4	1394.7	1308.6	1140.0	979.0
55°	622.3	662.0	727.6	817.3	936.5	1073.7	1194.1	1218.8	1106.8	940.7	810.1
57.5°	547.7	584.8	644.4	727.0	836.0	957.5	1051.7	1046.4	928.1	785.5	681.9
60°	497.1	533.2	586.2	666.8	766.2	870.9	951.5	932.3	814.9	692.1	604.8
62.5°	451.9	484.1	534.2	604.8	695.4	792.4	858.6	830.2	715.2	607.9	539.0
65°	385.2	412.2	455.0	515.2	590.4	670.5	721.7	684.9	586.8	503.2	447.8
67.5°	321.6	343.2	379.1	427.0	491.2	555.5	586.7	549.7	471.3	410.2	369.2
70°	281.1	300.3	328.0	370.8	426.7	480.9	504.4	471.3	403.9	351.5	322.0
72.5°	240.6	256.5	280.8	319.2	364.1	411.1	431.7	400.0	344.6	300.4	272.9
75°	186.0	196.8	213.7	240.1	275.6	313.0	324.4	296.8	261.2	228.1	210.1
77.5°	133.1	142.3	155.1	171.7	196.9	220.6	230.6	214.6	187.2	166.2	151.4
80°	102.3	107.1	118.0	131.8	151.7	166.7	173.3	163.1	143.8	128.2	116.7
82.5°	72.9	77.8	84.3	95.7	108.3	118.6	125.6	118.8	104.9	92.6	86.0
85°	35.5	38.5	42.1	46.9	56.5	62.6	62.0	57.8	52.3	47.5	44.0
87.5°	13.0	13.8	15.6	18.3	20.1	22.3	23.5	22.8	21.2	20.0	18.7
90°	2.5	4.1	5.7	7.3	8.8	10.3	11.6	13.0	14.4	15.4	16.4
92.5°	12.8	11.7	10.5	9.4	9.5	10.7	11.9	13.2	14.4	15.4	16.4
95°	50.8	50.2	49.6	49.0	44.9	37.3	29.7	22.0	14.4	15.4	16.4
97.5°	108.4	109.5	110.6	111.6	104.7	89.6	74.5	59.5	44.4	38.7	33.1
100°	151.2	151.8	152.4	153.0	153.7	154.5	155.3	156.1	156.9	127.1	97.2
102.5°	195.4	196.2	196.9	197.7	198.3	198.8	199.2	199.7	200.2	194.6	188.9
105°	265.9	266.7	267.5	268.3	268.8	268.8	268.8	268.8	268.8	268.8	268.8
107.5°	338.4	338.4	338.4	338.4	338.6	338.9	339.4	339.7	340.2	340.2	340.3
110°	386.0	386.0	386.0	386.0	386.2	386.6	387.0	387.4	387.8	387.2	386.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	431.2	431.7	432.1	432.7	433.0	433.3	433.5	433.7	434.0	433.2	432.5
115°	498.8	499.8	500.8	501.9	502.4	502.7	502.8	503.0	503.2	502.4	501.6
117.5°	567.2	567.2	567.1	567.1	567.5	568.2	569.0	569.7	570.5	569.4	568.5
120°	610.4	610.1	609.9	609.8	609.9	610.6	611.2	611.7	612.3	612.0	611.5
122.5°	649.5	650.3	651.0	651.8	652.4	652.6	652.9	653.2	653.4	653.1	652.6
125°	709.4	710.8	712.1	713.5	714.3	714.3	714.3	714.3	714.3	713.5	712.7
127.5°	765.4	766.4	767.4	768.4	768.8	768.7	768.7	768.5	768.4	767.9	767.5
130°	800.0	801.0	802.0	803.1	803.6	803.9	804.1	804.2	804.4	803.9	803.3
132.5°	834.8	836.0	837.1	838.3	838.7	838.2	837.8	837.3	837.0	836.8	836.7
135°	884.1	885.3	886.5	887.7	888.1	887.7	887.3	886.9	886.5	886.1	885.7
137.5°	929.3	930.2	931.3	932.4	932.7	932.4	932.0	931.6	931.2	931.3	931.4
140°	958.1	958.6	958.9	959.4	959.5	959.3	959.0	958.9	958.7	959.0	959.5
142.5°	984.7	985.0	985.2	985.4	985.7	986.0	986.2	986.5	986.8	986.9	986.9
145°	1024.0	1024.4	1024.8	1025.2	1025.4	1025.4	1025.4	1025.4	1025.4	1025.6	1025.8
147.5°	1057.8	1057.7	1057.7	1057.6	1057.7	1057.8	1058.1	1058.4	1058.5	1058.8	1059.1
150°	1079.1	1078.7	1078.3	1077.9	1077.9	1078.3	1078.7	1079.1	1079.5	1080.0	1080.3
152.5°	1099.6	1098.7	1097.8	1096.9	1096.7	1097.1	1097.5	1097.9	1098.2	1098.7	1099.0
155°	1126.1	1124.9	1123.7	1122.5	1122.1	1122.5	1122.9	1123.3	1123.7	1124.3	1124.9
157.5°	1147.4	1146.7	1145.9	1145.1	1144.9	1144.9	1144.9	1145.0	1145.0	1145.7	1146.3
160°	1161.3	1160.1	1158.9	1157.7	1157.2	1157.4	1157.6	1157.8	1158.0	1158.8	1159.6
162.5°	1172.9	1171.6	1170.5	1169.2	1168.7	1168.9	1169.1	1169.3	1169.5	1170.6	1171.8
165°	1188.4	1187.1	1186.0	1184.7	1184.2	1184.5	1184.6	1184.8	1185.0	1186.2	1187.4
167.5°	1199.9	1198.6	1197.4	1196.1	1195.6	1195.8	1196.0	1196.2	1196.4	1197.8	1199.3
170°	1206.2	1204.8	1203.4	1201.9	1201.4	1201.6	1201.8	1201.9	1202.2	1203.8	1205.4
172.5°	1210.5	1209.1	1207.7	1206.3	1205.8	1206.1	1206.5	1206.8	1207.2	1208.6	1210.1
175°	1215.4	1214.2	1213.0	1211.7	1211.3	1211.5	1211.7	1211.9	1212.1	1213.7	1215.3
177.5°	1217.8	1216.8	1215.8	1215.0	1214.5	1214.7	1214.9	1215.0	1215.1	1216.3	1217.4
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1483.0	1486.8	1495.0	1492.1	1496.0	1497.9	1499.9
5°	1602.8	1622.0	1630.4	1629.2	1641.9	1638.9	1635.8
7.5°	1738.0	1758.3	1769.6	1783.7	1791.9	1792.4	1799.6
10°	1814.6	1841.1	1851.9	1867.0	1876.6	1882.0	1881.4
12.5°	1873.4	1894.1	1918.3	1925.7	1938.8	1945.5	1943.0
15°	1944.0	1977.1	2002.4	2015.0	2031.3	2036.1	2042.7
17.5°	2007.1	2051.5	2081.0	2120.2	2135.0	2144.0	2138.8
20°	2054.8	2113.2	2142.6	2189.6	2215.5	2229.3	2224.5
22.5°	2111.1	2174.3	2228.8	2269.5	2308.8	2327.5	2331.4
25°	2207.6	2294.3	2374.4	2428.0	2476.6	2488.1	2513.4
27.5°	2315.5	2417.7	2503.3	2559.6	2593.5	2606.3	2614.2
30°	2383.4	2485.1	2549.5	2585.6	2596.4	2595.2	2594.0
32.5°	2416.6	2480.3	2492.7	2482.5	2457.7	2436.8	2414.9
35°	2369.5	2322.0	2250.9	2159.5	2092.0	2024.1	2017.4
37.5°	2131.1	1979.1	1860.8	1728.8	1652.6	1605.5	1573.1
40°	1906.7	1733.9	1590.7	1479.3	1401.8	1371.0	1341.0
42.5°	1663.0	1498.1	1371.2	1278.1	1219.8	1185.7	1161.8
45°	1351.2	1205.5	1106.3	1038.8	992.5	966.0	950.9
47.5°	1107.1	999.4	915.1	866.5	834.5	813.9	814.0
50°	976.2	873.3	817.3	778.8	751.1	734.9	737.9
52.5°	860.1	783.3	735.5	703.2	682.8	672.8	672.4
55°	719.3	663.9	632.6	609.1	595.2	583.8	586.2
57.5°	615.2	568.6	547.6	528.1	518.4	513.9	507.2
60°	550.7	514.6	496.5	480.9	471.3	467.6	461.0
62.5°	493.4	465.0	447.5	434.6	426.0	424.8	419.6
65°	414.6	393.0	377.4	371.3	362.3	359.9	359.9
67.5°	341.9	326.4	314.1	308.6	304.7	305.2	302.4
70°	296.1	283.5	275.6	269.7	266.6	267.2	264.8
72.5°	259.0	245.0	238.1	234.5	230.5	232.1	231.1
75°	196.2	189.0	185.4	181.7	179.3	178.2	176.9
77.5°	144.1	137.7	134.9	132.9	133.2	130.4	132.7
80°	111.4	105.9	104.2	101.1	100.5	100.5	99.9
82.5°	81.5	78.5	77.1	74.6	73.6	74.5	72.9
85°	42.1	39.7	39.1	39.1	37.9	36.7	39.7
87.5°	18.9	17.2	17.3	16.9	17.1	16.8	15.9
90°	17.5	18.5	19.3	19.9	20.4	21.0	21.7
92.5°	17.5	18.5	19.1	19.4	19.6	19.9	20.2
95°	17.5	18.5	18.9	18.9	18.9	18.9	18.9
97.5°	27.4	21.8	18.9	18.9	18.9	18.9	18.9
100°	67.3	37.5	22.1	21.3	20.5	19.7	18.9
102.5°	183.2	177.6	168.0	154.4	140.7	127.1	113.4
105°	268.8	268.8	268.7	268.5	268.2	268.0	267.9
107.5°	340.3	340.4	340.1	339.5	338.9	338.2	337.7
110°	386.0	385.4	385.2	385.4	385.6	385.8	386.0



TEST NUMBER: P333442-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	431.7	431.0	430.4	430.2	429.8	429.5	429.3
115°	500.8	500.0	499.0	497.8	496.6	495.4	494.2
117.5°	567.4	566.3	565.5	565.1	564.5	564.0	563.5
120°	611.2	610.7	610.0	609.0	608.1	607.1	606.0
122.5°	652.3	651.8	651.1	650.0	648.8	647.6	646.5
125°	711.9	711.1	710.3	709.8	709.2	708.6	707.9
127.5°	767.0	766.6	765.6	764.2	762.7	761.2	759.7
130°	802.6	802.0	801.2	800.2	799.2	798.3	797.3
132.5°	836.5	836.4	835.9	834.9	833.8	832.9	831.9
135°	885.3	884.9	884.1	882.9	881.7	880.5	879.3
137.5°	931.5	931.6	931.1	930.1	929.0	928.0	926.9
140°	959.8	960.3	959.8	958.7	957.4	956.3	955.0
142.5°	987.0	987.1	986.6	985.3	984.2	982.9	981.8
145°	1026.0	1026.2	1025.7	1024.5	1023.3	1022.1	1020.9
147.5°	1059.4	1059.5	1059.0	1057.5	1056.1	1054.6	1053.2
150°	1080.8	1081.1	1080.5	1078.9	1077.3	1075.7	1074.1
152.5°	1099.5	1099.8	1099.4	1097.9	1096.4	1095.0	1093.6
155°	1125.5	1126.1	1125.6	1124.0	1122.4	1120.8	1119.2
157.5°	1146.9	1147.5	1147.1	1145.5	1143.9	1142.3	1140.7
160°	1160.4	1161.2	1160.7	1159.2	1157.6	1156.0	1154.4
162.5°	1172.9	1174.0	1173.7	1171.9	1170.2	1168.4	1166.6
165°	1188.7	1189.8	1189.6	1188.0	1186.4	1184.8	1183.2
167.5°	1200.7	1202.2	1202.0	1200.2	1198.4	1196.6	1194.8
170°	1207.0	1208.6	1208.4	1206.7	1204.9	1203.1	1201.2
172.5°	1211.6	1213.0	1212.8	1211.0	1209.2	1207.4	1205.6
175°	1216.9	1218.5	1218.4	1216.6	1214.8	1213.0	1211.2
177.5°	1218.5	1219.7	1219.6	1218.3	1217.0	1215.8	1214.4
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6

(END OF REPORT)