

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333443-940

Luminaire Tested: **S125DIW-S1090D1050U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333443-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D1050U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7243.6 lumens  
Efficiency: N/A  
Efficacy: 118.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	35	31	29	25
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	25	31	26	23	26	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	16	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9158	9158	9158	9158
5°	10605	9189	8045	9189
10°	12338	9141	7050	9141
15°	13658	9074	6503	9074
20°	15289	8968	6064	8968
25°	17910	8848	5850	8848
30°	19345	8730	5665	8730
35°	15906	8508	5542	8508
40°	11306	8200	5409	8200
45°	8685	7784	5332	7784
50°	7414	7268	5322	7268
55°	6600	6764	5368	6764
60°	5955	6212	5504	6212
65°	5500	5656	5647	5656
70°	5000	5080	5729	5080
75°	4414	4474	5677	4474
80°	3715	3649	5192	3649
85°	2942	2631	4187	2631



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.5	1.9
10°-20°	406.4	5.6
20°-30°	660.0	9.1
30°-40°	805.0	11.1
40°-50°	732.3	10.1
50°-60°	583.3	8.1
60°-70°	406.3	5.6
70°-80°	216.7	3.0
80°-90°	57.2	0.8
90°-100°	77.8	1.1
100°-110°	229.6	3.2
110°-120°	388.9	5.4
120°-130°	511.9	7.1
130°-140°	573.6	7.9
140°-150°	562.1	7.8
150°-160°	472.2	6.5
160°-170°	313.9	4.3
170°-180°	109.8	1.5
0°-30°	1202.9	16.6
0°-40°	2008.0	27.7
0°-60°	3323.6	45.9
0°-90°	4003.8	55.3
90°-120°	696.4	9.6
90°-150°	2344.0	32.4
90°-180°	3240.0	44.7
0°-180°	7243.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1636	1417	1241	1417	1636	165
15°	2043	1357	973	1357	2043	585
25°	2513	1242	821	1242	2513	1148
35°	2017	1079	703	1079	2017	1235
45°	951	852	584	852	951	761
55°	586	601	477	601	586	528
65°	360	370	370	370	360	357
75°	177	179	228	179	177	191
85°	40	36	56	36	40	46
90°	22	1	22	1	22	14
95°	78	59	78	59	78	79
105°	224	206	224	206	224	237
115°	393	389	393	389	393	389
125°	572	568	572	568	572	511
135°	742	739	742	739	742	572
145°	899	895	899	895	899	561
155°	1025	1025	1025	1025	1025	471
165°	1111	1114	1111	1114	1111	313
175°	1154	1158	1154	1158	1154	110
180°	1161	1161	1161	1161	1161	



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1499.9	1497.9	1496.0	1492.1	1495.0	1486.8	1483.0	1476.2	1468.0	1465.2	1461.8
5°	1635.8	1638.9	1641.9	1629.2	1630.4	1622.0	1602.8	1587.1	1574.5	1558.2	1546.8
7.5°	1799.6	1792.4	1791.9	1783.7	1769.6	1758.3	1738.0	1712.3	1687.4	1658.9	1635.5
10°	1881.4	1882.0	1876.6	1867.0	1851.9	1841.1	1814.6	1789.3	1758.6	1722.5	1696.7
12.5°	1943.0	1945.5	1938.8	1925.7	1918.3	1894.1	1873.4	1843.3	1806.8	1777.9	1738.6
15°	2042.7	2036.1	2031.3	2015.0	2002.4	1977.1	1944.0	1912.7	1872.9	1836.3	1799.6
17.5°	2138.8	2144.0	2135.0	2120.2	2081.0	2051.5	2007.1	1964.3	1914.8	1865.5	1821.7
20°	2224.5	2229.3	2215.5	2189.6	2142.6	2113.2	2054.8	1999.4	1942.2	1879.0	1830.9
22.5°	2331.4	2327.5	2308.8	2269.5	2228.8	2174.3	2111.1	2043.7	1972.0	1900.7	1836.7
25°	2513.4	2488.1	2476.6	2428.0	2374.4	2294.3	2207.6	2108.9	2019.8	1925.4	1843.5
27.5°	2614.2	2606.3	2593.5	2559.6	2503.3	2417.7	2315.5	2195.2	2069.6	1950.3	1843.2
30°	2594.0	2595.2	2596.4	2585.6	2549.5	2485.1	2383.4	2254.0	2104.7	1970.5	1846.5
32.5°	2414.9	2436.8	2457.7	2482.5	2492.7	2480.3	2416.6	2299.7	2146.1	1993.6	1844.6
35°	2017.4	2024.1	2092.0	2159.5	2250.9	2322.0	2369.5	2317.7	2188.3	2013.2	1842.3
37.5°	1573.1	1605.5	1652.6	1728.8	1860.8	1979.1	2131.1	2201.0	2159.3	2019.6	1838.1
40°	1341.0	1371.0	1401.8	1479.3	1590.7	1733.9	1906.7	2054.1	2088.5	1999.4	1823.6
42.5°	1161.8	1185.7	1219.8	1278.1	1371.2	1498.1	1663.0	1855.7	1974.3	1940.6	1793.3
45°	950.9	966.0	992.5	1038.8	1106.3	1205.5	1351.2	1561.8	1745.4	1806.2	1721.4
47.5°	814.0	813.9	834.5	866.5	915.1	999.4	1107.1	1272.2	1468.3	1613.4	1606.6
50°	737.9	734.9	751.1	778.8	817.3	873.3	976.2	1108.0	1296.4	1460.7	1506.5
52.5°	672.4	672.8	682.8	703.2	735.5	783.3	860.1	979.0	1140.0	1308.6	1394.7
55°	586.2	583.8	595.2	609.1	632.6	663.9	719.3	810.1	940.7	1106.8	1218.8
57.5°	507.2	513.9	518.4	528.1	547.6	568.6	615.2	681.9	785.5	928.1	1046.4
60°	461.0	467.6	471.3	480.9	496.5	514.6	550.7	604.8	692.1	814.9	932.3
62.5°	419.6	424.8	426.0	434.6	447.5	465.0	493.4	539.0	607.9	715.2	830.2
65°	359.9	359.9	362.3	371.3	377.4	393.0	414.6	447.8	503.2	586.8	684.9
67.5°	302.4	305.2	304.7	308.6	314.1	326.4	341.9	369.2	410.2	471.3	549.7
70°	264.8	267.2	266.6	269.7	275.6	283.5	296.1	322.0	351.5	403.9	471.3
72.5°	231.1	232.1	230.5	234.5	238.1	245.0	259.0	272.9	300.4	344.6	400.0
75°	176.9	178.2	179.3	181.7	185.4	189.0	196.2	210.1	228.1	261.2	296.8
77.5°	132.7	130.4	133.2	132.9	134.9	137.7	144.1	151.4	166.2	187.2	214.6
80°	99.9	100.5	100.5	101.1	104.2	105.9	111.4	116.7	128.2	143.8	163.1
82.5°	72.9	74.5	73.6	74.6	77.1	78.5	81.5	86.0	92.6	104.9	118.8
85°	39.7	36.7	37.9	39.1	39.1	39.7	42.1	44.0	47.5	52.3	57.8
87.5°	15.9	16.8	17.1	16.9	17.3	17.2	18.9	18.7	20.0	21.2	22.8
90°	21.7	21.0	20.5	19.9	19.3	18.5	17.5	16.5	15.4	14.4	13.0
92.5°	42.6	42.2	41.7	41.3	40.8	40.0	38.7	37.4	36.0	34.7	33.0
95°	77.7	77.3	76.9	76.5	76.1	75.2	73.7	72.4	71.0	69.6	67.6
97.5°	117.8	117.6	117.3	117.1	116.8	116.1	114.8	113.4	112.1	110.8	108.0
100°	148.2	147.8	147.4	147.0	146.6	145.4	143.7	141.9	140.1	138.2	135.6
102.5°	178.5	178.0	177.5	176.8	176.3	175.0	173.1	171.1	169.2	167.2	165.9
105°	224.1	223.5	222.8	222.3	221.7	220.8	219.5	218.4	217.1	216.0	214.7
107.5°	270.7	270.7	270.8	270.8	270.9	270.5	270.0	269.4	268.8	268.1	267.2
110°	305.4	305.6	305.8	306.0	306.2	306.0	305.4	304.8	304.2	303.6	303.0



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	339.4	339.7	340.1	340.5	340.8	340.8	340.5	340.3	340.0	339.7	338.9
115°	393.1	393.2	393.4	393.6	393.9	394.0	394.2	394.4	394.7	394.8	394.4
117.5°	445.4	446.2	447.0	447.8	448.6	449.0	448.8	448.6	448.5	448.4	448.0
120°	481.6	482.4	483.2	484.0	484.8	485.2	485.2	485.2	485.2	485.2	485.0
122.5°	517.7	518.4	519.0	519.7	520.3	520.7	520.8	521.0	521.2	521.4	520.8
125°	571.9	572.1	572.3	572.6	572.7	573.0	573.5	573.8	574.3	574.6	574.4
127.5°	624.0	624.4	624.8	625.2	625.6	625.9	626.1	626.2	626.5	626.7	626.4
130°	658.7	659.1	659.5	659.9	660.3	660.6	660.8	661.0	661.2	661.4	661.0
132.5°	691.2	691.8	692.3	692.9	693.5	693.8	694.0	694.2	694.5	694.6	694.7
135°	741.8	742.6	743.4	744.2	745.0	745.4	745.4	745.4	745.4	745.4	745.2
137.5°	791.3	792.3	793.4	794.3	795.3	795.7	795.5	795.2	795.0	794.8	794.3
140°	823.1	824.1	825.1	826.2	827.2	827.4	827.1	826.6	826.3	825.8	825.2
142.5°	853.5	854.5	855.5	856.5	857.5	857.9	857.6	857.4	857.1	856.9	856.1
145°	899.0	899.6	900.2	900.8	901.4	901.7	901.7	901.7	901.7	901.7	901.2
147.5°	937.9	939.2	940.6	942.0	943.3	943.8	943.3	942.8	942.4	941.8	941.4
150°	966.8	967.1	967.6	968.0	968.4	968.6	968.6	968.6	968.6	968.6	967.8
152.5°	990.6	991.3	992.1	992.8	993.5	993.6	993.2	992.7	992.2	991.8	991.4
155°	1024.6	1025.6	1026.6	1027.6	1028.6	1028.8	1028.0	1027.2	1026.4	1025.6	1025.3
157.5°	1053.0	1054.3	1055.6	1056.9	1058.3	1058.5	1057.7	1056.9	1056.1	1055.3	1055.2
160°	1072.5	1073.5	1074.5	1075.5	1076.5	1076.7	1075.8	1075.0	1074.2	1073.4	1073.2
162.5°	1089.1	1090.3	1091.5	1092.6	1093.8	1093.9	1092.9	1092.0	1091.0	1090.0	1090.0
165°	1111.3	1112.6	1113.7	1115.0	1116.2	1116.3	1115.5	1114.7	1113.9	1113.1	1112.9
167.5°	1129.1	1130.3	1131.6	1132.8	1134.1	1134.1	1132.8	1131.7	1130.4	1129.3	1129.3
170°	1138.4	1139.9	1141.3	1142.6	1144.1	1144.2	1143.0	1141.7	1140.6	1139.3	1139.3
172.5°	1146.4	1147.6	1148.9	1150.1	1151.4	1151.4	1150.2	1149.0	1147.8	1146.6	1146.6
175°	1153.8	1155.2	1156.6	1158.1	1159.4	1159.6	1158.3	1157.1	1155.9	1154.7	1154.7
177.5°	1158.2	1159.3	1160.4	1161.5	1162.6	1162.7	1161.8	1160.8	1159.8	1158.9	1159.0
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1458.9	1455.5	1451.7	1444.9	1436.7	1432.4	1425.7	1421.4	1412.6	1405.4	1397.8
5°	1532.9	1517.3	1502.9	1484.2	1463.7	1450.5	1434.9	1417.4	1399.4	1380.6	1360.2
7.5°	1609.6	1581.9	1551.8	1519.5	1487.8	1458.7	1430.8	1403.6	1378.0	1347.2	1321.1
10°	1661.2	1626.2	1588.9	1545.0	1502.3	1464.9	1427.0	1393.9	1360.2	1324.1	1292.2
12.5°	1712.6	1666.2	1613.5	1565.2	1513.8	1468.7	1424.2	1381.9	1339.5	1299.6	1262.3
15°	1749.0	1708.1	1659.3	1590.7	1532.9	1471.0	1411.9	1357.2	1306.0	1261.5	1214.6
17.5°	1773.0	1720.2	1667.9	1602.0	1526.3	1457.0	1390.2	1327.5	1269.8	1213.4	1168.1
20°	1777.3	1723.1	1668.4	1603.9	1526.3	1446.9	1380.1	1304.8	1242.9	1184.5	1129.1
22.5°	1775.8	1714.5	1654.8	1588.6	1512.9	1439.7	1358.9	1282.2	1215.0	1157.5	1099.7
25°	1762.3	1696.7	1622.0	1555.2	1480.6	1402.9	1321.1	1241.6	1173.0	1107.4	1050.3
27.5°	1751.0	1665.8	1581.4	1503.4	1431.4	1360.2	1281.8	1200.5	1124.4	1057.9	1004.1
30°	1737.0	1643.7	1548.5	1467.3	1393.3	1324.1	1250.1	1170.6	1091.2	1026.2	968.4
32.5°	1724.5	1615.8	1515.4	1426.9	1348.5	1281.2	1213.0	1137.4	1059.4	993.5	935.7
35°	1700.2	1574.5	1459.6	1359.6	1275.9	1206.8	1149.6	1079.1	1007.5	943.7	888.3
37.5°	1669.6	1520.3	1397.0	1292.2	1200.5	1127.6	1074.3	1020.3	951.5	890.0	840.0
40°	1645.5	1481.8	1351.2	1244.0	1149.0	1073.1	1023.8	972.6	915.4	858.3	805.3
42.5°	1615.2	1447.2	1304.9	1189.6	1095.5	1021.6	969.8	926.4	875.9	822.6	773.5
45°	1559.4	1384.3	1230.2	1106.3	1011.1	938.3	884.8	852.2	814.3	763.8	722.2
47.5°	1477.5	1308.8	1149.4	1021.5	923.4	855.9	805.7	774.5	747.8	710.2	672.5
50°	1404.7	1252.5	1091.2	964.2	866.1	798.1	751.7	723.4	700.5	671.6	639.8
52.5°	1323.4	1181.7	1033.8	908.3	811.2	744.1	698.7	673.9	654.8	634.1	602.7
55°	1194.1	1073.7	936.5	817.3	727.6	662.0	622.3	600.7	585.1	569.4	550.1
57.5°	1051.7	957.5	836.0	727.0	644.4	584.8	547.7	526.6	514.4	506.4	495.1
60°	951.5	870.9	766.2	666.8	586.2	533.2	497.1	480.9	470.6	464.0	455.6
62.5°	858.6	792.4	695.4	604.8	534.2	484.1	451.9	436.1	426.3	423.1	416.2
65°	721.7	670.5	590.4	515.2	455.0	412.2	385.2	370.1	364.1	360.5	361.1
67.5°	586.7	555.5	491.2	427.0	379.1	343.2	321.6	310.0	306.9	302.1	302.0
70°	504.4	480.9	426.7	370.8	328.0	300.3	281.1	269.0	266.0	263.6	263.1
72.5°	431.7	411.1	364.1	319.2	280.8	256.5	240.6	233.4	228.5	227.0	226.9
75°	324.4	313.0	275.6	240.1	213.7	196.8	186.0	179.3	175.8	175.1	175.8
77.5°	230.6	220.6	196.9	171.7	155.1	142.3	133.1	130.8	126.7	126.9	126.3
80°	173.3	166.7	151.7	131.8	118.0	107.1	102.3	98.1	96.9	95.1	96.9
82.5°	125.6	118.6	108.3	95.7	84.3	77.8	72.9	71.6	70.9	70.1	70.4
85°	62.0	62.6	56.5	46.9	42.1	38.5	35.5	35.5	34.9	34.3	34.9
87.5°	23.5	22.3	20.1	18.3	15.6	13.8	13.0	13.2	12.0	11.9	12.7
90°	11.7	10.3	8.8	7.3	5.7	4.1	2.5	0.9	2.5	4.1	5.7
92.5°	31.2	29.5	27.8	26.4	25.2	24.1	23.0	21.8	23.0	24.1	25.2
95°	65.5	63.6	61.5	60.4	59.9	59.6	59.1	58.8	59.1	59.6	59.9
97.5°	105.2	102.5	99.7	98.3	98.1	97.9	97.7	97.6	97.7	97.9	98.1
100°	133.0	130.4	127.8	126.5	126.5	126.5	126.5	126.5	126.5	126.5	126.5
102.5°	164.5	163.2	161.8	160.8	160.0	159.2	158.4	157.6	158.4	159.2	160.0
105°	213.6	212.3	211.2	210.0	209.0	208.0	207.0	206.0	207.0	208.0	209.0
107.5°	266.4	265.4	264.5	263.5	262.5	261.5	260.5	259.5	260.5	261.5	262.5
110°	302.4	301.8	301.2	300.4	299.3	298.4	297.4	296.3	297.4	298.4	299.3





TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	338.2	337.4	336.7	336.0	335.6	335.0	334.5	333.9	334.5	335.0	335.6
115°	394.0	393.6	393.2	392.6	391.8	391.0	390.2	389.4	390.2	391.0	391.8
117.5°	447.6	447.3	446.9	446.6	446.1	445.8	445.4	445.1	445.4	445.8	446.1
120°	484.8	484.6	484.4	483.8	482.8	481.8	480.8	479.7	480.8	481.8	482.8
122.5°	520.3	519.8	519.2	518.8	518.4	518.1	517.7	517.4	517.7	518.1	518.4
125°	574.3	574.1	573.8	573.1	571.9	570.7	569.5	568.3	569.5	570.7	571.9
127.5°	626.2	626.0	625.7	625.3	624.6	623.9	623.2	622.5	623.2	623.9	624.6
130°	660.6	660.2	659.8	659.1	658.1	657.1	656.0	655.1	656.0	657.1	658.1
132.5°	694.8	694.9	695.0	694.2	692.5	690.9	689.2	687.6	689.2	690.9	692.5
135°	745.0	744.8	744.6	744.0	742.7	741.5	740.3	739.0	740.3	741.5	742.7
137.5°	793.9	793.4	793.0	792.2	791.0	789.9	788.7	787.6	788.7	789.9	791.0
140°	824.7	824.0	823.4	822.6	821.6	820.6	819.6	818.6	819.6	820.6	821.6
142.5°	855.4	854.6	853.9	853.1	852.2	851.4	850.5	849.7	850.5	851.4	852.2
145°	900.5	899.9	899.3	898.6	897.8	897.0	896.2	895.4	896.2	897.0	897.8
147.5°	940.8	940.4	940.0	939.4	939.0	938.6	938.2	937.7	938.2	938.6	939.0
150°	967.0	966.2	965.4	965.1	965.3	965.5	965.7	965.9	965.7	965.5	965.3
152.5°	991.0	990.8	990.4	990.2	989.9	989.5	989.3	989.0	989.3	989.5	989.9
155°	1025.1	1024.9	1024.7	1024.6	1024.6	1024.6	1024.6	1024.6	1024.6	1024.6	1024.6
157.5°	1054.9	1054.7	1054.5	1054.6	1055.1	1055.5	1056.0	1056.4	1056.0	1055.5	1055.1
160°	1073.0	1072.8	1072.6	1072.8	1073.4	1074.0	1074.6	1075.2	1074.6	1074.0	1073.4
162.5°	1089.9	1089.9	1089.8	1090.0	1090.5	1090.9	1091.4	1091.8	1091.4	1090.9	1090.5
165°	1112.8	1112.6	1112.3	1112.4	1112.9	1113.2	1113.7	1114.1	1113.7	1113.2	1112.9
167.5°	1129.3	1129.3	1129.3	1129.6	1130.4	1131.2	1132.0	1132.8	1132.0	1131.2	1130.4
170°	1139.3	1139.3	1139.3	1139.8	1140.6	1141.4	1142.2	1143.0	1142.2	1141.4	1140.6
172.5°	1146.6	1146.6	1146.6	1147.0	1147.8	1148.6	1149.4	1150.2	1149.4	1148.6	1147.8
175°	1154.7	1154.7	1154.7	1155.1	1155.9	1156.7	1157.5	1158.3	1157.5	1156.7	1155.9
177.5°	1159.2	1159.3	1159.5	1159.9	1160.6	1161.2	1161.8	1162.5	1161.8	1161.2	1160.6
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1393.4	1388.1	1383.8	1374.1	1368.9	1361.6	1355.8	1362.1	1355.4	1358.3	1354.0
5°	1350.0	1333.1	1321.1	1303.6	1288.6	1274.7	1264.5	1262.7	1257.8	1255.4	1248.2
7.5°	1297.7	1276.7	1256.0	1233.1	1213.8	1194.2	1181.7	1171.4	1164.5	1155.5	1149.3
10°	1266.9	1238.6	1214.6	1186.9	1162.8	1141.7	1124.9	1116.4	1108.7	1097.2	1093.0
12.5°	1228.9	1199.6	1170.3	1140.7	1117.5	1094.0	1079.6	1066.8	1061.4	1048.6	1047.2
15°	1183.3	1139.3	1110.4	1080.3	1048.5	1029.2	1017.2	1003.3	997.3	988.3	981.6
17.5°	1128.8	1089.6	1053.5	1022.3	995.0	978.7	963.9	954.3	944.0	938.1	927.2
20°	1089.4	1052.0	1015.9	982.8	961.8	943.1	931.0	922.0	911.2	908.2	897.4
22.5°	1056.1	1014.9	980.3	952.5	929.5	908.5	895.5	889.3	881.8	872.5	870.4
25°	1002.1	959.4	929.9	902.2	881.7	862.5	853.5	845.6	838.4	831.8	829.4
27.5°	955.4	917.2	882.2	857.2	839.4	821.8	813.9	804.3	799.1	793.7	787.2
30°	922.7	883.5	852.8	828.8	809.5	793.9	785.4	778.8	774.0	769.2	765.5
32.5°	888.9	852.7	823.0	799.4	780.2	768.3	760.9	756.2	750.9	745.1	740.6
35°	844.5	804.7	775.8	755.4	740.3	731.3	722.8	718.6	712.6	712.6	707.8
37.5°	794.2	759.9	734.4	715.8	702.2	694.2	685.0	682.2	678.3	675.7	674.0
40°	764.4	732.5	708.4	689.7	675.3	668.7	661.5	656.7	654.2	651.2	650.0
42.5°	733.5	703.1	680.0	662.8	650.2	644.6	637.8	634.5	629.6	625.7	625.0
45°	686.7	657.2	636.1	622.3	611.4	604.8	600.7	593.4	591.0	586.2	585.6
47.5°	642.3	614.0	593.3	582.0	572.5	567.0	560.4	553.2	550.5	548.0	547.8
50°	609.1	583.2	563.9	553.1	544.1	536.3	529.7	524.9	523.0	523.0	524.2
52.5°	575.4	553.3	537.0	523.7	515.2	506.8	500.8	497.8	495.1	498.0	500.2
55°	526.0	503.7	491.7	479.1	470.6	461.0	458.0	456.8	455.0	459.9	462.3
57.5°	473.8	458.2	444.1	431.5	423.9	418.4	414.3	413.6	417.0	419.3	427.0
60°	440.6	422.5	409.8	400.2	391.2	387.6	386.4	385.2	387.6	394.2	404.5
62.5°	403.9	389.3	375.7	368.5	361.9	355.8	355.6	356.3	361.1	368.7	378.9
65°	350.3	337.6	328.6	320.2	314.8	311.1	312.4	314.8	320.2	330.4	341.9
67.5°	295.8	287.1	279.0	272.2	267.0	267.0	268.2	271.8	278.2	290.0	300.4
70°	260.6	251.0	244.3	241.4	237.1	234.7	238.4	244.3	249.8	260.6	269.7
72.5°	225.4	217.3	212.1	210.1	208.2	206.3	207.5	214.0	221.3	232.2	242.6
75°	173.3	170.3	166.7	164.3	162.5	163.7	164.9	170.9	176.9	188.4	200.5
77.5°	126.5	123.4	121.2	120.6	119.7	120.3	123.6	128.0	133.9	142.3	151.4
80°	95.7	94.5	93.3	92.6	92.6	93.3	98.1	101.1	106.6	114.3	121.5
82.5°	69.7	68.9	68.8	68.6	69.1	69.2	72.1	76.1	80.5	86.4	92.6
85°	36.7	35.5	37.3	37.9	36.7	38.5	39.7	42.1	44.0	46.9	49.9
87.5°	13.5	14.8	14.5	15.3	15.6	16.9	16.6	18.7	19.9	21.0	20.7
90°	7.3	8.8	10.3	11.7	13.0	14.4	15.4	16.5	17.5	18.5	19.3
92.5°	26.4	27.8	29.5	31.2	33.0	34.7	36.0	37.4	38.7	40.0	40.8
95°	60.4	61.5	63.6	65.5	67.6	69.6	71.0	72.4	73.7	75.2	76.1
97.5°	98.3	99.7	102.5	105.2	108.0	110.8	112.1	113.4	114.8	116.1	116.8
100°	126.5	127.8	130.4	133.0	135.6	138.2	140.1	141.9	143.7	145.4	146.6
102.5°	160.8	161.8	163.2	164.5	165.9	167.2	169.2	171.1	173.1	175.0	176.3
105°	210.0	211.2	212.3	213.6	214.7	216.0	217.1	218.4	219.5	220.8	221.7
107.5°	263.5	264.5	265.4	266.4	267.2	268.1	268.8	269.4	270.0	270.5	270.9
110°	300.4	301.2	301.8	302.4	303.0	303.6	304.2	304.8	305.4	306.0	306.2



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	336.0	336.7	337.4	338.2	338.9	339.7	340.0	340.3	340.5	340.8	340.8
115°	392.6	393.2	393.6	394.0	394.4	394.8	394.7	394.4	394.2	394.0	393.9
117.5°	446.6	446.9	447.3	447.6	448.0	448.4	448.5	448.6	448.8	449.0	448.6
120°	483.8	484.4	484.6	484.8	485.0	485.2	485.2	485.2	485.2	485.2	484.8
122.5°	518.8	519.2	519.8	520.3	520.8	521.4	521.2	521.0	520.8	520.7	520.3
125°	573.1	573.8	574.1	574.3	574.4	574.6	574.3	573.8	573.5	573.0	572.7
127.5°	625.3	625.7	626.0	626.2	626.4	626.7	626.5	626.2	626.1	625.9	625.6
130°	659.1	659.8	660.2	660.6	661.0	661.4	661.2	661.0	660.8	660.6	660.3
132.5°	694.2	695.0	694.9	694.8	694.7	694.6	694.5	694.2	694.0	693.8	693.5
135°	744.0	744.6	744.8	745.0	745.2	745.4	745.4	745.4	745.4	745.4	745.0
137.5°	792.2	793.0	793.4	793.9	794.3	794.8	795.0	795.2	795.5	795.7	795.3
140°	822.6	823.4	824.0	824.7	825.2	825.8	826.3	826.6	827.1	827.4	827.2
142.5°	853.1	853.9	854.6	855.4	856.1	856.9	857.1	857.4	857.6	857.9	857.5
145°	898.6	899.3	899.9	900.5	901.2	901.7	901.7	901.7	901.7	901.7	901.4
147.5°	939.4	940.0	940.4	940.8	941.4	941.8	942.4	942.8	943.3	943.8	943.3
150°	965.1	965.4	966.2	967.0	967.8	968.6	968.6	968.6	968.6	968.6	968.4
152.5°	990.2	990.4	990.8	991.0	991.4	991.8	992.2	992.7	993.2	993.6	993.5
155°	1024.6	1024.7	1024.9	1025.1	1025.3	1025.6	1026.4	1027.2	1028.0	1028.8	1028.6
157.5°	1054.6	1054.5	1054.7	1054.9	1055.2	1055.3	1056.1	1056.9	1057.7	1058.5	1058.3
160°	1072.8	1072.6	1072.8	1073.0	1073.2	1073.4	1074.2	1075.0	1075.8	1076.7	1076.5
162.5°	1090.0	1089.8	1089.9	1089.9	1090.0	1090.0	1091.0	1092.0	1092.9	1093.9	1093.8
165°	1112.4	1112.3	1112.6	1112.8	1112.9	1113.1	1113.9	1114.7	1115.5	1116.3	1116.2
167.5°	1129.6	1129.3	1129.3	1129.3	1129.3	1129.3	1130.4	1131.7	1132.8	1134.1	1134.1
170°	1139.8	1139.3	1139.3	1139.3	1139.3	1139.3	1140.6	1141.7	1143.0	1144.2	1144.1
172.5°	1147.0	1146.6	1146.6	1146.6	1146.6	1146.6	1147.8	1149.0	1150.2	1151.4	1151.4
175°	1155.1	1154.7	1154.7	1154.7	1154.7	1154.7	1155.9	1157.1	1158.3	1159.6	1159.4
177.5°	1159.9	1159.5	1159.3	1159.2	1159.0	1158.9	1159.8	1160.8	1161.8	1162.7	1162.6
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1351.0	1354.4	1351.6	1355.4	1351.6	1354.4	1351.0	1354.0	1358.3	1355.4	1362.1
5°	1245.3	1239.8	1243.4	1241.0	1243.4	1239.8	1245.3	1248.2	1255.4	1257.8	1262.7
7.5°	1147.5	1142.4	1136.4	1133.6	1136.4	1142.4	1147.5	1149.3	1155.5	1164.5	1171.4
10°	1086.4	1079.8	1079.1	1075.0	1079.1	1079.8	1086.4	1093.0	1097.2	1108.7	1116.4
12.5°	1041.6	1035.5	1028.6	1026.8	1028.6	1035.5	1041.6	1047.2	1048.6	1061.4	1066.8
15°	978.0	973.2	969.0	972.6	969.0	973.2	978.0	981.6	988.3	997.3	1003.3
17.5°	925.1	921.2	920.5	916.1	920.5	921.2	925.1	927.2	938.1	944.0	954.3
20°	892.0	888.9	890.2	882.3	890.2	888.9	892.0	897.4	908.2	911.2	922.0
22.5°	865.5	859.6	858.9	857.3	858.9	859.6	865.5	870.4	872.5	881.8	889.3
25°	823.9	820.9	818.0	820.9	818.0	820.9	823.9	829.4	831.8	838.4	845.6
27.5°	787.7	784.1	783.3	783.6	783.3	784.1	787.7	787.2	793.7	799.1	804.3
30°	765.5	759.6	760.2	759.6	760.2	759.6	765.5	765.5	769.2	774.0	778.8
32.5°	741.5	737.4	736.6	735.5	736.6	737.4	741.5	740.6	745.1	750.9	756.2
35°	706.0	706.0	702.9	702.9	702.9	706.0	706.0	707.8	712.6	712.6	718.6
37.5°	672.6	672.0	670.2	670.5	670.2	672.0	672.6	674.0	675.7	678.3	682.2
40°	647.6	647.0	645.2	641.6	645.2	647.0	647.6	650.0	651.2	654.2	656.7
42.5°	623.5	621.5	620.6	619.5	620.6	621.5	623.5	625.0	625.7	629.6	634.5
45°	585.6	585.6	584.4	583.8	584.4	585.6	585.6	585.6	586.2	591.0	593.4
47.5°	548.8	549.8	552.1	551.8	552.1	549.8	548.8	547.8	548.0	550.5	553.2
50°	526.6	527.3	529.1	529.7	529.1	527.3	526.6	524.2	523.0	523.0	524.9
52.5°	502.0	505.6	507.8	507.5	507.8	505.6	502.0	500.2	498.0	495.1	497.8
55°	467.6	471.9	476.1	476.7	476.1	471.9	467.6	462.3	459.9	455.0	456.8
57.5°	433.5	439.4	443.9	445.4	443.9	439.4	433.5	427.0	419.3	417.0	413.6
60°	410.5	418.3	423.7	426.1	423.7	418.3	410.5	404.5	394.2	387.6	385.2
62.5°	388.3	397.1	402.5	403.0	402.5	397.1	388.3	378.9	368.7	361.1	356.3
65°	352.0	361.1	366.0	369.5	366.0	361.1	352.0	341.9	330.4	320.2	314.8
67.5°	313.1	322.1	327.4	330.3	327.4	322.1	313.1	300.4	290.0	278.2	271.8
70°	284.7	293.7	301.0	303.4	301.0	293.7	284.7	269.7	260.6	249.8	244.3
72.5°	256.7	264.8	270.6	273.5	270.6	264.8	256.7	242.6	232.2	221.3	214.0
75°	208.2	219.1	224.5	227.5	224.5	219.1	208.2	200.5	188.4	176.9	170.9
77.5°	160.6	170.4	173.7	175.2	173.7	170.4	160.6	151.4	142.3	133.9	128.0
80°	128.8	134.8	139.0	139.6	139.0	134.8	128.8	121.5	114.3	106.6	101.1
82.5°	99.0	104.0	105.3	106.9	105.3	104.0	99.0	92.6	86.4	80.5	76.1
85°	54.1	56.5	57.2	56.5	57.2	56.5	54.1	49.9	46.9	44.0	42.1
87.5°	21.8	21.4	21.6	22.6	21.6	21.4	21.8	20.7	21.0	19.9	18.7
90°	19.9	20.5	21.0	21.7	21.0	20.5	19.9	19.3	18.5	17.5	16.5
92.5°	41.3	41.7	42.2	42.6	42.2	41.7	41.3	40.8	40.0	38.7	37.4
95°	76.5	76.9	77.3	77.7	77.3	76.9	76.5	76.1	75.2	73.7	72.4
97.5°	117.1	117.3	117.6	117.8	117.6	117.3	117.1	116.8	116.1	114.8	113.4
100°	147.0	147.4	147.8	148.2	147.8	147.4	147.0	146.6	145.4	143.7	141.9
102.5°	176.8	177.5	178.0	178.5	178.0	177.5	176.8	176.3	175.0	173.1	171.1
105°	222.3	222.8	223.5	224.1	223.5	222.8	222.3	221.7	220.8	219.5	218.4
107.5°	270.8	270.8	270.7	270.7	270.7	270.8	270.8	270.9	270.5	270.0	269.4
110°	306.0	305.8	305.6	305.4	305.6	305.8	306.0	306.2	306.0	305.4	304.8



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	340.5	340.1	339.7	339.4	339.7	340.1	340.5	340.8	340.8	340.5	340.3
115°	393.6	393.4	393.2	393.1	393.2	393.4	393.6	393.9	394.0	394.2	394.4
117.5°	447.8	447.0	446.2	445.4	446.2	447.0	447.8	448.6	449.0	448.8	448.6
120°	484.0	483.2	482.4	481.6	482.4	483.2	484.0	484.8	485.2	485.2	485.2
122.5°	519.7	519.0	518.4	517.7	518.4	519.0	519.7	520.3	520.7	520.8	521.0
125°	572.6	572.3	572.1	571.9	572.1	572.3	572.6	572.7	573.0	573.5	573.8
127.5°	625.2	624.8	624.4	624.0	624.4	624.8	625.2	625.6	625.9	626.1	626.2
130°	659.9	659.5	659.1	658.7	659.1	659.5	659.9	660.3	660.6	660.8	661.0
132.5°	692.9	692.3	691.8	691.2	691.8	692.3	692.9	693.5	693.8	694.0	694.2
135°	744.2	743.4	742.6	741.8	742.6	743.4	744.2	745.0	745.4	745.4	745.4
137.5°	794.3	793.4	792.3	791.3	792.3	793.4	794.3	795.3	795.7	795.5	795.2
140°	826.2	825.1	824.1	823.1	824.1	825.1	826.2	827.2	827.4	827.1	826.6
142.5°	856.5	855.5	854.5	853.5	854.5	855.5	856.5	857.5	857.9	857.6	857.4
145°	900.8	900.2	899.6	899.0	899.6	900.2	900.8	901.4	901.7	901.7	901.7
147.5°	942.0	940.6	939.2	937.9	939.2	940.6	942.0	943.3	943.8	943.3	942.8
150°	968.0	967.6	967.1	966.8	967.1	967.6	968.0	968.4	968.6	968.6	968.6
152.5°	992.8	992.1	991.3	990.6	991.3	992.1	992.8	993.5	993.6	993.2	992.7
155°	1027.6	1026.6	1025.6	1024.6	1025.6	1026.6	1027.6	1028.6	1028.8	1028.0	1027.2
157.5°	1056.9	1055.6	1054.3	1053.0	1054.3	1055.6	1056.9	1058.3	1058.5	1057.7	1056.9
160°	1075.5	1074.5	1073.5	1072.5	1073.5	1074.5	1075.5	1076.5	1076.7	1075.8	1075.0
162.5°	1092.6	1091.5	1090.3	1089.1	1090.3	1091.5	1092.6	1093.8	1093.9	1092.9	1092.0
165°	1115.0	1113.7	1112.6	1111.3	1112.6	1113.7	1115.0	1116.2	1116.3	1115.5	1114.7
167.5°	1132.8	1131.6	1130.3	1129.1	1130.3	1131.6	1132.8	1134.1	1134.1	1132.8	1131.7
170°	1142.6	1141.3	1139.9	1138.4	1139.9	1141.3	1142.6	1144.1	1144.2	1143.0	1141.7
172.5°	1150.1	1148.9	1147.6	1146.4	1147.6	1148.9	1150.1	1151.4	1151.4	1150.2	1149.0
175°	1158.1	1156.6	1155.2	1153.8	1155.2	1156.6	1158.1	1159.4	1159.6	1158.3	1157.1
177.5°	1161.5	1160.4	1159.3	1158.2	1159.3	1160.4	1161.5	1162.6	1162.7	1161.8	1160.8
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1355.8	1361.6	1368.9	1374.1	1383.8	1388.1	1393.4	1397.8	1405.4	1412.6	1421.4
5°	1264.5	1274.7	1288.6	1303.6	1321.1	1333.1	1350.0	1360.2	1380.6	1399.4	1417.4
7.5°	1181.7	1194.2	1213.8	1233.1	1256.0	1276.7	1297.7	1321.1	1347.2	1378.0	1403.6
10°	1124.9	1141.7	1162.8	1186.9	1214.6	1238.6	1266.9	1292.2	1324.1	1360.2	1393.9
12.5°	1079.6	1094.0	1117.5	1140.7	1170.3	1199.6	1228.9	1262.3	1299.6	1339.5	1381.9
15°	1017.2	1029.2	1048.5	1080.3	1110.4	1139.3	1183.3	1214.6	1261.5	1306.0	1357.2
17.5°	963.9	978.7	995.0	1022.3	1053.5	1089.6	1128.8	1168.1	1213.4	1269.8	1327.5
20°	931.0	943.1	961.8	982.8	1015.9	1052.0	1089.4	1129.1	1184.5	1242.9	1304.8
22.5°	895.5	908.5	929.5	952.5	980.3	1014.9	1056.1	1099.7	1157.5	1215.0	1282.2
25°	853.5	862.5	881.7	902.2	929.9	959.4	1002.1	1050.3	1107.4	1173.0	1241.6
27.5°	813.9	821.8	839.4	857.2	882.2	917.2	955.4	1004.1	1057.9	1124.4	1200.5
30°	785.4	793.9	809.5	828.8	852.8	883.5	922.7	968.4	1026.2	1091.2	1170.6
32.5°	760.9	768.3	780.2	799.4	823.0	852.7	888.9	935.7	993.5	1059.4	1137.4
35°	722.8	731.3	740.3	755.4	775.8	804.7	844.5	888.3	943.7	1007.5	1079.1
37.5°	685.0	694.2	702.2	715.8	734.4	759.9	794.2	840.0	890.0	951.5	1020.3
40°	661.5	668.7	675.3	689.7	708.4	732.5	764.4	805.3	858.3	915.4	972.6
42.5°	637.8	644.6	650.2	662.8	680.0	703.1	733.5	773.5	822.6	875.9	926.4
45°	600.7	604.8	611.4	622.3	636.1	657.2	686.7	722.2	763.8	814.3	852.2
47.5°	560.4	567.0	572.5	582.0	593.3	614.0	642.3	672.5	710.2	747.8	774.5
50°	529.7	536.3	544.1	553.1	563.9	583.2	609.1	639.8	671.6	700.5	723.4
52.5°	500.8	506.8	515.2	523.7	537.0	553.3	575.4	602.7	634.1	654.8	673.9
55°	458.0	461.0	470.6	479.1	491.7	503.7	526.0	550.1	569.4	585.1	600.7
57.5°	414.3	418.4	423.9	431.5	444.1	458.2	473.8	495.1	506.4	514.4	526.6
60°	386.4	387.6	391.2	400.2	409.8	422.5	440.6	455.6	464.0	470.6	480.9
62.5°	355.6	355.8	361.9	368.5	375.7	389.3	403.9	416.2	423.1	426.3	436.1
65°	312.4	311.1	314.8	320.2	328.6	337.6	350.3	361.1	360.5	364.1	370.1
67.5°	268.2	267.0	267.0	272.2	279.0	287.1	295.8	302.0	302.1	306.9	310.0
70°	238.4	234.7	237.1	241.4	244.3	251.0	260.6	263.1	263.6	266.0	269.0
72.5°	207.5	206.3	208.2	210.1	212.1	217.3	225.4	226.9	227.0	228.5	233.4
75°	164.9	163.7	162.5	164.3	166.7	170.3	173.3	175.8	175.1	175.8	179.3
77.5°	123.6	120.3	119.7	120.6	121.2	123.4	126.5	126.3	126.9	126.7	130.8
80°	98.1	93.3	92.6	92.6	93.3	94.5	95.7	96.9	95.1	96.9	98.1
82.5°	72.1	69.2	69.1	68.6	68.8	68.9	69.7	70.4	70.1	70.9	71.6
85°	39.7	38.5	36.7	37.9	37.3	35.5	36.7	34.9	34.3	34.9	35.5
87.5°	16.6	16.9	15.6	15.3	14.5	14.8	13.5	12.7	11.9	12.0	13.2
90°	15.4	14.4	13.0	11.7	10.3	8.8	7.3	5.7	4.1	2.5	0.9
92.5°	36.0	34.7	33.0	31.2	29.5	27.8	26.4	25.2	24.1	23.0	21.8
95°	71.0	69.6	67.6	65.5	63.6	61.5	60.4	59.9	59.6	59.1	58.8
97.5°	112.1	110.8	108.0	105.2	102.5	99.7	98.3	98.1	97.9	97.7	97.6
100°	140.1	138.2	135.6	133.0	130.4	127.8	126.5	126.5	126.5	126.5	126.5
102.5°	169.2	167.2	165.9	164.5	163.2	161.8	160.8	160.0	159.2	158.4	157.6
105°	217.1	216.0	214.7	213.6	212.3	211.2	210.0	209.0	208.0	207.0	206.0
107.5°	268.8	268.1	267.2	266.4	265.4	264.5	263.5	262.5	261.5	260.5	259.5
110°	304.2	303.6	303.0	302.4	301.8	301.2	300.4	299.3	298.4	297.4	296.3



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	340.0	339.7	338.9	338.2	337.4	336.7	336.0	335.6	335.0	334.5	333.9
115°	394.7	394.8	394.4	394.0	393.6	393.2	392.6	391.8	391.0	390.2	389.4
117.5°	448.5	448.4	448.0	447.6	447.3	446.9	446.6	446.1	445.8	445.4	445.1
120°	485.2	485.2	485.0	484.8	484.6	484.4	483.8	482.8	481.8	480.8	479.7
122.5°	521.2	521.4	520.8	520.3	519.8	519.2	518.8	518.4	518.1	517.7	517.4
125°	574.3	574.6	574.4	574.3	574.1	573.8	573.1	571.9	570.7	569.5	568.3
127.5°	626.5	626.7	626.4	626.2	626.0	625.7	625.3	624.6	623.9	623.2	622.5
130°	661.2	661.4	661.0	660.6	660.2	659.8	659.1	658.1	657.1	656.0	655.1
132.5°	694.5	694.6	694.7	694.8	694.9	695.0	694.2	692.5	690.9	689.2	687.6
135°	745.4	745.4	745.2	745.0	744.8	744.6	744.0	742.7	741.5	740.3	739.0
137.5°	795.0	794.8	794.3	793.9	793.4	793.0	792.2	791.0	789.9	788.7	787.6
140°	826.3	825.8	825.2	824.7	824.0	823.4	822.6	821.6	820.6	819.6	818.6
142.5°	857.1	856.9	856.1	855.4	854.6	853.9	853.1	852.2	851.4	850.5	849.7
145°	901.7	901.7	901.2	900.5	899.9	899.3	898.6	897.8	897.0	896.2	895.4
147.5°	942.4	941.8	941.4	940.8	940.4	940.0	939.4	939.0	938.6	938.2	937.7
150°	968.6	968.6	967.8	967.0	966.2	965.4	965.1	965.3	965.5	965.7	965.9
152.5°	992.2	991.8	991.4	991.0	990.8	990.4	990.2	989.9	989.5	989.3	989.0
155°	1026.4	1025.6	1025.3	1025.1	1024.9	1024.7	1024.6	1024.6	1024.6	1024.6	1024.6
157.5°	1056.1	1055.3	1055.2	1054.9	1054.7	1054.5	1054.6	1055.1	1055.5	1056.0	1056.4
160°	1074.2	1073.4	1073.2	1073.0	1072.8	1072.6	1072.8	1073.4	1074.0	1074.6	1075.2
162.5°	1091.0	1090.0	1090.0	1089.9	1089.9	1089.8	1090.0	1090.5	1090.9	1091.4	1091.8
165°	1113.9	1113.1	1112.9	1112.8	1112.6	1112.3	1112.4	1112.9	1113.2	1113.7	1114.1
167.5°	1130.4	1129.3	1129.3	1129.3	1129.3	1129.3	1129.6	1130.4	1131.2	1132.0	1132.8
170°	1140.6	1139.3	1139.3	1139.3	1139.3	1139.3	1139.8	1140.6	1141.4	1142.2	1143.0
172.5°	1147.8	1146.6	1146.6	1146.6	1146.6	1146.6	1147.0	1147.8	1148.6	1149.4	1150.2
175°	1155.9	1154.7	1154.7	1154.7	1154.7	1154.7	1155.1	1155.9	1156.7	1157.5	1158.3
177.5°	1159.8	1158.9	1159.0	1159.2	1159.3	1159.5	1159.9	1160.6	1161.2	1161.8	1162.5
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1425.7	1432.4	1436.7	1444.9	1451.7	1455.5	1458.9	1461.8	1465.2	1468.0	1476.2
5°	1434.9	1450.5	1463.7	1484.2	1502.9	1517.3	1532.9	1546.8	1558.2	1574.5	1587.1
7.5°	1430.8	1458.7	1487.8	1519.5	1551.8	1581.9	1609.6	1635.5	1658.9	1687.4	1712.3
10°	1427.0	1464.9	1502.3	1545.0	1588.9	1626.2	1661.2	1696.7	1722.5	1758.6	1789.3
12.5°	1424.2	1468.7	1513.8	1565.2	1613.5	1666.2	1712.6	1738.6	1777.9	1806.8	1843.3
15°	1411.9	1471.0	1532.9	1590.7	1659.3	1708.1	1749.0	1799.6	1836.3	1872.9	1912.7
17.5°	1390.2	1457.0	1526.3	1602.0	1667.9	1720.2	1773.0	1821.7	1865.5	1914.8	1964.3
20°	1380.1	1446.9	1526.3	1603.9	1668.4	1723.1	1777.3	1830.9	1879.0	1942.2	1999.4
22.5°	1358.9	1439.7	1512.9	1588.6	1654.8	1714.5	1775.8	1836.7	1900.7	1972.0	2043.7
25°	1321.1	1402.9	1480.6	1555.2	1622.0	1696.7	1762.3	1843.5	1925.4	2019.8	2108.9
27.5°	1281.8	1360.2	1431.4	1503.4	1581.4	1665.8	1751.0	1843.2	1950.3	2069.6	2195.2
30°	1250.1	1324.1	1393.3	1467.3	1548.5	1643.7	1737.0	1846.5	1970.5	2104.7	2254.0
32.5°	1213.0	1281.2	1348.5	1426.9	1515.4	1615.8	1724.5	1844.6	1993.6	2146.1	2299.7
35°	1149.6	1206.8	1275.9	1359.6	1459.6	1574.5	1700.2	1842.3	2013.2	2188.3	2317.7
37.5°	1074.3	1127.6	1200.5	1292.2	1397.0	1520.3	1669.6	1838.1	2019.6	2159.3	2201.0
40°	1023.8	1073.1	1149.0	1244.0	1351.2	1481.8	1645.5	1823.6	1999.4	2088.5	2054.1
42.5°	969.8	1021.6	1095.5	1189.6	1304.9	1447.2	1615.2	1793.3	1940.6	1974.3	1855.7
45°	884.8	938.3	1011.1	1106.3	1230.2	1384.3	1559.4	1721.4	1806.2	1745.4	1561.8
47.5°	805.7	855.9	923.4	1021.5	1149.4	1308.8	1477.5	1606.6	1613.4	1468.3	1272.2
50°	751.7	798.1	866.1	964.2	1091.2	1252.5	1404.7	1506.5	1460.7	1296.4	1108.0
52.5°	698.7	744.1	811.2	908.3	1033.8	1181.7	1323.4	1394.7	1308.6	1140.0	979.0
55°	622.3	662.0	727.6	817.3	936.5	1073.7	1194.1	1218.8	1106.8	940.7	810.1
57.5°	547.7	584.8	644.4	727.0	836.0	957.5	1051.7	1046.4	928.1	785.5	681.9
60°	497.1	533.2	586.2	666.8	766.2	870.9	951.5	932.3	814.9	692.1	604.8
62.5°	451.9	484.1	534.2	604.8	695.4	792.4	858.6	830.2	715.2	607.9	539.0
65°	385.2	412.2	455.0	515.2	590.4	670.5	721.7	684.9	586.8	503.2	447.8
67.5°	321.6	343.2	379.1	427.0	491.2	555.5	586.7	549.7	471.3	410.2	369.2
70°	281.1	300.3	328.0	370.8	426.7	480.9	504.4	471.3	403.9	351.5	322.0
72.5°	240.6	256.5	280.8	319.2	364.1	411.1	431.7	400.0	344.6	300.4	272.9
75°	186.0	196.8	213.7	240.1	275.6	313.0	324.4	296.8	261.2	228.1	210.1
77.5°	133.1	142.3	155.1	171.7	196.9	220.6	230.6	214.6	187.2	166.2	151.4
80°	102.3	107.1	118.0	131.8	151.7	166.7	173.3	163.1	143.8	128.2	116.7
82.5°	72.9	77.8	84.3	95.7	108.3	118.6	125.6	118.8	104.9	92.6	86.0
85°	35.5	38.5	42.1	46.9	56.5	62.6	62.0	57.8	52.3	47.5	44.0
87.5°	13.0	13.8	15.6	18.3	20.1	22.3	23.5	22.8	21.2	20.0	18.7
90°	2.5	4.1	5.7	7.3	8.8	10.3	11.7	13.0	14.4	15.4	16.5
92.5°	23.0	24.1	25.2	26.4	27.8	29.5	31.2	33.0	34.7	36.0	37.4
95°	59.1	59.6	59.9	60.4	61.5	63.6	65.5	67.6	69.6	71.0	72.4
97.5°	97.7	97.9	98.1	98.3	99.7	102.5	105.2	108.0	110.8	112.1	113.4
100°	126.5	126.5	126.5	126.5	127.8	130.4	133.0	135.6	138.2	140.1	141.9
102.5°	158.4	159.2	160.0	160.8	161.8	163.2	164.5	165.9	167.2	169.2	171.1
105°	207.0	208.0	209.0	210.0	211.2	212.3	213.6	214.7	216.0	217.1	218.4
107.5°	260.5	261.5	262.5	263.5	264.5	265.4	266.4	267.2	268.1	268.8	269.4
110°	297.4	298.4	299.3	300.4	301.2	301.8	302.4	303.0	303.6	304.2	304.8





TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	334.5	335.0	335.6	336.0	336.7	337.4	338.2	338.9	339.7	340.0	340.3
115°	390.2	391.0	391.8	392.6	393.2	393.6	394.0	394.4	394.8	394.7	394.4
117.5°	445.4	445.8	446.1	446.6	446.9	447.3	447.6	448.0	448.4	448.5	448.6
120°	480.8	481.8	482.8	483.8	484.4	484.6	484.8	485.0	485.2	485.2	485.2
122.5°	517.7	518.1	518.4	518.8	519.2	519.8	520.3	520.8	521.4	521.2	521.0
125°	569.5	570.7	571.9	573.1	573.8	574.1	574.3	574.4	574.6	574.3	573.8
127.5°	623.2	623.9	624.6	625.3	625.7	626.0	626.2	626.4	626.7	626.5	626.2
130°	656.0	657.1	658.1	659.1	659.8	660.2	660.6	661.0	661.4	661.2	661.0
132.5°	689.2	690.9	692.5	694.2	695.0	694.9	694.8	694.7	694.6	694.5	694.2
135°	740.3	741.5	742.7	744.0	744.6	744.8	745.0	745.2	745.4	745.4	745.4
137.5°	788.7	789.9	791.0	792.2	793.0	793.4	793.9	794.3	794.8	795.0	795.2
140°	819.6	820.6	821.6	822.6	823.4	824.0	824.7	825.2	825.8	826.3	826.6
142.5°	850.5	851.4	852.2	853.1	853.9	854.6	855.4	856.1	856.9	857.1	857.4
145°	896.2	897.0	897.8	898.6	899.3	899.9	900.5	901.2	901.7	901.7	901.7
147.5°	938.2	938.6	939.0	939.4	940.0	940.4	940.8	941.4	941.8	942.4	942.8
150°	965.7	965.5	965.3	965.1	965.4	966.2	967.0	967.8	968.6	968.6	968.6
152.5°	989.3	989.5	989.9	990.2	990.4	990.8	991.0	991.4	991.8	992.2	992.7
155°	1024.6	1024.6	1024.6	1024.6	1024.7	1024.9	1025.1	1025.3	1025.6	1026.4	1027.2
157.5°	1056.0	1055.5	1055.1	1054.6	1054.5	1054.7	1054.9	1055.2	1055.3	1056.1	1056.9
160°	1074.6	1074.0	1073.4	1072.8	1072.6	1072.8	1073.0	1073.2	1073.4	1074.2	1075.0
162.5°	1091.4	1090.9	1090.5	1090.0	1089.8	1089.9	1089.9	1090.0	1090.0	1091.0	1092.0
165°	1113.7	1113.2	1112.9	1112.4	1112.3	1112.6	1112.8	1112.9	1113.1	1113.9	1114.7
167.5°	1132.0	1131.2	1130.4	1129.6	1129.3	1129.3	1129.3	1129.3	1129.3	1130.4	1131.7
170°	1142.2	1141.4	1140.6	1139.8	1139.3	1139.3	1139.3	1139.3	1139.3	1140.6	1141.7
172.5°	1149.4	1148.6	1147.8	1147.0	1146.6	1146.6	1146.6	1146.6	1146.6	1147.8	1149.0
175°	1157.5	1156.7	1155.9	1155.1	1154.7	1154.7	1154.7	1154.7	1154.7	1155.9	1157.1
177.5°	1161.8	1161.2	1160.6	1159.9	1159.5	1159.3	1159.2	1159.0	1158.9	1159.8	1160.8
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1483.0	1486.8	1495.0	1492.1	1496.0	1497.9	1499.9
5°	1602.8	1622.0	1630.4	1629.2	1641.9	1638.9	1635.8
7.5°	1738.0	1758.3	1769.6	1783.7	1791.9	1792.4	1799.6
10°	1814.6	1841.1	1851.9	1867.0	1876.6	1882.0	1881.4
12.5°	1873.4	1894.1	1918.3	1925.7	1938.8	1945.5	1943.0
15°	1944.0	1977.1	2002.4	2015.0	2031.3	2036.1	2042.7
17.5°	2007.1	2051.5	2081.0	2120.2	2135.0	2144.0	2138.8
20°	2054.8	2113.2	2142.6	2189.6	2215.5	2229.3	2224.5
22.5°	2111.1	2174.3	2228.8	2269.5	2308.8	2327.5	2331.4
25°	2207.6	2294.3	2374.4	2428.0	2476.6	2488.1	2513.4
27.5°	2315.5	2417.7	2503.3	2559.6	2593.5	2606.3	2614.2
30°	2383.4	2485.1	2549.5	2585.6	2596.4	2595.2	2594.0
32.5°	2416.6	2480.3	2492.7	2482.5	2457.7	2436.8	2414.9
35°	2369.5	2322.0	2250.9	2159.5	2092.0	2024.1	2017.4
37.5°	2131.1	1979.1	1860.8	1728.8	1652.6	1605.5	1573.1
40°	1906.7	1733.9	1590.7	1479.3	1401.8	1371.0	1341.0
42.5°	1663.0	1498.1	1371.2	1278.1	1219.8	1185.7	1161.8
45°	1351.2	1205.5	1106.3	1038.8	992.5	966.0	950.9
47.5°	1107.1	999.4	915.1	866.5	834.5	813.9	814.0
50°	976.2	873.3	817.3	778.8	751.1	734.9	737.9
52.5°	860.1	783.3	735.5	703.2	682.8	672.8	672.4
55°	719.3	663.9	632.6	609.1	595.2	583.8	586.2
57.5°	615.2	568.6	547.6	528.1	518.4	513.9	507.2
60°	550.7	514.6	496.5	480.9	471.3	467.6	461.0
62.5°	493.4	465.0	447.5	434.6	426.0	424.8	419.6
65°	414.6	393.0	377.4	371.3	362.3	359.9	359.9
67.5°	341.9	326.4	314.1	308.6	304.7	305.2	302.4
70°	296.1	283.5	275.6	269.7	266.6	267.2	264.8
72.5°	259.0	245.0	238.1	234.5	230.5	232.1	231.1
75°	196.2	189.0	185.4	181.7	179.3	178.2	176.9
77.5°	144.1	137.7	134.9	132.9	133.2	130.4	132.7
80°	111.4	105.9	104.2	101.1	100.5	100.5	99.9
82.5°	81.5	78.5	77.1	74.6	73.6	74.5	72.9
85°	42.1	39.7	39.1	39.1	37.9	36.7	39.7
87.5°	18.9	17.2	17.3	16.9	17.1	16.8	15.9
90°	17.5	18.5	19.3	19.9	20.5	21.0	21.7
92.5°	38.7	40.0	40.8	41.3	41.7	42.2	42.6
95°	73.7	75.2	76.1	76.5	76.9	77.3	77.7
97.5°	114.8	116.1	116.8	117.1	117.3	117.6	117.8
100°	143.7	145.4	146.6	147.0	147.4	147.8	148.2
102.5°	173.1	175.0	176.3	176.8	177.5	178.0	178.5
105°	219.5	220.8	221.7	222.3	222.8	223.5	224.1
107.5°	270.0	270.5	270.9	270.8	270.8	270.7	270.7
110°	305.4	306.0	306.2	306.0	305.8	305.6	305.4



TEST NUMBER: P333443-940

CATALOG NUMBER: S125DIW-S1090D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	340.5	340.8	340.8	340.5	340.1	339.7	339.4
115°	394.2	394.0	393.9	393.6	393.4	393.2	393.1
117.5°	448.8	449.0	448.6	447.8	447.0	446.2	445.4
120°	485.2	485.2	484.8	484.0	483.2	482.4	481.6
122.5°	520.8	520.7	520.3	519.7	519.0	518.4	517.7
125°	573.5	573.0	572.7	572.6	572.3	572.1	571.9
127.5°	626.1	625.9	625.6	625.2	624.8	624.4	624.0
130°	660.8	660.6	660.3	659.9	659.5	659.1	658.7
132.5°	694.0	693.8	693.5	692.9	692.3	691.8	691.2
135°	745.4	745.4	745.0	744.2	743.4	742.6	741.8
137.5°	795.5	795.7	795.3	794.3	793.4	792.3	791.3
140°	827.1	827.4	827.2	826.2	825.1	824.1	823.1
142.5°	857.6	857.9	857.5	856.5	855.5	854.5	853.5
145°	901.7	901.7	901.4	900.8	900.2	899.6	899.0
147.5°	943.3	943.8	943.3	942.0	940.6	939.2	937.9
150°	968.6	968.6	968.4	968.0	967.6	967.1	966.8
152.5°	993.2	993.6	993.5	992.8	992.1	991.3	990.6
155°	1028.0	1028.8	1028.6	1027.6	1026.6	1025.6	1024.6
157.5°	1057.7	1058.5	1058.3	1056.9	1055.6	1054.3	1053.0
160°	1075.8	1076.7	1076.5	1075.5	1074.5	1073.5	1072.5
162.5°	1092.9	1093.9	1093.8	1092.6	1091.5	1090.3	1089.1
165°	1115.5	1116.3	1116.2	1115.0	1113.7	1112.6	1111.3
167.5°	1132.8	1134.1	1134.1	1132.8	1131.6	1130.3	1129.1
170°	1143.0	1144.2	1144.1	1142.6	1141.3	1139.9	1138.4
172.5°	1150.2	1151.4	1151.4	1150.1	1148.9	1147.6	1146.4
175°	1158.3	1159.6	1159.4	1158.1	1156.6	1155.2	1153.8
177.5°	1161.8	1162.7	1162.6	1161.5	1160.4	1159.3	1158.2
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0

(END OF REPORT)