

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333452-940

Luminaire Tested: **S125DIW-S1090D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333452-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1340U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8745.4 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333452-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333452-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	55	46	45	44	38
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9827	9827	9827
5°	9849	9756	9818
10°	9789	9686	9742
15°	9682	9570	9610
20°	9531	9407	9423
25°	9368	9213	9204
30°	9165	9004	8959
35°	8949	8779	8656
40°	8728	8535	8413
45°	8488	8312	8147
50°	8225	8043	7801
55°	7970	7739	7523
60°	7665	7432	7167
65°	7303	7065	6825
70°	6956	6637	6411
75°	6338	6128	5916
80°	5642	5553	5415
85°	4905	4994	4728



TEST NUMBER: P333452-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.5	1.6
10°-20°	405.3	4.6
20°-30°	598.4	6.8
30°-40°	698.2	8.0
40°-50°	701.3	8.0
50°-60°	615.6	7.0
60°-70°	458.7	5.2
70°-80°	262.3	3.0
80°-90°	79.5	0.9
90°-100°	56.6	0.6
100°-110°	348.8	4.0
110°-120°	632.6	7.2
120°-130°	811.9	9.3
130°-140°	873.3	10.0
140°-150°	819.7	9.4
150°-160°	663.1	7.6
160°-170°	428.8	4.9
170°-180°	147.9	1.7
0°-30°	1147.1	13.1
0°-40°	1845.3	21.1
0°-60°	3162.2	36.2
0°-90°	3962.6	45.3
90°-120°	1038.1	11.9
90°-150°	3542.9	40.5
90°-180°	4783.0	54.7
0°-180°	8745.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1519	1516	1505	1515	1514	144
15°	1448	1444	1431	1437	1437	408
25°	1315	1308	1293	1295	1292	605
35°	1135	1130	1114	1107	1098	710
45°	929	924	910	896	892	716
55°	708	703	687	677	668	632
65°	478	475	462	452	447	474
75°	254	251	246	242	237	271
85°	66	67	67	66	64	74
90°	1	10	18	24	28	6
95°	66	60	18	24	24	84
105°	340	344	344	344	343	360
115°	637	643	644	640	633	632
125°	906	914	914	910	906	809
135°	1130	1137	1135	1132	1126	871
145°	1310	1313	1313	1313	1307	819
155°	1443	1437	1439	1441	1433	665
165°	1523	1516	1517	1523	1515	430
175°	1558	1551	1552	1560	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333452-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1525.4	1524.8	1524.1	1523.5	1522.9	1521.4	1519.3	1517.2	1515.0	1512.9	1515.0
5°	1519.2	1518.7	1518.1	1517.6	1517.1	1515.5	1512.8	1510.1	1507.4	1504.8	1507.2
7.5°	1505.2	1504.7	1504.1	1503.6	1503.1	1501.3	1498.3	1495.4	1492.5	1489.5	1491.9
10°	1492.7	1492.2	1491.7	1491.1	1490.6	1488.8	1485.9	1482.9	1480.0	1477.0	1479.2
12.5°	1477.3	1476.3	1475.3	1474.4	1473.5	1471.6	1468.8	1466.2	1463.4	1460.6	1462.4
15°	1448.1	1447.3	1446.5	1445.7	1444.9	1443.1	1440.1	1437.2	1434.2	1431.3	1432.6
17.5°	1414.7	1413.5	1412.3	1411.1	1410.0	1407.8	1404.8	1401.8	1398.7	1395.6	1397.3
20°	1386.8	1386.3	1385.7	1385.2	1384.6	1382.6	1379.1	1375.6	1372.2	1368.7	1370.6
22.5°	1358.8	1357.9	1356.9	1355.9	1355.0	1352.8	1349.6	1346.3	1343.1	1339.8	1341.0
25°	1314.6	1313.2	1311.9	1310.5	1309.2	1306.8	1303.3	1299.8	1296.4	1292.9	1293.4
27.5°	1262.8	1261.9	1261.1	1260.3	1259.5	1257.4	1253.7	1250.2	1246.6	1243.0	1243.1
30°	1229.0	1228.2	1227.4	1226.6	1225.8	1223.4	1219.4	1215.4	1211.4	1207.4	1206.8
32.5°	1192.5	1191.2	1190.0	1188.7	1187.6	1185.2	1181.5	1177.9	1174.4	1170.8	1169.8
35°	1135.1	1134.1	1133.0	1131.9	1130.9	1128.5	1124.7	1121.0	1117.2	1113.5	1112.1
37.5°	1075.7	1074.3	1073.0	1071.7	1070.3	1067.9	1064.3	1060.9	1057.3	1053.8	1051.8
40°	1035.3	1033.9	1032.6	1031.3	1029.9	1027.3	1023.6	1019.8	1016.1	1012.4	1010.0
42.5°	991.9	990.8	989.7	988.6	987.4	985.0	981.2	977.5	973.7	970.0	967.8
45°	929.3	928.3	927.2	926.1	925.1	922.9	919.7	916.5	913.3	910.1	906.9
47.5°	861.9	861.9	862.0	862.1	862.1	860.2	856.4	852.5	848.6	844.8	841.5
50°	818.6	817.8	817.0	816.2	815.4	813.3	810.1	806.9	803.7	800.5	797.0
52.5°	774.3	773.6	773.1	772.5	772.0	769.9	766.5	763.0	759.6	756.2	753.1
55°	707.8	707.0	706.2	705.4	704.6	702.3	698.6	694.8	691.1	687.3	684.9
57.5°	637.8	637.3	636.9	636.5	636.1	634.3	631.1	627.9	624.8	621.6	618.5
60°	593.4	592.4	591.3	590.2	589.2	587.2	584.2	581.3	578.4	575.4	572.7
62.5°	547.2	546.4	545.5	544.7	543.9	542.2	539.6	537.1	534.6	532.1	529.1
65°	477.9	477.3	476.8	476.3	475.7	474.0	471.1	468.1	465.2	462.3	459.9
67.5°	410.7	409.6	408.5	407.3	406.3	404.6	402.3	400.2	398.0	395.8	393.8
70°	368.4	367.0	365.7	364.4	363.0	361.1	358.7	356.3	353.9	351.5	349.9
72.5°	322.2	321.2	320.3	319.4	318.5	317.3	315.8	314.1	312.6	311.0	309.2
75°	254.0	253.4	252.9	252.4	251.8	250.9	249.6	248.3	246.9	245.6	244.8
77.5°	191.2	190.9	190.7	190.6	190.3	189.8	189.0	188.3	187.6	186.8	186.4
80°	151.7	151.7	151.7	151.7	151.7	151.4	150.9	150.3	149.8	149.3	149.0
82.5°	117.0	116.5	116.2	115.7	115.3	115.0	114.9	114.9	114.7	114.6	114.1
85°	66.2	66.4	66.7	67.0	67.2	67.4	67.4	67.4	67.4	67.4	67.1
87.5°	26.2	26.7	27.0	27.5	27.9	28.2	28.3	28.4	28.6	28.7	29.0
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	17.7	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8
95°	65.8	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8
97.5°	137.4	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6
100°	192.8	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6
102.5°	249.1	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1
105°	339.5	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5
110°	494.2	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7



TEST NUMBER: P333452-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	551.4	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6
115°	637.3	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2
117.5°	726.2	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1
120°	781.6	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5
122.5°	830.5	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1
125°	906.3	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4
127.5°	978.6	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1
130°	1022.9	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1
132.5°	1067.3	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3
135°	1130.3	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4
137.5°	1188.3	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3
140°	1226.1	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8
142.5°	1260.3	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4
145°	1310.4	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0
147.5°	1354.2	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5
150°	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5
152.5°	1408.7	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5
155°	1443.1	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3
157.5°	1469.7	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6
160°	1488.2	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5
162.5°	1503.0	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6
165°	1522.9	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6
167.5°	1537.6	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5
170°	1546.0	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1
172.5°	1551.5	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3
175°	1557.5	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7
177.5°	1560.2	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333452-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1517.2	1519.3	1521.4	1522.4	1522.2	1522.0	1521.8	1521.6
5°	1509.6	1512.0	1514.4	1515.5	1515.2	1514.9	1514.7	1514.4
7.5°	1494.2	1496.6	1499.0	1500.0	1499.8	1499.5	1499.2	1499.0
10°	1481.3	1483.5	1485.6	1486.6	1486.3	1486.0	1485.8	1485.5
12.5°	1464.1	1465.8	1467.5	1468.4	1468.3	1468.2	1468.2	1468.1
15°	1434.0	1435.3	1436.6	1437.3	1437.3	1437.3	1437.3	1437.3
17.5°	1399.0	1400.6	1402.3	1402.5	1401.1	1399.8	1398.5	1397.1
20°	1372.4	1374.3	1376.2	1376.4	1375.1	1373.8	1372.4	1371.1
22.5°	1342.3	1343.5	1344.7	1344.9	1344.0	1343.1	1342.2	1341.2
25°	1294.0	1294.5	1295.0	1294.9	1294.1	1293.2	1292.4	1291.6
27.5°	1243.2	1243.3	1243.5	1243.1	1242.3	1241.5	1240.7	1239.9
30°	1206.3	1205.8	1205.2	1204.6	1203.8	1203.0	1202.2	1201.4
32.5°	1168.9	1167.9	1167.0	1165.7	1164.3	1162.9	1161.4	1159.9
35°	1110.8	1109.5	1108.1	1106.4	1104.3	1102.2	1100.0	1097.9
37.5°	1049.8	1047.8	1045.9	1044.3	1043.0	1041.8	1040.5	1039.4
40°	1007.5	1005.1	1002.7	1001.1	1000.3	999.5	998.7	997.9
42.5°	965.6	963.4	961.3	959.5	958.3	957.1	955.8	954.6
45°	903.7	900.4	897.2	895.2	894.4	893.6	892.8	892.0
47.5°	838.3	835.0	831.8	829.2	827.3	825.5	823.6	821.7
50°	793.5	790.1	786.6	783.9	782.0	780.2	778.3	776.4
52.5°	750.1	747.1	744.0	741.5	739.3	737.3	735.2	733.1
55°	682.5	680.1	677.7	675.6	673.7	671.8	669.9	668.1
57.5°	615.5	612.3	609.2	607.2	606.2	605.1	604.1	603.1
60°	570.1	567.4	564.7	562.4	560.5	558.7	556.8	554.9
62.5°	526.3	523.4	520.5	518.4	516.9	515.5	514.0	512.6
65°	457.4	455.0	452.6	450.8	449.8	448.7	447.6	446.6
67.5°	391.7	389.7	387.6	386.3	385.7	385.0	384.4	383.8
70°	348.3	346.7	345.1	343.8	342.7	341.6	340.5	339.5
72.5°	307.5	305.6	303.8	302.4	301.3	300.2	299.2	298.1
75°	244.0	243.2	242.4	241.4	240.3	239.2	238.2	237.1
77.5°	185.8	185.4	184.9	184.3	183.5	182.8	182.0	181.3
80°	148.7	148.5	148.2	147.8	147.2	146.7	146.2	145.6
82.5°	113.6	113.2	112.7	112.4	112.3	112.2	112.1	111.9
85°	66.9	66.6	66.3	65.9	65.4	64.8	64.3	63.8
87.5°	29.2	29.5	29.8	29.8	29.5	29.2	28.9	28.6
90°	21.0	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	21.0	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	21.0	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	42.4	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	124.4	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	241.8	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.6	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.9	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333452-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	553.6	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	642.2	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	727.7	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.9	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.5	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	912.3	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.6	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1028.3	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1071.1	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.9	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.4	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.3	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.5	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.2	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1355.8	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.0	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.0	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.1	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1467.5	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1484.5	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1500.0	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1520.1	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1535.3	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1543.1	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1549.2	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1555.8	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1558.5	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)