

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333453-940

Luminaire Tested: **S125DIW-S1090D1340U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333453-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1340U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8110.2 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333453-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333453-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9827	9827	9827
5°	9849	9756	9818
10°	9789	9686	9742
15°	9682	9570	9610
20°	9531	9407	9423
25°	9368	9213	9204
30°	9165	9004	8959
35°	8949	8779	8656
40°	8728	8535	8413
45°	8488	8312	8147
50°	8225	8043	7801
55°	7970	7739	7523
60°	7665	7432	7167
65°	7303	7065	6825
70°	6956	6637	6411
75°	6338	6128	5916
80°	5642	5553	5415
85°	4905	4994	4728



TEST NUMBER: P333453-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.5	1.8
10°-20°	405.3	5.0
20°-30°	598.4	7.4
30°-40°	698.2	8.6
40°-50°	701.3	8.6
50°-60°	615.6	7.6
60°-70°	458.7	5.7
70°-80°	262.3	3.2
80°-90°	79.5	1.0
90°-100°	99.5	1.2
100°-110°	294.0	3.6
110°-120°	497.9	6.1
120°-130°	655.3	8.1
130°-140°	734.3	9.1
140°-150°	719.7	8.9
150°-160°	604.5	7.5
160°-170°	401.8	5.0
170°-180°	140.6	1.7
0°-30°	1147.1	14.1
0°-40°	1845.3	22.8
0°-60°	3162.2	39.0
0°-90°	3962.6	48.9
90°-120°	891.4	11.0
90°-150°	3000.7	37.0
90°-180°	4148.0	51.1
0°-180°	8110.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1519	1516	1505	1515	1514	144
15°	1448	1444	1431	1437	1437	408
25°	1315	1308	1293	1295	1292	605
35°	1135	1130	1114	1107	1098	710
45°	929	924	910	896	892	716
55°	708	703	687	677	668	632
65°	478	475	462	452	447	474
75°	254	251	246	242	237	271
85°	66	67	67	66	64	74
90°	1	10	18	24	28	8
95°	75	78	89	97	100	80
105°	264	270	276	283	287	282
115°	499	503	506	504	503	493
125°	728	734	736	733	732	651
135°	946	953	954	954	950	729
145°	1146	1151	1154	1154	1151	716
155°	1312	1312	1313	1317	1312	604
165°	1426	1424	1425	1429	1423	402
175°	1483	1479	1478	1484	1477	141
180°	1486	1486	1486	1486	1486	



TEST NUMBER: P333453-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1525.4	1524.8	1524.1	1523.5	1522.9	1521.4	1519.3	1517.2	1515.0	1512.9	1515.0
5°	1519.2	1518.7	1518.1	1517.6	1517.1	1515.5	1512.8	1510.1	1507.4	1504.8	1507.2
7.5°	1505.2	1504.7	1504.1	1503.6	1503.1	1501.3	1498.3	1495.4	1492.5	1489.5	1491.9
10°	1492.7	1492.2	1491.7	1491.1	1490.6	1488.8	1485.9	1482.9	1480.0	1477.0	1479.2
12.5°	1477.3	1476.3	1475.3	1474.4	1473.5	1471.6	1468.8	1466.2	1463.4	1460.6	1462.4
15°	1448.1	1447.3	1446.5	1445.7	1444.9	1443.1	1440.1	1437.2	1434.2	1431.3	1432.6
17.5°	1414.7	1413.5	1412.3	1411.1	1410.0	1407.8	1404.8	1401.8	1398.7	1395.6	1397.3
20°	1386.8	1386.3	1385.7	1385.2	1384.6	1382.6	1379.1	1375.6	1372.2	1368.7	1370.6
22.5°	1358.8	1357.9	1356.9	1355.9	1355.0	1352.8	1349.6	1346.3	1343.1	1339.8	1341.0
25°	1314.6	1313.2	1311.9	1310.5	1309.2	1306.8	1303.3	1299.8	1296.4	1292.9	1293.4
27.5°	1262.8	1261.9	1261.1	1260.3	1259.5	1257.4	1253.7	1250.2	1246.6	1243.0	1243.1
30°	1229.0	1228.2	1227.4	1226.6	1225.8	1223.4	1219.4	1215.4	1211.4	1207.4	1206.8
32.5°	1192.5	1191.2	1190.0	1188.7	1187.6	1185.2	1181.5	1177.9	1174.4	1170.8	1169.8
35°	1135.1	1134.1	1133.0	1131.9	1130.9	1128.5	1124.7	1121.0	1117.2	1113.5	1112.1
37.5°	1075.7	1074.3	1073.0	1071.7	1070.3	1067.9	1064.3	1060.9	1057.3	1053.8	1051.8
40°	1035.3	1033.9	1032.6	1031.3	1029.9	1027.3	1023.6	1019.8	1016.1	1012.4	1010.0
42.5°	991.9	990.8	989.7	988.6	987.4	985.0	981.2	977.5	973.7	970.0	967.8
45°	929.3	928.3	927.2	926.1	925.1	922.9	919.7	916.5	913.3	910.1	906.9
47.5°	861.9	861.9	862.0	862.1	862.1	860.2	856.4	852.5	848.6	844.8	841.5
50°	818.6	817.8	817.0	816.2	815.4	813.3	810.1	806.9	803.7	800.5	797.0
52.5°	774.3	773.6	773.1	772.5	772.0	769.9	766.5	763.0	759.6	756.2	753.1
55°	707.8	707.0	706.2	705.4	704.6	702.3	698.6	694.8	691.1	687.3	684.9
57.5°	637.8	637.3	636.9	636.5	636.1	634.3	631.1	627.9	624.8	621.6	618.5
60°	593.4	592.4	591.3	590.2	589.2	587.2	584.2	581.3	578.4	575.4	572.7
62.5°	547.2	546.4	545.5	544.7	543.9	542.2	539.6	537.1	534.6	532.1	529.1
65°	477.9	477.3	476.8	476.3	475.7	474.0	471.1	468.1	465.2	462.3	459.9
67.5°	410.7	409.6	408.5	407.3	406.3	404.6	402.3	400.2	398.0	395.8	393.8
70°	368.4	367.0	365.7	364.4	363.0	361.1	358.7	356.3	353.9	351.5	349.9
72.5°	322.2	321.2	320.3	319.4	318.5	317.3	315.8	314.1	312.6	311.0	309.2
75°	254.0	253.4	252.9	252.4	251.8	250.9	249.6	248.3	246.9	245.6	244.8
77.5°	191.2	190.9	190.7	190.6	190.3	189.8	189.0	188.3	187.6	186.8	186.4
80°	151.7	151.7	151.7	151.7	151.7	151.4	150.9	150.3	149.8	149.3	149.0
82.5°	117.0	116.5	116.2	115.7	115.3	115.0	114.9	114.9	114.7	114.6	114.1
85°	66.2	66.4	66.7	67.0	67.2	67.4	67.4	67.4	67.4	67.4	67.1
87.5°	26.2	26.7	27.0	27.5	27.9	28.2	28.3	28.4	28.6	28.7	29.0
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	28.0	29.4	30.9	32.3	33.7	35.6	37.8	40.0	42.2	44.4	46.1
95°	75.2	75.7	76.2	76.7	77.2	78.8	81.3	83.9	86.5	89.1	90.9
97.5°	124.9	125.1	125.4	125.6	125.7	127.6	131.2	134.7	138.3	141.8	143.5
100°	161.9	161.9	161.9	161.9	161.9	163.6	166.9	170.3	173.6	177.0	179.3
102.5°	201.7	202.8	203.8	204.8	205.8	207.2	208.9	210.6	212.3	214.0	216.5
105°	263.8	265.0	266.3	267.6	268.9	270.3	271.8	273.4	274.9	276.4	278.0
107.5°	332.2	333.5	334.7	336.1	337.3	338.6	339.7	340.9	342.1	343.3	344.1
110°	379.4	380.7	382.0	383.3	384.5	385.6	386.4	387.1	387.9	388.6	389.4



TEST NUMBER: P333453-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	427.5	428.2	428.8	429.5	430.2	431.1	431.9	432.9	433.9	434.9	435.2
115°	498.6	499.5	500.6	501.6	502.7	503.5	503.9	504.4	505.0	505.5	505.2
117.5°	569.8	570.2	570.7	571.1	571.7	572.1	572.6	573.0	573.5	574.0	574.2
120°	614.2	615.5	616.8	618.0	619.4	620.1	620.4	620.6	620.9	621.2	621.2
122.5°	662.4	662.8	663.3	663.7	664.1	664.8	665.4	666.1	666.7	667.4	667.2
125°	727.5	729.1	730.7	732.2	733.7	734.6	734.9	735.1	735.4	735.7	735.1
127.5°	796.9	797.8	798.7	799.6	800.5	801.0	801.4	801.6	802.0	802.3	802.0
130°	838.6	839.9	841.2	842.5	843.7	844.6	845.2	845.7	846.1	846.7	846.4
132.5°	880.2	882.3	884.5	886.5	888.7	889.7	889.6	889.5	889.4	889.3	889.0
135°	946.2	947.7	949.2	950.8	952.3	953.2	953.5	953.8	954.0	954.3	954.3
137.5°	1008.2	1009.7	1011.2	1012.6	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7
140°	1047.9	1049.3	1050.5	1051.9	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7
142.5°	1087.8	1088.9	1089.9	1091.0	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3
145°	1146.3	1147.3	1148.3	1149.3	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4
147.5°	1200.4	1201.0	1201.6	1202.1	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4
150°	1236.5	1236.3	1236.0	1235.7	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0
152.5°	1266.1	1266.5	1266.9	1267.2	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2
155°	1311.7	1311.7	1311.7	1311.7	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8
157.5°	1352.4	1351.8	1351.3	1350.7	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0
160°	1376.4	1375.7	1374.9	1374.1	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2
162.5°	1397.8	1397.2	1396.6	1396.1	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7
165°	1426.2	1425.7	1425.1	1424.7	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1
167.5°	1450.3	1449.2	1448.2	1447.2	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2
170°	1463.2	1462.2	1461.2	1460.2	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2
172.5°	1472.5	1471.4	1470.4	1469.4	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4
175°	1482.9	1481.8	1480.9	1479.8	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8
177.5°	1488.2	1487.4	1486.6	1485.8	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333453-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1517.2	1519.3	1521.4	1522.4	1522.2	1522.0	1521.8	1521.6
5°	1509.6	1512.0	1514.4	1515.5	1515.2	1514.9	1514.7	1514.4
7.5°	1494.2	1496.6	1499.0	1500.0	1499.8	1499.5	1499.2	1499.0
10°	1481.3	1483.5	1485.6	1486.6	1486.3	1486.0	1485.8	1485.5
12.5°	1464.1	1465.8	1467.5	1468.4	1468.3	1468.2	1468.2	1468.1
15°	1434.0	1435.3	1436.6	1437.3	1437.3	1437.3	1437.3	1437.3
17.5°	1399.0	1400.6	1402.3	1402.5	1401.1	1399.8	1398.5	1397.1
20°	1372.4	1374.3	1376.2	1376.4	1375.1	1373.8	1372.4	1371.1
22.5°	1342.3	1343.5	1344.7	1344.9	1344.0	1343.1	1342.2	1341.2
25°	1294.0	1294.5	1295.0	1294.9	1294.1	1293.2	1292.4	1291.6
27.5°	1243.2	1243.3	1243.5	1243.1	1242.3	1241.5	1240.7	1239.9
30°	1206.3	1205.8	1205.2	1204.6	1203.8	1203.0	1202.2	1201.4
32.5°	1168.9	1167.9	1167.0	1165.7	1164.3	1162.9	1161.4	1159.9
35°	1110.8	1109.5	1108.1	1106.4	1104.3	1102.2	1100.0	1097.9
37.5°	1049.8	1047.8	1045.9	1044.3	1043.0	1041.8	1040.5	1039.4
40°	1007.5	1005.1	1002.7	1001.1	1000.3	999.5	998.7	997.9
42.5°	965.6	963.4	961.3	959.5	958.3	957.1	955.8	954.6
45°	903.7	900.4	897.2	895.2	894.4	893.6	892.8	892.0
47.5°	838.3	835.0	831.8	829.2	827.3	825.5	823.6	821.7
50°	793.5	790.1	786.6	783.9	782.0	780.2	778.3	776.4
52.5°	750.1	747.1	744.0	741.5	739.3	737.3	735.2	733.1
55°	682.5	680.1	677.7	675.6	673.7	671.8	669.9	668.1
57.5°	615.5	612.3	609.2	607.2	606.2	605.1	604.1	603.1
60°	570.1	567.4	564.7	562.4	560.5	558.7	556.8	554.9
62.5°	526.3	523.4	520.5	518.4	516.9	515.5	514.0	512.6
65°	457.4	455.0	452.6	450.8	449.8	448.7	447.6	446.6
67.5°	391.7	389.7	387.6	386.3	385.7	385.0	384.4	383.8
70°	348.3	346.7	345.1	343.8	342.7	341.6	340.5	339.5
72.5°	307.5	305.6	303.8	302.4	301.3	300.2	299.2	298.1
75°	244.0	243.2	242.4	241.4	240.3	239.2	238.2	237.1
77.5°	185.8	185.4	184.9	184.3	183.5	182.8	182.0	181.3
80°	148.7	148.5	148.2	147.8	147.2	146.7	146.2	145.6
82.5°	113.6	113.2	112.7	112.4	112.3	112.2	112.1	111.9
85°	66.9	66.6	66.3	65.9	65.4	64.8	64.3	63.8
87.5°	29.2	29.5	29.8	29.8	29.5	29.2	29.0	28.6
90°	21.0	22.4	23.6	24.7	25.4	26.2	27.0	27.7
92.5°	47.8	49.5	51.2	52.3	52.9	53.5	54.0	54.6
95°	92.6	94.4	96.3	97.4	97.9	98.4	99.0	99.5
97.5°	145.2	146.9	148.6	149.6	149.9	150.3	150.5	150.9
100°	181.6	183.9	186.2	187.6	188.2	188.7	189.2	189.7
102.5°	219.0	221.5	224.1	225.7	226.4	227.1	227.8	228.5
105°	279.6	281.1	282.6	283.7	284.5	285.3	286.1	286.9
107.5°	344.8	345.6	346.4	346.8	346.7	346.6	346.6	346.5
110°	390.2	390.9	391.7	392.0	391.7	391.5	391.2	390.9



TEST NUMBER: P333453-940

CATALOG NUMBER: S125DIW-S1090D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.6	436.0	436.3	436.3	435.9	435.4	434.9	434.4
115°	505.0	504.7	504.4	504.2	503.9	503.6	503.5	503.2
117.5°	574.4	574.5	574.8	574.4	573.4	572.3	571.3	570.2
120°	621.2	621.2	621.2	620.6	619.6	618.6	617.5	616.5
122.5°	667.0	666.8	666.6	666.1	665.2	664.4	663.6	662.8
125°	734.6	734.1	733.6	733.3	733.0	732.7	732.5	732.2
127.5°	801.7	801.5	801.3	800.8	800.4	799.9	799.3	798.8
130°	846.1	846.0	845.7	845.3	844.8	844.3	843.7	843.2
132.5°	888.8	888.5	888.2	887.8	887.1	886.3	885.6	884.8
135°	954.3	954.3	954.3	953.8	952.7	951.7	950.7	949.7
137.5°	1018.1	1018.3	1018.7	1018.2	1016.9	1015.6	1014.3	1013.1
140°	1058.3	1058.7	1059.3	1058.9	1057.6	1056.3	1055.1	1053.7
142.5°	1097.6	1098.0	1098.2	1097.8	1096.4	1095.2	1093.9	1092.6
145°	1154.4	1154.4	1154.4	1154.0	1153.2	1152.4	1151.6	1150.9
147.5°	1206.9	1207.6	1208.2	1207.6	1205.9	1204.2	1202.4	1200.7
150°	1240.0	1240.0	1240.0	1239.7	1239.2	1238.7	1238.1	1237.7
152.5°	1270.8	1271.4	1272.0	1271.9	1271.0	1270.1	1269.1	1268.2
155°	1314.9	1315.9	1317.0	1316.8	1315.5	1314.3	1313.0	1311.7
157.5°	1353.1	1354.1	1355.1	1354.8	1353.1	1351.4	1349.7	1348.0
160°	1376.2	1377.2	1378.2	1378.1	1376.9	1375.6	1374.3	1373.0
162.5°	1397.9	1399.1	1400.3	1400.3	1398.7	1397.2	1395.8	1394.3
165°	1427.1	1428.2	1429.1	1428.9	1427.4	1425.8	1424.2	1422.7
167.5°	1448.8	1450.3	1451.8	1451.8	1450.2	1448.6	1447.0	1445.4
170°	1461.7	1463.2	1464.7	1464.6	1462.9	1461.1	1459.2	1457.4
172.5°	1471.0	1472.5	1474.0	1474.0	1472.4	1470.8	1469.2	1467.6
175°	1481.3	1482.9	1484.4	1484.3	1482.5	1480.7	1478.9	1477.1
177.5°	1486.0	1487.3	1488.5	1488.4	1486.9	1485.5	1484.1	1482.6
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4

(END OF REPORT)