

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333477-940

Luminaire Tested: **S125DIW-S1270D1050U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333477-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1050U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7815.2 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333477-940

CATALOG NUMBER: S125DIW-S1270D1050U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333477-940

CATALOG NUMBER: S125DIW-S1270D1050U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																												
1	100	95	91	88	93	89	85	82	77	75	72	66	65	63	56	55	54	49																												
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45	41																												
3	83	73	66	60	77	68	62	56	60	54	50	51	48	44	44	41	39	35																												
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33	30																												
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26																												
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23																												
7	59	47	39	33	55	44	37	31	39	33	28	34	29	26	29	26	23	20																												
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18																												
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16																												
10	48	36	28	23	45	34	27	22	30	24	21	26	22	19	23	19	17	15																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11349	11349	11349
5°	11374	11267	11339
10°	11305	11187	11252
15°	11183	11053	11099
20°	11008	10864	10883
25°	10819	10641	10630
30°	10586	10399	10347
35°	10336	10139	9996
40°	10080	9857	9716
45°	9803	9600	9409
50°	9499	9289	9010
55°	9205	8939	8688
60°	8853	8584	8280
65°	8436	8159	7882
70°	8033	7666	7404
75°	7321	7079	6832
80°	6512	6412	6259
85°	5669	5765	5461



TEST NUMBER: P333477-940

CATALOG NUMBER: S125DIW-S1270D1050U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.7	2.1
10°-20°	468.1	6.0
20°-30°	691.1	8.8
30°-40°	806.4	10.3
40°-50°	809.9	10.4
50°-60°	710.9	9.1
60°-70°	529.7	6.8
70°-80°	302.9	3.9
80°-90°	90.6	1.2
90°-100°	77.8	1.0
100°-110°	229.6	2.9
110°-120°	388.9	5.0
120°-130°	511.9	6.5
130°-140°	573.6	7.3
140°-150°	562.1	7.2
150°-160°	472.2	6.0
160°-170°	313.9	4.0
170°-180°	109.8	1.4
0°-30°	1324.8	17.0
0°-40°	2131.2	27.3
0°-60°	3652.1	46.7
0°-90°	4575.4	58.5
90°-120°	696.4	8.9
90°-150°	2344.0	30.0
90°-180°	3240.0	41.5
0°-180°	7815.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1757	1757	1757	1757	1757	
5°	1754	1751	1738	1750	1749	166
15°	1672	1668	1653	1660	1660	471
25°	1518	1511	1493	1496	1492	698
35°	1311	1305	1286	1279	1268	820
45°	1073	1067	1051	1035	1030	827
55°	818	812	794	781	772	730
65°	552	548	534	522	516	548
75°	293	290	284	279	274	313
85°	76	78	78	76	74	85
90°	1	8	14	19	22	7
95°	59	61	70	76	78	63
105°	206	211	216	221	224	220
115°	389	393	395	394	393	385
125°	568	573	575	573	572	509
135°	739	744	745	745	742	569
145°	895	899	902	902	899	560
155°	1025	1025	1026	1029	1025	472
165°	1114	1112	1113	1116	1111	314
175°	1158	1155	1155	1160	1154	110
180°	1161	1161	1161	1161	1161	



TEST NUMBER: P333477-940

CATALOG NUMBER: S125DIW-S1270D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1761.8	1761.0	1760.3	1759.5	1758.8	1757.2	1754.7	1752.2	1749.8	1747.3	1749.8
5°	1754.5	1753.9	1753.3	1752.7	1752.0	1750.2	1747.1	1744.0	1741.0	1737.9	1740.6
7.5°	1738.4	1737.8	1737.1	1736.5	1735.9	1733.9	1730.5	1727.2	1723.8	1720.4	1723.1
10°	1723.9	1723.3	1722.7	1722.1	1721.4	1719.5	1716.1	1712.7	1709.2	1705.8	1708.3
12.5°	1706.1	1705.0	1704.0	1702.8	1701.7	1699.6	1696.4	1693.3	1690.1	1686.9	1689.0
15°	1672.5	1671.6	1670.6	1669.7	1668.8	1666.6	1663.2	1659.8	1656.4	1653.1	1654.6
17.5°	1633.9	1632.5	1631.1	1629.8	1628.4	1625.9	1622.5	1618.9	1615.4	1611.9	1613.8
20°	1601.6	1601.0	1600.4	1599.7	1599.1	1596.8	1592.8	1588.8	1584.7	1580.7	1582.9
22.5°	1569.3	1568.3	1567.1	1566.0	1564.9	1562.5	1558.7	1555.0	1551.1	1547.4	1548.8
25°	1518.2	1516.6	1515.1	1513.6	1512.0	1509.2	1505.2	1501.2	1497.2	1493.2	1493.8
27.5°	1458.4	1457.5	1456.5	1455.6	1454.7	1452.2	1448.0	1443.9	1439.8	1435.6	1435.7
30°	1419.5	1418.5	1417.6	1416.7	1415.8	1413.0	1408.4	1403.7	1399.1	1394.5	1393.8
32.5°	1377.2	1375.8	1374.4	1373.0	1371.5	1368.8	1364.6	1360.5	1356.3	1352.2	1351.1
35°	1311.0	1309.8	1308.6	1307.3	1306.1	1303.3	1299.0	1294.7	1290.3	1286.0	1284.5
37.5°	1242.3	1240.8	1239.3	1237.7	1236.2	1233.3	1229.3	1225.2	1221.1	1217.1	1214.8
40°	1195.6	1194.1	1192.6	1191.0	1189.5	1186.5	1182.2	1177.9	1173.6	1169.2	1166.4
42.5°	1145.6	1144.3	1143.0	1141.7	1140.4	1137.6	1133.3	1128.9	1124.6	1120.3	1117.8
45°	1073.3	1072.1	1070.9	1069.6	1068.4	1065.9	1062.2	1058.5	1054.8	1051.1	1047.3
47.5°	995.4	995.5	995.6	995.6	995.7	993.5	989.1	984.6	980.2	975.7	972.0
50°	945.4	944.5	943.5	942.6	941.6	939.3	935.7	931.9	928.3	924.5	920.5
52.5°	894.2	893.6	892.9	892.2	891.5	889.2	885.2	881.3	877.4	873.3	869.9
55°	817.5	816.5	815.6	814.7	813.8	811.2	806.8	802.5	798.2	793.9	791.0
57.5°	736.6	736.1	735.6	735.1	734.6	732.5	728.9	725.2	721.6	717.9	714.3
60°	685.4	684.2	683.0	681.7	680.5	678.1	674.8	671.4	668.0	664.6	661.5
62.5°	632.0	631.1	630.1	629.0	628.0	626.2	623.2	620.3	617.4	614.5	611.2
65°	552.0	551.3	550.7	550.1	549.5	547.4	544.0	540.6	537.3	533.9	531.1
67.5°	474.4	473.1	471.8	470.5	469.2	467.3	464.8	462.2	459.7	457.1	454.8
70°	425.4	423.9	422.3	420.8	419.3	417.1	414.3	411.5	408.8	406.0	404.1
72.5°	372.0	371.0	370.0	368.9	367.8	366.4	364.6	362.8	361.1	359.3	357.1
75°	293.4	292.7	292.1	291.5	290.9	289.8	288.3	286.7	285.2	283.7	282.7
77.5°	220.8	220.5	220.3	220.1	219.8	219.3	218.4	217.5	216.6	215.8	215.3
80°	175.1	175.1	175.1	175.1	175.1	174.9	174.2	173.6	173.0	172.4	172.1
82.5°	135.1	134.6	134.1	133.7	133.1	132.9	132.7	132.6	132.5	132.3	131.8
85°	76.5	76.8	77.0	77.4	77.7	77.8	77.8	77.8	77.8	77.8	77.6
87.5°	30.2	30.5	30.9	31.2	31.5	31.7	31.7	31.7	31.7	31.8	32.0
90°	0.9	2.5	4.1	5.7	7.3	8.8	10.3	11.7	13.0	14.4	15.4
92.5°	21.8	23.0	24.1	25.2	26.4	27.8	29.5	31.2	33.0	34.7	36.0
95°	58.8	59.1	59.6	59.9	60.4	61.5	63.6	65.5	67.6	69.6	71.0
97.5°	97.6	97.7	97.9	98.1	98.3	99.7	102.5	105.2	108.0	110.8	112.1
100°	126.5	126.5	126.5	126.5	126.5	127.8	130.4	133.0	135.6	138.2	140.1
102.5°	157.6	158.4	159.2	160.0	160.8	161.8	163.2	164.5	165.9	167.2	169.2
105°	206.0	207.0	208.0	209.0	210.0	211.2	212.3	213.6	214.7	216.0	217.1
107.5°	259.5	260.5	261.5	262.5	263.5	264.5	265.4	266.4	267.2	268.1	268.8
110°	296.3	297.4	298.4	299.3	300.4	301.2	301.8	302.4	303.0	303.6	304.2



TEST NUMBER: P333477-940

CATALOG NUMBER: S125DIW-S1270D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.9	334.5	335.0	335.6	336.0	336.7	337.4	338.2	338.9	339.7	340.0
115°	389.4	390.2	391.0	391.8	392.6	393.2	393.6	394.0	394.4	394.8	394.7
117.5°	445.1	445.4	445.8	446.1	446.6	446.9	447.3	447.6	448.0	448.4	448.5
120°	479.7	480.8	481.8	482.8	483.8	484.4	484.6	484.8	485.0	485.2	485.2
122.5°	517.4	517.7	518.1	518.4	518.8	519.2	519.8	520.3	520.8	521.4	521.2
125°	568.3	569.5	570.7	571.9	573.1	573.8	574.1	574.3	574.4	574.6	574.3
127.5°	622.5	623.2	623.9	624.6	625.3	625.7	626.0	626.2	626.4	626.7	626.5
130°	655.1	656.0	657.1	658.1	659.1	659.8	660.2	660.6	661.0	661.4	661.2
132.5°	687.6	689.2	690.9	692.5	694.2	695.0	694.9	694.8	694.7	694.6	694.5
135°	739.0	740.3	741.5	742.7	744.0	744.6	744.8	745.0	745.2	745.4	745.4
137.5°	787.6	788.7	789.9	791.0	792.2	793.0	793.4	793.9	794.3	794.8	795.0
140°	818.6	819.6	820.6	821.6	822.6	823.4	824.0	824.7	825.2	825.8	826.3
142.5°	849.7	850.5	851.4	852.2	853.1	853.9	854.6	855.4	856.1	856.9	857.1
145°	895.4	896.2	897.0	897.8	898.6	899.3	899.9	900.5	901.2	901.7	901.7
147.5°	937.7	938.2	938.6	939.0	939.4	940.0	940.4	940.8	941.4	941.8	942.4
150°	965.9	965.7	965.5	965.3	965.1	965.4	966.2	967.0	967.8	968.6	968.6
152.5°	989.0	989.3	989.5	989.9	990.2	990.4	990.8	991.0	991.4	991.8	992.2
155°	1024.6	1024.6	1024.6	1024.6	1024.6	1024.7	1024.9	1025.1	1025.3	1025.6	1026.4
157.5°	1056.4	1056.0	1055.5	1055.1	1054.6	1054.5	1054.7	1054.9	1055.2	1055.3	1056.1
160°	1075.2	1074.6	1074.0	1073.4	1072.8	1072.6	1072.8	1073.0	1073.2	1073.4	1074.2
162.5°	1091.8	1091.4	1090.9	1090.5	1090.0	1089.8	1089.9	1089.9	1090.0	1090.0	1091.0
165°	1114.1	1113.7	1113.2	1112.9	1112.4	1112.3	1112.6	1112.8	1112.9	1113.1	1113.9
167.5°	1132.8	1132.0	1131.2	1130.4	1129.6	1129.3	1129.3	1129.3	1129.3	1129.3	1130.4
170°	1143.0	1142.2	1141.4	1140.6	1139.8	1139.3	1139.3	1139.3	1139.3	1139.3	1140.6
172.5°	1150.2	1149.4	1148.6	1147.8	1147.0	1146.6	1146.6	1146.6	1146.6	1146.6	1147.8
175°	1158.3	1157.5	1156.7	1155.9	1155.1	1154.7	1154.7	1154.7	1154.7	1154.7	1155.9
177.5°	1162.5	1161.8	1161.2	1160.6	1159.9	1159.5	1159.3	1159.2	1159.0	1158.9	1159.8
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333477-940

CATALOG NUMBER: S125DIW-S1270D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1752.2	1754.7	1757.2	1758.3	1758.1	1757.8	1757.6	1757.3
5°	1743.4	1746.2	1749.0	1750.2	1749.9	1749.6	1749.3	1749.0
7.5°	1725.7	1728.5	1731.2	1732.4	1732.1	1731.8	1731.5	1731.2
10°	1710.8	1713.3	1715.7	1716.8	1716.5	1716.2	1715.9	1715.7
12.5°	1691.0	1692.9	1694.9	1695.9	1695.8	1695.7	1695.7	1695.6
15°	1656.2	1657.7	1659.2	1660.0	1660.0	1660.0	1660.0	1660.0
17.5°	1615.7	1617.7	1619.5	1619.7	1618.2	1616.7	1615.1	1613.6
20°	1585.1	1587.2	1589.4	1589.7	1588.1	1586.6	1585.1	1583.5
22.5°	1550.2	1551.7	1553.1	1553.3	1552.2	1551.1	1550.1	1549.1
25°	1494.4	1495.0	1495.7	1495.5	1494.6	1493.6	1492.7	1491.7
27.5°	1435.8	1436.0	1436.1	1435.7	1434.8	1433.9	1432.9	1432.0
30°	1393.2	1392.6	1392.0	1391.2	1390.3	1389.4	1388.4	1387.5
32.5°	1350.0	1348.9	1347.7	1346.3	1344.7	1343.0	1341.3	1339.7
35°	1282.9	1281.4	1279.9	1277.8	1275.3	1272.9	1270.4	1267.9
37.5°	1212.5	1210.2	1207.9	1206.0	1204.6	1203.2	1201.8	1200.3
40°	1163.7	1160.9	1158.1	1156.3	1155.3	1154.4	1153.4	1152.5
42.5°	1115.3	1112.7	1110.2	1108.2	1106.8	1105.4	1103.9	1102.5
45°	1043.7	1039.9	1036.3	1033.9	1033.0	1032.1	1031.1	1030.2
47.5°	968.1	964.4	960.6	957.7	955.5	953.3	951.2	949.0
50°	916.5	912.5	908.5	905.4	903.2	901.1	898.9	896.7
52.5°	866.3	862.8	859.3	856.3	853.9	851.5	849.1	846.7
55°	788.3	785.5	782.7	780.2	778.1	776.0	773.7	771.6
57.5°	710.8	707.2	703.6	701.2	700.1	698.9	697.7	696.5
60°	658.4	655.3	652.2	649.6	647.4	645.2	643.1	641.0
62.5°	607.8	604.5	601.2	598.7	597.0	595.3	593.6	592.0
65°	528.3	525.5	522.7	520.8	519.5	518.3	517.0	515.8
67.5°	452.5	450.0	447.7	446.2	445.4	444.7	444.0	443.2
70°	402.3	400.4	398.5	397.0	395.7	394.5	393.3	392.1
72.5°	355.1	352.9	350.9	349.2	347.9	346.7	345.4	344.2
75°	281.8	280.8	279.9	278.8	277.6	276.3	275.1	273.8
77.5°	214.6	214.1	213.6	212.9	212.0	211.1	210.3	209.4
80°	171.7	171.5	171.1	170.7	170.0	169.4	168.8	168.3
82.5°	131.3	130.7	130.1	129.8	129.7	129.6	129.4	129.3
85°	77.2	77.0	76.6	76.2	75.5	74.9	74.3	73.7
87.5°	32.2	32.4	32.6	32.5	32.2	31.7	31.4	31.0
90°	16.5	17.5	18.5	19.3	19.9	20.5	21.0	21.7
92.5°	37.4	38.7	40.0	40.8	41.3	41.7	42.2	42.6
95°	72.4	73.7	75.2	76.1	76.5	76.9	77.3	77.7
97.5°	113.4	114.8	116.1	116.8	117.1	117.3	117.6	117.8
100°	141.9	143.7	145.4	146.6	147.0	147.4	147.8	148.2
102.5°	171.1	173.1	175.0	176.3	176.8	177.5	178.0	178.5
105°	218.4	219.5	220.8	221.7	222.3	222.8	223.5	224.1
107.5°	269.4	270.0	270.5	270.9	270.8	270.8	270.7	270.7
110°	304.8	305.4	306.0	306.2	306.0	305.8	305.6	305.4



TEST NUMBER: P333477-940

CATALOG NUMBER: S125DIW-S1270D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	340.3	340.5	340.8	340.8	340.5	340.1	339.7	339.4
115°	394.4	394.2	394.0	393.9	393.6	393.4	393.2	393.1
117.5°	448.6	448.8	449.0	448.6	447.8	447.0	446.2	445.4
120°	485.2	485.2	485.2	484.8	484.0	483.2	482.4	481.6
122.5°	521.0	520.8	520.7	520.3	519.7	519.0	518.4	517.7
125°	573.8	573.5	573.0	572.7	572.6	572.3	572.1	571.9
127.5°	626.2	626.1	625.9	625.6	625.2	624.8	624.4	624.0
130°	661.0	660.8	660.6	660.3	659.9	659.5	659.1	658.7
132.5°	694.2	694.0	693.8	693.5	692.9	692.3	691.8	691.2
135°	745.4	745.4	745.4	745.0	744.2	743.4	742.6	741.8
137.5°	795.2	795.5	795.7	795.3	794.3	793.4	792.3	791.3
140°	826.6	827.1	827.4	827.2	826.2	825.1	824.1	823.1
142.5°	857.4	857.6	857.9	857.5	856.5	855.5	854.5	853.5
145°	901.7	901.7	901.7	901.4	900.8	900.2	899.6	899.0
147.5°	942.8	943.3	943.8	943.3	942.0	940.6	939.2	937.9
150°	968.6	968.6	968.6	968.4	968.0	967.6	967.1	966.8
152.5°	992.7	993.2	993.6	993.5	992.8	992.1	991.3	990.6
155°	1027.2	1028.0	1028.8	1028.6	1027.6	1026.6	1025.6	1024.6
157.5°	1056.9	1057.7	1058.5	1058.3	1056.9	1055.6	1054.3	1053.0
160°	1075.0	1075.8	1076.7	1076.5	1075.5	1074.5	1073.5	1072.5
162.5°	1092.0	1092.9	1093.9	1093.8	1092.6	1091.5	1090.3	1089.1
165°	1114.7	1115.5	1116.3	1116.2	1115.0	1113.7	1112.6	1111.3
167.5°	1131.7	1132.8	1134.1	1134.1	1132.8	1131.6	1130.3	1129.1
170°	1141.7	1143.0	1144.2	1144.1	1142.6	1141.3	1139.9	1138.4
172.5°	1149.0	1150.2	1151.4	1151.4	1150.1	1148.9	1147.6	1146.4
175°	1157.1	1158.3	1159.6	1159.4	1158.1	1156.6	1155.2	1153.8
177.5°	1160.8	1161.8	1162.7	1162.6	1161.5	1160.4	1159.3	1158.2
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0

(END OF REPORT)