

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333479-940

Luminaire Tested: **S125DIW-S1270D1340U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333479-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1340U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8772.0 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	54	44	37	31	38	32	28	33	28	25	28	24	22	19
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10577	10577	10577	10577
5°	12248	10613	9292	10613
10°	14250	10558	8141	10558
15°	15774	10480	7511	10480
20°	17657	10357	7003	10357
25°	20685	10219	6757	10219
30°	22342	10082	6542	10082
35°	18370	9826	6401	9826
40°	13057	9470	6247	9470
45°	10030	8990	6158	8990
50°	8562	8395	6146	8395
55°	7624	7812	6199	7812
60°	6877	7174	6356	7174
65°	6353	6533	6522	6533
70°	5776	5867	6617	5867
75°	5100	5168	6558	5168
80°	4292	4214	5995	4214
85°	3394	3038	4846	3038



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.8
10°-20°	469.4	5.4
20°-30°	762.2	8.7
30°-40°	929.8	10.6
40°-50°	845.8	9.6
50°-60°	673.7	7.7
60°-70°	469.3	5.3
70°-80°	250.2	2.9
80°-90°	66.4	0.8
90°-100°	99.5	1.1
100°-110°	294.0	3.4
110°-120°	497.9	5.7
120°-130°	655.3	7.5
130°-140°	734.3	8.4
140°-150°	719.7	8.2
150°-160°	604.5	6.9
160°-170°	401.8	4.6
170°-180°	140.6	1.6
0°-30°	1389.3	15.8
0°-40°	2319.0	26.4
0°-60°	3838.6	43.8
0°-90°	4624.5	52.7
90°-120°	891.4	10.2
90°-150°	3000.7	34.2
90°-180°	4148.0	47.3
0°-180°	8772.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1638	1638	1638	1638	1638	
5°	1889	1637	1433	1637	1889	190
15°	2359	1567	1123	1567	2359	675
25°	2903	1434	948	1434	2903	1326
35°	2330	1246	812	1246	2330	1426
45°	1098	984	674	984	1098	879
55°	677	694	550	694	677	610
65°	416	428	427	428	416	413
75°	204	207	263	207	204	220
85°	46	41	65	41	46	54
90°	28	1	28	1	28	18
95°	100	75	100	75	100	101
105°	287	264	287	264	287	304
115°	503	499	503	499	503	498
125°	732	728	732	728	732	654
135°	950	946	950	946	950	733
145°	1151	1146	1151	1146	1151	718
155°	1312	1312	1312	1312	1312	604
165°	1423	1426	1423	1426	1423	401
175°	1477	1483	1477	1483	1477	140
180°	1486	1486	1486	1486	1486	



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1732.2	1730.0	1727.8	1723.3	1726.6	1717.2	1712.7	1705.0	1695.5	1692.2	1688.3
5°	1889.3	1892.7	1896.2	1881.7	1883.0	1873.3	1851.1	1833.0	1818.4	1799.7	1786.5
7.5°	2078.4	2070.2	2069.5	2060.0	2043.8	2030.7	2007.3	1977.5	1948.8	1916.0	1888.9
10°	2172.9	2173.6	2167.4	2156.2	2138.9	2126.4	2095.8	2066.5	2031.1	1989.4	1959.5
12.5°	2244.1	2247.0	2239.1	2224.1	2215.5	2187.5	2163.6	2128.9	2086.7	2053.3	2007.9
15°	2359.2	2351.5	2346.0	2327.2	2312.7	2283.4	2245.2	2209.0	2163.2	2120.8	2078.4
17.5°	2470.1	2476.3	2465.8	2448.7	2403.4	2369.4	2318.1	2268.5	2211.4	2154.6	2104.0
20°	2569.1	2574.7	2558.7	2528.8	2474.6	2440.5	2373.1	2309.2	2243.1	2170.2	2114.5
22.5°	2692.6	2688.2	2666.6	2621.1	2574.1	2511.1	2438.2	2360.3	2277.6	2195.1	2121.2
25°	2902.8	2873.5	2860.3	2804.1	2742.2	2649.7	2549.7	2435.6	2332.8	2223.7	2129.1
27.5°	3019.2	3010.1	2995.3	2956.2	2891.1	2792.2	2674.2	2535.3	2390.2	2252.5	2128.7
30°	2995.9	2997.3	2998.7	2986.2	2944.5	2870.1	2752.6	2603.2	2430.8	2275.8	2132.6
32.5°	2789.1	2814.3	2838.6	2867.2	2878.9	2864.5	2791.0	2656.0	2478.6	2302.5	2130.4
35°	2330.0	2337.6	2416.2	2494.0	2599.7	2681.7	2736.7	2676.8	2527.4	2325.1	2127.7
37.5°	1816.8	1854.3	1908.6	1996.6	2149.1	2285.6	2461.2	2542.0	2493.8	2332.5	2122.9
40°	1548.7	1583.5	1618.9	1708.6	1837.2	2002.6	2202.1	2372.4	2412.0	2309.2	2106.2
42.5°	1341.8	1369.4	1408.7	1476.1	1583.6	1730.1	1920.7	2143.3	2280.2	2241.3	2071.2
45°	1098.2	1115.6	1146.2	1199.8	1277.6	1392.3	1560.5	1803.8	2015.8	2086.0	1988.0
47.5°	940.0	940.0	963.7	1000.7	1056.9	1154.3	1278.7	1469.4	1695.8	1863.3	1855.6
50°	852.2	848.7	867.5	899.5	944.0	1008.6	1127.5	1279.7	1497.3	1687.0	1739.8
52.5°	776.6	776.9	788.5	812.2	849.4	904.6	993.5	1130.7	1316.5	1511.3	1610.9
55°	677.1	674.2	687.4	703.5	730.6	766.7	830.6	935.6	1086.5	1278.3	1407.6
57.5°	585.9	593.5	598.8	609.9	632.4	656.6	710.5	787.6	907.2	1071.8	1208.5
60°	532.4	540.1	544.3	555.4	573.5	594.3	636.1	698.6	799.4	941.2	1076.7
62.5°	484.6	490.6	492.0	502.0	516.7	537.1	569.9	622.4	702.0	826.1	958.9
65°	415.7	415.7	418.5	428.9	435.9	453.9	478.9	517.2	581.1	677.7	791.0
67.5°	349.2	352.6	351.9	356.4	362.8	376.9	394.8	426.4	473.8	544.3	634.9
70°	305.9	308.6	307.9	311.4	318.3	327.4	342.0	371.8	405.9	466.5	544.3
72.5°	266.9	268.0	266.3	270.8	275.0	282.9	299.2	315.1	347.0	398.1	462.0
75°	204.4	205.7	207.1	209.9	214.1	218.3	226.6	242.6	263.4	301.7	342.7
77.5°	153.2	150.5	153.9	153.5	155.9	159.1	166.4	174.9	192.0	216.2	247.9
80°	115.4	116.1	116.1	116.8	120.3	122.3	128.6	134.8	148.0	166.1	188.4
82.5°	84.3	86.1	85.0	86.2	89.1	90.6	94.1	99.2	106.9	121.1	137.2
85°	45.8	42.4	43.8	45.2	45.2	45.8	48.7	50.7	54.9	60.5	66.7
87.5°	18.9	19.9	20.2	20.1	20.5	20.3	22.3	22.0	23.5	24.8	26.7
90°	27.7	27.0	26.2	25.4	24.7	23.6	22.4	21.0	19.8	18.5	16.7
92.5°	54.6	54.0	53.5	52.9	52.3	51.2	49.5	47.8	46.1	44.4	42.2
95°	99.5	99.0	98.4	97.9	97.4	96.3	94.4	92.6	90.9	89.1	86.5
97.5°	150.9	150.5	150.3	149.9	149.6	148.6	146.9	145.2	143.5	141.8	138.3
100°	189.7	189.2	188.7	188.2	187.6	186.2	183.9	181.6	179.3	177.0	173.6
102.5°	228.5	227.8	227.1	226.4	225.7	224.1	221.5	219.0	216.5	214.0	212.3
105°	286.9	286.1	285.3	284.5	283.7	282.6	281.1	279.6	278.0	276.4	274.9
107.5°	346.5	346.6	346.6	346.7	346.8	346.4	345.6	344.8	344.1	343.3	342.1
110°	390.9	391.2	391.5	391.7	392.0	391.7	390.9	390.2	389.4	388.6	387.9



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.4	434.9	435.4	435.9	436.3	436.3	436.0	435.6	435.2	434.9	433.9
115°	503.2	503.5	503.6	503.9	504.2	504.4	504.7	505.0	505.2	505.5	505.0
117.5°	570.2	571.3	572.3	573.4	574.4	574.8	574.5	574.4	574.2	574.0	573.5
120°	616.5	617.5	618.6	619.6	620.6	621.2	621.2	621.2	621.2	621.2	620.9
122.5°	662.8	663.6	664.4	665.2	666.1	666.6	666.8	667.0	667.2	667.4	666.7
125°	732.2	732.5	732.7	733.0	733.3	733.6	734.1	734.6	735.1	735.7	735.4
127.5°	798.8	799.3	799.9	800.4	800.8	801.3	801.5	801.7	802.0	802.3	802.0
130°	843.2	843.7	844.3	844.8	845.3	845.7	846.0	846.1	846.4	846.7	846.1
132.5°	884.8	885.6	886.3	887.1	887.8	888.2	888.5	888.8	889.0	889.3	889.4
135°	949.7	950.7	951.7	952.7	953.8	954.3	954.3	954.3	954.3	954.3	954.0
137.5°	1013.1	1014.3	1015.6	1016.9	1018.2	1018.7	1018.3	1018.1	1017.7	1017.4	1016.9
140°	1053.7	1055.1	1056.3	1057.6	1058.9	1059.3	1058.7	1058.3	1057.7	1057.2	1056.4
142.5°	1092.6	1093.9	1095.2	1096.4	1097.8	1098.2	1098.0	1097.6	1097.3	1097.0	1096.0
145°	1150.9	1151.6	1152.4	1153.2	1154.0	1154.4	1154.4	1154.4	1154.4	1154.4	1153.6
147.5°	1200.7	1202.4	1204.2	1205.9	1207.6	1208.2	1207.6	1206.9	1206.4	1205.8	1205.1
150°	1237.7	1238.1	1238.7	1239.2	1239.7	1240.0	1240.0	1240.0	1240.0	1240.0	1238.9
152.5°	1268.2	1269.1	1270.1	1271.0	1271.9	1272.0	1271.4	1270.8	1270.2	1269.6	1269.2
155°	1311.7	1313.0	1314.3	1315.5	1316.8	1317.0	1315.9	1314.9	1313.8	1312.9	1312.6
157.5°	1348.0	1349.7	1351.4	1353.1	1354.8	1355.1	1354.1	1353.1	1352.0	1351.0	1350.8
160°	1373.0	1374.3	1375.6	1376.9	1378.1	1378.2	1377.2	1376.2	1375.2	1374.1	1373.9
162.5°	1394.3	1395.8	1397.2	1398.7	1400.3	1400.3	1399.1	1397.9	1396.7	1395.4	1395.3
165°	1422.7	1424.2	1425.8	1427.4	1428.9	1429.1	1428.2	1427.1	1426.1	1425.0	1424.8
167.5°	1445.4	1447.0	1448.6	1450.2	1451.8	1451.8	1450.3	1448.8	1447.2	1445.6	1445.6
170°	1457.4	1459.2	1461.1	1462.9	1464.6	1464.7	1463.2	1461.7	1460.2	1458.6	1458.6
172.5°	1467.6	1469.2	1470.8	1472.4	1474.0	1474.0	1472.5	1471.0	1469.4	1467.8	1467.8
175°	1477.1	1478.9	1480.7	1482.5	1484.3	1484.4	1482.9	1481.3	1479.8	1478.3	1478.3
177.5°	1482.6	1484.1	1485.5	1486.9	1488.4	1488.5	1487.3	1486.0	1484.8	1483.5	1483.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1685.0	1681.1	1676.6	1668.8	1659.4	1654.4	1646.5	1641.6	1631.6	1623.2	1614.4
5°	1770.4	1752.4	1735.7	1714.1	1690.5	1675.2	1657.2	1637.0	1616.1	1594.6	1570.9
7.5°	1859.0	1827.0	1792.2	1754.9	1718.3	1684.6	1652.5	1621.0	1591.5	1555.9	1525.8
10°	1918.5	1878.2	1835.1	1784.3	1735.0	1691.9	1648.1	1609.9	1570.9	1529.2	1492.4
12.5°	1978.0	1924.3	1863.4	1807.7	1748.4	1696.3	1644.8	1596.0	1547.0	1500.8	1457.9
15°	2020.0	1972.7	1916.4	1837.2	1770.4	1698.9	1630.8	1567.4	1508.4	1457.0	1402.8
17.5°	2047.6	1986.7	1926.3	1850.2	1762.8	1682.7	1605.5	1533.1	1466.5	1401.3	1349.1
20°	2052.6	1990.1	1926.8	1852.4	1762.8	1671.1	1593.8	1507.0	1435.4	1368.0	1304.0
22.5°	2051.0	1980.0	1911.3	1834.7	1747.2	1662.7	1569.4	1480.9	1403.1	1336.9	1270.1
25°	2035.2	1959.5	1873.3	1796.2	1709.9	1620.3	1525.8	1434.0	1354.8	1279.0	1213.0
27.5°	2022.2	1924.0	1826.3	1736.3	1653.1	1570.9	1480.4	1386.4	1298.6	1221.8	1159.6
30°	2006.1	1898.4	1788.5	1694.7	1609.2	1529.2	1443.8	1352.0	1260.3	1185.2	1118.5
32.5°	1991.6	1866.1	1750.2	1648.0	1557.5	1479.7	1400.9	1313.6	1223.5	1147.4	1080.6
35°	1963.7	1818.4	1685.6	1570.2	1473.6	1393.7	1327.7	1246.3	1163.6	1089.9	1026.0
37.5°	1928.2	1755.9	1613.4	1492.4	1386.4	1302.3	1240.7	1178.3	1098.9	1028.0	970.1
40°	1900.4	1711.4	1560.5	1436.8	1327.0	1239.4	1182.4	1123.3	1057.3	991.2	930.1
42.5°	1865.4	1671.3	1507.2	1373.9	1265.2	1179.9	1120.1	1069.9	1011.6	950.1	893.3
45°	1801.0	1598.7	1420.8	1277.6	1167.8	1083.7	1021.8	984.3	940.5	882.1	834.1
47.5°	1706.4	1511.5	1327.5	1179.7	1066.4	988.5	930.5	894.5	863.6	820.2	776.7
50°	1622.4	1446.5	1260.3	1113.6	1000.2	921.7	868.2	835.5	809.1	775.7	738.9
52.5°	1528.4	1364.8	1194.1	1049.1	936.8	859.4	807.0	778.3	756.3	732.4	696.1
55°	1379.1	1240.1	1081.6	944.0	840.3	764.6	718.7	693.8	675.6	657.5	635.3
57.5°	1214.6	1105.9	965.5	839.7	744.3	675.4	632.6	608.2	594.1	584.9	571.8
60°	1098.9	1005.8	884.8	770.2	677.1	615.9	574.2	555.4	543.6	535.9	526.2
62.5°	991.7	915.2	803.2	698.5	617.0	559.1	521.9	503.6	492.4	488.7	480.6
65°	833.4	774.4	681.9	595.0	525.5	476.2	444.9	427.5	420.5	416.3	417.1
67.5°	677.6	641.6	567.3	493.2	437.7	396.4	371.3	358.0	354.5	348.9	348.8
70°	582.5	555.4	492.8	428.2	378.8	346.9	324.6	310.7	307.2	304.4	303.8
72.5°	498.6	474.7	420.5	368.7	324.3	296.2	277.9	269.6	263.9	262.2	262.1
75°	374.7	361.5	318.3	277.3	246.7	227.3	214.8	207.1	203.0	202.2	203.0
77.5°	266.4	254.9	227.5	198.4	179.1	164.3	153.7	151.1	146.4	146.5	145.8
80°	200.2	192.5	175.1	152.2	136.3	123.8	118.2	113.3	111.9	109.9	111.9
82.5°	145.2	137.0	125.1	110.5	97.3	89.8	84.3	82.8	81.9	80.9	81.3
85°	71.6	72.3	65.4	54.2	48.7	44.5	41.0	41.0	40.3	39.6	40.3
87.5°	27.5	25.9	23.4	21.3	18.2	16.1	15.1	15.2	14.0	13.8	14.8
90°	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	40.0	37.8	35.6	33.7	32.3	30.9	29.4	28.0	29.4	30.9	32.3
95°	83.9	81.3	78.8	77.2	76.7	76.2	75.7	75.2	75.7	76.2	76.7
97.5°	134.7	131.2	127.6	125.7	125.6	125.4	125.1	124.9	125.1	125.4	125.6
100°	170.3	166.9	163.6	161.9	161.9	161.9	161.9	161.9	161.9	161.9	161.9
102.5°	210.6	208.9	207.2	205.8	204.8	203.8	202.8	201.7	202.8	203.8	204.8
105°	273.4	271.8	270.3	268.9	267.6	266.3	265.0	263.8	265.0	266.3	267.6
107.5°	340.9	339.7	338.6	337.3	336.1	334.7	333.5	332.2	333.5	334.7	336.1
110°	387.1	386.4	385.6	384.5	383.3	382.0	380.7	379.4	380.7	382.0	383.3



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	432.9	431.9	431.1	430.2	429.5	428.8	428.2	427.5	428.2	428.8	429.5
115°	504.4	503.9	503.5	502.7	501.6	500.6	499.5	498.6	499.5	500.6	501.6
117.5°	573.0	572.6	572.1	571.7	571.1	570.7	570.2	569.8	570.2	570.7	571.1
120°	620.6	620.4	620.1	619.4	618.0	616.8	615.5	614.2	615.5	616.8	618.0
122.5°	666.1	665.4	664.8	664.1	663.7	663.3	662.8	662.4	662.8	663.3	663.7
125°	735.1	734.9	734.6	733.7	732.2	730.7	729.1	727.5	729.1	730.7	732.2
127.5°	801.6	801.4	801.0	800.5	799.6	798.7	797.8	796.9	797.8	798.7	799.6
130°	845.7	845.2	844.6	843.7	842.5	841.2	839.9	838.6	839.9	841.2	842.5
132.5°	889.5	889.6	889.7	888.7	886.5	884.5	882.3	880.2	882.3	884.5	886.5
135°	953.8	953.5	953.2	952.3	950.8	949.2	947.7	946.2	947.7	949.2	950.8
137.5°	1016.3	1015.7	1015.1	1014.1	1012.6	1011.2	1009.7	1008.2	1009.7	1011.2	1012.6
140°	1055.7	1054.9	1054.1	1053.1	1051.9	1050.5	1049.3	1047.9	1049.3	1050.5	1051.9
142.5°	1095.0	1094.0	1093.1	1092.1	1091.0	1089.9	1088.9	1087.8	1088.9	1089.9	1091.0
145°	1152.8	1152.1	1151.3	1150.4	1149.3	1148.3	1147.3	1146.3	1147.3	1148.3	1149.3
147.5°	1204.5	1203.9	1203.3	1202.7	1202.1	1201.6	1201.0	1200.4	1201.0	1201.6	1202.1
150°	1238.0	1236.9	1235.8	1235.5	1235.7	1236.0	1236.3	1236.5	1236.3	1236.0	1235.7
152.5°	1268.7	1268.4	1267.9	1267.6	1267.2	1266.9	1266.5	1266.1	1266.5	1266.9	1267.2
155°	1312.3	1312.1	1311.8	1311.7	1311.7	1311.7	1311.7	1311.7	1311.7	1311.7	1311.7
157.5°	1350.5	1350.2	1350.0	1350.1	1350.7	1351.3	1351.8	1352.4	1351.8	1351.3	1350.7
160°	1373.7	1373.4	1373.1	1373.4	1374.1	1374.9	1375.7	1376.4	1375.7	1374.9	1374.1
162.5°	1395.3	1395.3	1395.3	1395.5	1396.1	1396.6	1397.2	1397.8	1397.2	1396.6	1396.1
165°	1424.5	1424.2	1424.1	1424.2	1424.7	1425.1	1425.7	1426.2	1425.7	1425.1	1424.7
167.5°	1445.6	1445.6	1445.6	1446.2	1447.2	1448.2	1449.2	1450.3	1449.2	1448.2	1447.2
170°	1458.6	1458.6	1458.6	1459.1	1460.2	1461.2	1462.2	1463.2	1462.2	1461.2	1460.2
172.5°	1467.8	1467.8	1467.8	1468.4	1469.4	1470.4	1471.4	1472.5	1471.4	1470.4	1469.4
175°	1478.3	1478.3	1478.3	1478.8	1479.8	1480.9	1481.8	1482.9	1481.8	1480.9	1479.8
177.5°	1484.0	1484.2	1484.4	1484.9	1485.8	1486.6	1487.4	1488.2	1487.4	1486.6	1485.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1609.3	1603.2	1598.2	1587.1	1580.9	1572.6	1565.9	1573.2	1565.4	1568.7	1563.7
5°	1559.2	1539.6	1525.8	1505.6	1488.3	1472.2	1460.4	1458.3	1452.8	1450.0	1441.6
7.5°	1498.8	1474.4	1450.5	1424.2	1401.9	1379.2	1364.8	1352.8	1344.9	1334.4	1327.4
10°	1463.2	1430.6	1402.8	1370.7	1342.9	1318.7	1299.1	1289.4	1280.4	1267.2	1262.3
12.5°	1419.2	1385.5	1351.6	1317.4	1290.7	1263.6	1246.9	1232.2	1225.9	1211.0	1209.5
15°	1366.5	1315.8	1282.5	1247.7	1210.9	1188.7	1174.7	1158.8	1151.8	1141.4	1133.7
17.5°	1303.8	1258.4	1216.7	1180.7	1149.1	1130.4	1113.1	1102.2	1090.2	1083.4	1070.9
20°	1258.1	1215.0	1173.3	1135.1	1110.8	1089.2	1075.3	1064.9	1052.4	1048.9	1036.4
22.5°	1219.8	1172.2	1132.2	1100.1	1073.5	1049.2	1034.2	1027.1	1018.5	1007.8	1005.2
25°	1157.4	1108.0	1074.0	1042.0	1018.3	996.1	985.7	976.6	968.3	960.6	957.9
27.5°	1103.4	1059.4	1018.9	990.0	969.4	949.1	940.0	929.0	922.8	916.7	909.2
30°	1065.6	1020.4	985.0	957.2	935.0	916.9	907.1	899.5	893.9	888.3	884.2
32.5°	1026.7	984.8	950.5	923.3	901.0	887.3	878.8	873.3	867.2	860.5	855.2
35°	975.3	929.3	896.0	872.4	855.0	844.5	834.8	829.9	823.0	823.0	817.4
37.5°	917.3	877.6	848.2	826.6	811.0	801.7	791.2	787.8	783.4	780.4	778.6
40°	882.8	846.0	818.1	796.6	779.9	772.2	763.9	758.4	755.5	752.1	750.7
42.5°	847.2	812.0	785.3	765.4	751.0	744.5	736.6	732.8	727.2	722.6	721.8
45°	793.1	759.0	734.8	718.7	706.2	698.6	693.8	685.4	682.6	677.1	676.4
47.5°	741.8	709.2	685.3	672.2	661.2	655.0	647.3	638.9	635.8	632.9	632.7
50°	703.5	673.6	651.3	638.8	628.4	619.4	611.7	606.1	604.0	604.0	605.5
52.5°	664.5	639.1	620.2	604.8	595.0	585.4	578.4	575.0	571.8	575.2	577.7
55°	607.5	581.8	567.9	553.3	543.6	532.4	529.0	527.6	525.5	531.1	533.9
57.5°	547.2	529.1	512.8	498.4	489.6	483.2	478.5	477.7	481.6	484.2	493.2
60°	508.8	487.9	473.4	462.3	451.8	447.6	446.3	444.9	447.6	455.3	467.1
62.5°	466.5	449.6	433.9	425.5	417.9	411.0	410.6	411.5	417.1	425.8	437.7
65°	404.6	389.9	379.5	369.8	363.6	359.4	360.8	363.6	369.8	381.7	394.8
67.5°	341.6	331.5	322.3	314.3	308.4	308.4	309.8	313.9	321.3	334.9	347.0
70°	301.0	289.9	282.2	278.7	273.8	271.1	275.3	282.2	288.5	301.0	311.4
72.5°	260.4	250.9	245.0	242.6	240.5	238.3	239.7	247.2	255.7	268.1	280.3
75°	200.2	196.7	192.5	189.8	187.7	189.0	190.5	197.4	204.4	217.6	231.5
77.5°	146.2	142.5	140.0	139.3	138.2	138.8	142.8	147.9	154.7	164.3	174.9
80°	110.5	109.1	107.7	107.0	107.0	107.7	113.3	116.8	123.1	132.1	140.4
82.5°	80.5	79.6	79.4	79.3	79.8	79.9	83.3	87.8	93.0	99.8	107.0
85°	42.4	41.0	43.1	43.8	42.4	44.5	45.8	48.7	50.7	54.2	57.7
87.5°	15.8	17.3	17.1	18.0	18.4	19.8	19.5	22.0	23.4	24.8	24.4
90°	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0	22.4	23.6	24.7
92.5°	33.7	35.6	37.8	40.0	42.2	44.4	46.1	47.8	49.5	51.2	52.3
95°	77.2	78.8	81.3	83.9	86.5	89.1	90.9	92.6	94.4	96.3	97.4
97.5°	125.7	127.6	131.2	134.7	138.3	141.8	143.5	145.2	146.9	148.6	149.6
100°	161.9	163.6	166.9	170.3	173.6	177.0	179.3	181.6	183.9	186.2	187.6
102.5°	205.8	207.2	208.9	210.6	212.3	214.0	216.5	219.0	221.5	224.1	225.7
105°	268.9	270.3	271.8	273.4	274.9	276.4	278.0	279.6	281.1	282.6	283.7
107.5°	337.3	338.6	339.7	340.9	342.1	343.3	344.1	344.8	345.6	346.4	346.8
110°	384.5	385.6	386.4	387.1	387.9	388.6	389.4	390.2	390.9	391.7	392.0



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	430.2	431.1	431.9	432.9	433.9	434.9	435.2	435.6	436.0	436.3	436.3
115°	502.7	503.5	503.9	504.4	505.0	505.5	505.2	505.0	504.7	504.4	504.2
117.5°	571.7	572.1	572.6	573.0	573.5	574.0	574.2	574.4	574.5	574.8	574.4
120°	619.4	620.1	620.4	620.6	620.9	621.2	621.2	621.2	621.2	621.2	620.6
122.5°	664.1	664.8	665.4	666.1	666.7	667.4	667.2	667.0	666.8	666.6	666.1
125°	733.7	734.6	734.9	735.1	735.4	735.7	735.1	734.6	734.1	733.6	733.3
127.5°	800.5	801.0	801.4	801.6	802.0	802.3	802.0	801.7	801.5	801.3	800.8
130°	843.7	844.6	845.2	845.7	846.1	846.7	846.4	846.1	846.0	845.7	845.3
132.5°	888.7	889.7	889.6	889.5	889.4	889.3	889.0	888.8	888.5	888.2	887.8
135°	952.3	953.2	953.5	953.8	954.0	954.3	954.3	954.3	954.3	954.3	953.8
137.5°	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7	1018.1	1018.3	1018.7	1018.2
140°	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7	1058.3	1058.7	1059.3	1058.9
142.5°	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3	1097.6	1098.0	1098.2	1097.8
145°	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4	1154.4	1154.4	1154.4	1154.0
147.5°	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4	1206.9	1207.6	1208.2	1207.6
150°	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0	1240.0	1240.0	1240.0	1239.7
152.5°	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2	1270.8	1271.4	1272.0	1271.9
155°	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8	1314.9	1315.9	1317.0	1316.8
157.5°	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0	1353.1	1354.1	1355.1	1354.8
160°	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2	1376.2	1377.2	1378.2	1378.1
162.5°	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7	1397.9	1399.1	1400.3	1400.3
165°	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1	1427.1	1428.2	1429.1	1428.9
167.5°	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2	1448.8	1450.3	1451.8	1451.8
170°	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2	1461.7	1463.2	1464.7	1464.6
172.5°	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4	1471.0	1472.5	1474.0	1474.0
175°	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8	1481.3	1482.9	1484.4	1484.3
177.5°	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8	1486.0	1487.3	1488.5	1488.4
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1560.4	1564.2	1560.9	1565.4	1560.9	1564.2	1560.4	1563.7	1568.7	1565.4	1573.2
5°	1438.2	1431.9	1436.1	1433.3	1436.1	1431.9	1438.2	1441.6	1450.0	1452.8	1458.3
7.5°	1325.3	1319.3	1312.5	1309.3	1312.5	1319.3	1325.3	1327.4	1334.4	1344.9	1352.8
10°	1254.6	1247.1	1246.3	1241.4	1246.3	1247.1	1254.6	1262.3	1267.2	1280.4	1289.4
12.5°	1202.9	1195.9	1187.9	1185.9	1187.9	1195.9	1202.9	1209.5	1211.0	1225.9	1232.2
15°	1129.5	1124.0	1119.1	1123.3	1119.1	1124.0	1129.5	1133.7	1141.4	1151.8	1158.8
17.5°	1068.5	1063.9	1063.1	1057.9	1063.1	1063.9	1068.5	1070.9	1083.4	1090.2	1102.2
20°	1030.2	1026.7	1028.1	1019.0	1028.1	1026.7	1030.2	1036.4	1048.9	1052.4	1064.9
22.5°	999.6	992.7	991.9	990.2	991.9	992.7	999.6	1005.2	1007.8	1018.5	1027.1
25°	951.6	948.2	944.7	948.2	944.7	948.2	951.6	957.9	960.6	968.3	976.6
27.5°	909.7	905.6	904.6	905.0	904.6	905.6	909.7	909.2	916.7	922.8	929.0
30°	884.2	877.3	877.9	877.3	877.9	877.3	884.2	884.2	888.3	893.9	899.5
32.5°	856.4	851.7	850.7	849.4	850.7	851.7	856.4	855.2	860.5	867.2	873.3
35°	815.4	815.4	811.9	811.9	811.9	815.4	815.4	817.4	823.0	823.0	829.9
37.5°	776.9	776.1	774.1	774.4	774.1	776.1	776.9	778.6	780.4	783.4	787.8
40°	748.0	747.3	745.1	741.0	745.1	747.3	748.0	750.7	752.1	755.5	758.4
42.5°	720.1	717.7	716.8	715.4	716.8	717.7	720.1	721.8	722.6	727.2	732.8
45°	676.4	676.4	674.9	674.2	674.9	676.4	676.4	676.4	677.1	682.6	685.4
47.5°	633.8	635.1	637.7	637.3	637.7	635.1	633.8	632.7	632.9	635.8	638.9
50°	608.2	608.9	611.0	611.7	611.0	608.9	608.2	605.5	604.0	604.0	606.1
52.5°	579.9	583.9	586.6	586.1	586.6	583.9	579.9	577.7	575.2	571.8	575.0
55°	540.1	544.9	549.8	550.5	549.8	544.9	540.1	533.9	531.1	525.5	527.6
57.5°	500.8	507.6	512.7	514.3	512.7	507.6	500.8	493.2	484.2	481.6	477.7
60°	474.0	483.1	489.4	492.1	489.4	483.1	474.0	467.1	455.3	447.6	444.9
62.5°	448.4	458.6	464.8	465.5	464.8	458.6	448.4	437.7	425.8	417.1	411.5
65°	406.6	417.1	422.6	426.8	422.6	417.1	406.6	394.8	381.7	369.8	363.6
67.5°	361.6	372.0	378.2	381.5	378.2	372.0	361.6	347.0	334.9	321.3	313.9
70°	328.8	339.2	347.6	350.4	347.6	339.2	328.8	311.4	301.0	288.5	282.2
72.5°	296.5	305.9	312.5	315.8	312.5	305.9	296.5	280.3	268.1	255.7	247.2
75°	240.5	253.0	259.3	262.8	259.3	253.0	240.5	231.5	217.6	204.4	197.4
77.5°	185.5	196.9	200.6	202.4	200.6	196.9	185.5	174.9	164.3	154.7	147.9
80°	148.7	155.7	160.6	161.2	160.6	155.7	148.7	140.4	132.1	123.1	116.8
82.5°	114.3	120.1	121.6	123.4	121.6	120.1	114.3	107.0	99.8	93.0	87.8
85°	62.6	65.4	66.1	65.4	66.1	65.4	62.6	57.7	54.2	50.7	48.7
87.5°	25.7	25.2	25.4	26.7	25.4	25.2	25.7	24.4	24.8	23.4	22.0
90°	25.4	26.2	27.0	27.7	27.0	26.2	25.4	24.7	23.6	22.4	21.0
92.5°	52.9	53.5	54.0	54.6	54.0	53.5	52.9	52.3	51.2	49.5	47.8
95°	97.9	98.4	99.0	99.5	99.0	98.4	97.9	97.4	96.3	94.4	92.6
97.5°	149.9	150.3	150.5	150.9	150.5	150.3	149.9	149.6	148.6	146.9	145.2
100°	188.2	188.7	189.2	189.7	189.2	188.7	188.2	187.6	186.2	183.9	181.6
102.5°	226.4	227.1	227.8	228.5	227.8	227.1	226.4	225.7	224.1	221.5	219.0
105°	284.5	285.3	286.1	286.9	286.1	285.3	284.5	283.7	282.6	281.1	279.6
107.5°	346.7	346.6	346.6	346.5	346.6	346.6	346.7	346.8	346.4	345.6	344.8
110°	391.7	391.5	391.2	390.9	391.2	391.5	391.7	392.0	391.7	390.9	390.2



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	435.9	435.4	434.9	434.4	434.9	435.4	435.9	436.3	436.3	436.0	435.6
115°	503.9	503.6	503.5	503.2	503.5	503.6	503.9	504.2	504.4	504.7	505.0
117.5°	573.4	572.3	571.3	570.2	571.3	572.3	573.4	574.4	574.8	574.5	574.4
120°	619.6	618.6	617.5	616.5	617.5	618.6	619.6	620.6	621.2	621.2	621.2
122.5°	665.2	664.4	663.6	662.8	663.6	664.4	665.2	666.1	666.6	666.8	667.0
125°	733.0	732.7	732.5	732.2	732.5	732.7	733.0	733.3	733.6	734.1	734.6
127.5°	800.4	799.9	799.3	798.8	799.3	799.9	800.4	800.8	801.3	801.5	801.7
130°	844.8	844.3	843.7	843.2	843.7	844.3	844.8	845.3	845.7	846.0	846.1
132.5°	887.1	886.3	885.6	884.8	885.6	886.3	887.1	887.8	888.2	888.5	888.8
135°	952.7	951.7	950.7	949.7	950.7	951.7	952.7	953.8	954.3	954.3	954.3
137.5°	1016.9	1015.6	1014.3	1013.1	1014.3	1015.6	1016.9	1018.2	1018.7	1018.3	1018.1
140°	1057.6	1056.3	1055.1	1053.7	1055.1	1056.3	1057.6	1058.9	1059.3	1058.7	1058.3
142.5°	1096.4	1095.2	1093.9	1092.6	1093.9	1095.2	1096.4	1097.8	1098.2	1098.0	1097.6
145°	1153.2	1152.4	1151.6	1150.9	1151.6	1152.4	1153.2	1154.0	1154.4	1154.4	1154.4
147.5°	1205.9	1204.2	1202.4	1200.7	1202.4	1204.2	1205.9	1207.6	1208.2	1207.6	1206.9
150°	1239.2	1238.7	1238.1	1237.7	1238.1	1238.7	1239.2	1239.7	1240.0	1240.0	1240.0
152.5°	1271.0	1270.1	1269.1	1268.2	1269.1	1270.1	1271.0	1271.9	1272.0	1271.4	1270.8
155°	1315.5	1314.3	1313.0	1311.7	1313.0	1314.3	1315.5	1316.8	1317.0	1315.9	1314.9
157.5°	1353.1	1351.4	1349.7	1348.0	1349.7	1351.4	1353.1	1354.8	1355.1	1354.1	1353.1
160°	1376.9	1375.6	1374.3	1373.0	1374.3	1375.6	1376.9	1378.1	1378.2	1377.2	1376.2
162.5°	1398.7	1397.2	1395.8	1394.3	1395.8	1397.2	1398.7	1400.3	1400.3	1399.1	1397.9
165°	1427.4	1425.8	1424.2	1422.7	1424.2	1425.8	1427.4	1428.9	1429.1	1428.2	1427.1
167.5°	1450.2	1448.6	1447.0	1445.4	1447.0	1448.6	1450.2	1451.8	1451.8	1450.3	1448.8
170°	1462.9	1461.1	1459.2	1457.4	1459.2	1461.1	1462.9	1464.6	1464.7	1463.2	1461.7
172.5°	1472.4	1470.8	1469.2	1467.6	1469.2	1470.8	1472.4	1474.0	1474.0	1472.5	1471.0
175°	1482.5	1480.7	1478.9	1477.1	1478.9	1480.7	1482.5	1484.3	1484.4	1482.9	1481.3
177.5°	1486.9	1485.5	1484.1	1482.6	1484.1	1485.5	1486.9	1488.4	1488.5	1487.3	1486.0
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1565.9	1572.6	1580.9	1587.1	1598.2	1603.2	1609.3	1614.4	1623.2	1631.6	1641.6
5°	1460.4	1472.2	1488.3	1505.6	1525.8	1539.6	1559.2	1570.9	1594.6	1616.1	1637.0
7.5°	1364.8	1379.2	1401.9	1424.2	1450.5	1474.4	1498.8	1525.8	1555.9	1591.5	1621.0
10°	1299.1	1318.7	1342.9	1370.7	1402.8	1430.6	1463.2	1492.4	1529.2	1570.9	1609.9
12.5°	1246.9	1263.6	1290.7	1317.4	1351.6	1385.5	1419.2	1457.9	1500.8	1547.0	1596.0
15°	1174.7	1188.7	1210.9	1247.7	1282.5	1315.8	1366.5	1402.8	1457.0	1508.4	1567.4
17.5°	1113.1	1130.4	1149.1	1180.7	1216.7	1258.4	1303.8	1349.1	1401.3	1466.5	1533.1
20°	1075.3	1089.2	1110.8	1135.1	1173.3	1215.0	1258.1	1304.0	1368.0	1435.4	1507.0
22.5°	1034.2	1049.2	1073.5	1100.1	1132.2	1172.2	1219.8	1270.1	1336.9	1403.1	1480.9
25°	985.7	996.1	1018.3	1042.0	1074.0	1108.0	1157.4	1213.0	1279.0	1354.8	1434.0
27.5°	940.0	949.1	969.4	990.0	1018.9	1059.4	1103.4	1159.6	1221.8	1298.6	1386.4
30°	907.1	916.9	935.0	957.2	985.0	1020.4	1065.6	1118.5	1185.2	1260.3	1352.0
32.5°	878.8	887.3	901.0	923.3	950.5	984.8	1026.7	1080.6	1147.4	1223.5	1313.6
35°	834.8	844.5	855.0	872.4	896.0	929.3	975.3	1026.0	1089.9	1163.6	1246.3
37.5°	791.2	801.7	811.0	826.6	848.2	877.6	917.3	970.1	1028.0	1098.9	1178.3
40°	763.9	772.2	779.9	796.6	818.1	846.0	882.8	930.1	991.2	1057.3	1123.3
42.5°	736.6	744.5	751.0	765.4	785.3	812.0	847.2	893.3	950.1	1011.6	1069.9
45°	693.8	698.6	706.2	718.7	734.8	759.0	793.1	834.1	882.1	940.5	984.3
47.5°	647.3	655.0	661.2	672.2	685.3	709.2	741.8	776.7	820.2	863.6	894.5
50°	611.7	619.4	628.4	638.8	651.3	673.6	703.5	738.9	775.7	809.1	835.5
52.5°	578.4	585.4	595.0	604.8	620.2	639.1	664.5	696.1	732.4	756.3	778.3
55°	529.0	532.4	543.6	553.3	567.9	581.8	607.5	635.3	657.5	675.6	693.8
57.5°	478.5	483.2	489.6	498.4	512.8	529.1	547.2	571.8	584.9	594.1	608.2
60°	446.3	447.6	451.8	462.3	473.4	487.9	508.8	526.2	535.9	543.6	555.4
62.5°	410.6	411.0	417.9	425.5	433.9	449.6	466.5	480.6	488.7	492.4	503.6
65°	360.8	359.4	363.6	369.8	379.5	389.9	404.6	417.1	416.3	420.5	427.5
67.5°	309.8	308.4	308.4	314.3	322.3	331.5	341.6	348.8	348.9	354.5	358.0
70°	275.3	271.1	273.8	278.7	282.2	289.9	301.0	303.8	304.4	307.2	310.7
72.5°	239.7	238.3	240.5	242.6	245.0	250.9	260.4	262.1	262.2	263.9	269.6
75°	190.5	189.0	187.7	189.8	192.5	196.7	200.2	203.0	202.2	203.0	207.1
77.5°	142.8	138.8	138.2	139.3	140.0	142.5	146.2	145.8	146.5	146.4	151.1
80°	113.3	107.7	107.0	107.0	107.7	109.1	110.5	111.9	109.9	111.9	113.3
82.5°	83.3	79.9	79.8	79.3	79.4	79.6	80.5	81.3	80.9	81.9	82.8
85°	45.8	44.5	42.4	43.8	43.1	41.0	42.4	40.3	39.6	40.3	41.0
87.5°	19.5	19.8	18.4	18.0	17.1	17.3	15.8	14.8	13.8	14.0	15.2
90°	19.8	18.5	16.7	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2
92.5°	46.1	44.4	42.2	40.0	37.8	35.6	33.7	32.3	30.9	29.4	28.0
95°	90.9	89.1	86.5	83.9	81.3	78.8	77.2	76.7	76.2	75.7	75.2
97.5°	143.5	141.8	138.3	134.7	131.2	127.6	125.7	125.6	125.4	125.1	124.9
100°	179.3	177.0	173.6	170.3	166.9	163.6	161.9	161.9	161.9	161.9	161.9
102.5°	216.5	214.0	212.3	210.6	208.9	207.2	205.8	204.8	203.8	202.8	201.7
105°	278.0	276.4	274.9	273.4	271.8	270.3	268.9	267.6	266.3	265.0	263.8
107.5°	344.1	343.3	342.1	340.9	339.7	338.6	337.3	336.1	334.7	333.5	332.2
110°	389.4	388.6	387.9	387.1	386.4	385.6	384.5	383.3	382.0	380.7	379.4



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	435.2	434.9	433.9	432.9	431.9	431.1	430.2	429.5	428.8	428.2	427.5
115°	505.2	505.5	505.0	504.4	503.9	503.5	502.7	501.6	500.6	499.5	498.6
117.5°	574.2	574.0	573.5	573.0	572.6	572.1	571.7	571.1	570.7	570.2	569.8
120°	621.2	621.2	620.9	620.6	620.4	620.1	619.4	618.0	616.8	615.5	614.2
122.5°	667.2	667.4	666.7	666.1	665.4	664.8	664.1	663.7	663.3	662.8	662.4
125°	735.1	735.7	735.4	735.1	734.9	734.6	733.7	732.2	730.7	729.1	727.5
127.5°	802.0	802.3	802.0	801.6	801.4	801.0	800.5	799.6	798.7	797.8	796.9
130°	846.4	846.7	846.1	845.7	845.2	844.6	843.7	842.5	841.2	839.9	838.6
132.5°	889.0	889.3	889.4	889.5	889.6	889.7	888.7	886.5	884.5	882.3	880.2
135°	954.3	954.3	954.0	953.8	953.5	953.2	952.3	950.8	949.2	947.7	946.2
137.5°	1017.7	1017.4	1016.9	1016.3	1015.7	1015.1	1014.1	1012.6	1011.2	1009.7	1008.2
140°	1057.7	1057.2	1056.4	1055.7	1054.9	1054.1	1053.1	1051.9	1050.5	1049.3	1047.9
142.5°	1097.3	1097.0	1096.0	1095.0	1094.0	1093.1	1092.1	1091.0	1089.9	1088.9	1087.8
145°	1154.4	1154.4	1153.6	1152.8	1152.1	1151.3	1150.4	1149.3	1148.3	1147.3	1146.3
147.5°	1206.4	1205.8	1205.1	1204.5	1203.9	1203.3	1202.7	1202.1	1201.6	1201.0	1200.4
150°	1240.0	1240.0	1238.9	1238.0	1236.9	1235.8	1235.5	1235.7	1236.0	1236.3	1236.5
152.5°	1270.2	1269.6	1269.2	1268.7	1268.4	1267.9	1267.6	1267.2	1266.9	1266.5	1266.1
155°	1313.8	1312.9	1312.6	1312.3	1312.1	1311.8	1311.7	1311.7	1311.7	1311.7	1311.7
157.5°	1352.0	1351.0	1350.8	1350.5	1350.2	1350.0	1350.1	1350.7	1351.3	1351.8	1352.4
160°	1375.2	1374.1	1373.9	1373.7	1373.4	1373.1	1373.4	1374.1	1374.9	1375.7	1376.4
162.5°	1396.7	1395.4	1395.3	1395.3	1395.3	1395.3	1395.5	1396.1	1396.6	1397.2	1397.8
165°	1426.1	1425.0	1424.8	1424.5	1424.2	1424.1	1424.2	1424.7	1425.1	1425.7	1426.2
167.5°	1447.2	1445.6	1445.6	1445.6	1445.6	1445.6	1446.2	1447.2	1448.2	1449.2	1450.3
170°	1460.2	1458.6	1458.6	1458.6	1458.6	1458.6	1459.1	1460.2	1461.2	1462.2	1463.2
172.5°	1469.4	1467.8	1467.8	1467.8	1467.8	1467.8	1468.4	1469.4	1470.4	1471.4	1472.5
175°	1479.8	1478.3	1478.3	1478.3	1478.3	1478.3	1478.8	1479.8	1480.9	1481.8	1482.9
177.5°	1484.8	1483.5	1483.8	1484.0	1484.2	1484.4	1484.9	1485.8	1486.6	1487.4	1488.2
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1646.5	1654.4	1659.4	1668.8	1676.6	1681.1	1685.0	1688.3	1692.2	1695.5	1705.0
5°	1657.2	1675.2	1690.5	1714.1	1735.7	1752.4	1770.4	1786.5	1799.7	1818.4	1833.0
7.5°	1652.5	1684.6	1718.3	1754.9	1792.2	1827.0	1859.0	1888.9	1916.0	1948.8	1977.5
10°	1648.1	1691.9	1735.0	1784.3	1835.1	1878.2	1918.5	1959.5	1989.4	2031.1	2066.5
12.5°	1644.8	1696.3	1748.4	1807.7	1863.4	1924.3	1978.0	2007.9	2053.3	2086.7	2128.9
15°	1630.8	1698.9	1770.4	1837.2	1916.4	1972.7	2020.0	2078.4	2120.8	2163.2	2209.0
17.5°	1605.5	1682.7	1762.8	1850.2	1926.3	1986.7	2047.6	2104.0	2154.6	2211.4	2268.5
20°	1593.8	1671.1	1762.8	1852.4	1926.8	1990.1	2052.6	2114.5	2170.2	2243.1	2309.2
22.5°	1569.4	1662.7	1747.2	1834.7	1911.3	1980.0	2051.0	2121.2	2195.1	2277.6	2360.3
25°	1525.8	1620.3	1709.9	1796.2	1873.3	1959.5	2035.2	2129.1	2223.7	2332.8	2435.6
27.5°	1480.4	1570.9	1653.1	1736.3	1826.3	1924.0	2022.2	2128.7	2252.5	2390.2	2535.3
30°	1443.8	1529.2	1609.2	1694.7	1788.5	1898.4	2006.1	2132.6	2275.8	2430.8	2603.2
32.5°	1400.9	1479.7	1557.5	1648.0	1750.2	1866.1	1991.6	2130.4	2302.5	2478.6	2656.0
35°	1327.7	1393.7	1473.6	1570.2	1685.6	1818.4	1963.7	2127.7	2325.1	2527.4	2676.8
37.5°	1240.7	1302.3	1386.4	1492.4	1613.4	1755.9	1928.2	2122.9	2332.5	2493.8	2542.0
40°	1182.4	1239.4	1327.0	1436.8	1560.5	1711.4	1900.4	2106.2	2309.2	2412.0	2372.4
42.5°	1120.1	1179.9	1265.2	1373.9	1507.2	1671.3	1865.4	2071.2	2241.3	2280.2	2143.3
45°	1021.8	1083.7	1167.8	1277.6	1420.8	1598.7	1801.0	1988.0	2086.0	2015.8	1803.8
47.5°	930.5	988.5	1066.4	1179.7	1327.5	1511.5	1706.4	1855.6	1863.3	1695.8	1469.4
50°	868.2	921.7	1000.2	1113.6	1260.3	1446.5	1622.4	1739.8	1687.0	1497.3	1279.7
52.5°	807.0	859.4	936.8	1049.1	1194.1	1364.8	1528.4	1610.9	1511.3	1316.5	1130.7
55°	718.7	764.6	840.3	944.0	1081.6	1240.1	1379.1	1407.6	1278.3	1086.5	935.6
57.5°	632.6	675.4	744.3	839.7	965.5	1105.9	1214.6	1208.5	1071.8	907.2	787.6
60°	574.2	615.9	677.1	770.2	884.8	1005.8	1098.9	1076.7	941.2	799.4	698.6
62.5°	521.9	559.1	617.0	698.5	803.2	915.2	991.7	958.9	826.1	702.0	622.4
65°	444.9	476.2	525.5	595.0	681.9	774.4	833.4	791.0	677.7	581.1	517.2
67.5°	371.3	396.4	437.7	493.2	567.3	641.6	677.6	634.9	544.3	473.8	426.4
70°	324.6	346.9	378.8	428.2	492.8	555.4	582.5	544.3	466.5	405.9	371.8
72.5°	277.9	296.2	324.3	368.7	420.5	474.7	498.6	462.0	398.1	347.0	315.1
75°	214.8	227.3	246.7	277.3	318.3	361.5	374.7	342.7	301.7	263.4	242.6
77.5°	153.7	164.3	179.1	198.4	227.5	254.9	266.4	247.9	216.2	192.0	174.9
80°	118.2	123.8	136.3	152.2	175.1	192.5	200.2	188.4	166.1	148.0	134.8
82.5°	84.3	89.8	97.3	110.5	125.1	137.0	145.2	137.2	121.1	106.9	99.2
85°	41.0	44.5	48.7	54.2	65.4	72.3	71.6	66.7	60.5	54.9	50.7
87.5°	15.1	16.1	18.2	21.3	23.4	25.9	27.5	26.7	24.8	23.5	22.0
90°	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0
92.5°	29.4	30.9	32.3	33.7	35.6	37.8	40.0	42.2	44.4	46.1	47.8
95°	75.7	76.2	76.7	77.2	78.8	81.3	83.9	86.5	89.1	90.9	92.6
97.5°	125.1	125.4	125.6	125.7	127.6	131.2	134.7	138.3	141.8	143.5	145.2
100°	161.9	161.9	161.9	161.9	163.6	166.9	170.3	173.6	177.0	179.3	181.6
102.5°	202.8	203.8	204.8	205.8	207.2	208.9	210.6	212.3	214.0	216.5	219.0
105°	265.0	266.3	267.6	268.9	270.3	271.8	273.4	274.9	276.4	278.0	279.6
107.5°	333.5	334.7	336.1	337.3	338.6	339.7	340.9	342.1	343.3	344.1	344.8
110°	380.7	382.0	383.3	384.5	385.6	386.4	387.1	387.9	388.6	389.4	390.2



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	428.2	428.8	429.5	430.2	431.1	431.9	432.9	433.9	434.9	435.2	435.6
115°	499.5	500.6	501.6	502.7	503.5	503.9	504.4	505.0	505.5	505.2	505.0
117.5°	570.2	570.7	571.1	571.7	572.1	572.6	573.0	573.5	574.0	574.2	574.4
120°	615.5	616.8	618.0	619.4	620.1	620.4	620.6	620.9	621.2	621.2	621.2
122.5°	662.8	663.3	663.7	664.1	664.8	665.4	666.1	666.7	667.4	667.2	667.0
125°	729.1	730.7	732.2	733.7	734.6	734.9	735.1	735.4	735.7	735.1	734.6
127.5°	797.8	798.7	799.6	800.5	801.0	801.4	801.6	802.0	802.3	802.0	801.7
130°	839.9	841.2	842.5	843.7	844.6	845.2	845.7	846.1	846.7	846.4	846.1
132.5°	882.3	884.5	886.5	888.7	889.7	889.6	889.5	889.4	889.3	889.0	888.8
135°	947.7	949.2	950.8	952.3	953.2	953.5	953.8	954.0	954.3	954.3	954.3
137.5°	1009.7	1011.2	1012.6	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7	1018.1
140°	1049.3	1050.5	1051.9	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7	1058.3
142.5°	1088.9	1089.9	1091.0	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3	1097.6
145°	1147.3	1148.3	1149.3	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4	1154.4
147.5°	1201.0	1201.6	1202.1	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4	1206.9
150°	1236.3	1236.0	1235.7	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0	1240.0
152.5°	1266.5	1266.9	1267.2	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2	1270.8
155°	1311.7	1311.7	1311.7	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8	1314.9
157.5°	1351.8	1351.3	1350.7	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0	1353.1
160°	1375.7	1374.9	1374.1	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2	1376.2
162.5°	1397.2	1396.6	1396.1	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7	1397.9
165°	1425.7	1425.1	1424.7	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1	1427.1
167.5°	1449.2	1448.2	1447.2	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2	1448.8
170°	1462.2	1461.2	1460.2	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2	1461.7
172.5°	1471.4	1470.4	1469.4	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4	1471.0
175°	1481.8	1480.9	1479.8	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8	1481.3
177.5°	1487.4	1486.6	1485.8	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8	1486.0
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1712.7	1717.2	1726.6	1723.3	1727.8	1730.0	1732.2
5°	1851.1	1873.3	1883.0	1881.7	1896.2	1892.7	1889.3
7.5°	2007.3	2030.7	2043.8	2060.0	2069.5	2070.2	2078.4
10°	2095.8	2126.4	2138.9	2156.2	2167.4	2173.6	2172.9
12.5°	2163.6	2187.5	2215.5	2224.1	2239.1	2247.0	2244.1
15°	2245.2	2283.4	2312.7	2327.2	2346.0	2351.5	2359.2
17.5°	2318.1	2369.4	2403.4	2448.7	2465.8	2476.3	2470.1
20°	2373.1	2440.5	2474.6	2528.8	2558.7	2574.7	2569.1
22.5°	2438.2	2511.1	2574.1	2621.1	2666.6	2688.2	2692.6
25°	2549.7	2649.7	2742.2	2804.1	2860.3	2873.5	2902.8
27.5°	2674.2	2792.2	2891.1	2956.2	2995.3	3010.1	3019.2
30°	2752.6	2870.1	2944.5	2986.2	2998.7	2997.3	2995.9
32.5°	2791.0	2864.5	2878.9	2867.2	2838.6	2814.3	2789.1
35°	2736.7	2681.7	2599.7	2494.0	2416.2	2337.6	2330.0
37.5°	2461.2	2285.6	2149.1	1996.6	1908.6	1854.3	1816.8
40°	2202.1	2002.6	1837.2	1708.6	1618.9	1583.5	1548.7
42.5°	1920.7	1730.1	1583.6	1476.1	1408.7	1369.4	1341.8
45°	1560.5	1392.3	1277.6	1199.8	1146.2	1115.6	1098.2
47.5°	1278.7	1154.3	1056.9	1000.7	963.7	940.0	940.0
50°	1127.5	1008.6	944.0	899.5	867.5	848.7	852.2
52.5°	993.5	904.6	849.4	812.2	788.5	776.9	776.6
55°	830.6	766.7	730.6	703.5	687.4	674.2	677.1
57.5°	710.5	656.6	632.4	609.9	598.8	593.5	585.9
60°	636.1	594.3	573.5	555.4	544.3	540.1	532.4
62.5°	569.9	537.1	516.7	502.0	492.0	490.6	484.6
65°	478.9	453.9	435.9	428.9	418.5	415.7	415.7
67.5°	394.8	376.9	362.8	356.4	351.9	352.6	349.2
70°	342.0	327.4	318.3	311.4	307.9	308.6	305.9
72.5°	299.2	282.9	275.0	270.8	266.3	268.0	266.9
75°	226.6	218.3	214.1	209.9	207.1	205.7	204.4
77.5°	166.4	159.1	155.9	153.5	153.9	150.5	153.2
80°	128.6	122.3	120.3	116.8	116.1	116.1	115.4
82.5°	94.1	90.6	89.1	86.2	85.0	86.1	84.3
85°	48.7	45.8	45.2	45.2	43.8	42.4	45.8
87.5°	22.3	20.3	20.5	20.1	20.2	19.9	18.9
90°	22.4	23.6	24.7	25.4	26.2	27.0	27.7
92.5°	49.5	51.2	52.3	52.9	53.5	54.0	54.6
95°	94.4	96.3	97.4	97.9	98.4	99.0	99.5
97.5°	146.9	148.6	149.6	149.9	150.3	150.5	150.9
100°	183.9	186.2	187.6	188.2	188.7	189.2	189.7
102.5°	221.5	224.1	225.7	226.4	227.1	227.8	228.5
105°	281.1	282.6	283.7	284.5	285.3	286.1	286.9
107.5°	345.6	346.4	346.8	346.7	346.6	346.6	346.5
110°	390.9	391.7	392.0	391.7	391.5	391.2	390.9



TEST NUMBER: P333479-940

CATALOG NUMBER: S125DIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	436.0	436.3	436.3	435.9	435.4	434.9	434.4
115°	504.7	504.4	504.2	503.9	503.6	503.5	503.2
117.5°	574.5	574.8	574.4	573.4	572.3	571.3	570.2
120°	621.2	621.2	620.6	619.6	618.6	617.5	616.5
122.5°	666.8	666.6	666.1	665.2	664.4	663.6	662.8
125°	734.1	733.6	733.3	733.0	732.7	732.5	732.2
127.5°	801.5	801.3	800.8	800.4	799.9	799.3	798.8
130°	846.0	845.7	845.3	844.8	844.3	843.7	843.2
132.5°	888.5	888.2	887.8	887.1	886.3	885.6	884.8
135°	954.3	954.3	953.8	952.7	951.7	950.7	949.7
137.5°	1018.3	1018.7	1018.2	1016.9	1015.6	1014.3	1013.1
140°	1058.7	1059.3	1058.9	1057.6	1056.3	1055.1	1053.7
142.5°	1098.0	1098.2	1097.8	1096.4	1095.2	1093.9	1092.6
145°	1154.4	1154.4	1154.0	1153.2	1152.4	1151.6	1150.9
147.5°	1207.6	1208.2	1207.6	1205.9	1204.2	1202.4	1200.7
150°	1240.0	1240.0	1239.7	1239.2	1238.7	1238.1	1237.7
152.5°	1271.4	1272.0	1271.9	1271.0	1270.1	1269.1	1268.2
155°	1315.9	1317.0	1316.8	1315.5	1314.3	1313.0	1311.7
157.5°	1354.1	1355.1	1354.8	1353.1	1351.4	1349.7	1348.0
160°	1377.2	1378.2	1378.1	1376.9	1375.6	1374.3	1373.0
162.5°	1399.1	1400.3	1400.3	1398.7	1397.2	1395.8	1394.3
165°	1428.2	1429.1	1428.9	1427.4	1425.8	1424.2	1422.7
167.5°	1450.3	1451.8	1451.8	1450.2	1448.6	1447.0	1445.4
170°	1463.2	1464.7	1464.6	1462.9	1461.1	1459.2	1457.4
172.5°	1472.5	1474.0	1474.0	1472.4	1470.8	1469.2	1467.6
175°	1482.9	1484.4	1484.3	1482.5	1480.7	1478.9	1477.1
177.5°	1487.3	1488.5	1488.4	1486.9	1485.5	1484.1	1482.6
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4

(END OF REPORT)