

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333365-940

Luminaire Tested: **S125DIW-S375D1560U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333365-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6195.8 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	59	57	56	43	41	40	27	26	26	19
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	21	20	19	14
4	70	59	52	46	61	53	47	42	41	36	33	30	27	24	19	17	16	12
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	39	34	52	42	36	31	33	28	24	24	21	18	15	14	12	9
7	54	42	35	30	48	38	31	27	29	25	21	22	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3135	3135	3135	3135
5°	3630	3146	2755	3146
10°	4224	3129	2413	3129
15°	4676	3107	2226	3107
20°	5234	3070	2076	3070
25°	6131	3029	2003	3029
30°	6623	2988	1939	2988
35°	5445	2912	1898	2912
40°	3871	2807	1851	2807
45°	2974	2665	1825	2665
50°	2538	2488	1822	2488
55°	2260	2315	1838	2315
60°	2038	2126	1885	2126
65°	1883	1936	1933	1936
70°	1713	1739	1962	1739
75°	1510	1532	1941	1532
80°	1272	1250	1778	1250
85°	1008	897	1438	897



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	0.8
10°-20°	139.1	2.2
20°-30°	225.9	3.6
30°-40°	275.6	4.4
40°-50°	250.7	4.0
50°-60°	199.7	3.2
60°-70°	139.1	2.2
70°-80°	74.2	1.2
80°-90°	22.5	0.4
90°-100°	115.7	1.9
100°-110°	341.8	5.5
110°-120°	578.9	9.3
120°-130°	761.9	12.3
130°-140°	853.7	13.8
140°-150°	836.7	13.5
150°-160°	702.8	11.3
160°-170°	467.2	7.5
170°-180°	163.5	2.6
0°-30°	411.8	6.6
0°-40°	687.4	11.1
0°-60°	1137.8	18.4
0°-90°	1373.6	22.2
90°-120°	1036.5	16.7
90°-150°	3488.8	56.3
90°-180°	4822.0	77.8
0°-180°	6195.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	560	485	425	485	560	56
15°	699	465	333	465	699	200
25°	860	425	281	425	860	393
35°	691	369	241	369	691	423
45°	326	292	200	292	326	261
55°	201	206	163	206	201	181
65°	123	127	126	127	123	122
75°	60	61	78	61	60	65
85°	14	12	19	12	14	17
90°	32	1	32	1	32	19
95°	116	87	116	87	116	118
105°	334	307	334	307	334	353
115°	585	580	585	580	585	579
125°	851	846	851	846	851	760
135°	1104	1100	1104	1100	1104	852
145°	1338	1333	1338	1333	1338	835
155°	1525	1525	1525	1525	1525	702
165°	1654	1658	1654	1658	1654	466
175°	1717	1724	1717	1724	1717	163
180°	1728	1728	1728	1728	1728	



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	513.4	512.8	512.1	510.9	511.8	509.0	507.7	505.4	502.6	501.6	500.4
5°	560.0	561.1	562.1	557.8	558.2	555.3	548.7	543.3	539.0	533.4	529.5
7.5°	616.1	613.7	613.4	610.6	605.8	601.9	595.0	586.2	577.7	567.9	559.9
10°	644.1	644.4	642.5	639.2	634.0	630.3	621.3	612.6	602.1	589.7	580.9
12.5°	665.2	666.1	663.7	659.2	656.7	648.5	641.3	631.1	618.6	608.7	595.2
15°	699.3	697.1	695.4	689.8	685.5	676.9	665.6	654.8	641.2	628.7	616.1
17.5°	732.2	734.1	730.9	725.9	712.4	702.3	687.2	672.4	655.5	638.6	623.7
20°	761.5	763.2	758.5	749.6	733.5	723.4	703.5	684.5	664.9	643.3	626.8
22.5°	798.2	796.8	790.4	776.9	763.0	744.4	722.7	699.6	675.1	650.7	628.7
25°	860.4	851.8	847.8	831.2	812.9	785.4	755.8	722.0	691.5	659.2	631.2
27.5°	895.0	892.2	887.9	876.3	857.0	827.7	792.7	751.5	708.6	667.7	631.0
30°	888.1	888.5	888.9	885.2	872.8	850.8	815.9	771.7	720.5	674.6	632.1
32.5°	826.7	834.2	841.4	849.9	853.4	849.1	827.3	787.3	734.7	682.5	631.5
35°	690.6	692.9	716.2	739.3	770.6	795.0	811.2	793.4	749.2	689.2	630.7
37.5°	538.5	549.7	565.8	591.8	637.0	677.5	729.6	753.5	739.2	691.4	629.3
40°	459.1	469.4	479.9	506.5	544.6	593.6	652.7	703.2	715.0	684.5	624.3
42.5°	397.8	405.9	417.6	437.6	469.4	512.8	569.4	635.3	675.9	664.4	613.9
45°	325.6	330.7	339.7	355.6	378.7	412.7	462.5	534.7	597.5	618.3	589.3
47.5°	278.7	278.7	285.7	296.6	313.3	342.1	379.1	435.5	502.7	552.3	550.0
50°	252.6	251.6	257.2	266.6	279.8	299.0	334.2	379.3	443.8	500.1	515.8
52.5°	230.2	230.3	233.7	240.8	251.8	268.1	294.4	335.2	390.2	448.0	477.5
55°	200.7	199.8	203.8	208.5	216.6	227.3	246.2	277.3	322.1	378.9	417.2
57.5°	173.6	175.9	177.5	180.7	187.4	194.7	210.6	233.4	268.9	317.7	358.2
60°	157.8	160.1	161.3	164.6	170.0	176.2	188.5	207.1	236.9	279.0	319.1
62.5°	143.7	145.4	145.9	148.8	153.2	159.2	168.9	184.5	208.1	244.9	284.2
65°	123.2	123.2	124.0	127.2	129.2	134.6	142.0	153.3	172.3	200.9	234.5
67.5°	103.5	104.5	104.3	105.7	107.5	111.7	117.0	126.4	140.4	161.3	188.2
70°	90.7	91.5	91.3	92.3	94.3	97.0	101.4	110.2	120.3	138.2	161.3
72.5°	79.1	79.5	78.9	80.3	81.5	83.8	88.7	93.5	102.8	118.0	137.0
75°	60.5	61.0	61.4	62.2	63.5	64.7	67.1	71.9	78.1	89.4	101.6
77.5°	45.4	44.6	45.7	45.5	46.2	47.2	49.3	51.8	56.9	64.1	73.5
80°	34.2	34.4	34.4	34.6	35.7	36.3	38.1	39.9	43.9	49.2	55.8
82.5°	25.0	25.5	25.1	25.6	26.4	26.8	27.9	29.4	31.7	35.9	40.7
85°	13.6	12.6	13.0	13.4	13.4	13.6	14.4	15.1	16.3	17.9	19.8
87.5°	10.4	10.5	10.5	10.3	10.3	10.1	10.4	10.2	10.3	10.6	10.8
90°	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5	23.0	21.5	19.4
92.5°	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6	53.6	51.6	49.0
95°	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7	105.7	103.5	100.6
97.5°	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8	166.8	164.9	160.8
100°	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2	208.5	205.7	201.9
102.5°	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7	251.7	248.8	246.8
105°	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0	323.2	321.5	319.6
107.5°	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9	400.0	399.1	397.8
110°	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7	452.7	451.8	450.9



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5	506.0	505.7	504.5
115°	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1	587.4	587.7	587.1
117.5°	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8	667.5	667.4	666.7
120°	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2	722.2	722.2	721.8
122.5°	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5	775.7	776.0	775.2
125°	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2	854.7	855.3	855.1
127.5°	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2	932.5	932.8	932.5
130°	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8	984.1	984.4	983.8
132.5°	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3	1033.6	1033.9	1034.0
135°	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5	1109.5	1109.5	1109.2
137.5°	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7	1183.3	1182.9	1182.2
140°	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4	1229.8	1229.2	1228.3
142.5°	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1	1275.8	1275.4	1274.3
145°	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1	1342.1	1342.1	1341.2
147.5°	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3	1402.6	1401.9	1401.1
150°	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7	1441.7	1441.7	1440.5
152.5°	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6	1476.9	1476.1	1475.6
155°	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7	1527.6	1526.4	1526.1
157.5°	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2	1572.0	1570.7	1570.5
160°	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1	1598.8	1597.7	1597.4
162.5°	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3	1623.9	1622.4	1622.4
165°	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2	1658.0	1656.9	1656.5
167.5°	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4	1682.6	1680.8	1680.8
170°	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4	1697.6	1695.9	1695.9
172.5°	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2	1708.4	1706.6	1706.6
175°	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3	1720.5	1718.7	1718.7
177.5°	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8	1726.4	1724.9	1725.1
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	499.4	498.3	497.0	494.6	491.9	490.4	488.1	486.6	483.7	481.2	478.5
5°	524.8	519.4	514.5	508.1	501.1	496.6	491.2	485.3	479.0	472.7	465.7
7.5°	551.1	541.5	531.3	520.2	509.3	499.4	489.8	480.5	471.8	461.2	452.3
10°	568.6	556.7	543.9	529.0	514.2	501.5	488.6	477.2	465.7	453.3	442.4
12.5°	586.3	570.4	552.3	535.8	518.3	502.8	487.6	473.1	458.6	444.9	432.1
15°	598.8	584.8	568.1	544.6	524.8	503.5	483.4	464.7	447.1	431.9	415.8
17.5°	607.0	588.9	571.0	548.5	522.5	498.8	475.9	454.4	434.7	415.4	399.9
20°	608.4	589.9	571.1	549.1	522.5	495.3	472.4	446.7	425.5	405.5	386.6
22.5°	608.0	586.9	566.5	543.9	517.9	492.8	465.2	439.0	415.9	396.3	376.5
25°	603.3	580.9	555.3	532.4	506.8	480.3	452.3	425.1	401.6	379.2	359.5
27.5°	599.4	570.3	541.4	514.7	490.0	465.7	438.8	411.0	385.0	362.2	343.8
30°	594.7	562.7	530.1	502.3	477.0	453.3	427.9	400.7	373.5	351.3	331.5
32.5°	590.4	553.1	518.8	488.5	461.6	438.6	415.3	389.4	362.7	340.1	320.3
35°	582.1	539.0	499.6	465.5	436.8	413.1	393.5	369.4	344.9	323.1	304.2
37.5°	571.6	520.5	478.2	442.4	411.0	386.0	367.8	349.3	325.7	304.7	287.6
40°	563.3	507.3	462.5	425.9	393.3	367.4	350.4	333.0	313.4	293.8	275.7
42.5°	552.9	495.4	446.7	407.2	375.1	349.7	332.0	317.2	299.9	281.6	264.8
45°	533.9	473.9	421.2	378.7	346.2	321.2	302.9	291.8	278.7	261.4	247.3
47.5°	505.8	448.1	393.5	349.7	316.1	293.0	275.8	265.1	256.0	243.2	230.2
50°	480.9	428.8	373.5	330.1	296.5	273.2	257.3	247.6	239.9	230.0	219.0
52.5°	453.1	404.6	353.9	310.9	277.7	254.8	239.2	230.7	224.2	217.1	206.3
55°	408.8	367.6	320.6	279.8	249.1	226.7	213.0	205.6	200.3	194.9	188.3
57.5°	360.1	327.8	286.2	248.9	220.6	200.2	187.5	180.3	176.1	173.3	169.5
60°	325.7	298.2	262.3	228.3	200.7	182.5	170.2	164.6	161.1	158.9	156.0
62.5°	293.9	271.3	238.1	207.1	182.9	165.8	154.7	149.3	146.0	144.8	142.5
65°	247.1	229.5	202.2	176.4	155.8	141.2	131.9	126.7	124.7	123.4	123.6
67.5°	200.8	190.2	168.2	146.2	129.7	117.5	110.0	106.1	105.0	103.4	103.4
70°	172.6	164.6	146.1	126.9	112.3	102.8	96.2	92.1	91.0	90.2	90.1
72.5°	147.8	140.7	124.7	109.3	96.1	87.8	82.4	79.9	78.2	77.8	77.7
75°	111.0	107.2	94.3	82.2	73.1	67.4	63.7	61.4	60.2	59.9	60.2
77.5°	78.9	75.5	67.4	58.8	53.1	48.7	45.6	44.8	43.4	43.4	43.2
80°	59.3	57.1	51.9	45.1	40.4	36.6	35.0	33.6	33.2	32.5	33.2
82.5°	43.0	40.6	37.1	32.7	28.8	26.7	25.0	24.5	24.3	24.0	24.1
85°	21.2	21.4	19.4	16.1	14.4	13.2	12.1	12.1	11.9	11.8	11.9
87.5°	10.7	10.0	8.9	7.9	6.7	5.7	5.0	4.7	4.7	5.0	5.6
90°	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3	3.7	6.2	8.6
92.5°	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5	34.2	35.9	37.5
95°	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4	88.0	88.6	89.2
97.5°	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3	145.4	145.7	146.0
100°	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2
102.5°	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5	235.8	236.9	238.1
105°	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7	308.1	309.6	311.1
107.5°	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2	387.7	389.2	390.7
110°	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1	442.6	444.1	445.6



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0	497.8	498.6	499.4
115°	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6	580.9	582.0	583.2
117.5°	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5	663.0	663.5	664.1
120°	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1	715.6	717.1	718.6
122.5°	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1	770.6	771.2	771.7
125°	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9	847.7	849.5	851.3
127.5°	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6	927.6	928.6	929.6
130°	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0	976.5	978.0	979.5
132.5°	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4	1025.9	1028.3	1030.8
135°	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1	1101.9	1103.7	1105.5
137.5°	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2	1173.9	1175.6	1177.3
140°	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4	1219.9	1221.4	1222.9
142.5°	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7	1266.0	1267.2	1268.5
145°	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8	1333.9	1335.2	1336.3
147.5°	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7	1396.3	1397.0	1397.7
150°	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6	1437.3	1437.1	1436.7
152.5°	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0	1472.5	1472.9	1473.3
155°	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4	1571.7	1571.1	1570.4
160°	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4	1599.5	1598.6	1597.7
162.5°	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1	1624.4	1623.8	1623.2
165°	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2	1657.6	1657.0	1656.4
167.5°	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1	1685.0	1683.8	1682.6
170°	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2	1700.0	1698.8	1697.6
172.5°	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0	1710.8	1709.6	1708.4
175°	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1	1722.9	1721.7	1720.5
177.5°	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3	1729.3	1728.4	1727.4
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	477.1	475.2	473.8	470.5	468.6	466.2	464.2	466.4	464.0	465.0	463.5
5°	462.2	456.4	452.3	446.3	441.1	436.4	432.9	432.3	430.6	429.8	427.3
7.5°	444.3	437.0	430.0	422.1	415.5	408.8	404.6	401.0	398.7	395.6	393.4
10°	433.7	424.0	415.8	406.4	398.1	390.8	385.1	382.2	379.5	375.6	374.2
12.5°	420.7	410.7	400.6	390.5	382.5	374.5	369.6	365.2	363.4	359.0	358.6
15°	405.1	390.0	380.1	369.9	358.9	352.3	348.2	343.5	341.4	338.3	336.1
17.5°	386.5	373.0	360.7	350.0	340.6	335.1	329.9	326.7	323.2	321.1	317.4
20°	372.9	360.2	347.8	336.4	329.2	322.9	318.8	315.7	311.9	310.9	307.2
22.5°	361.6	347.5	335.6	326.1	318.3	311.0	306.6	304.4	301.9	298.7	298.0
25°	343.0	328.4	318.3	308.9	301.8	295.2	292.2	289.5	287.0	284.7	283.9
27.5°	327.1	314.0	302.0	293.5	287.3	281.3	278.7	275.4	273.6	271.7	269.5
30°	315.8	302.5	291.9	283.7	277.1	271.8	268.9	266.6	265.0	263.3	262.1
32.5°	304.3	291.9	281.8	273.7	267.1	263.1	260.5	258.9	257.1	255.1	253.5
35°	289.1	275.4	265.6	258.6	253.4	250.3	247.4	246.0	244.0	244.0	242.3
37.5°	271.9	260.1	251.4	245.0	240.4	237.6	234.5	233.5	232.2	231.3	230.8
40°	261.7	250.7	242.5	236.1	231.2	228.9	226.4	224.8	224.0	222.9	222.6
42.5°	251.1	240.7	232.8	226.9	222.6	220.7	218.4	217.2	215.5	214.2	213.9
45°	235.1	225.0	217.8	213.0	209.4	207.1	205.6	203.1	202.3	200.7	200.5
47.5°	219.9	210.2	203.1	199.2	196.0	194.1	191.9	189.4	188.4	187.6	187.5
50°	208.5	199.7	193.1	189.4	186.3	183.6	181.3	179.7	179.1	179.1	179.5
52.5°	197.0	189.4	183.9	179.3	176.4	173.5	171.4	170.4	169.5	170.5	171.2
55°	180.1	172.5	168.4	164.0	161.1	157.8	156.8	156.4	155.8	157.4	158.3
57.5°	162.2	156.9	152.0	147.8	145.2	143.2	141.9	141.6	142.8	143.6	146.2
60°	150.8	144.6	140.4	137.1	133.9	132.7	132.2	131.9	132.7	134.9	138.5
62.5°	138.3	133.3	128.6	126.2	123.9	121.8	121.7	122.0	123.6	126.3	129.7
65°	119.9	115.6	112.5	109.6	107.7	106.6	106.9	107.7	109.6	113.2	117.0
67.5°	101.2	98.3	95.5	93.2	91.4	91.4	91.8	93.1	95.2	99.2	102.8
70°	89.3	86.0	83.6	82.7	81.1	80.3	81.6	83.6	85.5	89.3	92.3
72.5°	77.2	74.4	72.6	71.9	71.2	70.6	71.1	73.3	75.8	79.5	83.1
75°	59.3	58.3	57.1	56.3	55.6	56.1	56.4	58.5	60.5	64.5	68.6
77.5°	43.3	42.3	41.5	41.3	40.9	41.2	42.4	43.9	45.8	48.7	51.8
80°	32.7	32.4	31.9	31.7	31.7	31.9	33.6	34.6	36.5	39.1	41.6
82.5°	23.9	23.6	23.5	23.5	23.6	23.7	24.7	26.0	27.6	29.6	31.7
85°	12.6	12.1	12.8	13.0	12.6	13.2	13.6	14.4	15.1	16.1	17.1
87.5°	6.3	7.0	7.3	7.9	8.3	9.1	9.2	10.2	10.8	11.4	11.5
90°	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5	26.0	27.5	28.7
92.5°	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6	57.5	59.6	60.8
95°	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7	109.9	111.9	113.2
97.5°	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8	170.8	172.7	174.0
100°	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2	213.8	216.5	218.2
102.5°	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7	257.6	260.5	262.4
105°	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0	326.8	328.6	329.9
107.5°	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9	401.8	402.7	403.1
110°	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7	454.6	455.5	455.8



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5	506.9	507.3	507.3
115°	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1	586.8	586.5	586.2
117.5°	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8	668.1	668.2	667.8
120°	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2	722.2	722.2	721.6
122.5°	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5	775.3	775.0	774.5
125°	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2	853.5	852.9	852.5
127.5°	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2	931.9	931.6	931.1
130°	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8	983.6	983.2	982.8
132.5°	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3	1033.0	1032.7	1032.2
135°	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5	1109.5	1109.5	1108.9
137.5°	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7	1184.0	1184.4	1183.8
140°	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4	1231.0	1231.5	1231.1
142.5°	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1	1276.5	1276.9	1276.3
145°	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1	1342.1	1342.1	1341.7
147.5°	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3	1404.0	1404.7	1404.1
150°	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7	1441.7	1441.7	1441.4
152.5°	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6	1478.3	1479.0	1478.8
155°	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7	1530.0	1531.2	1531.1
157.5°	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2	1574.4	1575.6	1575.2
160°	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1	1601.2	1602.5	1602.3
162.5°	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3	1626.7	1628.2	1628.0
165°	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2	1660.5	1661.6	1661.3
167.5°	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4	1686.1	1687.9	1687.9
170°	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4	1701.2	1703.0	1702.9
172.5°	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2	1712.0	1713.8	1713.8
175°	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3	1724.1	1725.9	1725.7
177.5°	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8	1729.2	1730.6	1730.5
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	462.5	463.7	462.7	464.0	462.7	463.7	462.5	463.5	465.0	464.0	466.4
5°	426.3	424.5	425.7	424.9	425.7	424.5	426.3	427.3	429.8	430.6	432.3
7.5°	392.9	391.1	389.1	388.1	389.1	391.1	392.9	393.4	395.6	398.7	401.0
10°	371.9	369.6	369.4	368.0	369.4	369.6	371.9	374.2	375.6	379.5	382.2
12.5°	356.6	354.5	352.1	351.5	352.1	354.5	356.6	358.6	359.0	363.4	365.2
15°	334.8	333.1	331.7	333.0	331.7	333.1	334.8	336.1	338.3	341.4	343.5
17.5°	316.7	315.4	315.1	313.6	315.1	315.4	316.7	317.4	321.1	323.2	326.7
20°	305.3	304.3	304.8	302.0	304.8	304.3	305.3	307.2	310.9	311.9	315.7
22.5°	296.3	294.3	294.0	293.5	294.0	294.3	296.3	298.0	298.7	301.9	304.4
25°	282.0	281.1	280.0	281.1	280.0	281.1	282.0	283.9	284.7	287.0	289.5
27.5°	269.7	268.4	268.1	268.3	268.1	268.4	269.7	269.5	271.7	273.6	275.4
30°	262.1	260.0	260.2	260.0	260.2	260.0	262.1	262.1	263.3	265.0	266.6
32.5°	253.9	252.4	252.2	251.8	252.2	252.4	253.9	253.5	255.1	257.1	258.9
35°	241.7	241.7	240.7	240.7	240.7	241.7	241.7	242.3	244.0	244.0	246.0
37.5°	230.2	230.1	229.4	229.5	229.4	230.1	230.2	230.8	231.3	232.2	233.5
40°	221.7	221.5	220.9	219.6	220.9	221.5	221.7	222.6	222.9	224.0	224.8
42.5°	213.5	212.8	212.5	212.0	212.5	212.8	213.5	213.9	214.2	215.5	217.2
45°	200.5	200.5	200.1	199.8	200.1	200.5	200.5	200.5	200.7	202.3	203.1
47.5°	187.9	188.2	189.0	188.9	189.0	188.2	187.9	187.5	187.6	188.4	189.4
50°	180.3	180.5	181.1	181.3	181.1	180.5	180.3	179.5	179.1	179.1	179.7
52.5°	171.9	173.1	173.9	173.7	173.9	173.1	171.9	171.2	170.5	169.5	170.4
55°	160.1	161.6	163.0	163.2	163.0	161.6	160.1	158.3	157.4	155.8	156.4
57.5°	148.5	150.4	151.9	152.5	151.9	150.4	148.5	146.2	143.6	142.8	141.6
60°	140.5	143.2	145.1	145.9	145.1	143.2	140.5	138.5	134.9	132.7	131.9
62.5°	133.0	136.0	137.8	137.9	137.8	136.0	133.0	129.7	126.3	123.6	122.0
65°	120.6	123.6	125.3	126.5	125.3	123.6	120.6	117.0	113.2	109.6	107.7
67.5°	107.2	110.3	112.1	113.1	112.1	110.3	107.2	102.8	99.2	95.2	93.1
70°	97.5	100.6	103.0	103.9	103.0	100.6	97.5	92.3	89.3	85.5	83.6
72.5°	87.9	90.7	92.6	93.6	92.6	90.7	87.9	83.1	79.5	75.8	73.3
75°	71.2	75.0	76.9	77.8	76.9	75.0	71.2	68.6	64.5	60.5	58.5
77.5°	54.9	58.3	59.5	60.0	59.5	58.3	54.9	51.8	48.7	45.8	43.9
80°	44.1	46.2	47.6	47.8	47.6	46.2	44.1	41.6	39.1	36.5	34.6
82.5°	33.9	35.6	36.0	36.6	36.0	35.6	33.9	31.7	29.6	27.6	26.0
85°	18.5	19.4	19.6	19.4	19.6	19.4	18.5	17.1	16.1	15.1	14.4
87.5°	12.0	12.0	12.2	12.8	12.2	12.0	12.0	11.5	11.4	10.8	10.2
90°	29.6	30.5	31.4	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5
92.5°	61.5	62.2	62.8	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6
95°	113.9	114.5	115.0	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7
97.5°	174.3	174.7	175.0	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8
100°	218.7	219.4	220.0	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2
102.5°	263.2	264.0	264.9	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7
105°	330.8	331.7	332.6	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0
107.5°	403.1	403.1	403.0	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9
110°	455.5	455.1	454.9	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	506.8	506.2	505.7	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5
115°	585.9	585.6	585.3	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1
117.5°	666.6	665.4	664.2	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8
120°	720.4	719.2	718.0	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2
122.5°	773.5	772.5	771.5	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5
125°	852.2	851.9	851.6	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2
127.5°	930.5	930.0	929.3	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2
130°	982.2	981.6	981.0	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8
132.5°	1031.4	1030.5	1029.7	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3
135°	1107.7	1106.5	1105.3	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5
137.5°	1182.3	1180.8	1179.3	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7
140°	1229.7	1228.2	1226.6	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4
142.5°	1274.8	1273.4	1271.8	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1
145°	1340.8	1339.9	1339.0	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1
147.5°	1402.0	1400.0	1398.0	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3
150°	1440.7	1440.2	1439.6	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7
152.5°	1477.7	1476.7	1475.6	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6
155°	1529.6	1528.0	1526.5	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7
157.5°	1573.2	1571.2	1569.2	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2
160°	1600.8	1599.3	1597.9	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1
162.5°	1626.3	1624.5	1622.8	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3
165°	1659.6	1657.8	1656.0	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2
167.5°	1686.0	1684.3	1682.4	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4
170°	1700.8	1698.7	1696.6	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4
172.5°	1711.9	1710.0	1708.2	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2
175°	1723.7	1721.5	1719.5	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3
177.5°	1728.8	1727.2	1725.5	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	464.2	466.2	468.6	470.5	473.8	475.2	477.1	478.5	481.2	483.7	486.6
5°	432.9	436.4	441.1	446.3	452.3	456.4	462.2	465.7	472.7	479.0	485.3
7.5°	404.6	408.8	415.5	422.1	430.0	437.0	444.3	452.3	461.2	471.8	480.5
10°	385.1	390.8	398.1	406.4	415.8	424.0	433.7	442.4	453.3	465.7	477.2
12.5°	369.6	374.5	382.5	390.5	400.6	410.7	420.7	432.1	444.9	458.6	473.1
15°	348.2	352.3	358.9	369.9	380.1	390.0	405.1	415.8	431.9	447.1	464.7
17.5°	329.9	335.1	340.6	350.0	360.7	373.0	386.5	399.9	415.4	434.7	454.4
20°	318.8	322.9	329.2	336.4	347.8	360.2	372.9	386.6	405.5	425.5	446.7
22.5°	306.6	311.0	318.3	326.1	335.6	347.5	361.6	376.5	396.3	415.9	439.0
25°	292.2	295.2	301.8	308.9	318.3	328.4	343.0	359.5	379.2	401.6	425.1
27.5°	278.7	281.3	287.3	293.5	302.0	314.0	327.1	343.8	362.2	385.0	411.0
30°	268.9	271.8	277.1	283.7	291.9	302.5	315.8	331.5	351.3	373.5	400.7
32.5°	260.5	263.1	267.1	273.7	281.8	291.9	304.3	320.3	340.1	362.7	389.4
35°	247.4	250.3	253.4	258.6	265.6	275.4	289.1	304.2	323.1	344.9	369.4
37.5°	234.5	237.6	240.4	245.0	251.4	260.1	271.9	287.6	304.7	325.7	349.3
40°	226.4	228.9	231.2	236.1	242.5	250.7	261.7	275.7	293.8	313.4	333.0
42.5°	218.4	220.7	222.6	226.9	232.8	240.7	251.1	264.8	281.6	299.9	317.2
45°	205.6	207.1	209.4	213.0	217.8	225.0	235.1	247.3	261.4	278.7	291.8
47.5°	191.9	194.1	196.0	199.2	203.1	210.2	219.9	230.2	243.2	256.0	265.1
50°	181.3	183.6	186.3	189.4	193.1	199.7	208.5	219.0	230.0	239.9	247.6
52.5°	171.4	173.5	176.4	179.3	183.9	189.4	197.0	206.3	217.1	224.2	230.7
55°	156.8	157.8	161.1	164.0	168.4	172.5	180.1	188.3	194.9	200.3	205.6
57.5°	141.9	143.2	145.2	147.8	152.0	156.9	162.2	169.5	173.3	176.1	180.3
60°	132.2	132.7	133.9	137.1	140.4	144.6	150.8	156.0	158.9	161.1	164.6
62.5°	121.7	121.8	123.9	126.2	128.6	133.3	138.3	142.5	144.8	146.0	149.3
65°	106.9	106.6	107.7	109.6	112.5	115.6	119.9	123.6	123.4	124.7	126.7
67.5°	91.8	91.4	91.4	93.2	95.5	98.3	101.2	103.4	103.4	105.0	106.1
70°	81.6	80.3	81.1	82.7	83.6	86.0	89.3	90.1	90.2	91.0	92.1
72.5°	71.1	70.6	71.2	71.9	72.6	74.4	77.2	77.7	77.8	78.2	79.9
75°	56.4	56.1	55.6	56.3	57.1	58.3	59.3	60.2	59.9	60.2	61.4
77.5°	42.4	41.2	40.9	41.3	41.5	42.3	43.3	43.2	43.4	43.4	44.8
80°	33.6	31.9	31.7	31.7	31.9	32.4	32.7	33.2	32.5	33.2	33.6
82.5°	24.7	23.7	23.6	23.5	23.5	23.6	23.9	24.1	24.0	24.3	24.5
85°	13.6	13.2	12.6	13.0	12.8	12.1	12.6	11.9	11.8	11.9	12.1
87.5°	9.2	9.1	8.3	7.9	7.3	7.0	6.3	5.6	5.0	4.7	4.7
90°	23.0	21.5	19.4	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3
92.5°	53.6	51.6	49.0	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5
95°	105.7	103.5	100.6	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4
97.5°	166.8	164.9	160.8	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3
100°	208.5	205.7	201.9	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2
102.5°	251.7	248.8	246.8	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5
105°	323.2	321.5	319.6	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7
107.5°	400.0	399.1	397.8	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2
110°	452.7	451.8	450.9	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	506.0	505.7	504.5	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0
115°	587.4	587.7	587.1	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6
117.5°	667.5	667.4	666.7	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5
120°	722.2	722.2	721.8	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1
122.5°	775.7	776.0	775.2	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1
125°	854.7	855.3	855.1	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9
127.5°	932.5	932.8	932.5	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6
130°	984.1	984.4	983.8	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0
132.5°	1033.6	1033.9	1034.0	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4
135°	1109.5	1109.5	1109.2	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1
137.5°	1183.3	1182.9	1182.2	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2
140°	1229.8	1229.2	1228.3	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4
142.5°	1275.8	1275.4	1274.3	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7
145°	1342.1	1342.1	1341.2	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8
147.5°	1402.6	1401.9	1401.1	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7
150°	1441.7	1441.7	1440.5	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6
152.5°	1476.9	1476.1	1475.6	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0
155°	1527.6	1526.4	1526.1	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1572.0	1570.7	1570.5	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4
160°	1598.8	1597.7	1597.4	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4
162.5°	1623.9	1622.4	1622.4	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1
165°	1658.0	1656.9	1656.5	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2
167.5°	1682.6	1680.8	1680.8	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1
170°	1697.6	1695.9	1695.9	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2
172.5°	1708.4	1706.6	1706.6	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0
175°	1720.5	1718.7	1718.7	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1
177.5°	1726.4	1724.9	1725.1	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	488.1	490.4	491.9	494.6	497.0	498.3	499.4	500.4	501.6	502.6	505.4
5°	491.2	496.6	501.1	508.1	514.5	519.4	524.8	529.5	533.4	539.0	543.3
7.5°	489.8	499.4	509.3	520.2	531.3	541.5	551.1	559.9	567.9	577.7	586.2
10°	488.6	501.5	514.2	529.0	543.9	556.7	568.6	580.9	589.7	602.1	612.6
12.5°	487.6	502.8	518.3	535.8	552.3	570.4	586.3	595.2	608.7	618.6	631.1
15°	483.4	503.5	524.8	544.6	568.1	584.8	598.8	616.1	628.7	641.2	654.8
17.5°	475.9	498.8	522.5	548.5	571.0	588.9	607.0	623.7	638.6	655.5	672.4
20°	472.4	495.3	522.5	549.1	571.1	589.9	608.4	626.8	643.3	664.9	684.5
22.5°	465.2	492.8	517.9	543.9	566.5	586.9	608.0	628.7	650.7	675.1	699.6
25°	452.3	480.3	506.8	532.4	555.3	580.9	603.3	631.2	659.2	691.5	722.0
27.5°	438.8	465.7	490.0	514.7	541.4	570.3	599.4	631.0	667.7	708.6	751.5
30°	427.9	453.3	477.0	502.3	530.1	562.7	594.7	632.1	674.6	720.5	771.7
32.5°	415.3	438.6	461.6	488.5	518.8	553.1	590.4	631.5	682.5	734.7	787.3
35°	393.5	413.1	436.8	465.5	499.6	539.0	582.1	630.7	689.2	749.2	793.4
37.5°	367.8	386.0	411.0	442.4	478.2	520.5	571.6	629.3	691.4	739.2	753.5
40°	350.4	367.4	393.3	425.9	462.5	507.3	563.3	624.3	684.5	715.0	703.2
42.5°	332.0	349.7	375.1	407.2	446.7	495.4	552.9	613.9	664.4	675.9	635.3
45°	302.9	321.2	346.2	378.7	421.2	473.9	533.9	589.3	618.3	597.5	534.7
47.5°	275.8	293.0	316.1	349.7	393.5	448.1	505.8	550.0	552.3	502.7	435.5
50°	257.3	273.2	296.5	330.1	373.5	428.8	480.9	515.8	500.1	443.8	379.3
52.5°	239.2	254.8	277.7	310.9	353.9	404.6	453.1	477.5	448.0	390.2	335.2
55°	213.0	226.7	249.1	279.8	320.6	367.6	408.8	417.2	378.9	322.1	277.3
57.5°	187.5	200.2	220.6	248.9	286.2	327.8	360.1	358.2	317.7	268.9	233.4
60°	170.2	182.5	200.7	228.3	262.3	298.2	325.7	319.1	279.0	236.9	207.1
62.5°	154.7	165.8	182.9	207.1	238.1	271.3	293.9	284.2	244.9	208.1	184.5
65°	131.9	141.2	155.8	176.4	202.2	229.5	247.1	234.5	200.9	172.3	153.3
67.5°	110.0	117.5	129.7	146.2	168.2	190.2	200.8	188.2	161.3	140.4	126.4
70°	96.2	102.8	112.3	126.9	146.1	164.6	172.6	161.3	138.2	120.3	110.2
72.5°	82.4	87.8	96.1	109.3	124.7	140.7	147.8	137.0	118.0	102.8	93.5
75°	63.7	67.4	73.1	82.2	94.3	107.2	111.0	101.6	89.4	78.1	71.9
77.5°	45.6	48.7	53.1	58.8	67.4	75.5	78.9	73.5	64.1	56.9	51.8
80°	35.0	36.6	40.4	45.1	51.9	57.1	59.3	55.8	49.2	43.9	39.9
82.5°	25.0	26.7	28.8	32.7	37.1	40.6	43.0	40.7	35.9	31.7	29.4
85°	12.1	13.2	14.4	16.1	19.4	21.4	21.2	19.8	17.9	16.3	15.1
87.5°	5.0	5.7	6.7	7.9	8.9	10.0	10.7	10.8	10.6	10.3	10.2
90°	3.7	6.2	8.6	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5
92.5°	34.2	35.9	37.5	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6
95°	88.0	88.6	89.2	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7
97.5°	145.4	145.7	146.0	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8
100°	188.2	188.2	188.2	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2
102.5°	235.8	236.9	238.1	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7
105°	308.1	309.6	311.1	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0
107.5°	387.7	389.2	390.7	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9
110°	442.6	444.1	445.6	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.8	498.6	499.4	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5
115°	580.9	582.0	583.2	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1
117.5°	663.0	663.5	664.1	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8
120°	715.6	717.1	718.6	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2
122.5°	770.6	771.2	771.7	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5
125°	847.7	849.5	851.3	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2
127.5°	927.6	928.6	929.6	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2
130°	976.5	978.0	979.5	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8
132.5°	1025.9	1028.3	1030.8	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3
135°	1101.9	1103.7	1105.5	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5
137.5°	1173.9	1175.6	1177.3	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7
140°	1219.9	1221.4	1222.9	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4
142.5°	1266.0	1267.2	1268.5	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1
145°	1333.9	1335.2	1336.3	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1
147.5°	1396.3	1397.0	1397.7	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3
150°	1437.3	1437.1	1436.7	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7
152.5°	1472.5	1472.9	1473.3	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6
155°	1525.1	1525.1	1525.1	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7
157.5°	1571.7	1571.1	1570.4	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2
160°	1599.5	1598.6	1597.7	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1
162.5°	1624.4	1623.8	1623.2	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3
165°	1657.6	1657.0	1656.4	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2
167.5°	1685.0	1683.8	1682.6	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4
170°	1700.0	1698.8	1697.6	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4
172.5°	1710.8	1709.6	1708.4	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2
175°	1722.9	1721.7	1720.5	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3
177.5°	1729.3	1728.4	1727.4	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	507.7	509.0	511.8	510.9	512.1	512.8	513.4
5°	548.7	555.3	558.2	557.8	562.1	561.1	560.0
7.5°	595.0	601.9	605.8	610.6	613.4	613.7	616.1
10°	621.3	630.3	634.0	639.2	642.5	644.4	644.1
12.5°	641.3	648.5	656.7	659.2	663.7	666.1	665.2
15°	665.6	676.9	685.5	689.8	695.4	697.1	699.3
17.5°	687.2	702.3	712.4	725.9	730.9	734.1	732.2
20°	703.5	723.4	733.5	749.6	758.5	763.2	761.5
22.5°	722.7	744.4	763.0	776.9	790.4	796.8	798.2
25°	755.8	785.4	812.9	831.2	847.8	851.8	860.4
27.5°	792.7	827.7	857.0	876.3	887.9	892.2	895.0
30°	815.9	850.8	872.8	885.2	888.9	888.5	888.1
32.5°	827.3	849.1	853.4	849.9	841.4	834.2	826.7
35°	811.2	795.0	770.6	739.3	716.2	692.9	690.6
37.5°	729.6	677.5	637.0	591.8	565.8	549.7	538.5
40°	652.7	593.6	544.6	506.5	479.9	469.4	459.1
42.5°	569.4	512.8	469.4	437.6	417.6	405.9	397.8
45°	462.5	412.7	378.7	355.6	339.7	330.7	325.6
47.5°	379.1	342.1	313.3	296.6	285.7	278.7	278.7
50°	334.2	299.0	279.8	266.6	257.2	251.6	252.6
52.5°	294.4	268.1	251.8	240.8	233.7	230.3	230.2
55°	246.2	227.3	216.6	208.5	203.8	199.8	200.7
57.5°	210.6	194.7	187.4	180.7	177.5	175.9	173.6
60°	188.5	176.2	170.0	164.6	161.3	160.1	157.8
62.5°	168.9	159.2	153.2	148.8	145.9	145.4	143.7
65°	142.0	134.6	129.2	127.2	124.0	123.2	123.2
67.5°	117.0	111.7	107.5	105.7	104.3	104.5	103.5
70°	101.4	97.0	94.3	92.3	91.3	91.5	90.7
72.5°	88.7	83.8	81.5	80.3	78.9	79.5	79.1
75°	67.1	64.7	63.5	62.2	61.4	61.0	60.5
77.5°	49.3	47.2	46.2	45.5	45.7	44.6	45.4
80°	38.1	36.3	35.7	34.6	34.4	34.4	34.2
82.5°	27.9	26.8	26.4	25.6	25.1	25.5	25.0
85°	14.4	13.6	13.4	13.4	13.0	12.6	13.6
87.5°	10.4	10.1	10.3	10.3	10.5	10.5	10.4
90°	26.0	27.5	28.7	29.6	30.5	31.4	32.3
92.5°	57.5	59.6	60.8	61.5	62.2	62.8	63.5
95°	109.9	111.9	113.2	113.9	114.5	115.0	115.7
97.5°	170.8	172.7	174.0	174.3	174.7	175.0	175.4
100°	213.8	216.5	218.2	218.7	219.4	220.0	220.5
102.5°	257.6	260.5	262.4	263.2	264.0	264.9	265.7
105°	326.8	328.6	329.9	330.8	331.7	332.6	333.5
107.5°	401.8	402.7	403.1	403.1	403.1	403.0	402.9
110°	454.6	455.5	455.8	455.5	455.1	454.9	454.6



TEST NUMBER: P333365-940

CATALOG NUMBER: S125DIW-S375D1560U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	506.9	507.3	507.3	506.8	506.2	505.7	505.2
115°	586.8	586.5	586.2	585.9	585.6	585.3	585.1
117.5°	668.1	668.2	667.8	666.6	665.4	664.2	663.0
120°	722.2	722.2	721.6	720.4	719.2	718.0	716.8
122.5°	775.3	775.0	774.5	773.5	772.5	771.5	770.6
125°	853.5	852.9	852.5	852.2	851.9	851.6	851.3
127.5°	931.9	931.6	931.1	930.5	930.0	929.3	928.7
130°	983.6	983.2	982.8	982.2	981.6	981.0	980.4
132.5°	1033.0	1032.7	1032.2	1031.4	1030.5	1029.7	1028.8
135°	1109.5	1109.5	1108.9	1107.7	1106.5	1105.3	1104.1
137.5°	1184.0	1184.4	1183.8	1182.3	1180.8	1179.3	1177.8
140°	1231.0	1231.5	1231.1	1229.7	1228.2	1226.6	1225.1
142.5°	1276.5	1276.9	1276.3	1274.8	1273.4	1271.8	1270.3
145°	1342.1	1342.1	1341.7	1340.8	1339.9	1339.0	1338.1
147.5°	1404.0	1404.7	1404.1	1402.0	1400.0	1398.0	1396.0
150°	1441.7	1441.7	1441.4	1440.7	1440.2	1439.6	1439.0
152.5°	1478.3	1479.0	1478.8	1477.7	1476.7	1475.6	1474.5
155°	1530.0	1531.2	1531.1	1529.6	1528.0	1526.5	1525.1
157.5°	1574.4	1575.6	1575.2	1573.2	1571.2	1569.2	1567.3
160°	1601.2	1602.5	1602.3	1600.8	1599.3	1597.9	1596.3
162.5°	1626.7	1628.2	1628.0	1626.3	1624.5	1622.8	1621.0
165°	1660.5	1661.6	1661.3	1659.6	1657.8	1656.0	1654.1
167.5°	1686.1	1687.9	1687.9	1686.0	1684.3	1682.4	1680.5
170°	1701.2	1703.0	1702.9	1700.8	1698.7	1696.6	1694.5
172.5°	1712.0	1713.8	1713.8	1711.9	1710.0	1708.2	1706.4
175°	1724.1	1725.9	1725.7	1723.7	1721.5	1719.5	1717.3
177.5°	1729.2	1730.6	1730.5	1728.8	1727.2	1725.5	1723.9
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1

(END OF REPORT)