

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333350-940

Luminaire Tested: **S125DIW-S375D770U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333350-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D770U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4094.4 lumens
Efficiency: N/A
Efficacy: 134.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333350-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333350-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	82	85	81	78	75	65	62	60	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	45	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3364	3364	3364
5°	3371	3339	3361
10°	3351	3316	3335
15°	3315	3276	3290
20°	3263	3221	3226
25°	3207	3154	3151
30°	3138	3082	3067
35°	3064	3005	2964
40°	2989	2922	2880
45°	2906	2846	2789
50°	2816	2753	2671
55°	2728	2649	2575
60°	2623	2545	2454
65°	2500	2419	2337
70°	2381	2274	2194
75°	2168	2099	2024
80°	1930	1901	1852
85°	1675	1712	1615



TEST NUMBER: P333350-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	1.2
10°-20°	138.7	3.4
20°-30°	204.9	5.0
30°-40°	239.0	5.8
40°-50°	240.1	5.9
50°-60°	210.7	5.1
60°-70°	157.0	3.8
70°-80°	89.8	2.2
80°-90°	28.0	0.7
90°-100°	32.4	0.8
100°-110°	199.6	4.9
110°-120°	362.0	8.8
120°-130°	464.6	11.3
130°-140°	499.8	12.2
140°-150°	469.1	11.5
150°-160°	379.5	9.3
160°-170°	245.4	6.0
170°-180°	84.6	2.1
0°-30°	392.7	9.6
0°-40°	631.7	15.4
0°-60°	1082.6	26.4
0°-90°	1357.3	33.2
90°-120°	594.1	14.5
90°-150°	2027.6	49.5
90°-180°	2737.0	66.8
0°-180°	4094.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	521	521	521	521	521	
5°	520	519	515	519	518	49
15°	496	494	490	492	492	140
25°	450	448	443	443	442	207
35°	389	387	381	379	376	243
45°	318	316	312	307	305	245
55°	242	241	235	232	229	216
65°	164	163	158	155	153	162
75°	87	86	84	83	81	93
85°	23	23	23	23	22	25
90°	1	6	11	14	16	3
95°	38	34	11	14	14	48
105°	194	197	197	197	196	206
115°	365	368	369	366	362	361
125°	519	523	523	521	519	463
135°	647	651	650	648	644	498
145°	750	751	751	752	748	469
155°	826	822	823	825	820	380
165°	872	868	868	872	867	246
175°	891	888	888	893	887	85
180°	891	891	891	891	891	



TEST NUMBER: P333350-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	522.2	522.0	521.8	521.6	521.4	520.8	520.1	519.4	518.7	517.9	518.7
5°	520.0	519.9	519.7	519.5	519.3	518.8	517.9	517.0	516.0	515.1	515.9
7.5°	515.3	515.1	515.0	514.8	514.6	514.0	513.0	511.9	511.0	510.0	510.8
10°	511.0	510.9	510.7	510.5	510.3	509.7	508.7	507.7	506.7	505.7	506.4
12.5°	505.8	505.4	505.1	504.8	504.4	503.8	502.8	501.9	501.0	500.1	500.6
15°	495.8	495.5	495.3	495.0	494.6	494.0	493.0	492.0	491.0	490.0	490.4
17.5°	484.3	483.9	483.5	483.1	482.7	482.0	480.9	479.9	478.8	477.8	478.4
20°	474.7	474.6	474.4	474.2	474.0	473.3	472.2	470.9	469.8	468.6	469.2
22.5°	465.2	464.8	464.5	464.2	463.9	463.2	462.0	460.9	459.8	458.7	459.1
25°	450.0	449.6	449.1	448.6	448.2	447.4	446.2	445.0	443.8	442.6	442.8
27.5°	432.3	432.0	431.8	431.5	431.2	430.4	429.3	428.0	426.8	425.5	425.6
30°	420.8	420.5	420.2	419.9	419.6	418.8	417.5	416.1	414.7	413.3	413.1
32.5°	408.2	407.8	407.4	407.0	406.5	405.7	404.5	403.2	402.1	400.8	400.5
35°	388.6	388.3	387.9	387.5	387.2	386.3	385.0	383.8	382.5	381.2	380.8
37.5°	368.3	367.8	367.4	366.8	366.4	365.6	364.4	363.2	361.9	360.8	360.1
40°	354.5	353.9	353.5	353.0	352.6	351.7	350.4	349.2	347.9	346.6	345.8
42.5°	339.6	339.2	338.9	338.4	338.0	337.2	335.9	334.7	333.3	332.1	331.4
45°	318.2	317.8	317.4	317.1	316.6	315.9	314.9	313.8	312.6	311.6	310.5
47.5°	295.1	295.1	295.1	295.2	295.2	294.5	293.2	291.9	290.5	289.2	288.1
50°	280.3	280.0	279.7	279.4	279.1	278.5	277.3	276.3	275.2	274.0	272.9
52.5°	265.1	264.8	264.7	264.5	264.3	263.6	262.4	261.3	260.0	258.9	257.9
55°	242.3	242.0	241.7	241.5	241.2	240.4	239.2	237.9	236.6	235.3	234.5
57.5°	218.4	218.2	218.0	217.9	217.8	217.1	216.1	215.0	213.9	212.9	211.8
60°	203.1	202.8	202.4	202.1	201.7	201.0	200.0	199.0	198.0	197.0	196.1
62.5°	187.3	187.1	186.7	186.5	186.2	185.6	184.8	183.9	183.0	182.2	181.2
65°	163.6	163.5	163.3	163.1	162.9	162.3	161.3	160.2	159.3	158.3	157.4
67.5°	140.6	140.3	139.8	139.5	139.1	138.5	137.8	137.0	136.3	135.5	134.8
70°	126.1	125.6	125.2	124.8	124.3	123.6	122.8	122.0	121.2	120.4	119.8
72.5°	110.3	109.9	109.7	109.3	109.1	108.6	108.1	107.5	107.0	106.5	105.8
75°	86.9	86.8	86.6	86.4	86.2	85.9	85.4	85.0	84.5	84.1	83.8
77.5°	65.5	65.4	65.3	65.2	65.2	65.0	64.7	64.5	64.2	63.9	63.8
80°	51.9	51.9	51.9	51.9	51.9	51.8	51.6	51.5	51.3	51.1	51.0
82.5°	40.0	39.9	39.8	39.6	39.5	39.4	39.3	39.3	39.2	39.2	39.1
85°	22.6	22.7	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.1	23.0
87.5°	9.0	9.3	9.5	9.7	10.0	10.2	10.3	10.4	10.5	10.7	10.8
90°	0.6	1.9	3.0	4.2	5.4	6.4	7.5	8.6	9.5	10.6	11.3
92.5°	10.2	9.4	8.6	7.7	6.9	7.0	7.8	8.7	9.6	10.6	11.3
95°	37.6	37.2	36.7	36.4	35.9	32.9	27.3	21.8	16.1	10.6	11.3
97.5°	78.6	79.5	80.3	81.0	81.8	76.7	65.6	54.6	43.5	32.5	28.4
100°	110.3	110.8	111.2	111.6	112.1	112.6	113.2	113.8	114.4	114.9	93.1
102.5°	142.6	143.1	143.7	144.3	144.8	145.3	145.6	146.0	146.3	146.7	142.6
105°	194.2	194.8	195.5	196.0	196.6	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.9	247.9	247.9	247.9	247.9	248.1	248.3	248.6	249.0	249.2	249.2
110°	282.8	282.8	282.8	282.8	282.8	282.9	283.2	283.6	283.8	284.1	283.7



TEST NUMBER: P333350-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.6	315.9	316.3	316.6	317.0	317.3	317.4	317.6	317.8	318.0	317.4
115°	364.7	365.4	366.2	366.9	367.7	368.1	368.3	368.4	368.5	368.7	368.1
117.5°	415.6	415.5	415.5	415.5	415.4	415.7	416.3	416.9	417.4	417.9	417.2
120°	447.3	447.2	447.0	446.8	446.7	446.8	447.3	447.7	448.2	448.6	448.4
122.5°	475.3	475.9	476.4	477.0	477.6	478.0	478.1	478.3	478.6	478.8	478.5
125°	518.7	519.7	520.8	521.7	522.8	523.3	523.3	523.3	523.3	523.3	522.7
127.5°	560.0	560.8	561.5	562.2	562.9	563.3	563.2	563.1	563.0	562.9	562.6
130°	585.4	586.1	586.8	587.6	588.4	588.8	588.9	589.1	589.2	589.3	588.9
132.5°	610.7	611.6	612.5	613.3	614.2	614.5	614.1	613.8	613.5	613.1	613.1
135°	646.8	647.7	648.6	649.5	650.4	650.7	650.4	650.1	649.8	649.5	649.2
137.5°	680.0	680.8	681.5	682.3	683.1	683.3	683.1	682.8	682.5	682.2	682.3
140°	701.7	702.0	702.3	702.6	702.8	702.9	702.8	702.7	702.5	702.3	702.7
142.5°	721.2	721.4	721.6	721.8	721.9	722.1	722.4	722.6	722.7	723.0	723.0
145°	749.9	750.2	750.6	750.8	751.1	751.3	751.3	751.3	751.3	751.3	751.4
147.5°	775.1	775.0	774.9	774.9	774.8	774.9	775.1	775.2	775.3	775.5	775.7
150°	790.9	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	791.2
152.5°	806.2	805.6	804.9	804.3	803.6	803.4	803.8	804.1	804.3	804.6	804.9
155°	825.9	825.0	824.1	823.2	822.4	822.1	822.4	822.7	823.0	823.2	823.7
157.5°	841.1	840.6	840.1	839.5	839.0	838.7	838.7	838.8	838.8	838.8	839.4
160°	851.7	850.8	849.9	849.0	848.2	847.7	847.9	848.1	848.2	848.4	849.0
162.5°	860.1	859.3	858.4	857.5	856.6	856.2	856.4	856.6	856.7	856.8	857.6
165°	871.5	870.6	869.8	868.9	868.0	867.6	867.7	867.9	868.1	868.2	869.1
167.5°	879.9	879.0	878.2	877.3	876.3	875.9	876.1	876.2	876.4	876.6	877.5
170°	884.8	883.7	882.6	881.6	880.6	880.1	880.3	880.5	880.6	880.7	881.9
172.5°	887.9	886.9	885.8	884.8	883.8	883.4	883.7	884.0	884.2	884.5	885.5
175°	891.4	890.5	889.6	888.7	887.8	887.4	887.6	887.7	887.9	888.1	889.2
177.5°	892.9	892.2	891.5	890.8	890.1	889.7	889.9	890.0	890.1	890.3	891.1
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333350-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	519.4	520.1	520.8	521.2	521.1	521.0	521.0	520.9
5°	516.7	517.6	518.4	518.8	518.7	518.6	518.5	518.4
7.5°	511.6	512.4	513.2	513.5	513.4	513.4	513.3	513.2
10°	507.1	507.8	508.6	508.9	508.8	508.7	508.6	508.5
12.5°	501.2	501.9	502.4	502.7	502.7	502.7	502.7	502.6
15°	490.9	491.3	491.9	492.0	492.0	492.0	492.0	492.0
17.5°	478.9	479.5	480.1	480.1	479.7	479.2	478.8	478.3
20°	469.8	470.5	471.1	471.3	470.7	470.3	469.8	469.4
22.5°	459.5	459.9	460.4	460.4	460.1	459.8	459.5	459.1
25°	443.0	443.2	443.4	443.3	443.0	442.7	442.5	442.2
27.5°	425.6	425.6	425.7	425.6	425.3	425.0	424.7	424.5
30°	413.0	412.8	412.6	412.4	412.1	411.9	411.5	411.3
32.5°	400.2	399.8	399.5	399.1	398.6	398.1	397.6	397.1
35°	380.3	379.9	379.3	378.8	378.1	377.3	376.6	375.9
37.5°	359.4	358.7	358.0	357.5	357.0	356.7	356.2	355.8
40°	344.9	344.1	343.3	342.8	342.5	342.1	341.9	341.6
42.5°	330.6	329.8	329.0	328.5	328.1	327.6	327.3	326.8
45°	309.3	308.3	307.2	306.5	306.2	305.9	305.7	305.4
47.5°	287.0	285.9	284.7	283.8	283.2	282.6	282.0	281.3
50°	271.7	270.5	269.3	268.4	267.7	267.1	266.4	265.8
52.5°	256.8	255.7	254.7	253.9	253.2	252.4	251.7	251.0
55°	233.6	232.8	232.0	231.3	230.7	230.0	229.3	228.7
57.5°	210.7	209.6	208.6	207.9	207.5	207.1	206.8	206.4
60°	195.2	194.2	193.3	192.5	191.9	191.3	190.6	190.0
62.5°	180.2	179.1	178.2	177.5	177.0	176.5	175.9	175.5
65°	156.6	155.8	155.0	154.4	154.0	153.6	153.3	152.9
67.5°	134.1	133.4	132.7	132.2	132.1	131.8	131.6	131.3
70°	119.2	118.7	118.2	117.7	117.3	117.0	116.5	116.2
72.5°	105.2	104.6	104.0	103.5	103.2	102.8	102.4	102.0
75°	83.6	83.3	82.9	82.7	82.3	81.9	81.6	81.1
77.5°	63.7	63.5	63.3	63.1	62.9	62.6	62.3	62.1
80°	50.9	50.8	50.7	50.6	50.4	50.2	50.0	49.8
82.5°	38.9	38.7	38.6	38.4	38.4	38.4	38.3	38.3
85°	22.9	22.8	22.7	22.6	22.4	22.2	22.0	21.8
87.5°	11.0	11.1	11.2	11.3	11.2	11.2	11.1	11.1
90°	12.0	12.8	13.5	14.1	14.5	15.0	15.4	15.9
92.5°	12.0	12.8	13.5	14.0	14.2	14.4	14.6	14.8
95°	12.0	12.8	13.5	13.9	13.9	13.9	13.9	13.9
97.5°	24.3	20.1	16.0	13.9	13.9	13.9	13.9	13.9
100°	71.2	49.3	27.5	16.2	15.6	15.1	14.4	13.9
102.5°	138.4	134.3	130.1	123.1	113.1	103.1	93.1	83.1
105°	196.9	196.9	196.9	196.8	196.7	196.5	196.4	196.3
107.5°	249.3	249.3	249.3	249.1	248.7	248.3	247.8	247.4
110°	283.2	282.8	282.3	282.2	282.3	282.5	282.7	282.8



TEST NUMBER: P333350-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.8	316.3	315.7	315.3	315.1	315.0	314.7	314.5
115°	367.5	366.9	366.3	365.6	364.7	363.8	362.9	362.0
117.5°	416.4	415.7	414.9	414.4	413.9	413.6	413.2	412.9
120°	448.1	447.7	447.5	446.9	446.2	445.5	444.8	444.0
122.5°	478.1	477.9	477.6	477.0	476.2	475.3	474.5	473.6
125°	522.1	521.6	520.9	520.4	520.0	519.5	519.2	518.7
127.5°	562.3	562.0	561.7	561.0	559.8	558.7	557.7	556.6
130°	588.5	588.1	587.6	587.0	586.3	585.6	584.8	584.1
132.5°	613.0	612.9	612.8	612.4	611.6	610.9	610.2	609.5
135°	648.9	648.6	648.4	647.7	646.8	646.0	645.1	644.2
137.5°	682.4	682.4	682.5	682.2	681.4	680.6	679.8	679.1
140°	702.9	703.2	703.6	703.2	702.3	701.5	700.6	699.7
142.5°	723.1	723.2	723.2	722.8	721.9	721.0	720.1	719.3
145°	751.5	751.7	751.8	751.4	750.6	749.7	748.9	748.0
147.5°	775.9	776.1	776.2	775.8	774.8	773.7	772.7	771.6
150°	791.5	791.8	792.1	791.7	790.4	789.3	788.1	786.9
152.5°	805.2	805.5	805.8	805.4	804.3	803.3	802.3	801.2
155°	824.1	824.6	825.0	824.7	823.5	822.3	821.2	819.9
157.5°	839.8	840.3	840.7	840.3	839.2	838.0	836.9	835.7
160°	849.5	850.2	850.7	850.4	849.3	848.1	846.9	845.7
162.5°	858.4	859.3	860.1	859.9	858.6	857.3	856.0	854.7
165°	870.0	870.8	871.7	871.6	870.4	869.2	868.1	866.8
167.5°	878.6	879.7	880.7	880.7	879.3	878.0	876.6	875.3
170°	883.1	884.3	885.5	885.4	884.0	882.7	881.4	880.1
172.5°	886.5	887.6	888.7	888.5	887.3	885.9	884.6	883.2
175°	890.4	891.5	892.7	892.6	891.4	890.0	888.7	887.3
177.5°	891.9	892.7	893.6	893.5	892.5	891.6	890.6	889.7
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4

(END OF REPORT)