

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333351-940

Luminaire Tested: **S125DIW-S375D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333351-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D770U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3730.9 lumens  
Efficiency: N/A  
Efficacy: 122.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333351-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333351-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	22
4	72	61	53	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20	16
6	61	49	41	35	55	44	38	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3364	3364	3364
5°	3371	3339	3361
10°	3351	3316	3335
15°	3315	3276	3290
20°	3263	3221	3226
25°	3207	3154	3151
30°	3138	3082	3067
35°	3064	3005	2964
40°	2989	2922	2880
45°	2906	2846	2789
50°	2816	2753	2671
55°	2728	2649	2575
60°	2623	2545	2454
65°	2500	2419	2337
70°	2381	2274	2194
75°	2168	2099	2024
80°	1930	1901	1852
85°	1675	1712	1615



TEST NUMBER: P333351-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.1	1.3
10°-20°	138.7	3.7
20°-30°	204.9	5.5
30°-40°	239.0	6.4
40°-50°	240.1	6.4
50°-60°	210.7	5.6
60°-70°	157.0	4.2
70°-80°	89.8	2.4
80°-90°	28.0	0.7
90°-100°	57.0	1.5
100°-110°	168.2	4.5
110°-120°	285.0	7.6
120°-130°	375.0	10.1
130°-140°	420.2	11.3
140°-150°	411.8	11.0
150°-160°	345.9	9.3
160°-170°	229.9	6.2
170°-180°	80.5	2.2
0°-30°	392.7	10.5
0°-40°	631.7	16.9
0°-60°	1082.6	29.0
0°-90°	1357.4	36.4
90°-120°	510.2	13.7
90°-150°	1717.2	46.0
90°-180°	2374.0	63.6
0°-180°	3730.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	521	521	521	521	521	
5°	520	519	515	519	518	49
15°	496	494	490	492	492	140
25°	450	448	443	443	442	207
35°	389	387	381	379	376	243
45°	318	316	312	307	305	245
55°	242	241	235	232	229	216
65°	164	163	158	155	153	162
75°	87	86	84	83	81	93
85°	23	23	23	23	22	25
90°	1	6	11	14	16	4
95°	43	45	51	55	57	46
105°	151	154	158	162	164	161
115°	285	288	289	289	288	282
125°	416	420	421	420	419	373
135°	541	545	546	546	544	417
145°	656	659	661	661	659	410
155°	751	751	751	754	751	346
165°	816	815	816	818	814	230
175°	849	846	846	849	845	81
180°	851	851	851	851	851	



TEST NUMBER: P333351-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	522.2	522.0	521.8	521.6	521.4	520.8	520.1	519.4	518.7	517.9	518.7
5°	520.0	519.9	519.7	519.5	519.3	518.8	517.9	517.0	516.0	515.1	515.9
7.5°	515.3	515.1	515.0	514.8	514.6	514.0	513.0	511.9	511.0	510.0	510.8
10°	511.0	510.9	510.7	510.5	510.3	509.7	508.7	507.7	506.7	505.7	506.4
12.5°	505.8	505.4	505.1	504.8	504.4	503.8	502.8	501.9	501.0	500.1	500.6
15°	495.8	495.5	495.3	495.0	494.6	494.0	493.0	492.0	491.0	490.0	490.4
17.5°	484.3	483.9	483.5	483.1	482.7	482.0	480.9	479.9	478.8	477.8	478.4
20°	474.7	474.6	474.4	474.2	474.0	473.3	472.2	470.9	469.8	468.6	469.2
22.5°	465.2	464.8	464.5	464.2	463.9	463.2	462.0	460.9	459.8	458.7	459.1
25°	450.0	449.6	449.1	448.6	448.2	447.4	446.2	445.0	443.8	442.6	442.8
27.5°	432.3	432.0	431.8	431.5	431.2	430.4	429.3	428.0	426.8	425.5	425.6
30°	420.8	420.5	420.2	419.9	419.6	418.8	417.5	416.1	414.7	413.3	413.1
32.5°	408.2	407.8	407.4	407.0	406.5	405.7	404.5	403.2	402.1	400.8	400.5
35°	388.6	388.3	387.9	387.5	387.2	386.3	385.0	383.8	382.5	381.2	380.8
37.5°	368.3	367.8	367.4	366.8	366.4	365.6	364.4	363.2	361.9	360.8	360.1
40°	354.5	353.9	353.5	353.0	352.6	351.7	350.4	349.2	347.9	346.6	345.8
42.5°	339.6	339.2	338.9	338.4	338.0	337.2	335.9	334.7	333.3	332.1	331.4
45°	318.2	317.8	317.4	317.1	316.6	315.9	314.9	313.8	312.6	311.6	310.5
47.5°	295.1	295.1	295.1	295.2	295.2	294.5	293.2	291.9	290.5	289.2	288.1
50°	280.3	280.0	279.7	279.4	279.1	278.5	277.3	276.3	275.2	274.0	272.9
52.5°	265.1	264.8	264.7	264.5	264.3	263.6	262.4	261.3	260.0	258.9	257.9
55°	242.3	242.0	241.7	241.5	241.2	240.4	239.2	237.9	236.6	235.3	234.5
57.5°	218.4	218.2	218.0	217.9	217.8	217.1	216.1	215.0	213.9	212.9	211.8
60°	203.1	202.8	202.4	202.1	201.7	201.0	200.0	199.0	198.0	197.0	196.1
62.5°	187.3	187.1	186.7	186.5	186.2	185.6	184.8	183.9	183.0	182.2	181.2
65°	163.6	163.5	163.3	163.1	162.9	162.3	161.3	160.2	159.3	158.3	157.4
67.5°	140.6	140.3	139.8	139.5	139.1	138.5	137.8	137.0	136.3	135.5	134.8
70°	126.1	125.6	125.2	124.8	124.3	123.6	122.8	122.0	121.2	120.4	119.8
72.5°	110.3	109.9	109.7	109.3	109.1	108.6	108.1	107.5	107.0	106.5	105.8
75°	86.9	86.8	86.6	86.4	86.2	85.9	85.4	85.0	84.5	84.1	83.8
77.5°	65.5	65.4	65.3	65.2	65.2	65.0	64.7	64.5	64.2	63.9	63.8
80°	51.9	51.9	51.9	51.9	51.9	51.8	51.6	51.5	51.3	51.1	51.0
82.5°	40.0	39.9	39.8	39.6	39.5	39.4	39.3	39.3	39.2	39.2	39.1
85°	22.6	22.7	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.1	23.0
87.5°	9.0	9.3	9.5	9.7	10.0	10.2	10.3	10.4	10.5	10.7	10.9
90°	0.6	1.9	3.0	4.2	5.4	6.5	7.5	8.6	9.5	10.6	11.3
92.5°	16.1	16.9	17.7	18.5	19.4	20.3	21.7	22.9	24.2	25.4	26.4
95°	43.1	43.3	43.6	43.9	44.2	45.1	46.5	48.1	49.5	51.0	52.0
97.5°	71.5	71.6	71.7	71.9	72.0	73.0	75.1	77.1	79.1	81.1	82.1
100°	92.6	92.6	92.6	92.6	92.6	93.6	95.5	97.5	99.3	101.3	102.6
102.5°	115.5	116.0	116.6	117.2	117.8	118.6	119.6	120.6	121.5	122.4	123.9
105°	151.0	151.7	152.4	153.1	153.9	154.7	155.6	156.4	157.3	158.2	159.1
107.5°	190.1	190.8	191.6	192.3	193.1	193.8	194.5	195.1	195.8	196.4	196.9
110°	217.1	217.8	218.6	219.4	220.1	220.6	221.1	221.5	221.9	222.4	222.8



TEST NUMBER: P333351-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	244.7	245.0	245.4	245.8	246.2	246.6	247.2	247.8	248.3	248.9	249.1
115°	285.3	285.9	286.5	287.0	287.7	288.1	288.4	288.6	289.0	289.3	289.1
117.5°	326.1	326.4	326.6	326.9	327.2	327.4	327.7	328.0	328.2	328.5	328.6
120°	351.5	352.2	352.9	353.7	354.5	354.9	355.0	355.2	355.3	355.4	355.4
122.5°	379.1	379.3	379.6	379.9	380.1	380.4	380.8	381.2	381.6	381.9	381.8
125°	416.3	417.2	418.1	419.0	419.9	420.4	420.5	420.7	420.9	421.0	420.7
127.5°	456.1	456.6	457.1	457.6	458.1	458.4	458.6	458.8	459.0	459.1	459.0
130°	479.9	480.6	481.4	482.1	482.9	483.4	483.7	483.9	484.3	484.6	484.4
132.5°	503.7	505.0	506.1	507.4	508.5	509.2	509.1	509.0	509.0	508.9	508.8
135°	541.4	542.3	543.2	544.1	545.0	545.5	545.6	545.8	546.0	546.1	546.1
137.5°	576.9	577.8	578.6	579.5	580.4	580.9	581.3	581.6	581.9	582.3	582.5
140°	599.8	600.5	601.2	601.9	602.7	603.2	603.7	604.1	604.6	605.0	605.3
142.5°	622.5	623.1	623.8	624.4	625.0	625.5	626.2	626.7	627.2	627.8	627.9
145°	656.0	656.6	657.2	657.7	658.4	658.9	659.3	659.8	660.2	660.7	660.7
147.5°	687.0	687.3	687.6	688.0	688.3	688.6	688.9	689.3	689.6	690.0	690.4
150°	707.7	707.5	707.3	707.2	707.0	707.3	707.8	708.5	709.0	709.6	709.6
152.5°	724.6	724.8	725.0	725.2	725.4	725.6	725.9	726.1	726.3	726.6	726.9
155°	750.6	750.6	750.6	750.6	750.6	750.7	750.9	751.0	751.2	751.4	751.9
157.5°	774.0	773.6	773.3	773.0	772.7	772.6	772.8	772.8	773.0	773.2	773.7
160°	787.7	787.3	786.8	786.4	786.0	785.8	786.0	786.1	786.2	786.4	787.0
162.5°	800.0	799.6	799.2	799.0	798.6	798.4	798.5	798.5	798.5	798.6	799.3
165°	816.2	815.9	815.6	815.3	815.0	814.9	815.1	815.2	815.4	815.6	816.1
167.5°	830.0	829.4	828.8	828.2	827.6	827.3	827.3	827.3	827.3	827.3	828.2
170°	837.4	836.8	836.2	835.6	835.0	834.7	834.7	834.7	834.7	834.7	835.6
172.5°	842.7	842.0	841.5	840.9	840.3	840.0	840.0	840.0	840.0	840.0	840.9
175°	848.6	848.0	847.5	846.9	846.2	846.0	846.0	846.0	846.0	846.0	846.9
177.5°	851.7	851.2	850.7	850.2	849.8	849.5	849.4	849.3	849.2	849.0	849.7
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333351-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	519.4	520.1	520.8	521.2	521.1	521.0	521.0	520.9
5°	516.7	517.6	518.4	518.8	518.7	518.6	518.5	518.4
7.5°	511.6	512.4	513.2	513.5	513.4	513.4	513.3	513.2
10°	507.1	507.8	508.6	508.9	508.8	508.7	508.6	508.5
12.5°	501.2	501.9	502.4	502.7	502.7	502.7	502.7	502.6
15°	490.9	491.3	491.9	492.0	492.0	492.0	492.0	492.0
17.5°	478.9	479.5	480.1	480.1	479.7	479.2	478.8	478.3
20°	469.8	470.5	471.1	471.3	470.7	470.3	469.8	469.4
22.5°	459.5	459.9	460.4	460.4	460.1	459.8	459.5	459.1
25°	443.0	443.2	443.4	443.3	443.0	442.7	442.5	442.2
27.5°	425.6	425.6	425.7	425.6	425.3	425.0	424.7	424.5
30°	413.0	412.8	412.6	412.4	412.1	411.9	411.5	411.3
32.5°	400.2	399.8	399.5	399.1	398.6	398.1	397.6	397.1
35°	380.3	379.9	379.3	378.8	378.1	377.3	376.6	375.9
37.5°	359.4	358.7	358.0	357.5	357.0	356.7	356.2	355.8
40°	344.9	344.1	343.3	342.8	342.5	342.1	341.9	341.6
42.5°	330.6	329.8	329.0	328.5	328.1	327.6	327.3	326.8
45°	309.3	308.3	307.2	306.5	306.2	305.9	305.7	305.4
47.5°	287.0	285.9	284.7	283.8	283.2	282.6	282.0	281.3
50°	271.7	270.5	269.3	268.4	267.7	267.1	266.4	265.8
52.5°	256.8	255.7	254.7	253.9	253.2	252.4	251.7	251.0
55°	233.6	232.8	232.0	231.3	230.7	230.0	229.3	228.7
57.5°	210.7	209.6	208.6	207.9	207.5	207.1	206.8	206.4
60°	195.2	194.2	193.3	192.5	191.9	191.3	190.6	190.0
62.5°	180.2	179.1	178.2	177.5	177.0	176.5	175.9	175.5
65°	156.6	155.8	155.0	154.4	154.0	153.6	153.3	152.9
67.5°	134.1	133.4	132.7	132.2	132.1	131.8	131.6	131.3
70°	119.2	118.7	118.2	117.7	117.3	117.0	116.5	116.2
72.5°	105.2	104.6	104.0	103.5	103.2	102.8	102.4	102.0
75°	83.6	83.3	82.9	82.7	82.3	81.9	81.6	81.1
77.5°	63.7	63.5	63.3	63.1	62.9	62.6	62.3	62.1
80°	50.9	50.8	50.7	50.6	50.4	50.2	50.0	49.8
82.5°	38.9	38.7	38.6	38.4	38.4	38.4	38.3	38.3
85°	22.9	22.8	22.7	22.6	22.4	22.2	22.0	21.8
87.5°	11.0	11.1	11.2	11.3	11.2	11.2	11.1	11.1
90°	12.0	12.8	13.6	14.1	14.5	15.0	15.4	15.9
92.5°	27.4	28.4	29.3	30.0	30.3	30.6	30.9	31.2
95°	53.1	54.0	55.1	55.7	56.1	56.4	56.6	56.9
97.5°	83.1	84.1	85.1	85.6	85.8	86.0	86.1	86.3
100°	103.9	105.2	106.6	107.4	107.7	108.0	108.3	108.5
102.5°	125.4	126.8	128.2	129.1	129.6	130.0	130.4	130.8
105°	160.0	160.9	161.8	162.4	162.8	163.3	163.7	164.2
107.5°	197.3	197.8	198.2	198.4	198.4	198.4	198.3	198.3
110°	223.3	223.7	224.2	224.4	224.2	224.0	223.9	223.7





TEST NUMBER: P333351-940

CATALOG NUMBER: S125DIW-S375D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.3	249.5	249.7	249.7	249.4	249.1	248.9	248.6
115°	289.0	288.8	288.6	288.6	288.4	288.3	288.1	287.9
117.5°	328.7	328.8	329.0	328.7	328.1	327.5	326.9	326.4
120°	355.4	355.4	355.4	355.2	354.6	354.0	353.4	352.8
122.5°	381.7	381.6	381.5	381.2	380.7	380.2	379.8	379.3
125°	420.4	420.1	419.8	419.6	419.5	419.3	419.2	419.0
127.5°	458.9	458.7	458.5	458.3	458.1	457.7	457.4	457.2
130°	484.3	484.1	483.9	483.8	483.5	483.1	482.9	482.6
132.5°	508.6	508.5	508.4	508.0	507.7	507.2	506.8	506.4
135°	546.1	546.1	546.1	545.8	545.2	544.7	544.0	543.5
137.5°	582.6	582.8	583.0	582.6	581.9	581.2	580.5	579.7
140°	605.6	605.9	606.2	606.0	605.3	604.5	603.8	603.1
142.5°	628.1	628.3	628.5	628.2	627.5	626.8	626.0	625.3
145°	660.7	660.7	660.7	660.4	660.0	659.5	659.1	658.6
147.5°	690.7	691.1	691.4	691.1	690.1	689.1	688.1	687.2
150°	709.6	709.6	709.6	709.4	709.2	708.9	708.6	708.3
152.5°	727.3	727.6	728.0	727.9	727.4	726.8	726.3	725.8
155°	752.5	753.0	753.7	753.6	752.9	752.2	751.4	750.6
157.5°	774.4	774.9	775.5	775.3	774.4	773.4	772.4	771.4
160°	787.6	788.2	788.7	788.7	787.9	787.2	786.5	785.8
162.5°	800.0	800.7	801.4	801.4	800.5	799.6	798.8	797.9
165°	816.7	817.3	817.9	817.7	816.9	816.0	815.1	814.2
167.5°	829.1	830.0	830.8	830.8	829.9	829.0	828.1	827.2
170°	836.5	837.4	838.3	838.2	837.1	836.2	835.1	834.1
172.5°	841.8	842.7	843.6	843.6	842.7	841.7	840.8	839.9
175°	847.7	848.6	849.5	849.4	848.4	847.4	846.3	845.3
177.5°	850.4	851.1	851.9	851.8	851.0	850.2	849.4	848.5
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6

(END OF REPORT)