

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P436709

Luminaire Tested: **LSSQ1B08509030D010TExxSL**

Issue Date: 12/2/2020

Test Information

Test Method: LM-41-14
Report Number: P436709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-014-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 12/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSSQ1B08509030D010TExxSL
Description: PORTFOLIO 1INCH CYLINDER, 50 DEG REFLECTOR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 926.5 lumens
Efficiency: N/A
Efficacy: 56.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.9
Luminous Opening: Rectangular (W 0.08' x L: 0.08' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P436709

CATALOG NUMBER: LSSQ1B08509030D010TExxSL

Luminous Intensity Polar Plot





TEST NUMBER: P436709

CATALOG NUMBER: LSSQ1B08509030D010TExxSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66	66	66	66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54	54	54	54
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1341857
5°	1353256
10°	1402380
15°	1449367
20°	1419660
25°	1074917
30°	758303
35°	560023
40°	332262
45°	126615
50°	78271
55°	82268
60°	84999
65°	89101
70°	87256
75°	85121
80°	81881
85°	71710



TEST NUMBER: P436709

CATALOG NUMBER: LSSQ1B08509030D010TExxSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	9.0
10°-20°	251.0	27.1
20°-30°	285.6	30.8
30°-40°	180.0	19.4
40°-50°	56.6	6.1
50°-60°	26.9	2.9
60°-70°	23.4	2.5
70°-80°	15.1	1.6
80°-90°	4.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.8	66.9
0°-40°	799.7	86.3
0°-60°	883.3	95.3
0°-90°	926.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	926.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	859	
5°	863	83
15°	896	251
25°	624	286
35°	294	180
45°	57	57
55°	30	27
65°	24	23
75°	14	15
85°	4	5
90°	0	



TEST NUMBER: P436709

CATALOG NUMBER: LSSQ1B08509030D010TExxSL

CANDELA DISTRIBUTION (FULL):

	0°
0°	858.8
1°	855.8
2°	853.8
3°	855.8
4°	858.8
5°	862.8
6°	868.8
7°	873.9
8°	877.9
9°	880.9
10°	883.9
11°	887.9
12°	891.0
13°	894.0
14°	896.0
15°	896.0
16°	894.0
17°	888.9
18°	880.9
19°	868.8
20°	853.8
21°	831.6
22°	795.4
23°	744.1
24°	684.8
25°	623.5
26°	565.1
27°	515.9
28°	477.7
29°	446.5
30°	420.3
32.5°	359.0
35°	293.6
37.5°	222.2
40°	162.9
42.5°	107.6
45°	57.3
47.5°	37.2
50°	32.2
52.5°	31.2
55°	30.2
57.5°	29.2
60°	27.2



TEST NUMBER: P436709

CATALOG NUMBER: LSSQ1B08509030D010TExxSL

CANDELA DISTRIBUTION (continued):

	0°
67.5°	21.1
70°	19.1
72.5°	17.1
75°	14.1
77.5°	12.1
80°	9.1
82.5°	7.0
85°	4.0
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







62.5°		26.1
65°		24.1



(END OF REPORT)