

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333387-940

Luminaire Tested: **S125DIW-S610D1050U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333387-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1050U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5470.8 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333387-940

CATALOG NUMBER: S125DIW-S610D1050U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333387-940

CATALOG NUMBER: S125DIW-S610D1050U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	43	38	42	37	33	34	30	27	26	24	21	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333387-940

CATALOG NUMBER: S125DIW-S610D1050U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.5
10°-20°	228.1	4.2
20°-30°	336.8	6.2
30°-40°	393.0	7.2
40°-50°	394.7	7.2
50°-60°	346.5	6.3
60°-70°	258.2	4.7
70°-80°	147.6	2.7
80°-90°	45.5	0.8
90°-100°	77.8	1.4
100°-110°	229.6	4.2
110°-120°	388.9	7.1
120°-130°	511.9	9.4
130°-140°	573.6	10.5
140°-150°	562.1	10.3
150°-160°	472.2	8.6
160°-170°	313.9	5.7
170°-180°	109.8	2.0
0°-30°	645.6	11.8
0°-40°	1038.6	19.0
0°-60°	1779.7	32.5
0°-90°	2230.9	40.8
90°-120°	696.4	12.7
90°-150°	2344.0	42.8
90°-180°	3240.0	59.2
0°-180°	5470.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	1	8	14	19	22	5
95°	59	61	70	76	78	63
105°	206	211	216	221	224	220
115°	389	393	395	394	393	385
125°	568	573	575	573	572	509
135°	739	744	745	745	742	569
145°	895	899	902	902	899	560
155°	1025	1025	1026	1029	1025	472
165°	1114	1112	1113	1116	1111	314
175°	1158	1155	1155	1160	1154	110
180°	1161	1161	1161	1161	1161	



TEST NUMBER: P333387-940

CATALOG NUMBER: S125DIW-S610D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.8	15.2	15.4	15.8	16.1	16.3	16.5	16.7	16.9	16.9	17.2
90°	0.9	2.5	4.1	5.7	7.3	8.8	10.3	11.7	13.0	14.4	15.4
92.5°	21.8	23.0	24.1	25.2	26.4	27.8	29.5	31.2	33.0	34.7	36.0
95°	58.8	59.1	59.6	59.9	60.4	61.5	63.6	65.5	67.6	69.6	71.0
97.5°	97.6	97.7	97.9	98.1	98.3	99.7	102.5	105.2	108.0	110.8	112.1
100°	126.5	126.5	126.5	126.5	126.5	127.8	130.4	133.0	135.6	138.2	140.1
102.5°	157.6	158.4	159.2	160.0	160.8	161.8	163.2	164.5	165.9	167.2	169.2
105°	206.0	207.0	208.0	209.0	210.0	211.2	212.3	213.6	214.7	216.0	217.1
107.5°	259.5	260.5	261.5	262.5	263.5	264.5	265.4	266.4	267.2	268.1	268.8
110°	296.3	297.4	298.4	299.3	300.4	301.2	301.8	302.4	303.0	303.6	304.2



TEST NUMBER: P333387-940

CATALOG NUMBER: S125DIW-S610D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.9	334.5	335.0	335.6	336.0	336.7	337.4	338.2	338.9	339.7	340.0
115°	389.4	390.2	391.0	391.8	392.6	393.2	393.6	394.0	394.4	394.8	394.7
117.5°	445.1	445.4	445.8	446.1	446.6	446.9	447.3	447.6	448.0	448.4	448.5
120°	479.7	480.8	481.8	482.8	483.8	484.4	484.6	484.8	485.0	485.2	485.2
122.5°	517.4	517.7	518.1	518.4	518.8	519.2	519.8	520.3	520.8	521.4	521.2
125°	568.3	569.5	570.7	571.9	573.1	573.8	574.1	574.3	574.4	574.6	574.3
127.5°	622.5	623.2	623.9	624.6	625.3	625.7	626.0	626.2	626.4	626.7	626.5
130°	655.1	656.0	657.1	658.1	659.1	659.8	660.2	660.6	661.0	661.4	661.2
132.5°	687.6	689.2	690.9	692.5	694.2	695.0	694.9	694.8	694.7	694.6	694.5
135°	739.0	740.3	741.5	742.7	744.0	744.6	744.8	745.0	745.2	745.4	745.4
137.5°	787.6	788.7	789.9	791.0	792.2	793.0	793.4	793.9	794.3	794.8	795.0
140°	818.6	819.6	820.6	821.6	822.6	823.4	824.0	824.7	825.2	825.8	826.3
142.5°	849.7	850.5	851.4	852.2	853.1	853.9	854.6	855.4	856.1	856.9	857.1
145°	895.4	896.2	897.0	897.8	898.6	899.3	899.9	900.5	901.2	901.7	901.7
147.5°	937.7	938.2	938.6	939.0	939.4	940.0	940.4	940.8	941.4	941.8	942.4
150°	965.9	965.7	965.5	965.3	965.1	965.4	966.2	967.0	967.8	968.6	968.6
152.5°	989.0	989.3	989.5	989.9	990.2	990.4	990.8	991.0	991.4	991.8	992.2
155°	1024.6	1024.6	1024.6	1024.6	1024.6	1024.7	1024.9	1025.1	1025.3	1025.6	1026.4
157.5°	1056.4	1056.0	1055.5	1055.1	1054.6	1054.5	1054.7	1054.9	1055.2	1055.3	1056.1
160°	1075.2	1074.6	1074.0	1073.4	1072.8	1072.6	1072.8	1073.0	1073.2	1073.4	1074.2
162.5°	1091.8	1091.4	1090.9	1090.5	1090.0	1089.8	1089.9	1089.9	1090.0	1090.0	1091.0
165°	1114.1	1113.7	1113.2	1112.9	1112.4	1112.3	1112.6	1112.8	1112.9	1113.1	1113.9
167.5°	1132.8	1132.0	1131.2	1130.4	1129.6	1129.3	1129.3	1129.3	1129.3	1129.3	1130.4
170°	1143.0	1142.2	1141.4	1140.6	1139.8	1139.3	1139.3	1139.3	1139.3	1139.3	1140.6
172.5°	1150.2	1149.4	1148.6	1147.8	1147.0	1146.6	1146.6	1146.6	1146.6	1146.6	1147.8
175°	1158.3	1157.5	1156.7	1155.9	1155.1	1154.7	1154.7	1154.7	1154.7	1154.7	1155.9
177.5°	1162.5	1161.8	1161.2	1160.6	1159.9	1159.5	1159.3	1159.2	1159.0	1158.9	1159.8
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0



TEST NUMBER: P333387-940

CATALOG NUMBER: S125DIW-S610D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	17.4	17.6	17.7	17.8	17.7	17.6	17.5	17.4
90°	16.5	17.5	18.5	19.3	19.9	20.5	21.0	21.7
92.5°	37.4	38.7	40.0	40.8	41.3	41.7	42.2	42.6
95°	72.4	73.7	75.2	76.1	76.5	76.9	77.3	77.7
97.5°	113.4	114.8	116.1	116.8	117.1	117.3	117.6	117.8
100°	141.9	143.7	145.4	146.6	147.0	147.4	147.8	148.2
102.5°	171.1	173.1	175.0	176.3	176.8	177.5	178.0	178.5
105°	218.4	219.5	220.8	221.7	222.3	222.8	223.5	224.1
107.5°	269.4	270.0	270.5	270.9	270.8	270.8	270.7	270.7
110°	304.8	305.4	306.0	306.2	306.0	305.8	305.6	305.4



TEST NUMBER: P333387-940

CATALOG NUMBER: S125DIW-S610D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	340.3	340.5	340.8	340.8	340.5	340.1	339.7	339.4
115°	394.4	394.2	394.0	393.9	393.6	393.4	393.2	393.1
117.5°	448.6	448.8	449.0	448.6	447.8	447.0	446.2	445.4
120°	485.2	485.2	485.2	484.8	484.0	483.2	482.4	481.6
122.5°	521.0	520.8	520.7	520.3	519.7	519.0	518.4	517.7
125°	573.8	573.5	573.0	572.7	572.6	572.3	572.1	571.9
127.5°	626.2	626.1	625.9	625.6	625.2	624.8	624.4	624.0
130°	661.0	660.8	660.6	660.3	659.9	659.5	659.1	658.7
132.5°	694.2	694.0	693.8	693.5	692.9	692.3	691.8	691.2
135°	745.4	745.4	745.4	745.0	744.2	743.4	742.6	741.8
137.5°	795.2	795.5	795.7	795.3	794.3	793.4	792.3	791.3
140°	826.6	827.1	827.4	827.2	826.2	825.1	824.1	823.1
142.5°	857.4	857.6	857.9	857.5	856.5	855.5	854.5	853.5
145°	901.7	901.7	901.7	901.4	900.8	900.2	899.6	899.0
147.5°	942.8	943.3	943.8	943.3	942.0	940.6	939.2	937.9
150°	968.6	968.6	968.6	968.4	968.0	967.6	967.1	966.8
152.5°	992.7	993.2	993.6	993.5	992.8	992.1	991.3	990.6
155°	1027.2	1028.0	1028.8	1028.6	1027.6	1026.6	1025.6	1024.6
157.5°	1056.9	1057.7	1058.5	1058.3	1056.9	1055.6	1054.3	1053.0
160°	1075.0	1075.8	1076.7	1076.5	1075.5	1074.5	1073.5	1072.5
162.5°	1092.0	1092.9	1093.9	1093.8	1092.6	1091.5	1090.3	1089.1
165°	1114.7	1115.5	1116.3	1116.2	1115.0	1113.7	1112.6	1111.3
167.5°	1131.7	1132.8	1134.1	1134.1	1132.8	1131.6	1130.3	1129.1
170°	1141.7	1143.0	1144.2	1144.1	1142.6	1141.3	1139.9	1138.4
172.5°	1149.0	1150.2	1151.4	1151.4	1150.1	1148.9	1147.6	1146.4
175°	1157.1	1158.3	1159.6	1159.4	1158.1	1156.6	1155.2	1153.8
177.5°	1160.8	1161.8	1162.7	1162.6	1161.5	1160.4	1159.3	1158.2
180°	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0	1161.0

(END OF REPORT)