

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333392-940

Luminaire Tested: **S125DIW-S610D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333392-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1340U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7014.4 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333392-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333392-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333392-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.2
10°-20°	228.1	3.3
20°-30°	336.8	4.8
30°-40°	393.0	5.6
40°-50°	394.7	5.6
50°-60°	346.5	4.9
60°-70°	258.2	3.7
70°-80°	147.6	2.1
80°-90°	46.2	0.7
90°-100°	56.6	0.8
100°-110°	348.8	5.0
110°-120°	632.6	9.0
120°-130°	811.9	11.6
130°-140°	873.3	12.4
140°-150°	819.7	11.7
150°-160°	663.1	9.5
160°-170°	428.8	6.1
170°-180°	147.9	2.1
0°-30°	645.6	9.2
0°-40°	1038.6	14.8
0°-60°	1779.7	25.4
0°-90°	2231.6	31.8
90°-120°	1038.1	14.8
90°-150°	3542.9	50.5
90°-180°	4783.0	68.2
0°-180°	7014.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	1	10	18	24	28	5
95°	66	60	18	24	24	84
105°	340	344	344	344	343	360
115°	637	643	644	640	633	632
125°	906	914	914	910	906	809
135°	1130	1137	1135	1132	1126	871
145°	1310	1313	1313	1313	1307	819
155°	1443	1437	1439	1441	1433	665
165°	1523	1516	1517	1523	1515	430
175°	1558	1551	1552	1560	1550	148
180°	1558	1558	1558	1558	1558	



TEST NUMBER: P333392-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.9	15.2	15.7	16.1	16.5	16.9	17.0	17.3	17.6	17.7	18.0
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	17.7	16.3	14.9	13.5	12.0	12.1	13.7	15.2	16.9	18.5	19.8
95°	65.8	65.0	64.3	63.5	62.7	57.4	47.7	38.0	28.2	18.5	19.8
97.5°	137.4	138.8	140.2	141.5	142.9	133.9	114.7	95.4	76.1	56.8	49.6
100°	192.8	193.6	194.3	195.1	195.9	196.8	197.8	198.9	199.8	200.9	162.6
102.5°	249.1	250.1	251.1	252.1	253.1	253.9	254.5	255.1	255.7	256.3	249.1
105°	339.5	340.5	341.5	342.5	343.6	344.0	344.0	344.0	344.0	344.0	344.0
107.5°	433.2	433.2	433.2	433.2	433.2	433.5	434.0	434.4	435.0	435.5	435.5
110°	494.2	494.2	494.2	494.2	494.2	494.4	494.9	495.4	496.0	496.4	495.7



TEST NUMBER: P333392-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	551.4	552.1	552.7	553.2	553.8	554.4	554.6	554.9	555.3	555.5	554.6
115°	637.3	638.6	639.9	641.1	642.5	643.2	643.5	643.7	644.0	644.3	643.2
117.5°	726.2	726.1	726.1	726.0	726.0	726.5	727.5	728.4	729.4	730.4	729.1
120°	781.6	781.4	781.1	780.9	780.6	780.9	781.6	782.4	783.2	783.9	783.5
122.5°	830.5	831.5	832.5	833.5	834.5	835.2	835.5	835.9	836.2	836.6	836.1
125°	906.3	908.1	909.9	911.7	913.5	914.4	914.4	914.4	914.4	914.4	913.4
127.5°	978.6	979.9	981.1	982.4	983.7	984.3	984.1	984.0	983.8	983.6	983.1
130°	1022.9	1024.2	1025.5	1026.8	1028.1	1028.9	1029.1	1029.3	1029.6	1029.8	1029.1
132.5°	1067.3	1068.7	1070.2	1071.7	1073.2	1073.7	1073.1	1072.5	1072.0	1071.4	1071.3
135°	1130.3	1131.8	1133.4	1134.9	1136.5	1136.9	1136.5	1136.0	1135.4	1134.9	1134.4
137.5°	1188.3	1189.5	1190.9	1192.2	1193.6	1194.0	1193.6	1193.1	1192.7	1192.2	1192.3
140°	1226.1	1226.6	1227.2	1227.6	1228.2	1228.3	1228.1	1227.8	1227.5	1227.3	1227.8
142.5°	1260.3	1260.6	1260.9	1261.2	1261.5	1261.9	1262.2	1262.6	1262.9	1263.3	1263.4
145°	1310.4	1310.9	1311.4	1312.0	1312.4	1312.7	1312.7	1312.7	1312.7	1312.7	1313.0
147.5°	1354.2	1354.2	1354.1	1354.0	1353.9	1354.0	1354.2	1354.6	1354.9	1355.2	1355.5
150°	1382.0	1381.4	1381.0	1380.5	1379.9	1379.9	1380.5	1381.0	1381.4	1382.0	1382.5
152.5°	1408.7	1407.7	1406.5	1405.4	1404.3	1403.9	1404.4	1405.0	1405.5	1406.0	1406.5
155°	1443.1	1441.6	1440.1	1438.6	1437.0	1436.5	1437.0	1437.5	1438.1	1438.6	1439.3
157.5°	1469.7	1468.8	1467.8	1467.0	1466.1	1465.6	1465.6	1465.7	1465.8	1465.8	1466.6
160°	1488.2	1486.7	1485.1	1483.5	1482.0	1481.4	1481.7	1481.9	1482.2	1482.5	1483.5
162.5°	1503.0	1501.5	1499.9	1498.3	1496.8	1496.2	1496.5	1496.7	1496.9	1497.2	1498.6
165°	1522.9	1521.3	1519.7	1518.2	1516.7	1516.0	1516.3	1516.5	1516.8	1517.1	1518.6
167.5°	1537.6	1536.1	1534.5	1532.9	1531.2	1530.6	1530.8	1531.1	1531.3	1531.6	1533.5
170°	1546.0	1544.2	1542.3	1540.5	1538.7	1537.9	1538.2	1538.5	1538.7	1539.0	1541.1
172.5°	1551.5	1549.7	1547.9	1546.0	1544.3	1543.6	1544.1	1544.5	1545.0	1545.4	1547.3
175°	1557.5	1555.9	1554.4	1552.8	1551.3	1550.7	1551.0	1551.2	1551.5	1551.7	1553.7
177.5°	1560.2	1559.0	1557.8	1556.6	1555.3	1554.8	1555.1	1555.2	1555.4	1555.6	1557.1
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5



TEST NUMBER: P333392-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	18.3	18.5	18.8	18.9	18.8	18.7	18.6	18.5
90°	21.0	22.3	23.6	24.6	25.4	26.1	26.9	27.7
92.5°	21.0	22.3	23.6	24.4	24.8	25.1	25.5	25.9
95°	21.0	22.3	23.6	24.3	24.3	24.3	24.3	24.3
97.5°	42.4	35.1	27.8	24.3	24.3	24.3	24.3	24.3
100°	124.4	86.2	48.0	28.4	27.3	26.3	25.2	24.3
102.5°	241.8	234.6	227.4	215.0	197.6	180.1	162.6	145.3
105°	344.0	344.0	344.0	343.9	343.7	343.4	343.1	342.9
107.5°	435.6	435.7	435.7	435.3	434.5	433.8	433.0	432.3
110°	494.9	494.2	493.4	493.1	493.4	493.7	493.9	494.2



TEST NUMBER: P333392-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	553.6	552.7	551.7	551.0	550.6	550.3	549.9	549.6
115°	642.2	641.1	640.2	638.8	637.3	635.8	634.2	632.7
117.5°	727.7	726.4	725.1	724.0	723.4	722.7	722.0	721.4
120°	782.9	782.4	781.9	781.0	779.7	778.4	777.1	775.9
122.5°	835.5	835.0	834.6	833.5	832.1	830.5	829.0	827.6
125°	912.3	911.3	910.3	909.4	908.7	907.9	907.0	906.3
127.5°	982.6	982.0	981.4	980.2	978.3	976.4	974.5	972.6
130°	1028.3	1027.5	1026.8	1025.7	1024.5	1023.1	1021.9	1020.7
132.5°	1071.1	1070.9	1070.8	1070.1	1068.8	1067.6	1066.2	1065.0
135°	1133.9	1133.4	1132.8	1131.8	1130.3	1128.7	1127.2	1125.7
137.5°	1192.4	1192.5	1192.6	1191.9	1190.6	1189.3	1187.9	1186.6
140°	1228.3	1228.8	1229.3	1228.8	1227.3	1225.7	1224.2	1222.6
142.5°	1263.5	1263.6	1263.7	1263.0	1261.4	1259.9	1258.4	1256.9
145°	1313.2	1313.5	1313.8	1313.1	1311.5	1310.0	1308.5	1307.0
147.5°	1355.8	1356.1	1356.5	1355.7	1353.8	1351.9	1350.1	1348.3
150°	1383.0	1383.5	1384.0	1383.2	1381.2	1379.1	1377.1	1375.0
152.5°	1407.0	1407.6	1408.0	1407.4	1405.5	1403.7	1401.9	1400.0
155°	1440.1	1440.8	1441.6	1441.0	1439.0	1436.9	1434.9	1432.8
157.5°	1467.5	1468.3	1469.1	1468.5	1466.4	1464.4	1462.3	1460.3
160°	1484.5	1485.5	1486.6	1486.0	1484.0	1481.9	1479.9	1477.8
162.5°	1500.0	1501.6	1503.0	1502.5	1500.3	1498.0	1495.8	1493.5
165°	1520.1	1521.7	1523.2	1523.0	1520.9	1518.9	1516.8	1514.7
167.5°	1535.3	1537.1	1539.0	1538.7	1536.4	1534.2	1531.9	1529.6
170°	1543.1	1545.2	1547.2	1547.1	1544.8	1542.5	1540.2	1537.8
172.5°	1549.2	1551.0	1552.8	1552.6	1550.3	1548.0	1545.7	1543.4
175°	1555.8	1557.8	1559.9	1559.8	1557.5	1555.1	1552.8	1550.5
177.5°	1558.5	1560.0	1561.4	1561.3	1559.6	1558.0	1556.3	1554.7
180°	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5	1557.5

(END OF REPORT)