

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333393-940

Luminaire Tested: **S125DIW-S610D1340U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333393-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D1340U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6379.2 lumens  
Efficiency: N/A  
Efficacy: 118.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333393-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333393-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333393-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.7	1.3
10°-20°	228.1	3.6
20°-30°	336.8	5.3
30°-40°	393.0	6.2
40°-50°	394.7	6.2
50°-60°	346.5	5.4
60°-70°	258.2	4.0
70°-80°	147.6	2.3
80°-90°	46.2	0.7
90°-100°	99.5	1.6
100°-110°	294.0	4.6
110°-120°	497.9	7.8
120°-130°	655.3	10.3
130°-140°	734.3	11.5
140°-150°	719.7	11.3
150°-160°	604.5	9.5
160°-170°	401.8	6.3
170°-180°	140.6	2.2
0°-30°	645.6	10.1
0°-40°	1038.6	16.3
0°-60°	1779.7	27.9
0°-90°	2231.6	35.0
90°-120°	891.4	14.0
90°-150°	3000.7	47.0
90°-180°	4148.0	65.0
0°-180°	6379.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	1	10	18	24	28	6
95°	75	78	89	97	100	80
105°	264	270	276	283	287	282
115°	499	503	506	504	503	493
125°	728	734	736	733	732	651
135°	946	953	954	954	950	729
145°	1146	1151	1154	1154	1151	716
155°	1312	1312	1313	1317	1312	604
165°	1426	1424	1425	1429	1423	402
175°	1483	1479	1478	1484	1477	141
180°	1486	1486	1486	1486	1486	



TEST NUMBER: P333393-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.9	15.2	15.7	16.1	16.5	16.9	17.0	17.3	17.6	17.8	18.0
90°	1.2	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8
92.5°	28.0	29.4	30.9	32.3	33.7	35.6	37.8	40.0	42.2	44.4	46.1
95°	75.2	75.7	76.2	76.7	77.2	78.8	81.3	83.9	86.5	89.1	90.9
97.5°	124.9	125.1	125.4	125.6	125.7	127.6	131.2	134.7	138.3	141.8	143.5
100°	161.9	161.9	161.9	161.9	161.9	163.6	166.9	170.3	173.6	177.0	179.3
102.5°	201.7	202.8	203.8	204.8	205.8	207.2	208.9	210.6	212.3	214.0	216.5
105°	263.8	265.0	266.3	267.6	268.9	270.3	271.8	273.4	274.9	276.4	278.0
107.5°	332.2	333.5	334.7	336.1	337.3	338.6	339.7	340.9	342.1	343.3	344.1
110°	379.4	380.7	382.0	383.3	384.5	385.6	386.4	387.1	387.9	388.6	389.4



TEST NUMBER: P333393-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	427.5	428.2	428.8	429.5	430.2	431.1	431.9	432.9	433.9	434.9	435.2
115°	498.6	499.5	500.6	501.6	502.7	503.5	503.9	504.4	505.0	505.5	505.2
117.5°	569.8	570.2	570.7	571.1	571.7	572.1	572.6	573.0	573.5	574.0	574.2
120°	614.2	615.5	616.8	618.0	619.4	620.1	620.4	620.6	620.9	621.2	621.2
122.5°	662.4	662.8	663.3	663.7	664.1	664.8	665.4	666.1	666.7	667.4	667.2
125°	727.5	729.1	730.7	732.2	733.7	734.6	734.9	735.1	735.4	735.7	735.1
127.5°	796.9	797.8	798.7	799.6	800.5	801.0	801.4	801.6	802.0	802.3	802.0
130°	838.6	839.9	841.2	842.5	843.7	844.6	845.2	845.7	846.1	846.7	846.4
132.5°	880.2	882.3	884.5	886.5	888.7	889.7	889.6	889.5	889.4	889.3	889.0
135°	946.2	947.7	949.2	950.8	952.3	953.2	953.5	953.8	954.0	954.3	954.3
137.5°	1008.2	1009.7	1011.2	1012.6	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7
140°	1047.9	1049.3	1050.5	1051.9	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7
142.5°	1087.8	1088.9	1089.9	1091.0	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3
145°	1146.3	1147.3	1148.3	1149.3	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4
147.5°	1200.4	1201.0	1201.6	1202.1	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4
150°	1236.5	1236.3	1236.0	1235.7	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0
152.5°	1266.1	1266.5	1266.9	1267.2	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2
155°	1311.7	1311.7	1311.7	1311.7	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8
157.5°	1352.4	1351.8	1351.3	1350.7	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0
160°	1376.4	1375.7	1374.9	1374.1	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2
162.5°	1397.8	1397.2	1396.6	1396.1	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7
165°	1426.2	1425.7	1425.1	1424.7	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1
167.5°	1450.3	1449.2	1448.2	1447.2	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2
170°	1463.2	1462.2	1461.2	1460.2	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2
172.5°	1472.5	1471.4	1470.4	1469.4	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4
175°	1482.9	1481.8	1480.9	1479.8	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8
177.5°	1488.2	1487.4	1486.6	1485.8	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333393-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	18.3	18.5	18.8	18.9	18.8	18.7	18.6	18.5
90°	21.0	22.4	23.6	24.7	25.4	26.2	27.0	27.7
92.5°	47.8	49.5	51.2	52.3	52.9	53.5	54.0	54.6
95°	92.6	94.4	96.3	97.4	97.9	98.4	99.0	99.5
97.5°	145.2	146.9	148.6	149.6	149.9	150.3	150.5	150.9
100°	181.6	183.9	186.2	187.6	188.2	188.7	189.2	189.7
102.5°	219.0	221.5	224.1	225.7	226.4	227.1	227.8	228.5
105°	279.6	281.1	282.6	283.7	284.5	285.3	286.1	286.9
107.5°	344.8	345.6	346.4	346.8	346.7	346.6	346.6	346.5
110°	390.2	390.9	391.7	392.0	391.7	391.5	391.2	390.9





TEST NUMBER: P333393-940

CATALOG NUMBER: S125DIW-S610D1340U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.6	436.0	436.3	436.3	435.9	435.4	434.9	434.4
115°	505.0	504.7	504.4	504.2	503.9	503.6	503.5	503.2
117.5°	574.4	574.5	574.8	574.4	573.4	572.3	571.3	570.2
120°	621.2	621.2	621.2	620.6	619.6	618.6	617.5	616.5
122.5°	667.0	666.8	666.6	666.1	665.2	664.4	663.6	662.8
125°	734.6	734.1	733.6	733.3	733.0	732.7	732.5	732.2
127.5°	801.7	801.5	801.3	800.8	800.4	799.9	799.3	798.8
130°	846.1	846.0	845.7	845.3	844.8	844.3	843.7	843.2
132.5°	888.8	888.5	888.2	887.8	887.1	886.3	885.6	884.8
135°	954.3	954.3	954.3	953.8	952.7	951.7	950.7	949.7
137.5°	1018.1	1018.3	1018.7	1018.2	1016.9	1015.6	1014.3	1013.1
140°	1058.3	1058.7	1059.3	1058.9	1057.6	1056.3	1055.1	1053.7
142.5°	1097.6	1098.0	1098.2	1097.8	1096.4	1095.2	1093.9	1092.6
145°	1154.4	1154.4	1154.4	1154.0	1153.2	1152.4	1151.6	1150.9
147.5°	1206.9	1207.6	1208.2	1207.6	1205.9	1204.2	1202.4	1200.7
150°	1240.0	1240.0	1240.0	1239.7	1239.2	1238.7	1238.1	1237.7
152.5°	1270.8	1271.4	1272.0	1271.9	1271.0	1270.1	1269.1	1268.2
155°	1314.9	1315.9	1317.0	1316.8	1315.5	1314.3	1313.0	1311.7
157.5°	1353.1	1354.1	1355.1	1354.8	1353.1	1351.4	1349.7	1348.0
160°	1376.2	1377.2	1378.2	1378.1	1376.9	1375.6	1374.3	1373.0
162.5°	1397.9	1399.1	1400.3	1400.3	1398.7	1397.2	1395.8	1394.3
165°	1427.1	1428.2	1429.1	1428.9	1427.4	1425.8	1424.2	1422.7
167.5°	1448.8	1450.3	1451.8	1451.8	1450.2	1448.6	1447.0	1445.4
170°	1461.7	1463.2	1464.7	1464.6	1462.9	1461.1	1459.2	1457.4
172.5°	1471.0	1472.5	1474.0	1474.0	1472.4	1470.8	1469.2	1467.6
175°	1481.3	1482.9	1484.4	1484.3	1482.5	1480.7	1478.9	1477.1
177.5°	1486.0	1487.3	1488.5	1488.4	1486.9	1485.5	1484.1	1482.6
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4

(END OF REPORT)