

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333425-940

Luminaire Tested: **S125DIW-S850D1560U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333425-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1560U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7904.3 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	35	33	28				
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24				
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	26	25	21				
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18				
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	24	21	19	16				
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13				
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	11				
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7045	7045	7045	7045
5°	8159	7069	6190	7069
10°	9492	7033	5423	7033
15°	10508	6981	5003	6981
20°	11762	6899	4665	6899
25°	13779	6807	4501	6807
30°	14882	6716	4357	6716
35°	12236	6545	4264	6545
40°	8697	6308	4161	6308
45°	6682	5989	4103	5989
50°	5704	5591	4093	5591
55°	5078	5203	4130	5203
60°	4580	4779	4234	4779
65°	4232	4351	4345	4351
70°	3848	3909	4407	3909
75°	3399	3441	4367	3441
80°	2860	2804	3998	2804
85°	2267	2023	3223	2023



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.0	1.3
10°-20°	312.7	4.0
20°-30°	507.7	6.4
30°-40°	619.3	7.8
40°-50°	563.4	7.1
50°-60°	448.8	5.7
60°-70°	312.6	4.0
70°-80°	166.7	2.1
80°-90°	45.8	0.6
90°-100°	115.7	1.5
100°-110°	341.8	4.3
110°-120°	578.9	7.3
120°-130°	761.9	9.6
130°-140°	853.7	10.8
140°-150°	836.7	10.6
150°-160°	702.8	8.9
160°-170°	467.2	5.9
170°-180°	163.5	2.1
0°-30°	925.4	11.7
0°-40°	1544.8	19.5
0°-60°	2556.9	32.3
0°-90°	3082.1	39.0
90°-120°	1036.5	13.1
90°-150°	3488.8	44.1
90°-180°	4822.0	61.0
0°-180°	7904.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1258	1090	955	1090	1258	127
15°	1572	1044	748	1044	1572	450
25°	1934	955	632	955	1934	883
35°	1552	830	541	830	1552	950
45°	732	656	449	656	732	586
55°	451	462	367	462	451	406
65°	277	285	284	285	277	275
75°	136	138	175	138	136	147
85°	31	27	44	27	31	36
90°	32	1	32	1	32	20
95°	116	87	116	87	116	118
105°	334	307	334	307	334	353
115°	585	580	585	580	585	579
125°	851	846	851	846	851	760
135°	1104	1100	1104	1100	1104	852
145°	1338	1333	1338	1333	1338	835
155°	1525	1525	1525	1525	1525	702
165°	1654	1658	1654	1658	1654	466
175°	1717	1724	1717	1724	1717	163
180°	1728	1728	1728	1728	1728	



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1153.9	1152.4	1150.9	1147.9	1150.1	1143.9	1140.9	1135.7	1129.4	1127.2	1124.6
5°	1258.5	1260.8	1263.1	1253.4	1254.4	1247.9	1233.1	1221.0	1211.3	1198.8	1190.0
7.5°	1384.5	1378.9	1378.5	1372.3	1361.4	1352.7	1337.1	1317.3	1298.2	1276.3	1258.2
10°	1447.4	1447.9	1443.7	1436.3	1424.8	1416.4	1396.1	1376.5	1353.0	1325.2	1305.3
12.5°	1494.9	1496.7	1491.5	1481.5	1475.9	1457.1	1441.2	1418.1	1390.0	1367.8	1337.5
15°	1571.6	1566.4	1562.7	1550.2	1540.5	1521.1	1495.6	1471.5	1440.9	1412.6	1384.5
17.5°	1645.4	1649.5	1642.5	1631.1	1601.0	1578.2	1544.1	1511.1	1473.1	1435.2	1401.5
20°	1711.4	1715.0	1704.4	1684.5	1648.4	1625.7	1580.7	1538.2	1494.2	1445.6	1408.5
22.5°	1793.6	1790.6	1776.3	1746.0	1714.7	1672.8	1624.1	1572.3	1517.2	1462.2	1413.0
25°	1933.6	1914.1	1905.3	1867.9	1826.7	1765.1	1698.4	1622.5	1553.9	1481.2	1418.3
27.5°	2011.2	2005.1	1995.3	1969.2	1925.8	1860.0	1781.4	1688.8	1592.1	1500.4	1418.0
30°	1995.6	1996.5	1997.5	1989.1	1961.4	1911.8	1833.6	1734.0	1619.2	1515.9	1420.6
32.5°	1857.9	1874.7	1890.8	1909.9	1917.6	1908.2	1859.1	1769.2	1651.1	1533.7	1419.1
35°	1552.0	1557.2	1609.4	1661.3	1731.7	1786.4	1822.9	1783.2	1683.6	1548.8	1417.3
37.5°	1210.1	1235.2	1271.4	1330.0	1431.6	1522.5	1639.5	1693.3	1661.2	1553.7	1414.1
40°	1031.6	1054.8	1078.3	1138.1	1223.8	1334.0	1466.9	1580.3	1606.7	1538.2	1402.9
42.5°	893.9	912.1	938.3	983.3	1054.9	1152.4	1279.4	1427.7	1518.9	1493.0	1379.7
45°	731.6	743.2	763.6	799.2	851.0	927.5	1039.5	1201.6	1342.7	1389.6	1324.3
47.5°	626.2	626.1	641.9	666.6	704.0	768.9	851.8	978.7	1129.6	1241.2	1236.0
50°	567.7	565.3	577.8	599.1	628.7	671.8	751.0	852.4	997.4	1123.7	1159.0
52.5°	517.3	517.5	525.2	541.0	565.8	602.6	661.7	753.1	877.0	1006.7	1073.0
55°	451.0	449.2	457.9	468.6	486.6	510.7	553.3	623.2	723.7	851.5	937.6
57.5°	390.2	395.3	398.9	406.3	421.2	437.4	473.3	524.6	604.3	714.0	805.0
60°	354.6	359.8	362.6	370.0	382.0	395.9	423.7	465.4	532.4	627.0	717.2
62.5°	322.8	326.8	327.7	334.4	344.2	357.8	379.6	414.6	467.6	550.3	638.7
65°	276.9	276.9	278.7	285.7	290.3	302.4	319.1	344.5	387.1	451.5	526.9
67.5°	232.6	234.9	234.3	237.5	241.7	251.0	263.0	284.0	315.6	362.6	422.9
70°	203.8	205.5	205.1	207.4	212.0	218.1	227.8	247.7	270.4	310.7	362.6
72.5°	177.8	178.5	177.4	180.4	183.2	188.4	199.3	209.9	231.1	265.1	307.7
75°	136.2	137.1	137.9	139.8	142.6	145.3	151.0	161.6	175.5	201.0	228.3
77.5°	102.0	100.3	102.5	102.3	103.8	105.9	110.8	116.5	127.9	144.0	165.1
80°	76.9	77.3	77.3	77.8	80.1	81.5	85.7	89.8	98.6	110.7	125.5
82.5°	56.1	57.3	56.6	57.4	59.4	60.4	62.7	66.1	71.2	80.7	91.4
85°	30.6	28.3	29.2	30.1	30.1	30.6	32.4	33.8	36.6	40.3	44.4
87.5°	15.3	15.9	16.1	16.0	16.1	15.9	17.0	16.8	17.6	18.4	19.4
90°	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5	23.0	21.5	19.4
92.5°	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6	53.6	51.6	49.0
95°	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7	105.7	103.5	100.6
97.5°	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8	166.8	164.9	160.8
100°	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2	208.5	205.7	201.9
102.5°	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7	251.7	248.8	246.8
105°	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0	323.2	321.5	319.6
107.5°	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9	400.0	399.1	397.8
110°	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7	452.7	451.8	450.9



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5	506.0	505.7	504.5
115°	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1	587.4	587.7	587.1
117.5°	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8	667.5	667.4	666.7
120°	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2	722.2	722.2	721.8
122.5°	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5	775.7	776.0	775.2
125°	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2	854.7	855.3	855.1
127.5°	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2	932.5	932.8	932.5
130°	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8	984.1	984.4	983.8
132.5°	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3	1033.6	1033.9	1034.0
135°	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5	1109.5	1109.5	1109.2
137.5°	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7	1183.3	1182.9	1182.2
140°	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4	1229.8	1229.2	1228.3
142.5°	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1	1275.8	1275.4	1274.3
145°	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1	1342.1	1342.1	1341.2
147.5°	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3	1402.6	1401.9	1401.1
150°	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7	1441.7	1441.7	1440.5
152.5°	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6	1476.9	1476.1	1475.6
155°	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7	1527.6	1526.4	1526.1
157.5°	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2	1572.0	1570.7	1570.5
160°	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1	1598.8	1597.7	1597.4
162.5°	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3	1623.9	1622.4	1622.4
165°	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2	1658.0	1656.9	1656.5
167.5°	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4	1682.6	1680.8	1680.8
170°	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4	1697.6	1695.9	1695.9
172.5°	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2	1708.4	1706.6	1706.6
175°	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3	1720.5	1718.7	1718.7
177.5°	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8	1726.4	1724.9	1725.1
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1122.4	1119.8	1116.8	1111.6	1105.4	1102.0	1096.8	1093.5	1086.8	1081.3	1075.3
5°	1179.3	1167.2	1156.2	1141.8	1126.1	1115.9	1103.8	1090.4	1076.6	1062.2	1046.4
7.5°	1238.3	1217.0	1193.8	1168.9	1144.6	1122.2	1100.8	1079.8	1060.2	1036.4	1016.4
10°	1277.9	1251.1	1222.4	1188.6	1155.7	1127.0	1097.9	1072.4	1046.4	1018.7	994.1
12.5°	1317.6	1281.8	1241.3	1204.2	1164.6	1130.0	1095.6	1063.1	1030.6	999.8	971.2
15°	1345.6	1314.0	1276.6	1223.8	1179.3	1131.7	1086.3	1044.1	1004.8	970.5	934.4
17.5°	1364.0	1323.4	1283.2	1232.5	1174.2	1120.9	1069.5	1021.3	976.9	933.4	898.7
20°	1367.3	1325.6	1283.5	1233.9	1174.2	1113.1	1061.8	1003.8	956.2	911.2	868.6
22.5°	1366.2	1319.0	1273.1	1222.1	1163.9	1107.6	1045.4	986.4	934.7	890.5	846.1
25°	1355.8	1305.3	1247.9	1196.5	1139.1	1079.3	1016.4	955.2	902.4	851.9	808.0
27.5°	1347.0	1281.6	1216.6	1156.6	1101.2	1046.4	986.1	923.5	865.0	813.9	772.4
30°	1336.3	1264.5	1191.3	1128.8	1071.9	1018.7	961.7	900.6	839.5	789.4	745.0
32.5°	1326.7	1243.0	1165.8	1097.8	1037.4	985.7	933.2	875.0	815.0	764.3	719.8
35°	1308.1	1211.3	1122.8	1046.0	981.6	928.4	884.4	830.2	775.1	726.0	683.4
37.5°	1284.4	1169.6	1074.7	994.1	923.5	867.5	826.5	784.9	732.0	684.7	646.2
40°	1265.9	1140.0	1039.5	957.1	884.0	825.5	787.6	748.2	704.3	660.3	619.6
42.5°	1242.6	1113.3	1004.0	915.3	842.8	786.0	746.1	712.7	673.9	632.8	595.0
45°	1199.7	1065.0	946.5	851.0	777.8	721.8	680.6	655.7	626.5	587.5	555.6
47.5°	1136.7	1006.9	884.3	785.9	710.3	658.4	619.8	595.8	575.2	546.4	517.4
50°	1080.7	963.6	839.5	741.7	666.3	613.9	578.4	556.5	539.0	516.7	492.2
52.5°	1018.1	909.1	795.4	698.8	624.1	572.5	537.6	518.4	503.8	487.9	463.7
55°	918.6	826.1	720.5	628.7	559.8	509.3	478.8	462.1	450.0	438.0	423.2
57.5°	809.0	736.6	643.1	559.4	495.8	449.9	421.3	405.1	395.8	389.6	380.8
60°	732.0	670.0	589.4	513.0	451.0	410.3	382.5	370.0	362.1	357.0	350.5
62.5°	660.6	609.7	534.9	465.2	411.0	372.5	347.7	335.6	328.0	325.5	320.1
65°	555.2	515.9	454.2	396.4	350.1	317.2	296.3	284.7	280.1	277.3	277.9
67.5°	451.4	427.4	377.9	328.6	291.6	264.0	247.4	238.4	236.1	232.5	232.4
70°	388.0	370.0	328.3	285.3	252.4	231.0	216.2	207.0	204.6	202.8	202.3
72.5°	332.1	316.3	280.1	245.6	216.1	197.3	185.1	179.6	175.8	174.7	174.6
75°	249.6	240.8	212.0	184.8	164.3	151.4	143.1	137.9	135.2	134.7	135.2
77.5°	177.5	169.8	151.5	132.2	119.3	109.5	102.5	100.7	97.6	97.6	97.1
80°	133.3	128.2	116.7	101.4	90.8	82.4	78.7	75.4	74.5	73.1	74.5
82.5°	96.7	91.2	83.4	73.7	64.8	59.8	56.1	55.1	54.6	53.9	54.2
85°	47.7	48.2	43.5	36.1	32.4	29.6	27.3	27.3	26.8	26.4	26.8
87.5°	19.8	18.6	16.7	15.2	12.8	11.2	10.3	10.3	9.6	9.7	10.6
90°	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3	3.7	6.2	8.6
92.5°	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5	34.2	35.9	37.5
95°	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4	88.0	88.6	89.2
97.5°	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3	145.4	145.7	146.0
100°	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2	188.2
102.5°	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5	235.8	236.9	238.1
105°	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7	308.1	309.6	311.1
107.5°	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2	387.7	389.2	390.7
110°	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1	442.6	444.1	445.6





TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0	497.8	498.6	499.4
115°	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6	580.9	582.0	583.2
117.5°	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5	663.0	663.5	664.1
120°	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1	715.6	717.1	718.6
122.5°	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1	770.6	771.2	771.7
125°	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9	847.7	849.5	851.3
127.5°	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6	927.6	928.6	929.6
130°	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0	976.5	978.0	979.5
132.5°	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4	1025.9	1028.3	1030.8
135°	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1	1101.9	1103.7	1105.5
137.5°	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2	1173.9	1175.6	1177.3
140°	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4	1219.9	1221.4	1222.9
142.5°	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7	1266.0	1267.2	1268.5
145°	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8	1333.9	1335.2	1336.3
147.5°	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7	1396.3	1397.0	1397.7
150°	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6	1437.3	1437.1	1436.7
152.5°	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0	1472.5	1472.9	1473.3
155°	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4	1571.7	1571.1	1570.4
160°	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4	1599.5	1598.6	1597.7
162.5°	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1	1624.4	1623.8	1623.2
165°	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2	1657.6	1657.0	1656.4
167.5°	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1	1685.0	1683.8	1682.6
170°	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2	1700.0	1698.8	1697.6
172.5°	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0	1710.8	1709.6	1708.4
175°	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1	1722.9	1721.7	1720.5
177.5°	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3	1729.3	1728.4	1727.4
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1072.0	1067.9	1064.6	1057.2	1053.1	1047.6	1043.1	1047.9	1042.8	1045.0	1041.6
5°	1038.6	1025.6	1016.4	1002.9	991.3	980.7	972.9	971.4	967.7	965.9	960.3
7.5°	998.4	982.1	966.3	948.7	933.8	918.7	909.1	901.2	895.9	888.9	884.2
10°	974.6	952.9	934.4	913.1	894.6	878.3	865.4	858.9	852.9	844.1	840.9
12.5°	945.4	922.9	900.3	877.5	859.8	841.7	830.5	820.7	816.6	806.6	805.7
15°	910.3	876.6	854.3	831.2	806.6	791.8	782.5	771.9	767.2	760.3	755.2
17.5°	868.4	838.3	810.5	786.5	765.4	753.0	741.5	734.1	726.2	721.7	713.4
20°	838.1	809.4	781.6	756.1	739.9	725.6	716.3	709.4	701.1	698.7	690.4
22.5°	812.5	780.9	754.2	732.8	715.1	698.9	688.8	684.2	678.4	671.3	669.6
25°	771.0	738.1	715.4	694.1	678.3	663.5	656.6	650.6	645.0	639.9	638.0
27.5°	735.0	705.6	678.7	659.4	645.8	632.2	626.1	618.8	614.7	610.6	605.6
30°	709.8	679.8	656.1	637.6	622.8	610.7	604.2	599.1	595.5	591.7	589.0
32.5°	683.9	656.0	633.1	615.0	600.2	591.1	585.3	581.8	577.7	573.2	569.7
35°	649.6	619.0	596.8	581.1	569.5	562.6	556.1	552.9	548.2	548.2	544.5
37.5°	611.0	584.6	565.0	550.6	540.3	534.0	527.0	524.8	521.8	519.9	518.6
40°	588.1	563.5	545.0	530.7	519.5	514.4	508.9	505.2	503.3	501.0	500.1
42.5°	564.4	540.9	523.2	509.9	500.2	495.9	490.7	488.1	484.4	481.3	480.8
45°	528.3	505.6	489.5	478.8	470.5	465.4	462.1	456.6	454.7	451.0	450.5
47.5°	494.1	472.3	456.5	447.7	440.4	436.2	431.1	425.6	423.5	421.6	421.4
50°	468.6	448.7	433.8	425.5	418.6	412.6	407.4	403.8	402.3	402.3	403.3
52.5°	442.6	425.7	413.1	403.0	396.4	389.9	385.2	383.0	380.8	383.1	384.8
55°	404.7	387.5	378.3	368.5	362.1	354.6	352.4	351.4	350.1	353.7	355.6
57.5°	364.5	352.5	341.6	332.0	326.2	321.9	318.8	318.2	320.7	322.5	328.6
60°	338.9	325.0	315.3	307.9	301.0	298.2	297.3	296.3	298.2	303.3	311.1
62.5°	310.8	299.5	289.0	283.5	278.4	273.8	273.6	274.1	277.9	283.7	291.5
65°	269.5	259.8	252.8	246.3	242.2	239.4	240.3	242.2	246.3	254.2	263.0
67.5°	227.6	220.9	214.6	209.4	205.4	205.4	206.3	209.1	214.0	223.1	231.1
70°	200.5	193.1	188.0	185.7	182.4	180.6	183.3	188.0	192.2	200.5	207.4
72.5°	173.4	167.2	163.2	161.6	160.2	158.7	159.6	164.6	170.3	178.6	186.7
75°	133.3	131.0	128.2	126.4	125.0	125.9	126.9	131.5	136.2	144.9	154.2
77.5°	97.3	94.9	93.3	92.8	92.0	92.5	95.1	98.5	103.1	109.5	116.5
80°	73.7	72.7	71.8	71.3	71.3	71.8	75.4	77.8	81.9	88.0	93.5
82.5°	53.6	53.1	52.9	52.8	53.1	53.2	55.5	58.5	62.0	66.5	71.3
85°	28.3	27.3	28.7	29.2	28.3	29.6	30.6	32.4	33.8	36.1	38.4
87.5°	11.4	12.7	12.7	13.5	13.9	15.1	15.0	16.8	17.8	18.8	18.7
90°	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5	26.0	27.5	28.7
92.5°	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6	57.5	59.6	60.8
95°	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7	109.9	111.9	113.2
97.5°	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8	170.8	172.7	174.0
100°	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2	213.8	216.5	218.2
102.5°	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7	257.6	260.5	262.4
105°	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0	326.8	328.6	329.9
107.5°	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9	401.8	402.7	403.1
110°	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7	454.6	455.5	455.8



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5	506.9	507.3	507.3
115°	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1	586.8	586.5	586.2
117.5°	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8	668.1	668.2	667.8
120°	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2	722.2	722.2	721.6
122.5°	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5	775.3	775.0	774.5
125°	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2	853.5	852.9	852.5
127.5°	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2	931.9	931.6	931.1
130°	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8	983.6	983.2	982.8
132.5°	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3	1033.0	1032.7	1032.2
135°	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5	1109.5	1109.5	1108.9
137.5°	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7	1184.0	1184.4	1183.8
140°	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4	1231.0	1231.5	1231.1
142.5°	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1	1276.5	1276.9	1276.3
145°	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1	1342.1	1342.1	1341.7
147.5°	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3	1404.0	1404.7	1404.1
150°	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7	1441.7	1441.7	1441.4
152.5°	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6	1478.3	1479.0	1478.8
155°	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7	1530.0	1531.2	1531.1
157.5°	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2	1574.4	1575.6	1575.2
160°	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1	1601.2	1602.5	1602.3
162.5°	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3	1626.7	1628.2	1628.0
165°	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2	1660.5	1661.6	1661.3
167.5°	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4	1686.1	1687.9	1687.9
170°	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4	1701.2	1703.0	1702.9
172.5°	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2	1712.0	1713.8	1713.8
175°	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3	1724.1	1725.9	1725.7
177.5°	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8	1729.2	1730.6	1730.5
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1039.4	1042.0	1039.7	1042.8	1039.7	1042.0	1039.4	1041.6	1045.0	1042.8	1047.9
5°	958.0	953.9	956.6	954.8	956.6	953.9	958.0	960.3	965.9	967.7	971.4
7.5°	882.8	878.8	874.3	872.2	874.3	878.8	882.8	884.2	888.9	895.9	901.2
10°	835.8	830.6	830.2	827.0	830.2	830.6	835.8	840.9	844.1	852.9	858.9
12.5°	801.3	796.6	791.3	790.0	791.3	796.6	801.3	805.7	806.6	816.6	820.7
15°	752.4	748.7	745.5	748.2	745.5	748.7	752.4	755.2	760.3	767.2	771.9
17.5°	711.8	708.7	708.1	704.7	708.1	708.7	711.8	713.4	721.7	726.2	734.1
20°	686.2	683.9	684.8	678.8	684.8	683.9	686.2	690.4	698.7	701.1	709.4
22.5°	665.8	661.3	660.8	659.5	660.8	661.3	665.8	669.6	671.3	678.4	684.2
25°	633.9	631.6	629.3	631.6	629.3	631.6	633.9	638.0	639.9	645.0	650.6
27.5°	606.0	603.2	602.6	602.9	602.6	603.2	606.0	605.6	610.6	614.7	618.8
30°	589.0	584.3	584.8	584.3	584.8	584.3	589.0	589.0	591.7	595.5	599.1
32.5°	570.4	567.3	566.7	565.8	566.7	567.3	570.4	569.7	573.2	577.7	581.8
35°	543.1	543.1	540.8	540.8	540.8	543.1	543.1	544.5	548.2	548.2	552.9
37.5°	517.5	517.0	515.6	515.9	515.6	517.0	517.5	518.6	519.9	521.8	524.8
40°	498.2	497.8	496.3	493.6	496.3	497.8	498.2	500.1	501.0	503.3	505.2
42.5°	479.7	478.1	477.5	476.5	477.5	478.1	479.7	480.8	481.3	484.4	488.1
45°	450.5	450.5	449.6	449.2	449.6	450.5	450.5	450.5	451.0	454.7	456.6
47.5°	422.2	423.0	424.8	424.5	424.8	423.0	422.2	421.4	421.6	423.5	425.6
50°	405.1	405.6	407.0	407.4	407.0	405.6	405.1	403.3	402.3	402.3	403.8
52.5°	386.3	389.0	390.7	390.4	390.7	389.0	386.3	384.8	383.1	380.8	383.0
55°	359.8	363.0	366.2	366.8	366.2	363.0	359.8	355.6	353.7	350.1	351.4
57.5°	333.6	338.1	341.5	342.6	341.5	338.1	333.6	328.6	322.5	320.7	318.2
60°	315.8	321.8	326.0	327.8	326.0	321.8	315.8	311.1	303.3	298.2	296.3
62.5°	298.7	305.5	309.7	310.0	309.7	305.5	298.7	291.5	283.7	277.9	274.1
65°	270.9	277.9	281.5	284.3	281.5	277.9	270.9	263.0	254.2	246.3	242.2
67.5°	240.9	247.8	251.9	254.1	251.9	247.8	240.9	231.1	223.1	214.0	209.1
70°	219.0	226.0	231.5	233.4	231.5	226.0	219.0	207.4	200.5	192.2	188.0
72.5°	197.5	203.8	208.2	210.4	208.2	203.8	197.5	186.7	178.6	170.3	164.6
75°	160.2	168.5	172.7	175.0	172.7	168.5	160.2	154.2	144.9	136.2	131.5
77.5°	123.5	131.2	133.7	134.8	133.7	131.2	123.5	116.5	109.5	103.1	98.5
80°	99.1	103.7	106.9	107.5	106.9	103.7	99.1	93.5	88.0	81.9	77.8
82.5°	76.2	80.0	81.1	82.2	81.1	80.0	76.2	71.3	66.5	62.0	58.5
85°	41.6	43.5	44.0	43.5	44.0	43.5	41.6	38.4	36.1	33.8	32.4
87.5°	19.6	19.4	19.6	20.5	19.6	19.4	19.6	18.7	18.8	17.8	16.8
90°	29.6	30.5	31.4	32.3	31.4	30.5	29.6	28.7	27.5	26.0	24.5
92.5°	61.5	62.2	62.8	63.5	62.8	62.2	61.5	60.8	59.6	57.5	55.6
95°	113.9	114.5	115.0	115.7	115.0	114.5	113.9	113.2	111.9	109.9	107.7
97.5°	174.3	174.7	175.0	175.4	175.0	174.7	174.3	174.0	172.7	170.8	168.8
100°	218.7	219.4	220.0	220.5	220.0	219.4	218.7	218.2	216.5	213.8	211.2
102.5°	263.2	264.0	264.9	265.7	264.9	264.0	263.2	262.4	260.5	257.6	254.7
105°	330.8	331.7	332.6	333.5	332.6	331.7	330.8	329.9	328.6	326.8	325.0
107.5°	403.1	403.1	403.0	402.9	403.0	403.1	403.1	403.1	402.7	401.8	400.9
110°	455.5	455.1	454.9	454.6	454.9	455.1	455.5	455.8	455.5	454.6	453.7



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	506.8	506.2	505.7	505.2	505.7	506.2	506.8	507.3	507.3	506.9	506.5
115°	585.9	585.6	585.3	585.1	585.3	585.6	585.9	586.2	586.5	586.8	587.1
117.5°	666.6	665.4	664.2	663.0	664.2	665.4	666.6	667.8	668.2	668.1	667.8
120°	720.4	719.2	718.0	716.8	718.0	719.2	720.4	721.6	722.2	722.2	722.2
122.5°	773.5	772.5	771.5	770.6	771.5	772.5	773.5	774.5	775.0	775.3	775.5
125°	852.2	851.9	851.6	851.3	851.6	851.9	852.2	852.5	852.9	853.5	854.2
127.5°	930.5	930.0	929.3	928.7	929.3	930.0	930.5	931.1	931.6	931.9	932.2
130°	982.2	981.6	981.0	980.4	981.0	981.6	982.2	982.8	983.2	983.6	983.8
132.5°	1031.4	1030.5	1029.7	1028.8	1029.7	1030.5	1031.4	1032.2	1032.7	1033.0	1033.3
135°	1107.7	1106.5	1105.3	1104.1	1105.3	1106.5	1107.7	1108.9	1109.5	1109.5	1109.5
137.5°	1182.3	1180.8	1179.3	1177.8	1179.3	1180.8	1182.3	1183.8	1184.4	1184.0	1183.7
140°	1229.7	1228.2	1226.6	1225.1	1226.6	1228.2	1229.7	1231.1	1231.5	1231.0	1230.4
142.5°	1274.8	1273.4	1271.8	1270.3	1271.8	1273.4	1274.8	1276.3	1276.9	1276.5	1276.1
145°	1340.8	1339.9	1339.0	1338.1	1339.0	1339.9	1340.8	1341.7	1342.1	1342.1	1342.1
147.5°	1402.0	1400.0	1398.0	1396.0	1398.0	1400.0	1402.0	1404.1	1404.7	1404.0	1403.3
150°	1440.7	1440.2	1439.6	1439.0	1439.6	1440.2	1440.7	1441.4	1441.7	1441.7	1441.7
152.5°	1477.7	1476.7	1475.6	1474.5	1475.6	1476.7	1477.7	1478.8	1479.0	1478.3	1477.6
155°	1529.6	1528.0	1526.5	1525.1	1526.5	1528.0	1529.6	1531.1	1531.2	1530.0	1528.7
157.5°	1573.2	1571.2	1569.2	1567.3	1569.2	1571.2	1573.2	1575.2	1575.6	1574.4	1573.2
160°	1600.8	1599.3	1597.9	1596.3	1597.9	1599.3	1600.8	1602.3	1602.5	1601.2	1600.1
162.5°	1626.3	1624.5	1622.8	1621.0	1622.8	1624.5	1626.3	1628.0	1628.2	1626.7	1625.3
165°	1659.6	1657.8	1656.0	1654.1	1656.0	1657.8	1659.6	1661.3	1661.6	1660.5	1659.2
167.5°	1686.0	1684.3	1682.4	1680.5	1682.4	1684.3	1686.0	1687.9	1687.9	1686.1	1684.4
170°	1700.8	1698.7	1696.6	1694.5	1696.6	1698.7	1700.8	1702.9	1703.0	1701.2	1699.4
172.5°	1711.9	1710.0	1708.2	1706.4	1708.2	1710.0	1711.9	1713.8	1713.8	1712.0	1710.2
175°	1723.7	1721.5	1719.5	1717.3	1719.5	1721.5	1723.7	1725.7	1725.9	1724.1	1722.3
177.5°	1728.8	1727.2	1725.5	1723.9	1725.5	1727.2	1728.8	1730.5	1730.6	1729.2	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1043.1	1047.6	1053.1	1057.2	1064.6	1067.9	1072.0	1075.3	1081.3	1086.8	1093.5
5°	972.9	980.7	991.3	1002.9	1016.4	1025.6	1038.6	1046.4	1062.2	1076.6	1090.4
7.5°	909.1	918.7	933.8	948.7	966.3	982.1	998.4	1016.4	1036.4	1060.2	1079.8
10°	865.4	878.3	894.6	913.1	934.4	952.9	974.6	994.1	1018.7	1046.4	1072.4
12.5°	830.5	841.7	859.8	877.5	900.3	922.9	945.4	971.2	999.8	1030.6	1063.1
15°	782.5	791.8	806.6	831.2	854.3	876.6	910.3	934.4	970.5	1004.8	1044.1
17.5°	741.5	753.0	765.4	786.5	810.5	838.3	868.4	898.7	933.4	976.9	1021.3
20°	716.3	725.6	739.9	756.1	781.6	809.4	838.1	868.6	911.2	956.2	1003.8
22.5°	688.8	698.9	715.1	732.8	754.2	780.9	812.5	846.1	890.5	934.7	986.4
25°	656.6	663.5	678.3	694.1	715.4	738.1	771.0	808.0	851.9	902.4	955.2
27.5°	626.1	632.2	645.8	659.4	678.7	705.6	735.0	772.4	813.9	865.0	923.5
30°	604.2	610.7	622.8	637.6	656.1	679.8	709.8	745.0	789.4	839.5	900.6
32.5°	585.3	591.1	600.2	615.0	633.1	656.0	683.9	719.8	764.3	815.0	875.0
35°	556.1	562.6	569.5	581.1	596.8	619.0	649.6	683.4	726.0	775.1	830.2
37.5°	527.0	534.0	540.3	550.6	565.0	584.6	611.0	646.2	684.7	732.0	784.9
40°	508.9	514.4	519.5	530.7	545.0	563.5	588.1	619.6	660.3	704.3	748.2
42.5°	490.7	495.9	500.2	509.9	523.2	540.9	564.4	595.0	632.8	673.9	712.7
45°	462.1	465.4	470.5	478.8	489.5	505.6	528.3	555.6	587.5	626.5	655.7
47.5°	431.1	436.2	440.4	447.7	456.5	472.3	494.1	517.4	546.4	575.2	595.8
50°	407.4	412.6	418.6	425.5	433.8	448.7	468.6	492.2	516.7	539.0	556.5
52.5°	385.2	389.9	396.4	403.0	413.1	425.7	442.6	463.7	487.9	503.8	518.4
55°	352.4	354.6	362.1	368.5	378.3	387.5	404.7	423.2	438.0	450.0	462.1
57.5°	318.8	321.9	326.2	332.0	341.6	352.5	364.5	380.8	389.6	395.8	405.1
60°	297.3	298.2	301.0	307.9	315.3	325.0	338.9	350.5	357.0	362.1	370.0
62.5°	273.6	273.8	278.4	283.5	289.0	299.5	310.8	320.1	325.5	328.0	335.6
65°	240.3	239.4	242.2	246.3	252.8	259.8	269.5	277.9	277.3	280.1	284.7
67.5°	206.3	205.4	205.4	209.4	214.6	220.9	227.6	232.4	232.5	236.1	238.4
70°	183.3	180.6	182.4	185.7	188.0	193.1	200.5	202.3	202.8	204.6	207.0
72.5°	159.6	158.7	160.2	161.6	163.2	167.2	173.4	174.6	174.7	175.8	179.6
75°	126.9	125.9	125.0	126.4	128.2	131.0	133.3	135.2	134.7	135.2	137.9
77.5°	95.1	92.5	92.0	92.8	93.3	94.9	97.3	97.1	97.6	97.6	100.7
80°	75.4	71.8	71.3	71.3	71.8	72.7	73.7	74.5	73.1	74.5	75.4
82.5°	55.5	53.2	53.1	52.8	52.9	53.1	53.6	54.2	53.9	54.6	55.1
85°	30.6	29.6	28.3	29.2	28.7	27.3	28.3	26.8	26.4	26.8	27.3
87.5°	15.0	15.1	13.9	13.5	12.7	12.7	11.4	10.6	9.7	9.6	10.3
90°	23.0	21.5	19.4	17.3	15.2	13.1	10.9	8.6	6.2	3.7	1.3
92.5°	53.6	51.6	49.0	46.5	44.0	41.4	39.2	37.5	35.9	34.2	32.5
95°	105.7	103.5	100.6	97.6	94.6	91.6	89.8	89.2	88.6	88.0	87.4
97.5°	166.8	164.9	160.8	156.7	152.5	148.4	146.2	146.0	145.7	145.4	145.3
100°	208.5	205.7	201.9	198.0	194.1	190.2	188.2	188.2	188.2	188.2	188.2
102.5°	251.7	248.8	246.8	244.9	242.9	240.9	239.3	238.1	236.9	235.8	234.5
105°	323.2	321.5	319.6	317.8	316.0	314.2	312.6	311.1	309.6	308.1	306.7
107.5°	400.0	399.1	397.8	396.4	395.0	393.7	392.2	390.7	389.2	387.7	386.2
110°	452.7	451.8	450.9	450.0	449.2	448.3	447.1	445.6	444.1	442.6	441.1



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	506.0	505.7	504.5	503.4	502.2	501.1	500.2	499.4	498.6	497.8	497.0
115°	587.4	587.7	587.1	586.5	585.9	585.3	584.4	583.2	582.0	580.9	579.6
117.5°	667.5	667.4	666.7	666.2	665.7	665.1	664.6	664.1	663.5	663.0	662.5
120°	722.2	722.2	721.8	721.6	721.3	720.9	720.1	718.6	717.1	715.6	714.1
122.5°	775.7	776.0	775.2	774.5	773.6	772.8	772.2	771.7	771.2	770.6	770.1
125°	854.7	855.3	855.1	854.7	854.4	854.2	853.1	851.3	849.5	847.7	845.9
127.5°	932.5	932.8	932.5	932.1	931.7	931.4	930.7	929.6	928.6	927.6	926.6
130°	984.1	984.4	983.8	983.2	982.7	982.0	981.0	979.5	978.0	976.5	975.0
132.5°	1033.6	1033.9	1034.0	1034.1	1034.3	1034.4	1033.2	1030.8	1028.3	1025.9	1023.4
135°	1109.5	1109.5	1109.2	1108.9	1108.6	1108.3	1107.2	1105.5	1103.7	1101.9	1100.1
137.5°	1183.3	1182.9	1182.2	1181.6	1181.0	1180.3	1179.1	1177.3	1175.6	1173.9	1172.2
140°	1229.8	1229.2	1228.3	1227.4	1226.5	1225.6	1224.4	1222.9	1221.4	1219.9	1218.4
142.5°	1275.8	1275.4	1274.3	1273.2	1272.0	1270.9	1269.7	1268.5	1267.2	1266.0	1264.7
145°	1342.1	1342.1	1341.2	1340.3	1339.4	1338.5	1337.6	1336.3	1335.2	1333.9	1332.8
147.5°	1402.6	1401.9	1401.1	1400.4	1399.7	1399.0	1398.3	1397.7	1397.0	1396.3	1395.7
150°	1441.7	1441.7	1440.5	1439.3	1438.1	1436.9	1436.5	1436.7	1437.1	1437.3	1437.6
152.5°	1476.9	1476.1	1475.6	1475.2	1474.7	1474.2	1473.7	1473.3	1472.9	1472.5	1472.0
155°	1527.6	1526.4	1526.1	1525.8	1525.5	1525.2	1525.1	1525.1	1525.1	1525.1	1525.1
157.5°	1572.0	1570.7	1570.5	1570.2	1569.9	1569.6	1569.8	1570.4	1571.1	1571.7	1572.4
160°	1598.8	1597.7	1597.4	1597.1	1596.8	1596.5	1596.8	1597.7	1598.6	1599.5	1600.4
162.5°	1623.9	1622.4	1622.4	1622.3	1622.2	1622.2	1622.5	1623.2	1623.8	1624.4	1625.1
165°	1658.0	1656.9	1656.5	1656.3	1656.0	1655.6	1655.8	1656.4	1657.0	1657.6	1658.2
167.5°	1682.6	1680.8	1680.8	1680.8	1680.8	1680.8	1681.4	1682.6	1683.8	1685.0	1686.1
170°	1697.6	1695.9	1695.9	1695.9	1695.9	1695.9	1696.5	1697.6	1698.8	1700.0	1701.2
172.5°	1708.4	1706.6	1706.6	1706.6	1706.6	1706.6	1707.2	1708.4	1709.6	1710.8	1712.0
175°	1720.5	1718.7	1718.7	1718.7	1718.7	1718.7	1719.3	1720.5	1721.7	1722.9	1724.1
177.5°	1726.4	1724.9	1725.1	1725.4	1725.6	1725.8	1726.4	1727.4	1728.4	1729.3	1730.3
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1096.8	1102.0	1105.4	1111.6	1116.8	1119.8	1122.4	1124.6	1127.2	1129.4	1135.7
5°	1103.8	1115.9	1126.1	1141.8	1156.2	1167.2	1179.3	1190.0	1198.8	1211.3	1221.0
7.5°	1100.8	1122.2	1144.6	1168.9	1193.8	1217.0	1238.3	1258.2	1276.3	1298.2	1317.3
10°	1097.9	1127.0	1155.7	1188.6	1222.4	1251.1	1277.9	1305.3	1325.2	1353.0	1376.5
12.5°	1095.6	1130.0	1164.6	1204.2	1241.3	1281.8	1317.6	1337.5	1367.8	1390.0	1418.1
15°	1086.3	1131.7	1179.3	1223.8	1276.6	1314.0	1345.6	1384.5	1412.6	1440.9	1471.5
17.5°	1069.5	1120.9	1174.2	1232.5	1283.2	1323.4	1364.0	1401.5	1435.2	1473.1	1511.1
20°	1061.8	1113.1	1174.2	1233.9	1283.5	1325.6	1367.3	1408.5	1445.6	1494.2	1538.2
22.5°	1045.4	1107.6	1163.9	1222.1	1273.1	1319.0	1366.2	1413.0	1462.2	1517.2	1572.3
25°	1016.4	1079.3	1139.1	1196.5	1247.9	1305.3	1355.8	1418.3	1481.2	1553.9	1622.5
27.5°	986.1	1046.4	1101.2	1156.6	1216.6	1281.6	1347.0	1418.0	1500.4	1592.1	1688.8
30°	961.7	1018.7	1071.9	1128.8	1191.3	1264.5	1336.3	1420.6	1515.9	1619.2	1734.0
32.5°	933.2	985.7	1037.4	1097.8	1165.8	1243.0	1326.7	1419.1	1533.7	1651.1	1769.2
35°	884.4	928.4	981.6	1046.0	1122.8	1211.3	1308.1	1417.3	1548.8	1683.6	1783.2
37.5°	826.5	867.5	923.5	994.1	1074.7	1169.6	1284.4	1414.1	1553.7	1661.2	1693.3
40°	787.6	825.5	884.0	957.1	1039.5	1140.0	1265.9	1402.9	1538.2	1606.7	1580.3
42.5°	746.1	786.0	842.8	915.3	1004.0	1113.3	1242.6	1379.7	1493.0	1518.9	1427.7
45°	680.6	721.8	777.8	851.0	946.5	1065.0	1199.7	1324.3	1389.6	1342.7	1201.6
47.5°	619.8	658.4	710.3	785.9	884.3	1006.9	1136.7	1236.0	1241.2	1129.6	978.7
50°	578.4	613.9	666.3	741.7	839.5	963.6	1080.7	1159.0	1123.7	997.4	852.4
52.5°	537.6	572.5	624.1	698.8	795.4	909.1	1018.1	1073.0	1006.7	877.0	753.1
55°	478.8	509.3	559.8	628.7	720.5	826.1	918.6	937.6	851.5	723.7	623.2
57.5°	421.3	449.9	495.8	559.4	643.1	736.6	809.0	805.0	714.0	604.3	524.6
60°	382.5	410.3	451.0	513.0	589.4	670.0	732.0	717.2	627.0	532.4	465.4
62.5°	347.7	372.5	411.0	465.2	534.9	609.7	660.6	638.7	550.3	467.6	414.6
65°	296.3	317.2	350.1	396.4	454.2	515.9	555.2	526.9	451.5	387.1	344.5
67.5°	247.4	264.0	291.6	328.6	377.9	427.4	451.4	422.9	362.6	315.6	284.0
70°	216.2	231.0	252.4	285.3	328.3	370.0	388.0	362.6	310.7	270.4	247.7
72.5°	185.1	197.3	216.1	245.6	280.1	316.3	332.1	307.7	265.1	231.1	209.9
75°	143.1	151.4	164.3	184.8	212.0	240.8	249.6	228.3	201.0	175.5	161.6
77.5°	102.5	109.5	119.3	132.2	151.5	169.8	177.5	165.1	144.0	127.9	116.5
80°	78.7	82.4	90.8	101.4	116.7	128.2	133.3	125.5	110.7	98.6	89.8
82.5°	56.1	59.8	64.8	73.7	83.4	91.2	96.7	91.4	80.7	71.2	66.1
85°	27.3	29.6	32.4	36.1	43.5	48.2	47.7	44.4	40.3	36.6	33.8
87.5°	10.3	11.2	12.8	15.2	16.7	18.6	19.8	19.4	18.4	17.6	16.8
90°	3.7	6.2	8.6	10.9	13.1	15.2	17.3	19.4	21.5	23.0	24.5
92.5°	34.2	35.9	37.5	39.2	41.4	44.0	46.5	49.0	51.6	53.6	55.6
95°	88.0	88.6	89.2	89.8	91.6	94.6	97.6	100.6	103.5	105.7	107.7
97.5°	145.4	145.7	146.0	146.2	148.4	152.5	156.7	160.8	164.9	166.8	168.8
100°	188.2	188.2	188.2	188.2	190.2	194.1	198.0	201.9	205.7	208.5	211.2
102.5°	235.8	236.9	238.1	239.3	240.9	242.9	244.9	246.8	248.8	251.7	254.7
105°	308.1	309.6	311.1	312.6	314.2	316.0	317.8	319.6	321.5	323.2	325.0
107.5°	387.7	389.2	390.7	392.2	393.7	395.0	396.4	397.8	399.1	400.0	400.9
110°	442.6	444.1	445.6	447.1	448.3	449.2	450.0	450.9	451.8	452.7	453.7





TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.8	498.6	499.4	500.2	501.1	502.2	503.4	504.5	505.7	506.0	506.5
115°	580.9	582.0	583.2	584.4	585.3	585.9	586.5	587.1	587.7	587.4	587.1
117.5°	663.0	663.5	664.1	664.6	665.1	665.7	666.2	666.7	667.4	667.5	667.8
120°	715.6	717.1	718.6	720.1	720.9	721.3	721.6	721.8	722.2	722.2	722.2
122.5°	770.6	771.2	771.7	772.2	772.8	773.6	774.5	775.2	776.0	775.7	775.5
125°	847.7	849.5	851.3	853.1	854.2	854.4	854.7	855.1	855.3	854.7	854.2
127.5°	927.6	928.6	929.6	930.7	931.4	931.7	932.1	932.5	932.8	932.5	932.2
130°	976.5	978.0	979.5	981.0	982.0	982.7	983.2	983.8	984.4	984.1	983.8
132.5°	1025.9	1028.3	1030.8	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6	1033.3
135°	1101.9	1103.7	1105.5	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5	1109.5
137.5°	1173.9	1175.6	1177.3	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3	1183.7
140°	1219.9	1221.4	1222.9	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8	1230.4
142.5°	1266.0	1267.2	1268.5	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8	1276.1
145°	1333.9	1335.2	1336.3	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1	1342.1
147.5°	1396.3	1397.0	1397.7	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6	1403.3
150°	1437.3	1437.1	1436.7	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7	1441.7
152.5°	1472.5	1472.9	1473.3	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9	1477.6
155°	1525.1	1525.1	1525.1	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6	1528.7
157.5°	1571.7	1571.1	1570.4	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0	1573.2
160°	1599.5	1598.6	1597.7	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8	1600.1
162.5°	1624.4	1623.8	1623.2	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9	1625.3
165°	1657.6	1657.0	1656.4	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0	1659.2
167.5°	1685.0	1683.8	1682.6	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6	1684.4
170°	1700.0	1698.8	1697.6	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6	1699.4
172.5°	1710.8	1709.6	1708.4	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4	1710.2
175°	1722.9	1721.7	1720.5	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5	1722.3
177.5°	1729.3	1728.4	1727.4	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4	1727.8
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1140.9	1143.9	1150.1	1147.9	1150.9	1152.4	1153.9
5°	1233.1	1247.9	1254.4	1253.4	1263.1	1260.8	1258.5
7.5°	1337.1	1352.7	1361.4	1372.3	1378.5	1378.9	1384.5
10°	1396.1	1416.4	1424.8	1436.3	1443.7	1447.9	1447.4
12.5°	1441.2	1457.1	1475.9	1481.5	1491.5	1496.7	1494.9
15°	1495.6	1521.1	1540.5	1550.2	1562.7	1566.4	1571.6
17.5°	1544.1	1578.2	1601.0	1631.1	1642.5	1649.5	1645.4
20°	1580.7	1625.7	1648.4	1684.5	1704.4	1715.0	1711.4
22.5°	1624.1	1672.8	1714.7	1746.0	1776.3	1790.6	1793.6
25°	1698.4	1765.1	1826.7	1867.9	1905.3	1914.1	1933.6
27.5°	1781.4	1860.0	1925.8	1969.2	1995.3	2005.1	2011.2
30°	1833.6	1911.8	1961.4	1989.1	1997.5	1996.5	1995.6
32.5°	1859.1	1908.2	1917.6	1909.9	1890.8	1874.7	1857.9
35°	1822.9	1786.4	1731.7	1661.3	1609.4	1557.2	1552.0
37.5°	1639.5	1522.5	1431.6	1330.0	1271.4	1235.2	1210.1
40°	1466.9	1334.0	1223.8	1138.1	1078.3	1054.8	1031.6
42.5°	1279.4	1152.4	1054.9	983.3	938.3	912.1	893.9
45°	1039.5	927.5	851.0	799.2	763.6	743.2	731.6
47.5°	851.8	768.9	704.0	666.6	641.9	626.1	626.2
50°	751.0	671.8	628.7	599.1	577.8	565.3	567.7
52.5°	661.7	602.6	565.8	541.0	525.2	517.5	517.3
55°	553.3	510.7	486.6	468.6	457.9	449.2	451.0
57.5°	473.3	437.4	421.2	406.3	398.9	395.3	390.2
60°	423.7	395.9	382.0	370.0	362.6	359.8	354.6
62.5°	379.6	357.8	344.2	334.4	327.7	326.8	322.8
65°	319.1	302.4	290.3	285.7	278.7	276.9	276.9
67.5°	263.0	251.0	241.7	237.5	234.3	234.9	232.6
70°	227.8	218.1	212.0	207.4	205.1	205.5	203.8
72.5°	199.3	188.4	183.2	180.4	177.4	178.5	177.8
75°	151.0	145.3	142.6	139.8	137.9	137.1	136.2
77.5°	110.8	105.9	103.8	102.3	102.5	100.3	102.0
80°	85.7	81.5	80.1	77.8	77.3	77.3	76.9
82.5°	62.7	60.4	59.4	57.4	56.6	57.3	56.1
85°	32.4	30.6	30.1	30.1	29.2	28.3	30.6
87.5°	17.0	15.9	16.1	16.0	16.1	15.9	15.3
90°	26.0	27.5	28.7	29.6	30.5	31.4	32.3
92.5°	57.5	59.6	60.8	61.5	62.2	62.8	63.5
95°	109.9	111.9	113.2	113.9	114.5	115.0	115.7
97.5°	170.8	172.7	174.0	174.3	174.7	175.0	175.4
100°	213.8	216.5	218.2	218.7	219.4	220.0	220.5
102.5°	257.6	260.5	262.4	263.2	264.0	264.9	265.7
105°	326.8	328.6	329.9	330.8	331.7	332.6	333.5
107.5°	401.8	402.7	403.1	403.1	403.1	403.0	402.9
110°	454.6	455.5	455.8	455.5	455.1	454.9	454.6



TEST NUMBER: P333425-940

CATALOG NUMBER: S125DIW-S850D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	506.9	507.3	507.3	506.8	506.2	505.7	505.2
115°	586.8	586.5	586.2	585.9	585.6	585.3	585.1
117.5°	668.1	668.2	667.8	666.6	665.4	664.2	663.0
120°	722.2	722.2	721.6	720.4	719.2	718.0	716.8
122.5°	775.3	775.0	774.5	773.5	772.5	771.5	770.6
125°	853.5	852.9	852.5	852.2	851.9	851.6	851.3
127.5°	931.9	931.6	931.1	930.5	930.0	929.3	928.7
130°	983.6	983.2	982.8	982.2	981.6	981.0	980.4
132.5°	1033.0	1032.7	1032.2	1031.4	1030.5	1029.7	1028.8
135°	1109.5	1109.5	1108.9	1107.7	1106.5	1105.3	1104.1
137.5°	1184.0	1184.4	1183.8	1182.3	1180.8	1179.3	1177.8
140°	1231.0	1231.5	1231.1	1229.7	1228.2	1226.6	1225.1
142.5°	1276.5	1276.9	1276.3	1274.8	1273.4	1271.8	1270.3
145°	1342.1	1342.1	1341.7	1340.8	1339.9	1339.0	1338.1
147.5°	1404.0	1404.7	1404.1	1402.0	1400.0	1398.0	1396.0
150°	1441.7	1441.7	1441.4	1440.7	1440.2	1439.6	1439.0
152.5°	1478.3	1479.0	1478.8	1477.7	1476.7	1475.6	1474.5
155°	1530.0	1531.2	1531.1	1529.6	1528.0	1526.5	1525.1
157.5°	1574.4	1575.6	1575.2	1573.2	1571.2	1569.2	1567.3
160°	1601.2	1602.5	1602.3	1600.8	1599.3	1597.9	1596.3
162.5°	1626.7	1628.2	1628.0	1626.3	1624.5	1622.8	1621.0
165°	1660.5	1661.6	1661.3	1659.6	1657.8	1656.0	1654.1
167.5°	1686.1	1687.9	1687.9	1686.0	1684.3	1682.4	1680.5
170°	1701.2	1703.0	1702.9	1700.8	1698.7	1696.6	1694.5
172.5°	1712.0	1713.8	1713.8	1711.9	1710.0	1708.2	1706.4
175°	1724.1	1725.9	1725.7	1723.7	1721.5	1719.5	1717.3
177.5°	1729.2	1730.6	1730.5	1728.8	1727.2	1725.5	1723.9
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1

(END OF REPORT)